

## 生産終了予定商品

小形電磁ロック・セーフティドアスイッチ



形D4NL-□□□C-□  
形D4NL-□□□J-□



## 推奨代替商品

小形電磁ロック・セーフティドアスイッチ

形D4NL-□□□A-□  
形D4NL-□□□G-□

### 2012年3月末生産終了予定

#### 推奨代替商品をご利用いただいた場合の注意点

・ソレノイドの定格・仕様が異なります。

### 生産終了予定商品との相違点

形 式	本体 の色	外形 寸法	配線 接続	取付 寸法	定格 性能	動作 特性	操作 方法
形D4NL-□□□A-□ 形D4NL-□□□G-□	◎	◎	◎	◎	×	◎	◎

◎：完全互換

○：ほとんど変更ありません／相似性の高い変更

×：変更大

-：該当する仕様がありません

### 生産終了予定商品と推奨代替商品

生産終了予定商品	推奨代替商品	標準価格(¥)
形D4NL-1AFC-B	形D4NL-1AFA-B	12,400
形D4NL-1BFC-B	形D4NL-1BFA-B	12,400
形D4NL-1CFC-B	形D4NL-1CFA-B	12,400
形D4NL-1DFC-B	形D4NL-1DFA-B	12,400
形D4NL-1EFC-B	形D4NL-1EFA-B	13,500
形D4NL-1FFC-B	形D4NL-1FFA-B	13,500
形D4NL-1GFC-B	形D4NL-1GFA-B	13,500
形D4NL-1HFC-B	形D4NL-1HFA-B	13,500
形D4NL-2AFC-B	形D4NL-2AFA-B	12,400
形D4NL-2BFC-B	形D4NL-2BFA-B	12,400
形D4NL-2CFC-B	形D4NL-2CFA-B	12,400
形D4NL-2DFC-B	形D4NL-2DFA-B	12,400
形D4NL-2EFC-B	形D4NL-2EFA-B	13,500
形D4NL-2FFC-B	形D4NL-2FFA-B	13,500
形D4NL-2GFC-B	形D4NL-2GFA-B	13,500
形D4NL-2HFC-B	形D4NL-2HFA-B	13,500
形D4NL-4AFC-B	形D4NL-4AFA-B	12,400

## 生産終了予定商品と推奨代替商品

\*お問い合わせください

生産終了予定商品	推奨代替商品	標準価格(¥)
形D4NL-4BFC-B	形D4NL-4BFA-B	12,400
形D4NL-4CFC-B	形D4NL-4CFA-B	12,400
形D4NL-4DFC-B	形D4NL-4DFA-B	12,400
形D4NL-4EFC-B	形D4NL-4EFA-B	13,500
形D4NL-4FFC-B	形D4NL-4FFA-B	13,500
形D4NL-4GFC-B	形D4NL-4GFA-B	13,500
形D4NL-4HFC-B	形D4NL-4HFA-B	13,500
形D4NL-1AFC-B4	形D4NL-1AFA-B4	13,000
形D4NL-1BFC-B4	形D4NL-1BFA-B4	13,000
形D4NL-1CFC-B4	形D4NL-1CFA-B4	13,000
形D4NL-1DFC-B4	形D4NL-1DFA-B4	13,000
形D4NL-1EFC-B4	形D4NL-1EFA-B4	14,000
形D4NL-1FFC-B4	形D4NL-1FFA-B4	14,000
形D4NL-1GFC-B4	形D4NL-1GFA-B4	14,000
形D4NL-1HFC-B4	形D4NL-1HFA-B4	14,000
形D4NL-2AFC-B4	形D4NL-2AFA-B4	13,000
形D4NL-2BFC-B4	形D4NL-2BFA-B4	13,000
形D4NL-2CFC-B4	形D4NL-2CFA-B4	13,000
形D4NL-2DFC-B4	形D4NL-2DFA-B4	13,000
形D4NL-2EFC-B4	形D4NL-2EFA-B4	14,000
形D4NL-2FFC-B4	形D4NL-2FFA-B4	14,000
形D4NL-2GFC-B4	形D4NL-2GFA-B4	14,000
形D4NL-2HFC-B4	形D4NL-2HFA-B4	14,000
形D4NL-4AFC-B4	形D4NL-4AFA-B4	13,000
形D4NL-4BFC-B4	形D4NL-4BFA-B4	13,000
形D4NL-4CFC-B4	形D4NL-4CFA-B4	13,000
形D4NL-4DFC-B4	形D4NL-4DFA-B4	13,000
形D4NL-4EFC-B4	形D4NL-4EFA-B4	14,000
形D4NL-4FFC-B4	形D4NL-4FFA-B4	14,000
形D4NL-4GFC-B4	形D4NL-4GFA-B4	14,000
形D4NL-4HFC-B4	形D4NL-4HFA-B4	14,000
形D4NL-1AFC-BS	形D4NL-1AFA-BS	12,400
形D4NL-1BFC-BS	形D4NL-1BFA-BS	*
形D4NL-1CFC-BS	形D4NL-1CFA-BS	12,400
形D4NL-1DFC-BS	形D4NL-1DFA-BS	12,400
形D4NL-1EFC-BS	形D4NL-1EFA-BS	13,500
形D4NL-1FFC-BS	形D4NL-1FFA-BS	13,500
形D4NL-1GFC-BS	形D4NL-1GFA-BS	*
形D4NL-1HFC-BS	形D4NL-1HFA-BS	14,500
形D4NL-2AFC-BS	形D4NL-2AFA-BS	12,400
形D4NL-2BFC-BS	形D4NL-2BFA-BS	12,400
形D4NL-2CFC-BS	形D4NL-2CFA-BS	12,400

## 生産終了予定商品と推奨代替商品

\*お問い合わせください

生産終了予定商品	推奨代替商品	標準価格(¥)
形D4NL-2DFC-BS	形D4NL-2DFA-BS	12,400
形D4NL-2EFC-BS	形D4NL-2EFA-BS	13,500
形D4NL-2FFC-BS	形D4NL-2FFA-BS	13,500
形D4NL-2GFC-BS	形D4NL-2GFA-BS	*
形D4NL-2HFC-BS	形D4NL-2HFA-BS	13,500
形D4NL-4AFC-BS	形D4NL-4AFA-BS	12,400
形D4NL-4BFC-BS	形D4NL-4BFA-BS	*
形D4NL-4CFC-BS	形D4NL-4CFA-BS	12,400
形D4NL-4DFC-BS	形D4NL-4DFA-BS	12,400
形D4NL-4EFC-BS	形D4NL-4EFA-BS	13,500
形D4NL-4FFC-BS	形D4NL-4FFA-BS	13,500
形D4NL-4GFC-BS	形D4NL-4GFA-BS	*
形D4NL-4HFC-BS	形D4NL-4HFA-BS	13,500
形D4NL-1AFC-B4S	形D4NL-1AFA-B4S	*
形D4NL-1BFC-B4S	形D4NL-1BFA-B4S	*
形D4NL-1CFC-B4S	形D4NL-1CFA-B4S	*
形D4NL-1DFC-B4S	形D4NL-1DFA-B4S	13,000
形D4NL-1EFC-B4S	形D4NL-1EFA-B4S	*
形D4NL-1FFC-B4S	形D4NL-1FFA-B4S	*
形D4NL-1GFC-B4S	形D4NL-1GFA-B4S	*
形D4NL-1HFC-B4S	形D4NL-1HFA-B4S	14,000
形D4NL-2AFC-B4S	形D4NL-2AFA-B4S	13,000
形D4NL-2BFC-B4S	形D4NL-2BFA-B4S	*
形D4NL-2CFC-B4S	形D4NL-2CFA-B4S	13,000
形D4NL-2DFC-B4S	形D4NL-2DFA-B4S	12,800
形D4NL-2EFC-B4S	形D4NL-2EFA-B4S	*
形D4NL-2FFC-B4S	形D4NL-2FFA-B4S	14,000
形D4NL-2GFC-B4S	形D4NL-2GFA-B4S	*
形D4NL-2HFC-B4S	形D4NL-2HFA-B4S	14,000
形D4NL-4AFC-B4S	形D4NL-4AFA-B4S	13,000
形D4NL-4BFC-B4S	形D4NL-4BFA-B4S	*
形D4NL-4CFC-B4S	形D4NL-4CFA-B4S	13,000
形D4NL-4DFC-B4S	形D4NL-4DFA-B4S	*
形D4NL-4EFC-B4S	形D4NL-4EFA-B4S	*
形D4NL-4FFC-B4S	形D4NL-4FFA-B4S	14,000
形D4NL-4GFC-B4S	形D4NL-4GFA-B4S	*
形D4NL-4HFC-B4S	形D4NL-4HFA-B4S	14,000
形D4NL-1AFJ-B	形D4NL-1AFJ-B	13,300
形D4NL-1BFJ-B	形D4NL-1BFJ-B	13,300
形D4NL-1CFJ-B	形D4NL-1CFJ-B	13,300
形D4NL-1DFJ-B	形D4NL-1DFJ-B	13,300
形D4NL-1EFJ-B	形D4NL-1EFJ-B	14,300

## 生産終了予定商品と推奨代替商品

生産終了予定商品	推奨代替商品	標準価格(¥)
形D4NL-1FFJ-B	形D4NL-1FFG-B	14,300
形D4NL-1GFJ-B	形D4NL-1GFG-B	14,300
形D4NL-1HFJ-B	形D4NL-1HFG-B	14,300
形D4NL-2AFJ-B	形D4NL-2AFG-B	13,300
形D4NL-2BFJ-B	形D4NL-2BFG-B	13,300
形D4NL-2CFJ-B	形D4NL-2CFG-B	13,300
形D4NL-2DFJ-B	形D4NL-2DFG-B	13,300
形D4NL-2EFJ-B	形D4NL-2EFG-B	14,300
形D4NL-2FFJ-B	形D4NL-2FFG-B	14,300
形D4NL-2GFJ-B	形D4NL-2GFG-B	14,300
形D4NL-2HFJ-B	形D4NL-2HFG-B	14,300
形D4NL-4AFJ-B	形D4NL-4AFG-B	13,300
形D4NL-4BFJ-B	形D4NL-4BFG-B	13,300
形D4NL-4CFJ-B	形D4NL-4CFG-B	13,300
形D4NL-4DFJ-B	形D4NL-4DFG-B	13,300
形D4NL-4EFJ-B	形D4NL-4EFG-B	14,300
形D4NL-4FFJ-B	形D4NL-4FFG-B	14,300
形D4NL-4GFJ-B	形D4NL-4GFG-B	14,300
形D4NL-4HFJ-B	形D4NL-4HFG-B	14,300
形D4NL-1AFJ-B4	形D4NL-1AFG-B4	13,800
形D4NL-1BFJ-B4	形D4NL-1BFG-B4	13,800
形D4NL-1CFJ-B4	形D4NL-1CFG-B4	13,800
形D4NL-1DFJ-B4	形D4NL-1DFG-B4	13,800
形D4NL-1EFJ-B4	形D4NL-1EFG-B4	14,800
形D4NL-1FFJ-B4	形D4NL-1FFG-B4	14,800
形D4NL-1GFJ-B4	形D4NL-1GFG-B4	14,800
形D4NL-1HFJ-B4	形D4NL-1HFG-B4	14,800
形D4NL-2AFJ-B4	形D4NL-2AFG-B4	13,800
形D4NL-2BFJ-B4	形D4NL-2BFG-B4	13,800
形D4NL-2CFJ-B4	形D4NL-2CFG-B4	13,800
形D4NL-2DFJ-B4	形D4NL-2DFG-B4	13,800
形D4NL-2EFJ-B4	形D4NL-2EFG-B4	14,800
形D4NL-2FFJ-B4	形D4NL-2FFG-B4	14,800
形D4NL-2GFJ-B4	形D4NL-2GFG-B4	14,800
形D4NL-2HFJ-B4	形D4NL-2HFG-B4	14,800
形D4NL-4AFJ-B4	形D4NL-4AFG-B4	13,800
形D4NL-4BFJ-B4	形D4NL-4BFG-B4	13,800
形D4NL-4CFJ-B4	形D4NL-4CFG-B4	13,800
形D4NL-4DFJ-B4	形D4NL-4DFG-B4	13,800
形D4NL-4EFJ-B4	形D4NL-4EFG-B4	14,800
形D4NL-4FFJ-B4	形D4NL-4FFG-B4	14,800
形D4NL-4GFJ-B4	形D4NL-4GFG-B4	14,800

## 生産終了予定商品と推奨代替商品

\*お問い合わせください

生産終了予定商品	推奨代替商品	標準価格(¥)
形D4NL-4HFJ-B4	形D4NL-4HFG-B4	14,800
形D4NL-1AFJ-BS	形D4NL-1AFG-BS	13,300
形D4NL-1BFJ-BS	形D4NL-1BFG-BS	*
形D4NL-1CFJ-BS	形D4NL-1CFG-BS	13,500
形D4NL-1DFJ-BS	形D4NL-1DFG-BS	13,500
形D4NL-1EFJ-BS	形D4NL-1EFG-BS	*
形D4NL-1FFJ-BS	形D4NL-1FFG-BS	*
形D4NL-1GFJ-BS	形D4NL-1GFG-BS	*
形D4NL-1HFJ-BS	形D4NL-1HFG-BS	14,300
形D4NL-2AFJ-BS	形D4NL-2AFG-BS	13,300
形D4NL-2BFJ-BS	形D4NL-2BFG-BS	*
形D4NL-2CFJ-BS	形D4NL-2CFG-BS	13,300
形D4NL-2DFJ-BS	形D4NL-2DFG-BS	12,400
形D4NL-2EFJ-BS	形D4NL-2EFG-BS	14,300
形D4NL-2FFJ-BS	形D4NL-2FFG-BS	14,300
形D4NL-2GFJ-BS	形D4NL-2GFG-BS	14,300
形D4NL-2HFJ-BS	形D4NL-2HFG-BS	14,300
形D4NL-4AFJ-BS	形D4NL-4AFG-BS	13,300
形D4NL-4BFJ-BS	形D4NL-4BFG-BS	*
形D4NL-4CFJ-BS	形D4NL-4CFG-BS	*
形D4NL-4DFJ-BS	形D4NL-4DFG-BS	*
形D4NL-4EFJ-BS	形D4NL-4EFG-BS	*
形D4NL-4FFJ-BS	形D4NL-4FFG-BS	14,300
形D4NL-4GFJ-BS	形D4NL-4GFG-BS	*
形D4NL-4HFJ-BS	形D4NL-4HFG-BS	*
形D4NL-1AFJ-B4S	形D4NL-1AFG-B4S	13,800
形D4NL-1BFJ-B4S	形D4NL-1BFG-B4S	*
形D4NL-1CFJ-B4S	形D4NL-1CFG-B4S	*
形D4NL-1DFJ-B4S	形D4NL-1DFG-B4S	*
形D4NL-1EFJ-B4S	形D4NL-1EFG-B4S	*
形D4NL-1FFJ-B4S	形D4NL-1FFG-B4S	*
形D4NL-1GFJ-B4S	形D4NL-1GFG-B4S	*
形D4NL-1HFJ-B4S	形D4NL-1HFG-B4S	*
形D4NL-2AFJ-B4S	形D4NL-2AFG-B4S	13,800
形D4NL-2BFJ-B4S	形D4NL-2BFG-B4S	*
形D4NL-2CFJ-B4S	形D4NL-2CFG-B4S	*
形D4NL-2DFJ-B4S	形D4NL-2DFG-B4S	13,800
形D4NL-2EFJ-B4S	形D4NL-2EFG-B4S	*
形D4NL-2FFJ-B4S	形D4NL-2FFG-B4S	15,600
形D4NL-2GFJ-B4S	形D4NL-2GFG-B4S	*
形D4NL-2HFJ-B4S	形D4NL-2HFG-B4S	14,800
形D4NL-4AFJ-B4S	形D4NL-4AFG-B4S	13,800

**生産終了予定商品と推奨代替商品**

\*お問い合わせください

生産終了予定商品	推奨代替商品	標準価格(¥)
形D4NL-4BFJ-B4S	形D4NL-4BFG-B4S	*
形D4NL-4CFJ-B4S	形D4NL-4CFG-B4S	*
形D4NL-4DFJ-B4S	形D4NL-4DFG-B4S	*
形D4NL-4EFJ-B4S	形D4NL-4EFG-B4S	*
形D4NL-4FFJ-B4S	形D4NL-4FFG-B4S	14,800
形D4NL-4GFJ-B4S	形D4NL-4GFG-B4S	*
形D4NL-4HFJ-B4S	形D4NL-4HFG-B4S	*

**定格/性能**

●ソレノイド定格・特性

項目	生産終了予定商品 形D4NL-□□□C-□ 形D4NL-□□□J-□	推奨代替商品 形D4NL-□□□A-□ 形D4NL-□□□G-□
定格作動電圧(100%ED)	AC230V ± 10%	DC24V +10%/ - 15%
消費電流	約30mA	約200mA
絶縁クラス	Class F (~130°C)	Class F (~130°C)

2011年9月現在

お断りなく仕様・標準価格などを変更することがありますので、ご了承ください。