

生産終了商品

多軸モーションコントローラ

3-3958A-00-111M-□000



3-3958A-00-211M-□000

3-3958A-00-311M-□000

3-3958A-00-511M-□000

推奨代替商品

多軸モーションコントローラ

3-3958A-00-121M-□000

(2023年8月発売予定)

3-3958A-00-221M-□000

(2023年8月発売予定)

推奨代替商品なし

■最終受注年月

2023年9月末

■最終出荷年月

2023年12月末

■修理対応終了年月

2026年12月末

■推奨代替商品をご利用いただいた場合の注意点

- ・推奨代替商品「3-3958A-00-□21M-□000」は2023年8月に発売予定です。
- ・設定項目に互換性がないため、設定ツールを用いて再度設定を行う必要があります。

■生産終了商品との相違点

推奨代替商品形式	本体の色	外形寸法	配線接続	取付寸法	定格性能	動作特性	操作方法
3-3958A-00-□21M-□000	◎	◎	◎	◎	◎	◎	○

◎：互換

○：ほとんど変更ありません／相似性の高い変更

×：変更大

—：該当する仕様がありません

■生産終了商品と推奨代替商品

生産終了商品	推奨代替商品	標準価格(¥)
3-3958A-00-111M-B000	3-3958A-00-121M-B000	オープン価格
3-3958A-00-111M-F000	3-3958A-00-121M-F000	オープン価格
3-3958A-00-211M-B000	3-3958A-00-221M-B000	オープン価格
3-3958A-00-211M-F000	3-3958A-00-221M-F000	オープン価格
3-3958A-00-311M-B000	推奨代替商品はありません。	—
3-3958A-00-311M-F000	推奨代替商品はありません。	—
3-3958A-00-511M-B000	推奨代替商品はありません。	—
3-3958A-00-511M-F000	推奨代替商品はありません。	—

■操作方法

推奨代替商品「3-3958A-00-□21M-□000」をご使用の際に、Sycon software V1.0500.230227.42617 以上のバージョンを推奨します。

本案内に記載の仕様・価格は、発行時点のものです。予告なく変更することがありますので、ご了承ください。
 本案内では主に仕様上の変更点を記載しています。ご使用上の注意事項等、ご使用の際に必要な内容につきましては、必ずカタログ、仕様書、取扱説明書、マニュアル等をお読みください。

参考資料:

From ACC-72EXシリーズ 3-3958A-00-□11M-□000

(E) (F) (G) (H) (I) (K) (L)

UMAC ACC-72EX

3	-	3	9	5	8	A	-	0	0	-					-				0		
---	---	---	---	---	---	---	---	---	---	---	--	--	--	--	---	--	--	--	---	--	--

(E) (F) (G)

110 - PROFIBUS-DP Master
111 - PROFIBUS-DP Slave
210 - DeviceNet Master
211 - DeviceNet Slave
310 - CanOpen Master
311 - CanOpen Slave
511 - CC-Link Slave
610 - EtherCAT Master
611 - EtherCAT Slave
710 - EtherNet/IP Scanner
711 - EtherNet/IP Adapter
810 - Open MODBUS/TCP
910 - PROFINET IO RT-Controller
911 - PROFINET IO RT-Device

(H)

0 - No COMX gateway Module (Carrier)
M - COMX gateway Module

FieldBus Options

(I)

B - BLACK Front, top and bottom plates (Standard)
F - BLACK Front plate only Order as Spare Only

Plate Options

(K) (L)

00 - No Additional* Options
xx - Factory assigned digits for Additional* Options

Factory Assigned Options

* If Any Additional Option is required, contact factory for digits **K** and **L** (Factory Assigned digits).

To ACC-72EX シリーズ 3-3958A-00-□21M-□000

(E) (F) (G) (H) (I) (K) (L)

UMAC ACC-72EX

3	-	3	9	5	8	A	-	0	0	-					-				0		
---	---	---	---	---	---	---	---	---	---	---	--	--	--	--	---	--	--	--	---	--	--

(E) (F) (G)

110 - PROFIBUS-DP Master
121 - PROFIBUS-DP Slave
210 - DeviceNet Master
221 - DeviceNet Slave
310 - CanOpen Master
610 - EtherCAT Master
611 - EtherCAT Slave
710 - EtherNet/IP Scanner
711 - EtherNet/IP Adapter
810 - Open MODBUS/TCP
910 - PROFINET IO RT-Controller
911 - PROFINET IO RT-Device

(H)

0 - No COMX gateway Module (Carrier)
M - COMX gateway Module

FieldBus Options

(I)

B - BLACK Front, top and bottom plates (Standard)
F - BLACK Front plate only Order as Spare Only

Plate Options

(K) (L)

00 - No Additional* Options
xx - Factory assigned digits for Additional* Options

Factory Assigned Options

* If Any Additional Option is required, contact factory for digits **K** and **L** (Factory Assigned digits).