

Safety Multi-Light Beam

# F3SG-4PGA0970-3A



# 商品概要

Safety Multi-Light Beam, Advanced, Perimeter access guarding, Standard, 3 beams, Beam gap: 400 mm

## 販売状況

2026/05/15 00:00 情報更新

販売状況	販売中
機種区分	標準在庫機種
標準価格(税別)	¥ 113,000

推奨代替品の最新情報につきましては、当社Webサイト([www.fa.omron.co.jp](http://www.fa.omron.co.jp))の「生産終了品/推奨代替品」をご覧ください。  
在庫状況/標準価格の最新情報につきましては、当社Webサイト([www.fa.omron.co.jp](http://www.fa.omron.co.jp))の「在庫状況/標準価格照会」をご覧ください。

# 詳細情報

## 定格/性能

情報更新：2025/08/19

# RoHS/REACH対応状況

情報更新：2026/5/13

## EU RoHS

対応状況 ※1	対応予定月 ※2	非含有証明書 ※3
 対応済み		<a href="#">ダウンロードはこちら</a>

## 中国 RoHS

中国 RoHS表 ※1※2										
Pb	Hg	Cd	Cr(VI)	PBBs	PBDEs	DBP	DIBP	BBP	DEHP	環境保護 使用期限
X	0	0	0	0	0	0	0	0	0	10

- ・“対応済み”や非含有の記載がされた商品であっても、流通在庫等で未対応品が混在する可能性があります。
- ・非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

[この製品のRoHS/REACH対応状況ページへ>](#)

## 注意事項・凡例

”対応済み”で記載される商品であっても、流通在庫等で未対応品が混在する可能性があります。  
非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

### ※1 対応状況

- ・  対応済み : EU RoHS指令（10物質）の非含有に対応した製品が提供可能な商品です。
- ・ 対応予定 : EU RoHS指令（10物質）の非含有に対応した製品に切り替える予定のある商品です。
- ・ 対応予定なし : EU RoHS指令（10物質）の非含有に非対応の商品で、対応品を出す予定はありません。
- ・ 調査・確認中 : EU RoHS指令（10物質）の非含有の対応状況を調査中または確認中の商品です。
- ・ 非該当品 : ライセンス料など無形物で、有害物質有無と関係のない商品です。

仕入先様の事情により、非含有部品としていたものが、含有品と判明した場合などやむを得ず変更することがあります。

\* EU RoHS指令（10物質）：

鉛(Pb) 1000ppm以下、水銀(Hg) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、  
ポリ臭化ビフェニル類(PBB) 1000ppm以下、ポリ臭化ジフェニルエーテル類(PBDE) 1000ppm以下、  
フタル酸ビス(2-エチルヘキシル) (DEHP)(別名：DOP) 1000ppm以下、フタル酸ブチルベンジル (BBP) 1000ppm以下、  
フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジイソブチル (DIBP) 1000ppm以下  
但し、RoHS指令で産業用監視および制御機器に対する適用除外項目は除く。  
フタル酸エステル類の4物質については閾値を超える意図的な使用がないことを確認しています。

### ※2 対応予定月

部品在庫の切り替え状況などにより、予定月が前後することがあります。

### ※3 非含有証明書ダウンロード

下記の非含有証明書をダウンロードすることができます。

- ・ EU RoHS指令（10物質）の非含有証明書
- ・ 49物質の非含有証明書（当社基準）

※ 本証明書は発行日時時点で非含有を証明するもので、過去に遡って非含有を証明するものではありません。

また、RoHS指令のフタル酸エステル類4物質の対応では、対応完了までの期間は出荷製品に未対応品が混在することから備考欄に  
対応日を記載しておりました。

既に当社にて対応品への在庫切替を完了していることから、特段のことがない限り、2022年1月12日より割愛しております。

## 規格認証/適合状況

UL認証	CSA認証	CEマーキング	CCC認証	電波法
Yes	Yes	Yes	N/A	N/A

LR型式承認 (イギリス 船舶規格)	DNV型式承認 (ノルウェー 船舶規格)	BV型式承認 (フランス 船舶規格)	KR型式承認 (韓国 船舶規格)	NK型式承認 (日本 船舶規格)	ABS型式承認 (アメリカ 船舶規格)
No	No	No	No	No	No

[この製品の規格認証/適合状況ページへ>](#)  
[その他の認証はこちらのページからご検索ください>](#)

## 関連商品



Reflector  
E39-R1S



Muting Sensor Arm Mounter  
F39-FMA400R



Muting Sensor Connection Box  
F39-GCN5



Y-Joint Plug/Socket Connector  
F39-GCNY2



Single-Ended Cable  
F39-JG10A-D



Single-Ended Cable  
F39-JG10A-L



Double-Ended Cable  
F39-JG10B-D



Double-Ended Cable  
F39-JG10B-L



Root-Straight Cable  
F39-JG10C-D



Root-Straight Cable

F39-JG10C-L



Extension Cable (Double ended cable)

F39-JG20B-D



Extension Cable (Double ended cable)

F39-JG20B-L



Extension Cable (Single ended cable)

F39-JG3A-D



Extension Cable (Single ended cable)

F39-JG3A-L



Extension Cable (Double ended cable)

F39-JG3B-D



Extension Cable (Double ended cable)

F39-JG3B-L



Root-Straight Cable

F39-JG3C-D



Root-Straight Cable

F39-JG3C-L



Root-Straight Cable

F39-JG7C-D



Root-Straight Cable

F39-JG7C-L



Root-Plug Cable for Extended

F39-JGR3K-D



Root-Plug Cable for Extended

F39-JGR3K-L



Root Cable

F39-JGR3K-RE-D



Root Cable

F39-JGR3K-RE-L



Conversion Cable

F39-JGR3K-SJ-D



Conversion Cable

F39-JGR3K-SJ-L




Intelligent Tap Bracket for DIN in Panel


F39-LITF1



Muting Sensor Arm Mounter Bracket  
for SLC (Two brackets per set)  
F39-LMAF1



Adjustable Side-Mount Bracket  
(Intermediate Bracket)  
F39-LSGA



Side-Mount Bracket (Intermediate  
Bracket)  
F39-LSGF



Adjustable Top/Bottom Bracket  
F39-LSGTB-MS



Adjustable Top/Bottom Bracket  
F39-LSGTB-RE



Adjustable Top/Bottom Bracket  
F39-LSGTB-SJ



Laser Pointer  
F39-PTS



Bluetooth Communication Unit  
F39-SGBT




Intelligent Tap  
F39-SGIT-IL3



Lamp  
F39-SGLP



Floor Mount Column  
F39-ST1310



Mount-Column Adjustable Base  
F39-STB



Round Water-resistant Connector  
XS3W-M421-401-R



Round Water-resistant Connector  
XS3W-M421-402-R



Round Water-resistant Connector  
XS3W-M421-405-R



Round Water-resistant Connector  
XS3W-M421-410-R




Round Water-resistant Connector  
XS3W-M424-402-R



Round Water-resistant Connector  
XS3W-M424-405-R



Round Water-resistant Connector  
[XS3W-M42C-4C2-A](#)



Round Water-resistant Connector  
(M12 Smartclick)  
[XS5F-D421-C80-F](#)



Round Water-resistant Connector  
(M12 Smartclick)  
[XS5F-D421-D80-F](#)



Round Water-resistant Connector  
(M12 Smartclick)  
[XS5F-D421-G80-F](#)



Round Water-resistant Connector  
(M12 Smartclick)  
[XS5F-D421-J80-F](#)



Round Water-resistant Connector  
(M12 Smartclick)  
[XS5F-D421-L80-F](#)



Intelligent Tap-to-IO-Link Master  
Cable (Single ended cable)  
[XS5F-D521-DJ0-IL](#)