

カタログ訂正のお知らせ

当社発行のカタログにおいて下記のとおり印刷・記載の誤りがありました。  
お詫び申し上げます。

■カタログ名

『形3Z4L V2 レーザマイクロメータ 単品カタログ』 (2007年5月発行) (カタログ番号SCHA-001B)

■掲載箇所

7ページ 『定格／性能』の『測定値平均回数／測定間隔』

■正誤内容

誤	正																																																																																																						
<p>【7ページ】 測定値平均回数1、2、4回を削除します。</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th rowspan="3">測定値 平均回数</th> <th colspan="3">測定間隔</th> </tr> <tr> <th rowspan="2">単純平均</th> <th colspan="2">移動平均</th> </tr> <tr> <th>1回目の測定</th> <th>2回目以降</th> </tr> </thead> <tbody> <tr><td>1</td><td>0.6ms</td><td>—</td><td>—</td></tr> <tr><td>2</td><td>1.3ms</td><td>—</td><td>—</td></tr> <tr><td>4</td><td>2.5ms</td><td>—</td><td>—</td></tr> <tr><td>8</td><td>5ms</td><td>—</td><td>—</td></tr> <tr><td>16</td><td>10ms</td><td>—</td><td>—</td></tr> <tr><td>32</td><td>20ms</td><td>20ms</td><td>10ms</td></tr> <tr><td>64</td><td>40ms</td><td>40ms</td><td>10ms</td></tr> <tr><td>128</td><td>80ms</td><td>80ms</td><td>10ms</td></tr> <tr><td>256</td><td>160ms</td><td>160ms</td><td>10ms</td></tr> <tr><td>512</td><td>0.32s</td><td>0.32s</td><td>10ms</td></tr> <tr><td>1,024</td><td>0.64s</td><td>0.64s</td><td>10ms</td></tr> <tr><td>2,048</td><td>1.28s</td><td>1.28s</td><td>10ms</td></tr> </tbody> </table>	測定値 平均回数	測定間隔			単純平均	移動平均		1回目の測定	2回目以降	1	0.6ms	—	—	2	1.3ms	—	—	4	2.5ms	—	—	8	5ms	—	—	16	10ms	—	—	32	20ms	20ms	10ms	64	40ms	40ms	10ms	128	80ms	80ms	10ms	256	160ms	160ms	10ms	512	0.32s	0.32s	10ms	1,024	0.64s	0.64s	10ms	2,048	1.28s	1.28s	10ms	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th rowspan="3">測定値 平均回数</th> <th colspan="3">測定間隔</th> </tr> <tr> <th rowspan="2">単純平均</th> <th colspan="2">移動平均</th> </tr> <tr> <th>1回目の測定</th> <th>2回目以降</th> </tr> </thead> <tbody> <tr><td>8</td><td>5ms</td><td>—</td><td>—</td></tr> <tr><td>16</td><td>10ms</td><td>—</td><td>—</td></tr> <tr><td>32</td><td>20ms</td><td>20ms</td><td>10ms</td></tr> <tr><td>64</td><td>40ms</td><td>40ms</td><td>10ms</td></tr> <tr><td>128</td><td>80ms</td><td>80ms</td><td>10ms</td></tr> <tr><td>256</td><td>160ms</td><td>160ms</td><td>10ms</td></tr> <tr><td>512</td><td>0.32s</td><td>0.32s</td><td>10ms</td></tr> <tr><td>1,024</td><td>0.64s</td><td>0.64s</td><td>10ms</td></tr> <tr><td>2,048</td><td>1.28s</td><td>1.28s</td><td>10ms</td></tr> </tbody> </table>	測定値 平均回数	測定間隔			単純平均	移動平均		1回目の測定	2回目以降	8	5ms	—	—	16	10ms	—	—	32	20ms	20ms	10ms	64	40ms	40ms	10ms	128	80ms	80ms	10ms	256	160ms	160ms	10ms	512	0.32s	0.32s	10ms	1,024	0.64s	0.64s	10ms	2,048	1.28s	1.28s	10ms
測定値 平均回数		測定間隔																																																																																																					
		単純平均	移動平均																																																																																																				
	1回目の測定		2回目以降																																																																																																				
1	0.6ms	—	—																																																																																																				
2	1.3ms	—	—																																																																																																				
4	2.5ms	—	—																																																																																																				
8	5ms	—	—																																																																																																				
16	10ms	—	—																																																																																																				
32	20ms	20ms	10ms																																																																																																				
64	40ms	40ms	10ms																																																																																																				
128	80ms	80ms	10ms																																																																																																				
256	160ms	160ms	10ms																																																																																																				
512	0.32s	0.32s	10ms																																																																																																				
1,024	0.64s	0.64s	10ms																																																																																																				
2,048	1.28s	1.28s	10ms																																																																																																				
測定値 平均回数	測定間隔																																																																																																						
	単純平均	移動平均																																																																																																					
		1回目の測定	2回目以降																																																																																																				
8	5ms	—	—																																																																																																				
16	10ms	—	—																																																																																																				
32	20ms	20ms	10ms																																																																																																				
64	40ms	40ms	10ms																																																																																																				
128	80ms	80ms	10ms																																																																																																				
256	160ms	160ms	10ms																																																																																																				
512	0.32s	0.32s	10ms																																																																																																				
1,024	0.64s	0.64s	10ms																																																																																																				
2,048	1.28s	1.28s	10ms																																																																																																				

■対応方法

シール対応いたします。