

高解像度・低ディストーションレンズ 形FZ-LEHシリーズ 生産終了のお知らせ

生産終了予定商品

低ディストーションレンズ

形FZ-LEH5
形FZ-LEH8
形FZ-LEH12
形FZ-LEH16
形FZ-LEH25
形FZ-LEH35
形FZ-LEH50



推奨代替商品

低ディストーションレンズ

形3Z4S-LE SV-0614H
形3Z4S-LE SV-0814H
形3Z4S-LE SV-1214H
形3Z4S-LE SV-1614H
形3Z4S-LE SV-2514H
形3Z4S-LE SV-3514H
形3Z4S-LE SV-5014H

■生産終了予定時期

2013年3月末

■推奨代替商品をご利用いただいた場合の注意点

外形寸法に若干の違いがございますので、取付けの際はご注意ください。

形FZ-LEH5 焦点距離5mmの代替は、焦点距離6mmの形3Z4S-LE SV-0614Hとなります。

焦点距離が異なるため、カメラ設置距離が変わりますので、ご注意ください。

■生産終了予定商品との相違点

推奨代替商品形式	本体の色	外形寸法	配線接続	取付寸法	定格性能	動作特性	操作方法
形3Z4S-LE SV-0614H	○	○	—	◎	○	—	◎
形3Z4S-LE SV-0814H	○	○	—	◎	○	—	◎
形3Z4S-LE SV-1214H	○	○	—	◎	○	—	◎
形3Z4S-LE SV-1614H	○	○	—	◎	○	—	◎
形3Z4S-LE SV-2514H	○	○	—	◎	○	—	◎
形3Z4S-LE SV-3514H	○	○	—	◎	○	—	◎
形3Z4S-LE SV-5014H	○	○	—	◎	○	—	◎

◎：完全互換

○：ほとんど変更ありません／相似性の高い変更

×：変更大

—：該当する仕様がありません



■生産終了予定商品と推奨代替商品

生産終了予定商品	推奨代替商品	標準価格(¥)
形FZ-LEH5	形3Z4S-LE SV-0614H	39,000
形FZ-LEH8	形3Z4S-LE SV-0814H	28,000
形FZ-LEH12	形3Z4S-LE SV-1214H	24,000
形FZ-LEH16	形3Z4S-LE SV-1614H	21,000
形FZ-LEH25	形3Z4S-LE SV-2514H	20,000
形FZ-LEH35	形3Z4S-LE SV-3514H	39,000
形FZ-LEH50	形3Z4S-LE SV-5014H	39,000

■本体の色

生産終了予定商品 形FZ-LEHシリーズ	推奨代替商品 形3Z4S-LE SV-Hシリーズ
 <p>代表:FZ-LEH16</p>	<p>現状同等</p> 



■外形寸法



生産終了予定商品 形FZ-LEH5	推奨代替商品 形3Z4S-LE SV-0614H
	



<p>生産終了予定商品 形FZ-LEH8</p>	<p>推奨代替商品 形3Z4S-LE SV-0814H</p>

<p>生産終了予定商品 形FZ-LEH12</p>	<p>推奨代替商品 形3Z4S-LE SV-1214H</p>

<p>生産終了予定商品 形FZ-LEH16</p>	<p>推奨代替商品 形3Z4S-LE SV-1614H</p>

<p>生産終了予定商品 形FZ-LEH25</p>	<p>推奨代替商品 形3Z4S-LE SV-2514H</p>
 <p>Technical drawing of the discontinued product FZ-LEH25. It shows a cylindrical component with a total length of 39.5 mm and a mounting section length of 17.526 mm. The diameter is $\phi 33$. The drawing includes dimensions for the main body (28.5 mm), a section with a diameter of 28 mm and length 1.4 mm, a section with a diameter of 28 mm and length 2.8 mm, a section with a diameter of 28 mm and length 0.5 mm, and a section with a diameter of 28 mm and length 1 mm. The mounting section has a diameter of 22.5 mm and a thread of 1-32UNF. The mounting type is C-Mount.</p>	 <p>Technical drawing of the recommended replacement product 3Z4S-LE SV-2514H. It shows a cylindrical component with a total length of 36 mm and a mounting section length of 17.526 mm. The diameter is $\phi 30$. The drawing includes dimensions for the main body (28.5 mm), a section with a diameter of 28 mm and length 0.5 mm, a section with a diameter of 28 mm and length 2 mm, a section with a diameter of 28 mm and length 1.4 mm, and a section with a diameter of 28 mm and length 1 mm. The mounting section has a diameter of 22.5 mm and a thread of 2-M1.7 Lock screw. The mounting type is C-mount.</p>

<p>生産終了予定商品 形FZ-LEH35</p>	<p>推奨代替商品 形3Z4S-LE SV-3514H</p>
 <p>Technical drawing of the discontinued product FZ-LEH35. It shows a cylindrical component with a total length of 36.5 mm and a mounting section length of 17.526 mm. The diameter is $\phi 34$. The drawing includes dimensions for the main body (29 mm), a section with a diameter of 29 mm and length 2.0 mm, a section with a diameter of 29 mm and length 2.8 mm, a section with a diameter of 29 mm and length 0.5 mm, and a section with a diameter of 29 mm and length 1 mm. The mounting section has a diameter of 22.5 mm and a thread of 1-32UNF. The mounting type is C-Mount.</p>	 <p>Technical drawing of the recommended replacement product 3Z4S-LE SV-3514H. It shows a cylindrical component with a total length of 45.5 mm and a mounting section length of 17.526 mm. The diameter is $\phi 44$. The drawing includes dimensions for the main body (37 mm), a section with a diameter of 37 mm and length 0.5 mm, a section with a diameter of 37 mm and length 35 mm, a section with a diameter of 37 mm and length 1 mm, and a section with a diameter of 37 mm and length 1 mm. The mounting section has a diameter of 22.5 mm and a thread of 2-M1.7 Lock screw. The mounting type is C-mount.</p>

<p>生産終了予定商品 形FZ-LEH50</p>	<p>推奨代替商品 形3Z4S-LE SV-5014H</p>
 <p>Technical drawing of the discontinued product FZ-LEH50. It shows a cylindrical component with a total length of 55 mm and a mounting section length of 17.526 mm. The diameter is $\phi 34$. The drawing includes dimensions for the main body (28.5 mm), a section with a diameter of 28 mm and length 2.8 mm, a section with a diameter of 28 mm and length 1.4 mm, a section with a diameter of 28 mm and length 0.5 mm, and a section with a diameter of 28 mm and length 1 mm. The mounting section has a diameter of 22.5 mm and a thread of 1-32UNF. The mounting type is C-Mount.</p>	 <p>Technical drawing of the recommended replacement product 3Z4S-LE SV-5014H. It shows a cylindrical component with a total length of 57.5 mm and a mounting section length of 17.526 mm. The diameter is $\phi 44$. The drawing includes dimensions for the main body (42 mm), a section with a diameter of 42 mm and length 0.5 mm, a section with a diameter of 42 mm and length 40 mm, a section with a diameter of 42 mm and length 1 mm, and a section with a diameter of 42 mm and length 1 mm. The mounting section has a diameter of 22.5 mm and a thread of 2-M1.7 Lock screw. The mounting type is C-mount.</p>

■ 定格／性能

項目	生産終了予定商品 形FZ-LEH5	推奨代替商品 形3Z4S-LE SV-0614H
焦点距離(mm)	5	6.1
明るさ(開放F値)	F2.8	F1.4
画角(V × H)	82.4 × 66.9	71.5 × 56.8
最近接距離(mm)	50	100
中心解像力(本/mm)	100	100
TVディストーション(%)	0.5	-0.05
質量(g)	90	145
外形寸法	φ42 × 38.2	φ42 × 57.5
適合最大CCDサイズ	2/3インチ	2/3インチ
カメラマウント	Cマウント	Cマウント

項目	生産終了予定商品 形FZ-LEH8	推奨代替商品 形3Z4S-LE SV-0814H
焦点距離(mm)	8	8
明るさ(開放F値)	F1.4	F1.4
画角(V × H)	56.5 × 43.9	57.6 × 44.9
最近接距離(mm)	120	100
中心解像力(本/mm)	100	100
TVディストーション(%)	0.6	-0.06
質量(g)	90	125
外形寸法	φ34 × 41.6	φ39 × 52.5
適合最大CCDサイズ	2/3インチ	2/3インチ
カメラマウント	Cマウント	Cマウント

項目	生産終了予定商品 形FZ-LEH12	推奨代替商品 形3Z4S-LE SV-1214H
焦点距離(mm)	12.5	12.3
明るさ(開放F値)	F1.4	F1.4
画角(V × H)	38.3 × 26.2	39.6 × 30.2
最近接距離(mm)	150	100
中心解像力(本/mm)	100	100
TVディストーション(%)	-0.07	-0.04
質量(g)	75	85
外形寸法	φ34 × 37	φ30 × 51
適合最大CCDサイズ	2/3インチ	2/3インチ
カメラマウント	Cマウント	Cマウント

項目	生産終了予定商品 形FZ-LEH16	推奨代替商品 形3Z4S-LE SV-1614H
焦点距離(mm)	16	16
明るさ(開放F値)	F1.4	F1.4
画角(V × H)	30 × 22.7	30.6 × 23.1
最近接距離(mm)	210	100
中心解像力(本/mm)	100	100
TVディストション(%)	-0.05	0.1
質量(g)	81	85
外形寸法	φ33 × 36.5	φ30 × 47.5
適合最大CCDサイズ	2/3インチ	2/3インチ
カメラマウント	Cマウント	Cマウント

項目	生産終了予定商品 形FZ-LEH25	推奨代替商品 形3Z4S-LE SV-2514H
焦点距離(mm)	25	25
明るさ(開放F値)	F1.4	F1.4
画角(V × H)	19.6 × 14.8	20.0 × 15.0
最近接距離(mm)	210	150
中心解像力(本/mm)	100	100
TVディストション(%)	-0.04	0.07
質量(g)	89	65
外形寸法	φ33 × 39.5	φ30 × 36
適合最大CCDサイズ	2/3インチ	2/3インチ
カメラマウント	Cマウント	Cマウント

項目	生産終了予定商品 形FZ-LEH35	推奨代替商品 形3Z4S-LE SV-3514H
焦点距離(mm)	35	35.01
明るさ(開放F値)	F2.0	F1.4
画角(V × H)	14.4 × 10.8	14.3 × 10.8
最近接距離(mm)	210	200
中心解像力(本/mm)	100	100
TVディストション(%)	-0.2	-0.02
質量(g)	69	150
外形寸法	φ34 × 36.5	φ44 × 45.5
適合最大CCDサイズ	2/3インチ	2/3インチ
カメラマウント	Cマウント	Cマウント

項目	生産終了予定商品 形FZ-LEH50	推奨代替商品 形3Z4S-LE SV-5014H
焦点距離(mm)	50	50
明るさ(開放F値)	F2.8	F1.4
画角(V × H)	9.6 × 7.2	10.0 × 7.5
最近接距離(mm)	210	300
中心解像力(本/mm)	100	100
TVディストーション(%)	-0.03	0.03
質量(g)	92	170
外形寸法	φ34 × 55	φ44 × 57.5
適合最大CCDサイズ	2/3インチ	2/3インチ
カメラマウント	Cマウント	Cマウント

2012年10月現在

お断りなく仕様・標準価格などを変更することがありますので、ご了承ください。