

Sysmac Library for NJ/NX/NY Controller

SYSMAC-XR006


# **Vibration Suppression Library**



Increa	se material handling speed to reduce production cycle time.
Issue 1	When handling speed is increased, the machine and objects vibrates and vibration settling time is required.
lssue 2	Slides or spilling that occur during material handling result in poor product quality.


# Vibration Suppression Library offers solution!


Function Blocks in this library suppress vibration after and during high-speed material handling, significantly reducing production cycle time.






# Vibration Suppression Function Block Selection













Spilling


# **Applications**













# Compatible Models

Name	Model	Version
	NX701-1□□□/NJ101-1□□□	Version 1.10 or later
Marking Automatics Cantually	NJ501-□□□/NJ301-□□□	Version 1.10 or later
Machine Automation Controller NJ/NX CPU Unit	NX1P2-□□□□□(1)	Version 1.13 or later
	NX102-□□□	Version 1.30 or later
	NX502□□□	Version 1.60 or later
Industrial PC Platform NY IPC Machine Controller	NY5□□-1	Version 1.12 or later
industrial Charlotti White Machine Controller	NY5□□-5	Version 1.18 or later
Automation Software Sysmac Studio	SYSMAC-SE2□□□	Version 1.14 or higher
G5 Servo Drive with Built-in EtherCAT Communications	R88D-KN□□□-ECT	Version 2.10 or later

## Function Block (FB)/Function (FUN) Specifications

Name	FB/FUN name	Description
Multiple Frequency VS Filter 1	MultiVSFilter1	Creates, from the command position of the axis, the command position that can suppress up to five vibrations that occur on the equipment.
Time Specific Positioning Parameter Calculation 1	TimeToMoveParam1	Calculates parameters needed for creating the command pattern that can reach the target position in the specified time when positioning is performed using MultiVSFilter1.
Resonance Frequency Specific Vibration Suppression Parameter Calculation 1	VSMoveParam1	Calculates the S-curve (i.e., velocity, acceleration, and jerk) parameters for suppressing the vibration that occurs during single axis positioning. High-speed travel is achieved by suppressing vibration of the specified resonance frequency.
Constant Velocity Specific VS Profile 1	VSConstVelProfile1	Calculates the position profile with the specified velocity in constant velocity zone. Calculates a smooth position profile for each of the acceleration and deceleration distances, so that residual vibration at the stopping position can be reduced and the vibration during constant velocity motion can also be suppressed.
Time Specific Vibration Suppression Profile 1	VSConstTimeProfile1	Calculates the position profile for the high level S-curve with a specified travel time. Positioning can be made in smooth velocity and acceleration/deceleration from the start to end points.

Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products. EtherCAT® is registered trademark and patented technology, licensed by Beckho® Automation GmbH, Germany. Other company names and product names in this document are the trademarks or registered trademarks of their respective companies. The effects of reduction in time in this document are based on the comparison with the customers' existing equipment and for reference only. Omron does not warrant that the content of this document does not infringe any third-party intellectual property rights.

Note: Do not use this document to operate the Unit.

# **OMRON Corporation** Industrial Automation Company

Kyoto, JAPAN Contact: www.ia.omron.com

### Regional Headquarters

#### OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

### OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011

#### OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

### OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

©OMRON Corporation 2015-2023 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM\_2\_4

Cat. No. P099-E1-04 0523(1115)