

NX-series EtherNet/IP™ Unit

NX-EIP201


Collects large amounts of data at high speeds and increases scalability of safety



Features

- High-speed, high-capacity communications (allowed bandwidth per unit: 40,000 pps, baud rate: 1 Gbps)
- Connectable to NX5 via X bus for high-speed, high-capacity data transfer
- Expandable to eight EtherNet/IP networks (four NX-EIP201 EtherNet/IP Units per NX5)
- CIP communications service: Tag data links and message communications
- Used in conjunction with NX-SL5 Safety Control Unit for safety communications via CIP Safety
- · Network ports to connect HMI and Sysmac Studio

System Configuration



The following table shows the description, NX502 CPU Unit connection method, and quantity for each configuration element in the figure above.

Configuration element	Description	NX502 CPU Unit connection method	Qty	
NX502 CPU Unit	A CPU Unit to which the NX-series EtherNet/IP Unit is connected. This Unit performs machine control and process control of the system.		One Unit for machine control, and one Unit for overall process control	
NX-series EtherNet/IP Unit	One of X Bus Units which performs EtherNet/IP communications.	X Bus * 1	Up to four Units per an NX502 CPU Unit	
NX I/O Unit	An interface Unit to connect an NX-series CPU Unit to control devices such as sensors and actuators. This Unit can also be connected to an NX-series Communications Coupler Unit.	NX bus of CPU Unit and Slave Terminal	Zero to multiple Units (depends on application)	
Safety CPU Unit	A CPU Unit which controls the safety circuit of manufacturing equipment. This Unit controls both of the safety control within equipment by FSoE and the line safety control by CIP Safety.		One Unit per an NX502 CPU Unit	
FSoE I/O Unit	This Unit inputs safety input signals and outputs safety output signals in combination with a Safety CPU Unit.	NX bus of CPU Unit and Slave Terminal	Zero to multiple Units (depends on application)	
Servo Drive	A control device for an electric motor assembled in a control equipment. It is controlled by the Motion Control Function Module within the CPU Unit.	Built-in EtherCAT port	Zero to multiple Units (depends on application)	
EtherCAT general-purpose slave	A general-purpose slave connected to the EtherCAT.	Built-in EtherCAT port	Zero to multiple Units (depends on application)	
Ethernet switch	An Ethernet switch connects devices on the network by packet switching and transfers the received data to the target device.	EtherNet/IP port on CPU Unit and NX-series EtherNet/IP Unit	Zero to multiple Units (depends on application)	
НМІ	An HMI performs operation input to the manufacturing equipment and displays status of the manufacturing equipment.	EtherNet/IP port on CPU Unit and NX-series EtherNet/IP Unit	Zero to multiple Units (depends on application)	
Sysmac Studio Network Configurator	Support Software for NX502 CPU Unit.	EtherNet/IP port on CPU Unit and NX-series EtherNet/IP Unit	One to multiple Units (depends on application)	
HOST PC	OST PC This computer performs EtherNet/IP communications.		One to multiple Units (depends on application)	
RFID system	This system uses electromagnetic fields and radio waves to exchange product identification information. Communications is performed with a Modbus/TCP client.	EtherNet/IP port on CPU Unit and NX-series EtherNet/IP Unit	Zero to multiple Units (depends on application)	
CIP Safety I/O	A connection interface for sensors and actuators of safety I/O devices. CIP Safety on EtherNet/IP compatible.	EtherNet/IP port on NX-series EtherNet/IP Unit	Zero to multiple Units (depends on application)	

^{*1.} You can connect the NX series EtherNet/IP Unit on the left side of the NX502 CPU Unit.

Ordering Information

Applicable standards

Refer to the OMRON website (www.ia.omron.com) or ask your OMRON representative for the most recent applicable standards for each model.

EtherNet/IP Unit

Product name		Model		
Froduct name	Communications	Units per CPU Unit	Power consumption	Wodei
EtherNet/IP Unit	Tag data links, Message Communications	4 max.	8.1 W max.	NX-EIP201

Industrial Switching Hubs

Product name	Functions	No. of ports	Accessories	Current consumption (A)	Model
Industrial Switching Hubs	Packet priority control (QoS): EtherNet/IP control data priority Ethernet standard: IEEE 802.3 10Base-T, 100Base-TX Auto-negotiation: Supported Broadcast Storm Detection Function: Supported	5	Power supply connector	0.07	W4S1-05D

Recommended Network Devices

The following table shows the devices recommended for use with the EtherNet/IP.

Switching Hub

Manufacturer	Model number
Phoenix Contact USA	Consult the manufacturer.
Contec USA,Inc.	Consult the manufacturer.
Cisco Systems,Inc	Consult the manufacturer.

Twisted-pair Cables

Applicable EtherNet/IP communications cables and connectors vary depending on the used baud rate.

For 100Base-TX and 10Base-T, use an STP (shielded twisted-pair) cable of category 5 or higher.

You can use either straight or cross cable.

For 1000Base-T, use an STP (shielded twisted-pair) cable (double shielding with aluminum tape and braiding) of category 5e or higher. You can use either straight or cross cable

Cabling materials used for EtherNet/IP communication cables are shown in the table below.

Cables / Connectors

Product			Appearance	Recommended manufacturer	Model
For 1000BASE-T and	Size and conductor	Cables		Hitachi Metals, Ltd.	NETSTAR-C5E SAB 0.5 × 4P CP *1
100BASE-TX	pairs: AWG24 × 4P			Kuramo Electric Co., Ltd.	KETH-SB *1
		RJ45 Connectors		Panduit Corporation	MPS588 *1
	Size and conductor	Cables		Kuramo Electric Co., Ltd.	KETH-PSB-OMR *1
For 100BASE-TX		Cables		JMACS Japan Co., Ltd.	PNET/B *1
1011005/IGE 17	pairs: AWG22 × 2P	RJ45 Assembly Connector		OMRON	XS6G-T421-1 *1

^{*1.} We recommend that you use cables and connectors in above combinations.

[&]quot;100Base-TX" in the "Product" column of the table below indicates that either 100Base-TX or 10Base-T can be used.

General Specifications

	Item	Specification			
Enclosure		Mounted in a panel			
Grounding method		Ground to less than 100 Ω .			
Dimensions: He	eight × Depth × Width	100 × 120 × 39 (mm)			
Weight 350 g max.		350 g max.			
Power consum	ption	8.1 W max.			
	Ambient operating temperature	0 to 55 ℃			
	Ambient operating humidity	10% to 95% (with no icing or condensation)			
	Atmosphere	Must be free from corrosive gases.			
	Ambient storage temperature	-25 to 70 °C (with no icing or condensation)			
	Altitude	2,000 m max.			
	Pollution degree	2 or less: Meets IEC 61010-2-201.			
	Noise immunity	2 kV on power supply line (Conforms to IEC 61000-4-4.)			
Operating	Overvoltage category	Category II: Meets IEC 61010-2-201.			
environment	EMC immunity level	Zone B			
	Vibration resistance	Conforms to IEC 60068-2-6. 5 to 8.4 Hz with 3.5-mm amplitude, 8.4 to 150 Hz, acceleration of 9.8 m/s² 100 min each in X, Y, and Z directions (10 sweeps of 10 min each = 100 min total) Gravity acceleration is assumed to be G=9.8 m/s².			
	Shock resistance	Conforms to IEC 60068-2-27, 147 m/s², 3 times in X, Y, and Z directions. Gravity acceleration is assumed to be G=9.8 m/s².			
	Mounting method	Mount to DIN Track			
	Mounting direction	One direction (upright)			
Applicable stan	dards * 1	EU Directives, cULus, RCM, UKCA, KC			

^{*1.} Refer to the OMRON website (http://www.ia.omron.com/) or consult your OMRON representative for the most recent applicable standards for each model.

Performance Specifications

		Item		NX-EIP201	
	Number of ports			2	
	Physical layer			10BASE-T, 100BASE-TX, or 1000BASE-T	
	Frame length			1,514 bytes max.	
	Media access metho	od		CSMA/CD	
	Modulation			Baseband	
	Topology			Star	
	Baud rate			1 Gbps (1000BASE-T) max.	
	Transmission media	3		STP (shielded, twisted-pair) cable of Ethernet category 5, 5 or higher	
	Maximum transmiss	sion distance betwee	en Ethernet switch and node	100 m	
	Maximum number o	f cascade connection	ons	There are no restrictions if an Ethernet switch is used.	
	LLDP			Supported.	
	BOOTP client			Supported.	
	DNS client			Supported.	
	SNMP agent, traps			Supported.	
	3.0	Maximum numbe	r of connections	256 per port 512 total	
		Packet interval *1	1, *2	Can be set for each connection. 1.0 to 10,000 ms in 1-ms increments	
		Allowed communications bandwidth per Unit		40,000 pps *3, *4 (including heartbeat)	
		Maximum number of tag sets		256 per port 512 total	
		Tag types		Network variables CIO, Work, Holding, DM, or EM Areas can be used.	
EtherNet/IP	CIP service:	Number of tags per connection (i.e., per tag set)		64 (63 tags if Controller status is included in the tag set.)	
ort	Tag data links (cyclic communications)	Maximum number of tags		1,024 per port 2,048 total	
		Maximum link dat (total size for all t		369,664 bytes per port (total of 739,328 bytes with two por	
		Maximum data size per connection		1,444 bytes	
		Maximum number of registrable tag sets		256 per port 512 total (1 connection = 1 tag set)	
		Maximum tag set size		1,444 bytes (Two bytes are used if Controller status is included in the tag set.)	
		Multicast packet f	filter * 5	Supported.	
	CIP message	Class 3 (number of connections)		128 per port 256 total (clients plus server)	
	service: Explicit messages	UCMM	Maximum number of clients that can communicate at one time	32 per port 64 total	
		(non-connection type)	Maximum number of servers that can communicate at one time	32 per port 64 total	
	CIP Safety routing	Maximum numbe	r of routable CIP Safety connections	84 total (originator: 80, target: 4)	
	*6	Maximum routabl	e safety data length per connection	32 bytes	
	CNIMD	Agents		SNMPv1, SNMPv2C	
	SNMP	MIB		MIB-II	
	EtherNet/IP conform	nance test		Conforms to CT18.	
	Ethernet interface			10BASE-T, 100BASE-TX, or 1000BASE-T Auto negotiation	

- ***1.** Data will be refreshed at the set interval, regardless of the number of nodes.
- *2. The approximate I/O response time of the tag data link is determined by the relationship between the packet interval and the number of connections.
- *3. "pps" means packets per second, i.e., the number of communications packets that can be sent or received in one second.
 If the packet interval (RPI) is 0.5 ms, then this will be 30,000 pps.
 *4. When the Unit is performing tag data link communications where the allowable communications bandwidth per Unit is close to or greater than
- *4. When the Unit is performing tag data link communications where the allowable communications bandwidth per Unit is close to or greater than 30,000 pps, the following functions may not be used properly. In that case, use the built-in EtherNet/IP port on the CPU Unit or an EtherNet/IP port of a different NX-series EtherNet/IP Unit.
 - Connecting the Sysmac Studio online from the EtherNet/IP port of the NX-series EtherNet/IP Unit
 - Connecting the Network Configurator online from the EtherNet/IP port of the NX-series EtherNet/IP Unit
 - Connecting the NA-series Programmable Terminal online from the EtherNet/IP port of the NX-series EtherNet/IP Unit
 - Port forward via the NX-series EtherNet/IP Unit
 - CIP message communications
 - SNMP function

These functions of the NX-series EtherNet/IP Unit can be used via X Bus from the built-in EtherNet/IP port on the CPU Unit or an EtherNet/IP port of a different NX-series EtherNet/IP Unit.

- *5. As the EtherNet/IP port implements the IGMP client, unnecessary multi-cast packets can be filtered by using an Ethernet switch that supports IGMP Snooping.
- *6. CIP Safety communications and tag data links cannot be used together in one NX-series EtherNet/IP Unit

Function Specifications


		NX-EIP201		
		Communications proto	col	TCP/IP or UDP/IP
Communications		CIP communications	Tag data links	Programless cyclic data exchange is performed with the devices on the EtherNet/IP network.
	EtherNet/IP port	services	Message Communications	CIP commands are sent to or received from the devices on the EtherNet/IP network.
		TCP/IP application SNMP agent		EtherNet/IP port internal status information is provided to network management software that uses an SNMP manager.
		Function		Events are recorded in the logs.
System	Event lene		System event log	1,024
management	Event logs	Maximum number of events	Access event log	512
		CVCIIIS	User-defined event log	None

Version Information

NX-EIP201	Sysmac Studio	Network Configurator *1
Ver.1.0	Ver.1.54 or higher	Ver.3.74 or higher

^{*1.} This software is used to configure tag data links.

Part Names and Functions



Symbol	Name	Function
(A)	X Bus connectors	These connectors are used to connect another Unit.
(B)	DIN Track mounting hook	This hook is used to mount the Unit to a DIN Track.
(C)	Unit hookup guides	These guides are used to connect two Units.
(D)	Operation status indicators	The indicators show the current operating status of the Unit.
(E)	EtherNet/IP ports	The communications ports for EtherNet/IP connection. There are two ports.
(F)	DIP switch	This switch is for configuring internal settings of the Unit, but not used normally. Always keep all pins from SW1 to SW4 in OFF state.
(G)	Unit specifications	The specifications of the Unit are given here.

Functional Comparison of EtherNet/IP Ports on NJ/NX-series CPU Units and Other Series

OK: Supported, ---: Not supported

	Built-in EtherNet/IP	Built-in EtherNet/IP	EtherNet/IP EtherNet/IP I	Built-in EtherNet/IP	Built-in EtherNet/IP		CJ-series	EtherNet/IP Unit (built-in port on CJ2 CPU Unit)		
Item	port on NX701 CPU Unit	port on NX502 CPU Unit	port on NX102CPU Unit	port on NX1P2 CPU Unit	port on NJ-series CPU Unit	EtherNet/IP Unit	Ethernet Unit	Unit version 1.0	Unit version 2.0	Unit version 2.1
Tag data link communications service	ОК	ОК	ОК	ОК	ок	ОК		ОК	ОК	ОК
CIP message communications service	ОК	ОК	ОК	ОК	ОК	ОК		ОК	ОК	ОК
IP routing	OK	OK	OK			OK				
Socket service	OK	OK	OK	OK	OK		OK			
FTP server	OK	OK	OK	OK	OK		ОК		OK	ОК
FTP client	OK	OK	OK	OK	OK					
Mail send/receive							OK			
Web functions							OK			
Automatic adjustment of PLC/Controller's internal clock	ОК	ОК	ОК	ОК	ок		ок		ок	OK
Error history	OK * 1	OK * 1	OK * 1	OK *1	OK *1	OK * 1	OK	OK	OK	OK
Response to PING command	OK	OK	OK	ОК	ОК	OK	OK	OK	OK	ОК
SNMP/SNMP trap	OK	OK	OK	OK	OK	OK			OK	OK
CIDR function for IP addresses	OK	OK	OK	OK	ОК	OK			OK	ОК
DHCP client		OK					-			
Online connection via EtherNet/IP using CX- One							ок		ок	ОК
Online connection via EtherNet/IP using Network Configurator	ОК	ОК	ОК	ОК	ок	ОК		ОК	ОК	ОК
Mounting in an NJ- series CPU Unit										OK * 2
Connection settings using the Sysmac Studio	ОК	ОК	ОК	ОК	ОК	ОК				ОК


 $[\]textcolor{red}{\textbf{\$1.}} \textbf{This is equivalent to the event log in the EtherNet/IP of an NJ-series Controller}.$

^{*2.} You cannot use the following functions if you connect to the CPU Unit through an EtherNet/IP Unit.

Placing the Sysmac Studio online with the CPU Unit (However, you can place the Network Configurator online)
 Using the Troubleshooter of an NS-series PT

Dimensions (Unit: mm)

NX-EIP201



For dimensions after attaching the communications cables, refer to NX-series EtherNet/IPTM Unit User's Manual (W627).

Related Manuals

The following manuals are related. Use these manuals for reference.

Manual name	Cat. No.	Model numbers	Application	Description
NX-series EtherNet/IP TM Unit User's Manual	W627	NX-EIP201	Learning how to use the NX- series EtherNet/IP Unit.	Information on the NX-series EtherNet/ IP Unit is provided. Information is provided on the basic setup, tag data links, and other features.
NX-series NX502 CPU Unit Hardware User's Manual	W629	NX502-□□□	Learning the basic specifications of the NX502 CPU Units, including introductory information, designing, installation, and maintenance. Mainly hardware information is provided.	An introduction to the entire NX502 system is provided along with the following information on the CPU Unit. • Features and system configuration • Introduction • Part names and functions • General specifications • Installation and wiring • Maintenance and inspection
NJ/NX-series CPU Unit Software User's Manual	W501	NX701	Learning how to program and set up an NJ/NX-series CPU Unit. Mainly software information is provided.	The following information is provided on a Controller built with an NJ/NXseries CPU Unit. CPU Unit operation CPU Unit features Initial settings Programming based on IEC 61131-3 language specifications
NJ/NX-series Instructions Reference Manual	W502	NX701	Learning detailed specifications on the basic instructions of an NJ/NX-series CPU Unit.	The instructions in the instruction set (IEC 61131-3 specifications) are described.
NJ/NX-series CPU Unit Motion Control User's Manual	W507	NX701	Learning about motion control settings and programming concepts.	The settings and operation of the CPU Unit and programming concepts for motion control are described.
NJ/NX-series Motion Control Instructions Reference Manual	W508	NX701	Learning about the specifications of the motion control instructions.	The motion control instructions are described.
NJ/NX-series CPU Unit Built-in EtherCAT® Port User's Manual	W505	NX701-□□□□ NX502-□□□□ NX102-□□□□ NX1P2-□□□□ NJ501-□□□□ NJ301-□□□□ NJ101-□□□□	Using the built-in EtherCAT port on an NJ/NX-series CPU Unit.	Information on the built-in EtherCAT port is provided. This manual provides an introduction and provides information on the configuration, features, and setup.
NJ/NX-series CPU Unit Built-in EtherNet/IP™ Port User's Manual	W506	NX701-	Using the built-in EtherNet/IP port on an NJ/NX-series CPU Unit.	Information on the built-in EtherNet/IP port is provided. Information is provided on the basic setup, tag data links, and other features.
NJ/NX-series CPU Unit OPC UA User's Manual	W588	NX701-\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	Using the OPC UA.	Describes the OPC UA.
NX-series CPU Unit FINS Function User's Manual	W596	NX701-□20 NX502-□□□ NX102-□□□	Using the FINS function of an NX-series CPU Unit.	Describes the FINS function of an NX- series CPU Unit.
NJ/NX-series Troubleshooting Manual	W503	NX701-	Learning about the errors that may be detected in an NJ/NX-series Controller.	Concepts on managing errors that may be detected in an NJ/NX-series Controller and information on individual errors are described.

Manual name	Cat. No.	Model numbers	Application	Description
Sysmac Studio Version 1 Operation Manual	W504	SYSMAC-SE2	Learning about the operating procedures and functions of the Sysmac Studio.	Describes the operating procedures of the Sysmac Studio.
NXR-series IO-Link Master Unit for EtherNet/IP TM User's Manual	W619	NXR-ILM08C-EIT	Learning how to use an NXR- series IOLink Master Unit for EtherNet/IP.	The hardware, setup methods, and functions of the NXR-series IO-Link Master Unit for EtherNet/IP are described.

Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products. EtherCAT® is a registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany. ODVA, EtherNet/IP, and CIP Safety are trademarks of ODVA

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies. The product photographs and figures that are used in this catalog may vary somewhat from the actual products.

MEMO

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

Authorized Distributor:

©OMRON Corporation 2023 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM_2_2

Cat. No. P160-E1-03 1123 (0423)