

MC Command Table Library




Make programming for continuous positioning easy.

- Issue 1** PLCopen® Function Blocks for Motion Control do not support the familiar command table (memory operation) that is an efficient method for simple continuous operation
- Issue 2** The program must be modified to change the operation pattern.


MC Command Table Library offers solution!

The Command Table (Memory Operation) Function Block allows you to program motion control using the familiar command table (memory operation). No program modification is required to change the operation pattern.




[Example] Path control using the Command Table (Memory Operation) Function Block

With a single Command Table (Memory Operation) Function Block, you can perform path control with multi-execution of PTP, linear interpolation, and circular interpolation instructions as shown below.



Arrayed position data (Table)

001:X1	Y1
002:X2	Y2
005:X0	Y0



Compatible Models

Name	Model	Version
Machine Automation Controller NJ/NX CPU Unit	NX701-□□□□/ NJ101-□□□□*1 *2	Version 1.10 or later
	NJ501-□□□□/ NJ301-□□□□	Version 1.10 or later
	NX1P2-□□□□□□(1) *3 *4	Version 1.13 or later
Industrial PC Platform NY IPC Machine Controller	NY5□□-1	Version 1.12 or later
Automation Software Sysmac Studio	SYSMAC-SE2□□□	Version 1.14 or higher
G5 Servo Drive with Built-in EtherCAT Communications	R88D-KN□□□-ECT	Version 2.10 or later

*1. This Library is not available for NJ101-90□□ CPU Units.

*2. When you use this function block with NJ101-10□□, you can use a maximum of two real servo axes.

*3. This Library is not available for NX1P2-90□□□□ CPU Units.

*4. When you use this function block with NX1P2-10□□□□, you can use a maximum of two real servo axes.

Function Block (FB) Specifications

Name	FB name	Description
Command Table (Memory Operation)	MCCmdTbl	Continuously executes positioning that is specified in memory operation data for axes groups that are defined in the MC Function Module.

Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products. EtherCAT® is registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany. EtherNet/IP™ is a trademark of the ODVA. Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company
Kyoto, JAPAN

Contact: www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp
The Netherlands
Tel: (31)2356-81-300/Fax: (31)2356-81-388

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200
Hoffman Estates, IL 60169 U.S.A.
Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

OMRON ASIA PACIFIC PTE. LTD.

No. 438A Alexandra Road # 05-05/08 (Lobby 2),
Alexandra Technopark,
Singapore 119967
Tel: (65) 6835-3011/Fax: (65) 6835-2711

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower,
200 Yin Cheng Zhong Road,
PuDong New Area, Shanghai, 200120, China
Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200

Authorized Distributor:

© OMRON Corporation 2015 All Rights Reserved.
In the interest of product improvement,
specifications are subject to change without notice.

CSM_2_1_1116
Cat. No. P092-E1-01

1115(1115)