OMRON Machine Automation Controller

NJ/NX Series





2 Beyond the highest

A fully integrated platform

One machine control through one connection and one software is how we define the Sysmac automation platform. The Machine Automation Controller integrates logic, motion, safety, robotics, vision, information, visualization and networking under one software: Sysmac Studio. This one software provides a true Integrated Development Environment (IDE). The machine controller comes standard with built-in EtherCAT and EtherNet/IP. The two networks with one connection purpose is the perfect match between fast real time machine control and data plant management.

One Machine Controller

Complete integration of motion and logic

A large selection of CPU Units for up to 256 axes

Safety integration

Flexible system lets you integrate safety into machine automation through the use of Safety over EtherCAT (FSoE).

One Connection

Integration of machine control and Information

- Built-in EtherCAT and EtherNet/IP[™] ports : Global standard networks
- NX701-1 NX102- NJ501-1 00 CPU Unit with built-in international standard (IEC 62541) OPC UA communication functionality
- Database connection: Logs real-time data from production lines directly into SQL Databases. This enables preventive maintenance and quality traceability.

One Software

One integrated development environment software

- Fully conforms with IEC 61131-3 standards
- PLCopen function blocks for motion control
- · Packed with Omron's rich technical know-how. Various software components help reduce programming time.



Ħ____

Laser/Contact Sensor

ZW-7000 Displacement Sensor

FH Vision System





Advanced machine control and integrated production /

Motion Control


Complete integration of motion and logic

One controller integrates logic, motion, vision and information for complete control and management of machines. Position, displacement, and tension information collected from sensors can be quickly and easily fed back to the motion control.



Accurate feedback control with less than 1 µs jitter

The NJ/NX controller offers synchronous control of all machine devices, from input through to output. Distributed clock-based clock synchronization incorporated into EtherCAT slaves enables the I/O refresh cycle to be synchronized between units such as the FH Vision System, ZW Displacement Sensor, NX I/O, and G5/1S Servo Drive.




Preventive maintenance

Preventive maintenance of EtherCAT sensor

Monitoring the sensor status allows you to maintain before sensors malfunction due to dirt or aged deterioration.* The sensor settings can be saved and loaded, which minimizes downtime when troubles occur.

FROM

In harsh environments, sensors can become dirty, resulting in malfunctions.



Detection in dusty environment





Preventive maintenance of actuator devices

The NJ/NX controller that integrates EtherCAT and motion control can constantly monitor actuator devices with a fast cycle time.



Decreases in light intensity can be detected by monitoring sensors.

122 22 -	COLUMN A DAME DAME LOUGH	COLUMN 1	ALC: NAMES OF TAXABLE								
	the same of the same same			1981	5 -	97	-	0000	-1730 mar		1208
TEROLA	TLADA PRAM OUT L/D BTATUS	W. and the local division of the local divis	PV WOOE SHAPE	1990-14			-		-8535	-#185 L.R#	- 5 -
1942		10 11 11	1×4 III III								
			545								
ERROR LA.	PLAN-BRANK OUT LID STATUS		IN MORE DRAFT								
1982			8								x10
		1 K 12 K									AIV
EIRC-TA	PLAIN PRAK OUT LUD STATUS		IV MODE GRAPHI								
1982			V7N225V7								
		112 🖬 🖬	Y7NE55Y7	- 30							
	PLASH PRIME OUT LO ETATUS		PV MODE LITATION								
1042			38 = -								
10.00			7533								
DINE 7A	FLASH PHINE OUT L/D STATUS		PV MCCE GRAPHI								
4942			222 == ==								
		17 13 13	222 221 🖬 📾								
****	PLADE THE BUT LTD STATUS		PY HOLE STARL	81							
****			0	1000 1000				100 100	THE OWNER WHEN THE OWNER	100 100	1000
	Q - Q -		8	4 4				100	07		

Initial display





* When combining the NJ/NX controller with the E3NW EtherCAT Sensor communications unit and creating the programmable terminal screens.

The sample program for Omron NS/NA Programmable Terminal is available. Contact your Omron sales representative for details.

machine data management for a variety of applications

Information

NX102-020/NJ101-020/NJ501-020/NX701-120

Fast machine data storage in database

The controller connects directly to a database without the need for a gateway. The special instructions allow easy access to the database. Real-time data collection enables productivity improvement, predictive maintenance, and quality traceability.





NX701-1 // NX102- // NJ501-1 00

International standard communication protocol OPC UA directly connects automation and IT

OPC UA with strong security features (e.g., authentication and encryption) is widely used across the world and adopted for Industrie 4.0 and PackML communications. The host system can access production data directly without connecting a gateway computer.



NX102-

Easy and secure data collection in the cloud


The controllers supports MQTT (S) communication using MQTT Communication Library. It can easily connect to the cloud without a gateway PC and securely collect manufacturing site data.



NJ501-1340

Semiconductor industry standard SECS/GEM communications functionality

The SECS/GEM CPU Unit integrates machine control and host communications, reducing time, cost, and complexity to establish SECS/GEM communications.





Versatile NC functions

G-Code reduces time required to design and program complex profiling.

Conventional controller

Processing programs are designed based on CAD data. Programming using PLC instructions and debugging are required for each figure



Program design

- Exploding components into lines
- Types of lines: straight line, arc, free curve
- Target positions of lines
- Travel velocities
- Transition path between figures, etc.

NC Integrated Controlle

CAD/CAM software makes design easy



CAD/CAM software





③ Program is transferred to

NC integrated controller











NC functions for complex profiling applications

① Parameters are set using ② NC program in G-Code is generated

G-Code G-Code NC programming language allows manual programming on operation software and use in combination with any CAD/CAM software	High-speed control Logic sequence, motion control and NC functionality with the fastest cycle time of 500 µs	Cutter compensation 2D Tool diameter and shape compensation, matching the cutting point exactly as specifie in G-Code
Lookahead Future instructions are analyzed in advance, movements are blended and optimized in speed and acceleration for a better performance	3D interpolation Helical, spiral and conical interpolation for 3D profiling	Coordinate systems Various profiling using machine coordinate system, workpiece coordinate system, and local coordinate system

Robotics

NJ501-R

Integration of logic, motion, Omron Robot and kinematics makes automation more advanced and flexible


Industry first*:

Integrated control of different engines

Omron is the first in the industry* to provide a controller that integrates two very different types of engines _ one that works in program scan cycles (PLC feature) and another based on procedural programming (robot feature) _ and synchronizes their program tasks and I/O refreshing.

Collection of truly useful data

Devices such as robots and motion/vision sensors can be connected to an EtherCAT network for synchronized control. This synchronization ensures that the data collected on these devices is concurrent and therefore truly useful for visualizing facility operation. Robot integrated CPU unit NJ501-R



*Based on Omron investigation in November 2019

Maximized uptime NX102-00/NX1P2-00/NJ501-100/NJ301-100/NJ101-00

Redundancy minimizes downtime

Even if a part of the EtherCAT network is disconnected, Cable Redundancy provides continuous connectivity. This function allows you to fix disconnection without stopping the machines and production line where one controller provides both machine control and safety control.





EtherCAT.

Creative development environment for globalized

Design

Reusable programs

Development by multiple developers

Programming with variables

Project version control function^{*1}



One Integrated Development Envi-

ronment software Sysmac Studio is

fully compliant with the open stan-

dard IEC 61131-3. Programming

with variables eliminates the need

to learn the internal memory map of

the PLC and allows the programs to

be reused.


When you develop a project at the same time as your colleagues, the Sysmac Studio combined with the version control system (Git^{TM*}) merges changes automatically and resolves conflicting changes. This makes merging easier and faster. You can even revert to the previous revision after graphically comparing the current project with a previous one.

Maintenance

D

Highly efficient maintenance

Troubleshooting



Troubleshooting in the Sysmac Studio and NA Programmable Terminal can manage errors across the entire system including the controller. You can check details of errors and solutions without reading manuals.

*1. This function can be used by applying the Team Development Option to Sysmac Studio version 1.20 or higher. Project version control function is supported by CPU Unit version 1.16 or later. Git and the Git logo are either registered trademarks or trademarks of Software Freedom Conservancy, Inc., corporate home of the Git Project, in the United States and/or other countries.

*2. Available with the Sysmac Studio 64-bit version. 3D CAD data supports STEP/IGES.

manufacturing



Collection of software functional components Sysmac Library

Packed with Omron's rich technical know-how. Various software components help reduce programming time.

For advanced machine control

Motion programming



Advanced motion control applications can be created quickly just by combining PLCopen[®] Function Blocks for Motion Control.







Complex feedback control that is designed with MATLAB[®]/Simulink[®] can be imported into programs.



Circuit diagrams designed using electrical CAD data (e.g., unit configurations and signal lines) can be imported to the Sysmac Studio and automatically reflected in unit configurations and settings and allocated variables.

Seamless and accurate setup using electrical CAD design data speeds up the engineering process and improves design efficiency.

Verification

Fast system debugging

Virtual mechanical debugging



Movement of the machine connected online can be displayed on the CAD in real time, and movement can also be reproduced from the trace data. Maintenance and troubleshooting can be performed in remote locations.



Enhanced by 3D simulation option *2

Use only the Sysmac Studio with loaded 3D CAD data*2 for 3D simulations.Operation of a control program can be verified in a virtual environment, improving program accuracy during design and reducing rework during verification using physical devices.

For more information, see the video: www.fa.omron.co.jp/3d-simulation_e



Debugging in conjunction with a third-party simulator is possible.





NJ/NX-series Lineup

Series			NX Series						
Product name	э		NX701 CPU Units NX102 CPU Units		NX1P2 CPU Units				
Model			NX701-□□□	NX102-□□□	NX1P2-000				
Appearance			(NX701-100)	SPC UA					
	CPU Unit features		Ideal for large-scale, fast, and highly-accurate control with up to 256 axes.	Compact controller with up to 8 axes motion control.	Compact controller with up to 4 axes motion control, up to 4 axes single-axis control, and built-in I/O.				
	i struction	LD instructions	0.37 ns or more	3.3 ns	3.3 ns				
	Instruction execution times	Math instructions (for long real data)	3.2 ns or more	70 ns or more	70 ns or more				
	Program ca	pacity	80 MB	5 MB	1.5 MB				
Specifications	Variable capacity		4 MB : Retained during power interruptions 256 MB: Not retained during power interruptions	1.5 MB: Retained during power interruptions 32 MB : Not retained during power interruptions	32 KB: Retained during power interruptions 2 MB : Not retained during power interruptions				
	I/O capacity/maximum number of configuration Units (Expansion Racks)		-	Up to 32 NX I/O Units connectable	Built-in I/O: 40 points max. Up to eight NX I/O Units connectable				
	Number of motion axes		128, 256	0, 2, 4, 8 *1	0, 2, 4 *1				
	EtherCAT sl	laves	512	64	16				
	Number of controlled robots		-	-	-				
	Number of controlled OMRON robots		-	-	-				
	Database connection		● NX701-1□20	● NX102-□□20	-				
Functions	SECS/GEM communications functions		-	-	-				
	Numerical C functions	Control (NC)	-	-	-				
External mem	hory		Memory Cards	Memory Cards	Memory Cards				
Detailed specification (Datasheet)			P141	P130	P116				

*1. Motion control axes and 4 single-axis position control axes.
*2. The number of robots that can be controlled depends on the number of axes used in the system.
*3. The number of controlled axes of the MC Control Function Module is included.

Individual Pamphlets





OPC UA P123







Robot Integrated Controller 1856



NJ Series									
		NJ501 CP	NJ301 CPU Units	NJ101 CPU Units					
NJ501-1⊡00	NJ501-R□□□	NJ501-4□□□	NJ501-1□20	NJ501-1340	NJ501-5300	NJ301-1⊟00	NJ101-□□00	NJ101-□□20	
(NJ501-100)	X								
Ideal for large-s	cale, fast, and highl	y-accurate control w	Ideal for small control with up to 8 axes.	Ideal for simple machines.					
1.1 ns (1.7 ns o	r less)		1.6 ns (2.5 ns or less)	3.0 ns (4.5 ns or less)					
24 ns or more			35 ns or more 63 ns or more						
20 MB			5 MB 3 MB						
	during power interrined during power int		0.5 MB: Retained during power interruptions 2 MB: Not retained during power interruptions	2 MB : Not retained during power					
2,560 points/40 (3 Expansion R			2,560 points/40 Units (3 Expansion Racks)	2,560 points/40 Units (3 Expansion Racks)					
16, 32, 64 16 *3						4, 8	0, 2		
192			192	64					
_	8 robots max. *2 8 robots max. *2 -				-	-			
-	8 robots max. – –					-	-		
_	● NJ501-R□20	• NJ501-4320	•	_		-	_	•	
- · · -						-	-		
_			_	-					
Memory Cards						Memory Cards	Memory Cards		
P140									

Robotics P085



Database Connection P088

SECS/GEM P086



NC integrated R190



Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products. Intel and Intel Core are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Microsoft, Windows, Windows Vista and SQL Server are registered trademarks of Microsoft Corporation in the United States and other countries. Oracle and Oracle Database are trademarks or registered trademarks of Oracle Corporation and/or its affiliates in the United States and other countries. IBM and DB2 are trademarks or registered trademarks of International Business Machines Corp., registered in the United States and other countries.

SEMI® is a trademark or registered trademark of Semiconductor Equipment and Materials International in the United States and other countries.

EtherCAT® is a registered trademark of Beckhoff Automation GmbH for their patented technology.

EtherNet/IP[™] and DeviceNet[™] are trademarks of ODVA.

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (http://www.openssl.org/)

This product includes cryptographic software written by Eric Young (eay@cryptsoft.com).

The CAD data in inCAD Library is used with permission from MISUMI Corporation. Copyright of any of information in CAD data belongs to MISUMI Corporation or its respective manufacturer.

MISUMI Corporation may not offer all parts in each application design. Available parts can only be purchased separately not as a unit shown in each application design. MISUMI Corporation does not guarantee quality, accuracy, functionality, safety or reliability for the combination of the parts in each application example. Microsoft product screen shot(s) used with permission from Microsoft.

MATLAB® and Simulink® are registered trademarks of The MathWorks® Inc.

Safety over EtherCAT® is registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany.

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

OMRON Corporation

Kyoto, JAPAN

Industrial Automation Company

Contact: www.ia.omron.com

Regional Headquarters OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31)2356-81-300/Fax: (31)2356-81-388

OMRON ASIA PACIFIC PTE. LTD. 438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011/Fax: (65) 6835-2711

OMRON ELECTRONICS LLC 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200

Authorized Distributor:

© OMRON Corporation 2015-2022 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM 13 1 Cat. No. P089-E1-25