

生産終了商品

多軸モーションコントローラ



3-3494A-00-0000-B200
3-3494A-00-0000-F200



推奨代替商品

多軸モーションコントローラ

3-4027A-00-0211-B200
3-4027A-00-0211-F200

■最終受注年月

2024年3月末

■最終出荷年月

2024年9月末

■修理対応終了年月

2027年9月末

■推奨代替商品をご利用いただいた場合の注意点

- ・ACC-59Eシリーズ(3-3494A-00-0000-□200)の生産終了のお知らせとなります。
- 推奨代替商品はACC-59E3シリーズ(3-4027A-00-0211-□200)となります。
- ・プログラムの互換性がないため、プログラミングツールを用いた操作方法が変更となります。

■生産終了商品との相違点

推奨代替商品形式	本体の色	外形寸法	配線接続	取付寸法	定格性能	動作特性	操作方法
3-4027A-00-0211-□200	◎	◎	○	◎	○	○	×

- ◎：互換
○：ほとんど変更ありません／相似性の高い変更
×：変更大
－：該当する仕様がありません

■生産終了商品と推奨代替商品

生産終了商品	推奨代替商品	標準価格(¥)
3-3494A-00-0000-B200	3-4027A-00-0211-B200	オープン価格
3-3494A-00-0000-F200	3-4027A-00-0211-F200	オープン価格

■端子配置／配線接続

生産終了商品 3-3494A-00-0000-□200	推奨代替商品 3-4027A-00-0211-□200
D-Sub オプションと端子台オプションがあります。	D-Sub オプションのみです。
	

■定格／性能

項目	生産終了商品 3-3494A-00-0000-□200	推奨代替商品 3-4027A-00-0211-□200
ADC/DACビット数	12-bit	16-bit
入力チャンネル数	8	16
入力フィルタ	入力カットオフ周波数が固定	プログラム可能な入力フィルタ

■操作方法

生産終了商品 3-3494A-00-0000-□200	推奨代替商品 3-4027A-00-0211-□200
Turbo UMACシステムとPower UMACシステム両方使用可能です。	Power UMACシステムにのみ使用可能です。

本案内に記載の仕様・価格は、発行時点のものです。予告なく変更することがありますので、ご了承ください。
 本案内では主に仕様上の変更点を記載しています。ご使用上の注意事項等、ご使用の際に必要な内容につきましては、必ずカタログ、仕様書、取扱説明書、マニュアル等をお読みください。

参考資料:

3-3494A-00-0000-□200 Part Number

UMAC ACC-59E

I J K L

3	-	3	4	9	4	A	-	0	0	-	0	0	0	0	-				
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	--	--	--	--

I

B – BLACK Front, top and bottom plates (Standard)

F – BLACK Front plate only
Order as Spare Only

R – SILVER Front, top and bottom plates

A – SILVER Front plate only
Order as Spare Only

Plate Options

J

1 - Removable Terminal Blks

2 - DB15 connectors

Connection Options

K

L

00 - No Additional* Options

xx - Factory assigned digits for Additional* Options

Factory Assigned Options

* If Any Additional Option is required, contact factory for digits **K** and **L** (Factory Assigned digits).

3-4027A-00-0211-□200 Part Number

UMAC ACC-59E3

F G H

I J K L

3	-	4	0	2	7	A	-	0	0	-	0				-		2		
---	---	---	---	---	---	---	---	---	---	---	---	--	--	--	---	--	---	--	--

F G H

200 - 16-Channel +/- 10V or 4-20mA 16-Bit A/D Converter board

211 - 16-Channel +/- 10V or 4-20mA 16-Bit A/D Converter and 8-Channel 16-Bit DAC +/- 10V Output

222 - 16-Channel +/- 10V or 4-20mA 16-Bit A/D Converter and 8-Channel 18-Bit DAC +/- 10V Output

I/O Interface

I

B – BLACK Front, top and bottom plates (Standard)

F – BLACK Front plate only
Order as Spare Only

Plate Options

J

2 – Mezzanine Board

I/O Mezzanine

K

L

00 - No Additional* Options
xx - Factory assigned digits for Additional* Options

Factory Assigned Options

* If Any Additional Option is required, contact factory for digits **K** and **L** (Factory Assigned digits).