

**OMRON**

Multi-function Compact Inverter

# 3G3MX2-A2007-V2



## 商品概要

Multi-function Compact Inverter, Three-phase 200 VAC, Applicable motor capacity (ND): 0.75 kW

## 販売状況

2026/02/12 00:00 情報更新

販売状況	販売中
機種区分	標準在庫機種
標準価格(税別)	¥ 96,500

推奨代替品の最新情報につきましては、当社Webサイト([www.fa.omron.co.jp](http://www.fa.omron.co.jp))の「生産終了品/推奨代替品」をご覧ください。  
在庫状況/標準価格の最新情報につきましては、当社Webサイト([www.fa.omron.co.jp](http://www.fa.omron.co.jp))の「在庫状況/標準価格 照会」をご覧ください。

## 詳細情報

### 定格/性能

情報更新 : 2025/11/06

Product name	Inverter
Voltage Class	Three-phase 200 VAC
Applicable motor capacity (ND: Normal load)	0.75 kW
Applicable motor capacity (LD: Light load)	1.1 kW
Rated output capacity (ND: Normal load)	200 V: 1.7 kVA 240 V: 2.0 kVA
Rated output capacity (LD: Light load)	200 V: 2.0 kVA 240 V: 2.4 kVA
Rated output current (ND: Normal load)	5.0 A
Rated output current (LD: Light load)	6.0 A
Degree of protection	Non-cover (IP20)
Control method	Phase-to-phase sinusoidal modulation PWM
Output frequency range	0.01 to 590 Hz (Restrictions apply)
Output frequency accuracy	Digital command: $\pm 0.01\%$ of the max. frequency, Analog command: $\pm 0.2\%$ of the max. frequency (25±10°C)
Frequency setting resolution	0.01 Hz(Digital setting) One-thousandth of the maximum frequency(Analog setting)
Voltage/Frequency characteristics	Sensorless vector control, V/f control with speed feedback V/f characteristics (constant/reduced torque)
Overload current rating	120%/60 sec(Light-load rating (LD)) 150%/60 sec(Normal-load rating (ND))
Acceleration/Deceleration time	0.00 to 3600 s (line/curve arbitrary setting), 2nd acceleration/deceleration setting provided
Carrier frequency modification range	2 to 15 kHz (with Derating)
Starting torque	200%/0.5 Hz (under sensor-less vector control)
Protective Functions	Overcurrent, Overvoltage, Undervoltage, Electronic thermal, Temperature error, Ground-fault current at power-on, Inrush current protection circuit, Overload limit, Incoming overvoltage, External trip, Memory error, CPU error, USP error, Communication error, Overvoltage suppression during deceleration, Power interruption protection, Emergency shutoff, Analog current input, STO internal error, etc.

Multi-function inputs	7 point
Analog inputs	2 point
Ambient temperature (Operating)	-10 to 50 °C (Derating required)
Ambient temperature (Storage)	-20 to 65 °C (During shipment)
Ambient humidity (Operating)	20 to 90% (with no condensation)
Vibration resistance	10 to 55 Hz 5.9 m/s <sup>2</sup> (0.6G)
Width	68 mm
Height	128 mm
Depth	145.5 mm
Weight	Approx. 1.2 kg(Main Unit)

## RoHS/REACH対応状況

情報更新：2026/2/04

3G3MX2-A2007-V2のRoHS対応状況については、営業部門もしくは販売店にお問い合わせください。

## 注意事項・凡例

"対応済み"で記載される商品であっても、流通在庫等で未対応品が混在する可能性があります。  
非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

### ※1 対応状況

- ・ **(Ro) 対応済み** : EU RoHS指令（10物質）の非含有に対応した製品が提供可能な商品です。
- ・ 対応予定 : EU RoHS指令（10物質）の非含有に対応した製品に切り替える予定のある商品です。
- ・ 対応予定なし : EU RoHS指令（10物質）の非含有に非対応の商品で、対応品を出す予定はありません。
- ・ 調査・確認中 : EU RoHS指令（10物質）の非含有の対応状況を調査中または確認中の商品です。
- ・ 非該当品 : ライセンス料など無形物で、有害物質有無と関係のない商品です。

仕入先様の事情により、非含有部品としていたものが、含有品と判明した場合などやむを得ず変更することがあります。

\* EU RoHS指令（10物質） :

鉛(Pb) 1000ppm以下、水銀(Hg) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、  
ポリ臭化ビフェニル類(PBB) 1000ppm以下、ポリ臭化ジフェニルエーテル類(PBDE) 1000ppm以下、  
フタル酸ビス(2-エチルヘキシル) (DEHP)(別名:DOP) 1000ppm以下、フタル酸ブチルベンジル (BBP) 1000ppm以下、  
フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジイソブチル (DIBP) 1000ppm以下  
但し、RoHS指令で産業用監視および制御機器に対する適用除外項目は除く。  
フタル酸エステル類の4物質については閾値を超える意図的な使用がないことを確認しています。

### ※2 対応予定月

部品在庫の切り替え状況などにより、予定月が前後することがあります。

### ※3 非含有証明書ダウンロード

下記の非含有証明書をダウンロードすることができます。

- ・ EU RoHS指令（10物質）の非含有証明書
- ・ 49物質の非含有証明書（当社基準）

※ 本証明書は発行日時点で非含有を証明するもので、過去に遡って非含有を証明するものではありません。

また、RoHS指令のフタル酸エステル類4物質の対応では、対応完了までの期間は出荷製品に未対応品が混在することから備考欄に  
対応日を記載しておりました。

既に当社にて対応品への在庫切替を完了していることから、特段のことがない限り、2022年1月12日より割愛しております。

## 規格認証/適合状況

UL認証	CSA認証	CEマーキング適合	CCC認証
Yes	Yes	Yes	N/A

LR型式承認 (イギリス 船舶規格)	DNV型式承認 (ノルウェー 船舶規格)	BV型式承認 (フランス 船舶規格)	KR型式承認 (韓国 船舶規格)	NK型式承認 (日本 船舶規格)	ABS型式承認 (アメリカ 船舶規格)
No	No	No	No	No	No

[この製品の規格認証/適合状況ページへ>](#)  
[その他の認証はこちらのページからご検索ください>](#)

## 関連商品

No Image

DC Reactor

[3G3AX-DL2007](https://www.fa.omron.co.jp/product/item/3G3AX-DL2007)



EtherCAT Communication Unit

[3G3AX-MX2-ECT](https://www.fa.omron.co.jp/product/item/3G3AX-MX2-ECT)



Digital Operator

[3G3AX-OP01](https://www.fa.omron.co.jp/product/item/3G3AX-OP01)

No Image

No Image

No Image

Connecting Cable for Digital Operator

[3G3AX-OPCN3](https://www.fa.omron.co.jp/product/item/3G3AX-OPCN3)

Braking Resistor

[3G3AX-RBA1201](https://www.fa.omron.co.jp/product/item/3G3AX-RBA1201)

Radio Noise Filter

[3G3AX-ZCL2](https://www.fa.omron.co.jp/product/item/3G3AX-ZCL2)