

## Catalog Correction Notice

Catalog

Issue Date  
March 1, 2018  
No. 2018002DE

The mistake of the print and the description is found in the catalog that our company issued. We apologize.

### [ Name of catalog ]

" C200H I/O Terminal Block Conversion Adapter CATALOG "  
< Publication in March, 2015 > < Catalog number CSM001039288 >

### [ Page of publishing ]



Page 2 Ordering Information  
Page 3 Connection of I/O Units and Terminal Block Conversion Adapter

### [ Correction method ]

The catalog is revised.

### [ Content of correction ]

Page 2 Ordering Information

		Terminal Block Conversion Adapter			
		Product name	Specifications	Model	Standards
Before		C200H I/O Terminal Block Conversion Adapter	8-points, 10-pin type	CS1W-AT201	---
			8-points, 19-pin type	CS1W-AT202	---
			16-points, 19-pin type	CS1W-AT211	---
			16-points, 19-pin type (for C200H-OD21A)	CS1W-AT212	---
After		CS1W-AT212 is removed.			
		Terminal Block Conversion Adapter			
		Product name	Specifications	Model	Standards
		C200H I/O Terminal Block Conversion Adapter	8-points, 10-pin type	CS1W-AT201	---
			8-points, 19-pin type	CS1W-AT202	---
	16-points, 19-pin type	CS1W-AT211	---		

[ Content of correction ]

Page 3 Connection of I/O Units and Terminal Block Conversion Adapter

Before							
Before	CS1W-AT211	Transistor Output Unit	0.3 A at 24 VDC, 12 outputs, sinking	C200H-OD211	Transistor Output Unit	0.5 A at 12 to 24 VDC, 16 outputs	CS1W-OD211
			0.3 A at 24 VDC, 16 outputs, sinking	C200H-OD212			CS1W-OD211
			0.3 A at 5 to 24 VDC, 12 outputs, sourcing	C200H-OD217			CS1W-OD212
		Triac Output Unit	0.8 A at 250 VAC max, 16 outputs	C200H-OA225	Triac Output Unit	0.5 A at 250 VAC max., 16 outputs	CS1W-OA211
			0.3 A at 250 VAC max, 12 outputs	C200H-OA222			CS1W-OA211
			0.3 A at 250 VAC max, 12 outputs	C200H-OA222V			CS1W-OA211
	CS1W-AT202	Relay Output Unit	2 A at 250 VAC/24 VDC max., independent contacts, 8 outputs	C200H-OC224	Relay Output Unit	2 A at 250 VAC/24 VDC max., 0.1 A at 120 VDC, independent contacts, 8 outputs	CS1W-OC201
			2 A at 250 VAC/24 VDC max., independent contacts, 8 outputs	C200H-OC224V			CS1W-OC201
			2 A at 250 VAC/24 VDC max., independent contacts, 8 outputs	C200H-OC224N			CS1W-OC201
		CS1W-AT212	Transistor Output Unit	1 A at 24 VDC, 16 outputs, sourcing, load short-circuit protection	C200H-OD21A	Transistor Output Unit	0.5 A at 24 VDC, 16 outputs
After	CS1W-AT211 is adapted to C200H-OD21A.						
	CS1W-AT211	Transistor Output Unit	0.3 A at 24 VDC, 12 outputs, sinking	C200H-OD211	Transistor Output Unit	0.5 A at 12 to 24 VDC, 16 outputs	CS1W-OD211
			0.3 A at 24 VDC, 16 outputs, sinking	C200H-OD212			CS1W-OD211
			0.3 A at 5 to 24 VDC, 12 outputs, sourcing	C200H-OD217			CS1W-OD212
		Triac Output Unit	0.8 A at 250 VAC max, 16 outputs	C200H-OA225	Triac Output Unit	0.5 A at 250 VAC max., 16 outputs	CS1W-OA211
			0.3 A at 250 VAC max, 12 outputs	C200H-OA222			CS1W-OA211
			0.3 A at 250 VAC max, 12 outputs	C200H-OA222V			CS1W-OA211
	0.5 A at 250 VAC max, 12 outputs		C200H-OA224	CS1W-OA211			
	CS1W-AT202	Relay Output Unit	2 A at 250 VAC/24 VDC max., independent contacts, 8 outputs	C200H-OC224	Relay Output Unit	2 A at 250 VAC/24 VDC max., 0.1 A at 120 VDC, independent contacts, 8 outputs	CS1W-OC201
			2 A at 250 VAC/24 VDC max., independent contacts, 8 outputs	C200H-OC224V			CS1W-OC201
2 A at 250 VAC/24 VDC max., independent contacts, 8 outputs			C200H-OC224N	CS1W-OC201			

Specifications in this product news are as of the issue date and are subject to change without notice. Only main changes in specifications are described in this document. Please be sure to read the relevant catalogs, datasheets, product specifications, instructions, and manuals for precautions and necessary information when using products.