

Safety Limit Switch

D4B-4115N



商品概要

Safety Limit Switch, M20, 1-conduit, 1NC/1NO (snap-action), Roller lever (stainless steel roller)

販売状況

2026/03/30 00:00 情報更新

販売状況	販売中
機種区分	標準在庫機種
標準価格(税別)	¥ 7,000

推奨代替品の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「生産終了品/推奨代替品」をご覧ください。
在庫状況/標準価格の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「在庫状況/標準価格照会」をご覧ください。

詳細情報

定格/性能

情報更新：2025/12/01

Life expectancy	General type
Operating mechanism	Snap action
Rated frequency	50/60 Hz
Contact form	1NC/1NO
Load	General load
AC	(Lamp load (NC)) 0.8 A at 400 VAC(Lamp load (NO)) 0.8 A at 400 VAC(Motor load (NO)) 1 A at 250 VAC(Lamp load (NO)) 1.5 A at 125 VAC(Lamp load (NO)) 1.5 A at 250 VAC(Motor load (NO)) 1.5 A at 400 VAC(Lamp load (NC)) 1.5 A at 400 VAC(Motor load (NC)) 10 A at 125 VAC(Inductive load) 10 A at 125 VAC(Resistive load) 10 A at 250 VAC(Inductive load) 10 A at 250 VAC(Resistive load) 10 A at 400 VAC(Resistive load) 2 A at 250 VAC 2.5 A at 125 VAC(Motor load (NO)) 3 A at 125 VAC(Lamp load (NC)) 3 A at 250 VAC(Motor load (NC)) 3 A at 400 VAC(Inductive load) 5 A at 125 VAC(Motor load (NC))
DC	0.1 A at 250 VDC(Lamp load (NC)) 0.1 A at 250 VDC(Lamp load (NO)) 0.1 A at 250 VDC(Motor load) 0.2 A at 125 VDC(Lamp load (NC)) 0.2 A at 125 VDC(Lamp load (NO)) 0.2 A at 125 VDC(Motor load) 0.4 A at 250 VDC(Inductive load) 0.4 A at 250 VDC(Resistive load) 0.8 A at 125 VDC(Inductive load) 0.8 A at 125 VDC(Resistive load) 10 A at 14 VDC(Inductive load) 10 A at 14 VDC(Resistive load) 10 A at 8 VDC(Inductive load) 10 A at 8 VDC(Resistive load) 3 A at 14 VDC(Lamp load (NO)) 3 A at 30 VDC(Lamp load (NO)) 3 A at 8 VDC(Lamp load (NO)) 4 A at 30 VDC(Lamp load (NC)) 4 A at 30 VDC(Motor load) 6 A at 14 VDC(Lamp load (NC)) 6 A at 14 VDC(Motor load) 6 A at 30 VDC(Inductive load) 6 A at 30 VDC(Resistive load) 6 A at 8 VDC(Lamp load (NC)) 6 A at 8 VDC(Motor load)
Inrush current	30 A max.
Conduit	M20
Ground	With ground terminal
Ambient temperature (Operating)	-40 to 80 °C (with no icing)
Ambient humidity (Operating)	95% max.
Permissible operating speed	1 mm/s to 0.5 m/s
Permissible operating frequency	120 operations / 1 minute max.(Mechanical) 30 operations / 1 minute max.(Electrical)
Contact resistance (Initial value)	25 mΩ max.
Insulation resistance	100 MΩ min.(Between each terminal and non-live-metallic part) 100 MΩ min.(Between each terminal of the same polarities) at 500 VDC
Impulse withstand voltage	2.5 kV(Between each terminal of the same polarities) 4 kV(Between each terminal and ground)

Endurance	30 million operations min.(Mechanical) 500,000 operations min. (10 A at 250 VAC)(Electrical)
Vibration resistance	10 to 55 Hz, 0.75 mm single amplitude(Malfunction)
Shock resistance	1000 m/s ² min.(Destruction) 300 m/s ² min.(Malfunction)
Degree of protection	IP67
Classification of protection against electric shock	Class I (with ground terminal)
Operating Force (OF)	Standard value 9.41 N max.
Release Force (RF)	Standard value 1.47 N min.
Pre-Travel	Standard value 21±3 °
Movement Differential	Standard value 12 ° max.
Over-Travel	Standard value 50 ° min.
Total travel (TT)	Reference value 75 °
Direct Opening Force (DOF)	Standard value 19.61 N min.
Direct Opening Travel	Standard value 55 ° min.
Durability curve	S093_D4B-2111N_E.jpg(Electrical)

RoHS/REACH対応状況

情報更新：2026/4/15

EU RoHS

対応状況 ※1	対応予定月 ※2	非含有証明書 ※3
 対応済み		ダウンロードはこちら

中国 RoHS

中国 RoHS表 ※1※2										
Pb	Hg	Cd	Cr(VI)	PBBs	PBDEs	DBP	DIBP	BBP	DEHP	環境保護 使用期限
○	○	X	○	○	○	○	○	○	○	10

- ・“対応済み”や非含有の記載がされた商品であっても、流通在庫等で未対応品が混在する可能性があります。
- ・非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

[この製品のRoHS/REACH対応状況ページへ>](#)

注意事項・凡例

”対応済み”で記載される商品であっても、流通在庫等で未対応品が混在する可能性があります。
非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

※1 対応状況

- ・  対応済み : EU RoHS指令（10物質）の非含有に対応した製品が提供可能な商品です。
- ・ 対応予定 : EU RoHS指令（10物質）の非含有に対応した製品に切り替える予定のある商品です。
- ・ 対応予定なし : EU RoHS指令（10物質）の非含有に非対応の商品で、対応品を出す予定はありません。
- ・ 調査・確認中 : EU RoHS指令（10物質）の非含有の対応状況を調査中または確認中の商品です。
- ・ 非該当品 : ライセンス料など無形物で、有害物質有無と関係のない商品です。

仕入先様の事情により、非含有部品としていたものが、含有品と判明した場合などやむを得ず変更することがあります。

* EU RoHS指令（10物質）：

鉛(Pb) 1000ppm以下、水銀(Hg) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、
ポリ臭化ビフェニル類(PBB) 1000ppm以下、ポリ臭化ジフェニルエーテル類(PBDE) 1000ppm以下、
フタル酸ビス(2-エチルヘキシル) (DEHP)(別名：DOP) 1000ppm以下、フタル酸ブチルベンジル (BBP) 1000ppm以下、
フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジイソブチル (DIBP) 1000ppm以下
但し、RoHS指令で産業用監視および制御機器に対する適用除外項目は除く。
フタル酸エステル類の4物質については閾値を超える意図的な使用がないことを確認しています。

※2 対応予定月

部品在庫の切り替え状況などにより、予定月が前後することがあります。

※3 非含有証明書ダウンロード

下記の非含有証明書をダウンロードすることができます。

- ・ EU RoHS指令（10物質）の非含有証明書
- ・ 49物質の非含有証明書（当社基準）

※ 本証明書は発行日時時点で非含有を証明するもので、過去に遡って非含有を証明するものではありません。

また、RoHS指令のフタル酸エステル類4物質の対応では、対応完了までの期間は出荷製品に未対応品が混在することから備考欄に
対応日を記載しておりました。

既に当社にて対応品への在庫切替を完了していることから、特段のことがない限り、2022年1月12日より割愛しております。

規格認証/適合状況

D4B-4115Nについての規格認証/適合状況については、「カスタマーサポートセンタ お客様相談室」または貴社担当オムロン営業員または販売店にお問い合わせください。