

OMRON

モジュール型温度調節計

EJ1N-TC2B-CNB



商品概要

Modular Temperature Controller, Current output/Transistor output, Control points: 2 points, Screwless clamp terminals, CT input None, EV input 2 points

販売状況

2026/02/02 00:00 情報更新

販売状況	販売中
機種区分	標準在庫機種
標準価格(税別)	¥ 60,500

推奨代替品の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「生産終了品/推奨代替品」をご覧ください。
在庫状況/標準価格の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「在庫状況/標準価格 照会」をご覧ください。

詳細情報

Ratings / Performance

情報更新 : 2025/11/04

Ratings

Shape	Module type
Fixed/Programmable	Fixed
Power supply voltage	24 VDC
Allowable voltage variable range	85 to 110% of the power supply voltage
Power consumption	2.5 W max. (At maximum load)
Input	<p>Number of input points</p> <p>Temperature input</p> <p>Analog input</p> <p>Input impedance</p>
	<p>2 point</p> <p>Thermocouple: K, J, T, E, L, U, N, R, S, B, C/W, PLII Platinum resistance thermometer: Pt100, JPt100 Infrared Thermosensor: 10 to 70 °C, 60 to 120 °C, 115 to 165 °C, 140 to 260 °C</p> <p>4 to 20 mA or 0 to 20 mA</p> <p>Current input: 150 Ω max., voltage input: 1 MΩ min.</p>
Control method	ON/OFF or 2-PID control with auto-tuning and self-tuning
Control output	<p>Number of total control output</p> <p>Control output 1</p> <p>Control output 2</p> <p>Transistor output</p> <p>Current output</p>
	<p>2 point</p> <p>Current output 2-points</p> <p>Transistor output 2-points</p> <p>2 point Maximum operating voltage: 30 VDC Maximum load current: 100 mA</p> <p>2 point 4 to 20 mA DC / 0 to 20 mA DC, Load: 500 Ω max., Resolution: approx. 10000</p>
Event input	<p>2 point</p> <p>Contact input: ON: 1 kΩ max., OFF: 100 kΩ min. No-contact input: ON: Residual voltage 1.5 V max., OFF: Leakage current 0.1 mA max. Short-circuit current: Approx. 4 mA per point</p>
Sampling period	250 ms
Hysteresis	0.1 to 999.9 EU (in units of 0.1 EU)
Proportional band	0.1 to 999.9 EU (in units of 0.1 EU)
Integral time	0 to 3999 s (in units of 1 s)
Derivative time	0.0 to 999.9 s (in units of 0.1 s)
Control period	0.5 s or 1 to 99 s (in units of 1 s)

Manual reset value	0.0 to 100.0% (in units of 0.1%)
Insulation resistance	20 MΩ min. (at 500 VDC)
Dielectric strength	600 VAC 50/60 Hz for 1 min (Between current-carrying terminals of different polarity)
Vibration resistance	Malfunction: 10 to 55 Hz, 20 m/s ² for 2 h each in X, Y, and Z directions
Shock resistance	Malfunction: 150 m/s ² , in each 6 directions 3 times
Ambient temperature (Operating)	-10 to 55 °C (with no freezing or condensation) For 3-year warranty: -10 to 50 °C (with no freezing or condensation)
Ambient temperature (Storage)	-25 to 65 °C (with no freezing or condensation)
Ambient humidity (Operating)	25 to 85 % (with no freezing or condensation)
Degree of protection	Rear case: IP20, Terminal section: IP00
Memory protection	Non-volatile memory (number of writes: 100,000)
Terminal type	Screwless clamp terminals
Weight	Approx. 160 g
Sold separately	CX-Thermo Support Software: EST2-2C-MV4 USB Serial Conversion Cable: E58-CIFQ1 Connecting Cable for G3ZA: EJ1C-CBLA050 DIN Tracks: PFP-50N/PFP-100N End Unit: EJ1C-EDUA-NFLK/EJ1C-EDUC-NFLK

Accuracy

Indication accuracy	Thermocouple: ($\pm 0.3\%$ PV or $\pm 1\text{ }^\circ\text{C}$ whichever is larger) ± 1 digit max. Platinum resistance thermometer: ($\pm 0.2\%$ PV or $\pm 0.8\text{ }^\circ\text{C}$ whichever is larger) ± 1 digit max. Analog input: ($\pm 0.2\%$ FS) ± 1 digit max. (The indication accuracy of K thermocouples in the -200 to 1300 °C range, T and N thermocouples at a temperature of -100 °C max., and U and L thermocouples at any temperatures is $\pm 2\text{ }^\circ\text{C} \pm 1$ digit max. K thermocouples in the -199.9 to 999.9 °C range is ($\pm 0.5\%$ PV or $\pm 1\text{ }^\circ\text{C}$, whichever is greater) ± 10 digit maximum. K thermocouples in the -100 °C maximum range is $\pm 2\text{ }^\circ\text{C} + \pm 10$ digit maximum. B thermocouple at a temperature of 400 °C maximum is not specified. R and S thermocouples at a temperature of 200 °C maximum is $\pm 3\text{ }^\circ\text{C} \pm 1$ digit max. W/C thermocouples is ($\pm 0.5\%$ PV or $\pm 3\text{ }^\circ\text{C}$, whichever is greater) ± 1 digit max. PL II thermocouples is ($\pm 0.5\%$ PV or $\pm 2\text{ }^\circ\text{C}$, whichever is greater) ± 1 digit max.)
Influence of signal source resistance	Thermocouple: 0.1 °C (0.2 °F)/Ω max. (100 Ω max. per line) Platinum resistance thermometer: 0.1 °C (0.2 °F)/Ω max. (10 Ω max. per line)


Communication characteristics

Transmission path connection	Multipoint (RS-485)
Communications method	RS-485 (two-wire, half duplex)
Synchronization method	Start-stop synchronization

Protocol	Port A/G3ZA Connection Port: CompoWay/F, Port B: CompoWay/F, Modbus
Communication speed	Port A: 38400 bps (fixed) Port B: 9600, 19200, 38400, 57600, 115200 bps G3ZA Connection Port: 57600 bps (fixed)
Transmission code	Port A Terminal/G3ZA Connection Port: CompoWay/F: ASCII
Data bit length	Port A/G3ZA Connection Port: 7 bits Port B: 7 or 8 bits
Stop bit length	Port A/G3ZA Connection Port: 2 bits Port B: 1 or 2 bits
Error detection	Port A/G3ZA Connection Port: Vertical parity (even) Port B: Vertical parity (none, even, odd) Block check character (BCC) with CompoWay/F CRC-16 Modbus
Flow control	None
Retry function	None
Number of Units that can be connected in parallel	Port A: 64 Units (128 channels, Communications connection via port A on the End Unit) Port B: 64 Units (128 channels, Communications connection via port B on the End Unit) G3ZA Connection Port: 8 Units (Communications connection via G3ZA port on the Basic Unit)
Communications response send delay	Port A: 1 to 99 ms (Default: 1 ms) Port B: 0 to 99 ms (Default: 5 ms)

Connection diagram

情報更新 : 2025/11/04



Input ranges list

情報更新 : 2025/11/04

Input Ranges

Sensor inputs are fully universal. Therefore, platinum resistance thermometer, thermocouple, infrared thermosensor, and analog input can be selected. Inputs can be set for each channel using universal inputs.

Input type	Platinum resistance thermometer		Thermocouple										ES1B Infrared Thermosensor							
	Name		Pt100	JPt100	K	J	T	E	L	U	N	R	S	B	WIC	PL II	10 to 70 °C	60 to 120 °C	115 to 165 °C	140 to 260 °C
Temperature range (°C)	2300																			
	1800																			
	1700																			
	1600																			
	1500																			
	1400																			
	1300																			
	1200																			
	1100																			
	1000																			
	850																			
	500.0																			
	500.0																			
	100.0																			
	0.0																			
	0																			
	-100.0																			
	-200.0																			
Setting number	0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19
	20	21	22	23	24															

Input type	Analog input					Thermo couple
	Name	4 to 20 mA	0 to 20 mA	1 to 5 V	0 to 5 V	
Temperature range (°C)	2300					K
	1800					
	1700					
	1600					
	1500					
	1400					
	1300					
	1200					
	1100					
	1000	Any of the following ranges, by scaling:				
	900	-1999 to 9999				
	800	-199.9 to 999.9				
	700	-19.99 to 99.99				
	600	-1.999 to 9.999				
	500					
	400					
	300					
	200					
	100					
	0					
	-100.0					
	-200.0					
Setting number	25	26	27	28	29	30

Applicable standards by input type are as follows:

K, J, T, E, N, R, S, B: JIS C1602-2015, IEC60584-1

L: Fe-CuNi, DIN 43710-1985

U: Cu-CuNi, DIN 43710-1985

W/C: W5Re/W26Re, JIS C 1602-2015, ASTM E988-1990

PL II: ASTM E1751-000

JPt100: JIS C 1604-1989, JIS C 1606-1989

Pt100: JIS C 1604-1997, IEC 60751

 Shaded ranges indicate default settings.

RoHS/REACH対応状況

情報更新：2026/1/21

EU RoHS

対応状況 ※1	対応予定期間 ※2	非含有証明書 ※3
 対応済み		ダウンロードはこちら

中国 RoHS

中国 RoHS表 ※1※2										
Pb	Hg	Cd	Cr(VI)	PBBs	PBDEs	DBP	DIBP	BBP	DEHP	環境保護使用期限
X	0	0	0	0	0	0	0	0	0	10

- ・“対応済み”や非含有の記載がされた商品であっても、流通在庫等で未対応品が混在する可能性があります。
- ・非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

[この製品のRoHS/REACH対応状況ページへ>](#)

注意事項・凡例

"対応済み"で記載される商品であっても、流通在庫等で未対応品が混在する可能性があります。
非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

※1 対応状況

- ・ **対応済み** : EU RoHS指令（10物質）の非含有に対応した製品が提供可能な商品です。
- ・ 対応予定 : EU RoHS指令（10物質）の非含有に対応した製品に切り替える予定のある商品です。
- ・ 対応予定なし : EU RoHS指令（10物質）の非含有に非対応の商品で、対応品を出す予定はありません。
- ・ 調査・確認中 : EU RoHS指令（10物質）の非含有の対応状況を調査中または確認中の商品です。
- ・ 非該当品 : ライセンス料など無形物で、有害物質有無と関係のない商品です。

仕入先様の事情により、非含有部品としていたものが、含有品と判明した場合などやむを得ず変更することがあります。

* EU RoHS指令（10物質） :

鉛(Pb) 1000ppm以下、水銀(Hg) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、
ポリ臭化ビフェニル類(PBB) 1000ppm以下、ポリ臭化ジフェニルエーテル類(PBDE) 1000ppm以下、
フタル酸ビス(2-エチルヘキシル) (DEHP)(別名:DOP) 1000ppm以下、フタル酸ブチルベンジル (BBP) 1000ppm以下、
フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジイソブチル (DIBP) 1000ppm以下
但し、RoHS指令で産業用監視および制御機器に対する適用除外項目は除く。
フタル酸エステル類の4物質については閾値を超える意図的な使用がないことを確認しています。

※2 対応予定月

部品在庫の切り替え状況などにより、予定月が前後することがあります。

※3 非含有証明書ダウンロード

下記の非含有証明書をダウンロードすることができます。

- ・ EU RoHS指令（10物質）の非含有証明書
- ・ 49物質の非含有証明書（当社基準）

※ 本証明書は発行日時点で非含有を証明するもので、過去に遡って非含有を証明するものではありません。

また、RoHS指令のフタル酸エステル類4物質の対応では、対応完了までの期間は出荷製品に未対応品が混在することから備考欄に
対応日を記載しておりました。

既に当社にて対応品への在庫切替を完了していることから、特段のことがない限り、2022年1月12日より割愛しております。

規格認証/適合状況

UL認証	CSA認証	CEマーキング適合	CCC認証
Yes	Yes	Yes	N/A

LR型式承認 (イギリス 船舶規格)	DNV型式承認 (ノルウェー 船舶規格)	BV型式承認 (フランス 船舶規格)	KR型式承認 (韓国 船舶規格)	NK型式承認 (日本 船舶規格)	ABS型式承認 (アメリカ 船舶規格)
No	No	No	No	No	No

[この製品の規格認証/適合状況ページへ>](#)

[その他の認証はこちらのページからご検索ください>](#)