


小形パワーリレー

MKS2P-2 AC110



商品概要

General-purpose Relay, DPDT, Plug-in Terminal, Mechanical indicator, Non-standard connections, 110 VAC

販売状況 2025/12/18 00:00 情報更新

販売状況	販売中
機種区分	受注生産機種
標準価格(税別)	¥ 2,650

推奨代替品の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「生産終了品/推奨代替品」をご覧ください。 在庫状況/標準価格の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「在庫状況/標準価格 照会」をご覧ください。

情報更新: 2025/06/17

詳細情報

Ratings / Performance

Ratings

Operating indicator	Mechanical indicator		
Degree of protection	Closed type (cover)		
Terminal structure		Plug-in terminal	
Coil	Coil ratings	110 VAC 50 Hz 24.2 mA 110 VAC 60 Hz 21.0 mA	
	Coil resistance	932 Ω	
	Operate voltage (Set voltage)	80 % max.	
	Release voltage (Reset voltage)	25 % min. (50 Hz) 30 % min. (60 Hz)	
	Maximum voltage	110 %	
	Power consumption	Approx. 2.7 VA 50 Hz/Approx. 2.3 VA 60 Hz	
Contact	Contact rated load	250 VAC 10 A (NO contact: Resistive load) 250 VAC 5 A (NC contact: Resistive load) 250 VAC 7 A (Inductive load (cosφ = 0.4)) 30 VDC 10 A (NO contact: Resistive load) 30 VDC 5 A (NC contact: Resistive load)	
	Max. contact voltage	250 VAC 250 VDC	
	Max. contact current	AC: 10 A DC: 10 A	
	Maximum switching power	2500 VA (NO contact: Resistive load) 1250 VA (NC contact: Resistive load) 1750 VAAC (Inductive load (cosφ = 0.4)) 300 W (NO contact: Resistive load) 150 W (NC contact: Resistive load)	
	Contact form	DPDT	
	Contact method	Single	
	Contact material	Ag alloy	

Performance


Contact resistance	$100\text{m}\Omega$ max. (Voltage drop method with 5 VDC 1 A)
Operating time	20 ms max. (With rated operating power applied, 23 °C, not including contact bounce)
Reset time	20 ms max. (With rated operating power applied, 23 °C, not including contact bounce)

Maximum operating frequency	Mechanical: 18000 time/hour Rated load: 1800 time/hour
Insulation resistance	Between coil and contacts: 100 M Ω min. (at 500 VDC) Between contacts of different polarity: 100 M Ω min. (at 500 VDC) Between contacts of same polarity: 100 M Ω min. (at 500 VDC)
Dielectric strength	Between coil and contacts: 2500 VAC 50/60 Hz 1 min Between contacts of different polarity: 2500 VAC 50/60 Hz 1 min Between contacts of same polarity: 1000 VAC 50/60 Hz 1 min
Vibration resistance (destruction)	10 to 55 to 10 Hz, 0.75 mm single amplitude (1.5 mm double amplitude)
Vibration resistance (Malfunction)	10 to 55 to 10 Hz, 0.5-mm single amplitude (1-mm double amplitude)
Shock resistance (destruction)	1000 m/s ²
Shock resistance (Malfunction)	100 m/s ²
Endurance (Mechanical)	5,000,000 operations min. (switching frequency 1,800 operations/h)
Endurance (Electrical)	100,000 operations min. (23 °C, Rated load, switching frequency 1,800 operations/h)
Failure rate	1 VDC 10 mA (failure level: Preference value, Switching frequency: 30 operations per minute)
Ambient temperature (Operating)	-40 to 60 °C
Ambient humidity (Operating)	5 to 85 %
Weight	Approx. 90 g
Mounting method	Socket
Applicable socket	PF083A-E/ PF083A

情報更新: 2025/06/17

Dimensions

Outline drawing




情報更新: 2025/06/17

Terminal arrangement and internal connection

Terminal arrangement and internal connection


Standard Models (AC/DC Coil)



Characteristic chart
Switching capacities

情報更新: 2025/06/17

Maximum Switching Power



RoHS/REACH対応状況

情報更新: 2025/12/17

EU RoHS

対応状況 ※1	対応予定月 ※2	非含有証明書 ※3
® 対応済み		ダウンロードはこちら

中国 RoHS

中国 RoHS表 ※ 1 ※ 2										
Pb	Hg	Cd	Cr(VI)	PBBs	PBDE s	DBP	DIBP	BBP	DEH P	環境 保護 使用 期限
0	0	0	0	0	0	0	0	0	0	е

- ・"対応済み"や非含有の記載がされた商品であっても、流通在庫等で未対応品が混在する可能性があります。
- ・非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

この製品のRoHS/REACH対応状況ページへ >

注意事項 • 凡例

"対応済み"で記載される商品であっても、流通在庫等で未対応品が混在する可能性があります。 非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

※1 対応状況

・ le y RoHS指令 (10物質) の非含有に対応した製品が提供可能な商品です。

対応予定 : EU RoHS指令 (10物質) の非含有に対応した製品に切り替える予定のある商品です。
 対応予定なし : EU RoHS指令 (10物質) の非含有に非対応の商品で、対応品を出す予定はありません。
 調査・確認中 : EU RoHS指令 (10物質) の非含有の対応状況を調査中または確認中の商品です。

・非該当品 :ライセンス料など無形物で、有害物質有無と関係のない商品です。

仕入先様の事情により、非含有部品としていたものが、含有品と判明した場合などやむを得ず変更することがあります。

* EU RoHS指令(10物質):

鉛(Pb) 1000ppm以下、水銀(Hg) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、ポリ臭化ビフェニル類(PBB) 1000ppm以下、ポリ臭化ジフェニルエーテル類(PBDE) 1000ppm以下、フタル酸ビス(2-エチルヘキシル) (DEHP)(別名:DOP) 1000ppm以下、フタル酸ブチルベンジル (BBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ンプチル (DBP) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、プタル酸ブチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、カルマンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチル (DBP) 1000ppm以下、フタル酸シスタル酸シスタル酸シスタル酸シスタル酸シスタル (DBP) 1000ppm以下、フタル酸シスタル (DBP) 1000ppm以下、DBP (DBP) 1000ppm以下、D

※2 対応予定月

部品在庫の切り替え状況などにより、予定月が前後することがあります。

※3 非含有証明書ダウンロード

下記の非含有証明書をダウンロードすることができます。

- ・EU RoHS指令(10物質)の非含有証明書
- ・49物質の非含有証明書(当社基準)
- ※本証明書は発行日時点で非含有を証明するもので、過去に遡って非含有を証明するものではありません。

また、RoHS指令のフタル酸エステル類 4 物質の対応では、対応完了までの期間は出荷製品に未対応品が混在することから備考欄に対応日を記載しておりました。

既に当社にて対応品への在庫切替を完了していることから、特段のことがない限り、2022年1月12日より割愛しております。

規格認証/適合状況

UL認証	CSA認証	CEマーキング適合	CCC認証
Yes	Yes	Yes	N/A

LR型式承認	DNV型式承認	BV型式承認	KR型式承認	NK型式承認	ABS型式承認
(イギリス	(ノルウェー	(フランス	(韓国	(日本	(アメリカ
船舶規格)	船舶規格)	船舶規格)	船舶規格)	船舶規格)	船舶規格)
No	No	No	No	No	No

この製品の規格認証/適合状況ページへ > その他の認証はこちらのページからご検索ください >