NXシリーズ 温度調節ユニット

# NX-TC2407



# 商品概要

Temperature Control Unit, Number of input 2 point, Voltage output (for driving SSR) 4 point, Heating/cooling control

## 販売状況

2026/11/19 00:00 情報更新

| | |
|---|---|
| 販売状況 | 販売中 |
| 機種区分 | 標準在庫機種 |
| 標準価格(税別) | ¥ 70,500 |

推奨代替品の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「生産終了品/推奨代替品」をご覧ください。
在庫状況/標準価格の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「在庫状況/標準価格 照会」をご覧ください。

# 詳細情報

## Ratings / Performance

情報更新：2024/08/08

### Ratings and Specifications

| | | |
|---|---|---|
| Number of Channels | | 2 CH |
| External connection method | | Screwless clamping terminal block (16 terminals) |
| Input type | | Temperature Sensor |
| I/O refreshing method | | Free-Run refreshing |
| NX Unit power consumption | | Connected to a CPU Unit: 1.30 W max.<br>Connected to Communications Coupler Unit: 1.00 W max. |
| Isolation method | | Between sensor inputs and internal circuitry: Transformer for power supply and digital isolator for signals.<br>Between inputs: Transformer for power supply and digital isolator for signals.<br>Between control outputs and internal circuits: Photocoupler isolation<br>Between control outputs: Not isolated |
| Heater burnout alarm | | None |
| Input | Temperature input | K, J, T, E, L, U, N, R, S, B, C/W, PL II , Pt100 (Three-wires) , JPt100 (Three-wires) , Pt1000 (Three-wires) |
| | Influence of conductor resistance | Thermocouple input: 0.1 °C/Ω (100 Ω or less per conductor)<br>Platinum resistance thermometer input: 0.06 °C/Ω (20 Ω or less per conductor) |
| | Conversion time | 50 ms/Unit |
| | Input detection current | 0.25 mA |
| | Resolution | 0.1 °C max. |
| Output | Number of outputs | 4 point |
| | Rated voltage | 24 VDC |
| | Operating Load Voltage Range | 15 to 28.8 VDC |
| | Output type | Voltage output (for driving SSR) |
| | Internal I/O common processing | PNP |
| | Maximum load current | 21 mA/point, 84 mA/Unit |
| Insulation resistance | | Between isolated circuits: 20 MΩ min. (100 VDC) |
| Dielectric strength | | Between isolated circuits: 510 VAC 1 min, leakage current 5 mA max. |
| Vibration resistance | | Conforms to IEC60068-2-6, 5 to 8.4 Hz with 3.5-mm amplitude, 8.4 to 150 Hz acceleration 9.8 $m/s^2$, each in X, Y, and Z directions for 100 min (10 |

| | |
|---|---|
| | sweeps of 10 min each = 100 min total) |
| Shock resistance | Conforms to IEC60068-2-27, 147 $m/s^2$, 3 times each in X, Y, and Z directions |
| Noise immunity | Conforms to IEC61000-4-4, 2 kV on power supply line |
| Ambient temperature (Operating) | 0 to 55 °C |
| Ambient temperature (Storage) | -25 to 70 °C (with no freezing or condensation) |
| Ambient humidity (Operating) | 10 to 95 % (with no freezing or condensation) |
| Overvoltage category | Category II: Conforms to JIS B3502 and IEC 61131-2 |
| EMC immunity level | Zone B |
| Ground | Less than 100 Ω |
| Mounting method | DIN track mounting |
| Weight | Approx. 75 g |
| Sold separately | Unit/Terminal Block Coding Pins: NX-AUX02 |

# RoHS/REACH対応状況

情報更新：2026/11/18

## EU RoHS

| 対応状況 ※1 | 対応予定月 ※2 | 非含有証明書 ※3 |
|---|---|---|
| 対応済み | | ダウンロードはこちら |

## 中国 RoHS

| 中国 RoHS表 ※1※2 | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|
| Pb | Hg | Cd | Cr(VI) | PBBs | PBDEs | DBP | DIBP | BBP | DEHP | 環境保護使用期限 |
| X | O | O | O | O | O | O | O | O | O | 10 |

・“対応済み”や非含有の記載がされた商品であっても、流通在庫等で未対応品が混在する可能性があります。
・非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

この製品のRoHS/REACH対応状況ページへ >

# 注意事項・凡例

”対応済み”で記載される商品であっても、流通在庫等で未対応品が混在する可能性があります。
非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

## ※1 対応状況

- Ro対応済み　：EU RoHS指令（10物質）の非含有に対応した製品が提供可能な商品です。
- 対応予定　：EU RoHS指令（10物質）の非含有に対応した製品に切り替える予定のある商品です。
- 対応予定なし　：EU RoHS指令（10物質）の非含有に非対応の商品で、対応品を出す予定はありません。
- 調査・確認中　：EU RoHS指令（10物質）の非含有の対応状況を調査中または確認中の商品です。
- 非該当品　：ライセンス料など無形物で、有害物質有無と関係のない商品です。

仕入先様の事情により、非含有部品としていたものが、含有品と判明した場合などやむを得ず変更することがあります。

＊EU RoHS指令（10物質）：
鉛(Pb) 1000ppm以下、 水銀(Hg) 1000ppm以下、 カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、
ポリ臭化ビフェニル類(PBB) 1000ppm以下、ポリ臭化ジフェニルエーテル類(PBDE) 1000ppm以下、
フタル酸ビス(2-エチルヘキシル) (DEHP)(別名：DOP) 1000ppm以下、フタル酸ブチルベンジル (BBP) 1000ppm以下、
フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジイソブチル (DIBP) 1000ppm以下
但し、RoHS指令で産業用監視および制御機器に対する適用除外項目は除く。
フタル酸エステル類の４物質については閾値を超える意図的な使用がないことを確認しています。

## ※2 対応予定月

部品在庫の切り替え状況などにより、予定月が前後することがあります。

## ※3 非含有証明書ダウンロード

下記の非含有証明書をダウンロードすることができます。
・EU RoHS指令（10物質）の非含有証明書
・49物質の非含有証明書（当社基準）

※本証明書は発行日時点で非含有を証明するもので、過去に遡って非含有を証明するものではありません。
また、RoHS指令のフタル酸エステル類４物質の対応では、対応完了までの期間は出荷製品に未対応品が混在することから備考欄に対応日を記載しておりました。
既に当社にて対応品への在庫切替を完了していることから、特段のことがない限り、2022年1月12日より割愛しております。

# 規格認証/適合状況

| UL認証 | CSA認証 | CEマーキング | CCC認証 | 電波法 |
|---|---|---|---|---|
| Yes | Yes | Yes | N/A | N/A |

| LR型式承認（イギリス船舶規格） | DNV型式承認（ノルウェー船舶規格） | BV型式承認（フランス船舶規格） | KR型式承認（韓国船舶規格） | NK型式承認（日本船舶規格） | ABS型式承認（アメリカ船舶規格） |
|---|---|---|---|---|---|
| Yes | Yes | Yes | No | Yes | No |

この製品の規格認証/適合状況ページへ >
その他の認証はこちらのページからご検索ください >


©OMRON Corporation 2025 All Rights Reserved.
お断りなく仕様などを変更することがありますのでご了承ください