


## スイッチング・パワーサプライ

# S8JX-P30012N



# 商品概要

Switch Mode Power Supply, Capacity 300 W, Output voltage 12 V, Covered type, Front mounting, Without mounting bracket

販売状況 2025/11/28 00:00 情報更新

販売状況	販売中
機種区分	標準在庫機種
標準価格(税別)	¥ 27,500

推奨代替品の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「生産終了品/推奨代替品」をご覧ください。 在庫状況/標準価格の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「在庫状況/標準価格 照会」をご覧ください。

情報更新: 2025/11/04

# 詳細情報

### Specifications

300 W Power rating Output voltage 12 VDC Efficiency 77 % min. Input Rated input voltage 100 to 240 VAC Allowable input voltage variable range 85 to 264 VAC 80 to 370 VDC Frequency 50/60Hz (47 to 63 Hz) Rated input current 4.5 A max. (at 100 VAC input) 2.2 A max. (at 200 VAC input) Power factor 0.9 min. 0.5 mA max. (at 100 VAC input) Leakage current 1 mA max. (at 200 VAC input) Inrush current (cold start at 25 °C) 17.5 A max. (at 100 VAC input) 35 A max. (at 200 VAC input) Output Rated output current 27 A -10 to +15 % (With V.ADJ) Output voltage variable range Ripple 2 %(p-p) max. (at rated input and output) Static load variation influence 0.8 % max. (at rated input, 0 to 100% load) Ambient temperature variation influence 0.05 %/°C max. 1000 ms max. Start up time Hold time 20 ms min. (at 100 VAC input) (at 100% load) 20 ms min. (at 200 VAC input) Additional functions Overload protection Yes, automatic reset Overvoltage protection Yes, Shut off the input voltage and turn on the input again Overheat protection Yes, Shut off the input voltage and turn on the input again Series operation Yes (Up to 2 Power Supplies with external diode) Parallel operation Yes (Up to 5 Power Supplies) Alarm indication Yes (color: red) Output indicator Yes (color: green)

	Remote sensing function	Yes	
	Remote control function	Yes	
Insulation	Dielectric strength	Between all input terminals and all output terminals: 3 kVAC for 1 min, Detection current: 20 mA  Between all input terminals and PE terminals: 2 kVAC for 1 min, Detection current: 20 mA  Between all output terminals and PE terminals: 1 kVAC for 1 min, Detection current: 100 mA  Between all output terminals and RC terminals: 100 VAC for 1 min, Detection current: 100 mA  Between all output terminals and ALM terminals: 500 VAC for 1 min, Detection current: 20 mA	
	Insulation resistance	Between all output terminals and all input terminals/ PE terminals: 100 MΩ min., at 500 VDC	
Environment	Vibration resistance	10 to 55 Hz, 0.375 mm single amplitude in each 3 directions for 2 hours	
	Shock resistance	150 m/s², in each 6 directions 3 times	
	Ambient temperature (Operating)	-10 to 70 °C (with no freezing or condensation)	
	Ambient temperature (Storage)	-25 to 75 °C (with no freezing or condensation)	
	Ambient humidity (Operating)	25 to 85 %	
	Ambient humidity (Storage)	25 to 90 %	
Construction	Construction	Covered type	
	Connection	Terminal blocks	
	Terminal type	Screw terminal	
	Mounting	Front mounting	
	Cooling fan	Cooling fan Yes	
	Weight (Main)	1200 g max.	

#### Note

Do not use the Inverter output for the Power Supply. Inverters with an output frequency of 50/60 Hz are available, but the rise in the internal temperature of the Power Supply may result in ignition or burning.

情報更新: 2025/11/04

### Dimension

### S8JX-P300□□N (300 W)

22.5 max.
Four, M4 (Depth: 6 mm max.)

Four, M5

Four, M4 (Depth: 6 mm max.)

Four, M4 (Depth: 6 mm max.)


41.5 max

120±0.5

Mounting Mounting state

情報更新: 2025/11/04

### **Standard Mounting**




- Note: 1. Improper mounting will interfere with heat dissipation and may occasionally result in deterioration or damage of internal parts. Use the standard mounting method only.
   When mounting the Power Supply, mounting it to a metal plate (\*) is recommended.
   Do not cover the air holes (provided at fan mounted side and the opposite side) to have enough air-cooling.

情報更新: 2025/11/04

### Connection diagram

Terminal arrangement



Note: The S8JX-P30024N is shown above.

No.	Name	Function
1	Input Terminals (L), (N)	Connect the input lines to these terminals. *1
2	Protective Earth Terminal (PE) ( )	Connect the ground line to these terminals. *2
3	DC Output Terminals (-V), (+V)	Connect the load lines to these terminals.
4	Output Indicator (DC ON: Green)	Lights green while a direct current (DC) output is ON.
5	Output Voltage Adjuster (V. ADJ)	It is possible to increase or decrease the output voltage.
6	Alarm indicator (ALM: Red)	This lamp lights up at the time of output voltage deterioration or fan stoppage, and in standby mode by remote control function.
7	Signal output connector #3  11	1: Output voltage monitor terminal (+V) 2: Remote sensing terminal (+S) 3: Output voltage monitor terminal (-V) 4: Remote sensing terminal (-S) 5: Current balance terminal (CB) 6: Current balance ground terminal (CBG) 7: Remote control terminal (+RC) 8: Remote control terminal (-RC) 9: (Not connected) 10: (Not connected) 11: Alarm detection output terminal (ALMC) (Collector side) 12: Alarm detection output terminal (ALME) (Emitter side)


- \*1. The fuse is located on the (L) side. Ensure that the (L) side is set to (+).
- \*2. This is a PE (Protective Earth) terminal defined in safety standards and must be grounded.
  \*3. Signal input/output connectors are included as standard and implemented in the GN1 before shipment.

In this connector, the circuits of 1-2, 3-4, and 7-8 are shorted. Removal of the connector may deteriorate the output stability and accuracy, so be sure to perform the connection of +S and -S terminals.

Never connect a load to the output voltage monitor terminal (+V, -V).


Block diagram

### S8JX-P300□□□□ (300 W)



Derating curve ff報更新: 2025/11/04

# Derating Curves (Standard Mounting)




Note: 1. Internal parts may occasionally deteriorate or be damaged.

Do not use the Power Supply in areas outside the derating curve (i.e., the area shown by shading ① in the above graph).

The ambient temperature is defined at a location 50 mm forward from the center of the front surface of the product.

(For Customers using 300-/600-W type for a DC Input)
 Reduce the load calculated with the above derating curve
 by at least the following coefficients.



## RoHS/REACH対応状況

情報更新: 2025/11/19

### EU RoHS

対応状況 ※1	対応予定月 ※2	非含有証明書 ※3
<b>®</b> 対応済み		ダウンロードはこちら

### 中国 RoHS

中国 RoHS表 <b>※</b> 1 <b>※</b> 2										
Pb	Hg	Cd	Cr(VI)	PBBs	PBDE s	DBP	DIBP	BBP	DEH P	環境 保護 使用 期限
Х	0	0	0	0	0	0	0	0	0	10

- ・"対応済み"や非含有の記載がされた商品であっても、流通在庫等で未対応品が混在する可能性があります。
- ・非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

この製品のRoHS/REACH対応状況ページへ >

#### 注意事項 • 凡例

"対応済み"で記載される商品であっても、流通在庫等で未対応品が混在する可能性があります。 非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

#### ※1 対応状況

・ 📵 対応済み :EU RoHS指令(10物質)の非含有に対応した製品が提供可能な商品です。

対応予定 : EU RoHS指令 (10物質) の非含有に対応した製品に切り替える予定のある商品です。
 対応予定なし : EU RoHS指令 (10物質) の非含有に非対応の商品で、対応品を出す予定はありません。
 調査・確認中 : EU RoHS指令 (10物質) の非含有の対応状況を調査中または確認中の商品です。

・非該当品 :ライセンス料など無形物で、有害物質有無と関係のない商品です。

仕入先様の事情により、非含有部品としていたものが、含有品と判明した場合などやむを得ず変更することがあります。

#### \* EU RoHS指令(10物質):

鉛(Pb) 1000ppm以下、水銀(Hg) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、ポリ臭化ビフェニル類(PBB) 1000ppm以下、ポリ臭化ジフェニルエーテル類(PBDE) 1000ppm以下、フタル酸ビス(2-エチルヘキシル) (DEHP)(別名:DOP) 1000ppm以下、フタル酸ブチルベンジル (BBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ンプチル (DBP) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、プタル酸ブチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、カルマンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチル (DBP) 1000ppm以下、フタル酸シスタル酸シスタル酸シスタル酸シスタル酸シスタル (DBP) 1000ppm以下、フタル酸シスタル (DBP) 1000ppm以下、DBP (DBP) 1000ppm以下、D

#### ※2 対応予定月

部品在庫の切り替え状況などにより、予定月が前後することがあります。

### ※3 非含有証明書ダウンロード

下記の非含有証明書をダウンロードすることができます。

- ・EU RoHS指令(10物質)の非含有証明書
- ・49物質の非含有証明書(当社基準)
- ※本証明書は発行日時点で非含有を証明するもので、過去に遡って非含有を証明するものではありません。

また、RoHS指令のフタル酸エステル類 4 物質の対応では、対応完了までの期間は出荷製品に未対応品が混在することから備考欄に対応日を記載しておりました。

既に当社にて対応品への在庫切替を完了していることから、特段のことがない限り、2022年1月12日より割愛しております。

### 規格認証/適合状況

UL認証	CSA認証	CEマーキング適合	CCC認証
Yes	Yes	Yes	N/A

LR型式承認	DNV型式承認	BV型式承認	KR型式承認	NK型式承認	ABS型式承認
(イギリス	(ノルウェー	(フランス	(韓国	(日本	(アメリカ
船舶規格)	船舶規格)	船舶規格)	船舶規格)	船舶規格)	船舶規格)
No	No	No	No	No	No

この製品の規格認証/適合状況ページへ > その他の認証はこちらのページからご検索ください >