

スイッチング・パワーサプライ (240/480/960Wタイプ)

S8VK-WB96024



商品概要

Switch Mode Power Supply, Capacity 960 W, Rated input voltage 380 to 480 VACOutput voltage 24 V

販売状況 2025/12/15 00:00 情報更新

| 販売状況 | 販売中 |
|----------|-----------|
| 機種区分 | 標準在庫機種 |
| 標準価格(税別) | ¥ 107,000 |

推奨代替品の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「生産終了品/推奨代替品」をご覧ください。 在庫状況/標準価格の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「在庫状況/標準価格 照会」をご覧ください。

情報更新: 2025/11/04

詳細情報

Specifications


960 W Power rating Output voltage 24 VDC Efficiency 90 % min., 95 % typ. (at three-phase 380 VAC input) 95 % typ. (at two-phase 380 VAC input) 91 % min., 95 % typ. (Three-phase 400 VAC input) 95 % typ. (Two-phase 400 VAC input) 90 % min., 94 % typ. (at three-phase 480 VAC input) 95 % typ. (at two-phase 480 VAC input) 380 to 480 VAC (Three-phase / two-phase) Input Rated input voltage Allowable input voltage variable range 320 to 576 VAC (Three-phase / two-phase) 450 to 810 VDC Frequency 50/60Hz (47 to 63 Hz) Rated input current $1.8\,\mathrm{A}$ max., $1.7\,\mathrm{A}$ typ. (at three-phase 380 VAC input) 3.4 A max., 3.2 A typ. (at two-phase 380 VAC input) 1.8 A max., 1.6 A typ. (Three-phase 400 VAC input) 3.2 A max., 3.0 A typ. (Two-phase 400 VAC input) 1.5 A max., 1.3 A typ. (at three-phase 480 VAC input) 2.6 A max., 2.4 A typ. (at two-phase 480 VAC input) Power factor 0.9 min. Leakage current 3.5 mA max. (Three-phase 400 VAC input) 3.5 mA max. Inrush current (cold start at 25 °C) 10.6 A typ. (Three-phase 400 VAC input) Output Rated output current 40 A 24 to 28 V (With V.ADJ) Output voltage variable range Maximum peak current 60 A Ripple 50 mV(p-p) max. Static input variation influence 0.5 % max. Static load variation influence 1.5 % max. Ambient temperature variation influence 0.05 %/°C max. Start up time 1000 ms max. (Three-phase 400 VAC input) Hold time 16 ms min., 20 ms typ. (Three-phase 400 VAC input) Additional functions Yes (151 to 175% of rated current, voltage drop, Overload protection intermittent operation, automatic reset.)

| | Overvoltage protection | Yes, 130% or higher of rated output voltage, power shut off (shut off the input voltage and turn on the input again) | | |
|--------------|---------------------------------|--|--|--|
| | Overheat protection | No | | |
| | Series operation | Yes (Up to 2 Power Supplies with external diode) | | |
| | Parallel operation | Yes (Up to 2 Power Supplies) | | |
| | Alarm indication | Yes | | |
| Insulation | Dielectric strength | Between all input terminals and all output terminals, all signal terminals: 3 kVAC for 1 min, Cut-off current: 20 mA Between all input terminals and PE terminals: 2.5 kVAC for 1 min, Cut-off current: 20 mA Between all output terminals/all signal output terminals and PE terminals: 1 kVAC for 1 min, Cut-off current: 30 mA Between all output terminals and all single output terminals: 0.5 kVAC for 1 min, Cut-off current: 10 mA | | |
| | Insulation resistance | (Between all output terminals, signal output terminals and all input terminals /PE terminals): 100 MΩ min., at 500 VDC | | |
| Environment | Vibration resistance | 10 to 55 Hz, 5 G max., 0.42 mm single amplitude in each 3 directions for 2 hours | | |
| | Shock resistance | 294 m/s², 3 times each in 6 directions | | |
| | Altitude | 3000 m max. | | |
| | Ambient temperature (Operating) | -40 to 70 °C | | |
| | Ambient temperature (Storage) | -40 to 85 °C (with no freezing or condensation) | | |
| | Ambient humidity (Operating) | 95 %RH max. | | |
| | Ambient humidity (Storage) | 95 %RH max. | | |
| Reliability | MTBF | 60,000 hours min. | | |
| | Life expectancy | 10 years min. (at rated input, a load rate of 50% load, under the temperature of 40 °C max., standard mounting) | | |
| Construction | Construction | Covered type | | |
| | Connection | Terminal blocks | | |
| | Terminal type | Push-In Plus Terminal Block | | |
| | Mounting | DIN track mounting | | |
| | Coationg | Yes | | |
| | Cooling fan | Cooling fan No | | |
| | Degree of protection | IP20, EN/IEC 60529 | | |
| | Weight (Main) | 1800 g max. | | |

Note

Do not use the Inverter output for the Power Supply. Inverters with an output frequency of 50/60 Hz are available, but the rise in the internal temperature of the Power Supply may result in ignition or burning.

Dimension ff報更新: 2025/11/04




情報更新: 2025/11/04


Mounting

Mounting state


(A) 標準取り付け Standard mounting




(B) 上向き取り付け Face up mounting



(C) 正面密着取り付け Front, Side-by-sidemounting





*1. 空気の対流 Convection of air

*2. 上下間隔23mm以上

Vertical separation: 23 mm or more

*3. 左右間隔15mm以上(標準取り付け)

左右間隔15mm未満(正面密着取り付け)

Horizontal separation: 15 mm or more


(Standard mounting)

Horizontal separation:Less than 15 mm (Front, side-by-sidemounting)

情報更新: 2025/11/04


Connection diagram

Block diagram



Derating curve ff報更新: 2025/11/04

960 W <Horizontal separation: 15 mm or more>




Note: 1. At more than 528 VAC three-phase, derate the load at 0.5%/V.

- 2. At less than 380 VAC two-phase or at more than 528 VAC two-phase, derate the load at 0.5%/V.
- 3. At more than 746 VDC, derate the load at 0.5%/V.
- In the shaded area, time is required to reach the rated output voltage after the input voltage is applied.

A. Standard mounting, B. Face-up mounting

240 W/480 W/960 W < Horizontal separation: less than 15 mm>




- **Note: 1.** Apply the rated input voltage for both three-phase and two-phase.
 - 2. In the shaded area, time is required to reach the rated output voltage after the input voltage is applied.

C. Front, side-by-side mounting

This Power Supply can be used at an altitude of up to 3,000 m. Between 2,000 and 3,000 m, derate the load according to the following derating curve.


240 W/480 W/960 W < Horizontal separation: 15 mm or more>




Note: 1. At more than 528 VAC three-phase, derate the load at 0.5%/V.

- At less than 380 VAC two-phase or at more than 528 VAC two-phase, derate the load at 0.5%/V.
- 3. At more than 746 VDC, derate the load at 0.5%/V.

A. Standard mounting





Note: Apply the rated input voltage for both three-phase and two-phase.

C. Front, side-by-side mounting

RoHS/REACH対応状況

情報更新: 2025/12/03

EU RoHS

| 対応状況 ※1 | 対応予定月 ※2 | 非含有証明書 ※3 |
|---------|----------|------------|
| № 対応済み | | ダウンロードはこちら |

中国 RoHS

| 中国 RoHS表 ※ 1 ※ 2 | | | | | | | | | | |
|--------------------------------|----|----|--------|------|-----------|-----|------|-----|----------|----------------------|
| Pb | Hg | Cd | Cr(VI) | PBBs | PBDE s | DBP | DIBP | BBP | DEH P | 環境 保護 使用 期限 |
| Х | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 10 |

- ・"対応済み"や非含有の記載がされた商品であっても、流通在庫等で未対応品が混在する可能性があります。
- ・非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

この製品のRoHS/REACH対応状況ページへ >

注意事項·凡例

"対応済み"で記載される商品であっても、流通在庫等で未対応品が混在する可能性があります。 非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

※1 対応状況

・ le y RoHS指令 (10物質) の非含有に対応した製品が提供可能な商品です。

対応予定 : EU RoHS指令 (10物質) の非含有に対応した製品に切り替える予定のある商品です。
 対応予定なし : EU RoHS指令 (10物質) の非含有に非対応の商品で、対応品を出す予定はありません。
 調査・確認中 : EU RoHS指令 (10物質) の非含有の対応状況を調査中または確認中の商品です。

・非該当品:ライセンス料など無形物で、有害物質有無と関係のない商品です。

仕入先様の事情により、非含有部品としていたものが、含有品と判明した場合などやむを得ず変更することがあります。

* EU RoHS指令(10物質):

鉛(Pb) 1000ppm以下、水銀(Hg) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、ポリ臭化ビフェニル類(PBB) 1000ppm以下、ポリ臭化ジフェニルエーテル類(PBDE) 1000ppm以下、フタル酸ビス(2-エチルヘキシル) (DEHP)(別名:DOP) 1000ppm以下、フタル酸ブチルベンジル (BBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ンプチル (DBP) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、プタル酸ブチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、カルマンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチル (DBP) 1000ppm以下、フタル酸シスタル酸シスタル酸シスタル酸シスタル酸シスタル (DBP) 1000ppm以下、フタル酸シスタル (DBP) 1000ppm以下、DBP (DBP) 1000ppm以下、D

※2 対応予定月

部品在庫の切り替え状況などにより、予定月が前後することがあります。

※3 非含有証明書ダウンロード

下記の非含有証明書をダウンロードすることができます。

- ・EU RoHS指令(10物質)の非含有証明書
- ・49物質の非含有証明書(当社基準)
- ※本証明書は発行日時点で非含有を証明するもので、過去に遡って非含有を証明するものではありません。

また、RoHS指令のフタル酸エステル類 4 物質の対応では、対応完了までの期間は出荷製品に未対応品が混在することから備考欄に対応日を記載しておりました。

既に当社にて対応品への在庫切替を完了していることから、特段のことがない限り、2022年1月12日より割愛しております。

規格認証/適合状況

| UL認証 | CSA認証 | CEマーキング適合 | CCC認証 |
|------|-------|-----------|-------|
| Yes | Yes | Yes | N/A |

| LR型式承認 | DNV型式承認 | BV型式承認 | KR型式承認 | NK型式承認 | ABS型式承認 |
|--------|---------|--------|--------|--------|---------|
| (イギリス | (ノルウェー | (フランス | (韓国 | (日本 | (アメリカ |
| 船舶規格) | 船舶規格) | 船舶規格) | 船舶規格) | 船舶規格) | 船舶規格) |
| No | No | No | No | No | No |

この製品の規格認証/適合状況ページへ> その他の認証はこちらのページからご検索ください>