

FA Controller Catalog



Controllers ideal for all machines





4 FA Controller Catalog

Controllers ideal for all machines

The cost-effective CP Series and complete, robust NJ/NX/NY Series support from simple machine control through to large production line control and plant management. The controllers not only help reduce programming, set-up and maintenance times, but also enable fast and accurate fine-tuning control, quality traceability, predictive maintenance, preven-

tive maintenance, and remote maintenance.



The Machine Automation Controller integrates logic, motion, safety, vision, information, visualization and networking under one software: Sysmac Studio. This one software provides a true Integrated Development Environment (IDE) that also includes a custom 3D motion simulation tool.

The machine controller comes standard with built-in EtherCAT and EtherNet/IP. The two networks with one connection purpose is the perfect match between fast real time machine control and data plant management.





Omron's Industrial PC Platform includes the Industrial Box PC, Industrial Panel PC, and Industrial Monitor.

Choose from two different types of products to suit your system:

- Industrial PC comes equipped with Windows operating systems
- IPC Machine Controller combines the precision and utility of the Sysmac platform with the versatility and range of Windows programs





Programmable

Multi-Axis Controller

The Programmable Multi-Axis Controller was developed by combining Omron ILO+R+S (Input, Logic, Output, Robot, and Safety) control technology with proven technology from Omron's Delta Tau Data Systems, Inc., delivering world-beating* output speeds allied to exceptional precision.

Providing the high-speed processing capability to perform precise linear motor drive control and nanometer positioning that require ultra fast responses, it is appreciated by manufacturers of semiconductor manufacturing equipment and other products employing leading-edge technologies.





This series supports a wide variety of communication interface including Ether-Net/IPTM.

The FA Integrated Tool Package CX-One makes programming and debugging faster and easier. The PLC is suitable for small to medium machines - from simple stand-alone applications up to networked, high-speed machines. It is built to give you innovation without growing pains.





The CP Series provides a complete product line-up to automate compact machines and perform any other simple automation tasks, quickly and easily. Connect the HMI, servo drives, inverters, temperature controllers and other devices to create a more cost-effective system.



A fully integrated platform



Standard networks

Built-in international standard (IEC 62541) OPC UA communication functionality (NX701-

NX502-___, NX102-___, NJ501-1_00)

Built-in EtherCAT and EtherNet/IP ports

- EtherCAT: High-speed network to connect a wide range of machine automation devices such as I/O, sensors and drives. Fast, highly accurate control in synchronization with the EtherCAT cycle. Up to 512 slaves
- EtherNet/IP: Based on standard protocols (TCP/IP and UDP/IP). Allows for mixing Ethernet devices and Ethernet applications

Safety integration

Flexible system lets you integrate safety into machine automation through the use of Safety over EtherCAT (FSoE). Sysmac Studio reduces programming time

CPU Unit with advanced functionality

- Database Connection: Logs real-time data from production lines directly into SQL Databases. This enables predictive/preventive maintenance and quality traceability
- Robot Integrated CPU Unit: Integration of Logic, Motion, OMRON Robot and Kinematics in one CPU.
- SECS/GEM: Built-in SECS/GEM communications functions
- NC Integrated Controller: Realize high-accuracy synchronization motion control (MC) and numerical control (NC) functions by ONE controller. G-Code available.



Sysmac Library

The Sysmac Library is a collection of software functional components that can be used in programs for the NJ/NX Machine Automation Controllers. Please download it from following URL and install to Sysmac Studio. http://www.ia.omron.com/sysmac_library/



What's new

| | Integrated control, information, and safety brings a new |
|---------------------------------------|--|
| | level of speed to manufacturing sites: NX5 |
| C C C C C C C C C C C C C C C C C C C | Controls 32 axes with cycle time of 250 µs |
| | Used motion control servo axes : 256, 128, 64, 32, 16 axes |
| | Program capacity : 80 MB |
| | SQL functionality : Reliable, rapid, and easy direct |
| | access to databases and utilization of production data |
| | OPC UA functionality : Secure connection to IT |
| | systems such as MES and ERP |
| | 10 x 1 Gbps ports for high-speed, high-capacity |
| | communications *1 |
| | *1. When connecting four NX-EIP201 units |
| | |



NJ/NX Series Controller Catalog • P089

NX502_NX-201 • P158

Openness meets Automation Control









Omron's Industrial PC Platform includes the Industrial Box PC, Industrial Panel PC, and Industrial Monitor. Choose from three different types of products to suit your system.

Features

- Industrial Box PC: Powerful, reliable, scalable
- Industrial Panel PC: Combines the functionality of the Industrial Box PC and Industrial Monitor
- Industrial Monitor: Display and touch interface for the industrial PC platform
- Powerful performance maximize output
- Rock-solid build improve uptime
- Real-time OS inside reliable machine control

Industrial PC

Windows IPC. Powerful, reliable, scalable - and tough as they come

IPC Machine Controller

- Combines the precision and utility of the Sysmac platform with the versatility and range of Windows programs
- Automation Software Sysmac Studio: Integrates configuration of the machine automation controller and
- EtherCAT slaves, programming, debugging, and monitoring
- Collection of software functional components Sysmac Library: Simplicity for advanced control. Available to download from Omron website and install to the Sysmac Studio http://www.ia.omron.com/sysmac_library/











High-speed, high-precision motion controller

Programmable Multi-Axis Controller





OMRON and OMRON's Delta Tau Data Systems, Inc. (DT) worked together to develop the multi-axis controllers with global leading motion control technology from DT. The multi-axis controller achieves sophisticated fine-tuning control, including high-speed synchronous control of various factory automation (FA) devices, thanks to built-in EtherCAT connectivity which is used for production lines and equipment all over the world.

| Features | | | | | | | | | | |
|----------------|----------------|------------|-------------|----------|----------|----------|--------|-------|--|--|
| CAD/CAM for | easy motion o | control | | | | | | | | |
| Flexible funct | on developm | ent capab | ility enabl | es high- | orecisio | on curve | e mach | ining | | |
| G-Code/ANSI | C/original pro | gramming | g languag | e | | | | | | |
| EtherCAT for 1 | exible systen | n configur | ation | | | | | | | |
| | tion control | | | | | | | | | |

CK3M/CK5M Programmable Multi-Axis Controller

A next generation motion controller CK3M provides PMAC's superior motion control capability, multi-vendor connectivity, and flexible development capability. The modular design allows you to freely combine the CK3M with expansion units to enable a variety of applications.

CK3E Programmable Multi-Axis Controller

Vou can build a system capable of controlling up to 32 axes of motion and incorporate customized control algorithms into the system. The compact design saves space in machines and control panels. EtherCAT[®] connects servo drives, I/O, and other devices to the CK3E, reducing the number of cables.

Programmable Multi-Axis Controller

The Programmable Multi-Axis Controller has been developed by US-based Delta Tau Data Systems, Inc. to deliver the world's highest level* of motion control performance.Providing the high-speed processing capability to perform precise linear motor drive control and nanometer positioning that require ultra fast responses, the Programmable Multi-Axis Controller is appreciated by manufacturers of semiconductor manufacturing equipment and other products employing leading-edgetechnologies.Through working together with Delta Tau Data Systems which joined the Omron Group on September 1 2015, Omron will further advance automation technologies in an ever-changing manufacturing environment to help manufacturers improve productivity and manufacturing quality.

OMRON | 11



CK3M Programmable Multi-Axis Controller Catalog R196

CK3E Programmable Multi-Axis Controller Flyer R188



A wide range of PLC and I/O brings innovation to your machines and reduces costs

Faster and larger networks, a wide variety of communication interfaces







The PLC is suitable for small to medium machines - from simple stand-alone applications up to networked, high-speed machines. It is built to give you innovation without growing pains.

Features Supports open networks including EtherNet/IP, EtherCAT, FL-net, DeviceNet and CompoNet Efficient programming with variables and EtherNet/IP setting with variable names make the configuration more flexible

A wide range of CPU units and I/O units to suit your needs

Open to the world

- Data communication via standard Ethernet port with EtherNet/IP Data Link function
- Increased EtherNet/IP performance to 12,000 pps*1
- High-speed I/O link based on EtherCAT enables distributed control using multiple CPU units

Advanced motion control

- Multi-axes synchronous control
- Can replace expensive motion controllers

High-speed

Faster program execution and immediate I/O refreshing for flexible machine control

Highly flexible

Adapt the PLC unit to your needs with the wide variety of compatible CJ1 I/O Units





Temperature controller



Device/\et CompoNet[®]



Main conveyor

Pick up



OMRON | 13



More cost-effective automation for compact machines

Simple, Compact, Economical





The CP Series provides a complete product line-up to automate compact machines and perform any other simple automation tasks, quickly and easily.

Features

- 10 to 60 I/O base models, expandable to 320 I/O points
- Digital, analog and temperature sensor I/O expansion units
- Up to 4 high-speed pulse outputs and up to 4 high-speed counter inputs
- Excellent communication capabilities for both serial and Ethernet networking

Powerful instructions common within the CJ Series

Easy positioning, quick results

Easy control: Speed control, positioning, origin search and interrupt feedingModbus Master feature for easy inverter control

Saving programming time

Ladder diagram, Function Blocks or Structured Text programming

Versatile communication

- USB or Ethernet port^{*1} no special cables needed
- Communication with Temperature Controller E5 C without special programs
- Optional boards for RS-232C, RS-485 or Ethernet*2

More options - greater possibilities!

- Analog I/O unit with a resolution of 1/12,000 for high-accuracy inspections
- One multi-input unit for both temperature and analog control of a packaging machine or molding machine
- Analog option boards helps save space



Pick up



OMRON | 15

Make **Complex Machine Easy**



Fill and Seal

Temperature Sensor Unit

Multi-inputs: thermocouple/analog inputs

The CP1W-TS003 has two inputs that can be used for temperature sensor or analog inputs. Both temperature sensor and analog inputs can be achieved with only one unit.



CH1:Temperature sensor input CH2:Temperature sensor input H3:Temperature sensor/analog input nperature sensor/analog input



For a wide variety of applications The unit with multiple analog I/O or with multiple temperature sensor inputs provides more scalability and flexibility.

Analog I/O Unit/Temperature Sensor Unit







Controllers Selection

Omron offers a wide range of FA Controllers to suit your automation applications - from simple control to complex, highly accurate control.

| | J/NX ser | | | | | |
|----------------|--------------------|---|--|--|--|---|
| Serie | es | | | NX S | Series | 1 |
| Product name | | | NX701 CPU Units | NX502 CPU Units | NX102 CPU Units | NX1P2 CPU Units |
| Model | | | NX701- | NX502- | NX102-000 | NX1P2 - 🗆 🗆 🗆 |
| Appe | earance | | | | | |
| | CPU Unit fea | atures | Ideal for large-scale, fast, and highly-accurate control with up to 256 axes | Ideal for large-scale, fast, and highly-accurate control with up to 256 axes. Used with NX-EIP201 to configure up to 10 EtherNet/IP networks. | Compact controller with up to 8 axes motion control. | Compact package-type machine automation controller |
| | Support software | | Sysmac Studio | | | |
| | Instruction | LD instructions | 0.37 ns or more | 0.53 ns or more | 3.3 ns | 3.3 ns |
| Spec | execution times | Math instructions (for long real data) | 3.2 ns or more | 3.3 ns or more | 70 ns or more | 70 ns or more |
| ifica | Program cap | bacity | 80 MB | 80 MB | 5 MB | 1.5 MB |
| Specifications | Variables ca | pacity | 4 MB: Retained during power interruptions 256 MB: Not retained during power interruptions | 4 MB: Retain attributes 256 MB: No Retain attributes | 4 MB: Retained during power interruptions 256 MB: Not retained during power interruptions | 32 KB: Retained during power interruptions 2 MB: Not retained during power interruptions |
| | | maximum number of Units (Expansion Racks) | | Up to 63 NX I/O Units connectable | Up to 32 NX I/O Units connectable | Built-in I/O: 40 points max. Up to eight NX I/O Units connectable |
| | Number of n | notion axes | 128, 256 | 16, 32, 64, 128, 256 | 0, 2, 4, 8 *1 | 0, 2, 4 *1 |
| | EtherCAT sl | aves | 512 | 256 | 64 | 16 |
| | Number of c | ontrolled robots | | | | |
| | Number of c | ontrolled OMRON robots | | | | |
| Fun | Database co | onnection | Provided (NX701-1□20) | Provided | Provided (NX102-020) | |
| Functions | | communications functions | | | | |
| suk | Numerical C | ontrol (NC) functions | | | | |
| | ernal memory | | Memory Cards | | | |
| CJ | Special I/O Ur | nits and CPU Bus Units | | | | |

*1. Motion control axes and 4 single-axis position control axes.
*2. The number of robots that can be controlled depends on the number of axes used in the system.
*3. The number of controlled axes of the MC Control Function Module is included.
*4. For the details of mountable Units, refer to the user's manuals.

| | | | | NJ Series | | | | |
|------------------------------------|-----------------------------|----------------------------|------------|------------|------------|--|-----------------------------|----------|
| | 1 | NJ501 CPU Units | | | | NJ301 CPU Units | NJ101 C | PU Units |
| NJ501-1 | NJ501-R | NJ501-4 | NJ501-1□20 | NJ501-1340 | NJ501-5300 | NJ301-1 | NJ101-000 | NJ101-00 |
| | | | | | | | | |
| Ideal for large-sca | le, fast, and highly-accura | te control with up to 64 a | xes | | | Ideal for small-scale control with up to eight axes | Ideal for simple ma | chines |
| Sysmac Studio | | | | | | Sysmac Studio Sysmac Studio | | |
| 1.1 ns (1.7 ns or | less) | | | | | 1.6 ns (2.5 ns or less) | 3.0 ns (4.5 ns or less) | |
| 24 ns or more | | | | | | 35 ns or more | 63 ns or more 63 ns or more | |
| 20 MB | | | | | | 5 MB | 3 MB | |
| | during power interruption | | | | | 0.5 MB: Retained during power interruptions 2 MB: Not retained during power interruptions | | |
| 2,560 points/40 (3 Expansion Ra | | | | | | 2,560 points/40 Units (3 Expansion Racks) | | |
| 16, 32, 64 | | | | 16 | 16 *3 | 4, 8 | 0, 2 | |
| 192 | | | | | | 192 | 64 | |
| | 8 robots max. *2 | 8 robots max. *2 | | | | | | |
| | 8 robots max. | | | | | | | |
| | Provided (NJ501-R 20) | Provided (NJ501-4320) | Provided | | | | | Provided |
| | | | | Provided | | | | |
| | | | | | Provided | | | |
| Memory Cards | | | | | | | | |
| Mountable *4 | | | | | | | | |

| Product name | Indust | trial PC | IPC Machir | ne Controller |
|------------------|--|--|-------------------------------|----------------------------|
| Гуре | Industrial Box PC | Industrial Panel PC | Industrial Box PC | Industrial Panel PC |
| Vlodel | NYB | NYP | NY51□-1 | NY53□-1 |
| Appearance | | | | |
| Features | Compact design that offers flexibility, expandability and easy maintenance for applications in factory automation environments | Combines the functionality of the Industrial Box PC and Industrial Monitor | Two operating systems: Wir | ndows and Real-Time OS |
| Operating system | No operating system Windows 10 IoT Enterprise 2016 LTSB - 64 bit Windows 10 IoT Enterprise 2019 LTSC - 64 bit Windows 10 IoT Enterprise 2021 LTSC - 64 bit | | Windows 10 IoT Enterpri | ise 2019 LTSC - 64 bit |
| Function module | | | Machine Automation Cont | rol Software |
| Number of axes | | | 16, 32, 64 | |
| CPU type | Intel [®] Xeon [®] W-11865MRE 11th generation CPU with Fan Unit for active cooling Intel [®] Core [™] i7-1185GRE 11th generation CPU with Fan Unit for active cooling Intel [®] Core [™] i5-1145GRE 11th generation CPU with fanless cooling Intel [®] Core [™] i3-1115GRE 11th generation CPU with fanless cooling Intel [®] Core [™] i3-1115GRE 11th generation CPU with fanless cooling Intel [®] Core [™] i3-20EQ Processor 7th generation CPU with Fan Unit for active cooling Intel [®] Core [™] i5-7300U Processor 7th generation CPU with fanless cooling Intel [®] Core [™] 3965U Processor 7th generation CPU with fanless cooling Intel [®] Celeron [®] 3965U Processor 7th generation CPU with fanless cooling Intel [®] Atom [®] Apollo Lake x5-E3940 Processor with fanless cooling | Intel [®] Core [™] i5-1145GRE 11th generation CPU with fanless cooling Intel [®] Core [™] i3-1115GRE 11th generation CPU with fanless cooling Intel [®] Atom [®] x6425RE with fanless cooling Intel [®] Core [™] i5-7300L Processor 7th generation CPU with Fan Unit for active cooling Intel [®] Core [™] i5-7300L Processor 7th generation CPU with fanless cooling Intel [®] Celeron [®] 3965U Processor 7th generation CPU with fanless cooling Intel [®] Atom [®] Apollo Lake x5-E3940 Processor with fanless cooling | with Fan Unit for active cool | ocessor 4th generation CPU |
| RAM memory | 8 GB, 16 GB, 32 GB, 64 GB, 96 GB (ECC supported) *1 2 GB, 4 GB, 8 GB, 16 GB, 32 GB, 64 GB, 96 GB (non ECC) | 2 GB, 4 GB, 8 GB, 16 GB, 32 GB, 64 GB (non ECC) | 8 GB, 32 GB (non-ECC t | ype) |
| Storage | HDD, SSD, CFast, SD memory card *2 | | HDD, SSD, SD memory | card |
| Display size | | 12.1 inches, 15.4 inches, 18.5 inches | | 12.1 inches, 15.4 inche |
| Built-in ports | Ethernet, USB 2.0/3.0/3.1 Gen1, DVI, DisplayPort+- | + *2 | Ethernet, EtherNet/IP, Eth | erCAT, USB 2.0/3.0, DVI |
| Interface option | RS-232C, DVI-D, NY Monitor Link, GigE LAN, DisplayPort++ *2 | RS-232C, DVI-D, NY Monitor Link, DisplayPort++ *2 | RS-232C, DVI-D, NY Mc | nitor Link |
| Expansion slots | 1 PCIe slot | | 1 PCIe slot | |
| RAID | Hardware-RAID (RAID1) | | | |

Industrial PC Platform

 Note. Not all combination are possible, please visit the product selector on the global website to make your selection.

 *1. Only for models with Intel[®] Xeon[®] Processor.

 *2. 11th generation CPU: Equipped with DisplayPort (Dual mode: DP++) instead of DVI, but no SD Memory Card slot.

 *3. Not recommended for new projects.

| Product name | | Industrial Monitor | | | | |
|--------------------------------------|---|--------------------|-------------------------------------|--|--|--|
| Model | NYM12 | NYM15 | NYM19 | | | |
| Appearance | | | | | | |
| Description | Display and touch interface for the Industrial PC Platform | | | | | |
| Display device | TFT LCD | | | | | |
| Screen size | 12.1 inches | 15.4 inches | 18.5 inches * | | | |
| Resolution | Up to 1,280 x 800 pixels at 60 Hz | <u>Z</u> | Up to 1,920 x 1,080 pixels at 60 Hz | | | |
| Colors | 16,770,000 colors | | | | | |
| Connectors | 1 Power Connector, 1 DVI-D Connector, 2 USB Type-A Connector, 1 USB Type-B Connector | | | | | |
| Built-in options | NY Monitor Link | | | | | |
| Allowable power supply voltage range | 19.2 to 28.8 VDC | | | | | |

* 18.5 also available with Nickel Plated front.

| CK3M series | | | | | | |
|---------------------------|---|---|--|--|--|--|
| Series | CK3M/CK | CK3M/CK5M Series | | | | |
| Model | CK3M | CK5M | | | | |
| Appearance | | | | | | |
| Features | Controls analog servo drives at high speeds of up to 50 µs/5 axes, enabling high-precision processing | Controls analog servo drives at high speeds of up to 25 µs/5 axes, enabling high-precision processing | | | | |
| Support software | Power PMAC IDE | Power PMAC IDE | | | | |
| Memory | RAM: 1 GB, Built-In flash memory: 1 GB | RAM: 2 GB, Built-In flash memory: 4 GB | | | | |
| Built-in ports | Ethernet, EtherCAT, USB | Ethernet, EtherCAT | | | | |
| Number of motion axes | 24 (4 axes/axial interface unit x 4 units: 16, EtherCAT: 8) | 64 (4 axes/axial interface unit x 8 units: 32, EtherCAT: 32) | | | | |
| Number of EtherCAT slaves | 32 | 64 | | | | |
| | | | | | | |

| CK3E series | CK3E Series |
|---------------------------|---|
| Model | CK3E |
| Appearance | |
| Features | You can build a system capable of controlling up to 32 axes of motion and incorporate customized control algorithms into the system. |
| Support software | Power PMAC IDE |
| Memory | DDR3 memory: 1GB, Flash memory: 1GB |
| Built-in ports | Ethernet, EtherCAT |
| Number of motion axes | 8, 16 or 32 |
| Number of EtherCAT slaves | 32 |

CS/CI series

| Series | | CJ | Series | CS S | Series |
|----------------------|---------------------------------|--|---|---|--|
| Model | | CJ2H | CJ2M | CS1H/G | CS1D |
| Appeara | ance | | | | |
| CPU Unit features *1 | | A large data memory capacity, multi-func- tion Ethernet port, tag access function- ality, and a USB port. Ideal for high-speed, high-precision machines | Based on the long track record of the CJ1M and adds greater cost perfor- mance and flexibility. Ideal for gener- al-purpose machine control | From machine control to informa- tion management multiple-appli- cation Controllers with a wide range of functions | Redundant CPU Units, Power Supply Units, Communications Units, and Expansion I/O Cables |
| | | High-speed I/O Units, synchronized control, USB port, built-in Ether- Net/IP port, data structures and arrays, Function Blocks (Ladder di- agrams/Structured Text) | High-speed I/O Units, USB port, built-in EtherNet/IP port, data struc- tures and arrays, FB Program Area, Function Blocks (Ladder diagrams/- Structured Text), Serial Communica- tions Option Boards | Up to 5,120 points of I/O, Inner Board capability, Function Blocks (Ladder dia- grams/Structured Text) | Up to 5,120 points of I/O, redun- dant CPU Units and Power Supply Units, Inner Board capa- bility |
| Support | software | CX-One | CX-One | CX-One | CX-One |
| | on execution times nstructions) | 0.016 µs | 0.04 μs | CS1G: 0.04 μs CS1H: 0.02 μs | 0.02 µs |
| Max. no | . of I/O points | 2,560 | 2,560 | 960 to 5,120 | 960 to 5,120 |
| Progran | n capacity | 50K to 400K steps | 5K to 60K steps | 10K to 250K steps | 10K to 400K steps |
| Data me | emory capacity | 160K to 832K words | 64K to 160K words | 64K to 448K words (EM Area: 1 to 13 banks) | 64K to 832K words (EM Area: 1 to 25 banks) |
| | Built-in I/O | | 32 points *2 | | |
| Built-in | Interrupt inputs | | 8 inputs *2 | | |
| features | High-speed counter | | 4 inputs *2 | | |
| | Pulse outputs *1 | | 4 outputs *2 | | |
| Externa | al memory | Memory Cards | Memory Cards | Memory Cards | Memory Cards |
| | cial I/O Units 7U Bus Units | Mountable | Mountable | Mountable (units for CS series) | Mountable (units for CS series) |

*1. These features are not supported by all of the CPU Unit models in the relevant series. Refer to specific product catalogs for details. *2. Applicable when a Pulse I/O Block is mounted.

| CPoori | |
|--------|--|

| Series | | | CP Series | |
|---------------------|------------------------------------|--|--|---|
| Model | | CP1H | CP1L | CP2E |
| Appearance | | | | |
| CPU Unit features * | | Four axis position control and compre- hensive model | High performing model with embedded Ethernet for two axis position control | A network model equipped with an Eth- ernet port and an essential model for basic control are available. |
| | | Pulse outputs for up to 4 axes, CP1W Ex- pansion Units can be mounted, easy Mod- bus-RTU, Serial Communications Option Boards, Ethernet Option Board, CJ-series Special I/O Units and CPU Bus Units can be mounted, Function Blocks (Ladder dia- grams/Structured Text), LCD Option Board, analog adjuster, seven-segment LED display (2 digits) | Pulse outputs for up to 2 axes, models with USB port, models with Ethernet com- munications port, CP1W Expansion Units can be mounted, easy Modbus-RTU, Serial Communications Option Boards, Ethernet Option Board, Function Blocks (Ladder diagrams/Structured Text), LCD Option Board, analog adjuster, Analog I/O Option Boards | Pulse outputs for up to 4 axes, models with 2 Ethernet ports, models with RS-232C ports, CP1W Expansion Units can be mounted, easy Modbus-RTU, Function Blocks (Ladder diagrams/Struc- tured Text), Analog I/O Option Boards |
| Support | software | CX-One | CX-One | CX-One |
| | on execution times nstructions) | 0.10 μs | 0.55 μs | 0.23 μs |
| Max. no | . of I/O points | 320 points (40 built in + 280 expansion) | 180 points (60 built in + 120 expansion) | 180 points (60 built in + 120 expansion) |
| Program | n capacity | 20K steps | 5K or 10K steps | 4K to 10K steps |
| Data me | emory capacity | 32K words | 10K or 32K words | 4K to 16K words |
| | Built-in I/O | 20 or 40 points | 10 to 60 points | 14 to 60 points |
| Built-in | Interrupt inputs | 6 or 8 inputs | 2, 4 or 6 inputs | 6 or 8 inputs |
| features | High-speed counter | 4 inputs | 4 inputs | 2 inputs |
| | Pulse outputs * | 4 outputs | 2 outputs | 2 or 4 outputs |
| Externa | l memory | Memory Cassettes | Memory Cassettes | |
| | cial I/O Units U Bus Units | Mountable | | |

* These features are not supported by all of the CPU Unit models in the relevant series. Refer to specific product catalogs for details.

Service and support



COMPETENCE

OMRON



Design

Our wi de net work of machine automation specialists will help you to select the right automation architecture and products to meet your requirements. Our flat structure based on expert-to-expert contact ensures that you will have ONE accountable and responsible expert to deal with on your complete project.



Proof of concept

As your project matures make use of our Automation centers to test and catch-up with technology trends in motion, robotics, networking, safety, quality control etc. and to interface, test and validate your complete system with our new machine network (EtherCAT) and factory network (EtherNet/IP). We will assign a dedicated application engineer to assist with initial programming and proof testing of the critical aspects of your automation system. Our application engineers have indepth expertise in and knowledge of networks, PLCs, motion, safety and HMIs when applied to machine automation.



For the most recent information, refer to your OMRON website.

CONFIDENCE



Development

During your prototyping phase you will need flexibility in technical support, product supply and exchange. We will assign an inside sales contact to help you source the correct products fast during your prototyping phase.



Commissioning

With our world-wide network for service and support the export of your product is made simple, we will support you on-site with your customer, anywhere in the world. We can arrange a liaison sales engineer to facilitate training, spare parts supply or even machine commissioning. All this in a localised language with localised documentation - giving you complete peace of mind.

ASSURANCE



Serial production

As your production increases we will engage in supplying you within 24hrs and repairing within 3 days. All our products are global products meeting global standards - CE, cULus, NK, LR -

Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products.

Windows, SQL Server and Visual Basic are either registered trademarks or trademarks of Microsoft Corporation in the United Status and/or other countries.

EtherCAT® and Safety over EtherCAT® are registered trademarks and patented technologies, licensed by Beckhoff Automation GmbH, Germany.

EtherNet/IP[™], CompoNet[™] and DeviceNet[™] are the trademarks of ODVA.

OPC UA is a trademark of OPC Foundation.

Intel, Intel Xeon, and Intel Core are the trademarks or registered trademarks of Intel Corporation in the U.S. and/or other countries. zenon is a registered trademark of Ing. Punzenberger COPA-DATA GmbH.

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

The product photographs and figures that are used in this catalog may vary somewhat from the actual products.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company Kyoto, JAPAN Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD. 438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011 **OMRON ELECTRONICS LLC** 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

Authorized Distributor:

©OMRON Corporation 2015-2025 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.