EtherCAT® Remote I/O Terminals

GX-Series

CSM GX DS F 9 16

Realizes high-speed communication to match a variety of applications

• Digital I/O Terminals

Inputs/Outputs the digital ON/OFF signals.

Analog I/O Terminals


Inputs/Outputs the analog signal of 0-5V or 4-20mA, etc., and executes A/D or D/A conversion.

Encoder Input Terminal

Performs conversion for pulse input signals from an encoder.

• Expansion Units

Attached to the Digital I/O Unit to expands the I/O points. Can be attached to a two-tier terminal block type with 16 inputs, 16 outputs, and 16 relay outputs.



General Specifications

It is common specifications of Digital I/O Terminal, Analog I/O Terminal and Encoder Input Terminal GX-Series. Refer to the pages of specifications for individual I/O terminals for details.

For General Specification of IO-Link Master Unit(GX-ILM08C), refer to page 31.

Item	Specification	
Unit power supply voltage	20.4 to 26.4 VDC (24 VDC –15% to +10%)	
I/O power supply voltage	20.4 to 26.4 VDC (24 VDC –15% to +10%)	
Noise resistance	Conforms to IEC 61000-4-4, 2 kV (power line)	
Vibration resistance	10 to 60 Hz with amplitude of 0.7 mm, 60 to 150Hz and 50 m/s² in X, Y, and Z directions for 80 minutes *Relay Output Unit GX-OC1601 only> 10 to 55 Hz with double-amplitude of 0.7 mm X, Y, and Z directions for 80 minutes	
Impact resistance	150 m/s² with amplitude of 0.7 mm <relay gx-oc1601="" only="" output="" unit=""> 100 m/s² (3 times each in 6 directions on 3 axes)</relay>	
Dielectric strength	600 VAC (between isolated circuits)	
Isolation resistance	20 MΩ or more (between isolated circuits)	
Ambient operating temperature	−10 to 55 °C	
Operating humidity	25% to 85% (with no condensation)	
Operating atmosphere	No corrosive gases	
Storage temperature	−25 to 65 °C	
Storage humidity	25% to 85% (with no condensation)	
Terminal block screws tightening torque *	M3 wiring screws: 0.5 N•m M3 terminal block mounting screws: 0.5 N•m	
Mounting method	35-mm DIN track mounting	

^{*} Applicable only to 2-tier terminal block and 3-tier terminal block type slaves.

Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products. EtherCAT® is a registered trademark of Beckhoff Automation GmbH for their patented technology. EtherNet/IPTM is the trademarks of ODVA.

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

EtherCAT Communications Specifications

Communications Specifications of GX-Series EtherCAT Remote I/O Terminal

Item	Specification
Communication protocol	Dedicated protocol for EtherCAT
Modulation	Base band
Baud rate	100 Mbps
Physical layer	100BASE-TX (IEEE802.3)
Connectors	RJ45 shielded connector × 2 CN IN: EtherCAT input CN OUT: EtherCAT output
Topology	Daisy chain
Communications media	Category 5 or higher (cable with double, aluminum tape and braided shielding is recommended.)
Communications distance	Distance between nodes (slaves): 100 m max.
Noise resistance	Conforms to IEC 61000-4-4, 1 kV or higher
Node address setting method	Set with decimal rotary switch or Sysmac Studio
Node address range	1 to 99: Set with rotary switch 1 to 65535: Set with Sysmac Studio
LED display	PWR × 1 L/A IN (Link/Activity IN) × 1 L/A OUT (Link/Activity OUT) × 1 RUN × 1 ERR × 1
Process data	Fixed PDO mapping
PDO size/node	2 bit to 256 byte
Mailbox	Emergency messages, SDO requests, SDO responses, and SDO information
SYNCHRONIZATION mode	Digital I/O Slave Unit and Analog I/O Slave Unit: Free Run mode (asynchronous) Encoder Input Slave Unit: DC mode 1

Version Information

EtherCAT Slave Unit model	Unit version	Compatible version of Support Software	
EtherCAT Slave Unit model	Unit version	Sysmac Studio	Cx-ConfiguratorFDT
	Ver.1.2	Ver.1.25	-
GX-ID	Ver.1.1	Ver.1.01	
	Ver.1.0	Ver. 1.01	_
	Ver.1.2	Ver.1.25	-
GX-OD□□□□	Ver.1.1	Ver.1.01	
	Ver.1.0	Ver. 1.01	_
	Ver.1.2	Ver.1.25	-
GX-OC□□□□	Ver.1.1	Ver.1.01	
	Ver.1.0	Ver. 1.01	_
	Ver.1.2	Ver.1.25	-
GX-MD	Ver.1.1	Ver.1.01	
	Ver.1.0		_
	Ver.1.2	Ver.1.25	-
GX-AD□□□□	Ver.1.1	Ver.1.01	
	Ver.1.0		_
	Ver.1.2	Ver.1.25	-
GX-DA□□□□	Ver.1.1	Ver.1.01	
	Ver.1.0		_
	Ver.1.2	Ver.1.25	-
GX-EC	Ver.1.1	Vor 1 01	
	Ver.1.0	Ver.1.01	_
	Ver.1.2	Ver.1.25	Ver.2.2
GX-ILM□□□	Ver.1.1	Ver.1.20	Ver.2.2
	Ver.1.0	Ver.1.16	Ver.2.2

Note: Refer to User's Manual for details on the functions that have been added or changed due to the unit version upgrade of the EtherCAT Slave Units.

Digital I/O Terminal 2-tier Terminal Block Type

GX-\(\Box \) D16\(\Box \) 1/OC1601

High-speed digital I/O terminal with the screw type terminal block for EtherCAT communications

- Detachable screw terminal block facilitates the maintenance.
- The expansion unit can be connected.
 (One expansion unit per one I/O terminal unit.)
 Input/output point can be flexibly increased depending on the system.
- Input response time can be switched for high-speed processing.
- Selectable node address setting methods: setting with rotary switch and with tool software.
- When setting the nodes with rotary switch, setting is easy and node identification becomes possible for maintenance.



Expansion Units

One Expansion Unit can be combined with one Digital I/O Terminal (GX-ID16 \Box 1/OD16 \Box 1/OC1601). The following Expansion Units are available. They can be combined in various ways for flexible I/O capacity expansion.

Model	I/O points	Input capacity	Output capacity
XWT-ID08	8 DC inputs (NPN)	8	0
XWT-ID08-1	8 DC inputs (PNP)	8	0
XWT-OD08	8 transistor outputs (NPN)	0	8
XWT-OD08-1	8 transistor outputs (PNP)	0	8
XWT-ID16	16 DC inputs (NPN)	16	0
XWT-ID16-1	16 DC inputs (PNP)	16	0
XWT-OD16	16 transistor outputs (NPN)	0	16
XWT-OD16-1	16 transistor outputs (PNP)	0	16

General Specifications

For Common Specifications of I/O terminals, refer to page 1.

Input Section Specifications

16-point Input Terminals

Input capacity Internal I/O common NPN ON voltage 15 VDC min. (between each input terminal and the V terminal) OFF voltage 5 VDC max. (between each input terminal and the V terminal) OFF current 1.0 mA max. Input current 6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC) ON delay 0.1 ms max. OFF delay Input filter value Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms) Number of circuits per common Input indicators LED display (yellow) Isolation method Photocoupler isolation			
Internal I/O common NPN NPN ON voltage 15 VDC min. (between each input terminal and the V terminal) 5 VDC min. (between each input terminal and the V terminal) 5 VDC max. (between each input terminal and the V terminal) From the current 1.0 mA max. Input current 6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC) ON delay 0.1 ms max. OFF delay 0.2 ms max. Input filter value Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms) Number of circuits per common Input indicators LED display (yellow)			
ON voltage 15 VDC min. (between each input terminal and the V terminal) 5 VDC max. (between each input terminal and the V terminal) 5 VDC max. (between each input terminal and the V terminal) 5 VDC max. (between each input terminal and the O terminal) 5 VDC max. (between each input terminal and the O terminal) 6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC) ON delay 0.1 ms max. OFF delay 0.2 ms max. Input filter value Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms) Number of circuits per common Input indicators LED display (yellow)			
OFF voltage 5 VDC max. (between each input terminal and the V terminal) 5 VDC max. (between each input terminal and the C OFF current 1.0 mA max. Input current 6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC) ON delay 0.1 ms max. OFF delay 0.2 ms max. Input filter value Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms) Number of circuits per common 16 inputs/common Input indicators LED display (yellow)			
DFF current 1.0 mA max. 6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC) ON delay 0.1 ms max. OFF delay 0.2 ms max. Input filter value Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms) Number of circuits per common Input indicators LED display (yellow)	terminal)		
Input current 6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC) ON delay 0.1 ms max. OFF delay 0.2 ms max. Input filter value Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms) Number of circuits per common Input indicators LED display (yellow)			
ON delay OFF delay Out ms max. OFF delay Out ms max. Input filter value Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms) Number of circuits per common Input indicators LED display (yellow)	1.0 mA max.		
OFF delay 0.2 ms max. Input filter value Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms) Number of circuits per common Input indicators LED display (yellow)			
Input filter value Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms) Number of circuits per common 16 inputs/common Input indicators LED display (yellow)	0.1 ms max.		
Number of circuits per common 16 inputs/common Input indicators LED display (yellow)	0.2 ms max.		
Input indicators LED display (yellow)	Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms)		
	16 inputs/common		
Isolation method Photocoupler isolation	LED display (yellow)		
	Photocoupler isolation		
I/O power supply method Supply by I/O power supply	Supply by I/O power supply		
Unit power supply current consumption 90 mA max. (for 20.4 to 26.4-VDC power supply voltage)	90 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
I/O power supply current consumption 5 mA max. (for 20.4 to 26.4-VDC power supply voltage)	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
Weight 180 g max.	180 g max.		
Expansion functions Enabled	Enabled		
hort-circuit protection function No			

Note: For the I/O power supply current value to V and G terminals, refer to GX Series Operation Manual (Cat. No. W488).

Output Section Specifications

16-point Output Terminals

Item	Specification	
item	GX-OD1611	GX-OD1621
Output capacity	16 points	
Rated current (ON current)	0.5 A/output, 4.0 A/common	
Internal I/O common	NPN	PNP
Residual voltage	1.2 V max. (0.5 ADC, between each output termi- nal and the G ter- minal)	1.2 V max. (0.5 ADC, between each output termi- nal and the V termi- nal)
Leakage current	0.1 mA max.	
ON delay	0.5 ms max.	
OFF delay	1.5 ms max.	
Number of circuits per common	16 points/common	
Output indicators	LED display (yellow)	
Isolation method	Photocoupler isolation	
I/O power supply method	Supply by I/O power supply	
Unit power supply current consumption	90 mA max. (for 20.4 to 26.4-VDC power supply voltage)	
I/O power supply current consumption	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)	
Weight	180 g max.	
Expansion functions	Enabled	
Output handling for communications errors	Select either hold or clear	
Short-circuit protection function	tion No	
Note: For the I/O newer supply		

Note: For the I/O power supply current value to V and G terminals, refer to GX Series Operation Manual (Cat. No. W488).

Relay 16-point Output Terminals

Item	Specification
item	GX-OC1601
Output capacity	16 points
Mounted relays	DRTA-NY5W-K
Rated load	Resistance load 250 VAC 2 A/output, common 8 A 30 VDC 2 A/output, common 8 A
Rated ON current	3 A/output
Maximum contact voltage	250 VAC, 125 VDC
Maximum contact current	3 A/output
Maximum switching capacity	750 VAAC, 90 WDC
Minimum applicable load (reference value)	5 VDC 1mA
Mechanical service life	20,000,000 operations min.
Electrical service life	100,000 operations min.
Number of circuits per common	8 points/common
Output indicators	LED display (yellow)
Isolation method	Relay isolation
I/O power supply method	The relay drive power is supplied from the unit power supply.
Unit power supply current consumption	210 mA max. (for 20.4 to 26.4-VDC power supply voltage)
Weight	290 g max.
Expansion functions	Enabled
Output handling for communications errors	Select either hold or clear
Short-circuit protection function	No

Precautions for Correct Use

- With a current of between 2 and 3 A (8 to 10 A per common), either ensure that the number of points per common that simultaneously turn ON does not exceed 4 or ensure that the ambient temperature does not exceed 45 °C. Also, there are no restrictions if the current does not exceed 2 A (8 A per common).
- The rated current is the value for assuring normal operation, and not for assuring durability of the relays. The relay service life depends greatly on factors such as the operating temperature, the type of load, and switching conditions. The actual equipment must be checked under actual operating conditions.

Input and Output Section Specifications 8-point Input and 8-point output Terminals General Specifications

Itama	Specification		
Item	GX-MD1611	GX-MD1621	
Internal I/O common	NPN	PNP	
I/O indicators	LED display (yellow)		
Unit power supply current consumption	80 mA max. (for 20.4 to 26 age)	.4-VDC power supply volt-	
Weight	190 g max.		
Expansion functions	No		
Short-circuit protection function	No		

Input Section


Item	Specification		
item	GX-MD1611	GX-MD1621	
Input capacity	8 points		
ON voltage	15 VDC min. (between each input terminal and the V terminal) minal and the G terminal)		
OFF voltage	5 VDC max. (between each input terminal and the V terminal) 5 VDC max. (between each input terminal minal and the G terminal)		
OFF current	1.0 mA max.		
Input current	6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC)		
ON delay	0.1 ms max.		
OFF delay	0.2 ms max.		
Input filter value	Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms)		
Number of circuits per common	8 points/common		
Isolation method	Photocoupler isolation		
I/O power supply method	Supply by I/O power supply		
I/O power supply cur- rent consumption	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)		

Output Section


14	Specification		
Item	GX-MD1611	GX-MD1621	
Output capacity	8 points		
Rated output current	0.5 A/output, 2.0 A/commo	on	
Residual voltage	1.2 V max. (0.5 ADC, between each output terminal and the G terminal) 1.2 V max. (0.5 ADC, between each output terminal and the V terminal)		
Leakage current	0.1 mA max.		
ON delay	0.5 ms max.		
OFF delay	1.5 ms max.		
Number of circuits per common	8 points/common		
Isolation method	Photocoupler isolation		
I/O power supply method	Supply by I/O power supply		
I/O power supply cur- rent consumption	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
Output handling for communications errors	Select either hold or clear		

Components and Functions

16 Inputs Terminal GX-ID1611/ID1621 16 Outputs Terminal GX-OD1611/OD1621




Relay 16-point Output Terminals GX-OC1601



No.	Name	Function	
1	Communica- tions connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.	
2	Unit Power Supply Connector	Connect the unit power supply (24 VDC).	
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.	
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.	
5	Input terminal: Input indicator (0 to 15) Output terminal: Output indicator (0 to 15)	Indicates the state of input/output contact (ON/OFF). Input terminal: Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state) Output terminal: Not lit: Contact OFF (output OFF state) Lit in yellow: Contact ON (output ON state)	
6	Terminal Block	Connects external devices and the I/O power supply. V, G: I/O power supply terminals 0 to 15: Input terminals	
7	DIN track mounting hook	Fixes a slave to a DIN track.	

No.	Name	Function	
1	Communica- tions connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.	
2	Unit Power Supply Connector	Connect the unit power supply (24 VDC).	
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.	
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.	
5	Output indicator (0 to 15)	Indicates the state of output contact (ON/OFF). Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state)	
6	Output Relay	Turn ON/OFF the contacts.	
7	Terminal Block	Connects external devices and the I/O power supply. COM0, COM1: Common terminals 0 to 15: Output terminals	
8	DIN track mounting hook	Fixes a slave to a DIN track.	

8 Inputs Terminal / 8 Outputs Terminal GX-MD1611/MD1621




	+		
No.	Name	Function	
1	Communica- tions connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.	
2	Unit Power Sup- ply Connector	Connect the unit power supply (24 VDC).	
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.	
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.	
5	Input indicator (0 to 7)	Indicates the state of input contact (ON/OFF). Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state)	
6	Output indicator (0 to 7)	Indicates the state of output contact (ON/OFF). Not lit: Contact OFF (output OFF state) Lit in yellow: Contact ON (output ON state)	
7	Terminal Block	Connects external devices and the I/O power supply. <left side=""> V1, G1: Input I/O terminals 0 to 7: Input terminals <right side=""> V2, G2: Output I/O terminals 0 to 7: Output terminals</right></left>	
8	DIN track mounting hook	Fixes a slave to a DIN track.	


GX-Series Digital I/O Terminal 2-tier Terminal Block Type

Wiring


GX-ID1611 (NPN)




GX-OD1611 (NPN)




GX-OC1601




GX-MD1611 (NPN)




GX-ID1621 (PNP)



GX-OD1621 (PNP)





GX-MD1621 (PNP)




Note: Wire colors have been changed according to revisions in the JIS standards for photoelectric and proximity sensors. The colors in parentheses are the wire colors prior to the revisions.

Dimensions (Unit: mm)






GX-OC1601



GX-MD1611/MD1621



Digital I/O Terminal 3-tier Terminal Block Type


GX-ID16□2/OD16□2/MD16□2

A common terminal is provided for each contact.

It eliminate the needs for relay terminal blocks

- It is unnecessary to share the common terminal among multiple contacts.
 - Easy-to-find wiring locations.
- Detachable screw terminal block facilitates the maintenance.
- Input response time can be switched for high-speed processing.
- Selectable node address setting methods: setting with rotary switch and with tool software.

When setting the nodes with rotary switch, setting is easy and node identification becomes possible for maintenance.



General Specifications

For Common Specifications of I/O terminals, refer to page 1.

Input Section Specifications 16-point Input Terminals

14	Specification		
Item	GX-ID1612	GX-ID1622	
Input capacity	16 points		
Internal I/O com- mon	NPN	PNP	
ON voltage	15 VDC min. (between each input terminal and the V terminal)	15 VDC min. (between each input terminal and the G terminal)	
OFF voltage	5 VDC max. (between each input ter- minal and the V terminal)	5 VDC max. (between each input terminal and the G terminal)	
OFF current	1.0 mA max.		
Input current	6.0 mA max./input (at 24-V 3.0 mA min./input (at 17-VI		
ON delay	0.1 ms max.	_	
OFF delay	0.2 ms max.		
Input filter value Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 m 32 ms (Default setting: 1 ms)			
Number of circuits per common	8 points/common		
Input indicators	LED display (yellow)		
Isolation method	Photocoupler isolation		
I/O power supply method	Supply by I/O power supply		
Input device supply current	100 mA/point		
Unit power supply current consumption	90 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
I/O power supply current consump- tion	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
Weight	370 g max.		
Expansion functions	No		
Short-circuit pro- tection function	No		

Note: For the I/O power supply current value to V and G terminals, refer to GX Series Operation Manual (Cat. No. W488).

Output Section Specifications 16-point Output Terminals

ltown	Specification		
Item	GX-OD1612	GX-OD1622	
Output capacity	16 points		
Rated current (ON current)	0.5 A/output, 4.0 A/commo	n	
Internal I/O com- mon	NPN	PNP	
Residual voltage	1.2 V max. (0.5 ADC, between each output terminal and the G terminal)	1.2 V max. (0.5 ADC, between each output terminal and the V terminal)	
Leakage current	0.1 mA max.		
ON delay	0.5 ms max.		
OFF delay	1.5 ms max.		
Number of circuits per common	8 points/common		
Output indicators	LED display (yellow)		
Isolation method	Photocoupler isolation		
I/O power supply method	Supply by I/O power supply		
Output device sup- ply current	100 mA/point		
Unit power supply current consumption	90 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
I/O power supply current consump- tion	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
Weight	370 g max.		
Expansion functions	No		
Output handling for communications errors	Select either hold or clear		
Short-circuit protection function	No		

Input and Output Section Specifications 8-point Input and 8-point output Terminals General Specifications

Item	Specification		
item	GX-MD1612	GX-MD1622	
Internal I/O com- mon	NPN PNP		
I/O indicators	LED display (yellow)		
Unit power supply current consumption	90 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
Weight	370 g max.		
Expansion func- tions	No		
Short-circuit pro- tection function	No		

Input Section


14	Specification		
Item	GX-MD1612	GX-MD1622	
Input capacity	8 points		
ON voltage	15 VDC min. (between each input ter- minal and the V terminal)	15 VDC min. (between each input ter- minal and the G terminal)	
OFF voltage	5 VDC max. (between each input terminal and the V terminal)	5 VDC max. (between each input terminal and the G terminal)	
OFF current	1.0 mA max./input		
Input current	6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC)		
ON delay	0.1 ms max.		
OFF delay	0.2 ms max.		
Input filter value	Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms)		
Number of circuits per common	8 points/common		
Isolation method	Photocoupler isolation		
I/O power supply method	Supply by I/O power supply		
Input device supply current	100 mA/point		
I/O power supply current consumption 5 mA max. (for 20.4 to 26.4-VDC page)		1-VDC power supply volt-	

Output Section

	Specification		
Item	GX-MD1612	GX-MD1622	
Output capacity	8 points		
Rated output cur- rent	0.5 A/output, 2.0 A/commo	n	
Residual voltage	1.2 V max. (0.5 ADC, between each output terminal and the G terminal) 1.2 V max. (0.5 ADC, between each output terminal)		
Leakage current	0.1 mA max.		
ON delay	0.5 ms max.		
OFF delay	1.5 ms max.		
Number of circuits per common	8 points/common		
Isolation method	Photocoupler isolation		
I/O power supply method	Supply by I/O power supply		
Output device sup- ply current	100 mA/point		
I/O power supply current consumption	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
Output handling for communications errors	Select either hold or clear		


Components and Functions

16 Inputs Terminal GX-ID1612/ID1622 16 Outputs Terminal GX-OD1612/OD1622



No.	Name	Function
1	Communications connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.
2	Unit Power Supply Connector	Connect the unit power supply (24 VDC).
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.
5	Input terminal: Input indicator (0 to 15) Output terminal: Output indicator (0 to 15)	Indicates the state of input/output contact (ON/OFF). Input terminal: Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state) Output terminal: Not lit: Contact OFF (output OFF state) Lit in yellow: Contact ON (output ON state)
6	Terminal Block	Connects external devices and the I/O power supply. <left side=""> V1, G1: I/O power supply terminals 0 to 7: Output terminals <right side=""> V2, G2: I/O power supply terminals 8 to 15: Input terminals (Output terminals)</right></left>
7	DIN track mounting hook	Fixes a slave to a DIN track.


8 Inputs Terminal / 8 Outputs Terminal GX-MD1612/MD1622




No.	Name	Function
1	Communications connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.
2	Unit Power Supply Connector	Connect the unit power supply (24 VDC).
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.
5	Input indicator (0 to 7)	Indicates the state of input contact (ON/OFF). Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state)
6	Output indicator (0 to 7)	Indicates the state of output contact (ON/OFF). Not lit: Contact OFF (output OFF state) Lit in yellow: Contact ON (output ON state)
7	Terminal Block	Connects external devices and the I/O power supply. <left side=""> V1, G1: Input I/O puwer supply terminals 0 to 7: Input terminals <right side=""> V2, G2: Output I/O power supply terminals 0 to 7: Output terminals</right></left>
8	DIN track mounting hook	Fixes a slave to a DIN track.

Wiring


GX-ID1612 (NPN)




GX-OD1612 (NPN)




GX-MD1612 (NPN)




GX-ID1622 (PNP)



GX-OD1622 (PNP)




GX-MD1622 (PNP)



Note: Wire colors have been changed according to revisions in the JIS standards for photoelectric and proximity sensors. The colors in parentheses are the wire colors prior to the revisions.

Dimensions (Unit: mm)

GX-ID1612/ID1622 GX-OD1612/OD1622 GX-MD1612/MD1622



Digital I/O Terminal e-CON Connector Type


GX-_D16_8/_D32_8

Easy wiring using industry standard e-CON connectors. Special wiring tool is not necessary

- Digital I/O terminal with industry standard e-CON connectors.
- A common terminal is provided for each connector.

 The I/O terminal and the sensors can be connected directly.
- Input response time can be switched for high-speed processing.
- Selectable node address setting methods: setting with rotary switch and with tool software.

When setting the nodes with rotary switch, setting is easy and node identification becomes possible for maintenance.



General Specifications

For Common Specifications of I/O terminals, refer to page 1.

Input Section Specifications 16-point Input Terminals

	Specification	
Item	GX-ID1618	GX-ID1628
Input capacity	16 points	
Internal I/O common	NPN	PNP
ON voltage	15 VDC min. (between each input terminal and the V terminal)	15 VDC min. (between each input terminal and the G terminal)
OFF voltage	5 VDC max. (between each input terminal and the V terminal)	5 VDC max. (between each input terminal and the G terminal)
OFF current	1.0 mA max.	
Input current	6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC)	
ON delay	0.1 ms max.	
OFF delay	0.2 ms max.	
Input filter value	Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms)	
Number of circuits per common	16 points/common	
Input indicators	LED display (yellow)	
Isolation method	No isolation	
I/O power supply method	Supplied from unit p	ower supply
Input device supply current	50 mA/point	
Unit power supply current consumption	150 mA max. (for 20.4 to 26.4-VDC power supply voltage)	
e-CON Connector insertion durability	50 times	
Weight	140 g max.	
Expansion functions	No	
Short-circuit protection function	Available (Operates at 50 mA/point min.)	

Note: For the I/O power supply current value to V and G terminals, refer to GX Series Operation Manual (Cat. No. W488).

32-point Input Terminals

14	Specification	
Item	GX-ID3218	GX-ID3228
Input capacity	32 points	
Internal I/O common	NPN	PNP
ON voltage	15 VDC min. (between each in- put terminal and the V terminal)	15 VDC min. (between each in- put terminal and the G terminal)
OFF voltage	5 VDC max. (between each in- put terminal and the V terminal)	5 VDC max. (between each in- put terminal and the G terminal)
OFF current	1.0 mA max.	
Input current	6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC)	
ON delay	0.1 ms max.	
OFF delay	0.2 ms max.	
Input filter value	Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms)	
Number of circuits per common	32 points/common	
Input indicators	LED display (yellow)
Isolation method	No isolation	
I/O power supply method	d Supplied from unit power supply	
Input device supply current	50 mA/point	
Unit power supply current consumption 230 mA max. (for 20.4 to 26.4-V er supply voltage)		0.4 to 26.4-VDC pow-
e-CON Connector insertion durability	50 times	
Weight	220 g max.	
Expansion functions	No	
Short-circuit protection function	Available (Operates at 50 mA/point min.)	

Output Section Specifications 16-point Output Terminals

	Specification	
Item	•	1
	GX-OD1618	GX-OD1628
Output capacity	16 points	
Rated current (ON current)	0.5 A/output, 4.0 A/o	common
Internal I/O common	NPN	PNP
Residual voltage	1.2 V max. (0.5 ADC, between each output termi- nal and the G ter- minal)	1.2 V max. (0.5 ADC, between each output termi- nal and the V termi- nal)
Leakage current	0.1 mA max.	
ON delay	0.5 ms max.	
OFF delay	1.5 ms max.	
Number of circuits per common	16 points/common	
Output indicators	LED display (yellow)	
Isolation method	Photocoupler isolation	
I/O power supply method	Supply by I/O power supply	
Output device supply current	100 mA/point	
Unit power supply current consumption	80 mA max. (for 20.4 to 26.4-VDC power supply voltage)	
Current consumption from I/O power supply	10 mA max. (for 20.4 to 26.4-VDC power supply voltage)	
e-CON Connector insertion durability	50 times	
Weight	130 g max.	
Expansion functions	No	
Output handling for communications errors	Select either hold or clear	
Short-circuit protection function	No No	

Note: For the I/O power supply current value to V and G terminals, refer to GX Series Operation Manual (Cat. No. W488).

Input and Output Section Specifications 8-point Input and 8-point output Terminals General Specifications

Item	Specification	
item	GX-MD1618	GX-MD1628
Internal I/O common	NPN	PNP
I/O indicators	LED display (yellow)
Unit power supply current consumption	120 mA max. (for 20.4 to 26.4-VDC power supply voltage)	
e-CON Connector insertion durability	50 times	
Weight	140 g max.	
Expansion functions	No	
Short-circuit protection function	Available at input section only (Operates at 50 mA/point min.)	

32-point Output Terminals

	Specification	
Item	GX-OD3218	GX-OD3228
Output capacity	32 points	
Rated current (ON current)	0.5 A/output, 4.0 A/o	common
Internal I/O common	NPN	PNP
Residual voltage	1.2 V max. (0.5 ADC, between each output termi- nal and the G ter- minal)	1.2 V max. (0.5 ADC, between each output termi- nal and the V termi- nal)
Leakage current	0.1 mA max.	
ON delay	0.5 ms max.	
OFF delay	1.5 ms max.	
Number of circuits per common	16 points/common	
Output indicators	LED display (yellow)
Isolation method	Photocoupler isolati	on
I/O power supply method	Supply by I/O power	r supply
Output device supply current	100 mA/point	
Unit power supply current consumption	100 mA max. (for 20 er supply voltage)	0.4 to 26.4-VDC pow-
Current consumption from I/O power supply	10 mA max. (for 20.4 supply voltage)	to 26.4-VDC power
e-CON Connector insertion durability	50 times	
Weight	210 g max.	
Expansion functions	No	
Output handling for communications errors	Select either hold or	clear
Short-circuit protection function	No	

Input Section

	Specification	
Item	GX-MD1618	GX-MD1628
Input capacity	8 points	
ON voltage	15 VDC min. (between each input terminal and the V terminal)	15 VDC min. (between each input ter- minal and the G termi- nal)
OFF voltage	5 VDC max. (between each input terminal and the V terminal)	5 VDC max. (between each input terminal and the G terminal)
OFF current	1.0 mA max.	
Input current	6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC)	
ON delay	0.1 ms max.	
OFF delay	0.2 ms max.	
Input filter value	Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms)	
Number of circuits per common	8 points/common	
Isolation method	No-isolation	
I/O power supply method	Supplied from unit power supply	
Input device supply current	50 mA/point	
I/O power supply cur- rent consumption	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)	

16-point Input and 16-point output Terminals General Specifications

•	Specification		
Item	ореспісаціон		
	GX-MD3218	GX-MD3228	
Internal I/O common	NPN	PNP	
I/O indicators	LED display (yellow)		
Unit power supply current consumption	140 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
e-CON Connector inser- tion durability	50 times		
Weight	220 g max.		
Expansion functions	No		
Short-circuit protection function	Available at input section only (Operates at 50 mA/point min.)		

Input Section

	Specification	
Item	GX-MD3218	GX-MD3228
Input capacity	16 points	
ON voltage	15 VDC min. (between each input terminal and the V terminal)	15 VDC min. (between each input ter- minal and the G termi- nal)
OFF voltage	5 VDC max. (between each input terminal and the V terminal)	5 VDC max. (between each input terminal and the G terminal)
OFF current	1.0 mA max.	
Input current	6.0 mA max./input (at 24-VDC) 3.0 mA min./input (at 17-VDC)	
ON delay	0.1 ms max.	
OFF delay	0.2 ms max.	
Input filter value	Without filter, 0.5 ms, 1 ms, 2 ms, 4 ms, 8 ms, 16 ms, 32 ms (Default setting: 1 ms)	
Number of circuits per common	16 points/common	
Isolation method	No-isolation	
I/O power supply method	Supplied from unit power supply	
Input device supply current	50 mA/point	
I/O power supply cur- rent consumption	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)	

Output Section

	Specif	ication
Item	GX-MD1618	GX-MD1628
Output capacity	8 points	
Rated output current	0.5 A/output, 2.0 A/comm	on
Residual voltage	1.2 V max. (0.5 ADC, between each output terminal and the G terminal)	1.2 V max. (0.5 ADC, between each output terminal and the V terminal)
Leakage current	0.1 mA max.	_
ON delay	0.5 ms max.	
OFF delay	1.5 ms max.	
Number of circuits per common	8 points/common	
Isolation method	Photocoupler isolation	
I/O power supply method	Supply by I/O power supp	oly
Output device supply current	100 mA/point	
I/O power supply cur- rent consumption	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)	
Output handling for communications errors	Select either hold or clear	


Note: For the I/O power supply current value to V and G terminals, refer to GX Series Operation Manual (Cat. No. W488).

Output Section

Item	Specification	
item	GX-MD3218	GX-MD3228
Output capacity	16 points	
Rated output current	0.5 A/output, 2.0 A/comm	on
Residual voltage	1.2 V max. (0.5 ADC, between each output terminal and the G terminal)	1.2 V max. (0.5 ADC, between each output terminal and the V terminal)
Leakage current	0.1 mA max.	
ON delay	0.5 ms max.	
OFF delay	1.5 ms max.	
Number of circuits per common	16 points/common	
Isolation method	Photocoupler isolation	
I/O power supply method	Supply by I/O power supply	
Output device supply current	100 mA/point	
I/O power supply cur- rent consumption	5 mA max. (for 20.4 to 26.4-VDC power supply voltage)	
Output handling for communications errors	Select either hold or clear	


Components and Functions

16 Inputs Terminal GX-ID1618/ID1628




No.	Name	Function
1	Communications connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.
2	Unit Power Supply Connector	Connect the unit power supply (24 VDC).
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.
5	Input indicator (0 to 15)	Indicates the state of input contact (ON/OFF). Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state)
6	I/O connector (0 to 15)	Connects an external device.
7	DIN track mounting hook	Fixes a slave to a DIN track.

16 Outputs Terminal GX-OD1618/OD1628




No.	Name	Function
1	Communications con- nector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.
2	Unit Power Supply Connector	Connect the unit power supply (24 VDC).
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.
5	Output indicator (0 to 15)	Indicates the state of output contact (ON/OFF). Not lit: Contact OFF (output OFF state) Lit in yellow: Contact ON (output ON state)
6	I/O connector (0 to 15)	Connects an external device.
7	I/O power supply con- nector	Supplies the I/O power.
8	DIN track mounting hook	Fixes a slave to a DIN track.

8 Inputs/8 Outputs Terminal GX-MD1618/MD1628




No.	Name	Function
1	Communications connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.
2	Unit Power Supply Connector	Connect the unit power supply (24 VDC).
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.
5	Input indicator (0 to 7)	Indicates the state of input contact (ON/OFF). Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state)
6	Output indicator (0 to 7)	Indicates the state of output contact (ON/OFF). Not lit: Contact OFF (output OFF state) Lit in yellow: Contact ON (output ON state)
7	I/O connector (0 to 15)	Connects an external device. <top side=""> For input device <bottom side=""> For output device</bottom></top>
8	I/O power supply con- nector	Supplies the I/O power. (For output device)
9	DIN track mounting hook	Fixes a slave to a DIN track.

32 Inputs Terminal GX-ID3218/ID3228




No.	Name	Function	
1	Communications connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.	
2	Unit Power Sup- ply Connector	Connect the unit power supply (24 VDC).	
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.	
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.	
5	Input indicator (IN1 0 to 15, IN2 0 to 15)	Indicates the state of input contact (ON/OFF). Input terminal: Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state)	
6	I/O connector (0 to 15×2)	Connects an external device.	
7	DIN track mounting hook	Fixes a slave to a DIN track.	

32 Outputs Terminal GX-OD3218/OD3228



No.	Name	Function	
1	Communications connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.	
2	Unit Power Sup- ply Connector	Connect the unit power supply (24 VDC).	
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.	
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.	
5	Output indicator (OUT1 0 to 15, OUT2 0 to 15)	Indicates the state of output contact (ON/OFF). Not lit: Contact OFF (output OFF state) Lit in yellow: Contact ON (output ON state)	
6	I/O connector (0 to 15 × 2)	Connects an external device.	
7	I/O power supply connector	Supplies the I/O power.	
8	DIN track mounting hook	Fixes a slave to a DIN track.	


16 Inputs/16 Outputs Terminal GX-MD3218/MD3228




No.	Name	Function	
140.	Humo	1 111	
1	Communications connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.	
2	Unit Power Sup- ply Connector	Connect the unit power supply (24 VDC).	
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.	
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.	
5	Input indicator (0 to 15)	Indicates the state of input contact (ON/OFF). Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state)	
6	Output indicator (0 to 15)	Indicates the state of output contact (ON/OFF). Not lit: Contact OFF (output OFF state) Lit in yellow: Contact ON (output ON state)	
7	I/O connector (0 to 15 × 2)	Connects an external device. <top side=""> For input device <bottom side=""> For output device</bottom></top>	
8	I/O power supply connector	Supplies the I/O power. (For output device)	
9	DIN track mount- ing hook	Fixes a slave to a DIN track.	

Wiring


GX-ID1618 (NPN)




GX-ID1628 (PNP)




GX-OD1618 (NPN)




GX-OD1628 (PNP)




GX-ID3218 (NPN)




GX-ID3228 (PNP)




GX-OD3218 (NPN)




GX-OD3228 (PNP)



GX-MD3218 (NPN)




GX-MD3228 (PNP)



Note: Wire colors have been changed according to revisions in the JIS standards for photoelectric and proximity sensors. The colors in parentheses are the wire colors prior to the revisions.

Dimensions (Unit: mm)



Analog I/O Terminal 2-tier Terminal Block Type

GX-AD0471/DA0271

Analog I/O terminal with screw terminal block for EtherCAT communications

- The input/output range can be easily changed by the setting with the switch.
- Detachable screw terminal block facilitates the maintenance.
- Moving average calculation function. Settings within the range of $100\mu s$ -64ms. (For input only.)
- Disconnection detection function.
 (For input only and for usage with 1-5V or 4-20mA ranges.)
- Selectable node address setting methods: setting with rotary switch and with tool software.

When setting the nodes with rotary switch, setting is easy and node identification becomes possible for maintenance.



General Specifications

For Common Specifications of I/O terminals, refer to page 1.

Input Section Specifications 4-point Input Terminals

Item		Specification		
		Voltage input	Current input	
Input capacity		4 points (possible to abled channels)	set number of en-	
Input range		0 to 5V 1 to 5V 0 to 10V -10 to +10V	4 to 20mA	
Input range setting method		Input range switch: Common to input CH1/ CH2, common to input CH3/CH4 SDO communication: Possible to set input CH1 to CH4 individually		
Maximum signal i	nput	± 15 V	± 30 mA	
Input impedance		1 M Ω min.	Approx. 250 Ω	
Resolution		1/8000 (full scale)		
Overall acquirect	25 °C	± 0.3% FS	± 0.4% FS	
Overall accuracy	−10 to +55 °C	± 0.6% FS	± 0.8% FS	
Analog conversion cycle		500 μs/input When 4 points are used: 2 ms max.		
A/D converted data		Other than \pm 10 V: 0000 to 1F40 Hex full scale (0 to 8000) \pm 10 V: F060 to 0FA0 Hex full scale (-4000 to +4000) A/D conversion range: \pm 5% FS of the above data ranges.		
Isolation method		Photocoupler isolation (between input and communications lines) No isolation between input signals		
Unit power supply current consumption		120 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
Weight		180 g max.		
Accessories		Four short-circuit metal fixtures (for current input) *		

^{*} Short-circuit metal fixtures are used for current input only, but store in a safe place when using for voltage inputs as well.


Output Section Specifications 2-point Output Terminals

Item		Specification		
		Voltage output	Current output	
Output capacity		2 points (possible to abled channels)	set number of en-	
Output range		0 to 5V 1 to 5V 0 to 10V -10 to +10V	4 to 20mA	
Output range setting method		Output range switch, SDO communications: Possible to set outputs CH1 and CH2 separately.		
External output allowable load resistance		5 kΩ min.	600 Ω max.	
Resolution		1/8000 (full scale)		
Overell ecoures.	25 °C	± 0.4% FS		
Overall accuracy	−10 to +55 °C	± 0.8%FS		
Analog conversion cycle		500 μs/input When 2 points are used: 1 ms max.		
D/A converted data		Other than ± 10 V: 0000 to 1F40 Hex full scale (0 to 8000) ± 10 V: F060 to 0FA0 Hex full scale (-4000 to +4000) D/A conversion range: ± 5% FS of the above data ranges		
Isolation method		Photocoupler isolation (between output and communications lines) No isolation between output signals		
Unit power supply current consumption		150 mA max. (for 20.4 to 26.4-VDC power supply voltage)		
Weight		190 g max.		

GX-Series Analog I/O Terminal 2-tier Terminal Block Type


Components and functions

4-points Analog Inputs Terminal GX-AD0471



No.	Name	Function	
1	Communications connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.	
2	Unit Power Supply Connector	Connect the unit power supply (24 VDC).	
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.	
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.	
5	Input range switch	DIP switch for setting input range.	
6	Terminal Block	Terminal block for analog input signals V1 to V4: Voltage input terminals I1 to I4: Current input terminals AG: Analog GND NC: Not used	
7	DIN track mounting hook	Fixes a slave to a DIN track.	


2-points Analog Inputs Terminal GX-DA0271



No.	Name	Function	
1	Communications connector	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.	
2	Unit Power Supply Connector	Connect the unit power supply (24 VDC).	
3	Status indicator	It indicates the communication state and the operation state of I/O terminals.	
4	Node address Switch	It sets node addresses of terminals (decimal). Setting range is 00 to 99.	
5	Output range switch	DIP switch for setting output range.	
6	Terminal Block	Terminal block for analog output signals V1+, V2+: Voltage output positive terminals I1+, I2+: Current output positive terminals 1-, 2-: Voltage/current output negative terminals NC: Not used	
7	DIN track mounting hook	Fixes a slave to a DIN track.	

Wiring


GX-AD0471



* Short-circuit the "V positive" terminal and "I positive" terminal at current input.

Use the attached short-circuit metal fixture to short-circuit terminals.


GX-DA0271



GX-Series Analog I/O Terminal 2-tier Terminal Block Type

Dimensions (Unit: mm)

GX-AD0471 GX-DA0271



Encoder Input Terminal 3-tier Terminal Block Type

GX-EC0211/EC0241

EtherCAT-compatible encoder input terminal which enables high-speed and accurate control

- Two counter function available. Pulse count within 32 bit range.
- Maximum input pulse frequency of 4MHz (Line driver input after quadrature). High-speed network EtherCAT enables high-speed and accurate control.
- Selectable two input types: Open collector input and line driver input.
- Built-in two external latch inputs and one reset input .
- Selectable node address settings: setting with rotary switches and setting on tool software.
- Detachable screw terminal will facilitate the maintenance work.



General Specifications

For Common Specifications of I/O terminals, refer to page 1.

Open collector inputs Type

Terminal specifications

Item	Specification	
Counter point	2 points	
Input signal	Counter phase A Counter phase B Counter phase Z Latch input (A/B) Counter reset input	
Counter enabled status display	LED display (green)	
Input indicators	LED display (yellow)	
Unit power supply current consumption	130 mA max. (for 20.4 to 26.4 VDC power supply voltage)	
Weight	390 g max.	

Pulse input specifications

léana	Specification				
Item	Counte	er phase A/B	Count	ter phase Z	
Input voltage	20.4 to 26.4 VDC (24 VDC -15 to +10%)	4.5 to 5.5 VDC (5 VDC ±5%)	20.4 to 26.4 VDC (24 VDC -15 to +10%)	4.5 to 5.5 VDC (5 VDC ±5%)	
Input current	8.4 mA (at 24 VDC)	8.6 mA (at 5 VDC)	8.4 mA (at 24 VDC)	8.6 mA (at 5 VDC)	
ON voltage	19.6 V min.	4.5 V min.	18.6 V min.	4.5 V min.	
OFF voltage	4 V max.	1.5 V max.	4 V max.	1.5 V max.	
Input restriction resistance	2.7 kΩ	430 Ω	2.7 kΩ	430 Ω	
Maximum response frequency	Single phase 500 kHz (phase difference Multiplic	Single phase 500 kHz (phase difference Multiplication × 4, 125 kHz)			
Filter switching	NA	NA		NA	

Latch/reset input specifications

ltam		Specification		
Item	Latch input (A/B)	Reset input		
Internal I/O common	NPN			
Input voltage	20.4 to 26.4 VDC (24 VDC -15 to +10%)	20.4 to 26.4 VDC (24 VDC -15 to +10%)		
Input impedance	4.0 kΩ	3.3 kΩ		
Input current	5.5 mA (at 24 VDC)	7 mA (at 24 VDC)		
ON voltage/ON current	17.4 VDC min./3 mA min.	14.4 VDC min./3 mA min.		
OFF voltage/OFF current	5 VDC max./1 mA max.	5 VDC max./1 mA max.		
ON response time	3 μs max.	15 μs max.		
OFF response time	3 μs max.	90 μs max.		

Note: For the pulse input timing specifications, refer to USER'S MANUAL (Cat. No. W488).

Line Driver inputs Type

Terminal specifications

Item	Specification
Counter point	2 points
Input signal	Counter phase A Counter phase B Counter phase Z Latch input (A/B) Counter reset input
Counter enabled status display	LED display (green)
Input indicators	LED display (yellow)
Unit power supply current consumption	100 mA max. (for 20.4 to 26.4 VDC power supply voltage)
Weight	390 g max.

Pulse input specifications

Item	Specification		
iteiii	Counter phase A/B	Counter phase Z	
Input voltage	EIA standard RS-422-A line driver level		
Input impedance	120 Ω ±5%		
gH level input voltage	0.1 V		
gL level input voltage	-0.1 V		
Hysteresis voltage	60 mV		
Maximum response frequency	Single phase 4 MHz (phase difference Multiplication ×4, 1 MHz)	1 MHz	
Filter switching	NA NA		


Latch/reset input specifications

ltem	Specification		
item	Latch input (A/B)	Reset input	
Internal I/O common	PNP		
Input voltage	20.4 to 26.4 VDC (24 VDC -15 to +10%)	20.4 to 26.4 VDC (24 VDC -15 to +10%)	
Input impedance	4.0 kΩ	3.3 kΩ	
Input current	5.5 mA (at 24 VDC)	7 mA (at 24 VDC)	
ON voltage/ON current	17.4 VDC min./3 mA min.	14.4 VDC min./3 mA min.	
OFF voltage/OFF current	5 VDC max./1 mA max.	5 VDC max./1 mA max.	
ON response time	3 μs max.	15 μs max.	
OFF response time	3 μs max.	90 μs max.	

Note: For the pulse input timing specifications, refer to USER'S MANUAL (Cat. No. W488).

Components and functions


Open collector inputs Type GX-EC0211 Line driver inputs Type GX-EC0241




No.	Name	Function	
1	Communications Connectors	(CN IN) Connects the communications cable which comes from the Master Unit side. (CN OUT) Connects the communications cable of the next I/O terminal.	
2	Unit Power Supply Connector	Connect the unit power supply (24 VDC).	
3	Status Indicators	It indicates the communication state and the operation state of I/O terminals.	
4	Node address Switches	It sets node addresses of terminals (decimal). Setting range is 00 to 99.	
5	Inputs Indicators	The indicators show the status of the inputs of each channel. For details, refer to GX Series Operation Manual (Cat.No.W488).	
6	Terminal Block	Connects external devices and the I/O power supply. For details, refer to GX Series Operation Manual (Cat.No.W488).	
7	DIN track mounting hook	Fixes Slave Unit to a DIN track.	

Wiring

Open collector inputs Type GX-EC0211




Line driver inputs Type GX-EC0241



Dimensions (Unit: mm)

GX-EC0211/EC0241



Expansion Units

XWT-□D08(-1)/□D16(-16)

Expansion I/O Units make expansion easy!

- Flexible expansion with many different combinations.
- Removable I/O terminal block enables faster startup time and improved maintainability.
- Common expansion unit with DeviceNet (DRT2-Series) and CompoNet (CRT1-Series).



General Specifications

For Common Specifications of I/O terminals, refer to page 1.

Input Section Specifications 8-point Input Expansion Units

	Specification		
Item	•		
	XWT-ID08	XWT-ID08-1	
Internal I/O common	NPN	PNP	
I/O capacity	8 inputs		
ON voltage	15 VDC min. (between each input terminal and the V termi- nal)	15 VDC min. (between each input terminal and the G termi- nal)	
OFF voltage	5 VDC max. (between each input terminal and the V termi- nal)	5 VDC max. (between each input terminal and the G termi- nal)	
OFF current	1.0 mA max.		
Input current	At 24 VDC: 6.0 mA max./input At 17 VDC: 3.0 mA min./input		
ON delay	1.5 ms max.		
OFF delay	1.5 ms max.		
Number of circuits per common	8 inputs/common		
Communications power supply current consumption	5 mA		
Weight	80 g max.		

Output Section Specifications 8-point Input Expansion Units

16	Specification		
Item	XWT-OD08	XWT-OD08-1	
Internal I/O common	NPN	PNP	
I/O capacity	8 outputs		
Rated output current	0.5 A/output, 2.0 A/comm	on	
Residual voltage	1.2 V max. (0.5 A DC, between each output terminal and the G terminal)	1.2 V max. (0.5 A DC, between each output terminal and the V terminal)	
Leakage current	0.1 mA max.		
ON delay	0.5 ms max.		
OFF delay	1.5 ms max.		
Number of circuits per common	8 outputs/common		
Communications power supply current consumption	5 mA		
Weight	80 g max.		

16-point Input Expansion Units


	Specification		
Item	XWT-ID16	XWT-ID16-1	
Internal I/O common	NPN	PNP	
I/O capacity	16 inputs		
ON voltage	15 VDC min. (between each input terminal and the V termi- nal) 15 VDC min. (between each input terminal and the G terminal)		
OFF voltage	5 VDC max. (between each input terminal and the V termi- nal)	5 VDC max. (between each input terminal and the G termi- nal)	
OFF current	1.0 mA max.		
Input current	At 24 VDC: 6.0 mA max./input At 17 VDC: 3.0 mA min./input		
ON delay	1.5 ms max.		
OFF delay	1.5 ms max.		
Number of circuits per common	16 inputs/common		
Communications power supply current consumption	10 mA		
Weight	120 g max.		

16-point Input Expansion Units

Item	Specification		
item	XWT-OD16	XWT-OD16-1	
Internal I/O common	NPN	PNP	
I/O capacity	16 outputs		
Rated output current	0.5 A/output, 4.0 A/comm	ion	
Residual voltage	1.2 V max. (0.5 A DC, between each output terminal and the G terminal)	1.2 V max. (0.5 A DC, between each output terminal and the V terminal)	
Leakage current	0.1 mA max.		
ON delay	0.5 ms max.		
OFF delay	1.5 ms max.		
Number of circuits per common	16 outputs/common		
Communications power supply current consumption	10 mA		
Weight	120 g max.		


Components and functions

XWT-ID08/ID08-1




No.	Name	Function
1	Input indicator (0 to 7)	Indicates the state of input contact (ON/OFF). Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state)
2	Terminal connector	Connects the connector on the right side of the slave.
3	Terminal block	Connects external devices and the I/O power supply. V, G: I/O power supply terminals 0 to 7: Input terminals
4	DIN track mounting hook	Fixes a slave to a DIN track.

XWT-ID16/ID16-1




No.	Name	Function	
1	Input indicator (0 to 15)	Indicates the state of input contact (ON/OFF). Not lit: Contact OFF (input OFF state) Lit in yellow: Contact ON (input ON state)	
2	Terminal connector	Connects the connector on the right side of the slave.	
3	Terminal block	Connects external devices and the I/O power supply. V, G: I/O power supply terminals 0 to 15: Input terminals	
4	DIN track mounting hook	Fixes a slave to a DIN track.	

XWT-OD08/OD08-1



No.	Name	Function	
1	Output indicator (0 to 7)	Indicates the state of output contact (ON/OFF). Not lit: Contact OFF (output OFF state) Lit in yellow: Contact ON (output ON state)	
2	Terminal connector	Connects the connector on the right side of the slave.	
3	Terminal block	Connects external devices and the I/O power supply. V, G: I/O power supply terminals 0 to 7: Output terminals	
4	DIN track mounting hook	Fixes a slave to a DIN track.	


XWT-OD16/OD16-1




No.	Name	Function	
1	Output indicator (0 to 15)	Indicates the state of output contact (ON/OFF). Not lit: Contact OFF (output OFF state) Lit in yellow: Contact ON (output ON state)	
2	Terminal connector	Connects the connector on the right side of the slave.	
3	Terminal block	Connects external devices and the I/O power supply. V, G: I/O power supply terminals 0 to 15: Output terminals	
4	DIN track mounting	Fixes a slave to a DIN track.	

Wiring


XWT-ID08 (NPN)




XWT-ID16 (NPN)




XWT-OD08 (NPN)




XWT-OD16 (NPN)




XWT-ID08-1 (PNP)




XWT-ID16-1 (PNP)



XWT-OD08-1 (PNP)




XWT-OD016-1 (PNP)




Note: Wire colors have been changed according to revisions in the JIS standards for photoelectric and proximity sensors. The colors in parentheses are the wire colors prior to the revisions.


Dimensions (Unit: mm)


XWT-ID08/ID08-1 XWT-OD08/OD08-1





XWT-ID16/ID16-1 XWT-OD16/OD16-1





IO-Link Master Unit

GX-ILM08C

IO-Link makes sensor level information visible and solves the three major issues at manufacturing sites!

The unit for M12 Smartclick connector can be used in watery, and dusty environments.




- Downtime can be reduced.
 Notifies you of faulty parts and such phenomena in the Sensor in real time.
- The frequency of sudden failure can be decreased.

 Condition monitoring of sensors and equipment to prevent troubles.
- The efficiency of changeover can be improved.
 The batch check for individual sensor IDs significantly decreases commissioning time.

Features

- The host controller can cyclically read control signals, status *1, wiring, and power supply status of IO-Link sensors. Because an IO-Link System can cyclically read analog data such as the amount of incident light in addition to ON/OFF information, it can be used for predictive maintenance based on detection of such things as decreases in the amount of light.
- User-specified data in IO-Link devices can be read and written from the host controller when necessary.
- Digital signals can be input rapidly from IO-Link sensors *2 during IO-Link communications.
- IO-Link sensors can be combined with non-IO-Link sensors.
- Incorrect connections of IO-Link sensors can be checked when IO-Link communications start.
- Backup and restoration of IO-Link device parameters make replacement of IO-Link sensors easier.
- IO-Link sensors can be easily replaced with non-IO-Link sensors without changing the data address settings. *3
- Sensors can report their errors to the master, which facilitates locating errors from the host.
- The total number of retries in cyclic communications can be recorded. You can use this value to check for the influences of noise and other problems.
 - (When EtherCAT is used as the host communication interface)
- Up to eight sensors can be connected. IP67 protection.
- *1 Examples for Photoelectric Sensors: Instability detection and sensor errors
- *2 IO-Link sensors that support digital inputs that use pin 2 of IO-Link Master Unit ports
- *3 Bit data of IO-Link sensor can be reflected in the address of the digital input data by using digital input collection. This function is supported with the unit version 1.1 or later.

System Configuration



- *1. When a host controller from another company is used with EtherCAT host communications, use the EtherCAT software application from the other company for a GX-type IO-Link Master Unit.
 - Note. For an NX-type IO-Link Master Unit, connect the Sysmac Studio to the EtherCAT Coupler Unit, as shown above.
- *2. When a host controller from another company is used with EtherCAT host communications, for a GX-type IO-Link Master Unit, make the IO-Link device settings with message communications from the host controller from the other company.
 - Note. For an NX-type IO-Link Master Unit, connect CX-ConfiguratorFDT to the EtherCAT Coupler Unit, as shown above.
- *3. You can also connect a combination of general-purpose sensors and other devices.

General Specification

láo ma	Charification	
Item	Specification	
Unit power supply voltage	20.4 to 26.4 VDC (24 VDC –15%/+10%)	
I/O power supply	20.4 to 26.4 VDC (24 VDC -15%/+10%)	
Noise resistance	Conforms to IEC 61000-4-4, 2 kV (power line).	
Vibration resistance	10 to 60 Hz with amplitude of 0.7 mm, 60 to 150 Hz and 50 m/s² for 80 minutes each in X, Y, and Z directions	
Shock resistance	150 m/s ² with amplitude of 0.7 mm	
Dielectric strength	600 VAC (between isolated circuits)	
Insulation resistance	20 MΩ min. (between isolated circuits)	
Ambient operating temperature	−10 to 55°C	
Ambient operating humidity	25% to 85% (with no condensation)	
Ambient operating atmosphere	No corrosive gases	
Altitude	2,000 m max.	
Storage temperature	-25 to 65°C	
Storage humidity	25% to 85% (with no condensation)	
Degree of protection	IP67	
Mounting	M5 screw mounting	
Mounting strength	100 N	
Communications connector strength	30 N	
Connector types	Connectors for EtherCAT communications: M12 (D-coding, female) × 2 Power supply connector: M12 (A-coding, male) × 1 I/O connectors: M12 (A-coding, female) *1 × 8	
Screw tightening torque *2	Round connectors (communications connector, power supply, and I/O): 0.39 to 0.49 N·m M5 (Unit mounted from the front):1.47 to 1.96 N·m Cover for node address setting switches: 0.4 to 0.6 N·m	
Applicable standards *3	UL 61010-2-201, EU: EN 61131-2, RCM, KC, IO-Link conformance, and EtherCAT conformance	

^{*1} Confirms to Class A when used as an IO-Link connector.

^{*2} For SmartClick Connectors, insert the Connector all the way and turn it approx. 1/8 of a turn. Torque management is not required.

*3 Refer to the OMRON website (www.ia.omron.com) or ask your OMRON representative for the most recent applicable standards for each model.

Unit Specification

Item Specification				
Unit name		IO-Link Master Unit		
Model		GX-ILM08C		
		8 8		
Number of IO-Link ports	Communications protocol			
	Communications protocol	IO-Link protocol		
Communications	Baud rate	COM1: 4.8 kbps COM2: 38.4 kbps COM3: 230.4 kbps		
specifications	Topology	1:1		
	Compliant standards	IO-Link Interface and System Specification Version1.1.2 IO-Link Test Specification Version1.1.2		
Device power supply * in	Rated voltage	24 VDC (20.4 to 26.4 VDC)		
IO-Link Mode or SIO (DI)	Maximum load current	0.2 A/port		
Mode	Short-circuit protection	Yes		
	Internal I/O common	PNP		
	Rated voltage	24 VDC (20.4 to 26.4 VDC)		
Digital inputs	Input current	5 mA typical (at 24 VDC)		
(in SIO (DI) Mode)	ON voltage/ON current	15 VDC min., 5 mA min.		
	OFF voltage	5 VDC max.		
	Input filter time	No filter, 0.25 ms, 0.5 ms, 1 ms (default), 2 ms, 4 ms, 8 ms, 16 ms, 32 ms, 64 ms, 128 ms, or 256 ms		
	Internal I/O common	PNP		
	Output type	Push-pull		
	Rated voltage	24 VDC (20.4 to 26.4 VDC)		
Digital outputs	Maximum load current	0.3 A/port		
(in SIO (DIO) Mode)	Short-circuit protection	Provided.		
	Leakage current	0.1 mA max.		
	Residual voltage	1.5 V max.		
	Internal I/O common	PNP		
	Rated voltage	24 VDC (20.4 to 26.4 VDC)		
Digital inputs for pin 2	Input current	2 mA (24 VDC)		
(in IO-Link Mode)	ON voltage/ON current	15 VDC min., 2 mA min.		
	OFF voltage	5 VDC max.		
	Input filter time	No filter, 0.25 ms, 0.5 ms, 1 ms (default), 2 ms, 4 ms, 8 ms, 16 ms, 32 ms, 64 ms, 128 ms, or 256 ms		
	Cable type	Unshielded		
	Cable length	20 m max.		
Cable specifications	Electrostatic capacity	2.5		
	between lines	3 nF max.		
	Loop resistance	6Ω max.		
Dimensions		$175 \times 33 \times 60$ mm (W×H×D) (The height is 49.1 mm when the connectors are included.)		
Isolation method		Photocoupler isolation		
I/O power supply method		Supplied from the power supply connector.		
Unit power supply current c	· · · · · · · · · · · · · · · · · · ·	60 mA		
I/O power supply current co	nsumption	100 mA		
Weight		430 g		
Circuit layout		IN communications connector OUT communications circuits Internal circuits Internal circuits IO-LINK circuits		
Installation orientation and	restrictions	Installation orientation: 6 possible orientations Restrictions: No restrictions		
Protective functions		L+ terminal short-circuit protection		
. Totalita fullations		C/Q terminal short-circuit protection		

[★] I/O power supply to devices:

This is the voltage and current value supplied to devices when the communications modes of the ports on the IO-Link Master Unit are IO-Link Mode or SIO (DI) Mode.

Function Specification

Fu	nction	Description	
Communications	Cyclic communications	I/O data (process data) in the IO-Link devices is cyclically exchanged with the IO-Link Master Unit as the IO-Link communications master. At the same time, this data and the status of the IO-Link Master Unit is cyclically exchanged with the controller, with the IO-Link Master Unit operating as a slave of the controller. Cyclic communications can be used to check the amount of detection performance deterioration in devices, and to check changes in usage conditions such as the amount of incident light for photoelectric sensors, stability detection margins, and excessive proximity for proximity sensors.	
Communications	Message communications	The controller can send messages (commands) to the IO-Link Master Unit and receive the response from the IO-Link Master Unit. The IO-Link Master Unit can also function as a gateway to send messages (commands and responses) between the controller and the IO-Link devices. Refer to 6-3 Message Communications in the IO-Link System User's Manual (Cat. No. W568). During operation, you can change and adjust device parameters, such as threshold settings, tuning execution, and ON-delay time changes, from a program. Or, during operation, you can check the internal status, such as the operating times of devices.	
Communications mode	settings	You can select any of the following modes for each port: IO-Link Mode, SIO (DI) Mode, SIO (DO) Mode, and Disable Port This allows you to combine IO-Link communications and digital I/O in a single unit.	
Digital inputs for pin 2		In IO-Link Mode, you can perform digital input with pin 2 while performing IO-Link communications.	
Automatic baud rate setting for IO-Link communications		The IO-Link Master Unit automatically matches the specific baud rates (COM1, COM2, or COM3) of the IO-Link devices to communicate with the IO-Link devices. Therefore, it is not necessary to set the baud rate of the connected device for each port.	
Connected device verification		This function is used to verify the configuration of IO-Link devices that are connected to the IO-Link Master Unit against the registered IO-Link Device Configuration Settings when the power supply is turned ON. The user can enable or disable connected device verification.	
IO-Link communications error detection		This function detects I/O cable breaks, disconnections from IO-Link device ports, error-level device events, device configuration verification errors, and IO-Link device malfunctions.	
Detection of short-circu	its in I/O cables	This function detects short-circuits in I/O cables.	
Nortification of input data validity		The controller can use the Input Data Enabled Flags to determine whether the process input data for IO-Link communications is valid.	
Load rejection for controller communications error		This function turns OFF outputs from the IO-Link Master Unit when a communications error occurs in communications with the controller in IO-Link Mode or in an SIO mode. This prevents incorrect output operations when communications error occurs.	
IO-Link total communications lost frames		The IO-Link total communications lost frames can be read from the CX-ConfiguratorFDT. You can use this function to determine communications status as affected by I/O cable noise or other factors.	
Digital input filter		This function is used to eliminate chattering and noise of the input signal for digital inputs in SIO(DI) Mode or for digital inputs for pin 2 in IO-Link Mode. It prevents data change and stabilizes the input signal even in situations where the input data changes due to chattering or noise and the bit status is unstable.	
Digital input collection ≭		In IO-Link Mode, this function reflects the specified bit data in the input data from the IO-Link device on the digital input data of the IO-Link Master Unit. As a result, the bit data in the input data from the IO-Link device can be aggregated into the digital input data of the IO-Link Master Unit. One bit for each IO-Link port can be aggregated. This function cannot be used in SIO (DI) Mode and SIO (DO) Mode. If you use this function, digital inputs with pin 2 cannot be used.	
Backup and restoration of parameter settings in IO-Link devices		This function is used to back up parameter settings in IO-Link devices in the IO-Link Master Unit or restore them to IO-Link devices. This eliminates the need to set parameters again after replacing an IO-Link device.	
Event log		This function records events, such as errors and status changes, that occur in the IO-Link Master Unit and IO-Link devices.	

^{*}This function is supported with the unit version 1.1 or later.

EtherCAT Communications Specifications

Item	Specification	
Communications protocol	EtherCAT protocol	
Modulation	Baseband	
Baud rate	100 Mbps	
Physical layer	100BASE-TX (IEEE 802.3)	
Connectors	M12 (D-coding, female) × 2 (shielded) CN IN: EtherCAT input CN OUT: EtherCAT output	
Communications media	Category 5 or higher (cable with double, aluminum tape and braided shielding is recommended.)	
Communications distance	Distance between nodes (Slave Units): 100 m max.	
Noise resistance	Conforms to IEC 61000-4-4, 1 kV or higher.	
Node address setting method	Set on hexadecimal node address switches or with a Configuration Tool.	
Node address range	000 to FFF hex (0 to 4,095 decimal): Set on node address switches or with a Configuration Tool.	
Indicators	UNIT PWR × 1 IO PWR × 1 L/A IN (Link/Activity IN) × 1 L/A OUT (Link/Activity OUT) × 1 RUN × 1 ERR × 1	
Process data	Variable PDO mapping	
PDO size/node	2 to 270 bytes	
Mailbox	Emergency messages, SDO requests, SDO responses, and SDO information	
Synchronization mode	Free Run Mode (asynchronous)	


Version Information

GX Unit		Corresponding versions *		
			EtherCAT	
Model	Unit version	CPU Units	Sysmac Studio	CX-ConfiguratorFDT
GX-ILM08C	Ver.1.1	Ver.1.12 or later	Ver.1.20 or higher	Ver.2.2 or higher
GA-ILIVIOOC	Ver.1.0	Ver.1.12 or later	Ver.1.16 or higher	Ver.2.2 or higher

^{*}Some Units do not have all of the versions given in the above table. If a Unit does not have the specified version, support is provided by the oldest available version after the specified version. Refer to the user's manuals for the specific Units for the relation between models and versions.

Component Names and Functions


GX-ILM08C



No.	Name	Function
(1)	EtherCAT communications connector, IN	EtherCAT cable connection: IN side M12 connector (D-coding, female)
(2)	EtherCAT communications connector, OUT	EtherCAT cable connection: OUT side M12 connector (D-coding, female)
(3)	Power supply connector	Connects to Unit power supply and I/O power supply cable. M12 connector (A-coding, male)
(4)	I/O connectors	Connect to IO-Link sensor cables (IO-Link connector type: Class A) M12 connectors (A-coding, female)
(5)	Node address setting switches	Used to set the EtherCAT node address.
(6)	Status indicators	Indicate the current status of the EtherCAT Slave Unit. (RUN, ERR, L/A IN, L/A OUT, UNIT PWR, and I/O PWR)
(7)	I/O indicators	Indicate the I/O status. (C/E and C/Q)
(8)	Mounting holes	Used to mount the Unit with M5 screws.

Wiring


IO-Link Mode




Note: Even if you connect to IO-Link devices without digital inputs for pin 2, connect pin 2 as shown in the above figure. This is because connectors on the IO-Link devices and the cable with connectors on both ends connect pin 2. However, because no data enters pin 2 of the IO-Link Master Unit, digital IO-Link input data is always OFF.

SIO (DI) Mode

Wiring Three-wire Sensors




Wiring Two-wire Sensors




SIO (DO) Mode

Wiring Output Devices



Dimensions (Unit: mm)


GX-ILM08C



Ordering Information

Interpreting Model Numbers	41
Ordering Information	42
Digital I/O Terminal	42
Analog I/O Terminal	42
Encoder Input Terminal	42
Expansion Units	42
Recommended EtherCAT Communications Cables	
Software	
IO-Link Master Unit	
Recommended EtherCAT Communications Cables	
Power Supply Cables	45
Sensor I/O Connectors	
Power Supply T-Joint Connector	46
Waterproof Cover for Connectors	
Tool for M12 Threaded Connectors	
Software	46
Related Manuals	47

Interpreting Model Numbers



1) Type

Code	Specifications	
ID	DC Input	
OD	DC Output	
MD	DC Input/Output	
ОС	Relay Output	
AD	Analog Input	
DA	Analog Output	
EC	Encoder Input	

2) Number of I/O point 3) Input/Output type

Code	Specifications		
02	2 points (2CH)		
04	4 points (4CH)		
16	16 points		
32	32 points		

Code	Digital Input/ Analog Input/ Digital Output type Analog Output type		Encoder Input Type	
1	NPN/Sinking	_	Open collector input, NPN	
2	PNP/Sourcing	-	-	
4	_	_	Line driver input, PNP	
7	-	Multi 1 (Current/Voltage)	-	

4) Connecting

Code	Specifications				
1	Screw (Common) (2-tier Terminal Block)				
2	Screw (Divided common) (3-tier Terminal Block)				
8	e-CON				

5) Figure/Function

Code	Digital Input/ Digital Output type	Analog Input/ Analog Output type	Encoder Input Type	
None	Horizontal type	Standard type	_	

Ordering Information

International Standards

- The standards are abbreviated as follows: U: UL, U1: UL (Class I Division 2 Products for Hazardous Locations), C: CSA, UC: cULus, UC1: cULus (Class I Division 2 Products for Hazardous Locations), CU: cUL, N: NK, L: Lloyd, and CE: EU Directives, RCM: RCM mark, KC: KC Registration, and UK: UKCA.
- Contact your OMRON representative for further details and applicable conditions for these standards.

Digital I/O Terminal

Terminal Block Type

Name		Specifications		Model	Standards
	Innuto	16 innute	NPN	GX-ID1611	
	Inputs	16 inputs	PNP	GX-ID1621	
	Outputs	16 outputs	NPN	GX-OD1611	
2-tier terminal blocks	Outputs	16 outputs	PNP	GX-OD1621	
terminal blocks	Outputs	16 outputs	Relay	GX-OC1601	
	Inputs/Outputs	ts 8 inputs/8 outputs	NPN	GX-MD1611	
	inputs/Outputs		PNP	GX-MD1621	UC1, N, L, CE
	Innuta	16 inputs	NPN	GX-ID1612	
	Outputs 16 out		PNP	GX-ID1622	
3-tier		46 autouta	NPN	GX-OD1612	
terminal blocks		16 outputs	PNP	GX-OD1622	
		0 :	NPN	GX-MD1612	
	Inputs/Outputs 8 inputs/8 outputs		PNP	GX-MD1622	

e-CON Connector Type

Name		Specifications	Model	Standards	
	Inputs	16 inputs	NPN	GX-ID1618	
	ilipuis	To iriputs	PNP	GX-ID1628	
	Outputo	16 outputo	NPN	GX-OD1618	
	Outputs	16 outputs	PNP	GX-OD1628	UC1, N, L, CE
	Inputs/Outputs	8 inputs/8 outputs	NPN	GX-MD1618	
a CON Composter Type			PNP	GX-MD1628	
e-CON Connector Type		32 inputs	NPN	GX-ID3218	
	ilipuis		PNP	GX-ID3228	
	Outputs	20 autouta	NPN	GX-OD3218	
		32 outputs	PNP	GX-OD3228	
	1 10 1 1 10 1 1		NPN	GX-MD3218	
	inputs/Outputs	Inputs/Outputs 16 inputs/16 outputs		GX-MD3228	

Analog I/O Terminal

2-tier Terminal Block Type

Name	Name Specifications			Standards
O tion torminal block type	Analog inputs	4 inputs	GX-AD0471	LICA N. L. CE
2-tier terminal block type	Analog outputs	2 outputs	GX-DA0271	UC1, N, L, CE

Encoder Input Terminal

3-tier Terminal Block Type

Name	Specifi	cations	Model	Standards	
3-tier Terminal Block Type	Open collector inputs	2 inputs	GX-EC0211	UC1, N, L, CE	
3-tier remiliai block rype	Line driver inputs	2 inputs	GX-EC0241	OCI, N, L, CE	

Expansion Units

Name			Specifica	ations	Model	Standards
		8 inputs	NPN	One Expansion Unit can be mounted to one GX-ID16□1/OD16□1/OC1601 Digital I/O Terminal.	XWT-ID08	LIGA N. OF
	Inputs		PNP		XWT-ID08-1	UC1, N, CE
	Outputs 8 outputs Inputs 16 inputs Outputs 16 outputs	8 outputs	NPN		XWT-OD08	UC1, N, CE, UK UC1, N, CE
Evennian Unita			PNP		XWT-OD08-1	
Expansion Units		nputs 16 inputs	NPN		XWT-ID16	
			PNP		XWT-ID16-1	
			NPN		XWT-OD16	LICA N OF LIK
		PNP		XWT-OD16-1	UC1, N, CE, UK	

Recommended EtherCAT Communications Cables

Use Straight STP (shielded twisted-pair) cable of category 5 or higher with double shielding (braiding and aluminum foil tape) for EtherCAT. **Cable with Connectors**

Item	Appearance	Recommended manufacturer	Cable length (m)	Model
Cable with Connectors on Both Ends (RJ45/RJ45)			0.3	XS6W-6PUR8SS30CM-YF
Standard RJ45 plugs type * 1			0.5	XS6W-6PUR8SS50CM-YF
Wire Gauge and Number of Pairs: AWG26, 4-pair Cable Cable Sheath material: PUR		OMRON	1	XS6W-6PUR8SS100CM-YF
Cable color: Yellow *2	*	OWKON	2	XS6W-6PUR8SS200CM-YF
EtherCAT/			3	XS6W-6PUR8SS300CM-YF
EtherNet/IP (10BASE/100BASE)			5	XS6W-6PUR8SS500CM-YF
			0.3	XS5W-T421-AMD-K
Cable with Connectors on Both Ends (RJ45/RJ45) Rugged RJ45 plugs type *1			0.5	XS5W-T421-BMD-K
Wire Gauge and Number of Pairs: AWG22, 2-pair Cable Cable color: Light blue EtherCAT/ EtherNet/IP (10BASE/100BASE)	**	OMRON	1	XS5W-T421-CMD-K
			2	XS5W-T421-DMD-K
			5	XS5W-T421-GMD-K
			10	XS5W-T421-JMD-K
Cable with Connectors on Both Ends		OMRON	0.5	XS5W-T421-BM2-SS
(M12 Straight/M12 Straight) Shield Strengthening Connector cable *3			1	XS5W-T421-CM2-SS
M12/Smartclick Connectors			2	XS5W-T421-DM2-SS
Wire Gauge and Number of Pairs: AWG22, 2-pair Cable			3	XS5W-T421-EM2-SS
Cable color: Black EtherCAT/			5	XS5W-T421-GM2-SS
EtherNet/IP (10BASE/100BASE)			10	XS5W-T421-JM2-SS
Cable with Connectors on Both Ends (M12 Straight/RJ45)			0.5	XS5W-T421-BMC-SS
Shield Strengthening Connector cable *3			1	XS5W-T421-CMC-SS
M12/Smartclick Connectors Rugged RJ45 plugs type Wire Gauge and Number of Pairs: AWG22, 2-pair Cable Cable color: Black EtherCAT/	23	0.450.4	2	XS5W-T421-DMC-SS
		OMRON	3	XS5W-T421-EMC-SS
			5	XS5W-T421-GMC-SS
EtherNet/IP (10BASE/100BASE)			10	XS5W-T421-JMC-SS

^{*1} Standard type cables length 0.2, 0.3, 0.5, 1, 1.5, 2, 3, 5, 7.5, 10, 15 and 20 m are available. Rugged type cables length 0.3, 0.5, 1, 2, 3, 5, 10 and 15 m are available. For details, refer to Cat.No.G019.

Cables / Connectors

Wire Gauge and Number of Pairs: AWG24, 4-pair Cable

Item	Appearance	Recommended manufacturer	Model
Cables	-	Kuramo Electric Co.	KETH-SB *
RJ45 Connectors	_	Panduit Corporation	MPS588 *

^{*} We recommend you to use above cable and connector together.

Wire Gauge and Number of Pairs: AWG22, 2-pair Cable

Item	Appearance	Recommended manufacturer	Model
Cables	-	Kuramo Electric Co.	KETH-PSB-OMR *
Cables	-	JMACS Japan Co., Ltd.	PNET/B *
RJ45 Assembly Connector		OMRON	XS6G-T421-1 *

 $[\]ensuremath{\,\raisebox{.4ex}{\star}}\ensuremath{\,\text{We}}\ensuremath{\,\text{recommend}}\ensuremath{\,\text{you}}\ensuremath{\,\text{to}}\ensuremath{\,\text{use}}\ensuremath{\,\text{and}}\ensuremath{\,\text{RJ45}}\ensuremath{\,\text{Assembly}}\ensuremath{\,\text{Connector}}\ensuremath{\,\text{together}}.$

Note: Connect both ends of cable shielded wires to the connector hoods.

 *2 Cables colors are available in blue, yellow, or Green.

^{*3} For details, contact your OMRON representative.

Software

How to Select Required Support Software for Your Controller

The required Support Software depends on the Controller to connect. Please check the following table when purchasing the Support Software.

Product	Omron PLC System	Omron Machine Automation Controller System
Controller	CJ-series	NJ/NX-series
Software	FA Integrated Tool Package CX-One	Automation Software Sysmac Studio

FA Integrated Tool Package CX-One

	Specifications				
Product name		Number of licenses	Media	Model	Standards
FA Integrated Tool Package CX-One Ver.4.□	The CX-One is a comprehensive software package that integrates Support Software for OMRON PLCs and components. CX-One Version 4.□ includes CX-Programmer Ver.9.□	1 license *1	DVD	CXONE-AL01D-V4	-

Note: For details, refer to the CX-One Catalog (Cat. No. R134), visit your local OMRON website.

*1 Multi licenses (3, 10, 30, or 50 licenses) and DVD media without licenses are also available for the CX-One.

Automation Software Sysmac Studio

The Sysmac Studio is the software that provides an integrated environment for setting, programming, debugging and maintenance of machine automation controllers including the NJ/NX-series CPU Units, NY-series Industrial PC, EtherCAT Slave, and the HMI.

For details, refer to your local OMRON website and Sysmac Studio Catalog (Cat. No. P138).

IO-Link Master Unit

		Specifications			
Name	Environmental resistance	Number of IO-Link ports	I/O connection terminals	Model	Standards
GX-series IO-Link Master Unit	IP67	8	M12 connector (A-cording, female)	GX-ILM08C	UC, CE, RCM, KC

Recommended EtherCAT Communications Cables

Use Straight STP (shielded twisted-pair) cable of category 5 or higher with double shielding (braiding and aluminum foil tape) for EtherCAT.

Item	Appearance	Recommended manufacturer	Cable length (m)	Model
	Smartclick		0.5	XS5W-T421-BM2-SS
Cable with Connectors on Both Ends Shield Strengthening cable *1 Wire Gauge and Number of Pairs: AWG22, 2-pair Cable Cable color: Black	(M12 Straight/M12 straight)		1	XS5W-T421-CM2-SS
		OMRON	2	XS5W-T421-DM2-SS
		OWRON	3	XS5W-T421-EM2-SS
			5	XS5W-T421-GM2-SS
			10	XS5W-T421-JM2-SS
Cable with Connectors on Both Ends	Smartclick (M12 Straight/RJ45 straight)	OMRON	0.5	XS5W-T421-BMC-SS
			1	XS5W-T421-CMC-SS
Rugged type			2	XS5W-T421-DMC-SS
Shield Strengthening cable *1 Wire Gauge and Number of Pairs: AWG22, 2-pair Cable			3	XS5W-T421-EMC-SS
Cable color: Black			5	XS5W-T421-GMC-SS
			10	XS5W-T421-JMC-SS
			0.25	3RHS4-1100-0.25M
0.11 (11.0 1.1.0 1.1.1.1.1.1.1.1.1.1.1.1.1.1.1			0.5	3RHS4-1100-0.5M
Cable with Connectors on Both Ends (RJ45/RJ45) Rugged standard RJ45 plugs *2		200 1	1	3RHS4-1100-1M
Wire gauge and number of pairs: AWG22, 2-pair cable	/)	3M Japan Limited	2	3RHS4-1100-2M
Cable color: Yellow	**		5	3RHS4-1100-5M
			10	3RHS4-1100-10M

^{*1} For details, Contact your OMRON representative.

Power Supply Cables

Item	Appearance	Recommended manufacturer	Cable length (m)	Model
Connector connected to cable, socket on one cable end Fire-retardant, Robot cable			1	XS5F-D421-C80-F
			2	XS5F-D421-D80-F
	Smartclick (M12 Straight)	OMRON	3	XS5F-D421-E80-F
			5	XS5F-D421-G80-F
			10	XS5F-D421-J80-F
		OMRON	1	XS5W-D421-C81-F
Connectors connected to cable.			2	XS5W-D421-D81-F
socket and plug on cable ends Fire-retardant, Robot cable	Smartclick (M12 Straight/M12 straight)		3	XS5W-D421-E81-F
	(W12 Ottalgrit/W12 Straight)		5	XS5W-D421-G81-F
			10	XS5W-D421-J81-F

Note: Refer to the Round Water-resistant Connectors in the category of Sensor I/O Connector/Sensor Controller on your local OMRON website for details.

Sensor I/O Connectors

Order a cable with a connector on both ends to connect a sensor of connector type.

Item	Appearance	Recommended manufacturer	Cable length (m)	Model
Connectors connected to cable, M8 socket and M12 plug on cable ends Fire-retardant, Robot cable	M8 screw- M12 Smartclick (M8 Straight/M12 straight)	OMRON	0.2	XS3W-M42C-4C2-A
Connectors connected to cable, socket and plug on cable ends Fire-retardant, Robot cable	Smartclick (M12 Straight/M12 straight)	OMRON	1	XS5W-D421-C81-F
			2	XS5W-D421-D81-F
			3	XS5W-D421-E81-F
			5	XS5W-D421-G81-F
			10	XS5W-D421-J81-F

Note: Refer to the Ordering Information in the catalog of the sensor to connect or the Sensor I/O Connectors/Sensor Controllers on your local OMRON website for details.

^{*2} Cables are available from 0.25 m to 100 m. Ask the manufacturer for details.

Power Supply T-Joint Connector

This connector is used when branching a GX-type Unit power supply.

Item	Appearance	Specification	Connector type	Model
XS5R Plug/Socket T-Joint Connector		M12	Smartclick connector	XS5R-D427-5

Waterproof Cover for Connectors

This is a waterproof cover for unused M12 GX connectors (female).

When you use this waterproof cover, you can maintain the IP67 protective structure.

The following two types of covers are available. Either one can be mounted on an EtherCAT communications connector or I/O connector.

Item	Appearance	Specification	Connector type	Materials	Model
M12 Threaded Waterproof Cover 		M12	Screw-type connector	Brass/nickel plated	XS2Z-22
Smartclick Waterproof Cover *2		M12	Smartclick connector	PBT	XS5Z-11

^{*1} When mounting the M12 Threaded Waterproof Cover on a connector, always tighten it to a torque of 0.39 to 0.49 N•m.

Tool for M12 Threaded Connectors

The tool for tightening M12 Threaded Connectors is used when tightening to a specified torque.

Item	Appearance	Model
Torque Wrench		XY2F-0004

Software

Automation Software Sysmac Studio

Please purchase a DVD and required number of licenses the first time you purchase the Sysmac Studio. DVDs and licenses are available individually. Each model of licenses does not include any DVD.

	Specification				
Product name		Number of licenses	Media	Model	Standards
Sysmac Studio Standard Edition Ver.1.⊡⊡	The Sysmac Studio is the software that provides an integrated environment for setting, programming, debugging and maintenance of machine automation controllers including the NJ/NX-series CPU Units, NY-series Industrial PC, EtherCAT Slave, and the HMI. The Sysmac Studio Standard Edition DVD includes CX-ConfiguratorFDT to set up IO-Link Master Units and IO-Link devices.	(Media only)	DVD	SYSMAC-SE200D	
		1 license *		SYSMAC-SE201L	

Note: For details, refer to the Sysmac Studio Ver.1. □□ datasheet, visit your local OMRON website.

* Multi licenses are available for the Sysmac Studio (3, 10, 30, or 50 licenses).

^{*2} When mounting a Smartclick Waterproof Cover on a connector, torque management is not required.

Related Manuals

Cat. No.	Model number	Manual	
W488	GX-00000	GX-Series EtherCAT Slave USER'S MANUAL	
W570	NX-ILM400 GX-ILM08C	IO-Link System User's Manual	
W505	NX701-	NJ/NX-series CPU Unit Built-in EtherCAT Port User's Manual	
W487	CJ1W-NC□81/NC□82	CJ Series Position Control Unit OPERATION MANUAL	
W504	SYSMAC-SE2	Sysmac Studio version 1 OPERATION MANUAL	
W446	CXONE-AL D-V	CX-Programmer Operation Manual	
W562	NY532-□□□□ NY512-□□□□	NY-series IPC Machine Controller Industrial Panel PC / Industrial Box PC Built-in EtherCAT® Port User's Manual	
W560	NY532-□□□□ NY512-□□□□	NY-series Instructions Reference Manual	

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2024.12

In the interest of product improvement, specifications are subject to change without notice.