Powerful. Tough. Future-Proof.

Our NY industrial Box PC has been designed from first principles to be powerful, reliable and scalable, making it ideally suited to visualization, data handling, measuring and controlling. The latest insights in design simplification eliminates faults caused by complexity which, with other unique design features, maximizes uptime and reduces costs. The future will be IT driven: Omron's Industrial PC platform will make you part of it.





NYB2C, NYB2A, NYB13, NYB3A

Features

- No internal cables to cut faults, maximizes uptime
- Unique simplified thermal design to reduce downtime
- Powerful Intel[®] Core[™] technology for optimized performance
- Industrial CPU's with long availability
- Three Ethernet ports to increase connectivity
- USB3.0 for fast data-transmission
- Optional NY Monitor Link interface for connectivity up to 100 m

Windows is a registered trademark of Microsoft Corporation in the United States and other countries.

The SD and SDHC logos are trademarks of SD-3C, LLC.

CFAST is a registered trademark of CompactFlash Association.

Intel, Xeon, Celeron, Intel Atom and Intel Core are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries.

DisplayPort is trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries.

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

The product photographs and figures that are used in this document may vary somewhat from the actual products.

System Configuration



*NY Monitor Link option: Connect monitor up to 100 m via Ethernet cable.

Model Number Structure

The purpose of this model number legend is to provide understanding of the meaning of specifications from the model number. Models are not available for all combinations of code numbers.



Main memory

1: 2 GB, non-ECC 2: 4 GB, non-ECC 3: 8 GB, non-ECC 4: 16 GB, non-ECC 5: 32 GB, non-ECC 6: 64 GB, non-ECC 7: 96 GB, non-ECC C: 8 GB, ECC D: 16 GB, ECC E: 32 GB, ECC E: 32 GB, ECC G: 96 GB, ECC

Ordering Information

NY-series Industrial PC Platform

Recommended models

The industrial Box PC has extended configuration possibilities to meet your requirements, below an overview of the most used and recommended models. Selecting one of the models below will bring the benefit of faster delivery times.

In case your preferred model is not listed below, please contact your Omron representative to discuss the possibilities.

Product name			Model				
Product name	Operating system	CPU type	RAM memory	Storage size	Interface option	PCIe-slot	woder
		Intel [®] Core™	8 GB	256 GB CFast type (MLC)	No	No	NYB35-30370
	Windows 10 IoT Enterprise 2016	i5-7300U	(non-ECC type)	128 GB SSD type (MLC)	RS-232C	Yes	NYB35-313K1
	LTSB - 64 bit	Intel [®] Celeron™	8 GB	256 GB CFast type (MLC)	No	No	NYB2C-30370
		3965U	(non-ECC type)	128 GB SSD type (MLC)	RS-232C	Yes	NYB2C-313K1
	Windows 10 IoT Enterprise 2019 LTSC - 64bit	Intel [®] Atom [®]	4 GB (non-ECC type)	128 GB CFast type (MLC)	No	No	NYB2A-20460
		x5-E3940	8 GB (non-ECC type)	256 GB CFast type (MLC)	No	No	NYB2A-30470
		Intel [®] Core™ i7-7820EQ		128 GB CFast type (MLC)	No	No	NYB27-30460
Industrial Box			8 GB (non-ECC type)	500 GB SSD type (MLC)	RS-232C	Yes	NYB27-314M1
PC				500 GB SSD type (MLC) Hard RAID	RS-232C	Yes	NYB27-324M1
				1 TB SSD type (3DTLC)	RS-232C	Yes	NYB27-314P1
		Intel [®] Xeon [®]	32 GB (non-ECC type)	1 TB SSD type	Ethernet	Yes	NYB2E-515P9
		W-11865MRE	32 GB (ECC type)	(3DTLC)	Luiemer	165	NYB2E-E15P9
	Windows 10 IoT Enterprise 2021	Intel [®] Core™	16 GB	512 GB CFast type (3DTLC)	None	No	NYB37-40530
	LTSC - 64 bit	i7-1185GRE	(non-ECC type)	512 GB SSD type (3DTLC)	Ethernet	Yes	NYB37-415H9
		Intel [®] Core™	16 GB	256 GB CFast type (3DTLC)	None	No	NYB55-40520
		i5-1145GRE	(non-ECC type)	256 GB SSD type (3DTLC)	Ethernet	Yes	NYB55-415G9

Accessories

Optional Hardware

Product name	Specifications	Model
		NY000-AB00
	Book mount	NY000-AB02
Iounting Brackets *1		NY000-AB04
	Wall mount	NY000-AB05 NY000-AB01
		NY000-AB01
	Card type: SD Card Capacity: 2 GB	HMC-SD292
	Format: FAT16	
	Card type: SDHC Card	
D Memory Cards	Capacity: 4 GB	HMC-SD492
-	Format: FAT32	
	Card type: SDHC Card	
	Capacity: 16 GB	HMC-SD1A2
	Format: FAT32	
ISB Flash Drives	Capacity: 2 GB	FZ-MEM2G
	Capacity: 16 GB	FZ-MEM16G
	Storage type: SSD SLC, Capacity: 32 GB	NY000-AS00
	Storage type: SSD SLC (Apacer), Capacity: 64 GB	NY000-AS01
	Storage type: SSD SLC (Hagiwara), Capacity: 64 GB	NY000-AS03
	Storage type: SSD MLC (Innodisk), Capacity: 128 GB	NY000-AS04
	Storage type: SSD MLC, Capacity: 500 GB	NY000-AS05
	Storage type: SSD 3DTLC, Capacity: 1 TB	NY000-AS07
	Storage type: SSD MLC (Innodisk), Capacity: 256 GB	NY000-AS08
	Storage type: SSD 3DTLC (Acon), Capacity: 128 GB	NY000-AS09
Name and Devide a	Storage type: SSD 3DTLC (Acon), Capacity: 256 GB	NY000-AS10
Storage Devices	Storage type: SSD 3DTLC (Acon), Capacity: 512 GB	NY000-AS11
	Storage type: SSD 3DTLC (Acon), Capacity: 1 TB	NY000-AS12
	Storage type: SSD 3DTLC (Acon), Capacity: 2 TB	NY000-AS13
	Storage type: CFast MLC, Capacity: 64 GB	NY000-AT00
	Storage type: CFast MLC, Capacity: 128 GB	NY000-AT01
	Storage type: CFast MLC, Capacity: 256 GB	NY000-AT02
	Storage type: CFast 3DTLC (Acon), Capacity: 128 GB	NY000-AT05
	Storage type: CFast 3DTLC (Acon), Capacity: 256 GB	NY000-AT06
	Storage type: CFast 3DTLC (Acon), Capacity: 512 GB	NY000-AT07
	Cable length: 2 m	
	Supports DVI-D	NY000-AC00 2M
	Minimum bend radius: 36 mm	
OVI Cables	Cable length: 5 m	
	Supports DVI-D	NY000-AC00 5M
	Minimum bend radius: 36 mm	
	 LCD touchscreen Multi-touch functionality 	
	Supply voltage: 24 VDC	
ndustrial Monitor	2 USB Type-A Connectors	NYM1 W-C10
	 Programmable brightness control 	
	• Standard and 100 m cable models are available.	
	Output voltage: 24 VDC	S8VK-G
	Push-In Plus terminal blocks	
	Output voltage: 24 VDC EtherNet/IP_Medbus_TCP_Compatible	S8VK-X
Power Supply	EtherNet/IP, Modbus TCP-Compatible	
	Output voltage: 24 VDC Compact	S8VK-S
	Output voltage: 24 VDC	
	Three-phase 200-V Power Supplies	S8VK-WA
IPS *2	Output voltage during backup operation: 24 VDC ± 5%	S8BA
·· • • •	Cable length: 2 m	
	Signals for	
JPS Communication Cable	• Signal output (BL, TR, BU, WB)	S8BW-C02
	Remote ON/OFF input	
	UPS Stop Signal input (BS)	

Note: Orders for NY000-AS02 are no longer accepted, as of November 30, 2018.

 *1. Select the required type:

 NY000-AB00: NYB1E, NYB27-0100, NYB27-0200, NYB2E-0100, NYB2E-0200, NYB37-0100, NYB37-0200, NYB55-0100, NYB55-0200

 NY000-AB02: NYB35-0100, NYB55-0200

 NY000-AB02: NYB35-0100, NYB55-0200

 NY000-AB02: NYB35-0100, NYB35-0200

 NY000-AB02: NYB35-0100, NYB35-0200

NY000-AB04: NYB35-0, NYB2C-0, NYB2A-0, NYB65-00, NYB13-00, NYB3A-0000 NY000-AB05: NYB27-0, NYB2E-000, NYB37-000, NYB55-0000

***2.** Revision number 09 or higher.

The revision number of the UPS can be retrieved from the serial number label on the product and the product packaging.

A3 □ [Item	Description
1	2	3	4	1	Product code
				2	Product period and sequential number
				3	Revision number
				4	RoHS status

Spare Parts

The following spare parts for the Industrial Box PC are available.

Product name	Specifications	Model
Battery	One battery is supplied with the Industrial Box PC. The battery supplies power to the real-time clock. The battery is located inside the Industrial Box PC. Service life: 5 years at 25°C	CJ1W-BAT01*
Fan Unit	The Fan Unit is available for the Industrial Box PC that has active cooling. Service life: 70,000 hours of continuous operation at 40°C with 15% to 65% relative humidity. Shelf life: 6 months This is the storage limitation with no power supplied.	NY000-AF00
Accessory Kit	 Accessory Kit containing all accessories supplied with the Industrial Box PC. Power connector I/O connector Drive bracket for drive installation 4 mounting screws for drive installation PCIe Card support for PCIe Card installation PCIe Card clip for PCIe Card installation 	NY000-AK00
	Power connectors (10 pcs) for Industrial Box PC and Industrial Panel PC	NY000-AK01

* Only for models with replaceable battery.

Installed Support Software

ltem	Specifications
Industrial PC Support Utility	The Industrial PC Support Utility is a software utility to assist in diagnosing and resolving problems of the Industrial Box PC.
	It is pre-installed on the Industrial Box PC and the Industrial Panel PC.
Industrial PC Tray Utility	The Industrial PC Tray Utility is a software utility that provides information about the current state of the Industrial PC, its related devices, and associated software. It is pre-installed on the Industrial Box PC and the Industrial Panel PC.
Industrial PC System API	The Industrial PC System API allows programmers to create programs that can retrieve information or set an indicator status of the Industrial Box PC. The API makes use of the included IPC System Service to manage the hardware. It is pre-installed on the Industrial Box PC and the Industrial Panel PC.
Industrial Monitor Utility	For the optional OMRON Industrial Monitor. The Industrial Monitor Utility provides a user interface to control settings and display details of connected Industrial Monitors. It is pre-installed on the Industrial Box PC and the Industrial Panel PC.
Industrial Monitor Brightness Utility	For the optional OMRON Industrial Monitor. The Industrial Monitor Brightness Utility is a small software utility that allows you to control the brightness of the screen backlight of all connected Industrial Monitors. It is pre-installed on the Industrial Box PC and the Industrial Panel PC.
Industrial Monitor API	For the optional OMRON Industrial Monitor. The Industrial Monitor API allows programmers to create applications that can control the hardware features and retrieve information from connected Industrial Monitors. It is pre-installed on the Industrial Box PC and the Industrial Panel PC.
Industrial PC Rescue Disk Creator	The Industrial PC Rescue Disk Creator creates a USB Rescue Disk which can be used to back-up and restore the Omron IPC Operating System. It is pre-installed on the Industrial Box PC and the Industrial Panel PC.

Soft-NA

Product name	Specifications	Number of licenses	Media	Model
	The Soft-NA is software that displays information on FA	_ (Media only)	DVD	NA-RTSM
oft-NA	manufacturing sites while providing safety, reliability,	1 license		NA-RTLD01
	and maintainability as an industrial display on which operations can be performed as necessary.	3 licenses	USB dongle	NA-RTLD03
		10 licenses		NA-RTLD10

System Requirements

Item		Requi	rement
OS		Windows 10 Pro Version 1903 or later 64 bit	Windows 11 Pro Version 24H2 or later
Processor		Intel Atom [®] x5-E3940 equivalent or higher processor * 1	Intel Celeron [®] N4000 equivalent or higher processor * 1
RAM		4 GB or more	·
Free space in the hard drive neces	sary for installation	1 GB or more	
Optical disk drive		DVD-ROM drive *2	
Communication port	USB	USB2.0 Type-A x 2 * 3	
Communication port	LAN	Ethernet x 2 *3	

*1. ARM-based processors are not supported.
*2.It is required when installing using NA-RTSM.
*3.Since one port is for project transfer, it is not required unless the corresponding path is used.
Note: Refer to NA-series catalog (Cat. No. V413) for the system configuration of Soft-NA.

General Specifications

Performance Specifications

renor	manc	e Shei	Sincar	10115															
	lte	em		NYB2E- 100/ NYB2E- 200	NYB37- 1000/ NYB37- 2000	NYB55- 100/ NYB55- 2000	NYB65- 1000/ NYB65- 2000	NYB13- 1000/ NYB13- 2000	NYB2E-	NYB37-	NYB55-	NYB65-	NYB13-	NYB3A					
		CPU type		Intel® Xeon®	Intel [®] Core™	Intel [®] Cor		Intel [®] Core™	Intel® Xeon®	Intel [®] Core™	Intel [®] Cor		Intel [®] Core™	Intel Atom					
		Cores / TI		W-11865MRE 8 / 16	i7-1185GRE	i5-1145G	NE.	i3-1115GRE 2 / 4	W-11865MRE 8 / 16	i7-1185GRE 4 / 8	i5-1145G	NE.	i3-1115GRE	x6425RE					
		CPU base frequency	•	2.6 GHz	2.8 GHz	2.6 GHz	1.5 GHz	2.2 GHz	2.6 GHz	1.8 GHz	2.6 GHz	1.5 GHz	2.2 GHz	1.9 GH					
	CPU	Maximum	turbo	4.7 GHz	4.4 GHz	4.1 GHz		3.9 GHz	4.7 GHz	4.4 GHz	4.1 GHz		3.9 GHz	-					
		Cache		24 MB	12 MB 8 MB 6 MB			24 MB	12 MB	8 MB		6 MB	1.5 MB						
		Cooling d	etails	Active cooling	Active Active cooling (fan) (fan) (fan)			Active cooling	Active Active cooling cooling Passive cooling (fanless)										
		Intel CDU	ootogony	(fan) Industrial	(fan)	(fan) eration min	. ,		(fan)	(fan)	(fan) eration min	imal 10\rr)							
		Intel CPU		8, 16, 32,			inai ioyi)		Industrial 8, 16, 32,			inai ioyi)		4, 8, 16					
		Memory s	size *1	64 or 96 GB	8, 16, 32,	64 GB			64 or 96 GB	8, 16, 32,	64 GB			32 GB					
Main		Memory t	уре	DDR4 (ECC is available)	DDR4				DDR4 (ECC is available)	DDR4									
Main system	Memory	Package Format	Memory	SO-DIMN					SO-DIMM										
		Serial	Speed grade	3200 MT/	s				3200 MT/	s									
	Presence grade Detect CAS (SPD) latency								CL17										
	Trusted p (TPM)	dule	Available					Available											
	Graphics controller			Intel [®] UHD Graphics. Up to four independe nt screens.	Graphics. Jp to four hdepende Intel [®] Iris [®] Xe Graphics. Up to four independent screens. Graphics. Up to four independe					Intel [®] Iris [®] Xe Graphics. Up to four independent screens.									
				Intel [®] UHD Graphics (32 EU)	Intel [®] Iris [®] Xe Graphics (96 EU)	Intel [®] Iris [®] Graphics (Intel [®] UHD Graphics (48 EU)	Intel [®] UHD Graphics (32 EU)	Intel [®] Iris [®] Xe Graphics (96 EU)	Intel [®] Iris [®] Graphics		Intel [®] UHD Graphics (48 EU)	Intel [®] UHD Graphic (32 EU)					
	Watchdog	9		Yes					Yes										
Operating	Windows	os		Windows	10 IoT Ent	erprise 202	21 LTSC - 6	64 bit	Windows	10 IoT Ent	erprise 202	21 LTSC - 6	64 bit						
system		Hard Disk	Drive *2	500 GB, 1	ТВ							-							
			SLC	-															
	Drives *1	Solid State	type MLC type	<u></u>					-										
Storage devices		Drive	3DTLC type	128 GB, 2	256GB, 512	2 GB, 1 TB			128 GB, 256GB, 512 GB										
	Drive bay	s (HDD/SS	D) *3	2					CFast slot										
	Hardware	-RAID sup	port	RAID1: NYB2E-	RAID1: NYB37-	NYB55-	NYB65-	NYB13-	N/A										
	Power co	nnector		24 VDC	I				24 VDC										
	I/O conne	ctor		2 inputs a	nd 1 outpu	t			2 inputs a	nd 1 outpu	t								
		Number o	•						-										
	USB2.0 Type-A	Maximum							-										
	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	Maximum length	cable						-										
		Number o	of ports	4					4										
	USB3.0	Maximum	current	900 mA					900 mA										
	Туре-А	Maximum length		3 m					3 m										
-		Number o	of ports	3		E TV 4000			3										
Connectors				10BASE-T, 100BASE-TX, 1000BASE-T or 2500BASE-T					10BASE-T, 100BASE-TX, 1000BASE-T or 2500BASE-T										
Connectors	Ethernet	Physical I Maximum	ayer		E-T									100 m					
Connectors	Ethernet connectors	Physical Maximum transmission between Et switch and	on distance hernet		E-T				100 m										
Connectors	connectors	Maximum transmissio between Et	on distance hernet node	2500BAS	E-T				100 m -										
Connectors		Maximum transmissio between Et switch and Video inte Resolutio Maximum	on distance hernet node erface	2500BAS	E-T														
Connectors	connectors	Maximum transmissio between Et switch and Video inte Resolutio	on distance hernet node erface n DVI cable	2500BAS 100 m	E-T	at 60 Hz			-	96 x 2,304	at 60 Hz								

	lte	em	NYB2E-	NYB37-	NYB55- 100/ NYB55-	NYB65-	NYB13- 1000/ NYB13-	NYB2E-	NYB37-	NYB55-	NYB65-	NYB13-	NYB3A-			
	RS-232C		Standard S	Standard SUBD9 connector (Non-Isolated) Standard SUBD9 connector (Non-Isolated)												
		Video interface						-								
	DVI-D	Resolution						-								
	5115	Maximum DVI cable length						-								
		Video interface	Digital only	4				Digital on	у							
		Resolution	1,280 x 80	280 x 800 pixels at 60 Hz 1,280 x 800 pixels at 60 Hz												
Optional connector	NY	Connector type	RJ45					RJ45								
(select one per system)	Monitor Link	Cable shielding, type and max. length	S/FTP, Ca	S/FTP, Cat.6A, 100 m												
		USB data throughput	280 Mbps	max.				280 Mbps	max.							
	GigE LAN	Physical layer	10BASE-T, 100BASE-TX or 1000BASE-T					10BASE-	T, 100BASI	E-TX or 10	00BASE-T					
	DisplayPort	Resolution	Up to 4,09	6 x 2,304	at 60 Hz			Up to 4,096 x 2,304 at 60 Hz								
	++	Maximum cable length	3 m					3 m								
PCle	Configura	ition	X4 (4 lane	s) up to G	en 3			N/A								
Card	Card heig	ht	Standard h	neight card	ls, 4.20 inc	hes (106.7	mm) * 4	N/A								
Slot	Card leng	th	Half length	n cards, 6.0	6 inches (1	67.65 mm)		N/A								
Battery	Model		CJ1W-BA	T01				CJ1W-BA	T01							
Dattery	Service lit	fe	5 years at	25°C				5 years at	25°C							
	Model		NY000-AF				-	NY000-AF			-					
Fan unit	Service lit	fe	70,000 hou operation a 65% relativ	at 40°C with	n 15% to		-	operation	urs of contir at 40°C with ve humidity	n 15% to		ASE-T				
LED			PWR, ERF	R, HDD, R	UN			PWR, ER	R, HDD, R	UN						

*1. Not all combinations are possible or standard available. Please contact your Omron representative to dicuss the possibilities.
 *2. Orders for HDD models will be accepted until the end of December 2025.
 *3. Depending on the model one or two drives are supported.
 *4. Low profile cards, 2.536 inches (64.4 mm) are not supported.

				NYB1E-	NYB27-	NYB35-									
	lte	em		01000 NYB1E- 02000 *1	01000 NYB27- 02000	01000 NYB35- 02000	NYB2C-	NYB27-	NYB35-	NYB2C-	NYB2A-				
		CPU type		Intel [®] Xeon [®] E3-1515M v5	Intel [®] Core™ i7-7820EQ	Intel [®] Core™ i5-7300U	Intel [®] Celeron [®] 3965U	Intel [®] Core™ i7-7820EQ	Intel [®] Core™ i5-7300U	Intel [®] Celeron [®] 3965U	Intel [®] Atom [®] x5-E3940				
		Cores / TI		4 / 8	4 / 8	2/4	2/2	4 / 8	2/4	2/2	4 / 4				
		CPU base frequency		2.8 GHz	3.0 GHz	2.6 GHz	2.2 GHz	3.0 GHz	2.6 GHz	2.2 GHz	1.6 GHz				
	CPU	Maximum frequency		3.7 GHz	3.7 GHz	3.5 GHz	-	3.7 GHz	3.5 GHz	_	1.8 GHz				
		Cache		8 MB	8 MB	3 MB	2 MB	8 MB	3 MB	2 MB	2 MB				
		Cooling d	letails	Requires activ (fan)	ve cooling	Passive cooli	ng (fanless)	Requires active cooling (fan)	Passive cooli	ng (fanless)					
		Intel CPU	category	Industrial (100	0% operation m	ninimal 10yr)	T	T	T	T	1				
Main		Memory s	size *2	8, 16 or 32 GB	8, 16 or 32 GB	4 or 8 GB	4 or 8 GB	8, 16 or 32 GB	8 or 16 GB	4 or 8 GB	2, 4 or 8 GB				
system	system Memory Memory type			DDR4 (ECC is available)	DDR4 (non E	CC)					DDR3L (non ECC)				
	Trusted platform module (TPM)				valable										
	Graphics controller			Intel [®] Iris [™] Pro Graphics. Up to two independent screens.	Pro Graphics. Up to two independent screens. independent screens.										
				Intel [®] Iris™ Pro Graphics P580	Intel [®] HD Graphics 630	Intel [®] HD Graphics 620	Intel [®] HD Graphics 610	Intel [®] HD Graphics 630	Intel [®] HD Graphics 620	Intel [®] HD Graphics 610	Intel [®] HD Graphics 500				
	Watchdog)		Yes	i .	1	1	T	1		1				
Operating system	Windows	Windows OS		Windows 10 IoT Enterprise 2016 LTSB - 64 bit Windows 10 IoT Enterprise 2021 LTSC - 64 bit	Windows 10 IoT Enterprise 2019 LTSC - 64 bit Windows 10 IoT Enterprise 2021 LTSC - 64 bit	Windows 10 IoT Enterprise 2016 LTSB - 64 bit Windows 10 IoT Enterprise 2019 LTSC - 64 bit Windows 10 IoT Enterprise 2021 LTSC - 64 bit	Windows 10 IoT Enterprise 2016 LTSB - 64 bit Windows 10 IoT Enterprise 2019 LTSC - 64 bit Windows 10 IoT Enterprise 2021 LTSC - 64 bit	Windows 10 IoT Enterprise 2019 LTSC - 64 bit Windows 10 IoT Enterprise 2021 LTSC - 64 bit	2016 LTSB - Windows 10 2019 LTSC -	loT Enterprise 64 bit loT Enterprise	Windows 10 IoT Enterprise 2019 LTSC - 64 bit Windows 10 IoT Enterprise 2021 LTSC - 64 bit				
		Hard Disk	Drive *3	• 320 GB, 500 GB, 1 TB	• 500 GB, 1 TB	• 320 GB		N/A							
	Drives		type	• 64 GB				N/A							
Storage devices	*2	Solid State Drive	MLC type	• 128 GB, 500 GB	• 128 GB, 256 GB, 500 GB	• 128 GB		• 64 GB, 128	3 GB, 256 GB						
			3DTLC type	• 128 GB, 25	6 GB, 512 GB, ⁻	1 TB		• 128 GB, 25	56 GB						
	Drive bay	s (HDD/SS	D) *4	2	2	2	2	CFast slot	CFast slot	CFast slot	CFast slot				
	Hardware	-RAID supp	port	NYB1E- 2200 only	NYB27- 2200 only	NYB35- 2200 only	N/A	N/A	N/A	N/A	N/A				

		em	NYB1E- NYB27- □1□□□ □1□□□ NYB1E- NYB27- □2□□□ *1 □2□□□	NYB35- 1000 NYB35- 2000	NYB2C-	NYB27-	NYB35- 00000	NYB2C-	NYB2A-				
	Power co	nnector	24 VDC										
	I/O conne		2 inputs (UPS signal and power OFF control) and 1 output (Industrial Box PC power state)										
		Number of ports	2										
	USB2.0 Type-A	Maximum current	500 mA										
	Туре-А	Maximum cable length	5 m										
		Number of ports	2										
	USB3.0	Maximum current	900 mA										
Connectors	Туре-А	Maximum cable length	3 m										
	Ethernet	Number of ports	3										
	connect ors	Physical layer	10BASE-T, 100BASE-TX or	1000BASE-T									
	DVI-I	Video interface	Digital or analog	Digital only									
	Connect	Resolution	Up to 1,920 x 1,200 pixels at	t 60 Hz									
	or	Maximum DVI cable length	Dependent upon connected	monitor type and	resolution								
	DisplayPort	Resolution	N/A										
	++	Maximum cable length	N/A										
	RS-232C		Standard DSUB9 connector	(Non-Isolated)		N/A							
		Video interface	Digital only			N/A							
	DVI-D	Resolution	Up to 1,920 x 1,200 pixels at	t 60 Hz		N/A							
		Maximum DVI cable length	Dependent upon connected	monitor type and	resolution	N/A							
		Video interface	Digital only										
	Resolution		1,280 x 800 pixels at 60 Hz										
Optional	NY	Connector type	RJ45										
connector (select one per system)	Monitor Link	Cable shielding, type and max. length	S/FTP, Cat.6A, 100 m										
		USB data throughput	280 Mbps max.										
	GigE LAN	Physical layer	10BASE-T, 100BASE-TX or 1000BASE-T				_						
	DisplayPort	Resolution	N/A										
	++	Maximum cable length	N/A										
PCle	Configura	ition	X4 (4 lanes) up to Gen 3	X2 (2 lanes) up to Gen 3		N/A							
Card Slot	Card heig	ht	Standard height cards, 4.20	inches (106.7 m	m) *5	N/A							
5.01	Card leng	th	Half length cards, 6.6 inches	(167.65 mm)		N/A							
Batton	Model		CJ1W-BAT01	Non replaceab	e battery	CJ1W- BAT01	Non replaceal	ole battery					
Battery	Service life	ie	5 years at 25°C	10 years at 40°	C *6	5 years at 25°C	10 years at 40)°C *6					
	Model		NY000-AF00	No fan unit		NY000-AF00	No fan unit						
Fan unit	Service lit	ie	70,000 hours of continuous operation at 40°C with 15% to 65% relative humidity	-		70,000 hours of continuous operation at 40°C with 15% to 65% relative humidity		_					
LED			PWR, ERR, HDD, RUN	1			1						

*1. Orders for NYB1E accepted until the end of August 2025.
*2. Not all combinations are possible or standard available. Please contact your Omron representative to discuss the possibilities.
*3. Orders for HDD models will be accepted until the end of December 2025.

*4. Depending on the model one or two drives are supported.
*5. Low profile cards, 2.536 inches (64.4 mm) are not supported.
*6. Battery service life highly depend on circumtance and is in normal operation 20yr longer

Electrical Specifications

	Item	NYB2E- 01000 NYB2E- 02000	NYB37- 1000 NYB37- 02000	01000	NYB65- 01000 NYB65- 02000	NYB13- 1000 NYB13- 2000	NYB2E-	NYB37-	NYB55- 00000	NYB65- 00000	NYB13-	NYB3A			
U type		Intel [®] Xeon [®] W-11865MRE	Intel [®] Core™ i7-1185GRE	Intel [®] Core i5-1145GF	t™	Intel [®] Core™ i3-1115GRE	Intel [®] Xeon [®] W-11865MRE	Intel [®] Core™ i7-1185GRE	Intel [®] Core i5-1145GF		Intel [®] Core™ i3-1115GRE	Intel [®] Atom x6425RE			
ted pov Itage	wer supply	24 VDC, n	on-isolated												
owable Itage ra	e power supply ange	20.4 to 28.8 VDC													
oundin	g method	Ground to less than 100 Ω													
ush cu	rrent	At 24 VDC: 12 A / 6 ms max. for cold start at room temperature													
ervolta	ge category	JIS B3502	and IEC 61	131-2: Cate	gory II										
IC imm	unity level	IEC 61131	-2: Zone B												
C accu	racy	At ambient	t temperatur t temperatur t temperatur	e of 25°C: -	1.5 to +1.5 i	min error pe	r month								
wer bu	tton life	100,000 oj	perations												
ttery lif	e	5 years at	25°C (for ba	ttery CJ1W	-BAT01)										
n life		8 years of o 40°C	continuous o	peration at					-						
wer co	nsumption *						-								
cons inclu	imum power sumption uding drives and ansions	167 W	123 W	108 W	89 W	68 W	150 W	106 W	91 W	82 W	61 W	44 W			
Maximum power consumption excluding drives and expansions		130 W	86 W	71 W	62 W	41 W	130 W	86 W	71 W	62 W	41 W	24 W			
Drive	es						-								
	HDD 320 GB	2 W								-					
	HDD 500 GB	2 W								-					
	HDD 1 TB	2 W								-					
	SSD SLC 32 GB			-						-					
	SSD SLC 64 GB			-						-					
	SSD MLC 128 GB			-						-					
	SSD MLC 500 GB			-						-					
	SSD 3DTLC 128 GB	1 W								-					
	SSD 3DTLC 256 GB	1 W								-					
	SSD 3DTLC 512 GB	2 W								-					
	SSD 3DTLC 1 TB	2 W								-					
	CFast MLC 64 GB			-						-					
	CFast MLC 128 GB			-						-					
	CFast MLC 256 GB			-						-					
	CFast 3DTLC 128 GB			-			1 W								
	CFast 3DTLC 256 GB			-			1 W								
	CFast 3DTLC 512 GB			-			2 W								
Expar	nsions						-								
	USB	18 W max	. (4 x 900 m	A at 5 V)											
	PCle	15 W max			5 W max.										

Note: Refer to the Industrial Box PC User's Manual (W553) for details. * The total power consumption is the sum of the power consumption of all items that are installed in your Industrial Box PC.

To guarantee S8BA UPS operation in combination with our IPC, the specified combination of UPS and power-supply must be used.

ltem		NYB2E- 100 NYB2E- 200		01000		NYB13- 1000 NYB13- 2000	NYB2E-	NYB37- 00000	NYB55- _0	NYB65- _0	NYB13- 0	NYB3A-
Minimum	Power supply	240 W			120 W		240 W		120 W			
power requirements	UPS	240 W 120 W			240 W		120 W					

	ltem	NYB1E-	NYB27- 1000 NYB27- 2000	NYB35- 1000 NYB35- 2000	NYB2C-	NYB27-	NYB35-	NYB2C-	NYB2A-			
PU type		Intel [®] Xeon [®] E3-1515M v5	Intel [®] Core [™] i7-7820EQ CPU	Intel [®] Core™ i5-7300U	Intel [®] Celeron [®] 3965U	Intel [®] Core™ i7-7820EQ	Intel [®] Core™ i5-7300U	Intel [®] Celeron [®] 3965U	Intel [®] Atom x5-E3940			
ed pow	ver supply voltage	24 VDC, non-isolated										
wable age rai	power supply nge	20.4 to 28.8 VDC										
unding	g method	Ground to less	than 100 Ω									
sh cur	rent	At 24 VDC: 12 A / 6 ms max. for cold start at room temperature										
rvoltag	ge category	Meets IEC 610	10-2-201: Catego	ry II								
: immı	unity level	IEC 61131-2: 2	Zone B									
accur	racy	At ambient ten	nperature of 55°C: nperature of 25°C: nperature of 0°C: -	-1.5 to +1.5 mi	n error per mont							
er but	ton life	100,000 opera	tions									
ery life	9	5 years at 25° CJ1W-BAT01)		10 years at 40°C		5 years at 25°C (for battery CJ1W-BAT01)	10 years at 40	0°C				
ı life		8 years of cont at 40°C	inuous operation	-	-	8 years of continuous operation at 40°C	-	-	_			
er con	sumption *2				-	-						
cons	imum power sumption including es and expansions	121 W	121 W	69 W	50 W	101 W	61 W	42 W	41 W			
cons	imum power sumption excluding es and expansions	86 W	86 W	46 W	27 W	86 W	46 W	27 W	26 W			
Drive	es				-	-			1			
	HDD 320 GB	2 W					-	_				
	HDD 500 GB	2 W –						_				
	HDD 1 TB	2 W						_				
	SSD SLC 32 GB	2 W					-	_				
	SSD SLC 64 GB	2 W						_				
	SSD MLC 128 GB	2 W					-	_				
	SSD MLC 500 GB	3 W						_				
	SSD 3DTLC 128 GB	1 W						_				
	SSD 3DTLC 256 GB	1 W						_				
								_				
	SSD 3DTLC 512 GB						-					
	SSD 3DTLC 1 TB	2 W					-	-				
CFast MLC 64 GB						1 W						
	CFast MLC 128 GB		-			1 W						
CFast MLC 256 GB			_			1 W						
CFast 3DTLC 128 GB			_			1 W						
CFast 3DTLC 256 GB			-			1 W						
	CFast 3DTLC 512 GB		-			2 W						
Expa	ansions				_	-						
	USB	14 W max. ((2	x 500 mA at 5 V)	+ (2 x 900 mA a	at 5 V))							
	PCle	15 W max.	15 W max.	5 W max.	5 W max.							

Note: Refer to the *Industrial Box PC User's Manual* (W553) for detail.
*1. Product no longer available to order.
*2. The total power consumption is the sum of the power consumption of all items that are installed in your Industrial Box PC.

To guarantee S8BA UPS operation in combination with our IPC, the specified combination of UPS and power-supply must be used.

lt	em	NYB1E / NYB27	NYB35 / NYB2C / NYB27-🗆0 / NYB2A		
Minimum power requirements	Power supply	240 W	120 W		
	UPS	240 W	120 W		

Components and functions

The intent behind our IPC platform is to empower engineers to become unstoppable in developing machines and factories that are better, faster and safer by giving them the freedom and flexibility to explore the opportunities provided by modern IT. In line with Omron's traditional quality standards, the Industrial Box PC is designed to meet the demands of industrial users for maximum robustness and reliability. All maintenance sensitive products (HDD/SDD, fan, battery, and PCIe Card) can be easily reached from the outside of the system. No need to open the electronics compartment, less risk on failure.

Optional connection

RS-232C, DVI-D or DisplayPort++ *1, NY Monitor Link or GigE LAN. NY Monitor Link allows high speed video and data communication over 100 m via Ethernet cable.

DVI-D video Digital, up to 1,920 x 1,200 pixels at 60 Hz (Intel[®] Core™ i7: DVI-I (Digital or analog))

DisplayPort++ *1 Digital, Up to 4,096 x 2,304 pixels at 60 Hz

3x High speed Ethernet 10BASE-T, 100BASE-TX or 1000BASE-T

2x USB2.0 500 mA maximum current Maximum cable length: 5 m

2x USB3.0 900 mA maximum current Maximum cable length: 3 m

Indication LEDs

Robust Mechanics Full metal housing with black industrial coating

Industrial Design

Winner of the 2016 Red Dot design award *2 for excellent industrial design



1x PCIe slot

Half Length Cards 6.6 inches Standard Height Cards 4.2 inches Easy PCIe mounting drawer

Intel[®] Xeon[®], Intel[®] Core[™] i7: X4 (4 lanes) Other CPUs: X1 (1 lane)

1x SD Memory Card slot *1 SDHC type (SD 2.0 specification) Up to 32 GB capacity

1x CFast Card slot

Storage 2.5 inch Solid State Drive (SSD) or Hard Disk Drive (HDD), 7 mm height

I/O (UPS connection)
Input:
Power sequence signal
Output:
SPST-NO contact configuration
24 VDC at 2 A switching capacity (resistive load)

Power switch

24 VDC Power 24 VDC non isolated Lockable power connector

Note: Not all combinations are possible or standard available. Please contact your Omron representative to discuss the possibilities.

- *1. 11th generation CPU: Equipped with DisplayPort++ instead of DVI, but no SD Memory Card slot.
- *2. The Red Dot design award has been presented by the Design Zentrum Nordrhein Westfalen since 1955. It is one of the best-respected design competitions in the world, along with the iF award (Germany) and IDEA (the United States).

Environmental Specifications

	Item	Specifications
	Ambient operating temperature *1	0 to 55°C
	Ambient storage temperature *1	-20 to 70°C
	Ambient operating humidity *1	10% to 90% with no condensation
	Ambient storage humidity *1	10% to 90% with no condensation
	Operating atmosphere	No corrosive gases
	Altitude	2,000 m max.
Operation	Noise resistance (during operation)	Conforms to IEC61000-4-4, 2kV (power lines)
environment	Vibration resistance (during operation)	Conforms to IEC 60068-2-6. For a product with an SSD: 5 to 8.4 Hz with 3.5 mm single amplitude and 8.4 to 150 Hz with 9.8 m/s ² for 10 times each in X, Y and Z directions. For a product with a HDD the vibration resistance depends on the mounting orientation * 2.
	Shock resistance (during operation)	Conforms to IEC 60068-2-27. 147 m/s², 3 times in each X, Y and Z directions
	Installation method	Book mount, Wall mount
	Pollution degree	2 or less: Meets IEC 61010-2-201.
Applicable standards *3		EU Directives: EMC Directive 2014/30/EU (EN 61131-2) and RoHS Directive KC Registration, RCM, cULus

*1. The allowed ambient operating temperature and ambient humidity depend on product type, CPU type, mounting orientation, and storage device type.
 *2. Vibration resistance depends on the Industrial Box PC's mounting orientation and storage device type:

Mounting orientation	SSD or CFast Card	HDD
Book	9.8 m/s ²	2.5 m/s ²
Wall	1	4.9 m/s ²

*3. Refer to the OMRON website (www.ia.omron.com) or contact your OMRON representative for the most recent applicable standards for each model.

Storage Device Specifications

Item		-				Snecif	ications						
	NY000-	NY000-	NY000-	NY000-	NY000-	NY000-	NY000-	NY000-	NY000-	NY000-	NY000-	NY000-	
Model	AS00	AS01	AS03	AS04	AS05	AS07	AS08	AS09	AS10	AS11	AS12	AS13	
Capacity	32 GB	64 GB	64 GB	128 GB	500 GB	1 TB	256 GB	128 GB SSD	256 GB	512 GB	1 TB	2 TB	
Туре	SSD (SLC)		SSD (SLC)	SSD (MLC)					SSD (3DTLC)	SSD (3DTLC)	SSD (3DTLC)	SSD (3DTLC)	
S.M.A.R.T. support	Yes												
Rotation speed	-	-	-	-	-	-	-	-	-	-	-	-	
Interface	Serial ATA 3.1												
Sustained standard read speed	Up to 160 MB/s	Up to 160 MB/s	Up to 500 MB/s	Up to 530 MB/s	Up to 415 MB/s	Up to 550 MB/s	Up to 530 MB/s	Up to 550 MB/s	Up to 550 MB/s	Up to 550 MB/s	Up to 550 MB/s	Up to 550 MB/s	
Sustained standard write speed	Up to 145 MB/s	Up to 150 MB/s	Up to 370 MB/s	Up to 190 MB/s	Up to 200 MB/s	Up to 340 MB/s	Up to 210 MB/s	Up to 450 MB/s	Up to 485 MB/s	Up to 500 MB/s	Up to 510 MB/s	Up to 510 MB/s	
Operating temperature	0 to 70°C												
Operating humidity	10% to 95% (with no co		10% to 85% (with no condensat ion)	10% to 95% (with no co	% ndensation)			5% to 90%	% (with no condensation)				
Storage temperature	-40 to 100°	С	-45 to 90°C	-55 to 95°C	55 to 95°C				-40 to 85°C				
Storage humidity	10% to 95%	6 (with no co	ndensation)					5% to 93%	(with no cor	densation)	lensation)		
Life	1,500 TB written	3,000 TB written	1900 TB written	208 TB written	154 TB written	1000 TB written	416 TB written	90 TB written	230 TB written	550 TB written	1200 TB written	3000 TB written	
ltem						Specif	ications						
Model	NY000-AT0	0	NY000-AT)1	NY000-AT		1	05	NY000-AT	06	NY000-AT	07	
Capacity	64 GB	0	128 GB	71	256 GB	02	NY000-AT05 128 GB		256 GB		512 GB		
	CFast (MLC	ר <u>ר</u>	CFast (ML	ר <u>ר</u>	CFast (ML	\sim			CFast (3DTLC)		CFast (3DTLC)		
Type S.M.A.R.T. support	Yes	5)		5)		0)	CI asi (5D	110)	CI ast (5D	110)	Ci asi (5D	110)	
Rotation speed	-	_		_		_		_		-		_	
Interface	Serial ATA	3.1											
Sustained standard read speed	Up to 530 N		Up to 530 M	//B/s	Up to 530 MB/s		Up to 550	Up to 550 MB/s		MB/s	Up to 550 MB/s		
Sustained standard write speed	Up to 100 N	//B/s	Up to 190 M	//B/s	Up to 210 MB/s Up to		Up to 450 MB/s Up to 485 MB/		MB/s	Up to 500 MB/s			
Operating temperature	-40 to 85°C						-40 to 85°C						
Operating humidity	10% to 95% (with no condensation)					5% to 90% (with no condensation)							
Storage temperature	-55 to 95°C	:					-40 to 85°0	2					
Storage humidity	10% to 95%	6 (with no co	ndensation)				5% to 90%	(with no cor	ndensation)				
			1		1						1		

Life125 TB written208 TB written417 TB written90 TB written230 TB written550 TB writtenNote: Orders for NY000-AH00/-AH01/-AH02 will be accepted until the end of December 2025.550 TB written550 TB written

Dimensions



		Specifi	cations							
	Box									
ltem	NYB1E-00000 NYB27-01000 NYB27-02000 NYB2E-01000 NYB2E-02000 NYB37-01000 NYB37-02000 NYB35-01000 NYB55-02000	NYB351 NYB352 NYB2C1 NYB651 NYB652 NYB131 NYB132	NYB27-00 NYB2E00 NYB3700 NYB5500	NYB35-00000 NYB2C-00000 NYB2A-00000 NYB65-00000 NYB13-00000 NYB3A-00000						
Dimensions	Width X = 282 mm Depth Y = 195 mm. Y = 200 mm including the DVI connectors. Height Z = 89 mm	Width X = 282 mm Depth Y = 195 mm. Y = 200 mm including the DVI connectors. Height Z = 73 mm	Width X = 282 mm Depth Y = 195 mm. Y = 200 mm including the DVI connectors. Height Z = 56 mm	Width X = 282 mm Depth Y = 195 mm. Y = 200 mm including the DVI connectors. Height Z = 41 mm						
Weight	3.8 kg	3.0 kg	2.6 kg	2.1 kg						

Bracket Specifications

The metal mounting brackets mount your Industrial Box PC and they are the connection for the functional ground. Use metal screws with a diameter of 4 mm or 5 mm to mount the brackets. Mounting screw locations for book mount and wall mount orientation:



			Dri	II Specification	ons	Product Dimensions			
Model	Bracket type	Bracket ID	Hole Distance X	Hole Distance Y	Distance Z	Bracket Width	Bracket Height	Top to hole A	Top to hole B
All	Wall mount	NY000-AB01	245 mm	218 mm	12 mm	23 mm	245 mm	7.5 mm	19.5 mm
NYB1E NYB2711 NYB2722 NYB2E11 NYB2E22 NYB2E22 NYB3711 NYB3722 NYB5511 NYB5522	Book mount	NY000-AB00	60 mm	303 mm	11 mm	96 mm	319 mm	8 mm	8 mm
NYB35-01000 NYB35-02000 NYB2C-01000 NYB65-01000 NYB65-02000 NYB13-01000 NYB13-02000	Book mount	NY000-AB02	50 mm	303 mm	11 mm	80 mm	319 mm	8 mm	8 mm
NYB35-00 NYB2C00 NYB6500 NYB1300 NYB2A00 NYB3A00	Book mount	NY000-AB04	N/A	298 mm	11 mm	47 mm	339 mm	8 mm	28 mm
NYB27-00000 NYB2E-00000 NYB37-00000 NYB55-00000	Book mount	NY000-AB05	25 mm	303 mm	11 mm	63 mm	339 mm	8 mm	28 mm

Recommended Related Products



Industrial Monitor NY-series

The Industrial Monitor is of key importance at the interface between operator and system. The Industrial Monitor is efficient, effective and highly visible with an attractive design.



Industrial Panel PC NY-series

The Industrial Panel PC intelligently combines the functionality of the Industrial Box PC and Industrial Monitor. No cables are used between the two components, which ensures optimal signal distribution and reliable operation in industrial environments.



UPS S8BA-series

The OMRON S8BA UPS protects the Industrial Box PC from power failures, voltage variations and instantaneous voltage drops.

Related Manuals

The following manuals are related. Use these manuals for reference.

Manual name	Cat. No.	Model numbers	Application	Description
Industrial Box PC User's Manual	W553	NYB1E1	Learning all basic information about the Industrial Box PC. This includes introductory information with features, hardware overview, software overview, specifications, mounting, wiring, connecting, operating and maintaining the Industrial Box PC.	An introduction to the Industrial Box PC is provided along with the following information: • Overview • Hardware • Software • Specifications • Installation • Operating Procedures • Maintenance
Industrial Monitor User's Manual	W554	NYM19W-C1 NYM15W-C10 NYM12W-C10	Learning all basic information about the Industrial Monitor. This includes introductory information with features, hardware overview, specifications, mounting, wiring, connecting, operating and maintaining the Industrial Monitor.	An introduction to the Industrial Monitor is provided along with the following information: • Overview • Hardware • Software • Specifications • Installation • Operating Procedures • Maintenance
Industrial Panel PC User's Manual	W555	NYP27	Learning all basic information about the Industrial Panel PC. This includes introductory information with features, hardware overview, software overview, specifications, mounting, wiring, connecting, operating and maintaining the Industrial Panel PC.	An introduction to the Industrial Panel PC is provided along with the following information: • Overview • Hardware • Software • Specifications • Installation • Operating Procedures • Maintenance
UPS S8BA User's Manual	U702	S8BA	Learning the information that is necessary to use the Uninterruptible Power Supply (UPS) Unit.	An introduction to the UPS is provided along with the following information: • Overview • Preparation • Installation and Connection • Check and Start Operation • Maintenance and Inspection • Shutdown Processing • I/O Signal Functions • Troubleshooting
NY-series Operating Systems and Software Utilities Manual	W616	NYB - 0 NYB - 1 NYB - 2 NYB - 3 NYB - 4 NYB - 5 NYP - 0 NYP - 2 NYP - 2 NYP - 3 NYP - 3 NYP - 3 NYP - 3 NYP - 5	Learning all software related information about the Industrial Box PC. This includes introductory information, installation, operating procedures and maintenance. Mainly software information is provided.	An introduction to the Box PC is provided along with the following information: • Overview • Software • Specifications • Installation • Operating Procedures • Maintenance

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company