CJ-series CJ2M CPU Units, Pulse I/O Modules CJ2M-CPU3 /-CPU1 /-MD21

Since 2001, CJ1M-series PLCs are in control of a wide variety of applications worldwide.

The accumulated experience and advancements in technology now result in CJ2M; fully compatible, yet fully new.







CJ2M-MD21

CJ2M-CPU3

CJ2M-CPU1

- Increased performance, and increased memory capacity
- Up to 40 I/O unit on any CPU
- Pulse I/O Modules add position control functions to any CPU
- USB for plug-and-play access to the PLC
- All models available with or without Ethernet port
- · Choice of serial port plug-in modules

Features

- Five variations in program capacity from 5K steps to 60K steps; scale the CPU to your application needs.
- Faster processors; LD instruction execution time is reduced to 40 ns, floating point trigonometrics in less than 1 μ s.
- Optional Pulse I/O Modules can be mounted to enable positioning functions for up to four axes. The module provides high-speed counters, interrupt inputs and pulse train/PWM outputs. (CJ2M CPU Units with Unit Version 2.0 or Later)
- Faster Function Block calls and execution, faster interrupt handling, less overhead time.
- · Added execution memory for Function Blocks allows structured, object-oriented programming even in entry-level CPUs.
- General-purpose Ethernet port supports EtherNet/IP tag-based data links, connection to Support Software, communications between PLCs, FTP data transfers, and more (CJ2M-CPU3^[]).
- Standard USB port on all models allows Support Software to connect directly through standard USB cable.
- A Serial Option Module can be mounted to add RS-232C or RS-422A/485 communications ports (CJ2M-CPU3⁻).
- Compatible with all existing CJ1 power supply-, I/O-, control- and communication units.

Ordering Information

Applicable standards

Refer to the OMRON website (www.ia.omron.com) or ask your OMRON representative for the most recent applicable standards for each model.

CJ2M CPU Units (Built-in EtherNet/IP)

		Specifications					Current consumption (A)		
Product name	I/O capacity/ Mountable Units (Expansion Racks)	Program capacity	Data memory capacity	LD instruction execution time	EtherNet/IP function	Option board slot	5 V	24 V	Model
CJ2M (Built-in		in 60K steps 160K words (DM: 32K words,					CJ2M-CPU35		
EtherNet/IP) CPU Units		30K steps EM: 32K words × 4 banks)	-	0.04 μs YES	YES YES			_	CJ2M-CPU34
	2,560 points/40 Units (3 Expansion Racks max.)	20K steps	64K words			YES YES	0.7 (See note.)		CJ2M-CPU33
		10K steps	(DM: 32K words, EM: 32K words ×				1000.)		CJ2M-CPU32
		5K steps	1 bank)						CJ2M-CPU31

Note: Add 0.005A, 0.030A and 0.075A when using Serial Communications Option Boards (CP1W-CIF01/CIF11/CIF12-V1), respectively. Add 0.15A/Unit when using NT-AL001 RS-232C/RS-422A Adapters.

Add 0.04A/Unit when using CJ1W-CIF11 RS-422A Adapters.

Add 0.20A/Unit when using NV3W-M□20L(-V1) Programmable Terminals.

CJ2M CPU Units

		Specifications					Current consumption (A)		
Product name	I/O capacity/ Mountable Units (Expansion Racks)	Program capacity	Data memory capacity	LD instruction execution time	EtherNet/IP function	Option board slot	5 V	24 V	Model
	CPU Units2,560 points/40 Units (3 Expansion Racks max.)00K steps(DM: 3 EM: 32 420K steps 10K steps20K steps 64K w 10K steps64K w 64K w 10K steps	60K steps 160K words (DM: 32K words,					CJ2M-CPU15		
CJ2M CPU Units		EM: 32K words × 4 banks)						CJ2M-CPU14	
		20K steps	64K words	0.04 μs	-	-	0.5 (See note.)	-	CJ2M-CPU13
		10K steps	(DM: 32K words, EM: 32K words ×				1000.)		CJ2M-CPU12
		5K steps	1 bank)					CJ2M-CPU11	

Note: Add 0.15A/Unit when using NT-AL001 RS-232C/RS-422A Adapters.

Add 0.04A/Unit when using CJ1W-CIF11 RS-422A Adapters.

Add 0.20A/Unit when using NV3W-M□20L(-V1) Programmable Terminals.

Serial Communications Option Boards (Only CJ2M-CPU3)

The serial communications port can be equipped by installing the serial communications option board to the option board slot in front of CPU unit.

Product name	Specifications	Serial communications mode	Current consumption (A)		Model	
		mode	5 V	24 V		
RS-232C Option Board	One RS-232C port Connector: D-Sub, 9 pin, female Maximum transmission distance: 15m		0.005	_	CP1W-CIF01	
RS-422A/485 Option Board	One RS-422A/485 port Terminal block: using ferrules Maximum transmission distance: 50m	Host Link, 1:N NT Link, No-protocol, Serial PLC Link Slave, Serial PLC Link Master, Serial Gateway converted to CompoWay/F, and Tool Bus *	0.030	_	CP1W-CIF11	
RS-422A/485 Isolated-type Option Board	One RS-422A/485 port (Isolated) Terminal block: using ferrules Maximum transmission distance: 500m		0.075	_	CP1W-CIF12-V1	

Note: It is not possible to use a CP-series Ethernet Option Board (CP1W-CIF41), LCD Option Board (CP1W-DAM01) with a CJ2M CPU Unit. * The following modes cannot be used: 1:1 NT Link, Serial Gateway converted to Host Link FINS, 1:1 Link Master, and 1:1 Link Slave.

Pulse I/O Modules (Only CJ2M CPU Unit with Unit Version 2.0 or Later)

Optional Pulse I/O Modules can be mounted to enable pulse I/O. Up to two Pulse I/O Modules can be mounted to the left side of a CJ2M CPU Unit.

Product name	Specifications			Model
		5 V	24 V	
	Sinking outputs, MIL connector 10 inputs (including four interrupt/quickresponse inputs and two high-speed counter inputs) 6 outputs (including two pulse outputs and two PWM outputs)	0.08		CJ2M-MD211
	Sourcing outputs, MIL connector 10 inputs (including four interrupt/quickresponse inputs and two high-speed counter inputs) 6 outputs (including two pulse outputs and two PWM outputs)	0.08		CJ2M-MD212

Note: Connectors are not provided with Pulse I/O Modules. Purchase the following Connector, an OMRON Cable with Connectors for Connector Terminal Block Conversion Units, or an OMRON Cable with Connectors for Servo Relay Units.

Connecting to Pulse I/O Modules

On wiring, refer to Pulse I/O Modules Connector Wiring Methods.

Product name		Model		
Applicable Connector	MIL Flat Cable Connector	s (Pressure-fitted Connectors)		XG4M-4030-T
	Push-In Plus (Clamp 40-te	erminals)		XW2K-40G-T
Connector-Terminal Block Conversion Units	Phillips screw (M3 screw	terminals, 40-terminals)		XW2D-40G6
	Slotted screw (M3 Europe	ean type, 40-terminals)		XW2R-E40GD-T
		•	Cable length: 0.25 m	XW2Z-C25K
			Cable length: 0.5 m	XW2Z-C50K
		XW2Z-100K		
Cable for Connector-Terminal Block Conversion Unit		XW2Z-150K		
		XW2Z-200K		
		XW2Z-300K		
		XW2Z-500K		
	Servo Relay Unit for 1 axi	XW2B-20J6-8A		
Servo Relay Units	Servo Relay Unit for 2 axo	XW2B-40J6-9A		
		Cable for Pulse I/O Modules	Cable length: 0.5 m	XW2Z-050J-A33
	G5 Series		Cable length: 1 m	XW2Z-100J-A33
		Servo Driver Connecting Cables	Cable length: 1 m	XW2Z-100J-B31
Cables for Servo Relay Units			Cable length: 2 m	XW2Z-200J-B31
Cables for Gerve Relay Units		Cable for Pulse I/O Modules	Cable length: 0.5 m	XW2Z-050J-A33
	SMARTSTEP2		Cable length: 1 m	XW2Z-100J-A33
		Servo Driver Connecting Cables	Cable length: 1 m	XW2Z-100J-B32
		•	Cable length: 2 m	XW2Z-200J-B32

Accessories

The following accessories come with CPU Unit:

Item	Specification		
Battery CJ1W-BAT01			
End Cover	CJ1W-TER01 (necessary to be mounted at the right end of CPU Rack)		
End Plate	PFP-M (2 pcs)		
Note: A serial port (RS-232C) con	ector is not provided. Purchase a connector separately for serial port connection		

A serial port (RS-232C) connector is not provided. Purchase a connector separately for serial port connection. XM3A-0921 (manufactured by OMRON) or equivalent XM2S-0911-E (manufactured by OMRON) or equivalent Note: A

General Specifications

	Marina.		CJ2M-				
	Item	CPU1	CPU3				
Enclosure		Mounted in a panel					
Grounding		Less than 100 Ω					
CPU Unit Dimensions		90 mm × 75 mm × 31 mm	90 mm \times 75 mm \times 62 mm				
Weight *1		130 g or less	190 g or less * 2				
Current Consump	tion	5 VDC, 0.5 A	5 VDC, 0.7 A				
Ambient Operating Temperature		0 to 55°C					
	Ambient Operating Humidity	10% to 90% (with no condensation)					
	Atmosphere	Must be free from corrosive gases.					
	Ambient Storage Temperature	-20 to 70°C (excluding battery)					
	Altitude	2,000 m or less					
	Pollution Degree	2 or less: Meets IEC 61010-2-201.					
Operation	Noise Immunity	2 kV on power supply line (Conforms to IEC 61000-4-4.)					
Environment	Overvoltage Category	Category II: Meets IEC 61010-2-201.					
	EMC Immunity Level	Zone B					
	Vibration Resistance	Conforms to IEC60068-2-6 5 to 8.4 Hz with 3.5-mm amplitude, 8.4 to Acceleration of 9.8 m/s ² for 100 min in X, ^N 100 min total)	150 Hz ⁄, and Z directions (10 sweeps of 10 min each =				
	Shock Resistance	Conforms to IEC60068-2-27 147 m/s ² , 3 times in X, Y, and Z directions	(100 m/s ² for Relay Output Units)				
	Life	5 years at 25°C					
Battery	Weight	Approx. 10 g					
	Model	CJ1W-BAT01					
Applicable Standa	ards	Conforms to cULus, NK, LR, and EC Direct	tives.				

Note: 1. Includes wight of end covers and battery.2. Without a Serial Option Board.

Performance Specifications

Items			CJ2M- CPI111/31 CPI112/32 CPI113/33 CPI114/34 CPI115/35					
Liser Memory			CPU11/31	CPU12/32	CPU13/33	CPU14/34	CPU15/35	
User Memory I/O Bits		5K steps 2,560 bits	10K steps	20K steps	30K steps	60K steps		
	Overhead F	Processing Time	Normal Mode: CJ2M-CPU3⊡: 270 CJ2M-CPU1⊡: 160 * The following time 100 µs + (Nur The following time	μs * e must be added whe nber of words transfe	erred × 1.8 μs) en using Pulse I/O Moo	ag data links for the CJ dules with a CJ2M CPI		
Processing Speed	Execution	Time	Basic Instructions	: 0.04 µs min.				
-		I/O Interrupts and External Interrupts	Interrupt task startu Return time to cyclic	p time: 31 μs				
	Interrupts	Scheduled		/al : 0.4 ms (set in 0.7	1 ms increments)			
		Interrupts	Return time to cyclic	c task : 11 μs				
Maximum Numb	er of Conne	ctable Units	Total per PLC: 40 U	or Expansion Rack: Inits max.	10 Units max.;			
-	Basic I/O U	nits)1 Interrupt Input Units			
-	Special I/O	Units	1 and 8 unit number	rs.)	ounted. (Unit numbers	run from 0 to 95. Unit	s are allocated betwee	
-	CPU Bus U	nits	CJ2M-CPU3 : 15 U CJ2M-CPU1 : 16 U					
_	Pulse I/O M		2 Units max. * * Supported only b	y CJ2M CPU Units w	ith unit version 2.0 or	later. A Pulse I/O Mod	ule must be mounted.	
	used	hich interrupts can be	Slots 0 to 4 on CPU	Rack				
Maximum Numb	er of Expans	sion Racks	3 max.	ds):Words CIO 000				
-	Link Area		,	ds) : Words CIO 000				
-	CPU Bus Unit Area		6,400 bits (400 words) : Words CIO 1500 to CIO 1899					
-	Special I/O Unit Area		15,360 bits (960 words): Words CIO 2000 to CIO 2959 20 inputs, 12 outputs (CIO 2960 to CIO 2963) *					
:	Pulse I/O A		* Supported only b	y ĊJ2M CPU Units w	ith unit version 2.0 or	later. A Pulse I/O Mod	ule must be mounted.	
		Link Words	, ,	s) : Words CIO 310				
	DeviceNet	Area	, ,	ds) : Words CIO 320				
	Internal I/O	Area	37,504 bits (2,344 v	vords): Words CIO 38	300 to CIO 6143 (Can	ot be used for external not be used for externa		
Work Area			8,192 bits (512 words): Words W000 to W511 (Cannot be used for external I/O.)					
Holding Area			Bits in this area mai Words H512 to H15 block instances (i.e.	35: These words can , they are allocated c	tatus when PLC is turn be used only for funct	ned OFF or operating ion blocks. They can b es in function blocks).		
Auxiliary Area			 24,576 bits (1,53) Read/write: 16,384 * A960 to A1471 ar 	ords): Words A0 to A 6 words): Words A10 bits (1,024 words) in nd A10000 to A11535	000 to A11535 * words A448 to A1471	by CPU Bus Units, Spe	ecial I/O Units, PTs, an	
Temporary Area			16 bits: TR0 to TR1					
Fimer Area				· ·	eparate from counters			
Counter Area DM Area		 4,096 counter numbers (C0000 to C4095 (separate from timers)) 32k words * DM Area words for Special I/O Units: D20000 to D29599 (100 words × 96 Units) DM Area words for CPU Bus Units: D30000 to D31599 (100 words × 16 Units) Bits in the EM Area can be addressed either by bit or by word. These bits cannot be addressed by CPU Bi Units, Special I/O Units, PTs, and Support Software that do not specifically support the CJ2 CPU Units. 						
EM Area			32k words/bank × 4 * Bits in the EM Are	banks max.: E00_00 a can be addressed e Units, PTs, and Sup	0000 to E3_32767 max either by bit or by word	1 1 1	addressed by CPU Bu t the CJ2 CPU Units.	
	Force-S/R	Enabled Banks *1	Bank 0 hex			Bank 0 to 3 hex		
Index Registers			IR0 to IR15 These are special registers for storing PLC memory addresses for indirect addressing. (Index Registers can be set so that they are unique in each task or so that they are shared by all tasks.)					
Cyclic Task Flag	Area		128 flags					
Memory Card			128 MB, 256 MB, or	r 512 MB				
			PROGRAM Mode:	Programs are not exe	ecuted. Preparations c	an be executed prior to	o program execution i	
Operating Modes	5		MONITOR Mode:	present values in I/O	ed, and some operatic memory, are enabled ed. This is the normal		ting, and changes to	
				·	the EM Area force	· · ·		

	Items				CJ2M-		1
			CPU11/31	CPU12/32	CPU13/33	CPU14/34	CPU15/35
Execution Programm	Mode ing Languages		Normal Mode Ladder Logic (LD), Sequential Function Cl Structured Text (ST), a Instruction Lists (IL)				
Function	Maximum numbe	r of definitions	256			2,048	
Blocks	Maximum numbe		256			2,048	
FB Program		a of matances	20K steps			2,040	
Tasks	Type of Tasks		Cyclic tasks Interrupt tasks (Power (tasks, and input interru Cyclic tasks: 128		cheduled interrupt ta	sks, I/O interrupt tasks	, and external interrupt
	Number of Tasks		Interrupt tasks: 256 (Interrupt tasks can be tasks is actually 384 m	ax.)	-		total number of cyclic
	Type of Symbols		 Local symbols: Can Global symbols: Car Network symbols (ta depending on param * Supported only by th 	n be used in all tasks igs) * : I/O memory in neter settings.	in the PLC.		using symbols,
Symbols (Variables)	Data Type of Sym	nbols	 BOOL (bit) UINT (one-word uns UDINT (two-word ur ULINT (four-word ur INT (one-word signe DINT (two-word signe DINT (two-word signe UINT BCD (one-word UDINT BCD (two-word ULINT BCD (four-word float LREAL (two-word float LREAL (four-word float CHANNEL (word) * NUMBER (constant WORD (one-word flat DWORD (two-word flat LWORD (four-word flat STRING (1 to 255 A TIMER (timer) *4 COUNTER (counter User defined data ty 	isigned binary) isigned binary) ed binary) ed binary) ied binary) d unsigned BCD) *3 ord unsigned BCD) * ord unsigned BCD * ord un	3		
	Maximum Size of	Symbol	32k words				
	Array Symbols (A	Array Variables)	One-dimensional arrays				
	Number of Array	Elements	32,000 elements max.				
	Number of Regist Symbols (Tags) *		2,000 max.				
	Length of Networ Name *5	rk Symbol (Tag)	255 bytes max.				
	Encoding of Netwo	rk Symbols (Tags) *5	UTF-8				
	Memory Capacity	,	8,000 words (The EM Area can be specified from the CX-Programmer to use up to 32K words multiplied by the number of banks supported by the CPU Unit model.)				
	Number of Samp	lings	Bits = 31, one-word da	ta =16, two-word data	a = 8, four-word data	a = 4	
Data	Sampling Cycle		1 to 2,550 ms (Unit: 1 r	ns)			
Trigger Conditions			ON/OFF of specified bit Data comparison of specified word Data size: 1 word, 2 words, 4 words Comparison Method: Equals (=), Greater Than (>), Greater Than or Equals (≥), Less Than (<), Less Than or Equals (≤), Not Equal (≠)				
			-32,768 to +32,767 ms				
File Memory		Memory Card (128, 256, or 512 Mbytes) (Use the Memory Cards provided by OMRON.) EM file memory (Part of the EM Area can be converted for use as file memory.)					
Source/ Function block program memory, Comment comment file, program index file, Memory symbol tables		Capacity: 1 Mbytes					
		Logical Ports	8 ports (Used for SEN	, RECV, CMND, PM	ICR, TXDU, and RXI	DU instructions.)	
	Logical Ports for Communications Extended Logical 64 ports (Used for SEND2_RECV/2_CMND2_and PMCR2 instructions.)						
	Communications	Ports	04 poins (Used for SER	DZ, INECVZ, GIVINDZ	2, and PMCR2 instru	ictions.)	
Commu- nications	CIP		Number of connections		2, and PMCR2 instru		

*2. Supported only by CJ2M CPU Units with unit version 2.0 or later. A Pulse I/O Module must be mounted.
*3. Cannot be used in Function blocks.
*4. Can be used only in Function blocks.
*5. Supported only by the CJ2M-CPU3□.

				CJ2M-				
			Item	CPU11/31 CPU12/32 CPU13/33 CPU14/34 CPU15/35				
	Per	riph	eral (USB) Port	USB 2.0-compliant B-type connector				
	Ιr	Bau	ud Rate	12 Mbps max.				
		Tra	nsmission Distance	5 m max.				
				CJ2M-CPU1 interface: Conforms to EIA RS-232C. CJ2M-CPU3 : No serial ports with default system One of the following Serial Option Boards can be mounted. CP1W-CIF01 RS-232C Option Board CP1W-CIF11 RS-422A/485 Option Board (not isolated, max. transmission distance: 50 m) CP1W-CIF12-V1 RS-422A/485 Option Board (isolated, max. transmission distance: 500 m)				
				Half-duplex				
				Start-stop				
		Ваι	ud Rate	0.3, 0.6, 1.2, 2.4, 4.8, 9.6, 19.2, 38.4, 57.6, or 115.2 (kbps)				
		Tra	nsmission Distance	15 m max.				
	Eth	erN	let/IP Port *6					
		su	Media Access Method	CSMA/CD				
		Media Access Method Modulation Transmission Paths Baud Rate		Baseband				
				Star				
		bed	Baud Rate	100 Mbps (100Base-TX)				
			Transmission Media	Shielded twisted-pair (STP) cable; Categories: 5, 5e				
		ssic	Transmission Distance	100 m (between ethernet switch and node)				
		Transmission	Number of Cascade Connections	No restrictions if ethernet switch is used.				
			CIP Communications: Tag Data Links					
			Number of Connections	32				
			Packet Interval (Refresh period)	1 to 10,000 ms (Unit: 0.5 ms) Can be set for each connection. (Data will be refreshed at the set interval, regardless of the number of nodes.)				
			Permissible Communications Band	3,000 packets per second * 7				
Commu-			Number of Registerable Tag	32				
nications			Type of Tags	CIO, DM, EM, HR, WR, and Network symboles				
			Number of Tags per Connection	8 (Seven tags if PLC status is included in the segment.)				
			Maximum Link Data Size per Node (total size of all tags)	640 words				
			Maximum Data Size per Connection	1 640 words *8 (Data is synchronized within each connection.)				
		s	Number of Registrable Tag Set	32 (1 connection = 1 segment)				
		cifications	Maximum Tag Set Size	640 words ★8 (One word is used when PLC status is included in the segment.)				
		Spe	Maximum Number of Tags Refreshable in a Single Cycle of CPU Unit *9	Output/send (CPU Unit to EtherNet/IP): 32 Input/receive (EtherNet/IP to CPU Unit): 32				
		Communications	Data Size Refreshable in a Single Cycle of CPU Unit *9	Output/send (CPU to EtherNet/IP) : 640 words Input/receive (EtherNet/IP to CPU): 640 words				
		unuu	Change of Tag Data Link Parameter Settings during Operation	OK *10				
		on	Multi-cast Packet Filter *11	ОК				
		5	CIP Communications: Explicit Messages	-				
			Class 3 (Connection Type)	Number of connections: 128				
			UCMM (Non-connection Type)	Maximum number of clients that can communicate at the same time : 16 Maximum number of servers that can communicate at the same time: 16				
			CIP Routing	OK (CIP routing is enabled for the following remote Units: CJ1W-EIP21, CJ2H-CPU6□-EIP, CJ2M- CPU3□, and CS1W-EIP21.)				
			FINS Communications	-				
			FINS/UDP	OK				
			FINS/TCP	16 connections max.				
			EtherNet/IP Conformance Test	Conforms to A5.				
			EtherNet/IP Interface t/IP port is built into CJ2M-CPU3 o	10Base-T/100Base-TX Auto Negotiation/Fixed Setting				

***6.** The EtherNet/IP port is built into CJ2M-CPU3 only.

*7. "Packets per second" is the number of communications packets that can be processed per second.*8. Unit version 2.0 of built-in EtherNet/IP section: 20 words.

*9. If the maximum number is exceeded, refreshing will require more than one CPU Unit cycle.
*10. When changing parameters, however, the EtherNet/IP port where the change is made will be restarted. In addition, a timeout will temporarily occur at the other node that was communicating with that port, and it will then recover automatically.
*11. The EtherNet/IP port supports an IGMP client, so unnecessary multicast packets are filtered by using an Ethernet switch that supports IGMP

snooping.

Function Specifications

	Fu	unctions		Description
	Minimum Cycle Time			A minimum cycle time can be set. (0.2 to 32,000 ms; Unit: 0.1 ms) The minimum cycle time setting can be changed in MONITOR mode.
Cycle Time Management	Cycle Time Mon	itoring		The cycle time is monitored. (0.01 to 40,000 ms; Unit: 0.01 ms)
	Background Pro	ocessing		Instructions with long execution times can be executed over multiple cycles to prevent fluctuations in the cycle time.
			Cyclic Refreshing	Cyclic refreshing of Basic I/O Units, Special I/O Units, and CPU Bus Units
	Basic I/O Units, Special I/O	I/O Refreshing	Immediate Refreshing	I/O refreshing by immediate refreshing instructions
	Units, and CPU Bus Units		Refreshing by IORF	I/O refreshing by IORF instruction
		Unit Recognitio	n at Startup	The number of units recognized when the power is turned ON is displayed.
		Input Response	Time Setting	The input response times can be set for Basic I/O Units. The response time can be increased to reduce the effects of chattering and noise at input contacts. The response time can be decreased to enable detecting shorter input pulses.
	Basic I/O Units	c I/O Units Load OFF Function Basic I/O Unit Status Monitoring		All of the outputs on Basic I/O Units can be turned OFF when an error occurs in RUN or MONITOR mode.
Unit (I/O) Management				Alarm information can be read from Basic I/O Units and the number of Units recognized can be read.
		Reading/writing instructions for		Special instructions can be used to read/write required data for specific Units at high speed.
	Special I/O Units and CPU Bus Units	Unit Restart Bits	s to Restart Units	A Special I/O Unit or CPU Bus Unit can be restarted.
		Automatic I/O Allocation at Startup		I/O words can be automatically allocated to the Basic I/O Units that are connected in the PLC to start operation automatically without registering Units into I/O tables.
	Configuration Management			The current unit configuration can be registered in I/O tables to prevent it from being changed, to reserve words, and to set words.
		Rack/Slot First Word Settings		The first words allocated to a Units on the Racks can be set.
	Holding I/O Mem	nory when Changi	ng Operating Modes	The status of I/O memory can be held when the operating mode is changed or power is turned ON. The forced-set/reset status can be held when the operating mode is changed or power is turned ON.
	File Memory			Files (such as program files, data files, and symbol table files) can be stored in Memory Card, EM File Memory, or Comment Memory.
Memory Management	Built-in Flash Me	emory		The user program and Parameter Area can be backed up to an internal flash memory when they are transferred to the CPU Unit.
	EM File Function	n		Parts of the EM Area can be treated as file memory.
	Storing Comme	nts		I/O comments can be stored as symbol table files in a Memory Card, EM file memory, or comment memory.
	EM Configuration			EM Area can be set as trace memory or EM file memory.
	Automatic File T	ransfer at Startup	•	A program file and parameter files can be read from a Memory Card when the power is turned ON.
Memory Cards	Program Replac	ement during PLC	COperation	User programs can be transferred from a Memory Card to CPU Unit during operation.
	Function for Rea Card	ading and Writing	Data from a Memory	Data in I/O memory in the CPU Unit can be written to a Memory Card in CSV/TXT format. Data in CSV/TXT format in the Memory Card can be read to I/O memory in the CPU Unit.

	Funct	ion	Description				
Communicati	ons		-				
	Peripheral (USB) Port	Peripheral Bus	Bus for communications with various kinds of Support Software running on a personal computer. High-speed communications are supported.				
	Serial Port (Option) *12	Application is possible when a Serial Communications Option Board is mounted.				
	Host Link (SYS	WAY) Communications	Host Link commands or FINS commands placed between Host Link headers and terminators can be sent from a host computer or PT to read/write I/O memory, read/control the operating mode, and perform other operations for PLC.				
	NO-protocol communications		I/O instructions for communications ports (such as TXD/RXD instructions) can be used for data transfer with peripheral devices such as bar code readers and printers.				
			I/O memory in the PLC can be allocated and directly linked to various PT functions, including status control areas, status notification areas, touch switches, lamps, memory tables, and other objects.				
	Peripheral Bus		Bus for communications with various kinds of Support Software running on a personal computer. High-speed communications are supported.				
	Serial Gateway		This gateway enables receiving and automatically converting FINS to the CompoWay/F.				
	Serial PLC Link	s	Data is exchanged between CPU Units using serial ports without communications programming. PTs set to the 1:N NT Link protocol can be included in the network.				
	EtherNet/IP Port *	13	100Base-TX/10Base-T Protocols: TCP/IP, UDP, ARP, ICMP (ping only), BOOTP Applications: FINS, CIP, SNTP, DNS (Client), FTP (Server)				
	CIP	Tag Data Links	Programless cyclic data exchanges with the devices on the EtherNet/IP network.				
	Communications Service	Message Communications	Any CIP commands can be received from the devices on the EtherNet/IP network.				
	FINS Communications Service	Message Communications	Any FINS commands can be transferred with the devices on the EtherNet/IP network.				
	Scheduled Interrup	ots	Tasks can be executed at a specified interval (minimum of 0.2 ms, Unit: 0.1 ms).				
	Resetting and r	restarting with MSKS(690)	When MSKS(690) is executed, the internal timer is restarted and the time to first interrupt is set to a fixed value.				
Interrupt	Reading preser MSKS(690)	nt value of internal timer with	MSKS(690) can be used to read the time that has elapsed until the schedule interrupt is started or since the previous scheduled interrupt.				
	Power OFF Interru	pts	A task can be executed when CPU Unit's power turns OFF.				
	I/O Interrupt Tasks	;	A task can be executed when an input signal is input to an Interrupt Input Unit.				
	External Interrupt	Tasks	A task can be executed when interrupts are requested from a Special I/O Unit or a CPU Bus Unit.				
	Clock Function		Clock data is stored in memory. Accuracy (Accuracy depends on the temperature.) Ambient temperature of $55^{\circ}C$: -3.5 to +0.5 min error per month Ambient temperature of $25^{\circ}C$: -1.5 to +1.5 min error per month Ambient temperature of $0^{\circ}C$: -3 to +1 min error per month				
	Operation Start Tir	me Storage	The time when operating mode was last changed to RUN mode or MONITOR mode is stored.				
Clock	Operation Stop Tin	ne Storage	The last time a fatal error occurred or the last time the operating mode was changed to PROGRAM mode is stored.				
	Startup Time Stora	age	The time when the power was turned ON is stored.				
	Power Interruption	Time Storage	The time when the power is turned OFF is stored.				
	Total Power ON Til	me Calculation	The total time that the PLC has been ON is stored in increments of 10 hours.				
	Power ON Clock D	ata Storage	A history of the times when the power was turned ON is stored.				
	User Program Ove	rwritten Time Storage	The time that the user program was last overwritten is stored.				
	Parameter Date St	orage	The time when the Parameter Area was overwritten is stored.				
	Memory Protection Power OFF Detection Time Setting		Holding Area data, DM Area data, EM Area data, Counter Completion Flags, and counter present values are held even when power is turned OFF. CIO Area, Work Area, some Auxiliary Area data, and Timer Completion Flags, timer present values, index registers, and data registers can be protected by turning ON the IOM Hold Bit in the Auxiliary Area, and by also setting the IOM Hold Bit to "Hold" in the PLC Setup.				
Power Supply Management			The detection time for power interruptions can be set. AC power supply: 10 to 25 ms (variable) DC power supply: 2 to 5 ms (CJ1W-PD022) or 2 to 20 ms (CJ1W-PD025)				
	Power OFF Detecti	ion Delay Time	The detection of power interruptions can be delayed: 0 to 10 ms (Not supported by the CJ1W-PD022.)				

***12.** A Serial Option Board is required to use a serial port for the CJ2M-CPU3□ CJ2M CPU Unit. ***13.** Supported only by the CJ2M-CPU3□.

	Funct	ion	Description
Function Blog			Standard programming can be encapsulated as function blocks.
	Languages in Fun	ction Block Definitions	Ladder programming or structured text
	Online Editing		The program can be changed during operation (in MONITOR or PROGRAM mode), except for block programming areas.
	Force-Set/Reset		Specified bits can be set or reset. Force-set/reset to the EM Area is enabled by specifying a start bank in parameter setting.
	Differentiate Monit	oring	ON/OFF changes in specified bits can be monitored.
Debugging	Data Tracing		The specified I/O memory data can be stored in the trace memory in the CPU Unit. The triggers can be set.
Debugging	Continuous Tra	acing	The trace data can be uploaded during data tracing using CX-Programmer, which enables continuously logging the data by constantly uploading the trace data.
	Automatically s starts	starting tracing when operation	Data tracing can be automatically started when operation is started (i.e., when the operating mode is changed from PROGRAM mode to MONITOR or RUN mode).
	Storing Location of	f Error when an Error Occurs	The location and task number where execution stopped for a program error is recorded.
	Program Check		The programs can be checked for items such as no END instruction and FALS/FAL errors at startup.
	Error Log		A function is provided to store predefined error codes in CPU Unit, error information, and time at which the error occurred.
	CPU Error Detection	on	CPU Unit WDT errors are detected.
	User-defined Failu	re Diagnosis	Errors can be generated for user-specified conditions: Non-fatal errors (FAL) and fatal errors (FALS). (FALS). Program section time diagnosis and program section logic diagnosis are supported (FPD
			instruction).
	Load OFF Function	n	This function turns OFF all outputs from Output Units when an error occurs.
	RUN Output		The RUN output from the CJ1W-PA205R turns ON while CPU Unit is in RUN mode or MONITOR mode.
	Basic I/O Load She	ort-circuit Detection	This function provides alarm information from Basic I/O Units that have load short-circuit protection.
	Failure Point Deter	ction	The time and logic of an instruction block can be analyzes using the FPD instruction.
	CPU Standby Dete	ction	This function indicates when the CPU Unit is on standby because all Special I/O Units and CPU Bus Units have not been recognized at the startup in RUN or MONITOR mode.
		System FAL Error Detection (User-defined non-fatal error)	This function generates a non-fatal (FAL) error when the user-defined conditions are met in program.
		Duplicate Refreshing Error Detection	This function detects an error when an immediate refreshing Instruction in an interrupt task is competing with I/O refreshing of a cyclic task.
		Basic I/O Unit Error Detection	This function detects the errors in Basic I/O Units.
0.17		Backup Memory Error Detection	This function detects errors in the memory backup of the user programs and parameter area (backup memory).
Self- diagnosis		PLC Setup Error Detection	This function detects setting errors in the PLC Setup.
and Restoration	Non-fatal Error	CPU Bus Unit Error Detection	This function detects an error when there is an error in data exchange between the CPU Unit and a CPU Bus Unit.
	Detection	Special I/O Unit Error Detection	This function detects an error when there is an error in data exchange between the CPU Unit and a Special I/O Unit.
		Tag Memory Error Detection *14	This function detects errors in tag memory.
		Battery Error Detection	This function detects an error when a battery is not connected to the CPU Unit or when the battery voltage drops.
		CPU Bus Unit Setting Error Detection	This function detects an error when the model of a CPU Bus Unit in the registered I/O tables does not agree with the model that is actually mounted in the PLC.
		Special I/O Unit Setting Error Detection	This function detects an error when the model of a Special I/O Unit in the registered I/O tables does not agree with the model of Unit that is actually mounted.
		Option Board Error Detection *14	This function detects the errors in Serial Option Board mounting status.
		Memory Error Detection	This function detects errors that occur in memory of the CPU Unit.
		I/O Bus Error Detection	This function detects when an error occurs in data transfers between the Units mounted in Rack slots and the CPU Unit and detects when the End Cover is not connected to the CPU Rack or an Expansion Rack.
	Fatal Error Detection	Unit/Rack Number Duplication Error	This function detects an error when the same unit number is set for two or more Units, the same word is allocated to two or more Basic I/O Units, or the same rack number is set for two or more Racks.
		Too Many I/O Points Error Detection	This function detects an error when the total number of I/O points set in the I/O tables or the number of Units per Rack exceeds the specified range.
		I/O Setting Error Detection	This function detects an error when the number of Units in the registered I/O tables does not agree with the actual number of Units that is mounted, or an Interrupt Unit has been connected

∗14.Supported only by the CJ2M-CPU3□.


Function					Description			
					This function detects errors in programs.			
			Instruction P Error Detection		This function detects an error when the given data value is invalid when executing an instruction, or execution of instruction between tasks was attempted.			
			Indirect DM/EM BCD Error Detection Illegal Area Access Error Detection		This function detects an error when an indirect DM/EM address in BCD mode is not BCD.			
					This function detects an error when an attempt is made to access an illegal area with an instruction operand.			
			No END Erro	r Detection	This function detects an error when there is no END instruction at the end of the program.			
0.17	Fatal Error Detection		Task Error D	etection	This function detects an error when there are no tasks that can be executed in a cycle, there is no program for a task, or the execution condition for an interrupt task was met but there is no interrupt task with the specified number.			
Self- diagnosis and			Differentiation Error Detection		This function detects an error when too many differentiated instructions are entered or deleted during online editing (131,072 times or more).			
Restoration			Invalid Instru Detection	ction Error	This function detects an error when an attempt is made to execute an instruction that is not defined in the system.			
		User Program Area Overflow Error Detection			This function detects an error when instruction data is stored after the last address in user program area.			
		-	cle Time Exce tection	eded Error	This function monitors the cycle time (10 to $40,000 \text{ ms}$) and stops the operation when the se value is exceeded.			
	Fatal Error		stem FALS Er ser-defined Fa		This function generates a fatal (FALS) error when the user-defined conditions are met in program.			
	Detection (Continued from	Ve	rsion Error De	etection	This function detects an error when a user program includes a function that is not supported by the current unit version.			
	previous page)		mory Card Tr tection	ansfer Error	This function detects an error when the automatic file transfer from Memory Card fails at startup.			
	Simple Backup Fu	nction			This function collectively backs up the data in CPU Unit (user programs, parameters, and I/O memory) and internal backup data in the I/O Units.			
	Unsolicited Comm	unic	ations		A function that allows the PLC to use Network Communications Instruction to send required FINS commands to a computer connected via a Host Link			
Maintenance	Remote Programm	note Programming and Monitoring			Host Link communications can be used for remote programming and remote monitoring through a Controller Link, Ethernet, DeviceNet, or SYSMAC LINK Network. Communications across network layers can be performed. Controller Link or Ethernet : 8 layers DeviceNet or SYSMAC LINK : 3 layers			
	Automatic Online (Coni	nection via	Direct Serial Connection	This function enables automatically connecting to the PLC online when the CX-Programmer is directly connected by a serial connection (peripheral (USB) port or serial port).			
	Network			Via Networks	This function enables connecting the CX-Programmer online to a PLC that is connected via an EtherNet/IP network.			
	Read Protection us	sing	Password		This function protects reading and displaying programs and tasks using passwords. Write protection: Set using the DIP switch. Read protection: Set a password using the CX-Programmer.			
Socurity	FINS Write Protect	ion			This function prohibits writing by using FINS commands sent over the network.			
Security	Unit Name Functio	n			This function allows the users to give any names to the Units. Names are verified at online connection to prevent wrong connection			
	Hardware ID Using	Lot	Numbers		This function sets operation protection by identifying hardware using the user programs according to lot numbers stored in the Auxiliary Area.			


Specifications for Pulse I/O Functions

The following functions of CJ2M can be used by installing one or two Pulse I/O Modules. Each module has 10 high-speed inputs and 6 high-speed outputs. Pulse I/O Modules can be installed on CJ2M CPU Units with Unit Version 2.0 or Later.

- The inputs can be used as general-purpose inputs, interrupt inputs, quick-response inputs, high-speed counters, or origin search inputs.
- The outputs can be used as general-purpose outputs, pulse outputs, origin search outputs, or PWM outputs.

One Pulse I/O Module can be mounted





Performance Specifications

	Item	Description
	Model of Pulse I/O Modules	CJ2M-MD211 (Sinking-type) CJ2M-MD212 (Sourcing-type)
	External Interface	40-pin MIL connector
	Pulse Inputs	Can be used as normal inputs, interrupt inputs, quick-response inputs, or high-speed counter inputs. (Function of each input must be selected in the PLC Setup.) Input method: Line-driver input or 24-VDC input (selected by wiring)
	Normal Inputs	20 max. (10 per Pulse I/O Module) Input constants: Set in the PLC Setup (0, 0.5, 1, 2, 4, 8, 16, or 32 ms). Default: 8 ms
	Interrupt Inputs and Quick-response Inputs	8 max. (4 per Pulse I/O Module) Input signal minimum ON pulse width: 30 μs
Pulse I/O	High-speed Counter Inputs	4 max. (2 per Pulse I/O Module) Input method: Differential-phase (×4) pulses, pulse + direction, up/down pulses, or increment pulse Maximum response frequency: 50 kHz for differential phases or 100 kHz for single phase Counting mode: Linear mode or circular (ring) mode Count value: 32 bits Counter reset: Phase Z + software reset or software reset Control method: Target-value comparison or range comparison Gate function: Supported
	Pulse Outputs	Can be used as normal outputs, pulse outputs, or PWM outputs. (Function of each output must be selected in the PLC Setup.) Output method: Sinking or sourcing transistor outputs (The method is determined by Pulse I/O Module model.)
	Normal Outputs	12 max. (6 per Pulse I/O Module)
	Pulse Outputs	4 max. (2 per Pulse I/O Module) Output method: CW/CCW or pulse + direction (The method is determined by the I/O wiring and the instructions used in the ladder program.) Output frequency: 1 pps to 100 kpps (in increments of 1 pps) Output Mode: Continuous mode (for speed control) or independent mode (for position control) Output pulses: Relative coordinates: 0000 0000 to 7FFF FFFF hex (0 to 2,147,483,647 pulses) Absolute coordinates: 8000 0000 to 7FFF FFFF hex (-2,147,483,648 to 2,147,483,647) Acceleration/deceleration curves: Linear or S-curve Origin search function: Supported
	PWM Outputs	4 max. (2 per Pulse I/O Module) Output frequency: 0.1 to 6,553.5 Hz (in 0.1-Hz increments) or 1 to 32,800 Hz (in 1-Hz increments) Duty ratio: 0.0% to 100.0% (in 0.1% increments)

Function Specifications

	Func	tions	Description				
		Normal Inputs	Input signals are read during I/O refreshing and stored in I/O memory.				
	Pulse Input	Interrupt Inputs	An interrupt task can be started when an input signal turns ON or turns OFF.				
	Functions	Quick-response Inputs	Input signals that are shorter than the cycle time are read and stored in I/O memory.				
		High-speed Counter Inputs	High-speed pulse signals are counted. Interrupt tasks can also be started.				
Pulse I/O	Pulse	Normal Outputs	The status of I/O memory is output during I/O refreshing.				
Functions	Output	Pulse Outputs	A pulse signal is output with the specified frequency and number of pulses at a fixed duty ratio (50%).				
	Functions	PWM Outputs	A pulse signal is output at the specified duty ratio.				
	Origin Searc	hes	The origin point of the machine is determined according to the specified origin search parameters while actually outputting pulses and using the origin and origin proximity input signals as conditions. (Pulse inputs and outputs are also used for this function.)				
	Input Interru	pt Function	A task is started for an interrupt input from a Pulse I/O Module or for a high-speed counter input.				
Interrupt	Interrupt		Interrupt tasks are executed when the interrupt input turns ON or turns OFF. Direct Mode: An interrupt task is executed each time an input signal changes. Counter Mode: Changes in the input signal are counted up or down and the interrupt task is executed when the counter counts out. (The maximum response frequency is 3 kHz.)				
	High-speed	d Counter Interrupts	An interrupt task is executed when preset comparison conditions for a high-speed counter are met. Target-value comparison: The interrupt task is executed when the count matches a specified value. Range comparison: The interrupt task is executed when the count enters or leaves a specified range of values.				

Allocating Functions I/O signals Pulse I/O Module 0 (on the right)

Ter	minal s	symbol	IN 00	IN 01	IN 02	IN 03	IN 04	IN 05	IN 06	IN 07	IN 08	IN 09	OUT 00	OUT 01	OUT 02	OUT0 3	OUT 04	OUT 05
Addres	s		2960										2961					
Bit			0	1	2	3	4	5	6	7	8	9	0	1	2	3	4	5
	Norma	al inputs	Normal input 0	Normal input 1	Normal input 2	Normal input 3	Normal input 4	Normal input 5	Normal input 6	Normal input 7	Normal input 8	Normal input 9						
	(Direc	upt inputs t Mode/ ter Mode)	Interrupt input 0	Interrupt input 1	Interrupt input 2	Interrupt input 3												
Inputs	Quick inputs	response	Quick response input 0	Quick response input 1	Quick response input 2	Quick response input 3												
	High-s count				Highspeed counter 1 (phase- Z/ reset)	Highspeed counter 0 (phase- Z/ reset)			High- speed counter 1 (phase-A, increment, or count input)	High- speed counter 1 (phase-B, decrement, or direction input)	High- speed counter 0 (phase-A, increment, or count input)	High- speed counter 0 (phase-B, decrement, or direction input)						
	Norma	al outputs											Normal output 0	Normal output 1	Normal output 2	Normal output 3	Normal output 4	Normal output 5
		CW/CCW outputs											Pulse output 0 (CW)	Pulse output 0 (CCW)	Pulse output 1 (CW)	Pulse output 1 (CCW)		
Out puts	Pulse out puts	Pulse + direction outputs											Pulse output 0 pulse)	Pulse output 1 (pulse)	Pulse output 0 (direction)	Pulse output 1 (direction)		
	puto	Variable duty ratio outputs															PWM output 0	PWM output 1
Origin	search		Origin search 0 (Origin Input Signal)	Origin search 0 (Origin Proximity Input Signal)	Origin search 1 (Origin Input Signal)	Origin search 1 (Origin Proximity Input Signal)	Origin search 0 (Positio ning Complet ed Signal)	Origin search 1 (Positio ning Complet ed Signal)									Pulse output 0 error counter reset output (operatio n modes 1 and 2)	Pulse output 1 error counter reset output (operatio n modes 1 and 2)

Pulse I/O Module 1 (on the left)

Ter	minal s	symbol	IN 10	IN 11	IN 12	IN 13	IN 14	IN 15	IN 16	IN 17	IN 18	IN 19	OUT 10	OUT 11	OUT 12	OUT 13	OUT 14	OUT 15
Addres	s		2962										2963					
Bit			0	1	2	3	4	5	6	7	8	9	0	1	2	3	4	5
	Norma	al inputs	Normal input 10	Normal input 11	Normal input 12	Normal input 13	Normal input 14	Normal input 15	Normal input 16	Normal input 17	Normal input 18	Normal input 19						
	(Direc	upt inputs t Mode/ ter Mode)	Interrupt input 4	Interrupt input 5	Interrupt input 6	Interrupt input 7												
Inputs	Quick inputs	response	Quick response input 4	Quick response input 5	Quick response input 6	Quick response input 7												
	High-s				Highspeed counter 3 (phase- Z/ reset)	Highspeed counter 2 (phase- Z/ reset)			High- speed counter 3 (phase-A, increment, or count input)	High- speed counter 3 (phase-B, decrement, or direction input)	High- speed counter 2 (phase-A, increment, or count input)	High- speed counter 2 (phase-B, decrement, or direction input)						
	Norma	al outputs											Normal output 6	Normal output 7	Normal output 8	Normal output 9	Normal output 10	Normal output 11
		CW/CCW outputs											Pulse output 2 (CW)	Pulse output 2 (CCW)	Pulse output 3 (CW)	Pulse output 3 (CCW)		
Out puts	Pulse out puts	Pulse + direction outputs											Pulse output 2 pulse)	Pulse output 3 (pulse)	Pulse output 2 (direction)	Pulse output 3 (direction)		
	puto	Variable duty ratio outputs															PWM output 2	PWM output 3
Origin	search		Origin search 2 (Origin Input Signal)	Origin search 2 (Origin Proximity Input Signal)	Origin search 3 (Origin Input Signal)	Origin search 3 (Origin Proximity Input Signal)	Origin search2 (Positio ning Complet ed Signal)	Origin search 3 (Positio ning Complet ed Signal)									Pulse output 2 error counter reset output (operatio n modes 1 and 2)	Pulse output 3 error counter reset output (operatio n modes 1 and 2)

Specifications of Pulse Input Functions Interrupt Inputs

Item	Direct Mode	Counter Mode
Number of interrupt inputs	Max. 8 inputs	
Allocated bit	CIO 2960 and CIO 2962, bits 00 to 03	
Interrupt detection method	ON-to-OFF or OFF-to-ON transitions	
Interrupt task numbers	140 to 147 (fixed)	
Counting method		Incrimenting or decrementing (Set with the MSKS(690) instruction.)
Counting range		0001 to FFFF hex (16 bits) (Set in A532 to A535 and A544 to A547.)
Response frequency		Single-phase: 3 kHz x 8 inputs
Storage locations for PVs for interrupt inputs in Counter Mode		A536 to A539 and A548 to A551

Quick-response inputs

Quien respense inpute	
Item	Specifications
Number of Quick-response inputs	Max. 8 inputs
Quick-response inputs	Signals that are shorter than the cycle time are latched for one PLC cycle, so they can be detected in the PLC program. Minimum detectable pulse width is 30 μs.

High-speed Counter Inputs

	Item	Description								
Number of High-	speed Counter Inputs	Max. 4 inputs								
Pulse input meth	od (counting mode)	Incremental pulse inputs	Pulse + direction inputs							
		Increment pulse	ncrement pulse Phase A Up pulse Pulse							
Input signals			Phase B Down pulse Direction							
			Phase Z	Reset	Reset					
Frequency and n counters	umber of high-speed	100 kHz, 2 inputs \times 2 I/O Modules	50 kHz, 2 inputs × 2 I/O Modules	100 kHz, 2 inputs × 2 I/O Modules	100 kHz, 2 inputs × 2 I/O Modules					
Counting mode		Linear mode or ring mode								
Count value		Linear mode:	Linear mode: 8000 0000 to 7FFF FFFF hex 0000 0000 to FFFF FFFF hex (for increment pulse)							
		Ring mode: 0000 0000 to Max. ring value								
High-speed cour	ter PV storage locations	High-speed counter 0: A271 (upper 4 digits) and A270 (lower 4 digits) High-speed counter 1: A273 (upper 4 digits) and A272 (lower 4 digits) High-speed counter 2: A317 (upper 4 digits) and A316 (lower 4 digits) High-speed counter 3: A319 (upper 4 digits) and A318 (lower 4 digits) Refreshed during overseeing processing. Use PRV(881) to read the most recent PVs.								
0	Ŭ	Data format: 8 digit hexadecimal • Linear mode: 8000 0000 to 7FFF FFFF hex 0000 0000 to FFFF FFFF hex (for increment pulse)								
		Ring mode:	0000 0000 to Ma	5						
	Target value comparison	Up to 48 target values and corresponding interrupt task numbers can be registered.								
Control method	Range Comparison	Up to 8 or up to 32 ranges can be registered, with a separate upper limit, lower limit, and interrupt task number for each range.								
Counter reset method		 Software reset The counter is reset whe 	t n the phase-Z input goes ON w n the Reset Bit (A531.00 to A53 top or continue the comparisor	31.03) is turned ON.	,					

Specifications of Pulse Output Functions Position Control and Speed Control

Item	Specifications
Number of Pulse Outputs	Max. 4 outputs (Pulse Output 00 to 03)
Output mode	Continuous mode (for speed control) or independent mode (for position control)
Positioning (independent mode) instructions	PULS (886) and SPED (885), PULS (886) and ACC (888), or PULS2 (887) instruction
Speed control (continuous mode) instructions	SPED (885) and ACC (888) instructions
Origin (origin search and origin return) instructions	ORG (889) instruction
Interrupt feeding instruction	IFEED (892) instruction
Output frequency	1 pps to 100 kpps (1 pps units), two pulse outputs × 2 Pulse I/O Modules
Frequency acceleration and deceleration rates	Set in increments of 1 pps for acceleration/deceleration rates from 1 to 65,535 pps (every 4 ms). The acceleration and deceleration rates can be set independently only with the PLS2 (887) instruction.
Changing SVs during instruction execution	The target frequency, acceleration/deceleration rate, and target position can be changed.
Pulse output method	CW/CCW or pulse + direction
Number of output pulses	Relative coordinates: 0000 0000 to 7FFF FFFF hex (Accelerating or decelerating in either direction: 2,147,483,647) Absolute coordinates: 8000 0000 to 7FFF FFFF hex (-2,147,483,648 to 2,147,483,647)
Relative/absolute coordinate specifications for pulse output PVs	Absolute coordinates are specified automatically when the origin location has been defined by changing the pulse output PV with the INI (880) instruction or performing an origin search with the ORG(889) instruction. Relative coordinates must be used when the origin is undefined.
Relative pulse/absolute pulse specifications	The pulse type can be specified with an operand in the PULS (886) or PLS2 (887) instruction. Absolute pulses can be used when absolute coordinates are specified for the pulse output PV, i.e. the origin location has been defined. Absolute pulse cannot be used when relative coordinates are specified, i.e., when the origin location is undefined. An instruction error will occur.
Pulse output PV's storage location	The following Auxiliary Area words contain the pulse output PVs Pulse output 0: A277 (leftmost 4 digits) and A276 (rightmost 4 digits) Pulse output 1: A279 (leftmost 4 digits) and A278 (rightmost 4 digits) Pulse output 2: A323 (leftmost 4 digits) and A322 (rightmost 4 digits) Pulse output 3: A325 (leftmost 4 digits) and A324 (rightmost 4 digits) The PVs are refreshed during regular I/O refreshing.


Variable-duty Pulse Outputs (PWM)

ltem	Specifications
Number of PWM Outputs	Max. 4 outputs (PWM Output 00 to 03)
Duty ratio	0.0% to 100.0% in 0.1% increments
Frequency	0.1 Hz to 6,553.5 Hz (Set in 0.1-Hz increments.) 1 Hz to 32,800 Hz (Set in 1-Hz increments.)
Output mode	Continuous Mode
Instruction	PWM (891) instruction

Specifications of Pulse I/O Modules Input Specifications (IN00 to IN09/IN10 to IN19) Normal Inputs

Inputs	IN00 to IN05 and IN10 to IN15	IN06 to IN09 and IN16 to IN19	IN00 to IN05 and IN10 to IN15	IN06 to IN09 and IN16 to IN19				
Input form	24 VDC inputs		Line driver inputs					
Input current	6.0 mA typical	5.5 mA typical	13 mA typical	10 mA typical				
Input voltage range	24 VDC +10%/-15%		RS-422A or RS-422 line driver (conforming to AM26LS31), Power supply voltage of 5 V \pm 5%					
Input impedance	3.6 kΩ	4.0 kΩ						
Number of circuits	1 common, 1 circuit	L.						
ON voltage/current	17.4 VDC min., 3 mA min.							
OFF voltage/current	/current 1 mA max. at 5 VDC max							
ON response time	8 ms max. (The input time	8 ms max. (The input time constant can be set to 0, 0.5, 1, 2, 4, 8, 16, or 32 ms in the PLC Setup.)						
OFF response time	8 ms max. (The input time constant can be set to 0, 0.5, 1, 2, 4, 8, 16, or 32 ms in the PLC Setup.)							

Input Circuit Configuration



Interrupt Input and Quick-response Input Specifications (IN00 to IN03 and IN10 to IN13)


Item	Specifications		
ON response time	30 μs max.		
OFF response time	150 μs max.		
Response pulse	ON		

High-speed Counter	r Input Specifications (IN06 to IN09 and IN16 to IN1	19)
	24-VDC input	Line driver input
Set to 60 kHz	Phase-A/Phase-B encoder input, Single-phase 60-kHz pulse input with 50% duty ratio Rise time and fall time: 3.0 μs max.	Encoder input phase A or B, single-phase 60-kHz pulse input with 50% duty ratio
Set to 100 kHz	Phase-A/Phase-B encoder input, Single-phase 100-kHz pulse input with 50% duty ratio Rise time and fall time: 2.5 μs max.	Single-phase 100-kHz pulse input with 50% duty ratio $10.0 \ \mu s \ min.$ $5.0 \ \mu s \ min.$ 0N 50% OFF Differential-phase 50-kHz pulse input Changes in phases A and B must be separated by at least 2.5 \ \mu. $20.0 \ \mu s \ min.$ ON 50% OFF OFF OFF OFF OFF OFF OFF OFF OFF OFF OFF OFF OFF T1 T2 T3 T4 $T1, T2, T3, T4: 2.5 \ \mu s \ min.$
Phase Z/reset input	Encoder input phase Z (IN02/IN03 or IN12/IN13) Maintain an ON time of 30 μs min. and an OFF time of 150 μs min. ON 50% OFF	Constant of the set of

Output Specifications (OUT00 to OUT05 and OUT10 to OUT15)

Item	Specifications		
Output Specifications	Sinking-type (CJ2M-MD211) Sourcing-type (CJ2M-MD212)		
Rated voltage	5 to 24 VDC		
Allowable voltage range	4.75 to 26.4 VDC		
Maximum switching current	0.3 A/output, 1.8 A/Unit		
Number of circuits	6 outputs (6 outputs/common)		
Maximum inrush current	3.0 A/output, 10 ms max. 2.0 A/output, 10 ms max.		
Leakage current	0.1 mA max.		
Residual voltage	0.6 V max.		
ON response time	0.1 ms max.		
OFF response time	0.1 ms max.		
Fuse	None		
External supply power (power supply input for outputs)	10.2 to 26.4 VDC, 20 mA min.		
Circuit configuration	Stinolo Isolation circuit Rated voltage circuit COM COM Com Com Com Com Com Com Com Com		

Pulse Outputs (OUT00 to OUT03 and OUT10 to OUT13)



PWM Outputs (OUT04, OUT05, OUT14, and OUT15)

Item	Specifications		
Output Specifications	Sinking-type (CJ2M-MD211)	Sourcing-type (CJ2M-MD212)	
Rated voltage	5 to 24 VDC		
Allowable voltage range	4.75 to 26.4 VDC		
Maximum switching capacity	6.5535 kHz or less: 300 mA, 6.5535 to 32.8 kHz: 100 mA		
Maximum output frequency	32,800 Hz		
PWM output accuracy (for ON pulse width of 2 μs or longer)	ON duty at 6.5535 kHz or less: -0.2% to +1%, ON duty at 32.8 kHz: -1% to +5% (at switching current of 30 mA)	ON duty at 6.5535 kHz or less: ±0.5%, ON duty at 32.8 kHz: +2.5% (at switching current of 30 mA)	
Output waveform	OFF 50% ON t_{ON}	ON 50% OFF T ON duty = $\frac{t_{ON}}{T}$ X 100%	

Unit Versions

Units	Models	Unit version
	CJ2M-CPU3	CPU: Unit version 1.0 (Built-in EtherNet/IP section: Unit version 2.0)
		CPU: Unit version 2.0 (Built-in EtherNet/IP section: Unit version 2.0)
CJ2M CPU Units		CPU: Unit version 2.0 (Built-in EtherNet/IP section: Unit version 2.1)
	CJ2M-CPU1□	CPU: Unit version 1.0
		CPU: Unit version 2.0

Function Support by Unit Version

Functions Supported for Unit Version 2.0 or Later

The following tables show the relationship between unit versions and CX-Programmer versions.

CPU Unit	CJ2M CPU Unit		
Model	CJ2M-CPU		
Unit Version Function	Unit version 2.0 or higher	Unit version 1.0	
	ОК	-	

A Pulse I/O Module must be mounted for CJ2M CPU Units with unit version 2.0 or later.

Unit Versions and Programming Devices

The following tables show the relationship between unit versions and CX-Programmer versions.

Unit Versions and Programming Devices

		Required Programming Device				
CPU Unit	Functions		CX-Programmer			Programming
			Ver. 9.0 or lower	Ver. 9.1 or higher	Ver. 9.12 or higher	Console
CJ2M-CPU	Functions for unit version 1.0		_	OK *1	ОК	
CJ2M-CPU Unit version 2.0		Using new functions	-	-	OK	- *3
		_	OK *2	ОК		

***1.** CX-Programmer version 9.1 or higher is required to use CJ2M CPU Units.

*2. It is not necessary to upgrade the version of the CX-Programmer if functionality that was enhanced for the upgrade of the CPU Unit will not be used.

***3.** A Programming Console cannot be used with a CJ2M CPU Unit.

Device Type Setting

The unit version does not affect the setting made for the device type on the CX-Programmer. Select the device type as shown in the following table regardless of the unit version of the CPU Unit.

Series	CPU Unit group	CPU Unit model	Device type setting on CX-Programmer Ver. 9.1 or higher
CJ Series	CJ2M CPU Units	CJ2M-CPU3□ CJ2M-CPU1□	CJ2M


External Interface

CJ2M-CPU3 (CJ2M with Built-in EtherNet/IP)

A CJ2M-CPU3 provides two communications ports for external interfaces: a peripheral (USB) port and an EtherNet/IP port.


The Pulse I/O functions of the CJ2M can be used by mounting a Pulse I/O Module. Up to two Pulse I/O Modules can be connected to the left side of a CJ2M CPU Unit.

Serial ports can be added by mounting a Serial Communications Option Board (sold separately) in an option slot.



CJ2M-CPU1

A CJ2M-CPU1 provides two communications ports for external interfaces: a peripheral (USB) port and a serial port. The Pulse I/O of the CJ2M can be used by mounting a Pulse I/O Module. Up to two Pulse I/O Modules can be connected to the left side of a CJ2M CPU Unit.



Pulse I/O Module (2 units max.) CJ2M-MD21□

Peripheral (USB) Port

Item	Specification
Baud Rate	12 Mbps max.
Transmission Distance	5 m max.
Interface	USB 2.0-compliant B-type connector
Protocol	Peripheral Bus


EtherNet/IP Port

Item	Specification	
Media Access Method	CSMA/CD	
Modulation	Baseband	
Transmission Paths	Star	
Baud Rate 100 Mbps (100Base-TX)		
Transmission Media	Shielded twisted-pair (STP) cable; Categories: 5, 5e	
Transmission Distance	100 m (between ethernet switch and node)	
Number of Cascade Connections	No restrictions if ethernet switch is used.	
Communications	CIP Communications (tag data links, Explicit Messages). FINS communications	

Built-in Serial Port (Only CJ2M-CPU1)

Item	Specification
Communications method	Half duplex
Synchronization	Start-stop
Baud rate	0.3/0.6/1.2/2.4/4.8/9.6/19.2/38.4/57.6/115.2 kbps *
Transmission distance	15 m max.
Interface	EIA RS-232C
Protocol	Host Link, NT Link, 1:N, No-protocol, or Peripheral Bus

* Baud rates for the RS-232C are specified only up to 19.2 kbps. The CJ Series supports serial communications from 38.4 kbps to 115.2 kbps, but some computers cannot support these speeds. Lower the baud rate if necessary.



Pin No.	Signal	Name	Direction
1	FG	Protection earth	-
2	SD (TXD)	Send data	Output
3	RD (RXD)	Receive data	Input
4	RS (RTS)	Request to send	Output
5	CS (CTS)	Clear to send	Input
6	5 V	Power supply	-
7	DR (DSR)	Data set ready	Input
8	ER (DTR)	Data terminal ready	Output
9	SG (0 V)	Signal ground	-
Connector hood	FG	Protection earth	-

Note: Do not use the 5-V power from pin 6 of the RS-232C port for anything but CJ1W-CIF11 RS-422A Conversion Adapter, NT-AL001 RS-232C/ RS-422A Conversion Adapter and NV3W-M_20L(-V1) Programmable Terminal. The external device or the CPU Unit may be damaged.

Serial Option Board (Only CJ2M-CPU3) A Serial Option Board can be used with a CJ2M-CPU3 CJ2M CPU Unit.


Model Port Maximum transmission distance **Connection method** CP1W-CIF01 One RS-232C port Connector: D-sub, 9-pin female 15 m One RS-422A/485 port (not CP1W-CIF11 50 m Terminal block: Using ferrules isolated) CP1W-CIF12-V1 One RS-422A/485 port (isolated) 500 m Terminal block: Using ferrules

CP1W-CIF01 RS-232C Option Board

Front


Back

Communications Status Indicator



RS-232 Connector

•RS-232C Connector





Pin No.	Signal	Name	Direction
1	FG	Protection earth	-
2	SD (TXD)	Send data	Output
3	RD (RXD)	Receive data	Input
4	RS (RTS)	Request to send	Output
5	CS (CTS)	Clear to send	Input
6	5 V Po		-
7	DR (DSR)	Data set ready	Input
8	ER (DTR)	Data terminal ready	Output
9	SG (0 V)	Signal ground	-
Connector hood	FG	Protection earth	-

Note: Do not use the 5-V power from pin 6 of the RS-232C port for anything but CJ1W-CIF11 RS-422A Conversion Adapter, NT-AL001 RS-232C/ RS-422A Conversion Adapter and NV3W-M_20L(-V1) Programmable Terminal. The external device or the CPU Unit may be damaged.

CP1W-CIF11/CIF12-V1 RS-422A/485 Option Board

Front






Back

RS-422A/485 Connector

•RS-422A/485 Terminal Block



Connector Pin Allocations of Pulse I/O Module (40 pins)

Connector on Sinking-type I/O Module (CJ2M-MD211)

Pin layout	Terminal symbol	Input signal type	Pin	*	Terminal symbol	Input signal type	Pin	*
	IN00/IN10	24 VDC	1	A1	IN01/IN11	24 VDC	2	B1
		LD+	3	A2		LD+	4	B2
		0 V/LD-	5	A3		0 V/LD-	6	B3
		24 VDC	7	A4	IN03/IN13	24 VDC	8	B4
	IN02/IN12	LD+	9	A5		LD+	10	B5
		0 V/LD-	11	A6		0 V/LD-	12	B6
3 - 4 - 4		24 VDC	13	A7		24 VDC	14	B7
	IN04/IN14	LD+	15	A8	IN05/IN15	LD+	16	B8
		0 V/LD-	17	A9		0 V/LD-	18	B9
	IN06/IN16	24 VDC	19	A10	IN07/IN17	24 VDC	20	B10
$19 \xrightarrow{\circ} 20$ $21 \xrightarrow{\circ} 22$		LD+	21	A11		LD+	22	B11
$\begin{array}{c c c c c c c c c c c c c c c c c c c $		0 V/LD-	23	A12		0 V/LD-	24	B12
	IN08/IN18	24 VDC	25	A13	IN09/IN19	24 VDC	26	B13
$\begin{array}{c ccccccccccccccccccccccccccccccccccc$		LD+	27	A14		LD+	28	B14
35 36 $37 $ 38 38 $39 $ 40		0 V/LD-	29	A15		0 V/LD-	30	B15
39	OUT00/OUT10		31	A16	OUT01/OUT11		32	B16
	OUT02/OUT12		33	A17	OUT03/OUT13		34	B17
	OUT04/OUT14		35	A18	OUT05/OUT15		36	B18
	Power supply input +V for outputs		37	A19	Power supply input +V for outputs		38	B19
	COM		39	A20	COM		40	B20

* Terminals numbers on the XW2 (General-Purpose) Connector-Terminal Block Conversion Unit.

Sourcing-type I/O Module (CJ2M-MD212)

Pin layout	Terminal symbol	Input signal type	Pin	*	Terminal symbol	Input signal type	Pin	*
	IN00/IN10	24 VDC	1	A1		24 VDC	2	B1
		LD+	3	A2	IN01/IN11	LD+	4	B2
		0 V/LD-	5	A3		0 V/LD-	6	B3
		24 VDC	7	A4		24 VDC	8	B4
	IN02/IN12	LD+	9	A5	IN03/IN13	LD+	10	B5
1		0 V/LD-	11	A6		0 V/LD-	12	B6
3 - 4		24 VDC	13	A7		24 VDC	14	B7
7 — • • • • • 8 9 — • • • • • 10	IN04/IN14	LD+	15	A8	IN05/IN15	LD+	16	B8
		0 V/LD-	17	A9		0 V/LD-	18	В9
15 <u>16</u> 17 <u>18</u>	IN06/IN16	24 VDC	19	A10	IN07/IN17	24 VDC	20	B10
		LD+	21	A11		LD+	22	B11
23 - 24 - 24 - 26		0 V/LD-	23	A12		0 V/LD-	24	B12
$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	IN08/IN18	24 VDC	25	A13	IN09/IN19	24 VDC	26	B13
$31 \xrightarrow{31} 32$ $33 \xrightarrow{31} 32$		LD+	27	A14		LD+	28	B14
37		0 V/LD-	29	A15		0 V/LD-	30	B15
39 — +••+ 40	OUT00/OUT10		31	A16	OUT01/OUT11		32	B16
	OUT02/OUT12		33	A17	OUT03/OUT13		34	B17
	OUT04/OUT14		35	A18	OUT05/OUT15		36	B18
	COM		37	A19	СОМ		38	B19
	Power supply input –V for outputs		39	A20	Power supply input –V for outputs		40	B20

* Terminals numbers on the XW2 (General-Purpose) Connector-Terminal Block Conversion Unit.

Pulse I/O Module MIL connector Wiring Methods


To connect to a Terminal Block, use an OMRON Cable preassembled with the special connector or attach the special connector (sold separately) to a cable yourself.

Using User-made Cables with Connector

Connector Models

Compatible Connector Specifications


• MIL Flat Cable Connectors (40-pin Pressure-fitted Connectors)



Name	OMRON model number				
Socket	XG4M-4030				
Stain Relief	XG4M-4004				
Set model number	XG4M-4030-T				
Recommended Flat Cable	XY3A-200 *				
te Dreduct na langen available te anden					

* Product no longer available to order.

• MIL Loose Wire Crimp Connectors (40-pin Pressure-fitted Connectors)



	Name	OMRON model number
Socket	AWG24	XG5M-4032-N
SUCKEL	AWG26 to AWG28	XG5M-4035-N
Spare Contacts	AWG24	XG5W-0031-N
(See note 1.)	AWG26 to AWG28	XG5W-0034-N
Hood Cover (See note 2.)		XG5S-4022
Partial Cover (See note 2.) (2 required for each socket)		XG5S-2001

Note: 1. Contacts are included with the Socket.

2. Select either the Hood Cover or the Partial Cover.

Wiring


We recommend using a cable with wires sized between 28 and 24 AWG (0.2 to 0.08 mm²). Use a wire with an outer diameter of 1.61 mm max.

Compatible Terminal Blocks


Recommended Cable	Compatible Terminal Block	Wiring method	Number of terminals	Temperature (°C)
	XW2K-40G-T	Push-In Plus		-20 to 75
XW2Z-	XW2D-40G6	Phillips screw	40	0 to 55
	XW2R-E40GD-T	Slotted screw (rise up)		0 10 55

Using preassembled cables and terminal blocks.

Connection of Pulse I/O module to a General-purpose Terminal Block




Connection of Pulse I/O module to a Servo Drive Terminal Block




Dimensions

CJ2M-CPU3









CJ2M-CPU1









CJ2M-MD211/MD212







(Unit: mm)

Related Manuals

Cat. No.	Model	Manual	Application	Description
W472	CJ2H-CPU6□-EIP CJ2H-CPU6□ CJ2M-CPU□□	CJ-series CJ2 CPU Unit Hardware User's Manual	Hardware specifications for CJ2 CPU Units	Describes the following for CJ2 CPU Units: • Overview and features • Basic system configuration • Part nomenclature and functions • Mounting and setting procedure • Remedies for errors • Also refer to the <i>Software User's Manual</i> (W473).
W473	CJ2H-CPU6□-EIP CJ2H-CPU6□ CJ2M-CPU□□	CJ-series CJ2 CPU Unit Software User's Manual	Software specifications for CJ2 CPU Units	Describes the following for CJ2 CPU Units: • CPU Unit operation • Internal memory • Programming • Settings • Functions built into the CPU Unit Also refer to the <i>Hardware User's Manual</i> (W472)
W486	CJ2M-CPU + CJ2M-MD21	CJ-series CJ2M CPU Unit Pulse I/O Module User's Manual	Information on using Pulse I/O on CJ2M CPU Units	Provides the following information on the CJ2M CPU Units: • Specifications and wiring methods • I/O functions • Quick-response inputs • Interrupt functions • High-speed counters • Pulse outputs • PWM outputs When programming, use this manual together with the Instructions Reference Manual (Cat. No. W474).
W474	CJ2H-CPU6-EIP CJ2H-CPU6 CJ2M-CPU3 CS16/H-CPU-H CS16/H-CPU-H CJ16/H-CPU-H CJ16-CPU-H CJ16-CPU- CJ1M-CPU-HA CS1D-CPU-HA CS1D-CPU-H CS1D-CPU-S NSJ	CS/CJ/NSJ-series Instructions Reference Manual	Information on instructions	Describes each programming instruction in detail. Also refer to the <i>Software User's Manual</i> (W473) when you do programming.
W342	CJ2H-CPU6-EIP CJ2H-CPU6 CJ2M-CPU CS1G/H-CPU-H CS1D-CPUHA CS1D-CPUHA CS1D-CPUHA CS1D-CPUH CS1D-CPUH CS1D-CPUH CS1D-CPUH CS1W-SCU-V1 CJ1H-CPUH+R CJ1G-CPUH+R CJ1G-CPUH CJ1G-CPU CJ1M-CPU	CS/CJ/CP/NSJ-series Communications Command Reference Manual	Information on communications for CS/CJ/CP-series CPU Units and NSJ-series Controllers	Describes C-mode commands and FINS commands Refer to this manual for a detailed description of commands for communications with the CPU Unit using C mode commands or FINS commands. Note: This manual describes the communications commands that are addressed to CPU Units. The communications path that is used is not relevant and can include any of the following: serial ports on CPU Units, communications ports on Serial Communications Units/Boards, and Communications Units. For communications commands addressed to Special I/O Units or CPU Bus Units, refer to the operation manual for the related Unit.
W465	CJ2H-CPU6 CJ2M-CPU3 CS1W-EIP21 CJ1W-EIP21	CS and CJ Series EtherNet/IP Units CS1W-EIP21, CJ1W- EIP21, CJ2H-CPU6□- EIP, CJ2M-CPU3□ Operation Manual	Information for EtherNet/IP function of CJ2M built-in Ethernet port	Describes EtherNet/IP port/units. A basic setting, a tag data link, FINS communication, and other function are described.
W463	CXONE-AL D-V	CX-One Setup Manual	Installing software from the CX- One	Provides an overview of the CX-One FA Integrated Tool Package and describes the installation procedure.
W446		CX-Programmer		
W447	WS02-CXPC□-V□	Operation Manual CX-Programmer Operation Manual Functions Blocks/ Structured Text	Support Software for Windows computers CX-Programmer operating procedure	Describes operating procedures for the CX-Programmer. Also refer to the <i>Software User's Manual</i> (W473) and <i>Instructions Reference Manual</i> (W474) when you do programming.
W469		CX-Programmer Operation Manual SFC Programming	procedure	

Cat. No.	Model	Manual	Application	Description
W366	WS02-SIMC1-E	CS/CJ/CP/NSJ-series CX-Simulator Operation Manual	Operating procedures for CX- Simulator Simulation Support Software for Windows computers Using simulation in the CX- Programmer with CX- Programmer version 6.1 or higher	Describes the operating procedures for the CX-Simulator. When you do simulation, also refer to the CX-Programmer Operation Manual (W446), Software User's Manual (W473), and CS/CJ/NSJ series Instructions Reference Manual (W474).
W464	CXONE-AL D-V	CS/CJ/CP/NSJ-series CX-Integrator Network Configuration Software Operation Manual	Network setup and monitoring	Describes the operating procedures for the CX-Integrator.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company