# CJ-series EtherNet/IP Unit CJ1W-EIP21


- EtherNet/IP is an industrial multivendor network that uses Ethernet. Managed by the ODVA (Open DeviceNet Vendors Association), it has open standards and is used with a wide range of industrial devices.
- The EtherNet/IP Unit supports tag data links to enable sharing data between devices at Ethernet nodes and a message service for sending and receiving data when required.
- The EtherNet/IP Unit supports the same FINS/UDP and FINS/TCP functionality as Ethernet Units.



EtherNet/IP<sup>®</sup>

### Features

- Large-capacity tag data links are easily enabled by simply setting connections, with no programming required.
- Tag data links can be used to exchange data with up to 256 nodes over up to 256 connections.
- Up to 256 connections can be set per Unit with up to 722 words of data per connection, for a total of up to 184,832 words of link data. (There is no limit to the data link capacity for the overall network.)
- Data concurrency is maintained within each connection (for up to 722 words).
- Tag data link settings can be changed for individual Units even while tag data links are being used on a network.
- Errors can be diagnosed using the Network Configurator, and system errors can be monitored with a wide array of status flags.



### System Configuration

\* EtherNet/IP Unit with unit version 2.1 or later is required to connect C1JW-EIP21 to NJ-series CPU Unit. Use CPU Unit with version 1.01 or later and Sysmac Studio with version 1.02 or later.

### **Ordering Information**

#### International Standards

- The standards are abbreviated as follows: U: UL, U1: UL (Class I Division 2 Products for Hazardous Locations), C: CSA, UC: cULus, UC1: cULus (Class I Division 2 Products for Hazardous Locations), CU: cUL, N: NK, L: Lloyd, and CE: EC Directives.
- Contact your OMRON representative for further details and applicable conditions for these standards.
- Refer to the OMRON website (www.ia.omron.com) or ask your OMRON representative for the most recent applicable standards for each model.

#### **EtherNet/IP Unit**

Unit	Product	Specifications			No. of unit		rent ption (A)	Model	Standards
type	name	Communications cable	Communications functions	Units per CPU Unit	numbers allocated	5 V system	24 V system	Model	Standards
CJ1 CPU Bus Unit		Shielded twisted-pair (STP) cable Categories: 100 Ω at 5, 5e	Tag Data Link Functions, Message Communications Functions	8 max. *1	1	0.41	_	CJ1W-EIP21 *2	UC1, N, L, CE

\*1. Up to four EtherNet/IP Units can be connected to a NJ CPU Unit. Up to seven EtherNet/IP Units can be connected to a CJ2H-CPU6 - EIP. Up to two EtherNet/IP Units can be connected to a CJ2M CPU Unit.

\*2. EtherNet/IP Unit with unit version 2.1 or later is required to connect C1JW-EIP21 to NJ-series CPU Unit. Use CPU Unit with version 1.01 or later and Sysmac Studio with version 1.02 or later.

#### Industrial Switching Hubs

Product name	Appearance	Functions	No. of ports	Accessories	Current consumption (A)	Model
Industrial Switching Hubs		Quality of Service (QoS): EtherNet/IP control data priority 10/100BASE-TX, Auto-Negotiation	5	Power supply connector	0.07	W4S1-05D

#### **Recommended Network Devices**

The following table shows the devices recommended for use with the EtherNet/IP.

Part	Manufacturer	Model number	Inquires				
	Phoenix Contact	FL SWITCH SFN 8TX (8 ports)	Phoenix Contact USA Customer Service				
Switching Hub	Contec USA, Inc.	SH8008(FIT)H (8 ports)	CONTEC USA Inc.				
	Cisco Systems, Inc.	WS-C2955T-12 (12 ports)	Cisco Systems, Inc. Main Corporate HQ				
Twisted-pair	100BASE-TX						
cable	EtherNet/IP compliant cable		-				
Connectors	STP Plug						
(Modular plug)	Panduit Corporation	MPS588	Panduit Corporation US Headquarters				
Boots	Tsuko Company	MK boot (IV) LB	Tsuko Company Japan Headquarters				

Note: 1. Always use a switching hub when using tag data links in the network.

2. If a repeater hub is used for EtherNet/IP tag data links (cyclic communications), the network's communications load will increase, data collisions will occur frequently, and stable communications will be impossible.

### **Mountable Racks**

	NJ system		CJ1 system		CP1H system	NSJ sy	NSJ system *1	
Model	CPU Rack	Expansion Rack	CPU Rack	Expansion Backplane	CP1H PLC	NSJ Controller	Expansion Backplane	
CJ1W-EIP21 4 Units (per CPU Unit)		8 Units (pe *	r CPU Unit) 3	2 Units *4	Not supported	8 Units		

\*1. Product no longer available to order.

\*2. therNet/IP Unit with unit version 2.1 or later is required to connect C1JW-EIP21 to NJ-series CPU Unit. Use CPU Unit with version 1.01 or later and Sysmac Studio with version 1.02 or later.

\*3. Up to seven EtherNet/IP Units can be connected to a CJ2H-CPU6 -EIP. Up to two EtherNet/IP Units can be connected to a CJ2M CPU Unit. \*4. A CP1W-EXT01 CJ Unit Adaptor is required.

Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products. Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. EtherNet/IP<sup>™</sup> and DeviceNet<sup>™</sup> are trademarks of the ODVA.

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

### **EtherNet/IP Units Specifications**

	Item	Specifications				
Model number		CJ1W-EIP21				
Туре		100Base-TX *1				
Applicable PLC	s	NJ-series, CJ (CJ1, CJ2) series, CP1H, and NSJ series PLCs.				
Unit classificat	ion	CJ-series CPU Bus Unit				
Mounting locat	ion	CPU Rack or Expansion Rack				
Number of Unit	ts that can be mounted	NJ-series System : 4 max. (including Expansion Racks) CJ series System and NSJ series System: 8 max. (including Expansion Racks) *2 CP1H System: 2 max.				
		25 words/Unit (one unit number's words)				
	Allocated CIO Area words (CPU Bus Unit words)	These words contain control bits and flags, the target node PLC's operating and error information, Unit status, communications status, registered/normal target node information, and FINS/TCP connection status.				
	Allocated DM Area words	100 words/Unit (one unit number's words)				
CPU Unit words used	(CPU Bus Unit words)	These words contain the IP address display/setting area.				
words used		Any usable data area words				
	User-set area	Target node PLC's operating and error information, and registered/normal target node information				
	CPU Bus Unit System Setup	Not used.				
Non-volatile mo Unit (See note.	emory within EtherNet/IP )	The following settings are stored in the EtherNet/IP Unit's non-volatile memory. <b>Note:</b> Unlike the regular Ethernet Units, the CPU Bus Unit Setup Area in the CPU Unit is not used for these settings. 1. Unit Setup (communications settings for the EtherNet/IP Unit, such as the IP address, DNS server settings, host name, baud rate, FINS/UDP settings, and FINS/TCP settings) 2. Tag data link settings (device parameters)				
	Media access method	CSMA/CD				
	Modulation method	Baseband				
	Transmission paths	Star form				
Transfer	Baud rate	100 Mbit/s (100Base-TX)				
specifications	Transmission media	Shielded twisted-pair (STP) cable Categories: 100 $\Omega$ at 5, 5e				
	Transmission distance	100 m (distance between hub and node)				
	Number of cascade connections	There is no limitation when a switching hub is used.				
Current consumption (Unit)		410 mA max. at 5 V DC				
Weight		94 g max.				
Dimensions		$31 \times 90 \times 65 \text{ mm} (W \times H \times D)$				
Other general s	specifications	Other specifications conform to the general specifications of the CJ-series.				
		100 Deap TV. Otherwise, 10 Deap T can be used but this is not recommended				

\*1. If tag data links are being used, use 100Base-TX. Otherwise, 10Base-T can be used, but this is not recommended.
\*2. Up to seven EtherNet/IP Units can be connected to a CJ2H-CPU6□-EIP. Up to two EtherNet/IP Units can be connected to a CJ2M CPU Unit.

### **Communications Specifications**

ltow				Specifications						
	Item		NJ	CJ2	CJ1					
		Number of connections	256							
		Packet interval (refresh cycle)		0.5 to 10,000 ms (in 0.5-ms units) Can be set independently for each connection. Data is refreshed over the network at the preset interval and does not depend on the number of nodes.)						
		Maximum allowed communications bandwidth per Unit	6,000 to 12,000 pps *1 *2	,000 to 12,000 pps *1 *2						
		Number of tag sets	256	56						
		Tag types	CIO Area, DM Area, EM Area, Holding	Area, Work Area, and network symbols	*3					
		Number of tags per connection (= 1 tag set)	8 (7 tags when the tag set contains the	7 tags when the tag set contains the controller status)						
		Maximum link data size per node	184,832 words							
	Tag data links (Cyclic	Maximum data size per connection *4		4 bytes (252 words) or 1444 bytes (722 words) *3 ata synchronicity is maintained within each connection.						
	communications)	Number of registrable tag sets	256 (1 connection = 1 tag set)							
CIP service		Maximum size of 1 tag set	722 words (The controller status uses 1 word when the tag set contains the PLC status.)							
		Maximum number of tags that can be refreshed per CPU Unit cycle *5	Output/Transmission (CPU to EtherNet Input/Reception (EtherNet/IP to CPU):	Output/Transmission (CPU to EtherNet/IP): 19 Input/Reception (EtherNet/IP to CPU): 20 *6						
		Data that can be refreshed per CPU Unit cycle *5	Output/Transmission (CPU to EtherNet/IP): 6,432 words Input/Reception (EtherNet/IP to CPU): 6,432 words	Output/Transmission (CPU to EtherNet/IP): 7,405 words Input/Reception (EtherNet/IP to CPU): 7,405 words						
		Changing tag data link parameters during operation	Supported *7		·					
		Multicast packet filter function *8	Supported							
		Class 3 (connected)	Number of connections: 128							
	Explicit	UCMM	Number of clients that can communicat							
	messaging *9	(unconnected)	Number of servers that can communica Supported	ate at one time: 32 max.						
		CIP routing *10	CJ1W-EIP21, CS1W-EIP21, NJ-501-	□□□, NJ-301-□□□□, CJ2H-CPU□□-E	IP, CJ2M-CPU3□					
FINS s	ervice	FINS/UDP FINS/TCP	Not supported Not supported	Supported 16 connections max.						
Ether	let/IP conforma		Conforms to A8	TO CONNECTIONS MAX.						
			10BASE-T or 100BASE-TX							
Etherr	Ethernet interface		Auto Negotiation or fixed settings							

\*1. In this case, pps means "packets per second" and indicates the number of packets that can be processed in one second.

\*2. When using the EtherNet/IP Unit with version 3.0 or later. When using the EtherNet/IP Unit with version 2.1 or earlier, the maximum allowed communications bandwidth per Unit is 6,000 pps. When using the EtherNet/IP Unit with version 3.0 or later, the Network Configurator with version 3.57 or higher is required.

\*3. Network symbols can be used only by the NJ501-

\*4. To use 505 to 1,444 bytes as the data size, the system must support the Large Forward Open standard (an optional CIP specification). The CS/CJ-series Units support this standard, but before connecting to nodes of other companies, confirm that those devices also support it.

\*5. If the maximum data size is exceeded, the data refreshing with the CPU Unit will extend over two or more cycles.

\*6. If status layout is selected in the user settings, the maximum number of tags that can be received is 19 tags.
\*7. If parameters are changed in the EtherNet/IP Unit, however, the EtherNet/IP Unit will be restarted. When other nodes are communicating with the affected node, the communications will temporarily time out and automatically recover later.

\*8. Because the EtherNet/IP Unit is equipped with an IGMP client, unnecessary multicast packets can be filtered by using a switching hub that supports IGMP snooping.

\*9. The EtherNet/IP Unit uses the TCP/UDP port numbers shown in the following table.

Service	Protocol		Po	Port number		Remarks		
Service	CJ1/CJ2	NJ	CJ1/CJ2	NJ	CJ1/CJ2	NJ		
Used by system		UDP		2223, 2224				
Tag data links	UDP		2222			Fixed value		
Class3, UCMM	TCP/UDP		44818		Fixed value			
DNS	UDP		53	53				
BOOTP client		UDP		68		-		
FINS/UDP service	UDP		9600					
FINS/TCP service	TCP		9600		Port numbers in the	Port numbers in the		
FTP	TCP		20, 21	21	Unit Setup can be	Unit Setup can be		
SNTP	UDP	UDP		123		changed with the		
SNMP	UDP		161	161		Sysmac Studio.		
SNMP trap	UDP		162	162				

\*10. When NJ-Series CPU Units is described, Supported only by the EtherNet/IP Units with unit version 2.1 or later and NJ-Series CPU Units with unit version 1.01 or later.

### Unit Versions and Software Versions

The following versions of the Sysmac Studio, CX-Programmer and Network Configurator are required to set EtherNet/IP Units.

						Yes:Supported	I,:Not supported
CJ1W-EIP21	Sysmac	Studio *1		CX-Programmer *2	Network Configurator for EtherNet/IP		
	Ver.1.01 or lower	Ver.1.02 or higher	Ver.7.1 or lower	Ver.8.0 or higher	Ver.8.02 or higher	Ver.3.40 or lower	Ver.3.50 or higher
Ver.1.0				Yes *3	Yes	Yes	Yes
Ver.2.0				Yes	Yes	Yes	Yes
Ver.2.1		Yes		Yes	Yes		Yes
Ver.3.0 *4		Yes		Yes	Yes		Yes

\*1. Available only when connecting with NJ-series CPU Units.

\*2. Available only when connecting with CJ1/CJ2-series CPU Units.

\*3. The most recent version of the common module for CX-One version 3.

\*4. Using the Sysmac Studio auto-update (November 2014 or later).


### **Network Configurator Requirements**

The Network Configurator Ver. 3.0 or higher is a software package designed for building, setting, and controlling a multi-vendor EtherNet/IP Network using OMRON's EtherNet/IP. It is included in CX-One version 3.0. The Network Configurator provides the following functions for building, setting, and controlling EtherNet/IP.

	Item	Specification					
Operating environment		Refer to the <i>CX-One Setup Manual</i> (Cat. No. W463). CXONE-AL_D-V					
Network		CS1/CJ1	CJ2	NJ			
Network connection	Serial interface	CPU Unit's Peripheral or RS-232C port	CPU Unit's USB or RS-232C port	CPU Unit's USB port			
method	Ethernet interface	EtherNet/IP Unit's Ethernet port	CPU Unit's Ethernet port EtherNet/IP Unit's Ethernet port				
Location on	Network	A single node address is used (only when directly connected to EtherNet/IP).					
Number of U Network	nits that can be connected to	A single Network Configurator per Network (More than one Configurator cannot be used in the same system.)					
Main functions	Network control functions	<ul> <li>The Network configuration can be created</li> <li>The Network configuration can be readed</li> </ul>	ated and edited regardless of whether the ead from a file or the network.	Network Configurator is online or offline.			
lunctions	Configuration functions	The EDS files used by the Network C	onfigurator can be installed and delete	d.			
Supported file formats		Configurator network configuration files (*.ncf) Configuration files (*.ncf) created using the Network Configurator for EtherNet/IP (version 2) can be imported by selecting <i>External Data - Import</i> from the File Menu.					

### **External Interface**

CJ1W-EIP21



#### **Ethernet Connectors**

The following standards and specifications apply to the connectors for the Ethernet twisted-pair cable. • Electrical specifications: Conforming to IEEE802.3 standards.

- RJ45 8-pin Modular Connector
- Connector structure: (conforming to ISO 8877)



Connector pin	Signal name	Abbr.	Signal direction
1	Transmission data +	TD+	Output
2	Transmission data –	TD-	Output
3	Reception data +	RD+	Input
4	Not used.	-	-
5	Not used.	-	-
6	Reception data -	RD-	Input
7	Not used.	-	-
8	Not used.	-	-
Hood	Frame ground	FG	-

## **Functional Comparsion of EtherNet/IP Functionality**


				OK:Supported,	:Not supported
	EtherNet/IP U	nit (built-in port on (	Built-in EtherNet/	CJ-series Ethernet	
Item	Unit version 1.0	Unit version 2.0	Unit version 2.1 Unit version 3.0	IP port on NJ- series CPU Unit	Unit
Tag data link communications service	ОК	ОК	OK	ОК	
CIP message communications service	ОК	ОК	OK	OK	
Socket service				OK	ОК
File transfer (FTP)		ОК	OK	ОК	ОК
Mail send/receive					ОК
Web functions					OK
Automatic adjustment of PLC/Controller's internal clock		ОК	OK	OK	OK
Error history	ОК	ОК	OK	OK *1	OK
Response to PING command	ОК	ОК	OK	OK	OK
SNMP/SNMP trap		ОК	OK	OK	
CIDR function for IP addresses		ОК	OK	ОК	
Online connection via EtherNet/IP using CX-One/Sysmac Studio		ОК	OK		
Online connection via EtherNet/IP using Network Configurator	ОК	ОК	OK	OK	
Mounting in a Controller with an NJseries CPU Unit			OK *2		


\*1. This is equivalent to the event log of the built-in EtherNet/IP port of an NJ-series Controller.
\*2. You cannot use the following functions if you connect to the CPU Unit through an EtherNet/IP Unit.
• Going online with a CPU Unit from the Sysmac Studio. (However, you can go online from the Network Configurator.)
• Troubleshooting from an NS-series PT

### **Dimensions**

### CJ1W-EIP21







(Unit: mm)

### **Related Manuals**

Manual number	Model	Name	Contents
W465	CS1W-EIP21 CJ1W-EIP21 CJ2H-CPU CJ2M-CPU3	EtherNet/IP Units Operation Manual	Provides information on operating and installing EtherNet/IP Units, including details on basic settings, tag data links, and FINS communications. Refer to the <i>Communications Commands Reference Manual</i> (W342) for details on FINS commands that can be sent to CS-series and CJ-series CPU Units when using the FINS communications service. Refer to the <i>Ethernet Units Operation Manual Construction of Applications</i> (W421) for details on constructing host applications that use FINS communications.
W495	CJ1W-EIP21	CJ-series EtherNet/IP Units Operation Manual for NJ-series CPU Unit	Information on using an EtherNet/IP Unit that is connected to an NJ-series CPU Unit is provided. Information is provided on the basic setup, tag data links, and other features. Use this manual together with the NJ-series CPU Unit Hardware User's Manual (Cat. No. W500) and NJ-series CPU Unit Software User's Manual (Cat. No. W501).
W421	CS1W-ETN21 CJ1W-ETN21	Ethernet Units Operation Manual Construction of Applications	Provides information on constructing host applications for 100Base-TX Ethernet Units, including functions for sending/receiving mail, socket service, automatic clock adjustment, FTP server functions, and FINS communications.
W342	CS1G/H-CPU H CS1G/H-CPU- CS1W-SCU21 CS1W-SCB21/41 CJ1G/H-CPU CJ1G-CPU CJ1W-SCU41	Communications Commands Reference Manual	Describes the C-series (Host Link) and FINS communications commands used when sending communications commands to CS-series and CJ-series CPU Units.
W463	CXONE-AL	CX-One Setup Manual	Describes the setup procedures for the CX-One. Information is also provided on the operating environment for the CX-One.

### Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warrantv.

See http://www.omron.com/global/ or contact your Omron representative for published information.

#### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

#### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

#### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

#### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

#### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

**OMRON** Corporation Industrial Automation Company

http://www.ia.omron.com/