# **Pull-reset Safety Limit Switch**

# D4N-□R

CSM D4N- R DS F 6 7

# A Series of Pull-reset Models Now Available

- Lineup includes three contact models with 2NC/1NO and 3NC contact forms in addition to the previous contact forms 1NC/ 1NO and 2NC.
- M12-connector models are available, saving on labor and simplifying replacement.
- Can be used with both standard loads and microloads.
- Conforms to the requirements for safety contacts in EN 115-1, EN 81-20, and EN 81-50 (slow-action models only).
- Certified standards: UL, EN (TÜV), and CCC



Be sure to read the Safety Precautions on page 12.

**Note:** Contact your sales representative for details on models with safety standard certification.



# **Model Number Structure**

Model Number Legend (Not all combinations are possible. Ask your OMRON representative for details.)

D4N-\_\_\_R

# 1. Conduit size

- 1: Pg13.5 (1-conduit)
- 2: G1/2 (1-conduit)
- 4: M20 (1-conduit)
- 6: G1/2 (2-conduit)
- 8: M20 (2-conduit)
- 9: M12 connector (1-conduit)

# 2. Built-in Switch

- A: 1NC/1NO (slow-action)
- B: 2NC (slow-action)
- C: 2NC/1NO (slow-action)
- D: 3NC (slow-action)

# 3. Actuator

- 20: Roller lever (resin lever, resin roller)
- 2G:Adjustable roller lever, form lock (metal lever, resin roller)
- 2H:Adjustable roller lever, form lock (metal lever, rubber roller)
- 31: Plunger
- 32: Roller plunger
- 62: One-way roller arm lever (horizontal)
- 72: One-way roller arm lever (vertical)

# **Ordering Information**

# **List of Models**

# Safety Limit Switches (with Direct Opening Mechanism) Consult with your OMRON representative when ordering any models that are not listed in this table.

					Bu	ıilt-in switc	h mechanism			
Actuator	Co	onduit size	1NC/1 (Slow-ad		2NC (Slow-action)		2NC/1NO (Slow-action)		3NC (Slow-action)	
			Model	Direct opening	Model	Direct opening	Model	Direct opening	Model	Direct opening
		Pg13.5	D4N-1A20R		D4N-1B20R		D4N-1C20R			
Roller lever	4 1 2	G1/2	D4N-2A20R	( <del>-</del> )	D4N-2B20R	( <del>-</del> )	D4N-2C20R	$\bigcirc$		$\bigcirc$
(resin lever, resin roller)	1-conduit	M20	D4N-4A20R		D4N-4B20R		D4N-4C20R		D4N-4D20R	
, p		M12 connector	D4N-9A20R	+	D4N-9B20R					
P	0 1 11	G1/2	D4N-6A20R		D4N-6B20R					
	2-conduit	M20		$\rightarrow$	D4N-8B20R	$\rightarrow$	D4N-8C20R	$\odot$		
		Pg13.5	D4N-1A2GR		D4N-1B2GR		D4N-1C2GR		D4N-1D2GR	
Adjustable roller lever, form lock	4 1 2	G1/2	D4N-2A2GR	( <del>-</del> )	D4N-2B2GR	$\bigcirc$	D4N-2C2GR	( <del>-</del> )	D4N-2D2GR	$\rightarrow$
(metal lever, resin roller)	1-conduit	M20	D4N-4A2GR		D4N-4B2GR		D4N-4C2GR			
P		M12 connector	D4N-9A2GR		D4N-9B2GR					
<i>5</i> /4	0	G1/2	D4N-6A2GR		D4N-6B2GR					
V.s.	2-conduit	M20	D4N-8A2GR			$\rightarrow$				
Adjustable roller lever,		Pg13.5	D4N-1A2HR							
form lock	4	G1/2	D4N-2A2HR	$\bigcirc$	D4N-2B2HR	$\bigcirc$	D4N-2C2HR	( <del>-</del> )	D4N-2D2HR	$\bigcirc$
(metal lever, rubber roller)	1-conduit M20	M20	D4N-4A2HR				D4N-4C2HR			
		M12 connector	D4N-9A2HR							
	0 1 11	G1/2	D4N-6A2HR	IR _						
E State .	2-conduit	M20		$\rightarrow$				$\rightarrow$	D4N-8D2HR	$\odot$
	1-conduit	Pg13.5	D4N-1A31R	$\odot$	D4N-1B31R	$\odot$	D4N-1C31R	<b>•</b>		
		G1/2	D4N-2A31R		D4N-2B31R		D4N-2C31R		D4N-2D31R	$\ominus$
Plunger		M20	D4N-4A31R		D4N-4B31R		D4N-4C31R			
A		M12 connector	D4N-9A31R		D4N-9B31R					
	2-conduit	G1/2	D4N-6A31R	-						
		M20				$\rightarrow$	D4N-8C31R	$\odot$		
		Pg13.5	D4N-1A32R		D4N-1B32R			( <del>-</del> )	D4N-1D32R	
	4	G1/2	D4N-2A32R	( <del>-</del> )	D4N-2B32R	( <del>-</del> )	D4N-2C32R			( <del>-</del> )
Roller plunger	1-conduit	M20	D4N-4A32R		D4N-4B32R		D4N-4C32R		D4N-4D32R	
R		M12 connector	D4N-9A32R		D4N-9B32R					
<u></u>	O conduit	G1/2	D4N-6A32R		D4N-6B32R		D4N-6C32R			
	2-conduit	M20	D4N-8A32R	$\rightarrow$	D4N-8B32R	$\rightarrow$	D4N-8C32R	$\rightarrow$		
		Pg13.5	D4N-1A62R		D4N-1B62R		D4N-1C62R		D4N-1D62R	
One-way roller arm lever	1 conduit	G1/2	D4N-2A62R	$\bigcirc$	D4N-2B62R	$\bigcirc$		<b>-</b>		$\rightarrow$
(horizontal)	1-conduit	M20	D4N-4A62R		D4N-4B62R		D4N-4C62R		D4N-4D62R	
		M12 connector	D4N-9A62R		D4N-9B62R					
<u>lía</u>	2 conduit	G1/2	D4N-6A62R		D4N-6B62R		D4N-6C62R		D4N-6D62R	
	2-conduit	M20	D4N-8A62R	$\Theta$		$\rightarrow$		$\odot$		$\odot$
		Pg13.5	D4N-1A72R		D4N-1B72R					
One-way roller arm lever (vertical)	1-conduit	G1/2	D4N-2A72R	$\rightarrow$	D4N-2B72R	$\odot$		$\rightarrow$		
(10.000)		M20	D4N-4A72R							
A	2 conduit	G1/2	D4N-6A72R		D4N-6B72R					
<del></del>	2-conduit	M20	D4N-8A72R	$\rightarrow$		$\rightarrow$				

# **Specifications**

# Standards and EC Directives Conforms to the following EC Directives:

- Machinery Directive
- Low Voltage Directive
- EN50047
- EN60204-1
- EN ISO 14119
- GS-ET-15

# **Certified Standards**

Certification body	Standard	File No.
TÜV SÜD	EN60947-5-1 (certified direct opening)	*1
UL <b>*</b> 2	UL508, CSA C22.2 No.14	E76675
CQC (CCC) *3	GB/T14048.5	*1

<sup>\*1.</sup> Consult your OMRON representative for details.

# Certified Standard Ratings TÜV (EN60947-5-1), CCC (GB/T14048.5)

Item	Utilization category	AC-15	DC-13
Rated operat	ting current (l <sub>e</sub> )	3 A	0.27 A
Rated operat	ting voltage (U₀)	240 V	250 V

Note: Use a 10 A fuse type gI or gG that conforms to IEC60269 as a short-circuit protection device. This fuse is not built into the Switch.

# UL/CSA (UL508, CSA C22.2 No. 14) A300

Rated	Carry current	Current (A)		Volt-amperes (VA)	
voltage	Carry Current	Make	Break	Make	Break
120 VAC	10 A	60	6	7,200	720
240 VAC	10 A	30	3		720

# Q300

Rated	Corry ourrent	Curre	nt (A)	Volt-amperes (VA)	
voltage	tage Carry current		Break	Make	Break
125 VDC	2.5 A	0.55	0.55	69	69
250 VDC	2.5 A	0.27	0.27	09	09

**<sup>\*2.</sup>** Certification for CSA C22.2 No. 14 is authorized by the UL mark.

**<sup>\*3.</sup>** Ask your OMRON representative for information on certified models.

# **Characteristics**

Degree of protection	<b>k</b> 1	IP67 (EN60947-5-1)		
	Mechanical	1,000,000 operations min.		
Durability *2	Electrical	500,000 operations min. (3 A resistive load at 250 VAC) <b>*</b> 3 300,000 operations min. (10 A resistive load at 250 VAC)		
Operating speed		1 to 500 mm/s (D4N-1A20R)		
Operating frequency		30 operations/minute max.		
Contact resistance		25 m $Ω$ max.		
Minimum applicable lo	oad <b>*</b> 4	1 mA resistive load at 5 VDC (N-level reference value)		
Rated insulation volta	ge (Ui)	300 V		
Rated frequency		50/60 Hz		
Protection against ele	ctric shock	Class II (double insulation)		
Pollution degree (operating environment)		3 (EN60947-5-1)		
	Between terminals of same polarity	2.5 kV		
Impulse withstand voltage	Between terminals of different polarity	4 kV		
(EN60947-5-1)	Between each terminal and non-current carrying metallic parts	6 kV		
Insulation resistance		100 M $\Omega$ min.		
Contact gap		$2 \times 2$ mm min.		
Vibration resistance	Malfunction	10 to 55 Hz, 0.75 mm single amplitude		
Shock resistance	Destruction	1,000 m/s <sup>2</sup>		
Shock resistance	Malfunction	300 m/s <sup>2</sup>		
Conditional short-circuit current		100 A (EN60947-5-1)		
Conventional free air	thermal current (Ith)	10 A (EN60947-5-1)		
Ambient operating ter	mperature	−30 to 70°C (with no icing)		
Ambient operating hu	midity	95% max.		
Weight		Approx. 92 g (D4N-1A20R)		

Note: 1. The above values are initial values.

- 2. Once a contact has been used to switch a standard load, it cannot be used for a load of a smaller capacity. Doing so may result in roughening of the contact surface and contact reliability may be lost.
- \*1. The degree of protection is tested using the method specified by the standard (EN60947-5-1). Confirm that sealing properties are sufficient for the operating conditions and environment beforehand. Although the switch box is protected from dust or water penetration, do not use the D4N-□R in places where foreign material such as dust, dirt, oil, water, or chemicals may penetrate through the head. Otherwise, accelerated wear, Switch damage or malfunctioning may occur.
- **\*2.** The durability is for an ambient temperature of 5 to 35°C and an ambient humidity of 40% to 70%. For more details, consult your OMRON representative.
- **\*3.** Do not pass the 3 A, 250 VAC load through more than 2 circuits.
- **\*4.** This value will vary with the switching frequency, environment, and reliability level. Confirm that correct operation is possible with the actual load beforehand.

# **Structure and Nomenclature**

# **Structure**

# Safety-oriented Lever Setting (Form lock mechanism)

Grooves which engage the lever are cut in the lever and rotary shaft to prevent the lever from slipping against the rotary shaft. The actuator locks (self-holding) when it moves to the lock position.

# Reset Head (Blue)

The direction of the reset head can be adjusted to any of the four directions.

### **Built-in Switch**

The built-in switch has a direct opening mechanism that forcibly separates the NC contact even when there is contact deposit.

# Cover

The cover, with a hinge on its lower part, can be opened by removing the screw of the cover, which ensures ease of maintenance and wiring.

### Head

The direction of the Switch Head can be adjusted to any of the four directions, except for Switches with Roller Plungers, which can be adjusted to either of two directions differing by 90°C.

# Conduit

A wide variety of conduits is available.


Size Box	1-conduit model	2-conduit model
Pg13.5	Yes	
G1/2	Yes	Yes
M20	Yes	Yes
M12 connector	Yes	

**Note:** M12 connector types are not available for Switches with three contacts.

# **Contact Form**

Model	Contact	Contact form	Operating pattern	Remarks
D4N-□A□R	1NC/1NO	Zb 11 12 33 34	11-12 ON Stroke	Only NC contacts 11-12 have a certified direct opening mechanism.  The terminals 11-12 and 33-34 can be used as unlike poles.
D4N-□B□R	2NC	Zb 11———————————————————————————————————	11-12 31-32 ON Stroke	Only NC contacts 11-12 and 31-32 have a certified direct opening mechanism.  The terminals 11-12 and 31-32 can be used as unlike poles.
D4N-□C□R	2NC/1NO	Zb 11 12 21 22 33 34	11-12 21-22 33-34 ON	Only NC contacts 11-12 and 21-22 have a certified direct opening mechanism. The terminals 11-12, 21-22, and 33-34 can be used as unlike poles.
D4N-□D□R	3NC	Zb 11———————————————————————————————————	11-12 21-22 31-32 ON	Only NC contacts 11-12, 21-22, and 31-32 have a certified direct opening mechanism. The terminals 11-12, 21-22, and 31-32 can be used as unlike poles.


# **Direct Opening Mechanism** 1NC/1NO Contact (Slow-action)



Conforms to EN60947-5-1 Direct Opening (Only NC Contact has a direct opening mechanism.)

When contact welding occurs, the contacts are separated from each other by the plunger being pushed in.

# **2NC Contact (Slow-action)**




Conforms to EN60947-5-1 Direct Opening (Both NC Contacts have a direct opening mechanism.)

When contact welding occurs, the contacts are separated from each other by the plunger being pushed in.


(Unit: mm)

# **Switches**

# 1-conduit Models




Adjustable Roller Lever, Form Lock (with Metal Lever, Resin Roller)
D4N-1□2GR D4N-2□2GR
D4N-4□2GR D4N-9□2GR \*




Adjustable Roller Lever, Form Lock (with Metal Lever, Rubber Roller) D4N-1□2HR D4N-2□2HR

D4N-4 2HR D4N-9 2HR \*



# 1-conduit M12 Connectors

D4N-9□□□R




**Note:** Unless otherwise specified, a tolerance of  $\pm 0.4$  mm applies to all dimensions. \* Refer to the right above diagram for details on 1-conduit M12 connectors.

	Model	D4N-□□20R	D4N-□□2GR	D4N-□□2HR
Operating characteristics			<b>*</b> 1	
Locking force	LF max.	6.4 N	5.6 N	5.4 N
Locking travel	LT max.	55°	55°	55°
Pretravel	PT 1 *2	18 to 27°	18 to 27°	18 to 27°
Pretravel	(PT 2) <b>*</b> 3	(44°)	(44°)	(44°)
Total travel	(TT) <b>*</b> 4	80°	80°	80°
Direct opening force	DOF min. *5	20 N	20 N	20 N
Direct opening travel	DOT min. *5	50°	50°	50°


- **\*1.** The operating characteristics of these Switches were measured with the roller lever set at 32 mm.
- \*2. These PT values are possible when the NC contacts are open (OFF).
- \*3. These PT values are reference values possible when the NO contacts are closed (ON). (1NC/1NO models only)
- \*4. Reference value.
- **\*5.** For safe use, always make sure that the minimum values or greater are provided.

# 1-conduit Models

Plunger D4N-1□31R D4N-2□31R D4N-4□31R D4N-9□31R \*



Roller Plunger D4N-1□32R D4N-2□32R D4N-4□32R D4N-9□32R \*




One-way Roller Arm Lever

(Horizontal)

D4N-1□62R D4N-2□62R D4N-4□62R D4N-9□62R \*

Operating direction 14.8 11±0.2 12 dia. × 5 - 11±0.2 resin roller 14 dia 35.5±0.2 39.3 2.5 20±0.1 2.15±0.05R -22±0.1 mounting holes 22±0.2 Conduit cap Two, 4<sup>+0.15</sup> dia. - 30 holes 36 Depth: 5

One-way Roller Arm Lever (Vertical)
D4N-1□72R D4N-2□72R
D4N-4□72R




**Note:** Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

\* Refer to page 7 for details on 1-conduit M12 connectors.


Operating characteri	Model stics	D4N-□□31R	D4N-□□32R	D4N-□□62R	D4N-□□72R
Locking force	LF max.	10.8 N	10.8N	7.5 N	7.9 N
Locking travel	LT max.	4.5 mm	4.5 mm	7 mm	7 mm
Pretravel	PT 1 max. *1	2 mm	2 mm	4 mm	4 mm
Pretravel	(PT 2) *2	(2.9 mm)	(2.9 mm)	(5.2 mm)	(4.3 mm)
Operating position	OP	34 ±0.5 mm	44.4 ±0.8 mm	53 ±0.8 mm	27 ±0.8 mm
Total travel	(TT) <b>*</b> 3	(6 mm)	(6 mm)	(9 mm)	(9 mm)
Direct opening force	DOF min. *4	20 N	20 N	20 N	20 N
Direct opening travel	DOT min. *4	3.2 mm	3.2 mm	5.8 mm	4.8 mm

- **\*1.** These PT values are possible when the NC contacts are open (OFF).
- \*2. These PT values are reference values possible when the NO contacts are closed (ON) (1NC/1NO models only)
- **\*3.** Reference value.
- **\*4.** For safe use, always make sure that the minimum values or greater are provided.

# 2-conduit Models




Adjustable Roller Lever, Form Lock (with Metal Lever, Resin Roller) D4N-6□2GR D4N-8□2GR



Adjustable Roller Lever, Form Lock (with Metal Lever, Rubber Roller) D4N-6□2HR

D4N-8□2HR




Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

Model Operating characteristics		D4N-□□20R	D4N-□□2GR	D4N-□□2HR
Locking force	LF max.	6.4 N	5.6 N	5.4 N
Locking travel	LT max.	55°	55°	55°
Pretravel	PT 1 <b>*</b> 1	18° to 27°	18° to 27°	18° to 27°
Pretravel	(PT 2) *2	(44°)	(44°)	(44°)
Total travel	(TT) <b>*</b> 3	80°	80°	80°
Direct opening force	DOF min. *4	20 N	20 N	20 N
Direct opening trave	el DOT min. *4	50°	50°	50°

- **\*1.** These PT values are possible when the NC contacts are open (OFF).
- \*2. These PT values are reference values possible when the NO contacts are closed (ON). (1NC/ 1NO models only)
- **\*3.** Reference value.
- **\*4.** For safe use, always make sure that the minimum values or greater are provided.

# 2-conduit Models


# Plunger D4N-6□31R D4N-8□31R



# Roller Plunger D4N-6 32R D4N-8 32R 9.5 dia. × 5 20.5 × 20.5 resin roller 14 dia. OP 41 5.4 2.15±0.05R mounting holes Conduit cap Two, 4\*0.15 dia. holes Depth: 5


# One-way Roller Arm Lever (Horizontal)

D4N-6□62R D4N-8□62R



# One-way Roller Arm Lever (Vertical)

D4N-6□72R




**Note:** Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

Operating characteris	Model	D4N-□□31R	D4N-□□32R	D4N-□□62R	D4N-□□72R
Locking force	LF max.	10.8 N	10.8N	7.5 N	7.9 N
Locking travel	LT max.	4.5 mm	4.5 mm	7 mm	7 mm
Pretravel	PT 1 max. *1	2 mm	2 mm	4 mm	4 mm
Pretravel	(PT 2) <b>*</b> 2	(2.9 mm)	(2.9 mm)	(5.2 mm)	(4.3 mm)
Operating position	OP	34 ±0.5 mm	44.4 ±0.8 mm	53 ±0.8 mm	27 ±0.8 mm
Total travel	(TT) <b>*</b> 3	(6 mm)	(6 mm)	(9 mm)	(9 mm)
Direct opening force	DOF min. *4	20 N	20 N	20 N	20 N
Direct opening travel	DOT min. *4	3.2 mm	3.2 mm	5.8 mm	4.8 mm

- **\*1.** These PT values are possible when the NC contacts are open (OFF).
- **\*2.** These PT values are reference values possible when the NO contacts are closed (ON). (1NC/1NO models only)
- **\*3.** Reference value.
- **\*4.** For safe use, always make sure that the minimum values or greater are provided.

**Levers** Refer to the following diagrams for the angles and positions of the dogs.



Note: Unless otherwise specified, a tolerance of  $\pm 0.4$  mm applies to all dimensions.

# **Safety Precautions**

■ Be sure to read the precautions for all D4N-□R models in the website at: http://www.ia.omron.com/.

# / CAUTION

Electric shock may occasionally occur. Do not use metal connectors or metal conduits.



# **Precautions for Safe Use**

- Do not use the Switch submerged in oil or water, or in locations continuously subject to splashes of oil or water. Doing so may result in oil or water entering the Switch interior. (The IP67 degree of protection specification for the Switch refers to water penetration while the Switch is submersed in water for a specified period of time.)
- Always attach the cover after completing wiring and before using the Switch. Also, do not turn ON the Switch with the cover open. Doing so may result in electric shock.
- Do not switch circuits for two or more standard loads (250 VAC,
   3 A). Doing so may adversely affect insulation performance.
- Make sure that the actuator is pushed into the lock position. Not doing so may result in the actuator becoming unlocked, causing an accident.
- Always reset the Switch manually. Not doing so may result in damage to the reset function.

# **Precautions for Correct Use**


The Switch contacts can be used with either standard loads or microloads. Once the contacts have been used to switch a load, however, they cannot be used to switch smaller loads. The contact surfaces will become rough once they have been used and contact reliability for smaller loads may be reduced.

# **Mounting Method**

# **Appropriate Tightening Torque**

Tighten each of the screws to the specified torque. Loose screws may result in malfunction of the Switch within a short time.


1	Terminal screw	0.6 to 0.8 N·m
2	Cover mounting screw	0.5 to 0.7 N·m
3	Head mounting screw	0.5 to 0.6 N·m
4	Lever mounting screw	1.6 to 1.8 N·m
5	Body mounting screw	0.5 to 0.7 N·m
6	Connector, M12 adaptor	1.8 to 2.2 N·m
7	Cap screw	1.3 to 1.7 N·m




# **Switch Mounting**

- Mount the Switch using M4 screws and spring washers and tighten the screws to the specified torque.
- For safety, use screws that cannot be easily removed, or use an equivalent measure to ensure that the Switch is secure.
- As shown below, two studs with a maximum height of 4.8 mm and a diameter of 4-0.05 mm can be provided, the studs inserted into the holes on the bottom of the Switch, and the Switch secured at four locations to increase the mounting strength.

# Switch Mounting Holes One-conduit Type



# **Two-conduit Type**



# **Changing the Head Direction**

By removing the four screws of the head, the mounting direction of the head can be changed. The head can be mounted in four directions.

Be sure that no foreign material will enter the head during a change in direction.

# Changing the Lever

The lever mounting screws can be used to set the lever position to any position in a 360° angle at 7.5° increments. Grooves are incised on the lever and rotary shaft that engage to prevent the lever from slipping against the rotary shaft. The screws on adjustable roller lever models can also loosened to change the length of the lever. Remove the screws from the front of the lever before mounting the lever in reverse (front/back), and set the level so that operation will be completed before exceeding a range of 180° on the horizontal.


# Wiring

# Wiring


When connecting to the terminals via insulating tube and M3.5 crimp terminals, arrange the crimp terminals as shown below so that they do not rise up onto the case or the cover.
 Applicable lead wire size: AWG20 to AWG18 (0.5 to 0.75 mm²). Use lead wires of an appropriate length, as shown below. Not doing so may result in excess length causing the cover to rise and not fit properly.

# **One-conduit Type (3 Poles)**






# Two-conduit Type (3 Poles)



- Do not push crimp terminals into gaps in the case interior. Doing so may cause damage or deformation of the case.
- Use crimp terminals not more than 0.5 mm in thickness. Otherwise, they will interfere with other components inside the case.

[Reference] The crimp terminals shown below are not more than 0.5 mm thick.


Manufacturer	Туре	
IST Mfg Co	FN0.5-3.7 (F Type)	
J.S.T. Mfg. Co.	N0.5-3.7 (Straight Type)	




# **Contact Arrangement**

• The contact arrangements are shown below.

# **Screw Terminal Type**



# **Connector Type**



- Applicable socket: XS2F-D421 series (OMRON).
- Refer to the *Connector Catalog* for details on socket pin numbers and lead wire colors.

# **Socket Tightening (Connector Type)**

- Turn the socket connector screws by hand and tighten until no space remains between the socket and the plug.
- Make sure that the socket connector is tightened securely.
   Otherwise, the rated degree of protection (IP67) may not be maintained and vibration may loosen the socket connector.

# **Conduit Opening**

- Connect a recommended connector to the opening of the conduit and tighten the connector to the specified torque. The case may be damaged if an excessive tightening torque is applied.
- Use a cable with a suitable diameter for the connector.
- Attach and tighten a conduit cap to the unused conduit opening when wiring. Tighten the conduit cap to the specified torque. The conduit cap is provided with the Switch (2-conduit types).

# **Recommended Connectors**

Use connectors with screws not exceeding 9 mm, otherwise the screws will protrude into the case interior, interfering with other components in the case.

The connectors listed in the following table have connectors with thread sections not exceeding 9 mm.

Use the recommended connectors to ensure conformance to IP67.

Size	Manufacturer	Model	Applicable cable diameter
G1/2	LAPP	ST-PF1/2 5380-1002	6.0 to 12.0 mm
Pg13.5	LAPP	ST-13.5 5301-5030	6.0 to 12.0 mm
M20	LAPP	ST-M20 × 1.5 5311-1020	7.0 to 13.0 mm

Use LAPP connectors together with seal packing (JPK-16, GP-13.5, or GPM20), and tighten to the specified tightening torque. Seal packing is sold separately.

• LAPP is a German manufacturer.

# **Others**

- When attaching a cover, be sure that the seal rubber is in place and that there is no foreign material present. If the cover is attached with the seal rubber out of place or if foreign material is stuck to the rubber, a proper seal will not be obtained.
- Do not use any screws to connect the cover other than the specified ones. The seal characteristics may be reduced.
- With rubber roller lever models, the rubber roller may turn white over time, but this will not affect the quality of operation.
- Use the following recommended countermeasures to prevent telegraphing when using adjustable or long levers.
  - 1. Make the rear edge of the dog smooth with an angle of 15° to 30° or make it in the shape of a quadratic curve.
- 2. Design the circuit so that no error signal will be generated.

# Terms and Conditions Agreement

### Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

# Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See <a href="http://www.omron.com/global/">http://www.omron.com/global/</a> or contact your Omron representative for published information.

# Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

# Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

# Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

# Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

# Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2024.4

In the interest of product improvement, specifications are subject to change without notice.