


Data Flow Controller DX1

An edge controller
that provides a simple entry point
to data utilization




System Configuration



DX1

Ordering Information

CPU Unit





Product name	Specifications		Model
	Communications	Built-in software	
DX-series Data Flow Controller 	2 Ethernet ports, 1 USB port	<ul style="list-style-type: none">• Data collection: SpeedBee Synapse• Chart Display Tool• Package:<ul style="list-style-type: none">Equipment Monitoring PackageFactory Monitoring PackageStatus Monitoring PackageEvent-triggered Video Logging Package	DX100-0010

Power Supply Units

The Data Flow Controller does not have a built-in power supply. You must install a Power Supply Unit on it.

Product name	Power supply voltage	Output current		Output capacity	Options			Model
		5-VDC output capacity	24-VDC output capacity	Total power consumption	24-VDC service power supply	RUN output	Maintenance forecast monitor	
AC Power Supply Unit	100 to 240 VAC	6.0 A	1.0 A	30 W	No	Yes	No	NJ-PA3001
DC Power Supply Unit	24 VDC							NJ-PD3001

Cable with Connectors


Item	Appearance	Recommended manufacturer	Cable length (m)	Model
Cable with Connectors on Both Ends (RJ45/RJ45) Standard RJ45 plugs *1 Wire gauge and number of pairs: AWG26, 4-pair cable Cable sheath material: PUR Cable color: Yellow *2 EtherCAT/ EtherNet/IP (10BASE/100BASE)		OMRON	0.3	XS6W-6PUR8SS30CM-YF
			0.5	XS6W-6PUR8SS50CM-YF
			1	XS6W-6PUR8SS100CM-YF
			2	XS6W-6PUR8SS200CM-YF
			3	XS6W-6PUR8SS300CM-YF
			5	XS6W-6PUR8SS500CM-YF
Cable with Connectors on Both Ends (RJ45/RJ45) Rugged RJ45 plugs *1 Wire gauge and number of pairs: AWG22, 2-pair cable Cable color: Light blue EtherCAT/ EtherNet/IP (10BASE/100BASE)		OMRON	0.3	XS5W-T421-AMD-K
			0.5	XS5W-T421-BMD-K
			1	XS5W-T421-CMD-K
			2	XS5W-T421-DMD-K
			5	XS5W-T421-GMD-K
			10	XS5W-T421-JMD-K
Cable with Connectors on Both Ends (M12 Straight/M12 Straight) Shield strengthening connector cable *3 M12/Smartclick connectors Wire gauge and number of pairs: AWG22, 2-pair cable Cable color: Black EtherCAT/ EtherNet/IP (10BASE/100BASE)		OMRON	0.5	XS5W-T421-BM2-SS
			1	XS5W-T421-CM2-SS
			2	XS5W-T421-DM2-SS
			3	XS5W-T421-EM2-SS
			5	XS5W-T421-GM2-SS
			10	XS5W-T421-JM2-SS
Cable with Connectors on Both Ends (M12 Straight/RJ45) Shield strengthening connector cable *3 M12/Smartclick connector and rugged RJ45 plug Wire gauge and number of pairs: AWG22, 2-pair cable Cable color: Black EtherCAT/ EtherNet/IP (10BASE/100BASE)		OMRON	0.5	XS5W-T421-BMC-SS
			1	XS5W-T421-CMC-SS
			2	XS5W-T421-DMC-SS
			3	XS5W-T421-EMC-SS
			5	XS5W-T421-GMC-SS
			10	XS5W-T421-JMC-SS

*1. Cables with standard RJ45 plugs are available in the following lengths: 0.2 m, 0.3 m, 0.5 m, 1 m, 1.5 m, 2 m, 3 m, 5 m, 7.5 m, 10 m, 15 m, 20 m. Cables with rugged RJ45 plugs are available in the following lengths: 0.3 m, 0.5 m, 1 m, 2 m, 3 m, 5 m, 10 m, 15 m. For details, refer to the *Industrial Ethernet Connectors Catalog* (Cat. No. G019).

*2. Cables colors are available in yellow, green, and blue.

*3. For details, contact your OMRON representative.

Cables/Connectors

Product name			Recommended manufacturer	Model
Products for EtherCAT or Ethernet (1000BASE-T/100BASE-TX)	Wire gauge and number of pairs: AWG24, 4-pair cable	Cable	Kuramo Electric Co.	KETH-SB *1
			JMACS Japan Co., Ltd.	IETP-SB *1
		RJ45 Connector	Panduit Corporation	MPS588-C *1
Products for EtherCAT or Ethernet (100BASE-TX)	Wire gauge and number of pairs: AWG22, 2-pair cable	Cable	Kuramo Electric Co.	KETH-PSB-OMR *2
			JMACS Japan Co., Ltd.	PNET/B *2
		RJ45 Assembly Connector 	OMRON Corporation	XS6G-T421-1 *2

*1. We recommend you to use the Cable for EtherCAT or Ethernet marked with *1 and the RJ45 Connector marked with *1 together.

*2. We recommend you to use the Cable for EtherCAT or Ethernet marked with *2 and the RJ45 Assembly Connector marked with *2 together.

Options

Product name	Specifications	Model
USB Memory	2 GB	FZ-MEM2G *1
DIN Track	Length: 0.5 m. Height: 7.3 mm	PFP-50N
	Length: 1 m. Height: 7.3 mm	PFP-100N
	Length: 1 m. Height: 16 mm	PFP-100N2
End Plate	Stopper to prevent units from moving on the DIN track. The minimum order quantity is 10 units.	PFP-M

*1. OMRON is not responsible for the operation of any other USB memory devices.

General Specifications

The general specifications of the CPU unit are shown below.

There are items for which restrictions on the operating environment of the Power Supply Unit are greater than those listed here. Also check the specifications in the NJ-PA/PD Datasheet.

Item		Specification
Structure		Mounted in a panel
Installation method		Ground to less than 100 Ω.
Operating Environment	Ambient operating temperature	0 to 55°C
	Ambient operating humidity	10% to 90% (with no condensation or icing)
	Atmosphere	Must be free of corrosive gases.
	Ambient storage temperature	-25 to 70°C (with no condensation or icing)
	Altitude	2,000 m max.
	Pollution degree	2 or less: Meets IEC 61010-2-201.
	Noise immunity	Conforms to IEC 61000-4-4. 2 kV on power supply line
	Overvoltage category	Category II: Meets IEC 61010-2-201.
	EMC immunity level	Zone B
	Vibration resistance	Conforms to IEC 60068-2-6. 5 to 8.4 Hz with 3.5-mm amplitude, 8.4 to 150 Hz, acceleration of 9.8 m/s ² 100 min each in X, Y, and Z directions (10 sweeps of 10 min each =100 min total)
	Shock resistance	Conforms to IEC 60068-2-27. 147 m/s ² , 3 times each in X, Y, and Z directions
Insulation Resistance		20 MΩ min. between isolated circuits (at 100 VDC)
Dielectric strength		510 VAC between isolated circuits for 1 minute with a leakage current of 5 mA max.
Applicable standards *1		cULus, EU: EN61131, RCM, KC

*1. Refer to the OMRON website (<http://www.ia.omron.com/>) or consult your OMRON representative for the most recent applicable standards.

Function Specifications

The functional specifications of the Data Flow Controller are shown below.


Item			Specification
Hardware	Communications		2 Ethernet ports and 1 USB port
	User interface	Indicators	PWR, RUN, and ERR
	Supported power supply		NJ-PA3001 and NJ-PD3001
	Clock		Built-in RTC <ul style="list-style-type: none">Monthly fluctuation of power supply<ul style="list-style-type: none">At ambient temperature of 55°C: -4.5 to 4.5 min error per monthAt ambient temperature of 25°C: -3.5 to 3.5 min error per monthAt ambient temperature of 0°C: -4.5 to 4.5 min error per month
		Retention time of builtin capacitor	At ambient temperature of 40°C: 10 days
	Ethernet communications specifications	Baud rate	Port 1: 1 Gbps Port 2: 100 Mbps
		Physical layer	1000BASE-T·100BASE-TX (IEEE 802.3)
		Frame length	1,514 bytes max.
		Media access method	CSMA/CD
		Transmission distance	100 mm
		Transmission media	Twisted-pair cable of category 5, 5e, or higher (shielded cable)
		Communications protocol	TCP/IP, UDP/IP, HTTP(S), NTP, DHCP, and DNS/mDNS
	USB port	Physical layer	USB 2.0 compliant, type A connector. Output voltage: 5 V, 0.5 A max.
		Transmission distance	3 m
Dimensions [mm]		78.8 × 90 × 80 mm (W × H × D)	
Weight		250 g max.	
Built-in software			<ul style="list-style-type: none">Data collection: SpeedBee SynapseChart Display ToolPackage: Equipment Monitoring Package Factory Monitoring Package Status Monitoring Package Event-triggered Video Logging Package

Part Names and Functions

CPU Unit

The name and function of each part of the CPU unit are shown below.


Front view



Symbol	Name	Function
A	Slider	Locks the adjacent Unit in place. This part is used to mount the Power Supply Unit.
B	Operation Indicators	Show the operation status by the combination of multiple indicators.
C	RSV (Reserve)	Do not use this.
D	USB 2.0 connector	USB 2.0 interface connector. Connects a USB memory device.
E	RSV (Reserve)	Do not use this.
F	Ethernet communications connector (Port 1)	Connects an Ethernet communications cable. Port 1 supports a communications speed of 1 Gbps and is recommended for connecting the network for data collection.
G	Ethernet communications port (Port 1) operation indicator	Shows the operation status of Ethernet.
H	Ethernet communications connector (Port 2)	Connects an Ethernet communications cable. Port 2 supports a communications speed of 100 Mbps and is recommended for connecting a computer that use the Web UI.
I	Ethernet communications port (Port 2) operation indicator	Shows the operation status of Ethernet.

Note: 1. The Data Flow Controller does not support wireless LAN.


Rear view




Symbol	Name	Function
J	DIP switch	Use this in such a case where the computer cannot be connected.
K	DIN Track mounting hook	Use this to mount the Data Flow Controller to a DIN Track.

Power Supply Unit

NJ-PA3001



NJ-PD3001



Version Information


Unit Version and Supportes Browser Versions

Refer to *DX-series Data Flow Controller User's Manual* (Cat. No. V241).


Dimensions

(Unit: mm)

CPU unit DX100-0010



Power Supply Units NJ-PA3001 NJ-PD3001



DX1

System Configuration of the Packages

The following is an example of system configurations for using each package.

Equipment Monitoring Package

Product name	Manufacturer	Model	Quantity	Remarks
Data Flow Controller	OMRON Corporation	DX100-0010	1	
IO-Link Master Unit for EtherNet/IP	OMRON Corporation	NXR-ILM08C-EIT	1	
IO-Link Photoelectric Sensor M12 Pre-wired Smartclick Connector type	OMRON Corporation	E3AS-HL150LMT-M1TJ 0.3M E3AS-HL500LMT-M1TJ 0.3M E3AS-HL150MT-M1TJ 0.3M E3AS-HL500MT-M1TJ 0.3M	2	

Factory Monitoring Package

Product name	Manufacturer	Model	Quantity	Remarks
Data Flow Controller	OMRON Corporation	DX100-0010	2 or more	

Note: 1. For equipment used in the facility monitoring package managed by the factory monitoring package, refer to the *Equipment Monitoring Package*.

Event-triggered Video Logging Package

Product name	Manufacturer	Model	Quantity	Remarks
Data Flow Controller	OMRON Corporation	DX100-0010	1	
IO-Link Master Unit for EtherNet/IP	OMRON Corporation	NXR-ILM08C-EIT	1	
Camera	Axis Communications	M1055-L	1	Evaluated *1
Switching Hub PoE	TP-Link Systems Inc.	TL-SG105PE	1	Evaluated *1

*1. This product has been confirmed to operate correctly in combination with our products.

Condition Monitoring Package (Variable Speed Motor)

Product name	Manufacturer	Model	Quantity	Remarks
Data Flow Controller	OMRON Corporation	DX100-0010	1	
Advanced Motor Condition Monitoring Device	OMRON Corporation	K7DD-PQMD/PQMA *1	1	
CT	OMRON Corporation	K6CM-CICB□□□ *2	1 or 3 *3	
Modbus Gateway	Moxa Inc.	MGateMB3170	1	Evaluated *4

*1. PQMD: DC type, PQMA: AC type

*2. Model name may vary depending on the CT sensor. Select a CT that can measure the motor current within the applicable range.

*3. The number of CTs required depends on the number of phases of the motor current being measured.

*4. This product has been confirmed to operate correctly in combination with our products.

Condition Monitoring Package (Induction Motor, Current type)

Product name	Manufacturer	Model	Quantity	Remarks
Data Flow Controller	OMRON Corporation	DX100-0010	1	
Motor Condition Monitoring Device Comprehensive current diagnosis type	OMRON Corporation	K6CM-CI2MD-EIP K6CM-CI2MA-EIP *1	1	
CT	OMRON Corporation	K6CM-CICB□□□ *2	1	

*1. CI2MD: DC type, CI2MA: AC type

*2. Model name may vary depending on the CT sensor. Select a CT that can measure the motor current within the applicable range.

Condition Monitoring Package (Induction Motor, Vibration type)

Product name	Manufacturer	Model	Quantity	Remarks
Data Flow Controller	OMRON Corporation	DX100-0010	1	
Motor Condition Monitoring Device Vibration & temperature type	OMRON Corporation	K6CM-VBMD-EIP K6CM-VBMA-EIP	1	
Vibration & Temperature Sensor	OMRON Corporation	K6CM-VBS1	1	

*1. VBMD: DC type, VBMA: AC type

Condition Monitoring Package (Equipment Temperature)

Product name	Manufacturer	Model	Quantity	Remarks
Data Flow Controller	OMRON Corporation	DX100-0010	1	
Thermal Condition Monitoring Device	OMRON Corporation	K6PM-THMD-EIP	1	
Infrared thermal sensor	OMRON Corporation	K6PM-THS3232	1 to 31 *1	

*1. Select the number of temperature sensors according to the target and range you wish to monitor.

In Common

Product name	Manufacturer	Model	Quantity	Remarks
USB memory stick	OMRON Corporation	FZ-MEM2G	1	

DX1



Related Manuals

The following manuals are related. Use these manuals for reference.

Manual name	Cat. No.	Model	Application	Description
DX-series Data Flow Controller User's Manual	V241	DX100-0010	Learning the overview, installation, troubleshooting, and maintenance of the DX-series Data Flow Controller.	The following information is provided on the DX-series Data Flow Controller. <ul style="list-style-type: none">• Features and system configuration• Overview• Part names and functions• General specifications• Overview of functions• Initial setup• Installation and wiring• Maintenance and inspection
DX-series Web UI User's Manual	V242	DX100-0010	Learning the settings and operation details of the DX-series Data Flow Controller.	The following information is provided on the DX-series Data Flow Controller. <ul style="list-style-type: none">• Settings• Operation method
DX-series SpeedBee Synapse User's Manual	V243	DX100-0010	Learning how to collect and utilize data with the DX-series Data Flow Controller.	The following information is provided on the data collection and utilization functions of the DX-series Data Flow Controller. <ul style="list-style-type: none">• Functions• Setting method
DX-series Dashboard Generator User's Manual	N700	DX100-0010	Learning the common usage of Packages with the DX-series Data Flow Controller.	The following information is provided on the Packages for the DX-series Data Flow Controller. <ul style="list-style-type: none">• Common functions• Common usage
DX-series Equipment Monitoring Package User's Manual	N701	DX100-0010	Learning how to use the Equipment Monitoring Package with the DX-series Data Flow Controller.	The following information is provided on the Equipment Monitoring Package for the DX-series Data Flow Controller. <ul style="list-style-type: none">• Functions• Usage
DX-series Factory Monitoring Package User's Manual	N702	DX100-0010	Learning how to use the Factory Monitoring Package with the DX-series Data Flow Controller.	The following information is provided on the Factory Monitoring Package for the DX-series Data Flow Controller. <ul style="list-style-type: none">• Functions• Usage
DX-series Status Monitoring Package User's Manual	N703	DX100-0010	Learning how to use the Status Monitoring Package with the DX-series Data Flow Controller.	The following information is provided on the Status Monitoring Package for the DX-series Data Flow Controller. <ul style="list-style-type: none">• Functions• Usage
DX-series Event-triggered Video Logging Package User's Manual	N704	DX100-0010	Learning how to use the Dashboard Event-triggered Video Logging Package with the DX-series Data Flow Controller.	The following information is provided on the Dashboard Event-triggered Video Logging Package for the DX-series Data Flow Controller. <ul style="list-style-type: none">• Functions• Usage

ODVA, CIP, CompoNet, DeviceNet and EtherNet/IP are trademarks of ODVA.

Modbus is a registered trademark of Schneider Electric.

The SD and SDHC logos are trademarks of SD-3C, LLC.  

SpeedBee Synapse is a trademark of SALTYSER Co., Ltd.

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

The product photographs and figures that are used in this catalog may vary somewhat from the actual products

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See <http://www.omron.com/global/> or contact your Omron representative for published information.

Limitation on Liability: Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Product Inquiries (For DX-series):
DataPF-contactdesk-OC@omron.com
Inquiry response days: Excluding Saturdays, Sundays, and December 31 to January 3 (based on Japan Standard Time)

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN

Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp
The Netherlands
Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra
Technopark, Singapore 119968
Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200
Hoffman Estates, IL 60169 U.S.A.
Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower,
200 Yin Cheng Zhong Road,
PuDong New Area, Shanghai, 200120, China
Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

Authorized Distributor:

©OMRON Corporation 2025 All Rights Reserved.
In the interest of product improvement,
specifications are subject to change without notice.

CSM_1_1

Cat. No. V305-E1-01 0925 (0925)