



New standards for proximity sensors Fewer collisions, easier replacement and design, and greater flexibility



E2E NEXT Series brings great flexibility to manufacturing sites

Proximity sensors are often used in harsh environments. Due to their short sensing distances, they tend to be damaged by collisions and require frequent replacements. When a proximity sensor is installed in the innermost corner of equipment, the poor visibility of the indicator makes operation difficult. Also it takes time to select appropriate sensors for design requirements. With our long experience in manufacturing, we provide effective solutions from design and commissioning through to operation and maintenance, contributing to streamlining operations and improving productivity at manufacturing sites.



^{*1.}Based on Omron investigation in October 2025. *2. DC 2-wire, M12 shielded model.

Note: 1. The image shows the actual size of the proximity sensors and sensing distances.

Note: 2. DC 2-wire, M8 and M12 triple distance models include two toothed washers.

Minimize replacement frequency of damaged sensors



Long-distance detection ensures stable operation and reduces unexpected maintenance P.4

Reduce adjustment time during installation



Standardize on a single series for most applications



A wide range of applications facilitate equipment design P.8


Long-distance detection ensures stable operation and reduces unexpected maintenance

Free from malfunctions and collisions

Quadruple/triple distance model


Reduces false detection due to a stationary moved by machine vibration

Vibration associated with machines or heavy load pallets can cause malfunction of proximity sensors, which results in the equipment stoppage. E2E NEXT triple distance models reduce such malfunctions, increasing equipment uptime.



Reduces collisions caused by variation in workpiece sitting position


Proximity sensors sometimes collide with workpieces during sitting position detection, causing sensor failure.E2E NEXT triple distance models reduce these collisions and improve equipment uptime.



,

Double the sensing distance of standard models

Quadruple/triple distance model



Improvement example

The E2E NEXT Series reduces equipment downtime caused by proximity sensors to 1/3

The annual total of unexpected equipment downtime at an automotive parts manufacturing site was around 1,600 hours, of which 240 hours were caused by proximity sensors.

The use of E2E NEXT triple distance models reduced the number of equipment stoppages due to collisions and malfunctions from 240 to 80, shortening equipment downtime to 1/3.

(Based on Omron investigation in September 2017.)

Previous models

240 hours per year

Number of proximity sensor failures: 240/year × recovery time: about 60 min/sensor*2

E2E NEXT

80 hours per year Long sensing distance reduces failures caused by collisions and malfunctions.

Number of proximity sensor failures: 80/year × recovery time: about 60 min/sensor*2

Thermal Distance Control technology for stable long-distance detection × IoT

With the Thermal Distance Control technology for stable long-distance detection and the analog digital hybrid IC, the E2E NEXT Series eliminates the influence of temperature changes and variation between different sensors, which were difficulties in increasing the sensing distance.


DC 2-wire, triple distance model (Thermal Distance Control)

Temperature correction values are written into the analog digital hybrid IC (PROX2) for the factory setting, which was not possible for previous analog ICs, to minimize the influence of temperature changes on sensing distance.

DC 3-wire, quadruple distance model (Thermal Distance Control × IoT)

Patented *3

Temperature characteristics of each sensor are measured in an IoT-enabled production process, and then optimal correction values are calculated based on our unique algorithm and written to the analog digital hybrid IC (PROX3). This minimizes the influence of temperature change on sensing distance and variation between different sensors.



^{*3. &}quot;Patent Pending" means that we applied for a patent in Japan, and "Patented" means that we obtained a patent in Japan. (As of October 2025)

^{*1.} DC 2-wire, Triple distance models. Based on Omron investigation in October 2025. *2. Time required from locating failure to replacing a sensor and recovering.

Installation requires no special skills, shortening setup and recovery time

No adjustment of indicator orientation required

All models

360° visible indicator for ease of work


The indicator can be seen regardless of the mounting orientation of the proximity sensor, making it easy to check the detection status.

Previous models

The indicator is invisible depending on the orientation of the installed sensor. When the sensor is installed in the innermost corner of equipment, the detection status cannot be checked.




The high-brightness LED indicator is visible from 360°, allowing easy confirmation of the detection status.



The 360° visible indicator reduces adjustment time.

Note: The image is of the 2-wire model



No distance adjustment required during replacement

Ouadruple/triple distance model


Simple 10-second*1 replacement using e-jig

Virtually anyone can easily fix the proximity sensor in the same position, greatly reducing replacement time.

Previous models

A lot of time is required to optimize the distance.

The adjustment position varies depending on skills, making detection unstable.



3. Loosen the nut and adjust the distance.

E2E NEXT

Replacement time is reduced significantly to approximately 10 seconds*1.


Anyone can mount the sensor in the same position without adjustment.



Patented

The O-ring blocks the ingress of foreign matter, including cutting oil, into the e-jig and ensures positioning precision (IP67G).

- *1. Time required to adjust the distance during sensor installation. Based on Omron investigation.
- *2. "Patent Pending" means that we applied for a patent in Japan, and "Patented" means that we obtained a patent in Japan. (As of September 2022)




A wide range of applications facilitate equipment design

Downsize equipment

Smaller sensors for same sensing distance

Quadruple/triple distance model

The increased sensing distance allows you to use one size smaller sensors without reducing sensing distance, which helps save installation space.



Smaller proximity sensors can be installed closer to each other thanks to their shorter mutual interference distance.



*1. Quadruple and triple distance models.

Note: The sensing distance is for the DC 2-wire, M12 triple distance model.

Bring IoT to equipment


Predictive maintenance by detecting changes in equipment using IO-Link

3-wire model

By connecting IO-Link proximity sensors to the IO-Link master, you can monitor the equipment status in real time, leading to predictive maintenance.


When workpiece is too close to sensor

IO-Link allows the sensor to output measured values for monitoring in order to detect that a workpiece is too close to the sensor and avoid collision.



When workpiece is too far from sensor


IO-Link allows the sensor to output measured values for monitoring in order to detect that a workpiece is too far from the sensor and prevent false detection.



Detection of proximity sensor failure with 2-output models

3-wire model

Failure can be detected by wiring two outputs, NO (Normally Open) and NC (Normally Closed), without using IO-Link.



Improve environmental resistance of machines

Proven 2-year oil resistance to brought by cable with enhanced oil resistance

All models

Unexpected failures caused by cutting oil, which account for approximately 30%*3 of unexpected component failures, can be reduced.

Previous models

The cable is damaged by cutting oil.



The PUR cable was cracked in environments where water-soluble cutting oil is used.

IP67G

Oil type	N3 (water-insoluble cutting oil)
Evaluation time	48 hours
Evaluation temperature	Room temperature
Dilution concentration	_
Criteria	Appearance and performance



(Illustration)

E2E NEXT

Tests to IP67G and our oil-resistant component evaluation standards have proven that the E2E NEXT Series withstands oil for two years*2.



The E2E NEXT Proximity Sensors using a PVC cable with enhanced oil resistance have been evaluated according to IP67G (JIS C 0920) and our own, even stricter evaluation standards for oil-resistant components.

Omron's oil-resistant component evaluation standards

Oil type	A1 (water-soluble cutting oil)
Evaluation time	1,000 hours of machining
Evaluation temperature	55°C
Dilution concentration	Undiluted
Criteria	Appearance, performance, and no label text loss





(Illustration)

Eight representative types of tested cutting oil

Test oil type	JIS classification	Oil
Water-soluble cutting oil	A1	Yushiroken EC50T-3 YushirokenFGE366 YushirokenFX90
	A2	YushirokenFGM427 YushirokenFGS700
cutting on	A3	YushirokenFGC950PR
Water-insoluble	N3	Yushiron Cut Abas BZ224K
cutting oil	N4	Yushiron Cut Abas KZ440

Pre-wired connector models have also been proven to provide stable operation for 2 years*2 by same tests

Pre-wired connector models, which use a highly oil-resistant PVC cable and our unique technology, have been proven to withstand oil for two years*2.

Patented *

The Smartclick connector allows anyone to tighten cables with the same torque and blocks the ingress of cutting oil.

©martclick

Note: Smartclick is a registered trademark of OMRON Corporation.

- *2. Tested on cutting oil specified in JIS K 2241:2000 ("2-year oil resistance" refers to median values (=Typical values) of the product designs and the oil-resistance performance evaluation results. Products to be shipped will have around 2 years of oil resistance; actual oil resistance will vary depending on the product.)The pre-wired connector model has been proven to offer 2 years of oil resistance when mated with the XS5 NEXT Round Oil-resistant Connector. 3-wire connector models (M1, M3, M5) have not been tested.
- *3. Based on Omron investigation in June 2016.
- *4. "Patent Pending" means that we applied for a patent in Japan, and "Patented" means that we obtained a patent in Japan. (As of September 2022)

E2E NEXT Series Functions and Specifications

						DC 2-wire				
				Shie	elded	Unshielded				
			W. Control of the Con		HISTORY		STATE OF THE PARTY		Mark Control of the C	
Main functi	ione and ene	Model	Triple distance	Double distance	Standard	Single distance	Triple distance	Double distance	Standard	
Widili Tulleti	ons and spe	M8	3mm	_	2mm	1.5mm	6mm	_	4mm	
Detection performance In	O-main n		M12	7mm	4mm	3mm	2.5mm	10mm	_	8mm
	Sensing distance	M18	11mm	8mm	7mm	5mm	20mm	16mm	14mm	
		M30	20mm	15mm	10mm	_	40mm	30mm	20mm	
performance		Flush with surface	_	_	•	•	_	_	_	
	Installation	Flush with surface using nut	• *1	•	•	•	_	_	_	
	360° visib	le indicator	•	•	•	•	•	•	•	
Usability	360° visible indicator e-jig		• *3	_	_	_	_	_	_	
Industrial	Detection level and temp. I visualization with IO-Link		_	_	_	_	_	_	_	
loT enabled	2-outp	ut model	_	_	_	_	_	_	_	
Environmental resistance	Oil resistance	2 years	•	•	•	•	•	•	•	
	Datasheet		P.14 ~	P.25 ~	P.24 ~	P.25 ~	P.14 ~	P.25 ~	P.24 ~	

			DC 3	-wire				
	Shie	lded		Unshielded				
		A Property of the Parket of th		a)		A The same		
Quadruple distance	Triple distance	Double distance	Single distance	Quadruple distance	Triple distance	Double distance	Single distance	
4mm	3mm	2mm	1.5mm	8mm	6mm	4mm	2mm	
9mm	6mm	4mm	2mm	16mm	10mm	8mm	5mm	
14mm	12mm	8mm	5mm	30mm	20mm	16mm	10mm	
23mm	22mm	15mm	10mm	50mm	40mm	30mm	18mm	
_	_	• *2	•	_	_	_	_	
_	• *1	•	•	_	_	_	_	
•	•	•	•	•	•	•	•	
• *3	• *3	_	_	_	_	_	_	
•	•	•	•	•	•	•	•	
_	•	•	•	_	•	•	•	
•	•	•	•	•	•	•	•	
P.40 ~	P.43 ~	P.47 ~	P.51 ~	P.42 ~	P.45 ~	P.49 ~	P.53 ~	

^{*1.} The nuts are longer than other models. Please refer to the datasheet for details.

^{*2.} Applicable to some models. Please refer to datasheet for details. *3. Pre-wired models only.

MEMO

Proximity Sensor

E2E NEXT Series

DC 2-wire (Triple distance model)

Long-distance Detection Prevents Unexpected Facility Stoppages

- The world's longest sensing distance*1
 Nearly double the sensing distance of previous
- With high-brightness LED, the indicator is visible anywhere from 360°.
- Only 10 Seconds*2 to Replace a Proximity Sensor with the "e-jig" (Mounting Sleeve).
- Cables with enhanced oil resistance enabled 2-year oil resistance*3.
- IP69K compliant for water resistance and wash resistance.
- UL certification (UL60947-5-2) and CSA certification (CSA C22.2 UL60947-5-2-14)
- *1. Based on October 2025 OMRON investigation.
- *2. Time required to adjust the distance when installing a Sensor. Based on OMRON investigation.
- *3. Refer to page 16 for details.



Be sure to read Safety Precautions on page 19.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Model Number Legend

E2E - X (1) (2) D (3) (4) (5) - (6) - (7) (8) (9)

No.	Classification	Code	Meaning
(1)	Sensing distance	Number	Sensing distance (Unit: mm) (R: Indication of decimal point)
(2)	Shielding	Blank	Shielded Models
(2)	Sillelaing	М	Unshielded Models
(2)	Operation mode	1	Normally open (NO)
(3)	Operation mode	2	Normally closed (NC)
(4)	Pody size	Blank	Standard
(4)	Body size	L	Long Body
		8	M8
(E)	Size	12	M12
(5)	Size	18	M18
		30	M30
		Blank	Pre-wired Models
(6)	Connecting method	M1TGJ	M12 Pre-wired Smartclick Connector Models
		M1TGJR	M12 Pre-wired Smartclick Connector Models (Robot (bending-resistant) PVC cable)
(7)	Dalarita.	Blank	Polarity
(7)	Polarity	Т	No polarity
(8)	Cable specifications (Only shown in the model		Standard PVC cable
(0)	number of Pre-wired Models.)	R	Robot (bending-resistant) PVC cable
(9)	Cable length	Number M	Cable length

Note: 1. The purpose of this model number legend is to provide understanding of the meaning of specifications from the model number.

2. Pin arrangements vary depending on the model. Refer to I/O Circuit Diagrams on page 18 for details.

Ordering Information

Sensors

DC 2-wire (Triple distance model) [Refer to Dimensions on page 21.] Shielded Models *1

Size	Connection method	Delevity		Model	
(Sensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: NC	
	Deci.c.d (0. m) *0.*0	Yes	E2E-X3D18 2M	E2E-X3D28 2M	
M8	Pre-wired (2 m) *2 *3	No	E2E-X3D18-T 2M	E2E-X3D28-T 2M	
(3 mm)	M12 Pre-wired	Yes	E2E-X3D18-M1TGJ 0.3M	E2E-X3D28-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X3D18-M1TGJ-T 0.3M	E2E-X3D28-M1TGJ-T 0.3M	
M12 (7 mm)	Dro wined (2 m) *2 *2	Yes	E2E-X7D112 2M	E2E-X7D212 2M	
	Pre-wired (2 m) *2 *3	No	E2E-X7D112-T 2M	E2E-X7D212-T 2M	
	M12 Pre-wired	Yes	E2E-X7D112-M1TGJ 0.3M	E2E-X7D212-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X7D112-M1TGJ-T 0.3M	E2E-X7D212-M1TGJ-T 0.3M	
	Deci.e.d (0. e.) +0.+0	Yes	E2E-X11D118 2M	E2E-X11D218 2M	
M18	Pre-wired (2 m) *2 *3	No	E2E-X11D118-T 2M	E2E-X11D218-T 2M	
(11 mm)	M12 Pre-wired	Yes	E2E-X11D118-M1TGJ 0.3M	E2E-X11D218-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X11D118-M1TGJ-T 0.3M	E2E-X11D218-M1TGJ-T 0.3M	
	Dro wired (2 m) *2 *2	Yes	E2E-X20D130 2M	E2E-X20D230 2M	
M30	Pre-wired (2 m) *2 *3	No	E2E-X20D130-T 2M	E2E-X20D230-T 2M	
(20 mm)	M12 Pre-wired	Yes	E2E-X20D130-M1TGJ 0.3M	E2E-X20D230-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X20D130-M1TGJ-T 0.3M	E2E-X20D230-M1TGJ-T 0.3M	

Unshielded Models

Size	Connection method	Delevity	1	Model	
(Sensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: NC	
	Dro wired (2 m) *2 *2	Yes	E2E-X6MD18 2M	E2E-X6MD28 2M	
M8	Pre-wired (2 m) *2 *3	No	E2E-X6MD18-T 2M	E2E-X6MD28-T 2M	
(6 mm)	M12 Pre-wired	Yes	E2E-X6MD18-M1TGJ 0.3M	E2E-X6MD28-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X6MD18-M1TGJ-T 0.3M	E2E-X6MD28-M1TGJ-T 0.3M	
	D	Yes	E2E-X10MD112 2M	E2E-X10MD212 2M	
M12	Pre-wired (2 m) *2 *3	No	E2E-X10MD112-T 2M	E2E-X10MD212-T 2M	
(10 mm)	M12 Pre-wired	Yes	E2E-X10MD112-M1TGJ 0.3M	E2E-X10MD212-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X10MD112-M1TGJ-T 0.3M	E2E-X10MD212-M1TGJ-T 0.3M	
	D	Yes	E2E-X20MD1L18 2M	E2E-X20MD2L18 2M	
M18	Pre-wired (2 m) *2 *3	No	E2E-X20MD1L18-T 2M	E2E-X20MD2L18-T 2M	
(20 mm)	M12 Pre-wired	Yes	E2E-X20MD1L18-M1TGJ 0.3M	E2E-X20MD2L18-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X20MD1L18-M1TGJ-T 0.3M	E2E-X20MD2L18-M1TGJ-T 0.3M	
	D	Yes	E2E-X40MD1L30 2M	E2E-X40MD2L30 2M	
M30	Pre-wired (2 m) *2 *3	No	E2E-X40MD1L30-T 2M	E2E-X40MD2L30-T 2M	
(40 mm)	M12 Pre-wired	Yes	E2E-X40MD1L30-M1TGJ 0.3M	E2E-X40MD2L30-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X40MD1L30-M1TGJ-T 0.3M	E2E-X40MD2L30-M1TGJ-T 0.3M	

^{*1.} When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 20.

^{*2.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2E-X3D18 5M)
*3. Models with a 2-m or 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X3D18-R 2M/E2E-X3D18-R 5M)

^{*4.} Models with M12 Pre-wired Smartclick Connectors and robot (bending-resistant) cables are also available with "R" in the model number. (Example: E2E-X3D18-M1TGJR 0.3M/E2E-X3D18-M1TGJR-T 0.3M)

Accessories (Sold Separately)

e-jig (Mounting Sleeves) [Refer to Dimensions on page 22.]

A Mounting Bracket is not provided with the Sensor. It must be ordered separately as required.

Appearance	Model	Applicable Sensor size	Applicable Sensor type
and the same	Y92E-J8S12	M8	Triple distance model
	Y92E-J12S18	M12	Shielded models Pre-wired models
	Y92E-J18S30	M18	Standard body-sized

Nut Sets

A Nut Set is included with the Sensor. Order a Nut Set when required, e.g., if you lose the nuts.

Model	Applicable Sensors	Applicable Sensor diameter	Set contents
Y92E-NWM08-E2EN		M8	Clamping nuts (bronze with nickel plating): 2
Y92E-NWM12-E2EN	E2E NEXT Series	M12	Toothed washer (iron with zinc plating): 2
Y92E-NWM18-E2EN	 Triple distance model (Shielded models) 	M18	
Y92E-NWM30-E2EN		M30	
Y92E-NWM08-E2E		M8	Clamping nuts (bronze with nickel plating): 2
Y92E-NWM12-E2E	E2E NEXT Series	M12	Toothed washer (iron with zinc plating): 1
Y92E-NWM18-E2E	Triple distance model (Unshielded models)	M18	
Y92E-NWM30-E2E		M30	

Sensor I/O Connectors (Sold Separately)

For details of the connector, refer to XS5 NEXT Series Round Oil-resistant Connectors (M12 Smartclick) on page 84. For details of the connector, refer to XS5 Series Round Water-resistant Connectors (M12 Smartclick) on page 87.

Ratings and Specifications

DC 2-wire (Triple distance model)

	Size	N	18	М	112	М	18	М	30	
	Shielded	Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded	
Item	Model	E2E-X3D□	E2E-X6MD□	E2E-X7D□	E2E-X10MD□	E2E-X11D□	E2E-X20MD□	E2E-X20D□	E2E-X40MD□	
Sensing d	distance	3 mm ±10%	6 mm ±10%	7 mm ±10%	10 mm ±10%	11 mm ±10%	20 mm ±10%	20 mm ±10%	40 mm ±10%	
Setting di	istance *1	0 to 2.4 mm	0 to 4.8 mm	0 to 5.6 mm	0 to 8 mm	0 to 8.8 mm	0 to 16 mm	0 to 16 mm	0 to 32 mm	
Differentia	al travel	15% max. of se	nsing distance							
Detectable	e object	Ferrous metal (The sensing dista	ance decreases v	with non-ferrous r	netal. Refer to E	ngineering Data	on page 17.)		
Standard	sensing object	Iron, 9 × 9 × 1 mm	Iron, 18 × 18 × 1 mm	Iron, 21 × 21 × 1 mm	Iron, 30 × 30 × 1 mm	Iron, 33 × 33 × 1 mm	Iron, 60 × 60 × 1 mm	Iron, 60 × 60 × 1 mm	Iron, 120 x 120 x 1 mm	
Response	e frequency *2	350 Hz	250 Hz	350 Hz	200 Hz	250 Hz	200 Hz	200 Hz	50 Hz	
Power su	pply voltage	10 to 30 VDC, (including 10% rip	pple (p-p))						
Leakage o	current	0.8 mA max.								
Control	Load current	3 to 100 mA								
output	Residual voltage		arity: 3 V max. (Load current: 100 mA, Cable length: 2 m) polarity: 5 V max. (Load current: 100 mA, Cable length: 2 m)							
Indicator D1 Models: Operation indicator (orange), Setting indicator (green) D2 Models: Operation indicator (orange)										
Operation mode D1 Models: NO D2 Models: NC Refer to the timing charts under I/O Circuit Diagrams on page 18 for details.										
Protection	n circuits	Surge suppress	or, Load short-ci	rcuit protection						
Ambient t range	ent temperature Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)									
Ambient h	humidity range	Operating and	Storage: 35% to 9	95% (with no con	densation)					
Temperat	ure influence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C				±20% max. of sensing distance at 23°C in the temperature range of -25 to 70°C	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C	±20% max. of sensing distance at 23°C in the temperature range of -25 to 70°C		
Voltage in	nfluence	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range								
Insulation	resistance	50 M Ω min. (at 500 VDC) between current-carrying parts and case								
Dielectric	strength	1,000 VAC, 50/	60 Hz for 1 minu	te between curre	nt-carrying parts	and case				
Vibration (destructi	resistance ion)	10 to 55 Hz, 1.5	5-mm double amp	olitude for 2 hours	s each in X, Y, ar	nd Z directions				
Shock res (destructi		500 m/s ² 10 tim and Z directions	es each in X, Y,	1,000 m/s ² 10 t	mes each in X, Y, and Z directions					
Degree of	f protection	Component Eva	els/Pre-wired Cor aluation Standard 10050 PART9) IP	ds *4 (Cutting oil	P67 (IEC 60529) type: specified in	, IP67G *3 (JIS C JIS K 2241:2000	0920 Annex 1) , Temperature: 3	Passed OMRON' 35 °C max.) and I	s Oil-resistant SO 20653 (old	
Connectir	ng method	Pre-wired Mode	els (Standard cab	le length: 2 m) a	nd Pre-wired Cor	nector Models (S	Standard cable le	ength: 0.3 m)		
Weight	Pre-wired Models	Approx. 60 g		Approx. 70 g		Approx. 130 g	Approx. 150 g	Approx. 180 g	Approx. 210 g	
(packed state)	Pre-wired Connector Models	Approx. 30 g		Approx. 40 g		Approx. 70 g	Approx. 90 g	Approx.110 g	Approx. 140 g	
	Case	Nickel-plated brass	Stainless steel (SUS303)	Nickel-plated b	rass					
	Sensing surface	Polybutylene te	rephthalate (PBT)						
Materials	Clamping nuts	Nickel-plated br	ass							
	Toothed washer	Zinc-plated iron								
	Cable	Vinyl chloride (F	PVC)							
Accessor			ual, Clamping nu							
(A	an Canaar within t				1.50/ : 01/					

^{*1.} Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).

^{*2.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

^{*3.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).


The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

^{*4.} The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.
2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value).
The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly.
The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

Engineering Data (Reference Value)

Sensing Area


Triple distance model **Shielded Models**



Influence of Sensing Object Size and Materials


Triple distance model **Shielded Models**

Size: M8 E2E-X3D□8




Unshielded Models

Size: M8 E2E-X6MD□8




Leakage Current


Triple distance model **Shielded / Unshielded Models** E2E-X□(M)D□(-T)




Unshielded Models



Size: M12 E2E-X7D□12




Size: M12 E2E-X10MD□12




Residual Output Voltage


Triple distance model **Shielded / Unshielded Models** $E2E-X\square(M)D\square(-T)$




Size: M18 E2E-X11D□18




Size: M18 E2E-X20MD□L18



Size: M30 E2E-X20D□30




Size: M30 E2E-X40MD□L30




I/O Circuit Diagrams

DC 2-wire Models (Triple distance model)



Note: For the Pre-wired Connector Models, the core wire color and pin number are different.

Connector Pin Arrangement



Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

∆WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

General prohibition Indicates the instructions of unspecified prohibited action.
Caution, explosion Indicates the possibility of explosion under specific conditions.

MARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Risk of explosion.


Do not connect sensor to AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- Do not use the product in an environment where flammable or explosive gas is present.
- 2. Do not attempt to disassemble, repair, or modify the product.
- Do not use a voltage that exceeds the rated operating voltage range. Applying a voltage that is higher than the operating voltage range may result in damage or burnout.
- **4.** Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or burnout.
- 5. If the power supply is connected directly without a load, the internal elements may explode or burn. Be sure to insert a load when connecting the power supply.



Precautions for Correct Use

Do not use this product under ambient conditions that exceed the ratings.


Operating Environment

- Do not install the product in the following locations.
 Doing so may result in product failure or malfunction.
 - Outdoor locations directly subject to sunlight, rain, snow, water droplets, or oil.
 - (2) Locations subject to atmospheres with chemical vapors, in particular solvents and acids.
 - (3) Locations subject to corrosive gases.
- 2. The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com) for typical measures.
- 3. Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ratio recommended by its manufacturer
 - · Usage in oil or water is prohibited

Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.


AND Connection of Proximity Sensors

Two or more sensors cannot be connected in series on the AND circuit. Use them via a relay as shown on the figure.



OR Wiring of Proximity Sensors

As a general principle, two or more sensors cannot be used in parallel on the OR circuit. It is possible only when sensors do not operate simultaneously and loads do not need to be maintained. When loads need to be maintained, use the sensors via a relay as shown on the figure.




Design

Influence of Surrounding Metal

When mounting the Proximity Sensor using a nut, only use the provided nut. And ensure that the minimum distances given in the following table are maintained.

When mounting the Proximity Sensor using a nut, only use the provided nut. Nuts that are supplied along with each Sensor are different. Refer to Dimensions for details on shapes.



(Unit: mm)

Shielded

Type	Size	Model	L	d	D	m	n
Triple distance model	M8	E2E-X3D□8	0	20	2	9	18
	M12	E2E-X7D□12	0	20	4	18	20
	M18	E2E-X11D□18	0	50	4	33	54
	M30	E2E-X20D□30	0	70	8	60	90


Unshielded

Туре	Size	Model	L	d	D	m	n
	M8	E2E-X6MD□8	10	30	13	18	30
Triple distance	M12	E2E-X10MD□12	16	50	20	30	50
model	M18	E2E-X20MD□18	31	90	35	60	80
M30		E2E-X40MD□30	50 *1	170	55 *2	120	140

^{*1.} If you use the M30 Triple distance model of Unshielded Model, the panel thickness (t) is 4 mm or less.

*2. Cannot be mounted if countersunk holes are used.

When the Proximity Sensor is mounted in metal, ensure that the minimum distances given in the following table are maintained.



(Unit: mm)

Shielded


Туре	Size	Model	ı	d	D	m	n
	M8	E2E-X3D□8	2	20	2	9	18
Triple distance	M12	E2E-X7D□12	4	20	4	18	20
model	M18	E2E-X11D□18	4	50	4	33	54
	M30	E2E-X20D□30	8	70	8	60	90

Unshielded

Туре	Size	Model	ı	d	D	m	n
	M8	E2E-X6MD□8	13	30	13	18	30
Triple M12	E2E-X10MD□12	20	50	20	30	50	
model	M18	E2E-X20MD□18	35	90	35	60	80
	M30	E2E-X40MD□30	55	170	55	120	140

Mutual Interference

When the Proximity Sensor is embedded in metal, ensure that the minimum distances given in the following table are maintained.



Shielded

(Unit: mm)

Туре	Size	Model	Α	В
	M8	E2E-X3D□8	25	20
Triple distance model M12 M18 M30	M12	E2E-X7D□12	40	30
	E2E-X11D□18	70	45	
	M30	E2E-X20D□30	140	70

Unshielded

Туре	Size	Model	Α	В
Triple distance	М8	E2E-X6MD□8	80	60
	M12	E2E-X10MD□12	120	100
model	M18	E2E-X20MD□18	200	120
	M30	E2E-X40MD□30	380	280


Mounting

Tightening Force

Do not tighten the sensor mounting nuts with excessive force. Secure the mounting nuts to the corresponding torque values in the following table.







Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table. (A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)

2. The following strengths assume washers are being used.

Triple distance model

	Model	Part	Part B	
	Model	Dimension (mm)	Torque	Torque
M8	Shielded	9	4 N·m	10 N·m
IVIO	Unshielded	3	4 IN-III	10 N-III
M12	Shielded	16	8 N∙m	15 N·m
WIZ	Unshielded	9	6 N·m	ID IN-III
M18	Shielded	16	15 N⋅m	60 N·m
IVIIO	Unshielded	3	13 14-111	60 N-III
1420	Shielded	23	40 N⋅m	80 N·m
M30	Unshielded	8	40 N·M	80 N-III

Dimensions

Sensor DC 2-wire (Triple distance model)

Pre-wired Models Pre-wired Connector Models (Shielded)




Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.

Pre-wired Models Pre-wired Connector Models (Unshielded)




Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.

E2E-X3D₈




4-dia. vinyl-insulated round cable with 2 conductors (Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm), Standard length: 2 m

E2E-X6MD₈ 15 dia




4-dia. vinyl-insulated round cable with 2 conductors (Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm), Standard length: 2 m


E2E-X7D□12









E2E-X11D 18




E2E-X20MD L18



E2E-X20D □30



E2E-X40MD L30



*1. D1 Models: Operation indicator (Orange), Setting indicator (Green) / D2 Models: Operation indicator (Orange)

Pre-wired Connector Models (-M1TGJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

(+)	Dimensions	F (mm)
4	M8	8.5 dia. +0.5
FI	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



Dimensions	R (mm)
M8	12
M12	12
M18	18
M30	10

Wire pullout position




nsions Sc (mm)
18
- (0)
2.5
30


Accessories (Sold Separately)

e-jig (Mounting Sleeves)


Y92E-J8S12



Y92E-J12S18



Y92E-J18S30



Material

Mounting Sleeve	Polyetheretherketone (PEEK) / Polybutylene terephthalate (PBT)			
Mounting Sleeve clamping nut	Polybutylene terephthalate (PBT)			
Sensor lock nut	Polybutylene terephthalate (PBT)			
Sensor lock O-ring	Material combining HNBR and fluororubber			

Tightening Force

	Torque				
Model	Mounting Sleeve clamping nut	Sensor lock nut			
Y92E-J8S12	0.6 N°m	0.6 N°m			
Y92E-J12S18	1.2 N°m	1.2 N m			
Y92E-J18S30	5 N • m	3.5 N°m			

Note: The dimensional control of the threaded part is based on the fit with the accompanying nut.

DC 2-wire (Standard/Double/Single distance model)

Enhanced Usability Enables Installation without Special Skills and Shortens **Commissioning and Recovery Time**

- With high-brightness LED, the indicator is visible anywhere from 360°.
- Cables with enhanced oil resistance enabled 2-year oil resistance*1.
- IP69K compliant for water resistance and wash resistance.
- UL certification (UL60947-5-2) and CSA certification (CSA C22.2 UL60947-5-2-14)
- *1. Refer to page 27 to 29 for details.



Be sure to read Safety Precautions on page 33.







Note: Some models are not certified.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Model Number Legend

E2E - X (1) (2) D (3) (4) (5) - (6) - (7) (8) - (9)

No.	Туре	Code	Meaning				
(1)	Sensing distance	Number	Sensing distance (Unit: mm) (R: Indication of decimal point)				
(2)	Chialding	Blank	Shielded				
(2)	2) Shielding	М	Unshielded				
(2)	Operation made	1	Normally open (NO)				
(3)	Operation mode	2	Normally closed (NC)				
(4)	Oscillation fraguency type	Blank	Standard frequency				
(4)	Oscillation frequency type	5	Different frequency				
(E)	Dody size	Blank	Standard				
(5)	Body size	L	Long-body				
		Blank	Pre-wired Models				
		M1	M12 Connector Models (Old pin arrangement)				
		M1G	M12 Connector Models (IEC pin arrangement)				
		M1J	M12 Pre-wired Standard Connector Models (Old pin arrangement)				
(6)	Connection method	M1GJ	M12 Pre-wired Standard Connector Models (IEC pin arrangement)				
(0)		M1TJ	M12 Pre-wired Smartclick Connector Models (Old pin arrangement)				
		M1TGJ	M12 Pre-wired Smartclick Connector Models (IEC pin arrangement)				
		M1TGJR	M12 Pre-wired Smartclick Connector Models Robot (bending-resistant) cable (IEC pin arrangement)				
		M3G	M8 (4-pin) Connector Models (IEC pin arrangement)				
(7)	Delegit	Blank	Polarity				
(7)	Polarity	Т	No polarity				
(8)	Cable specifications (Only shown in the model	Blank	Standard PVC cable				
(0)	number of Pre-wired Models.)	R	Robot (bending-resistant) PVC cable				
(9)	New model	N	New model This is blank if the cable specification in number (8) is R.				
(10)	Cable length	Number M	Cable length (Applicable to Pre-wired Models and Prewired Connector Models.)				

2. Pin arrangements vary depending on the model. Refer to I/O Circuit Diagrams on page 32 for details.

Ordering Information

Sensors

DC 2-wire (Standard model) [Refer to *Dimensions* on page 35.] Shielded Models

Size	Connection method	Body size	Polarity	Model		
(Sensing distance)	Connection metriod	Body Size	Polarity	Operation mode: NO	Operation mode: NC	
	Pre-wired (2 m)	38 mm	Yes	E2E-X2D1-N 2M *1 *2	E2E-X2D2-N 2M *1 *2	
M8	M12 Pre-wired Smartclick Connector (0.3 m)	38 mm	Yes	E2E-X2D1-M1TGJ 0.3M *4 *5		
(2mm)	M12 Connector	43 mm Yes E2E-X2D1-M1G *5	E2E-X2D1-M1G *5	E2E-X2D2-M1G *5		
	M8 (4-pin) Connector	39 mm	Yes	E2E-X2D1-M3G	E2E-X2D2-M3G	
	Dro wined (2 m)	47 mm	Vee	E2E-X3D1-N 2M *1 *2 *3	E2E-X3D2-N 2M *1 *2 *3	
	Pre-wired (2 m)	69 mm	Yes	E2E-X3D1L 2M *1 *3	E2E-X3D2L 2M *1	
M12	M12 Pre-wired	47 mm	Yes	E2E-X3D1-M1TGJ 0.3M *4 *5		
(3 mm)	Smartclick Connector (0.3 m)	47 mm	No	E2E-X3D1-M1TJ-T 0.3M		
(•)	M12 Pre-wired Standard Connector (0.3 m)	47 mm	No		E2E-X3D2-M1GJ-T 0.3M	
	M12 Connector	48 mm	Yes	E2E-X3D1-M1G *3 *5	E2E-X3D2-M1G *5	
	Pre-wired (2 m)	55 mm	Yes	E2E-X7D1-N 2M *1 *2 *3	E2E-X7D2-N 2M *1 *2 *3	
	Fie-wiled (2 iii)	77 mm	res	E2E-X7D1L 2M *1 *3	E2E-X7D2L 2M *1	
M18	M12 Pre-wired	55 mm	Yes	E2E-X7D1-M1TGJ 0.3M *4 *5		
(7 mm)	Smartclick Connector (0.3 m)	55 11111	No	E2E-X7D1-M1TJ-T 0.3M		
,	M12 Pre-wired Standard Connector (0.3 m)	55 mm	No		E2E-X7D2-M1GJ-T 0.3M	
	M12 Connector	53 mm	Yes	E2E-X7D1-M1G *3 *5	E2E-X7D2-M1G *5	
	Dro wined (2 m)	60 mm	Yes	E2E-X10D1-N 2M *1 *2	E2E-X10D2-N 2M *1 *3	
• • • •	Pre-wired (2 m)	82 mm	res	E2E-X10D1L 2M *1 *3	E2E-X10D2L 2M *1	
M30 (10 mm)	M12 Pre-wired	CO mm-	Yes	E2E-X10D1-M1TGJ 0.3M *3 *4 *5		
(10 1/111)	Smartclick Connector (0.3 m)	60 mm	No	E2E-X10D1-M1TJ-T 0.3M		
	M12 Connector	58 mm	Yes	E2E-X10D1-M1G *3 *5	E2E-X10D2-M1G *5	

Unshielded Models

Size	Connection method	Pody size	Polarity	Me	odel
(Sensing distance)	Connection method	Body size	Polarity	Operation mode: NO	Operation mode: NC
140	Pre-wired (2 m)	38 mm	Yes	E2E-X4MD1 2M *1 *2	E2E-X4MD2 2M *1 *2
M8 (4 mm)	M12 Connector	43 mm	Yes	E2E-X4MD1-M1G *5	E2E-X4MD2-M1G *5
(M8 (4-pin) Connector	39 mm	mm Yes E2E-X4MD1-M3G	E2E-X4MD1-M3G	E2E-X4MD2-M3G
	B : 1/0)	47 mm	Yes	E2E-X8MD1 2M *1 *2	E2E-X8MD2 2M *1 *3
M12	Pre-wired (2 m)	69 mm	res	E2E-X8MD1L 2M *1 *3	E2E-X8MD2L 2M *1
(8 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	47 mm	Yes	E2E-X8MD1-M1TGJ 0.3M *4 *5	
	M12 Connector	48 mm	Yes	E2E-X8MD1-M1G *3 *5	E2E-X8MD2-M1G *5
	5	55 mm	V	E2E-X14MD1 2M *1 *2 *3	E2E-X14MD2 2M *1 *2 *3
M18	Pre-wired (2 m)	77 mm	Yes	E2E-X14MD1L 2M *1 *3	E2E-X14MD2L 2M
(14 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	55 mm	Yes	E2E-X14MD1-M1TGJ 0.3M *4 *5	
	M12 Connector	53 mm	Yes	E2E-X14MD1-M1G *3 *5	E2E-X14MD2-M1G *5
	5	60 mm	Yes	E2E-X20MD1 2M *1 *2 *3	E2E-X20MD2 2M *1 *3
M30	Pre-wired (2 m)	82 mm	res	E2E-X20MD1L 2M *1 *3	E2E-X20MD2L 2M *1
(20 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	60 mm	Yes	E2E-X20MD1-M1TGJ 0.3M *4 *5	
	M12 Connector	58 mm	Yes	E2E-X20MD1-M1G *3 *5	E2E-X20MD2-M1G *5

^{*1.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2E-X2D1-N 5M)

^{*2.} Models with a 2-m or 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X2D1-R 2M/E2E-X2D1-R 5M)

^{*3.} Models with different frequencies are also available. The model number is E2E-X□D□5. (Example: E2E-X3D15-N 2M/E2E-X3D15L 2M)

^{*4.} M12 Pre-wired Standard Connector Models with a 0.3-m cable are also available. The model numbers of models with IEC pin arrangement include "-M1GJ". (Example: E2E-X2D1-M1GJ 0.3M)

The model numbers of models with old pin arrangement include "-M1J". (Example: E2E-X2D1-M1J 0.3M)

Models with old pin arrangement of M12 Pre-wired Smartclick Connector Models are also available. The model numbers include "-M1TJ". (Example: E2E-X3D1-M1TJ 0.3M)

^{*5.} Models with old pin arrangement are also available. The model number is E2E-X□D□-M1. (Example: E2E-X2D1-M1)

Sensors

DC 2-wire (Double distance model) [Refer to *Dimensions* on page 35.] <u>NEW</u> Shielded Models

Size	Connection method	Connection method Body size Polarity		Model	
(Sensing distance)			Operation mode: NO	Operation mode: NC	
M12 (4 mm)	Pre-wired (2 m)	47 mm	No	E2E-X4D1-T 2M *1	E2E-X4D2-T 2M *1
M18 (8 mm)	Pre-wired (2 m)	55 mm	No	E2E-X8D1-T 2M *1	E2E-X8D2-T 2M *1
M30 (15 mm)	Pre-wired (2 m)	60 mm	No	E2E-X15D1-T 2M *1	E2E-X15D2-T 2M *1

Unshielded Models

Size	Connection method	Body size	Polarity -	Model		
(Sensing distance)	Connection method	Bouy Size		Operation mode: NO	Operation mode: NC	
M18 (16 mm)	Pre-wired (2 m)	77 mm	No	E2E-X16MD1L-T 2M *1	E2E-X16MD2L-T 2M	
M30 (30 mm)	Pre-wired (2 m)	82 mm	No	E2E-X30MD1L-T 2M *1	E2E-X30MD2L-T 2M *1	

^{*1.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2E-X4D1-T 5M)

DC 2-wire (Single distance model) [Refer to *Dimensions* on page 38.] Shielded Models

Size	Connection method	Delerity		Model
(Sensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: NC
	Deci.e.d (0 -e.) *0 *0	Yes	E2E-X1R5D1-N 2M	E2E-X1R5D2-N 2M
M8	Pre-wired (2 m) *2 *3	No	E2E-X1R5D1-T-N 2M	E2E-X1R5D2-T-N 2M
(1.5 mm)	M12 Pre-wired	Yes	E2E-X1R5D1-M1TGJ 0.3M	E2E-X1R5D2-M1TGJ 0.3M
	Smartclick Connector (0.3 m) *4	No	E2E-X1R5D1-M1TGJ-T 0.3M	E2E-X1R5D2-M1TGJ-T 0.3M
	Deci.e.d (0e.) *0. *0	Yes	E2E-X2R5D1-N 2M	E2E-X2R5D2-N 2M
M12	Pre-wired (2 m) *2 *3	No E2E-X2R5D1-T-N 2M	E2E-X2R5D1-T-N 2M	E2E-X2R5D2-T-N 2M
(2.5 mm)	M12 Pre-wired	Yes	E2E-X2R5D1-M1TGJ 0.3M	E2E-X2R5D2-M1TGJ 0.3M
	Smartclick Connector (0.3 m) *4	No	E2E-X2R5D1-M1TGJ-T 0.3M	E2E-X2R5D2-M1TGJ-T 0.3M
	Deci.e.d (0 -e.) *0 *0	Yes	E2E-X5D1-N 2M	E2E-X5D2-N 2M
M18	Pre-wired (2 m) *2 *3) *2 *3	E2E-X5D1-T-N 2M	E2E-X5D2-T-N 2M
(5 mm)	M12 Pre-wired	Yes	E2E-X5D1-M1TGJ 0.3M	E2E-X5D2-M1TGJ 0.3M
	Smartclick Connector (0.3 m) *4	No	E2E-X5D1-M1TGJ-T 0.3M	E2E-X5D2-M1TGJ-T 0.3M

^{*1.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2E-X1R5D1-N 5M)

^{*2.} Models with a 2-m or 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X1R5D1-R-N 2M/ E2E-X1R5D1-R-N 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with "R" in the model number. (Example: E2E-X1R5D1-M1TGJR 0.3M/E2E-X1R5D1-M1TGJR-T 0.3M)

Accessories (Sold Separately)

Nut Sets

A Nut Set is included with the Sensor. Order a Nut Set when required, e.g., if you lose the nuts.

Model	Applicable Sensors	Applicable Sensor diameter	Set contents
Y92E-NWM08-E2E	E2E NEXT Series Standard model (Shielded/Unshielded Models) Single distance model (Shielded Models)	M8	
Y92E-NWM12-E2E	E2E NEXT Series Standard model (Shielded/Unshielded Models) Double distance model (Shielded Models) Single distance model (Shielded Models)	M12	Clamping nuts (bronze with nickel plating): 2
Y92E-NWM18-E2E	E2E NEXT Series Standard model (Shielded/Unshielded Models) Double distance model (Shielded/Unshielded Models) Single distance model (Shielded Models)	M18	Toothed washer (iron with zinc plating): 1
Y92E-NWM30-E2E	E2E NEXT Series Standard model (Shielded/Unshielded Models) Double distance model (Shielded/Unshielded Models)	M30	

Sensor I/O Connectors (Sold Separately)

For details of the connector, refer to XS5 NEXT Series Round Oil-resistant Connectors (M12 Smartclick) on page 84. For details of the connector, refer to XS5 Series Round Water-resistant Connectors (M12 Smartclick) on page 87. For details of the connector, refer to XS3 Series Round Water-resistant Connectors (M8) on page 91.

Ratings and Specifications

DC 2-wire (Standard model)

	Size	M8		М	M12		M18		M30		
	Shielded	Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded		
Item	Model	E2E-X2D□	E2E-X4MD□	E2E-X3D□	E2E-X8MD□	E2E-X7D□	E2E-X14MD□	E2E-X10D□	E2E-X20MD□		
Sensing di	istance	2 mm ±10%	4 mm ±10%	3 mm ±10%	8 mm ±10%	7 mm ±10%	14 mm ±10%	10 mm ±10%	20 mm ±10%		
Setting dis	stance *1	0 to 1.6 mm	0 to 3.2 mm	0 to 2.4 mm	0 to 6.4 mm	0 to 5.6 mm	0 to 11.2 mm	0 to 8 mm	0 to 16 mm		
Differentia	I travel	15% max. of sensing distance 10% max. of sensing distance									
Detectable	object		The sensing dista			metal. Refer to E	ngineering Data o	on page 30.)			
Standard s	sensing object	Iron, 8 × 8 × 1 mm	Iron, 20 × 20 × 1 mm	Iron, 12 × 12 × 1 mm	Iron, 30 × 30 × 1 mm	Iron, 18 × 18 × 1 mm	Iron, 30 × 30 × 1 mm	Iron, 30 × 30 × 1 mm	Iron, 54 × 54 × 1 mn		
Response	frequency *2	1.5 kHz	1 kHz	1 kHz	0.8 kHz	0.5 kHz	0.4 kHz	0.4 kHz	0.1 kHz		
•	ply voltage	12 to 24 VDC (including 10% ripple (p-p)), Class 2									
Leakage c		0.8 mA max.	3 7	1 - (1 1 ///							
	Load current	3 to 100 mA									
Control	Residual		ax. (Load current:	100 mA Cable	length: 2 m)						
output	voltage	No polarity: 5 V max. (Load current: 100 mA, Cable length: 2 m) D1 Models: Operation indicator (orange), Setting indicator (green)									
Indicator			eration indicator (eration indicator (indicator (green)						
Operation	mode	D1 Models: NO D2 Models: NC		timing charts und	er I/O Circuit Dia	grams on page 3	2 for details.				
Protection	circuits	Surge suppress	sor, Load short-ci	rcuit protection							
Ambient temperature range Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)											
Ambient h	umidity range	Operating and Storage: 35% to 95% (with no condensation)									
Temperatu	re influence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C									
Voltage inf	fluence	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range									
Insulation	resistance	50 M Ω min. (at 500 VDC) between current-carrying parts and case									
Dielectric s	strength	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case									
Vibration r		10 to 55 Hz, 1.5	5-mm double amp	olitude for 2 hours	s each in X, Y, ar	nd Z directions					
Shock resi		500 m/s ² 10 tim X, Y, and Z dire		1,000 m/s ² 10 ti	imes each in X, \	, and Z direction	S				
Degree of	protection	IP67 (IEC 6052 Passed OMRO	els/Pre-wired Cor 9), IP67G *3 (JIS N's Oil-resistant (I ISO 20653 (old	C 0920 Annex 1	uation Standards		pe: specified in Jl	S K 2241:2000,	Temperature:		
Connectin	g method		els (Standard cab Models and M12			ctor Models (Stan	dard cable length	n: 0.3 m),			
	Pre-wired Models	Approx. 60 g		Approx. 70 g		Approx. 130 g	Approx. 150 g	Approx. 180 g	Approx. 210 g		
Weight *5 (packed state)	Pre-wired Connector Models	Approx. 30 g		Approx. 40 g		Approx. 70 g	Approx. 90 g	Approx. 110 g	Approx. 140 g		
	Connector Models	Approx. 40 g (M8/M12 Conn	ector)	Approx. 55 g		Approx. 85 g	Approx. 80 g	Approx. 160 g	Approx. 150 g		
	Case	M8 Size: Stainl	ess steel (SUS30	3), M12/M18/M3	0 Size: Nickel-pla	ated brass		1			
	Sensing surface	Polybutylene te	rephthalate (PBT	<u></u>							
Materials	Clamping nuts	Nickel-plated b	rass								
	Toothed washer	Zinc-plated iron	1								
	Cable	Vinyl chloride (I	PVC) Note: Ma	terial of Pre-wire	d Models and Pre	e-wired Connecto	r Models.				
Accessorie	es	Instruction man	ual, Clamping nu	ts, Toothed wash	ner						
	e Sensor within t					avaant D2 Mac	dala)				

^{*1.} Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).

^{*2.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard.

^{*3.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards). The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

^{*4.} The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards. 2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value). The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

^{*5.} Weight of the standard body-sized model.

DC 2-wire (Double distance model)

Control output	object cy *2 age oad current	Iron, 12 × 12 × 1 mm 1 kHz 12 to 24 VDC (including 0.8 mA max. 3 to 100 mA 5 V max. (Load current	Iron, 18 x 18 x 1 mm 0.5 kHz g 10% ripple (p-p)), Clas	Shielded E2E-X16MD 16 mm ±10% 0 to 12.8 mm s with non-ferrous metal Iron, 45 × 45 × 1 mm 0.4 kHz is 2	Shielded E2E-X15D□ 15 mm ±10% 0 to 12 mm Refer to Engineering D Iron, 30 × 30 × 1 mm 0.25 kHz	Unshielded E2E-X30MD□ 30 mm ±10% 0 to 24 mm Pata on page 30.) Iron, 70 × 70 × 1 mm 0.1 kHz			
Sensing distance Setting distance *1 Differential travel Detectable object Standard sensing o Response frequenc Power supply voltage Leakage current Control output Re	object cy *2 age oad current	4 mm ±10% 0 to 3.2 mm 15% max. of sensing di Ferrous metal (The sen Iron, 12 × 12 × 1 mm 1 kHz 12 to 24 VDC (including 0.8 mA max. 3 to 100 mA 5 V max. (Load current	8 mm ±10% 0 to 6.4 mm istance using distance decreases Iron, 18 × 18 × 1 mm 0.5 kHz g 10% ripple (p-p)), Clas	16 mm ±10% 0 to 12.8 mm s with non-ferrous metal lron, 45 × 45 × 1 mm 0.4 kHz	15 mm ±10% 0 to 12 mm Refer to Engineering D Iron, 30 × 30 × 1 mm	30 mm ±10% 0 to 24 mm Pata on page 30.) Iron, 70 × 70 × 1 mm			
Setting distance *1 Differential travel Detectable object Standard sensing o Response frequenc Power supply voltage Leakage current Control output Re	object cy *2 age oad current	0 to 3.2 mm 15% max. of sensing differrous metal (The sensing of the sensing differrous metal (The sensing of the sensing of t	0 to 6.4 mm istance sing distance decreases Iron, 18 × 18 × 1 mm 0.5 kHz g 10% ripple (p-p)), Clas	0 to 12.8 mm s with non-ferrous metal lron, 45 × 45 × 1 mm 0.4 kHz	0 to 12 mm Refer to Engineering D Iron, 30 × 30 × 1 mm	0 to 24 mm Pata on page 30.) Iron, 70 × 70 × 1 mm			
Differential travel Detectable object Standard sensing o Response frequenc Power supply voltage Leakage current Control output Re	object cy *2 age oad current	15% max. of sensing di Ferrous metal (The sen Iron, 12 x 12 x 1 mm 1 kHz 12 to 24 VDC (including 0.8 mA max. 3 to 100 mA 5 V max. (Load current	istance nsing distance decreases Iron, 18 × 18 × 1 mm 0.5 kHz g 10% ripple (p-p)), Clas	s with non-ferrous metal Iron, 45 × 45 × 1 mm 0.4 kHz	Refer to Engineering D	Pata on page 30.) Iron, 70 × 70 × 1 mm			
Detectable object Standard sensing o Response frequenc Power supply voltage Leakage current Control output Re	cy *2 age oad current	Ferrous metal (The ser Iron, 12 x 12 x 1 mm 1 kHz 12 to 24 VDC (including 0.8 mA max. 3 to 100 mA 5 V max. (Load current	Iron, 18 x 18 x 1 mm 0.5 kHz g 10% ripple (p-p)), Clas	Iron, 45 × 45 × 1 mm 0.4 kHz	Iron, 30 × 30 × 1 mm	Iron, 70 × 70 × 1 mm			
Standard sensing o Response frequenc Power supply voltage Leakage current Control output Re	cy *2 age oad current	Iron, 12 × 12 × 1 mm 1 kHz 12 to 24 VDC (including 0.8 mA max. 3 to 100 mA 5 V max. (Load current	Iron, 18 × 18 × 1 mm 0.5 kHz g 10% ripple (p-p)), Clas	Iron, 45 × 45 × 1 mm 0.4 kHz	Iron, 30 × 30 × 1 mm	Iron, 70 × 70 × 1 mm			
Response frequence Power supply voltage Leakage current Control output Re	cy *2 age oad current	1 kHz 12 to 24 VDC (including 0.8 mA max. 3 to 100 mA 5 V max. (Load current	0.5 kHz g 10% ripple (p-p)), Clas	0.4 kHz	,	· · · · · · · · · · · · · · · · · · ·			
Power supply voltage Leakage current Control output Re	age oad current	12 to 24 VDC (including 0.8 mA max. 3 to 100 mA 5 V max. (Load current	g 10% ripple (p-p)), Clas		0.25 kHz	0.1 kHz			
Leakage current Control output Lo	oad current	0.8 mA max. 3 to 100 mA 5 V max. (Load current		s 2					
Control output Re		3 to 100 mA 5 V max. (Load current	: 100 mA, Cable length:						
Control output Re		5 V max. (Load current	: 100 mA, Cable length:						
Re	esidual voltage	,	: 100 mA, Cable length:	3 to 100 mA					
Indicator		D1 Models: Operation i	Residual voltage 5 V max. (Load current: 100 mA, Cable length: 2 m)						
		D2 Models: Operation i	ndicator (orange), Settir ndicator (orange)	ng indicator (green)					
Operation mode		D1 Models: NO Ref	er to the timing charts ur	nder I/O Circuit Diagram	s on page 32 for details.				
Protection circuits		Surge suppressor, Load short-circuit protection							
Ambient temperatur	ıre range	Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)							
Ambient humidity ra	range	Operating and Storage: 35% to 95% (with no condensation)							
Temperature influer	ence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C							
Voltage influence		±1% max. of sensing distance at rated voltage in the rated voltage ±15% range							
Insulation resistance	се	50 M Ω min. (at 500 VDC) between current-carrying parts and case							
Dielectric strength		1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case							
Vibration resistance	e (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions							
Shock resistance (d	destruction)	500 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions							
Degree of protection	on	IP67 (IEC 60529), IP67 Passed OMRON's Oil-r				in JIS K 2241:2000,			
Connecting method	d	Pre-wired Models (Star	ndard cable length: 2 m)	, Pre-wired Connector M	lodels (Standard cable le	ength: 0.3 m)			
Weight	re-wired Models	Approx. 70 g	Approx. 130 g	Approx. 150 g	Approx. 180 g	Approx. 210 g			
(packed state) Pro	re-wired Connector lodels	Approx. 40 g	Approx. 70 g	Approx. 90 g	Approx. 110 g	Approx. 140 g			
Ca	ase	Nickel-plated brass				-			
Se	ensing surface	Polybutylene terephtha	late (PBT)						
Materials Cla	lamping nuts	Nickel-plated brass							
То	oothed washer	Zinc-plated iron							
Ca	able	Vinyl chloride (PVC)							
Accessories		Instruction manual, Cla	mping nuts, Toothed wa	sher					

^{*1.} Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).

^{*2.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard.

^{*3.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

^{*4.} The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.

2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value).

The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

DC 2-wire (Single distance model)

Size		M8	M12	M18				
	Shielded		Shielded	1				
Item	Model	E2E-X1R5D□	E2E-X2R5D□	E2E-X5D□				
Sensing distance	•	1.5 mm ±10%	2.5 mm ±10%	5 mm ±10%				
Setting distance	*1	0 to 1.2 mm	0 to 2 mm	0 to 4 mm				
Differential travel		10% max. of sensing distance	10% max. of sensing distance					
Detectable object		Ferrous metal (The sensing distance decreases with non-ferrous metal. Refer to Engineering Data on page 30.)						
Standard sensing	g object	Iron, 10 × 10 × 1 mm	Iron, 12 × 12 × 1 mm	Iron, 18 × 18 × 1 mm				
Response freque	ncy *2	250 Hz	250 Hz	250 Hz				
Power supply vo	Itage	10 to 30 VDC, (including 10% ripple (p	p-p))					
Leakage current		0.8 mA max.						
	Load current	3 to 100 mA						
Control output	Residual voltage	olarity: 3 V max. (Load current: 100 mA, Cable length: 2 m) lo polarity: 5 V max. (Load current: 100 mA, Cable length: 2 m)						
Indicator		D1 Models: Operation indicator (orang D2 Models: Operation indicator (orang						
Operation mode		D1 Models: NO D2 Models: NO Refer to the timing charts under <i>I/O Circuit Diagrams</i> on page 32 for details.						
Protection circuit	ts	Surge suppressor, Load short-circuit protection						
Ambient tempera	ture range	Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)						
Ambient humidity	y range	Operating and Storage: 35% to 95% (with no condensation)						
Temperature influ	uence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C						
Voltage influence)	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range						
Insulation resista	ince	50 M Ω min. (at 500 VDC) between current-carrying parts and case						
Dielectric strengt	h	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case						
Vibration resistar	nce (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions						
Shock resistance	(destruction)	500 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions						
Degree of protect	tion	Pre-wired Models/Pre-wired Connector Models: IP67 (IEC 60529), IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35°C max.) and ISO 20653 (old standard: DIN 40050 PART9) IP69K						
Connecting meth	od	Pre-wired Models (Standard cable len	gth: 2 m) and Pre-wired Connector Mod	lels (Standard cable length: 0.3 m)				
Woight	Pre-wired Models	Approx. 60 g	Approx. 70 g	Approx. 130 g				
Weight (packed state)	Pre-wired Connector Models	Approx. 30 g	Approx. 40 g	Approx. 70 g				
	Case	Stainless steel (SUS303)	Nickel-plated brass					
	Sensing surface	Polybutylene terephthalate (PBT)						
Materials	Clamping nuts	Nickel-plated brass						
	Toothed washer	Zinc-plated iron						
	Cable	Vinyl chloride (PVC)						
Accessories		Instruction manual, Clamping nuts, To	othed washer					

- *1. Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).
- *2. The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard.
- *3. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

 The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.
- *4. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.


 2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value).

 The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.


Engineering Data (Reference Value)

Sensing Area

Standard model Shielded



Double distance model Shielded




Influence of Sensing Object Size and Materials


Standard model

Shielded


Size: M8 E2E-X2D□




Unshielded




Unshielded




Unshielded




Size: M12 E2E-X3D□




Size: M12 E2E-X8MD□




Single distance model Shielded




Size: M18 E2E-X7D□




Size: M18 E2E-X14MD□



Size: M30 E2E-X10D□



Size: M30 E2E-X20MD□




Influence of Sensing Object Size and Materials


Double distance model

Shielded

Size: M12 E2E-X4D□




Unshielded



Single distance model Shielded

Size: M8 E2E-X1R5D□




Shielded/Unshielded E2E-X□(M)D□(-T)


Single distance model

Standard/Double distance/


Leakage Current




Size: M18 E2E-X8D□




Size: M30 E2E-X30MD□




Size: M12 E2E-X2R5D□




Residual Output Voltage






Size: M30 E2E-X15D□




Size: M18 E2E-X5D□



I/O Circuit Diagrams

DC 2-wire (Standard/Double distance/Single distance model)



Note: For the Pre-wired Connector Models, the core wire color and pin number are different.

Connector Pin Arrangement

M12 Connector M12 Smartclick Connector	M8 (4-pin) Connector
-M1/M1G -M1T \(\text{2} \)	-M3G

Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

⚠WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.		
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.		
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.		

Meaning of Product Safety Symbols

General prohibition Indicates the instructions of unspecified prohibited action.
Caution, explosion Indicates the possibility of explosion under specific conditions.

№ WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Risk of explosion.


Do not connect sensor to AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- Do not use the product in an environment where flammable or explosive gas is present.
- 2. Do not attempt to disassemble, repair, or modify the product.
- Do not use a voltage that exceeds the rated operating voltage range. Applying a voltage that is higher than the operating voltage range may result in damage or burnout.
- **4.** Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or burnout.
- 5. If the power supply is connected directly without a load, the internal elements may explode or burn. Be sure to insert a load when connecting the power supply.



Precautions for Correct Use

Do not use this product under ambient conditions that exceed the ratings.


Operating Environment

- Do not install the product in the following locations. Doing so may result in product failure or malfunction.
 - Outdoor locations directly subject to sunlight, rain, snow, water droplets, or oil.
 - (2) Locations subject to atmospheres with chemical vapors, in particular solvents and acids.
 - (3) Locations subject to corrosive gases.
- 2. The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com) for typical measures.
- Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ratio recommended by its manufacturer
 - Usage in oil or water is prohibited

Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.


AND Connection of Proximity Sensors

Two or more sensors cannot be connected in series on the AND circuit. Use them via a relay as shown on the figure.



OR Wiring of Proximity Sensors

As a general principle, two or more sensors cannot be used in parallel on the OR circuit. It is possible only when sensors do not operate simultaneously and loads do not need to be maintained. When loads need to be maintained, use the sensors via a relay as shown on the figure.




Design

Influence of Surrounding Metal

When mounting the Proximity Sensor using a nut, only use the provided nut. And ensure that the minimum distances given in the following table are maintained.

When mounting the Proximity Sensor using a nut, only use the provided nut. Nuts that are supplied along with each Sensor are different. Refer to Dimensions for details on shapes.



Shielded


(Unit: mm)

Туре	Size	Model	L	d	D	m	n
	M8	E2E-X2D□	0	8	0	4.5	12
Standard	M12	E2E-X3D□	0	12	0	8	18
model	M18	E2E-X7D□	0	18	0	20	27
	M30	E2E-X10D□	0	30	0	40	45
	M12	E2E-X4D□	0	18	0	12	18
Double distance model	M18	E2E-X8D□	0	27	0	24	27
distance model	M30	E2E-X15D□	0	45	0	45	45
Single distance model	M8	E2E-X1R5D□	0	8	0	4.5	12
	M12	E2E-X2R5D□	0	12	0	8	18
	M18	E2E-X5D□	0	18	0	20	27

Unshielded

Туре	Size	Model	L	d	D	m	n
Standard model	M8	E2E-X4MD□	9	24	9	8	24
	M12	E2E-X8MD□	11	40	11	20	40
	M18	E2E-X14MD□	18	55	18	40	54
	M30	E2E-X20MD□	25	90	25	70	90
Double	M18	E2E-X16MD□	21	70	21	48	70
distance model	M30	E2E-X30MD□	40	120	40	90	120

When the Proximity Sensor is mounted in metal, ensure that the minimum distances given in the following table are maintained.



Shielded

(Unit: mm)


Silleided							
Type	Size	Model	I	d	D	m	n
	M8	E2E-X2D□	0	8	0	4.5	12
Standard	M12	E2E-X3D□	0	12	0	8	18
model	M18	E2E-X7D□	0	18	0	20	27
	M30	E2E-X10D□	0	30	0	40	45
	M12	E2E-X4D□	2.4	18	2.4	12	18
Double distance model	M18	E2E-X8D□	3.6	27	3.6	24	27
distance moder	M30	E2E-X15D□	6	45	6	45	45
Single distance model	M8	E2E-X1R5D□	0	8	0	4.5	12
	M12	E2E-X2R5D□	0	12	0	8	18
	M18	E2E-X5D□	0	18	0	20	27

Unshielded

Type	Size	Model	ı	d	D	m	n
Standard model	M8	E2E-X4MD□	12	24	12	8	24
	M12	E2E-X8MD□	15	40	15	20	40
	M18	E2E-X14MD□	22	55	22	40	54
	M30	E2E-X20MD□	30	90	30	70	90
Double	M18	E2E-X16MD□	25	70	25	48	70
distance model	M30	E2E-X30MD□	45	120	45	90	120

Mutual Interference

When installing two or more Proximity Sensors face-to-face or sideby-side, ensure that the minimum distances given in the following table are maintained.



Shielded

(Unit: mm)

Type	Size	Model	Α	В
	M8	E2E-X2D□	20	15
Standard model	M12	E2E-X3D□	30(20)	20(12)
Standard model	M18	E2E-X7D□	50(30)	35(18)
	M30	E2E-X10D□	100(50)	70(35)
	M12	E2E-X4D□	30	20
Double distance model	M18	E2E-X8D□	60	35
illouei	M30	E2E-X15D□	110	90
Single distance model	M8	E2E-X1R5D□	20	15
	M12	E2E-X2R5D□	30	20
mouoi	M18	E2E-X5D□	50	35

Unshielded

Туре	Size	Model	Α	В
	M8	E2E-X4MD□	80	60
Standard model	M12	E2E-X8MD□	120(60)	100(50)
Standard model	M18	E2E-X14MD□	200(100)	110(60)
	M30	E2E-X20MD□	300(100)	200(100)
Double distance	M18	E2E-X16MD□	200	120
model	M30	E2E-X30MD□	350	300

- Note: 1. Values in parentheses apply to Sensors operating at different frequencies.
 - The values of mutual interference are provided for reference. Test the sensors on the actual machine or contact your OMRON sales representative to validate that there is no interference.

Mounting

Tightening Force

Do not tighten the sensor mounting nuts with excessive force. Secure the mounting nuts to the corresponding torque values in the following table.







- Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table.

 (A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)
 - 2. The following strengths assume washers are being used.

Standard/Double distance model

Model		Par	Part B	
	Wiodei	Dimension (mm)	Torque	Torque
M8	Shielded	9	9 N⋅m	12 N⋅m
IVIO	Unshielded	3	9 111111	12 111111
M12			108	√m
M18			70 1	V·m
M30		180 N⋅m		N∙m

Single distance model

onigio diotarios modo.						
Model	Par	Part B				
Wodei	Dimension (mm)	Torque	Torque			
M8	9	9 N⋅m	12 N⋅m			
M12		30 1	V·m			
M18		70 1	V·m			

Dimensions

Tolerance class IT16 applies to dimensions in this data sheet unless otherwise specified

Sensor

DC 2-wire (Standard/Double distance model)

Pre-wired Models Pre-wired Connector Models (Shielded)





Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.


Pre-wired Models Pre-wired Connector Models (Unshielded)





Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.





















*1. D1 Models: Operation indicator (Orange), Setting indicator (Green)/ D2 Models: Operation indicator (Orange)

Pre-wired Connector Models (-M1TGJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

\rightarrow		
	Dimensions	F (mm)
<u> </u>	M8	8.5 dia. +0.5
- F - - -1	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



Dimensions	R (mm)
M8	12
M12	
M18	18
M30	


Wire pullout position



Ì	Dimensions	Sc (mm)
ij	M8	(0)
	M12	- (0)
	M18	2.5
	M30	2.5

Sensor

DC 2-wire (Long-body Standard/Double distance model)



*1. D1 Models: Operation indicator (Orange), Setting indicator (Green)/ D2 Models: Operation indicator (Orange)

Mounting Hole Dimensions



Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



_		
0 mm	Dimensions	R (mm)
R	M8	12
Ш	M12	12
	M18	18
	M30	10

Wire pullout position



Dimensions	Sc (mm)	
M8	- (0)	
M12		
M18	2.5	
M30		

Sensor

DC 2-wire (Standard model)


M12 Connector Models (Shielded)




M12 Connector Models (Unshielded)




E2E-X2D□-M1/-M1G




E2E-X4MD -M1/-M1G




E2E-X3D -M1/-M1G




E2E-X8MD -M1/-M1G




E2E-X7D -M1/-M1G




E2E-X14MD - M1/-M1G



E2E-X10D .- M1/-M1G



E2E-X20MD -M1/-M1G



*1. D1 Models: Operation indicator (Orange), Setting indicator (Green)/ D2 Models: Operation indicator (Orange)

Mounting Hole Dimensions



Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Sensor

DC 2-wire (Standard model)


M8 Connector Models (Shielded)




M8 Connector Models (Unshielded)



E2E-X2D□-M3G






DC 2-wire (Single distance model)

Pre-wired Models Pre-wired Connector Models (Shielded)




Note: 1.
Refer to the figure below the table for the connections of the Pre-wired Connector Model.


E2E-X1R5D



4-dia. vinyl-insulated round cable with 2 conductors (Conductor, cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm), Standard length: 2 m




4-dia. vinyl-insulated round cable with 2 conductors (Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm), Standard length: 2 m



*1. D1 Models: Operation indicator (Orange), Setting indicator (Green)/ D2 Models: Operation indicator (Orange)

Pre-wired Connector Models (-M1TGJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

(Dimensions	F (mm)
	M8	8.5 dia. +0.5
- F 1	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



Dimensions	R (mm)	
M8	12	
M12	12	
M18	18	
M30	10	

Wire pullout position



Dimensions	Sc (mm)
M8	(0)
M12	- (0)
M18	2.5
M30	2.5

DC 3-wire

Enables easier and standardized designs previously not possible

- Nearly double the sensing distance*1 of previous
- With high-brightness LED, the indicator is visible anywhere from 360°.
- Only 10 Seconds*2 to Replace a Proximity Sensor with the "e-jig" (Mounting Sleeve).
- Cables with enhanced oil resistance enabled 2-year oil resistance*3.
- IP69K compliant for water resistance and wash resistance
- Comes in a wide variation to make sensor selection easy
- UL certification (UL60947-5-2)*4 and CSA certification (CSA C22.2 UL60947-5-2-14)



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

- *1. Comparison with our previous model E2E.
- *2. Time required to adjust the distance when installing a Sensor. Based on OMRON investigation.
- *3. Refer to Ratings and Specifications for details. However, E2E Connector Models is excluded.
- *4. M8 (4-pin) Connector Models are not UL certified.



Be sure to read Safety Precautions on page 72.

Model Number Legend

E2E-X(1)(2)(3)(4)(5)(6)(7)(8)-(9)-(10)(11)

No.	Туре	Code	Meaning
(1)	Sensing distance	Number	Sensing distance (Unit: mm) (R: Indication of decimal point)
(2)	Shielding	Blank	Shielded
(2)	Sillefully	М	Unshielded
(3)	Output configuration	В	PNP open collector
(3)	Output configuration	С	NPN open collector
		1	Normally open (NO)
(4)	Operation mode	2	Normally closed (NC)
		3	Normally open, Normally closed (NO+NC)
(5)	Oscillation frequency type	Blank	Standard frequency
(3)	Oscillation frequency type	5	Different frequency
		Blank	Non IO-Link compliant
(6)) IO-Link baud rate	D	COM2 (38.4 kbps)
		Т	COM3 (230.4 kbps)
(7)	Body size	Blank	Standard
(1)	Body Size	L	Long Body
		8	M8
(8)	Size	12	M12
(0)	Size	18	M18
		30	M30
		Blank	Pre-wired Models
		M1	M12 Connector Models
		M3	M8 (4-pin) Connector Models
(9)	Connection method	M5	M8 (3-pin) Connector Models
		M1TJ	M12 Pre-wired Smartclick Connector Models
		M1TJR	M12 Pre-wired Smartclick Connector Models Robot (bending-resistant) cable
(10)	Cable specifications (Only shown in the model number	Blank	Standard PVC cable
(10)	of Pre-wired Models.)	R	Robot (bending-resistant) cable
(11)	Cable length	Number M	Cable length

Note: The purpose of this model number legend is to provide understanding of the meaning of specifications from the model number.

riple distance model

Ordering Information

PREMIUM Model

DC 3-wire (Quadruple distance model) [Refer to *Dimensions* on page 75.] Shielded *1

Size (Sensing	Connection method	Dady sine	Operation	Model	
distance)	Connection method	Body size	mode	PNP	NPN
		38 mm *3	NO	E2E-X4B1D8 2M	E2E-X4C18 2M
	Pre-wired (2 m) *2	30 111111 3	NC	E2E-X4B28 2M	E2E-X4C28 2M
	Pre-wired (2 III) 2	40	NO	E2E-X4B1DL8 2M	E2E-X4C1L8 2M
		48 mm	NC	E2E-X4B2L8 2M	E2E-X4C2L8 2M
		00 *4	NO	E2E-X4B1D8-M1TJ 0.3M	E2E-X4C18-M1TJ 0.3M
	M12 Pre-wired	38 mm *4	NC	E2E-X4B28-M1TJ 0.3M	E2E-X4C28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	40	NO	E2E-X4B1DL8-M1TJ 0.3M	E2E-X4C1L8-M1TJ 0.3M
		48 mm	NC	E2E-X4B2L8-M1TJ 0.3M	E2E-X4C2L8-M1TJ 0.3M
		40	NO	E2E-X4B1D8-M1	E2E-X4C18-M1
M0 (4)	MAC Commenter	43 mm	NC	E2E-X4B28-M1	E2E-X4C28-M1
M8 (4 mm)	M12 Connector		NO	E2E-X4B1DL8-M1	E2E-X4C1L8-M1
		53 mm	NC	E2E-X4B2L8-M1	E2E-X4C2L8-M1
		20	NO	E2E-X4B1D8-M3	E2E-X4C18-M3
	140.0	39 mm	NC	E2E-X4B28-M3	E2E-X4C28-M3
	M8 Connector (4-pin)	40	NO	E2E-X4B1DL8-M3	E2E-X4C1L8-M3
		49 mm	NC	E2E-X4B2L8-M3	E2E-X4C2L8-M3
			NO	E2E-X4B1D8-M5	E2E-X4C18-M5
		39 mm	NC	E2E-X4B28-M5	E2E-X4C28-M5
	M8 Connector (3-pin)	49 mm	NO	E2E-X4B1DL8-M5	E2E-X4C1L8-M5
			NC	E2E-X4B2L8-M5	E2E-X4C2L8-M5
		47 mm *3	NO	E2E-X9B1D12 2M	E2E-X9C112 2M
	D : 1/0) to		NC	E2E-X9B212 2M	E2E-X9C212 2M
	Pre-wired (2 m) *2		NO	E2E-X9B1DL12 2M	E2E-X9C1L12 2M
		69 mm	NC	E2E-X9B2L12 2M	E2E-X9C2L12 2M
			NO	E2E-X9B1D12-M1TJ 0.3M	E2E-X9C112-M1TJ 0.3M
	M12 Pre-wired	47 mm *4	NC	E2E-X9B212-M1TJ 0.3M	E2E-X9C212-M1TJ 0.3M
M12 (9 mm)	Smartclick Connector (0.3 m)		NO	E2E-X9B1DL12-M1TJ 0.3M	E2E-X9C1L12-M1TJ 0.3M
		69 mm	NC	E2E-X9B2L12-M1TJ 0.3M	E2E-X9C2L12-M1TJ 0.3M
			NO	E2E-X9B1D12-M1	E2E-X9C112-M1
		48 mm	NC	E2E-X9B212-M1	E2E-X9C212-M1
	M12 Connector		NO	E2E-X9B1DL12-M1	E2E-X9C1L12-M1
		70 mm	NC	E2E-X9B2L12-M1	E2E-X9C2L12-M1
			NO	E2E-X14B1D18 2M	E2E-X14C118 2M
		55 mm *3	NC	E2E-X14B218 2M	E2E-X14C218 2M
	Pre-wired (2 m) *2		NO	E2E-X14B1DL18 2M	E2E-X14C1L18 2M
		77 mm	NC	E2E-X14B2L18 2M	E2E-X14C2L18 2M
			NO	E2E-X14B1D18-M1TJ 0.3M	E2E-X14C118-M1TJ 0.3M
	M12 Pre-wired	55 mm *4	NC	E2E-X14B218-M1TJ 0.3M	E2E-X14C218-M1TJ 0.3M
118 (14 mm)	Smartclick Connector (0.3 m)		NO	E2E-X14B1DL18-M1TJ 0.3M	E2E-X14C1L18-M1TJ 0.3M
		77 mm	NC	E2E-X14B2L18-M1TJ 0.3M	E2E-X14C2L18-M1TJ 0.3M
			NO	E2E-X14B1D18-M1	E2E-X14C118-M1
		53 mm	NC	E2E-X14B218-M1	E2E-X14C218-M1
	M12 Connector		NO	E2E-X14B1DL18-M1	E2E-X14C1L18-M1
		75 mm	NC	E2E-X14B2L18-M1	E2E-X14C2L18-M1

PREMIUM Model

Size (Sensing	Connection method	Body size	Operation	Мо	Model	
distance)	Connection method	Body Size	mode	PNP	NPN	
		60 mm *4	NO	E2E-X23B1D30 2M	E2E-X23C130 2M	
	Pre-wired (2 m) *2	60 mm 4	NC	E2E-X23B230 2M	E2E-X23C230 2M	
	Pre-wired (2 m) 2	82 mm	NO	E2E-X23B1DL30 2M	E2E-X23C1L30 2M	
		8∠ mm	NC	E2E-X23B2L30 2M	E2E-X23C2L30 2M	
	M12 Pre-wired Smartclick	60 mm *4	NO	E2E-X23B1D30-M1TJ 0.3M	E2E-X23C130-M1TJ 0.3M	
M30 (23 mm)			NC	E2E-X23B230-M1TJ 0.3M	E2E-X23C230-M1TJ 0.3M	
10130 (23 11111)	Connector (0.3 m)	82 mm	NO	E2E-X23B1DL30-M1TJ 0.3M	E2E-X23C1L30-M1TJ 0.3M	
			NC	E2E-X23B2L30-M1TJ 0.3M	E2E-X23C2L30-M1TJ 0.3M	
		58 mm	NO	E2E-X23B1D30-M1	E2E-X23C130-M1	
			NC	E2E-X23B230-M1	E2E-X23C230-M1	
	M12 Connector	90	NO	E2E-X23B1DL30-M1	E2E-X23C1L30-M1	
		80 mm	NC	E2E-X23B2L30-M1	E2E-X23C2L30-M1	

^{*1.} When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 73.

Note: 1. Models in _____ are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X□□□T□" (Example: E2E-X9B1T12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*2.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2E-X9B1D12 5M)

^{*3.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X9B1D12-R 2M/ E2E-X9B1D12-R 5M)

^{*4.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with "R" in the model number. (Example: E2E-X9B1D12-M1TJR 0.3M)

PREMIUM Model

DC 3-wire (Quadruple distance model) [Refer to Dimensions on page 76.]

Unshielded

Size (Sensing	Connection method	Body size	Operation mode	Model	
distance)				PNP	NPN
		38 mm *2	NO	E2E-X8MB1D8 2M	E2E-X8MC18 2M
	Dro wired (2 m) *1	30 111111 2	NC	E2E-X8MB28 2M	E2E-X8MC28 2M
	Pre-wired (2 m) *1	40	NO	E2E-X8MB1DL8 2M	E2E-X8MC1L8 2M
		48 mm	NC	E2E-X8MB2L8 2M	E2E-X8MC2L8 2M
		20 *2	NO	E2E-X8MB1D8-M1TJ 0.3M	E2E-X8MC18-M1TJ 0.3M
	M12 Pre-wired	38 mm *3	NC	E2E-X8MB28-M1TJ 0.3M	E2E-X8MC28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	40	NO	E2E-X8MB1DL8-M1TJ 0.3M	E2E-X8MC1L8-M1TJ 0.3M
		48 mm	NC	E2E-X8MB2L8-M1TJ 0.3M	E2E-X8MC2L8-M1TJ 0.3M
		42	NO	E2E-X8MB1D8-M1	E2E-X8MC18-M1
M8	M42 Connector	43 mm	NC	E2E-X8MB28-M1	E2E-X8MC28-M1
(8 mm)	M12 Connector	F0	NO	E2E-X8MB1DL8-M1	E2E-X8MC1L8-M1
		53 mm	NC	E2E-X8MB2L8-M1	E2E-X8MC2L8-M1
		20	NO	E2E-X8MB1D8-M3	E2E-X8MC18-M3
	M0 Connector (4 = !=)	39 mm	NC	E2E-X8MB28-M3	E2E-X8MC28-M3
	M8 Connector (4-pin)	40	NO	E2E-X8MB1DL8-M3	E2E-X8MC1L8-M3
		49 mm	NC	E2E-X8MB2L8-M3	E2E-X8MC2L8-M3
		39 mm	NO	E2E-X8MB1D8-M5	E2E-X8MC18-M5
	MO Connector (2 nin)		NC	E2E-X8MB28-M5	E2E-X8MC28-M5
	M8 Connector (3-pin)	49 mm	NO	E2E-X8MB1DL8-M5	E2E-X8MC1L8-M5
			NC	E2E-X8MB2L8-M5	E2E-X8MC2L8-M5
	B : 1/0) **	47 mm *2	NO	E2E-X16MB1D12 2M	E2E-X16MC112 2M
			NC	E2E-X16MB212 2M	E2E-X16MC212 2M
	Pre-wired (2 m) *1	69 mm	NO	E2E-X16MB1DL12 2M	E2E-X16MC1L12 2M
			NC	E2E-X16MB2L12 2M	E2E-X16MC2L12 2M
		47 mm *3	NO	E2E-X16MB1D12-M1TJ 0.3M	E2E-X16MC112-M1TJ 0.3M
M12	M12 Pre-wired	47 111111 3	NC	E2E-X16MB212-M1TJ 0.3M	E2E-X16MC212-M1TJ 0.3M
(16 mm)	Smartclick Connector (0.3 m)	60	NO	E2E-X16MB1DL12-M1TJ 0.3M	E2E-X16MC1L12-M1TJ 0.3M
		69 mm	NC	E2E-X16MB2L12-M1TJ 0.3M	E2E-X16MC2L12-M1TJ 0.3M
		10 mm	NO	E2E-X16MB1D12-M1	E2E-X16MC112-M1
	M12 Connector	48 mm	NC	E2E-X16MB212-M1	E2E-X16MC212-M1
	M12 Connector	70 mm	NO	E2E-X16MB1DL12-M1	E2E-X16MC1L12-M1
		70 mm	NC	E2E-X16MB2L12-M1	E2E-X16MC2L12-M1
	Pre-wired (2 m) *1	77 mm *2	NO	E2E-X30MB1DL18 2M	E2E-X30MC1L18 2M
	Fie-wiled (2 iii)	77 111111 2	NC	E2E-X30MB2L18 2M	E2E-X30MC2L18 2M
M18	M12 Pre-wired	77 mm *2	NO	E2E-X30MB1DL18-M1TJ 0.3M	E2E-X30MC1L18-M1TJ 0.3M
(30 mm)	Smartclick Connector (0.3 m)	77 mm *3	NC	E2E-X30MB2L18-M1TJ 0.3M	E2E-X30MC2L18-M1TJ 0.3M
	M12 Connector	75 mm	NO	E2E-X30MB1DL18-M1	E2E-X30MC1L18-M1
	M12 Connector	7.5 111111	NC	E2E-X30MB2L18-M1	E2E-X30MC2L18-M1
	Pre-wired (2 m) *1	07 mm *2	NO	E2E-X50MB1DL30 2M	E2E-X50MC1L30 2M
	FIE-WIIEU (Z III) I	97 mm *2	NC	E2E-X50MB2L30 2M	E2E-X50MC2L30 2M
M30	M12 Pre-wired	07 mm *2	NO	E2E-X50MB1DL30-M1TJ 0.3M	E2E-X50MC1L30-M1TJ 0.3M
(50 mm)	Smartclick Connector (0.3 m)	97 mm *3	NC	E2E-X50MB2L30-M1TJ 0.3M	E2E-X50MC2L30-M1TJ 0.3M
	M12 Connector	05 mm	NO	E2E-X50MB1DL30-M1	E2E-X50MC1L30-M1
	M12 Connector	95 mm	NC	E2E-X50MB2L30-M1	E2E-X50MC2L30-M1

^{*1.} Models with 5-m cable length are also available (Example: E2E-X16MB1D12 5M)

Note: 1. Models in] are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X $\Box\Box\Box\Box\Box$ " (Example: E2E-X16MB1T12 2M).

^{*2.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X16MB1D12-R 2M/E2E-X16MB1D12-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X16MB1D12-M1TJR 0.3M)

Operation mode NO can be changed to NC via IO-Link communications.

2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

PREMIUM Model

DC 3-wire (Triple distance model) [Refer to Dimensions on page 75.]

Shielded *1

ize (Sensing	Connection method	Body size	Operation mode	Model	
distance)				PNP	NPN
		38 mm *3	NO	E2E-X3B1D8 2M	E2E-X3C18 2M
	Pre-wired (2 m) *2	30 11111 3	NC	E2E-X3B28 2M	E2E-X3C28 2M
	Fie-wiled (2 iii) 2	48 mm	NO	E2E-X3B1DL8 2M	E2E-X3C1L8 2M
		40 111111	NC	E2E-X3B2L8 2M	E2E-X3C2L8 2M
		38 mm *4	NO	E2E-X3B1D8-M1TJ 0.3M	E2E-X3C18-M1TJ 0.3M
	M12 Pre-wired	30 111111 4	NC	E2E-X3B28-M1TJ 0.3M	E2E-X3C28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	48 mm	NO	E2E-X3B1DL8-M1TJ 0.3M	E2E-X3C1L8-M1TJ 0.3M
		40 111111	NC	E2E-X3B2L8-M1TJ 0.3M	E2E-X3C2L8-M1TJ 0.3M
		43 mm	NO	E2E-X3B1D8-M1	E2E-X3C18-M1
M8	M12 Connector	43 11111	NC	E2E-X3B28-M1	E2E-X3C28-M1
(3 mm)	W12 Connector	52 mm	NO	E2E-X3B1DL8-M1	E2E-X3C1L8-M1
		53 mm	NC	E2E-X3B2L8-M1	E2E-X3C2L8-M1
		39 mm	NO	E2E-X3B1D8-M3	E2E-X3C18-M3
	M8 Connector (4-pin)	39 11111	NC	E2E-X3B28-M3	E2E-X3C28-M3
	ivio Connector (4-pin)	49 mm	NO	E2E-X3B1DL8-M3	E2E-X3C1L8-M3
		49 111111	NC	E2E-X3B2L8-M3	E2E-X3C2L8-M3
	M8 Connector (3-pin)	39 mm	NO	E2E-X3B1D8-M5	E2E-X3C18-M5
			NC	E2E-X3B28-M5	E2E-X3C28-M5
		49 mm	NO	E2E-X3B1DL8-M5	E2E-X3C1L8-M5
			NC	E2E-X3B2L8-M5	E2E-X3C2L8-M5
			NO	E2E-X6B1D12 2M	E2E-X6C112 2M
		47 mm *3	NC	E2E-X6B212 2M	E2E-X6C212 2M
	Dro wired (2 m) *2		NO+NC	E2E-X6B3D12 2M	E2E-X6C312 2M
	Pre-wired (2 m) *2		NO	E2E-X6B1DL12 2M	E2E-X6C1L12 2M
		69 mm	NC	E2E-X6B2L12 2M	E2E-X6C2L12 2M
			NO+NC	E2E-X6B3DL12 2M	E2E-X6C3L12 2M
			NO	E2E-X6B1D12-M1TJ 0.3M	E2E-X6C112-M1TJ 0.3M
		47 mm *4	NC	E2E-X6B212-M1TJ 0.3M	E2E-X6C212-M1TJ 0.3M
M12	M12 Pre-wired		NO+NC	E2E-X6B3D12-M1TJ 0.3M	E2E-X6C312-M1TJ 0.3M
(6 mm)	Smartclick Connector (0.3 m)		NO	E2E-X6B1DL12-M1TJ 0.3M	E2E-X6C1L12-M1TJ 0.3M
		69 mm	NC	E2E-X6B2L12-M1TJ 0.3M	E2E-X6C2L12-M1TJ 0.3M
			NO+NC	E2E-X6B3DL12-M1TJ 0.3M	E2E-X6C3L12-M1TJ 0.3M
			NO	E2E-X6B1D12-M1	E2E-X6C112-M1
		48 mm	NC	E2E-X6B212-M1	E2E-X6C212-M1
	M40 O		NO+NC	E2E-X6B3D12-M1	E2E-X6C312-M1
	M12 Connector		NO	E2E-X6B1DL12-M1	E2E-X6C1L12-M1
		70 mm	NC	E2E-X6B2L12-M1	E2E-X6C2L12-M1
			NO+NC	E2E-X6B3DL12-M1	E2E-X6C3L12-M1

PREMIUM Model

Size (Sensing	Connection method	Body size	Operation	ration Model	
distance)	Connection method	Bouy Size	mode	PNP	NPN
			NO	E2E-X12B1D18 2M	E2E-X12C118 2M
		55 mm *3	NC	E2E-X12B218 2M	E2E-X12C218 2M
	Pre-wired (2 m) *2		NO+NC	E2E-X12B3D18 2M	E2E-X12C318 2M
	Fie-wired (2 iii) 2		NO	E2E-X12B1DL18 2M	E2E-X12C1L18 2M
		77 mm	NC	E2E-X12B2L18 2M	E2E-X12C2L18 2M
			NO+NC	E2E-X12B3DL18 2M	E2E-X12C3L18 2M
			NO	E2E-X12B1D18-M1TJ 0.3M	E2E-X12C118-M1TJ 0.3M
		55 mm *4	NC	E2E-X12B218-M1TJ 0.3M	E2E-X12C218-M1TJ 0.3M
M18	M12 Pre-wired		NO+NC	E2E-X12B3D18-M1TJ 0.3M	E2E-X12C318-M1TJ 0.3M
(12 mm)	Smartclick Connector (0.3 m)		NO	E2E-X12B1DL18-M1TJ 0.3M	E2E-X12C1L18-M1TJ 0.3M
		77 mm	NC	E2E-X12B2L18-M1TJ 0.3M	E2E-X12C2L18-M1TJ 0.3M
			NO+NC	E2E-X12B3DL18-M1TJ 0.3M	E2E-X12C3L18-M1TJ 0.3M
			NO	E2E-X12B1D18-M1	E2E-X12C118-M1
		53 mm	NC	E2E-X12B218-M1	E2E-X12C218-M1
	M42 Connector		NO+NC	E2E-X12B3D18-M1	E2E-X12C318-M1
	M12 Connector	75 mm	NO	E2E-X12B1DL18-M1	E2E-X12C1L18-M1
			NC	E2E-X12B2L18-M1	E2E-X12C2L18-M1
			NO+NC	E2E-X12B3DL18-M1	E2E-X12C3L18-M1
			NO	E2E-X22B1D30 2M	E2E-X22C130 2M
		60 mm *3	NC	E2E-X22B230 2M	E2E-X22C230 2M
	Pre-wired (2 m) *2		NO+NC	E2E-X22B3D30 2M	E2E-X22C330 2M
	Pre-wired (2 m) 2		NO	E2E-X22B1DL30 2M	E2E-X22C1L30 2M
		82 mm	NC	E2E-X22B2L30 2M	E2E-X22C2L30 2M
			NO+NC	E2E-X22B3DL30 2M	E2E-X22C3L30 2M
			NO	E2E-X22B1D30-M1TJ 0.3M	E2E-X22C130-M1TJ 0.3M
		60 mm *4	NC	E2E-X22B230-M1TJ 0.3M	E2E-X22C230-M1TJ 0.3M
M30	M12 Pre-wired		NO+NC	E2E-X22B3D30-M1TJ 0.3M	E2E-X22C330-M1TJ 0.3M
(22 mm)	Smartclick Connector (0.3 m)		NO	E2E-X22B1DL30-M1TJ 0.3M	E2E-X22C1L30-M1TJ 0.3M
		82 mm	NC	E2E-X22B2L30-M1TJ 0.3M	E2E-X22C2L30-M1TJ 0.3M
			NO+NC	E2E-X22B3DL30-M1TJ 0.3M	E2E-X22C3L30-M1TJ 0.3M
			NO	E2E-X22B1D30-M1	E2E-X22C130-M1
		58 mm	NC	E2E-X22B230-M1	E2E-X22C230-M1
	M12 Connector		NO+NC	E2E-X22B3D30-M1	E2E-X22C330-M1
	IVI 12 CONNECTOR		NO	E2E-X22B1DL30-M1	E2E-X22C1L30-M1
		80 mm	NC	E2E-X22B2L30-M1	E2E-X22C2L30-M1
			NO+NC	E2E-X22B3DL30-M1	E2E-X22C3L30-M1

^{*1.} When embedding the Proximity Sensor in metal, refer to *Influence of Surrounding Metal* on page 73.

Note: 1. Models in are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X 🗆 🗆 T 🗀 🗀 T 🗀 🗀 T (Example: E2E-X6B1T12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*2.} Models with 5-m cable length are also available (Example: E2E-X6B1D12 5M)

*3. Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X6B1D12-R 2M/ E2E-X6B1D12-R 5M)

^{*4.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X6B1D12-M1TJR 0.3M)

PREMIUM Model

DC 3-wire (Triple distance model) [Refer to *Dimensions* on page 76.] Unshielded

Size (Sensing			Operation	tion Model	
distance)	Connection method	Body size	mode	PNP	NPN
		00 +0	NO	E2E-X6MB1D8 2M	E2E-X6MC18 2M
Di d (0 -	Dec	38 mm *2	NC	E2E-X6MB28 2M	E2E-X6MC28 2M
	Pre-wired (2 m) *1		NO	E2E-X6MB1DL8 2M	E2E-X6MC1L8 2M
		48 mm	NC	E2E-X6MB2L8 2M	E2E-X6MC2L8 2M
			NO	E2E-X6MB1D8-M1TJ 0.3M	E2E-X6MC18-M1TJ 0.3M
	M12 Pre-wired	38 mm *3	NC	E2E-X6MB28-M1TJ 0.3M	E2E-X6MC28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	40	NO	E2E-X6MB1DL8-M1TJ 0.3M	E2E-X6MC1L8-M1TJ 0.3M
		48 mm	NC	E2E-X6MB2L8-M1TJ 0.3M	E2E-X6MC2L8-M1TJ 0.3M
		40	NO	E2E-X6MB1D8-M1	E2E-X6MC18-M1
M8	M40 Commenter	43 mm	NC	E2E-X6MB28-M1	E2E-X6MC28-M1
(6 mm)	M12 Connector	50	NO	E2E-X6MB1DL8-M1	E2E-X6MC1L8-M1
		53 mm	NC	E2E-X6MB2L8-M1	E2E-X6MC2L8-M1
		20	NO	E2E-X6MB1D8-M3	E2E-X6MC18-M3
	MO Connector (4 = i=)	39 mm	NC	E2E-X6MB28-M3	E2E-X6MC28-M3
	M8 Connector (4-pin)	40	NO	E2E-X6MB1DL8-M3	E2E-X6MC1L8-M3
		49 mm	NC	E2E-X6MB2L8-M3	E2E-X6MC2L8-M3
			NO	E2E-X6MB1D8-M5	E2E-X6MC18-M5
	110.0	39 mm	NC	E2E-X6MB28-M5	E2E-X6MC28-M5
	M8 Connector (3-pin)	40	NO	E2E-X6MB1DL8-M5	E2E-X6MC1L8-M5
		49 mm	NC	E2E-X6MB2L8-M5	E2E-X6MC2L8-M5
			NO	E2E-X10MB1D12 2M	E2E-X10MC112 2M
		47 mm *2 69 mm	NC	E2E-X10MB212 2M	E2E-X10MC212 2M
	D : 1/0)*4		NO+NC	E2E-X10MB3D12 2M	E2E-X10MC312 2M
	Pre-wired (2 m) *1		NO	E2E-X10MB1DL12 2M	E2E-X10MC1L12 2M
			NC	E2E-X10MB2L12 2M	E2E-X10MC2L12 2M
			NO+NC	E2E-X10MB3DL12 2M	E2E-X10MC3L12 2M
			NO	E2E-X10MB1D12-M1TJ 0.3M	E2E-X10MC112-M1TJ 0.3M
		47 mm *3	NC	E2E-X10MB212-M1TJ 0.3M	E2E-X10MC212-M1TJ 0.3M
M12	M12 Pre-wired		NO+NC	E2E-X10MB3D12-M1TJ 0.3M	E2E-X10MC312-M1TJ 0.3M
(10 mm)	Smartclick Connector (0.3 m)		NO	E2E-X10MB1DL12-M1TJ 0.3M	E2E-X10MC1L12-M1TJ 0.3M
		69 mm	NC	E2E-X10MB2L12-M1TJ 0.3M	E2E-X10MC2L12-M1TJ 0.3M
			NO+NC	E2E-X10MB3DL12-M1TJ 0.3M	E2E-X10MC3L12-M1TJ 0.3M
			NO	E2E-X10MB1D12-M1	E2E-X10MC112-M1
		48 mm	NC	E2E-X10MB212-M1	E2E-X10MC212-M1
	M12 Connector		NO+NC	E2E-X10MB3D12-M1	E2E-X10MC312-M1
	WITZ COMINGUION		NO	E2E-X10MB1DL12-M1	E2E-X10MC1L12-M1
		70 mm	NC	E2E-X10MB2L12-M1	E2E-X10MC2L12-M1
			NO+NC	E2E-X10MB3DL12-M1	E2E-X10MC3L12-M1
			NO	E2E-X20MB1DL18 2M	E2E-X20MC1L18 2M
	Pre-wired (2 m) *1	77 mm *2	NC	E2E-X20MB2L18 2M	E2E-X20MC2L18 2M
			NO+NC	E2E-X20MB3DL18 2M	E2E-X20MC3L18 2M
Mac			NO	E2E-X20MB1DL18-M1TJ 0.3M	E2E-X20MC1L18-M1TJ 0.3M
M18 (20 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	77 mm *3	NC	E2E-X20MB2L18-M1TJ 0.3M	E2E-X20MC2L18-M1TJ 0.3M
(20 11111)	5artonor Connoctor (0.0 III)		NO+NC	E2E-X20MB3DL18-M1TJ 0.3M	E2E-X20MC3L18-M1TJ 0.3M
			NO	E2E-X20MB1DL18-M1	E2E-X20MC1L18-M1
	M12 Connector	75 mm	NC	E2E-X20MB2L18-M1	E2E-X20MC2L18-M1
			NO+NC	E2E-X20MB3DL18-M1	E2E-X20MC3L18-M1

PREMIUM Model

Size (Sensing	Connection method	Body size	Operation	Мо	del
distance)	Connection method	Body Size	mode	PNP	NPN
			NO	E2E-X40MB1DL30 2M	E2E-X40MC1L30 2M
	Pre-wired (2 m) *1	82 mm *2	NC	E2E-X40MB2L30 2M	E2E-X40MC2L30 2M
			NO+NC	E2E-X40MB3DL30 2M	E2E-X40MC3L30 2M
1400		82 mm *3	NO	E2E-X40MB1DL30-M1TJ 0.3M	E2E-X40MC1L30-M1TJ 0.3M
M30 (40 mm)	M12 Pre-wired Smartclick Connector (0.3 m)		NC	E2E-X40MB2L30-M1TJ 0.3M	E2E-X40MC2L30-M1TJ 0.3M
(40 mm) Smarte	Cinartolick Confidence (0.5 m)		NO+NC	E2E-X40MB3DL30-M1TJ 0.3M	E2E-X40MC3L30-M1TJ 0.3M
			NO	E2E-X40MB1DL30-M1	E2E-X40MC1L30-M1
M12 Con	M12 Connector	80 mm	NC	E2E-X40MB2L30-M1	E2E-X40MC2L30-M1
			NO+NC	E2E-X40MB3DL30-M1	E2E-X40MC3L30-M1

^{*1.} Models with 5-m cable length are also available (Example: E2E-X10MB1D12 5M)

Note: 1. Models in _____ are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X□□T□" (Example: E2E-X10MB1T12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*2.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X10MB1D12-R 2M/E2E-X10MB1D12-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X10MB1D12-M1TJR 0.3M)

BASIC Model

DC 3-wire (Double distance model) [Refer to *Dimensions* on page 79.] Shielded

Size (Sensing	Connection method	Body size	Operation	Мо	del
distance)	Connection method	Body Size	mode	PNP	NPN
		38 mm *2	NO	E2E-X2B1D8 2M	E2E-X2C18 2M
	Pre-wired (2 m) *1	30 111111 2	NC	E2E-X2B28 2M	E2E-X2C28 2M
	Fie-wired (2 iii)	48 mm	NO	E2E-X2B1DL8 2M	E2E-X2C1L8 2M
		40 11111	NC	E2E-X2B2L8 2M	E2E-X2C2L8 2M
		38 mm *3	NO	E2E-X2B1D8-M1TJ 0.3M	E2E-X2C18-M1TJ 0.3M
	M12 Pre-wired	30 111111 3	NC	E2E-X2B28-M1TJ 0.3M	E2E-X2C28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	48 mm	NO	E2E-X2B1DL8-M1TJ 0.3M	E2E-X2C1L8-M1TJ 0.3M
		40 111111	NC	E2E-X2B2L8-M1TJ 0.3M	E2E-X2C2L8-M1TJ 0.3M
		43 mm	NO	E2E-X2B1D8-M1	E2E-X2C18-M1
		43 11111	NC	E2E-X2B28-M1	E2E-X2C28-M1
M8 (2 mm)	M12 Connector		NO	E2E-X2B1DL8-M1	E2E-X2C1L8-M1
(2 11111)		53 mm	NC	E2E-X2B2L8-M1	E2E-X2C2L8-M1
			NO+NC	E2E-X2B3DL8-M1	E2E-X2C3L8-M1
		20	NO	E2E-X2B1D8-M3	E2E-X2C18-M3
	MO Connector (4 pin)	39 mm	NC	E2E-X2B28-M3	E2E-X2C28-M3
	M8 Connector (4-pin)	49 mm	NO	E2E-X2B1DL8-M3	E2E-X2C1L8-M3
			NC	E2E-X2B2L8-M3	E2E-X2C2L8-M3
	M8 Connector (3-pin)	39 mm	NO	E2E-X2B1D8-M5	E2E-X2C18-M5
			NC	E2E-X2B28-M5	E2E-X2C28-M5
		49 mm	NO	E2E-X2B1DL8-M5	E2E-X2C1L8-M5
			NC	E2E-X2B2L8-M5	E2E-X2C2L8-M5
			NO	E2E-X4B1D12 2M	E2E-X4C112 2M
		47 mm *2	NC	E2E-X4B212 2M	E2E-X4C212 2M
	Pre-wired (2 m) *1		NO+NC	E2E-X4B3D12 2M	E2E-X4C312 2M
	Fie-wired (2 iii)		NO	E2E-X4B1DL12 2M	E2E-X4C1L12 2M
		69 mm	NC	E2E-X4B2L12 2M	E2E-X4C2L12 2M
			NO+NC	E2E-X4B3DL12 2M	E2E-X4C3L12 2M
			NO	E2E-X4B1D12-M1TJ 0.3M	E2E-X4C112-M1TJ 0.3M
		47 mm *3	NC	E2E-X4B212-M1TJ 0.3M	E2E-X4C212-M1TJ 0.3M
M12	M12 Pre-wired		NO+NC	E2E-X4B3D12-M1TJ 0.3M	E2E-X4C312-M1TJ 0.3M
(4 mm)	Smartclick Connector (0.3 m)		NO	E2E-X4B1DL12-M1TJ 0.3M	E2E-X4C1L12-M1TJ 0.3M
		69 mm	NC	E2E-X4B2L12-M1TJ 0.3M	E2E-X4C2L12-M1TJ 0.3M
			NO+NC	E2E-X4B3DL12-M1TJ 0.3M	E2E-X4C3L12-M1TJ 0.3M
			NO	E2E-X4B1D12-M1	E2E-X4C112-M1
		48 mm	NC	E2E-X4B212-M1	E2E-X4C212-M1
	M12 Connector		NO+NC	E2E-X4B3D12-M1	E2E-X4C312-M1
	IVITZ CONNECTOR		NO	E2E-X4B1DL12-M1	E2E-X4C1L12-M1
		70 mm	NC	E2E-X4B2L12-M1	E2E-X4C2L12-M1
			NO+NC	E2E-X4B3DL12-M1	E2E-X4C3L12-M1

BASIC Model

Size (Sensing	Connection method	Body size	Operation	Мо	del
distance)	Connection method	Bouy Size	mode	PNP	NPN
			NO	E2E-X8B1D18 2M	E2E-X8C118 2M
		55 mm *2	NC	E2E-X8B218 2M	E2E-X8C218 2M
	Pre-wired (2 m) *1		NO+NC	E2E-X8B3D18 2M	E2E-X8C318 2M
	Fie-wired (2 iii)		NO	E2E-X8B1DL18 2M	E2E-X8C1L18 2M
		77 mm	NC	E2E-X8B2L18 2M	E2E-X8C2L18 2M
			NO+NC	E2E-X8B3DL18 2M	E2E-X8C3L18 2M
			NO	E2E-X8B1D18-M1TJ 0.3M	E2E-X8C118-M1TJ 0.3M
		55 mm *3	NC	E2E-X8B218-M1TJ 0.3M	E2E-X8C218-M1TJ 0.3M
M18	M12 Pre-wired		NO+NC	E2E-X8B3D18-M1TJ 0.3M	E2E-X8C318-M1TJ 0.3M
(8 mm)	Smartclick Connector (0.3 m)		NO	E2E-X8B1DL18-M1TJ 0.3M	E2E-X8C1L18-M1TJ 0.3M
		77 mm	NC	E2E-X8B2L18-M1TJ 0.3M	E2E-X8C2L18-M1TJ 0.3M
			NO+NC	E2E-X8B3DL18-M1TJ 0.3M	E2E-X8C3L18-M1TJ 0.3M
			NO	E2E-X8B1D18-M1	E2E-X8C118-M1
		53 mm	NC	E2E-X8B218-M1	E2E-X8C218-M1
	M12 Connector		NO+NC	E2E-X8B3D18-M1	E2E-X8C318-M1
		75 mm	NO	E2E-X8B1DL18-M1	E2E-X8C1L18-M1
			NC	E2E-X8B2L18-M1	E2E-X8C2L18-M1
			NO+NC	E2E-X8B3DL18-M1	E2E-X8C3L18-M1
		60 mm *2	NO	E2E-X15B1D30 2M	E2E-X15C130 2M
			NC	E2E-X15B230 2M	E2E-X15C230 2M
	Dro wired (2 m) *4		NO+NC	E2E-X15B3D30 2M	E2E-X15C330 2M
	Pre-wired (2 m) *1		NO	E2E-X15B1DL30 2M	E2E-X15C1L30 2M
		82 mm	NC	E2E-X15B2L30 2M	E2E-X15C2L30 2M
			NO+NC	E2E-X15B3DL30 2M	E2E-X15C3L30 2M
			NO	E2E-X15B1D30-M1TJ 0.3M	E2E-X15C130-M1TJ 0.3M
		60 mm *3	NC	E2E-X15B230-M1TJ 0.3M	E2E-X15C230-M1TJ 0.3M
M30	M12 Pre-wired		NO+NC	E2E-X15B3D30-M1TJ 0.3M	E2E-X15C330-M1TJ 0.3M
(15 mm)	Smartclick Connector (0.3 m)		NO	E2E-X15B1DL30-M1TJ 0.3M	E2E-X15C1L30-M1TJ 0.3M
		82 mm	NC	E2E-X15B2L30-M1TJ 0.3M	E2E-X15C2L30-M1TJ 0.3M
			NO+NC	E2E-X15B3DL30-M1TJ 0.3M	E2E-X15C3L30-M1TJ 0.3M
			NO	E2E-X15B1D30-M1	E2E-X15C130-M1
		58 mm	NC	E2E-X15B230-M1	E2E-X15C230-M1
	M12 Connector		NO+NC	E2E-X15B3D30-M1	E2E-X15C330-M1
	IVI 12 CONNECTOR		NO	E2E-X15B1DL30-M1	E2E-X15C1L30-M1
		80 mm	NC	E2E-X15B2L30-M1	E2E-X15C2L30-M1
			NO+NC	E2E-X15B3DL30-M1	E2E-X15C3L30-M1

^{*1.} Models with 5-m cable length are also available (Example: E2E-X2B1D8 5M)

Note: 1. Models in _____ are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X□□T□" (Example: E2E-X2B1T8 2M).

Operation mode NO can be changed to NC via IO-Link communications.

2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*2.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X2B1D8-R 2M/ E2E-X2B1D8-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X4B1T12-M1TJR 0.3M)

BASIC Model

DC 3-wire (Double distance model) [Refer to Dimensions on page 80.]

Unshielded

Size (Sensing	Connection method	Pody size	Operation	Мо	del
distance)	Connection method	Body size	mode	PNP	NPN
		38 mm *2	NO	E2E-X4MB1D8 2M	E2E-X4MC18 2M
	Pre-wired (2 m) *1	30 111111 2	NC	E2E-X4MB28 2M	E2E-X4MC28 2M
	Fie-wired (2 iii)	48 mm	NO	E2E-X4MB1DL8 2M	E2E-X4MC1L8 2M
		40 11111	NC	E2E-X4MB2L8 2M	E2E-X4MC2L8 2M
		38 mm *3	NO	E2E-X4MB1D8-M1TJ 0.3M	E2E-X4MC18-M1TJ 0.3M
	M12 Pre-wired	30 111111 3	NC	E2E-X4MB28-M1TJ 0.3M	E2E-X4MC28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	48 mm	NO	E2E-X4MB1DL8-M1TJ 0.3M	E2E-X4MC1L8-M1TJ 0.3M
			NC	E2E-X4MB2L8-M1TJ 0.3M	E2E-X4MC2L8-M1TJ 0.3M
		43 mm	NO	E2E-X4MB1D8-M1	E2E-X4MC18-M1
140		43 11111	NC	E2E-X4MB28-M1	E2E-X4MC28-M1
M8 (4 mm)	M12 Connector		NO	E2E-X4MB1DL8-M1	E2E-X4MC1L8-M1
(4 11111)		53 mm	NC	E2E-X4MB2L8-M1	E2E-X4MC2L8-M1
			NO+NC	E2E-X4MB3DL8-M1	E2E-X4MC3L8-M1
		20	NO	E2E-X4MB1D8-M3	E2E-X4MC18-M3
	MO Connector (4 nin)	39 mm	NC	E2E-X4MB28-M3	E2E-X4MC28-M3
	M8 Connector (4-pin)	49 mm	NO	E2E-X4MB1DL8-M3	E2E-X4MC1L8-M3
			NC	E2E-X4MB2L8-M3	E2E-X4MC2L8-M3
	M8 Connector (3-pin)	39 mm	NO	E2E-X4MB1D8-M5	E2E-X4MC18-M5
			NC	E2E-X4MB28-M5	E2E-X4MC28-M5
		49 mm	NO	E2E-X4MB1DL8-M5	E2E-X4MC1L8-M5
			NC	E2E-X4MB2L8-M5	E2E-X4MC2L8-M5
			NO	E2E-X8MB1D12 2M	E2E-X8MC112 2M
		47 mm *2	NC	E2E-X8MB212 2M	E2E-X8MC212 2M
	Dro wired (2 m) *1		NO+NC	E2E-X8MB3D12 2M	E2E-X8MC312 2M
	Pre-wired (2 m) *1		NO	E2E-X8MB1DL12 2M	E2E-X8MC1L12 2M
		69 mm	NC	E2E-X8MB2L12 2M	E2E-X8MC2L12 2M
			NO+NC	E2E-X8MB3DL12 2M	E2E-X8MC3L12 2M
			NO	E2E-X8MB1D12-M1TJ 0.3M	E2E-X8MC112-M1TJ 0.3M
		47 mm *3	NC	E2E-X8MB212-M1TJ 0.3M	E2E-X8MC212-M1TJ 0.3M
M12	M12 Pre-wired		NO+NC	E2E-X8MB3D12-M1TJ 0.3M	E2E-X8MC312-M1TJ 0.3M
(8 mm)	Smartclick Connector (0.3 m)		NO	E2E-X8MB1DL12-M1TJ 0.3M	E2E-X8MC1L12-M1TJ 0.3M
		69 mm	NC	E2E-X8MB2L12-M1TJ 0.3M	E2E-X8MC2L12-M1TJ 0.3M
			NO+NC	E2E-X8MB3DL12-M1TJ 0.3M	E2E-X8MC3L12-M1TJ 0.3M
			NO	E2E-X8MB1D12-M1	E2E-X8MC112-M1
		48 mm	NC	E2E-X8MB212-M1	E2E-X8MC212-M1
	M42 Connector		NO+NC	E2E-X8MB3D12-M1	E2E-X8MC312-M1
	M12 Connector		NO	E2E-X8MB1DL12-M1	E2E-X8MC1L12-M1
		70 mm	NC	E2E-X8MB2L12-M1	E2E-X8MC2L12-M1
			NO+NC	E2E-X8MB3DL12-M1	E2E-X8MC3L12-M1

BASIC Model

Size (Sensing	Connection method	Body size	Operation	Мо	del
distance)	Connection method	Body Size	mode	PNP	NPN
			NO	E2E-X16MB1D18 2M	E2E-X16MC118 2M
		55 mm *2	NC	E2E-X16MB218 2M	E2E-X16MC218 2M
	Pre-wired (2 m) *1		NO+NC	E2E-X16MB3D18 2M	E2E-X16MC318 2M
	Fie-wiled (2 iii)		NO	E2E-X16MB1DL18 2M	E2E-X16MC1L18 2M
		77 mm	NC	E2E-X16MB2L18 2M	E2E-X16MC2L18 2M
			NO+NC	E2E-X16MB3DL18 2M	E2E-X16MC3L18 2M
			NO	E2E-X16MB1D18-M1TJ 0.3M	E2E-X16MC118-M1TJ 0.3M
		55 mm *3	NC	E2E-X16MB218-M1TJ 0.3M	E2E-X16MC218-M1TJ 0.3M
M18	M12 Pre-wired		NO+NC	E2E-X16MB3D18-M1TJ 0.3M	E2E-X16MC318-M1TJ 0.3M
(16 mm)	Smartclick Connector (0.3 m)		NO	E2E-X16MB1DL18-M1TJ 0.3M	E2E-X16MC1L18-M1TJ 0.3M
		77 mm	NC	E2E-X16MB2L18-M1TJ 0.3M	E2E-X16MC2L18-M1TJ 0.3M
			NO+NC	E2E-X16MB3DL18-M1TJ 0.3M	E2E-X16MC3L18-M1TJ 0.3M
		53 mm	NO	E2E-X16MB1D18-M1	E2E-X16MC118-M1
			NC	E2E-X16MB218-M1	E2E-X16MC218-M1
	M12 Connector		NO+NC	E2E-X16MB3D18-M1	E2E-X16MC318-M1
	W12 Connector		NO	E2E-X16MB1DL18-M1	E2E-X16MC1L18-M1
		75 mm	NC	E2E-X16MB2L18-M1	E2E-X16MC2L18-M1
			NO+NC	E2E-X16MB3DL18-M1	E2E-X16MC3L18-M1
			NO	E2E-X30MB1DL30 2M	E2E-X30MC1L30 2M
	Pre-wired (2 m) *1	82 mm *2	NC	E2E-X30MB2L30 2M	E2E-X30MC2L30 2M
			NO+NC	E2E-X30MB3DL30 2M	E2E-X30MC3L30 2M
Moo			NO	E2E-X30MB1DL30-M1TJ 0.3M	E2E-X30MC1L30-M1TJ 0.3M
M30 (30 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	82 mm *3	NC	E2E-X30MB2L30-M1TJ 0.3M	E2E-X30MC2L30-M1TJ 0.3M
(00 11111)	Ca.tonon Co.miootor (0.0 m)		NO+NC	E2E-X30MB3DL30-M1TJ 0.3M	E2E-X30MC3L30-M1TJ 0.3M
			NO	E2E-X30MB1DL30-M1	E2E-X30MC1L30-M1
	M12 Connector	80 mm	NC	E2E-X30MB2L30-M1	E2E-X30MC2L30-M1
			NO+NC	E2E-X30MB3DL30-M1	E2E-X30MC3L30-M1

^{*1.} Models with 5-m cable length are also available (Example: E2E-X8MB1D12 5M)

Note: 1. Models in _____ are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X□□□T□" (Example: E2E-X8MB1T12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*2.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X8MB1D12-R 2M/ E2E-X8MB1D12-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X8MB1D12-M1TJR 0.3M)

BASIC Model

DC 3-wire (Single distance model) [Refer to *Dimensions* on page 79.] Shielded

Size (Sensing	0		Operation	M	odel
distance)	Connection method	Body size	mode	PNP	NPN
		00 *0	NO	E2E-X1R5B1D8 2M	E2E-X1R5C18 2M
	D : 1/0)*4	38 mm *2	NC	E2E-X1R5B28 2M	E2E-X1R5C28 2M
	Pre-wired (2 m) *1	40	NO	E2E-X1R5B1DL8 2M	E2E-X1R5C1L8 2M
		48 mm	NC	E2E-X1R5B2L8 2M	E2E-X1R5C2L8 2M
		00 *0	NO	E2E-X1R5B1D8-M1TJ 0.3M	E2E-X1R5C18-M1TJ 0.3M
	M12 Pre-wired	38 mm *3	NC	E2E-X1R5B28-M1TJ 0.3M	E2E-X1R5C28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	40	NO	E2E-X1R5B1DL8-M1TJ 0.3M	E2E-X1R5C1L8-M1TJ 0.3M
		48 mm	NC	E2E-X1R5B2L8-M1TJ 0.3M	E2E-X1R5C2L8-M1TJ 0.3M
		43 mm	NO	E2E-X1R5B1D8-M1	E2E-X1R5C18-M1
140		43 11111	NC	E2E-X1R5B28-M1	E2E-X1R5C28-M1
M8 (1.5 mm)	M12 Connector		NO	E2E-X1R5B1DL8-M1	E2E-X1R5C1L8-M1
(1.5 11111)		53 mm	NC	E2E-X1R5B2L8-M1	E2E-X1R5C2L8-M1
			NO+NC	E2E-X1R5B3DL8-M1	E2E-X1R5C3L8-M1
		39 mm	NO	E2E-X1R5B1D8-M3	E2E-X1R5C18-M3
	M8 Connector (4-pin)	39 11111	NC	E2E-X1R5B28-M3	E2E-X1R5C28-M3
		49 mm	NO	E2E-X1R5B1DL8-M3	E2E-X1R5C1L8-M3
			NC	E2E-X1R5B2L8-M3	E2E-X1R5C2L8-M3
	M8 Connector (3-pin)	39 mm	NO	E2E-X1R5B1D8-M5	E2E-X1R5C18-M5
		39 11111	NC	E2E-X1R5B28-M5	E2E-X1R5C28-M5
		49 mm	NO	E2E-X1R5B1DL8-M5	E2E-X1R5C1L8-M5
			NC	E2E-X1R5B2L8-M5	E2E-X1R5C2L8-M5
			NO	E2E-X2B1D12 2M *4	E2E-X2C112 2M *4
		47 mm *2	NC	E2E-X2B212 2M	E2E-X2C212 2M
	Pre-wired (2 m) *1		NO+NC	E2E-X2B3D12 2M	E2E-X2C312 2M
	Fie-wired (2 iii)		NO	E2E-X2B1DL12 2M	E2E-X2C1L12 2M
		69 mm	NC	E2E-X2B2L12 2M	E2E-X2C2L12 2M
			NO+NC	E2E-X2B3DL12 2M	E2E-X2C3L12 2M
			NO	E2E-X2B1D12-M1TJ 0.3M	E2E-X2C112-M1TJ 0.3M
		47 mm *3	NC	E2E-X2B212-M1TJ 0.3M	E2E-X2C212-M1TJ 0.3M
M12	M12 Pre-wired		NO+NC	E2E-X2B3D12-M1TJ 0.3M	E2E-X2C312-M1TJ 0.3M
(2 mm)	Smartclick Connector (0.3 m)		NO	E2E-X2B1DL12-M1TJ 0.3M	E2E-X2C1L12-M1TJ 0.3M
		69 mm	NC	E2E-X2B2L12-M1TJ 0.3M	E2E-X2C2L12-M1TJ 0.3M
			NO+NC	E2E-X2B3DL12-M1TJ 0.3M	E2E-X2C3L12-M1TJ 0.3M
			NO	E2E-X2B1D12-M1	E2E-X2C112-M1
		48 mm	NC	E2E-X2B212-M1	E2E-X2C212-M1
	M12 Connector		NO+NC	E2E-X2B3D12-M1	E2E-X2C312-M1
	WITZ COMINGUION		NO	E2E-X2B1DL12-M1	E2E-X2C1L12-M1
		70 mm	NC	E2E-X2B2L12-M1	E2E-X2C2L12-M1
			NO+NC	E2E-X2B3DL12-M1	E2E-X2C3L12-M1

BASIC Model

Size (Sensing	Connection method	Body size	Operation	Мо	del
distance)	Connection method	Bouy Size	mode	PNP	NPN
			NO	E2E-X5B1D18 2M *4	E2E-X5C118 2M *4
		55 mm *2	NC	E2E-X5B218 2M	E2E-X5C218 2M *4
	Pre-wired (2 m) *1		NO+NC	E2E-X5B3D18 2M	E2E-X5C318 2M
	Tie-wiled (2 III)		NO	E2E-X5B1DL18 2M	E2E-X5C1L18 2M
		77 mm	NC	E2E-X5B2L18 2M	E2E-X5C2L18 2M
			NO+NC	E2E-X5B3DL18 2M	E2E-X5C3L18 2M
			NO	E2E-X5B1D18-M1TJ 0.3M	E2E-X5C118-M1TJ 0.3M
		55 mm *3	NC	E2E-X5B218-M1TJ 0.3M	E2E-X5C218-M1TJ 0.3M
M18	M12 Pre-wired		NO+NC	E2E-X5B3D18-M1TJ 0.3M	E2E-X5C318-M1TJ 0.3M
(5 mm)	Smartclick Connector (0.3 m)		NO	E2E-X5B1DL18-M1TJ 0.3M	E2E-X5C1L18-M1TJ 0.3M
		77 mm	NC	E2E-X5B2L18-M1TJ 0.3M	E2E-X5C2L18-M1TJ 0.3M
			NO+NC	E2E-X5B3DL18-M1TJ 0.3M	E2E-X5C3L18-M1TJ 0.3M
			NO	E2E-X5B1D18-M1	E2E-X5C118-M1 *4
		53 mm	NC	E2E-X5B218-M1	E2E-X5C218-M1
	M12 Connector		NO+NC	E2E-X5B3D18-M1	E2E-X5C318-M1
		75 mm	NO	E2E-X5B1DL18-M1	E2E-X5C1L18-M1
			NC	E2E-X5B2L18-M1	E2E-X5C2L18-M1
			NO+NC	E2E-X5B3DL18-M1	E2E-X5C3L18-M1
		60 mm *2	NO	E2E-X10B1D30 2M	E2E-X10C130 2M *4
			NC	E2E-X10B230 2M	E2E-X10C230 2M
	Pre-wired (2 m) *1		NO+NC	E2E-X10B3D30 2M	E2E-X10C330 2M
	Pre-wired (2 m) 1		NO	E2E-X10B1DL30 2M	E2E-X10C1L30 2M
		82 mm	NC	E2E-X10B2L30 2M	E2E-X10C2L30 2M
			NO+NC	E2E-X10B3DL30 2M	E2E-X10C3L30 2M
			NO	E2E-X10B1D30-M1TJ 0.3M	E2E-X10C130-M1TJ 0.3M *4
		60 mm *3	NC	E2E-X10B230-M1TJ 0.3M	E2E-X10C230-M1TJ 0.3M
M30	M12 Pre-wired		NO+NC	E2E-X10B3D30-M1TJ 0.3M	E2E-X10C330-M1TJ 0.3M
(10 mm)	Smartclick Connector (0.3 m)		NO	E2E-X10B1DL30-M1TJ 0.3M	E2E-X10C1L30-M1TJ 0.3M
		82 mm	NC	E2E-X10B2L30-M1TJ 0.3M	E2E-X10C2L30-M1TJ 0.3M
			NO+NC	E2E-X10B3DL30-M1TJ 0.3M	E2E-X10C3L30-M1TJ 0.3M
			NO	E2E-X10B1D30-M1	E2E-X10C130-M1
		58 mm	NC	E2E-X10B230-M1	E2E-X10C230-M1
	M12 Connector		NO+NC	E2E-X10B3D30-M1	E2E-X10C330-M1
	IVITZ COTTRECTOR		NO	E2E-X10B1DL30-M1	E2E-X10C1L30-M1
		80 mm	NC	E2E-X10B2L30-M1	E2E-X10C2L30-M1
			NO+NC	E2E-X10B3DL30-M1	E2E-X10C3L30-M1

^{*1.} Models with 5-m cable length are also available (Example: E2E-X2B1D12 5M)

Note: 1. Models in _____ are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X□□□T□" (Example: E2E-X2B1T12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*2.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X2B1D12-R 2M/ E2E-X2B1D12-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X2B1D12-M1TJR 0.3M)

^{*4.} Models with different frequencies are also available. The model number is E2E-X□□5□ (Example: E2E-X2B15D12 2M).

BASIC Model

DC 3-wire (Single distance model) [Refer to *Dimensions* on page 80.] Unshielded

ize (Sensing	Connection method	Body size	Operation	Мо	del
distance)	Connection method	body Size	mode	PNP	NPN
		38 mm *2	NO	E2E-X2MB1D8 2M	E2E-X2MC18 2M
	Dro wined (2 m) *4	36 11111 2	NC	E2E-X2MB28 2M	E2E-X2MC28 2M
	Pre-wired (2 m) *1	40	NO	E2E-X2MB1DL8 2M	E2E-X2MC1L8 2M
		48 mm	NC	E2E-X2MB2L8 2M	E2E-X2MC2L8 2M
		20 *2	NO	E2E-X2MB1D8-M1TJ 0.3M	E2E-X2MC18-M1TJ 0.3M
	M12 Pre-wired	38 mm *3	NC	E2E-X2MB28-M1TJ 0.3M	E2E-X2MC28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	40	NO	E2E-X2MB1DL8-M1TJ 0.3M	E2E-X2MC1L8-M1TJ 0.3M
		48 mm	NC	E2E-X2MB2L8-M1TJ 0.3M	E2E-X2MC2L8-M1TJ 0.3M
		40	NO	E2E-X2MB1D8-M1	E2E-X2MC18-M1
		43 mm	NC	E2E-X2MB28-M1	E2E-X2MC28-M1
M8 (2mm)	M12 Connector		NO	E2E-X2MB1DL8-M1	E2E-X2MC1L8-M1
(411111)		53 mm	NC	E2E-X2MB2L8-M1	E2E-X2MC2L8-M1
			NO+NC	E2E-X2MB3DL8-M1	E2E-X2MC3L8-M1
		39 mm	NO	E2E-X2MB1D8-M3	E2E-X2MC18-M3
	MO O (4)		NC	E2E-X2MB28-M3	E2E-X2MC28-M3
	M8 Connector (4-pin)	49 mm	NO	E2E-X2MB1DL8-M3	E2E-X2MC1L8-M3
			NC	E2E-X2MB2L8-M3	E2E-X2MC2L8-M3
	M0.0 (0.1)	39 mm	NO	E2E-X2MB1D8-M5	E2E-X2MC18-M5
			NC	E2E-X2MB28-M5	E2E-X2MC28-M5
	M8 Connector (3-pin)	49 mm	NO	E2E-X2MB1DL8-M5	E2E-X2MC1L8-M5
			NC	E2E-X2MB2L8-M5	E2E-X2MC2L8-M5
			NO	E2E-X5MB1D12 2M	E2E-X5MC112 2M *4
		47 mm *2	NC	E2E-X5MB212 2M	E2E-X5MC212 2M *4
	Dro wined (2 m) *4		NO+NC	E2E-X5MB3D12 2M	E2E-X5MC312 2M
	Pre-wired (2 m) *1		NO	E2E-X5MB1DL12 2M	E2E-X5MC1L12 2M
		69 mm	NC	E2E-X5MB2L12 2M	E2E-X5MC2L12 2M
			NO+NC	E2E-X5MB3DL12 2M	E2E-X5MC3L12 2M
			NO	E2E-X5MB1D12-M1TJ 0.3M	E2E-X5MC112-M1TJ 0.3M
		47 mm *3	NC	E2E-X5MB212-M1TJ 0.3M	E2E-X5MC212-M1TJ 0.3M
M12	M12 Pre-wired		NO+NC	E2E-X5MB3D12-M1TJ 0.3M	E2E-X5MC312-M1TJ 0.3M
(5mm)	Smartclick Connector (0.3 m)		NO	E2E-X5MB1DL12-M1TJ 0.3M	E2E-X5MC1L12-M1TJ 0.3M
		69 mm	NC	E2E-X5MB2L12-M1TJ 0.3M	E2E-X5MC2L12-M1TJ 0.3M
			NO+NC	E2E-X5MB3DL12-M1TJ 0.3M	E2E-X5MC3L12-M1TJ 0.3M
			NO	E2E-X5MB1D12-M1	E2E-X5MC112-M1
		48 mm	NC	E2E-X5MB212-M1	E2E-X5MC212-M1
	MAO O		NO+NC	E2E-X5MB3D12-M1	E2E-X5MC312-M1
	M12 Connector		NO	E2E-X5MB1DL12-M1	E2E-X5MC1L12-M1
		70 mm	NC	E2E-X5MB2L12-M1	E2E-X5MC2L12-M1

NO+NC

E2E-X5MB3DL12-M1

E2E-X5MC3L12-M1

BASIC Model

No	Size (Sensing	Connection method	Body size	Operation	Мо	del
Pre-wired (2 m) *1	distance)	Connection method	Bouy Size	mode	PNP	NPN
Pre-wired (2 m) "1				NO	E2E-X10MB1D18 2M	E2E-X10MC118 2M *4
Pre-wired (2 m) "1			55 mm *2	NC	E2E-X10MB218 2M	E2E-X10MC218 2M *4
NO E2E-X10MB1D18 2M E2E-X10MC218 2M NO+NC E2E-X10MB2D18 2M E2E-X10MC218 2M NO+NC E2E-X10MB2D18 2M E2E-X10MC318 2M E2E-		Pro wired (2 m) *1		NO+NC	E2E-X10MB3D18 2M	E2E-X10MC318 2M
NO+NC E2E-X10MB3DL18 2M E2E-X10MC3L18 2M E2E-X10MC3L18 2M E2E-X10MC118-M1TJ 0.3M E2E-X10MC3L18-M1TJ 0.3M E2E-X10MC3L30-M1TJ 0.3M E2E		Pre-wired (2 m) 1		NO	E2E-X10MB1DL18 2M	E2E-X10MC1L18 2M
M18 (10mm) M18 (10mm) M18 (10mm) M18 (10mm) M19 Pre-wired M10 Pre-wired M10 Pre-wired M110 Pre-wired M1110 Pre-wired M11110 Pre			77 mm	NC	E2E-X10MB2L18 2M	E2E-X10MC2L18 2M
M18				NO+NC	E2E-X10MB3DL18 2M	E2E-X10MC3L18 2M
M18				NO	E2E-X10MB1D18-M1TJ 0.3M	E2E-X10MC118-M1TJ 0.3M
NO E2E-X10MB1DL18-M1TJ 0.3M E2E-X10MC2L18-M1TJ 0.3M E2E-X10MC2L13-M1TJ 0.3M E2E-X10MC2L13-M1TJ 0.3M E2E-X10MC2L13-M1TJ 0.3M E2E-X10MC2L30-M1TJ 0.3M E2E-X10MC2			55 mm *3	NC	E2E-X10MB218-M1TJ 0.3M	E2E-X10MC218-M1TJ 0.3M
NC E2E-X10MB2L18-M1TJ 0.3M E2E-X10MC2L18-M1TJ 0.3M NO+NC E2E-X10MB3DL18-M1TJ 0.3M E2E-X10MC3L18-M1TJ 0.3M NO NO+NC E2E-X10MB3DL18-M1 E2E-X10MC3L8-M1 NO NO+NC E2E-X10MB3D18-M1 E2E-X10MC318-M1 NO+NC E2E-X10MB3D18-M1 E2E-X10MC318-M1 NO NO+NC E2E-X10MB3DL18-M1 E2E-X10MC3L8-M1 NO+NC E2E-X10MB3DL18-M1 E2E-X10MC3L8-M1 NO+NC E2E-X10MB3DL18-M1 E2E-X10MC3L8-M1 NO+NC E2E-X10MB3DL18-M1 E2E-X10MC3L18-M1 NO+NC E2E-X10MB3DL18-M1 E2E-X10MC3L18-M1 NO+NC E2E-X10MB3DL18-M1 E2E-X10MC3L18-M1 NO+NC E2E-X10MB3DL18-M1 E2E-X10MC3L18-M1 NO+NC E2E-X10MB3DL18-M1 E2E-X10MC3L30-M NO+NC E2E-X10MB3D30-M1 E2E-X10MC3DM NO+NC E2E-X10MB3D30-M1 E2E-X10MC3DM NO+NC E2E-X10MB3D30-M1 E2E-X10MC3DM NO+NC E2E-X10MB3D30-M1TJ 0.3M E2E-X10MC3DM NO+NC E2E-X10MB3D30-M1TJ 0.3M E2E-X10MC3DM NO+NC E2E-X10MB3D30-M1TJ 0.3M E2E-X10MC3DM-M1TJ 0.3M NO+NC E2E-X10MB3D30-M1 E2E-X10MC3DM-M1TJ 0.3M NO+NC E2E-X10MB3D30-M1 E2E-X10MC3DM-M1TJ 0.3M NO+NC E2E-X10MB3D30-M1 E2E-X10MC3DM-M1 NO+NC E2E-X10MB3D3DM-M1 E2E-X10MC3DM-M1 NO+NC E2	M18	M12 Pre-wired		NO+NC	E2E-X10MB3D18-M1TJ 0.3M	E2E-X10MC318-M1TJ 0.3M
NO+NC E2E-X10MB3DL18-M1TJ 0.3M E2E-X10MC3L18-M1TJ 0.3M	(10mm)	Smartclick Connector (0.3 m)		NO	E2E-X10MB1DL18-M1TJ 0.3M	E2E-X10MC1L18-M1TJ 0.3M
M12 Connector			77 mm	NC	E2E-X10MB2L18-M1TJ 0.3M	E2E-X10MC2L18-M1TJ 0.3M
M12 Connector				NO+NC	E2E-X10MB3DL18-M1TJ 0.3M	E2E-X10MC3L18-M1TJ 0.3M
NO+NC E2E-X10MB3D18-M1 E2E-X10MC318-M1				NO	E2E-X10MB1D18-M1	E2E-X10MC118-M1 *4
NO E2E-X10MB1DL18-M1 E2E-X10MC2L18-M1 NC E2E-X10MB2L18-M1 E2E-X10MC2L18-M1 NC E2E-X10MB3DL18-M1 E2E-X10MC3L18-M1 E2E-X10MC3L18-M1 E2E-X10MC3L18-M1 E2E-X10MC3L18-M1 E2E-X10MC3L18-M1 E2E-X18MC30 2M E2E-X18MC3L30 2M E2E-X18MC3L30 2M E2E-X18MC3L30 2M E2E-X18MC3L30 2M E2E-X18MC3L30 2M E2E-X18MC3L30 2M E2E-X18MC30-M1TJ 0.3M E3E-X18MC30-M1TJ 0.3M E3E-X18MC30-M1TJ 0.3M E3E-X18MC30-M1TJ 0.3M E3E-X18MC30-M1TJ 0.3M E3E-X18MC30-M1TJ 0.3M E3E-X18MC30-M1TJ 0.3M E3E-			53 mm	NC	E2E-X10MB218-M1	E2E-X10MC218-M1
NO E2E-X10MB1DL18-M1 E2E-X10MC1L18-M1 NC E2E-X10MB2DL18-M1 E2E-X10MC2L18-M1 NO+NC E2E-X10MB3DL18-M1 E2E-X10MC2L18-M1 E2E-X10MC3L18-M1 E2E-X10MC3L30-M1 E2E-X10MC		M12 Connector		NO+NC	E2E-X10MB3D18-M1	E2E-X10MC318-M1
NO+NC E2E-X10MB3DL18-M1 E2E-X10MC3L18-M1				NO	E2E-X10MB1DL18-M1	E2E-X10MC1L18-M1
M30 (18mm) M30 (18mm) M30 (18mm) M31 Connector M12 Connector M12 Connector M30 (18mm) M30 (18mm) M31 Connector M30 (18mm) M31 Connector M30 (18mm) M30				NC	E2E-X10MB2L18-M1	E2E-X10MC2L18-M1
Pre-wired (2 m) *1 NC E2E-X18MB230 2M E2E-X18MC230 2M *4 NO+NC E2E-X18MB3D30 2M E2E-X18MC330 2M NO+NC E2E-X18MB1DL30 2M E2E-X18MC2L30 2M NO+NC E2E-X18MB2L30 2M E2E-X18MC2L30 2M NO+NC E2E-X18MB3DL30 2M E2E-X18MC3L30 2M NO+NC E2E-X18MB3DL30 2M E2E-X18MC3L30 2M NO+NC E2E-X18MB3D30-M1TJ 0.3M E2E-X18MC3L30 2M NO+NC E2E-X18MB3D30-M1TJ 0.3M E2E-X18MC30-M1TJ 0.3M NO+NC E2E-X18MB3D30-M1TJ 0.3M E2E-X18MC30-M1TJ 0.3M NO+NC E2E-X18MB3D30-M1TJ 0.3M E2E-X18MC30-M1TJ 0.3M NO+NC E2E-X18MB3D30-M1TJ 0.3M E2E-X18MC31-M1TJ 0.3M NO+NC E2E-X18MB3D30-M1TJ 0.3M E2E-X18MC31-M1TJ 0.3M NO+NC E2E-X18MB3D1-M1TJ 0.MM E2E-X18MC31-M1TJ 0.MM NO+NC E2E-X18MB3D1-M1TJ 0.MM E2E-X18MC31-M1TJ 0.MM NO+NC E2E-X18MB3D30-M1 E2E-X18MC31-M1TJ 0.MM NO+NC E2E-X18MB3D30-M1 E2E-X18MC330-M1 NO+NC E2E-X18MB3D30-M1 E2E-X18MC3130-M1 NO+NC E2E-X18MB				NO+NC	E2E-X10MB3DL18-M1	E2E-X10MC3L18-M1
NO+NC E2E-X18MB3D30 2M E2E-X18MC330 2M 82 mm				NO	E2E-X18MB1D30 2M *4	E2E-X18MC130 2M *4
NO E2E-X18MB1DL30 2M E2E-X18MC2L30 2M NO+NC E2E-X18MB1DL30 2M E2E-X18MC2L30 2M NO+NC E2E-X18MB1DL30 2M E2E-X18MC2L30 2M NO+NC E2E-X18MB1D30-M1TJ 0.3M E2E-X18MC2L30 2M E2E-X18MC2L30 2M E2E-X18MC3L30 2M E2E-X18MC3L30 2M E2E-X18MC3L30 2M E2E-X18MC3L30 2M E2E-X18MC3L30 2M E2E-X18MC3L30 2M E2E-X18MC3L30-M1TJ 0.3M E2E-				NC	E2E-X18MB230 2M	E2E-X18MC230 2M *4
M30 (18mm) M30 (1		Dro wired (2 m) *1		NO+NC	E2E-X18MB3D30 2M	E2E-X18MC330 2M
M30 (18mm) M12 Pre-wired Smartclick Connector (0.3 m) M12 Pre-wired M12 Connector M12 Connector M12 Connector M12 Connector M13 Connector M14 Connector M15 Connector M16 Connector M17 Connector M17 Connector M18 Connector M19 Connector M10 Connector M10 E2E-X18MB3DL30 2M M11		Fre-wired (2 III)		NO	E2E-X18MB1DL30 2M	E2E-X18MC1L30 2M
M30 (18mm) M12 Pre-wired Smartclick Connector (0.3 m) M13 Pre-wired Smartclick Connector (0.3 m) M14 Pre-wired Smartclick Connector (0.3 m) M15 Pre-wired Smartclick Connector (0.3 m) M16 E2E-X18MB2J30-M1TJ 0.3M M17 Pre-wired Smartclick Connector (0.3 m) M18 Pre-wired Smartclick Connector (0.3 m) M0 E2E-X18MB1DL30-M1TJ 0.3M M17 Pre-wired Smartclick Connector (0.3 m) M0 E2E-X18MB1DL30-M1TJ 0.3M M17 Pre-wired Smartclick C230-M1TJ 0.3M M0 E2E-X18MB2L30-M1TJ 0.3M M17 Pre-wired Smartclick C230-M1TJ 0.3M M18 Pre-wired Smartclick C230-M1TJ 0.3M M19 Pre-wired Smartclick C230-M1TJ 0.3M M10 E2E-X18MB2L30-M1 M11 Pre-wired Smartclick C230-M1TJ 0.3M M15 Pre-wired Smartclick C230-M1TJ 0.3M M16 Pre-wired Smartclick C230-M1TJ 0.3M M17 Pre-wired Smartclick C230-M1TJ 0.3M M18 Pre-wired Smartclick C230-M1TJ 0.3M M19 Pre-wired Smartclick C230-M1TJ 0.3M M10 Pre-wired Smartclick C230-M1TJ 0.3M M11 Pre-wired Smartclick C230-M1TJ 0.3M M12 Pre-wired Smartclick C230-M1TJ 0.3M M17 Pre-wired Smartclick C230-M1TJ 0.3M M18 Pre-wired Smartclick C230-M1TJ 0.3M M19 Pre-wired Smartclick C230-M1TJ 0.3M M10 Pre-wired Smartclick C230-M1TJ 0.3M M10 Pre-wired Smartclick C230-M1TJ 0.3M M11 Pre-wired Smartclick C230-M1TJ 0.3M M17 Pre-wired Smartclick C230-M1TJ 0.3M M18 Pre-wired Smartclick C230-M1TJ 0.3M M19 Pre-wired Smartclick C230-M1TJ 0.3M M19 Pre-wired Smartclick C230-M1TJ 0.3M M10 Pre-wired Smartclick C230-M1TJ 0.3M M10 Pre-wired Smartclick C230-M1TJ 0.3M M11 Pre-wired Smartclick C230-M1TJ 0.3M M18 Pre-wired Smartclick C230-M1TJ 0.3M M19 Pre-wired Smartclick C230-M1TJ 0.3M M19 Pre-wired Smartclick C230-M1TJ 0.3M M10 Pre-wired Smartclick C230-M1TJ 0.3M M10 Pre-wired Smartclick C230-M1TJ 0.3M M11 Pre-wired Smartclick C230-M1TJ 0.3M M12 Pre-wired Smartclick C230-M1TJ 0.3M M18 Pre-wired Sm			82 mm	NC	E2E-X18MB2L30 2M	E2E-X18MC2L30 2M
M30 (18mm) M12 Pre-wired Smartclick Connector (0.3 m) M13 Pre-wired Smartclick Connector (0.3 m) M14 Pre-wired Smartclick Connector (0.3 m) M15 Pre-wired Smartclick Connector (0.3 m) M16 Pre-wired Smartclick Connector (0.3 m) M17 Pre-wired Smartclick Connector (0.3 m) M18 Pre-wired Smartclick Connector (0.3 m) M19 Pre-wired Smartclick Connector (0.3 m) M10 E2E-X18MB1D130-M1TJ 0.3M M11 Pre-wired Smartclick Connector (0.3 m) M10 E2E-X18MB1D130-M1TJ 0.3M M11 Pre-wired Smartclick Connector (0.3 m) M10 E2E-X18MB2L30-M1TJ 0.3M M11 Pre-wired Smartclick Connector (0.3 m) M10 E2E-X18MB2L30-M1TJ 0.3M M11 Pre-wired Smartclick Connector (0.3 m) M15 E2E-X18MC2130-M1TJ 0.3M M16 E2E-X18MC2130-M1TJ 0.3M M17 Pre-wired Smartclick Connector (0.3 m) M17 Pre-wired Smartclick Connector (0.3 m) M18 Pre-wired Smartclick Connector (0.3 m) M19 Pre-wired Smartclick Connector (0.3 m) M10 E2E-X18MB2L30-M1TJ 0.3M M11 E2E-X18MC2L30-M1TJ 0.3M M11 Pre-wired Smartclick Connector (0.3 m) M17 Pre-wired Smartclick Connector (0.3 m) M18 Pre-wired Smartclick Connector (0.3 m) M19 Pre-wired Smartclick Connector (0.3 m) M10 E2E-X18MB2L30-M1TJ 0.3M E2E-X18MC2L30-M1TJ 0.3M M11 Pre-wired Smartclick Connector (0.3 m) M17 Pre-wired Smartclick Connector (0.3 m) M18 Pre-wired Smartclick Connector (0.3 m) M19 Pre-wired Smartclick Connector (0.3 m) M10 E2E-X18MB2L30-M1TJ 0.3M E2E-X18MC2L30-M1TJ 0.3M M10 E2E-X18MC2L30-M1TJ 0.3M M10 E2E-X18MC2L30-M1TJ 0.3M M11 Pre-wired Smartclick Connector (0.3 m) M10 E2E-X18MB2L30-M1TJ 0.3M M11 Pre-wired Smartclick Connector (0.3 m) M10 E2E-X18MB2L30-M1TJ 0.3M M11 Pre-wired Smartclick Connector (0.3 m) M11 Pre-wired Smartclick Connector (0.3 m) M11 Pre-wired Smartclick Connector (0.3 m) M12 Pre-wired Smartclick Connector (0.3 m) M12 Pre-wired Smartclick Connector (0.3 m) M18 Pre-wired Smartclick Connector (0.3 m) M19 Pre-wired Smartclick Connector (NO+NC	E2E-X18MB3DL30 2M	E2E-X18MC3L30 2M
M30 (18mm) M12 Pre-wired Smartclick Connector (0.3 m) NO+NC E2E-X18MB3D30-M1TJ 0.3M E2E-X18MC330-M1TJ 0.3M NO E2E-X18MB1DL30-M1TJ 0.3M E2E-X18MC2L30-M1TJ 0.3M NO+NC E2E-X18MB2L30-M1TJ 0.3M E2E-X18MC2L30-M1TJ 0.3M NO+NC E2E-X18MB3DL30-M1TJ 0.3M E2E-X18MC3L30-M1TJ 0.3M NO E2E-X18MB1D30-M1 E2E-X18MC330-M1 NO+NC E2E-X18MB230-M1 E2E-X18MC230-M1 NO+NC E2E-X18MB3D30-M1 E2E-X18MC330-M1 NO+NC E2E-X18MB1DL30-M1 E2E-X18MC1L30-M1 NO+NC E2E-X18MB2L30-M1 E2E-X18MC2L30-M1				NO	E2E-X18MB1D30-M1TJ 0.3M	E2E-X18MC130-M1TJ 0.3M
(18mm) Smartclick Connector (0.3 m)			60 mm *3	NC	E2E-X18MB230-M1TJ 0.3M	E2E-X18MC230-M1TJ 0.3M
82 mm NC E2E-X18MB2L30-M1TJ 0.3M E2E-X18MC2L30-M1TJ 0.3M NO+NC E2E-X18MB3DL30-M1TJ 0.3M E2E-X18MC3L30-M1TJ 0.3M NO+NC E2E-X18MB1D30-M1 E2E-X18MC130-M1 NO E2E-X18MB1D30-M1 E2E-X18MC230-M1 NO+NC E2E-X18MB230-M1 E2E-X18MC330-M1 NO+NC E2E-X18MB3D30-M1 E2E-X18MC330-M1 NO E2E-X18MB1DL30-M1 E2E-X18MC1L30-M1 80 mm NC E2E-X18MB2L30-M1 E2E-X18MC2L30-M1	M30	M12 Pre-wired		NO+NC	E2E-X18MB3D30-M1TJ 0.3M	E2E-X18MC330-M1TJ 0.3M
NO+NC E2E-X18MB3DL30-M1TJ 0.3M E2E-X18MC3L30-M1TJ 0.3M NO E2E-X18MB1D30-M1 E2E-X18MC3L30-M1 NC E2E-X18MB230-M1 E2E-X18MC230-M1 NO+NC E2E-X18MB230-M1 E2E-X18MC330-M1 NO+NC E2E-X18MB1DL30-M1 E2E-X18MC330-M1 NO E2E-X18MB1DL30-M1 E2E-X18MC1L30-M1 NO E2E-X18MB2L30-M1 E2E-X18MC2L30-M1	(18mm)	Smartclick Connector (0.3 m)		NO	E2E-X18MB1DL30-M1TJ 0.3M	E2E-X18MC1L30-M1TJ 0.3M
M12 Connector NO E2E-X18MB1D30-M1 E2E-X18MC130-M1 NC E2E-X18MB230-M1 E2E-X18MC230-M1 NO+NC E2E-X18MB3D30-M1 E2E-X18MC330-M1 NO E2E-X18MB1DL30-M1 E2E-X18MC1L30-M1 NO E2E-X18MB1DL30-M1 E2E-X18MC1L30-M1			82 mm	NC	E2E-X18MB2L30-M1TJ 0.3M	E2E-X18MC2L30-M1TJ 0.3M
M12 Connector NC				NO+NC	E2E-X18MB3DL30-M1TJ 0.3M	E2E-X18MC3L30-M1TJ 0.3M
M12 Connector NO+NC E2E-X18MB3D30-M1 E2E-X18MC330-M1 NO E2E-X18MB1DL30-M1 E2E-X18MC1L30-M1 NC E2E-X18MB2L30-M1 E2E-X18MC2L30-M1				NO	E2E-X18MB1D30-M1	E2E-X18MC130-M1
M12 Connector NO E2E-X18MB1DL30-M1 E2E-X18MC1L30-M1 80 mm NC E2E-X18MB2L30-M1 E2E-X18MC2L30-M1			58 mm	NC	E2E-X18MB230-M1	E2E-X18MC230-M1
NO E2E-X18MB1DL30-M1 E2E-X18MC1L30-M1 80 mm NC E2E-X18MB2L30-M1 E2E-X18MC2L30-M1		M12 Connector		NO+NC	E2E-X18MB3D30-M1	E2E-X18MC330-M1
		WITZ COTTRECTOR		NO	E2E-X18MB1DL30-M1	E2E-X18MC1L30-M1
NO+NC			80 mm	NC	E2E-X18MB2L30-M1	E2E-X18MC2L30-M1
LZE-X TOMOSESO-WIT				NO+NC	E2E-X18MB3DL30-M1	E2E-X18MC3L30-M1

^{*1.} Models with 5-m cable length are also available (Example: E2E-X5MB1D12 5M)

- are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X = To-Link". (Example: E2E-X5MB1T12 2M).

 - Operation mode NO can be changed to NC via IO-Link communications.

 2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*2.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X5MB1D12-R 2M/ E2E-X5MB1D12-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X5MB1D12-M1TJR 2M)

^{*4.} Models with different frequencies are also available. The model number is E2E-X□□5□ (Example: E2E-X10MC1518 2M).

Accessories (Sold Separately)

e-jig (Mounting Sleeves) [Refer to Dimensions on page 83.]

A Mounting Bracket is not provided with the Sensor. It must be ordered separately as required.

Appearance	Model	Applicable Sensor size	Applicable Sensor type
Con.	Y92E-J8S12	M8	Triple distance model
	Y92E-J12S18	M12	Shielded models Pre-wired models
	Y92E-J18S30	M18	Standard body-sized

Nut Sets

A Nut Set is included with the Sensor. Order a Nut Set when required, e.g., if you lose the nuts.

Model	Applicable Sensors	Applicable Sensor diameter	Set contents
Y92E-NWM08-E2EN		M8	Clamping nuts (bronze with nickel plating): 2
Y92E-NWM12-E2EN	E2E NEXT Series Quadruple distance/Triple distance model	M12	Toothed washer (iron with zinc plating): 2
Y92E-NWM18-E2EN	(Shielded models)	M18	
Y92E-NWM30-E2EN		M30	
Y92E-NWM08-E2E	E2E NEXT Series	M8	Clamping nuts (bronze with nickel plating): 2
Y92E-NWM12-E2E	Quadruple distance/Triple distance model (Unshielded models)	M12	Toothed washer (iron with zinc plating): 1
Y92E-NWM18-E2E	Double distance/Single distance model (Shielded/Unshielded models)	M18	
Y92E-NWM30-E2E		M30	

Sensor I/O Connectors (Sold Separately)

For details of the connector, refer to XS5 NEXT Series Round Oil-resistant Connectors (M12 Smartclick) on page 84. For details of the connector, refer to XS5 Series Round Water-resistant Connectors (M12 Smartclick) on page 87. For details of the connector, refer to XS3 Series Round Water-resistant Connectors (M8) on page 91.

Ratings and Specifications

PREMIUM Model

DC 3-wire (Quadruple/Triple distance model)

Shielded

	Types		Quadruple di	stance model			Triple dista	ance model					
	Size	M8	M12	M18	M30	M8	M12	M18	M30				
Item	Model	E2E-X4□8	E2E-X9□12	E2E-X14□18	E2E-X23□30	E2E-X3□8	E2E-X6□12	E2E-X12□18	E2E-X22□30				
Sensing di	istance	4 mm±10%	9 mm±10%	14 mm±10%	23 mm±10%	3 mm±10%	6 mm±10%	12 mm±10%	22 mm±10%				
Setting dis	stance	0 to 3 mm	0 to 6.8 mm	0 to 10.6 mm	0 to 17.6 mm	0 to 2.4 mm	0 to 4.8 mm	0 to 9.6 mm	0 to 16.8 mm				
Differentia		15% max. of ser	nsing distance	1	1	I			1				
Detectable	object	Ferrous metals (For non-ferrous n	netals, refer to the	Engineering Dat	a on page 64.)							
Standard s	sensing	Iron, 12 × 12 × 1 mm	Iron, 27 × 27 × 1 mm	Iron, 42 × 42 × 1 mm	Iron, 69 × 69 × 1 mm	Iron, 9 × 9 × 1 mm	Iron, 18 × 18 × 1 mm	Iron, 36 × 36 × 1 mm	Iron, 66 × 66 × 1 mm				
Response *1	frequency	700 Hz	700 Hz	350 Hz	200 Hz	1,000 Hz	800 Hz	500 Hz	200 Hz				
Power sup	ply voltage	10 to 30 VDC (including 10% ripple (p-p)), Class 2											
Current co	onsumption	1-output models	1-output models: 16 mA max. 1-output models: 16 mA max. 2-output models: 20 mA max.										
Output coi	nfiguration	B□ Models: PNF	open collector, (C□ Models: NPN	open collector								
Operation (with sens approachi	ing object		(B1, C1): NO (No (B2, C2): NC (No				1-output models	(B1, C1): NO (No (B2, C2): NC (No (B3, C3): NO+NC)	ormally closed),				
Control	Load current	1-output models 10 to 30 VDC, C	: lass 2, 50 mA ma	nx.	1-output models: 10 to 30 VDC, Class 2, 100 mA max.	2-output models	lass 2, 100 mA m						
output	Residual voltage	1-output models 2 V max. (Load	: current: 50 mA, C	able length: 2 m)		1-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m)	1-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m 2-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m						
Indicator *	2						ation indicator (grommunication indication		ng at 1 s intervals)				
Protection	circuits	Power supply re	verse polarity pro	tection, Surge su	opressor, Output	short-circuit prote	ction, Output reve	rse polarity protec	ction				
Ambient temperature range Operating: -25 to 60°C Storage: -25 to 70°C (with no icing or condensation) Operating/Storage: -25 to 70°C (with no icing or condensation)													
Ambient h	umidity	Operating/Stora	ge: 35% to 95% (with no condensa	tion)								
Temperatu influence	ıre	-15% to 25% max. of sensing distance at 23°C in the temperature range of -25 to 60°C		ensing distance a ge of -25 to 70°C	t 23°C in the	±10% max. of se -25 to 70°C	ensing distance at	23°C in the temp	erature range of				
Voltage in	fluence		eina dietance at I	rated voltage in th	e rated voltage ±	15% range							
Voltage inf			500 VDC) betwee			10 /0 lalige							
	resistance	,	,	, ,	•	d 0000							
Dielectric :		1,000 VAC, 50/6	ou riz iui i minute	between current	-carrying parts an	u case							
Vibration r (destruction)		, , , , , , , , , , , , , , , , , , ,	-mm double ampl	itude for 2 hours of	each in X, Y, and	Т	T						
Shock resistance (destruction) times each in X, Y, and Z 1,000 m/s² 10 times each in X, Y, and Z directions						500 m/s² 10 times each in X, Y, and Z directions	th in Z 1,000 m/s² 10 times each in X, Y, and Z directions						
Degree of	protection	1: IP67G, Passe 35°C max.)	d OMRON's Oil-re	esistant Compone		dards *3 (Cutting	dard: DIN 40050 F oil type: specified						
Connectio	n method	Pre-wired Model		e length: 2 m), Pre	e-wired Connector	•	d cable length: 0.	3 m) and Connec	tor Models (M12				
	Pre-wired	Approx. 85 g	Approx. 95 g	Approx. 180 g	Approx. 260 g	Approx. 85 g	Approx. 95 g	Approx. 180 g	Approx. 260 g				
Weight*4 (packed state)	M12 Pre-wired Smartclick Connector	Approx. 55 g	Approx. 70 g	Approx. 115 g	Approx. 200 g	Approx. 55 g	Approx. 70 g	Approx. 115 g	Approx. 200 g				
		Approx. 40 g (M8/M12	Approx. 55 g			Approx. 40 g							

	Types		Quadruple di	stance model		Triple distance model				
	Size	M8	M12	M18	M30	M8	M12	M18	M30	
Item	Model	E2E-X4□8	E2E-X9□12	E2E-X14□18	E2E-X23□30	E2E-X3□8	E2E-X6□12	E2E-X12□18	E2E-X22□30	
	Case	Nickel-plated bra	ass							
	Sensing surface	Polybutylene ter	ephthalat (PBT)							
Materials	Clamping nuts	Nickel-plated bra	ass							
Toothed washers Zinc-plated iron										
	Cable	Vinyl chloride (P	VC) Note: Mate	rial of Pre-wired I	Models and Pre-wi	ired Connector M	lodels.			
Main IO-Li functions*		the control outpu	t and timer time s	electing, instability	f diagnosis enablir output (IO-Link m erature, and initial	ode) ON delay tir				
IO-Link	IO-Link specificati on	Ver 1.1								
Commun	Baud rate	COM2 (38.4 kbp	s), COM3 (230.4	kbps)						
ication specifica tions *2 length PD size: 2 bytes, OD size: 1 byte (M-sequence type: TYPE_2_2)										
	Minimum cycle time	COM2: 2.3 ms,	COM3: 0.4 ms							
Accessori	es	Instruction manu	al. Clamping nut	s, Toothed washe	r					

^{*2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

*3. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.

*4. Weight of the standard body-sized model.

²⁻year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value). The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

PREMIUM Model

DC 3-wire (Quadruple/Triple distance model)

Unshielded

	Types	Types Quadruple distance model Triple distance model							
	Size	M8	M12	M18	M30	M8	M12	M18	M30
Item	Model	E2E-X8M□8	E2E-X16M□12	E2E-X30M□18	E2E-X50M□30	E2E-X6M□8	E2E-X10M□12	E2E-X20M□18	E2E-X40M□30
Sensing d	istance	8 mm±10%	16 mm±10%	30 mm±10%	50 mm±10%	6 mm±10%	10 mm±10%	20 mm±10%	40 mm±10%
Setting dis	stance	0 to 6 mm	0 to 12.2 mm	0 to 23 mm	0 to 38.2 mm	0 to 4.8 mm	0 to 8 mm	0 to 16 mm	0 to 32 mm
Differentia	al travel	15% max. of ser	nsing distance						
Detectable object Ferrous metals (For non-ferrous metals, refer to the Engineering Data on page 64.)									
Standard s object	sensing	Iron, 24 × 24 × 1 mm	Iron, 48 × 48 × 1 mm	Iron, 90 × 90 × 1 mm	Iron, 150 x 150 x 1 mm	Iron, 18 × 18 × 1 mm	Iron, 30 × 30 × 1 mm	Iron, 60 × 60 × 1 mm	Iron, 120 x 120 x 1 mm
Response *1	frequency	500 Hz	400 Hz	200 Hz	100 Hz	800 Hz	400 Hz	200 Hz	100 Hz
Power sup	oply voltage	10 to 30 VDC (ir	ncluding 10% rippl	le (p-p)), Class 2					
Current co	onsumption	1-output models	: 16 mA max.				1-output models 2-output models		
Output co	nfiguration	B□ Models: PNI C□ Models: NPI	P open collector N open collector						
Operation (with sens approachi	ing object		(B1, C1): NO (No (B2, C2): NC (No				1-output models 2-output models	s (B1, C1): NO (No s (B2, C2): NC (No s (B3, C3): illy open, Normally	ormally closed),
Control	Load current	1-output models 10 to 30 VDC, C	: Class 2, 50 mA ma	ux.		1-output models: 10 to 30 VDC, Class 2, 100 mA max.	10 to 30 VDC, Class 2, 100 mA max.,		
output Residual voltage 1-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m) 1-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m) 1-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m) 2 v max. (Load current: 50 mA, Cable length: 2 m)				current: 100 mA, Ca	,				
Indicator *	In the Standard I/O mode (SIO mode): Operation indicator (orange, lit) and communication indicator (green, not lit) In the IO-Link communication mode (COM mode): Operation indicator (orange, lit) and communication indicator (green, blinki						ng at 1 s intervals)		
Protection	circuits	Power supply re	verse polarity pro	tection, Surge su	opressor, Output	short-circuit protec	ction, Output reve	rse polarity protec	ction
Ambient to range	emperature	Operating/Stora	ge: -25 to 70°C (w	vith no icing or co	ndensation)				
Ambient h range	umidity	Operating/Stora	ge: 35% to 95% (v	with no condensa	tion)				
Temperatu influence	ure	±15% max. of se -25 to 70°C	ensing distance at	23°C in the temp	erature range of	±10% max. of se -25 to 70°C	ensing distance at	t 23°C in the temp	erature range of
Voltage in	fluence	±1% max. of ser	nsing distance at r	rated voltage in th	e rated voltage ±	15% range			
Insulation	resistance	50 MΩ min. (at	500 VDC) between	n current-carrying	parts and case				
Dielectric	strength	1,000 VAC, 50/6	60 Hz for 1 minute	between current	-carrying parts an	d case			
Vibration r		10 to 55 Hz, 1.5	-mm double ampli	itude for 2 hours	each in X, Y, and	Z directions			
Shock resident					and Z directions				
Pre-wired Models, Pre-wired Connector Models: IEC 60529:IP67, ISO 20653 (old standard: DIN 40050 PART9): IP69K, 1: IP67G, Passed OMRON's Oil-resistant Component Evaluation Standards *3 (Cutting oil type: specified in JIS K 2241: 2 35°C max.) Connector Models: IEC 60529: IP67, ISO 20653 (old standard: DIN 40050 PART9): IP69K									
Connectio	n method		ls (Standard cable 4-pin) Connector			Models (Standar	d cable length: 0.	3 m) and Connec	tor Models (M12
	Pre-wired	Approx. 85 g	Approx. 95 g	Approx. 190 g	Approx. 310 g	Approx. 85 g	Approx. 95 g	Approx. 190 g	Approx. 280 g
Weight*4 (packed state)	M12 Pre-wired Smartclick Connector	Approx. 55 g	Approx. 70 g	Approx. 125 g	Approx. 250 g	Approx. 55 g	Approx. 70 g	Approx. 125 g	Approx. 220 g
	Connector	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 105 g	Approx. 230 g	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 105 g	Approx. 200 g

	Types		Quadruple di	stance model			Triple dista	ance model			
	Size	M8	M12	M18	M30	M8	M12	M18	M30		
Item	Model	E2E-X8M□8	E2E-X16M□12	E2E-X30M□18	E2E-X50M□30	E2E-X6M□8	E2E-X10M□12	E2E-X20M□18	E2E-X40M□30		
	Case	Stainless (SUS303)	Nickel-plated bra	ass		Stainless (SUS303)	Nickel-plated bra	ass			
	Sensing surface	Polybutylene ter	ephthalat (PBT)								
Materials	Clamping nuts	Nickel-plated bra	ass								
	Toothed washers	Zinc-plated iron									
	Cable	Vinyl chloride (P	VC) Note: Mate	rial of Pre-wired I	Models and Pre-w	ired Connector M	lodels.				
Main IO-Li functions*		the control outpu		electing, instability	output (IO-Link m	ode) ON delay tin	ximity judgment di ner time selecting t				
IO-Link	IO-Link specificati on	Ver1.1									
Commun	Baud rate	COM2 (38.4 kbp	os), COM3 (230.4	kbps)							
ication specifica tions *2 PD size: 2 bytes, OD size: 1 byte (M-sequence type: TYPE_2_2)											
	Minimum cycle time	COM2: 2.3 ms, COM3: 0.4 ms									
Accessories Instruction manual, Clamping nuts, Toothed washer											

 ^{1.} The response frequency is an average value. Measurement conditions are as for sensing object, and a set distance of half the sensing distance.
 *2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.
 *3. The Oil-resistant Component Evaluation Standards are OMPONIO over distance.

The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards. 2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value). Actual performance can be expected to decline after two years on average from shipment. The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

^{*4.} Weight of the standard body-sized model.

BASIC Model

DC 3-wire (Double/Single distance model) Shielded

	Types	Double distance					Single distance			
	Size	M8	M12	M18	M30	M8	M12	M18	M30	
Item	Model	E2E-X2□8	E2E-X4□12	E2E-X8□18	E2E-X15□30	E2E-X1R5□8	E2E-X2□12	E2E-X5□18	E2E-X10□30	
Sensing d	istance	2 mm±10%	4 mm±10%	8 mm±10%	15 mm±10%	1.5 mm±10%	2 mm±10%	5 mm±10%	10 mm±10%	
Setting dis	stance	0 to 1.6 mm	0 to 3.2 mm	0 to 6.4 mm	0 to 12 mm	0 to 1.2 mm	0 to 1.6 mm	0 to 4 mm	0 to 8 mm	
Differentia	l travel	15% max. of sensi	ng distance	1		10% max. of sensi	ng distance			
Detectable	object	Ferrous metals (Fo	r non-ferrous me	etals, refer to the	Engineering Dat	a on page 64.)				
Standard s	sensing	Iron, 8 × 8 × 1 mm	Iron, 12 x 12 x 1 mm	Iron, 24 × 24 × 1 mm	Iron, 45 × 45 × 1 mm	Iron, 8 × 8 × 1 mm	Iron, 12 x 12 x 1 mm	Iron, 18 × 18 × 1 mm	Iron, 30 × 30 × 1 mm	
Response *1	frequency	1,500 Hz	1,000 Hz	500 Hz	250 Hz	2,000 Hz	1,500 Hz	600 Hz	400 Hz	
Power sup	ply voltage	10 to 30 VDC (incli	uding 10% ripple	(p-p)), Class 2	I	l	I	I	I	
Current co	onsumption	1-output models: 1 2-output models: 2								
Output co	nfiguration	B□ Models: PNP o C□ Models: NPN o								
Operation (with sens approachi	ing object	1-output models (B 1-output models (B 2-output models (B	2, C2): NC (Nori	mally closed),	Normally closed)	*3				
Control output	Load current	1-output models: 10 to 30 VDC, Class 2, 200 mA max., (-40 to 70°C), 100 mA max., (70 to 85°C) 2-output models: 10 to 30 VDC, Class 2, 50 mA max.	2-output model	Class 2, 200 mA		1-output models: 10 to 30 VDC, Class 2, 200 mA max., (-40 to 70°C), 100 mA max., (70 to 85°C) 2-output models: 10 to 30 VDC, Class 2, 50 mA max.	2-output model	Class 2, 200 mA	,	
Residual voltage		1-output models: 2 V max. (Load current: 200 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m)	m), 2-output model	current: 200 mA,	· ·	1-output models: 2 V max. (Load current: 200 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m)	1-output models: 2 V max. (Load current: 200 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m)			
Indicator *	2					it) and communication			g at 1 s intervals)	
Protection	circuits	Power supply reve	rse polarity prote	ction, Surge sup	pressor, Output	short-circuit protection	on, Output revers	e polarity protec	tion	
Ambient to	emperature	Operating/Storage: Note: The UL terr				lels is -25 to 70°C.				
Ambient h range	umidity	Operating/Storage:	: 35% to 95% (wi	th no condensati	on)					
Temperatu influence	ıre	±15% max. of sens								
Voltage in	fluence	±1% max. of sensi	ng distance at ra	ted voltage in the	rated voltage ±	15% range				
	resistance	50 MΩ min. (at 500	· · · · · · · · · · · · · · · · · · ·	, ,						
Dielectric		1,000 VAC, 50/60	Hz for 1 minute b	etween current-	carrying parts an	d case				
Vibration r (destruction		10 to 55 Hz, 1.5-m	m double amplitu	ude for 2 hours e	ach in X, Y, and	Z directions				
Shock resident		500 m/s ² 10 times each in X, Y, and Z directions	1,000 m/s ² 10 t directions	imes each in X, \	Υ, and Z	500 m/s ² 10 times each in X, Y, and Z directions	1,000 m/s ² 10 t directions	imes each in X,	Y, and Z	
Pre-wired Models, Pre-wired Connector Models: IEC 60529:IP67, ISO 20653 (old standard: DIN 40050 PART9): IP69K Pre-wired Models, Pre-wired Connector Models: IEC 60529:IP67, ISO 20653 (old standard: DIN 40050 PART9): IP69K Pre-wired Models, Pre-wired Connector Models: IEC 60529:IP67, ISO 20653 (old standard: DIN 40050 PART9): IP69K Pre-wired Models, Pre-wired Connector Models: IEC 60529:IP67, ISO 20653 (old standard: DIN 40050 PART9): IP69K										
Connectio	n method	Pre-wired Models (Models (M12 Conn				Models (Standard o	cable length: 0.3	m) and Connect	or	
	Pre-wired	Approx. 85 g	Approx. 95 g	Approx. 170 g	Approx. 240 g	Approx. 85 g	Approx. 95 g	Approx. 170 g	Approx. 240 g	
Weight *5 (packed state)	M12 Pre-wired Smartclick Connector	Approx. 55 g	Approx. 70 g	Approx. 105 g	Approx. 170 g	Approx. 55 g	Approx. 70 g	Approx. 105 g	Approx. 170 g	
ļ	Connector	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 85 g	Approx. 160 g	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 85 g	Approx. 160 g	

	Types		Double di	stance			Single di	stance				
	Size	M8	M12	M18	M30	M8	M12	M18	M30			
Item	Model	E2E-X2□8	E2E-X4□12	E2E-X8□18	E2E-X15□30	E2E-X1R5□8	E2E-X2□12	E2E-X5□18	E2E-X10□30			
	Case	Stainless (SUS303)	Nickel-plated b	rass		Stainless (SUS303)	Nickel-plated b	rass				
	Sensing surface	Polybutylene terep	Polybutylene terephthalat (PBT)									
Materials	Clamping nuts	Nickel-plated brass	Nickel-plated brass									
	Toothed washers	Zinc-plated iron										
	Cable	Vinyl chloride (PV	C) Note: Materi	al of Pre-wired M	lodels and Pre-w	rired Connector Mod	els.					
Main IO-Li functions			and timer time sele	ecting, instability	output (IO-Link m	ng, excessive proxin node) ON delay time I reset						
IO-Link	IO-Link specification	Ver1.1										
Commun	Baud rate	COM2 (38.4 kbps)	, COM3 (230.4 kl	ops)								
ication specifica	Data length	PD size: 2 bytes, 0	PD size: 2 bytes, OD size: 1 byte (M-sequence type: TYPE_2_2)									
tions *2 Minimum cycle time COM2: 2.3 ms, COM3: 0.4 ms												
Accessories Instruction manual, Clamping nuts, Toothed washer												

^{*2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

*5. Weight of the standard body-sized model.

^{*3.} Dual-output specification for the M8-size models is only applicable to long-size M12 Connector models.

*4. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards. 2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value). Actual performance can be expected to decline after two years on average from the pre-wired Connector Model verified years of oil resistance when mating with Round Oil resista Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

BASIC Model

DC 3-wire (Double/Single distance model)

Unshielded

	Types		Double dista	nce model			Single distar	nce model	
	Size	M8	M12	M18	M30	M8	M12	M18	M30
Item	Model	E2E-X4M□8	E2E-X8M□12	E2E-X16M□18	E2E-X30M□30	E2E-X2M□8	E2E-X5M□12	E2E-X10M□18	E2E-X18M□30
Sensing d	istance	4 mm±10%	8 mm±10%	16 mm±10%	30 mm±10%	2 mm±10%	5 mm±10%	10 mm±10%	18 mm±10%
Setting dis	stance	0 to 3.2 mm	0 to 6.4 mm	0 to 12.8 mm	0 to 24 mm	0 to 1.6 mm	0 to 4 mm	0 to 8 mm	0 to 14.4 mm
Differentia	ıl travel	15% max. of sensi	ng distance			10% max. of sensi	ng distance		
Detectable	e object	Ferrous metals (Fo	r non-ferrous me	tals, refer to the	Engineering Dat	a on page 64.)	T.		
Standard s	sensing	Iron,	Iron, 24 × 24 × 1 mm	Iron,	Iron,	Iron,	Iron,	Iron,	Iron,
object	frequency	12 × 12 × 1 mm	24 × 24 × 1 mm	48 × 48 × 1 mm	90 × 90 × 1 mm	8 × 8 × 1 mm	15 × 15 × 1 mm	30 × 30 × 1 mm	54 × 54 × 1 mm
*1	rrequericy	1,000 Hz	800 Hz	400 Hz	100 Hz	1,000 Hz	800 Hz	400 Hz	100 Hz
Power sup	ply voltage	10 to 30 VDC (inclu	iding 10% ripple	(p-p)), Class 2				1	1
Current co	onsumption	1-output models: 10 2-output models: 20							
Output co	nfiguration	B□ Models: PNP o C□ Models: NPN o							
Operation (with sens approachi	ing object	1-output models (B 1-output models (B 2-output models (B	2, C3): NC (Norr	nally closed)	Normally closed)	*3			
Control	Load current	1-output models: 10 to 30 VDC, Class 2, 200 mA max., (-40 to 70°C), 100 mA max., (70 to 85°C) 2-output models: 10 to 30 VDC, Class 2, 50 mA max.	2-output model	Class 2, 200 mA		1-output models: 10 to 30 VDC, Class 2, 200 mA max., (-40 to 70°C), 100 mA max., (70 to 85°C) 2-output models: 10 to 30 VDC, Class 2, 50 mA max.	2-output model	Class 2, 200 mA	•
	Residual voltage	1-output models: 2 V max. (Load current: 200 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m)	1-output models: 2 V max. (Load current: 200 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m)			1-output models: 2 V max. (Load current: 200 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m)	2-output models: 2 V max. (under load current of 100 mA with cable length of 2 m)		
Indicator *	2					it) and communication			g at 1 s intervals)
Protection	circuits	Power supply reve	rse polarity prote	ction, Surge sup	pressor, Output	short-circuit protection	on, Output revers	e polarity protect	ion
Ambient to range	emperature	Operating/Storage: Note: The UL tem				els is -25 to 70°C.			
Ambient h range	umidity	Operating/Storage:	35% to 95% (wi	th no condensati	on)				
Temperatu influence	ure	±15% max. of sens ±10% max. of sens	ing distance at 2	3°C in the temper	erature range of	25 to 70°C			
Voltage in		±1% max. of sensi		_	_	15% range			
	resistance	50 MΩ min. (at 500	· · · · · · · · · · · · · · · · · · ·	, ,	•				
Vibration r	resistance	1,000 VAC, 50/60 I 10 to 55 Hz, 1.5-mi							
(destruction) Shock resistance (destruction) 1,000 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions			imes each in X, `	∕, and Z					
Pre-wired Models, Pre-wired Connector Models: IEC 60529:IP67, ISO 20653 (old standard: DIN 40050 PART9): IP69K, 1: IP67G, Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:20 35°C max.) Connector Models: IEC 60529:IP67, ISO 20653 (old standard: DIN 40050 PART9): IP69K									
Connectio	n method	Pre-wired Models (M8 (4-pin) Connec			wired Connector	Models (Standard o	able length: 0.3 r	m) and Models (M	112 Connector,
Weight *5 (packed	Pre-wired M12 Pre-wired Smartclick Connector	Approx. 85 g Approx. 55 g	Approx. 70 g	Approx. 170 g Approx. 105 g	Approx. 280 g Approx. 220 g	Approx. 85 g Approx. 55 g	Approx. 70 g	Approx. 170 g Approx. 105 g	Approx. 240 g Approx. 170 g
state)	Connector	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 85 g	Approx. 200 g	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 85 g	Approx. 160 g

	Types		Double distar	nce model			Single distar	nce model	
	Size	M8	M12	M18	M30	M8	M12	M18	M30
ltem	Model	E2E-X4M□8	E2E-X8M□12	E2E-X16M□18	E2E-X30M□30	E2E-X2M□8	E2E-X5M□12	E2E-X10M□18	E2E-X18M□30
	Case	Stainless (SUS303)	Nickel-plated b	ass		Stainless (SUS303)	Nickel-plated bi	rass	
	Sensing surface	Polybutylene terep	hthalat (PBT)				•		
Materials	Clamping nuts	Nickel-plated brass	3						
	Toothed washers	Zinc-plated iron							
	Cable	Vinyl chloride (PVC) Note: Materi	al of Pre-wired M	odels and Pre-w	ired Connector Mod	dels.		
Main IO-Li functions			nd timer time sele	ecting, instability	output (IO-Link m	ng, excessive proxir ode) ON delay time I reset			
IO-Link	IO-Link specificati on	Ver 1.1	Ver 1.1						
Commun	Baud rate	COM2 (38.4 kbps), COM3 (230.4 kbps)							
ication specifica tions *2 PD size: 2 bytes, OD size: 1 byte (M-sequence type: TYPE_2_2)									
	Minimum cycle time	COM2: 2.3 ms, COM3: 0.4 ms							
Accessori	es	Instruction manual	Clamping nuts,	Toothed washer					

sensing object, and a set distance of half the sensing distance.

*5. Weight of the standard body-sized model.

^{*2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

*3. Dual-output specification for the M8-size models is only applicable to long-size M12 Connector models.


*4. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards. 2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value). Actual performance can be expected to decline after two years on average from shipment. The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

Engineering Data (Reference Value)

Sensing Area


PREMIUM Model

Quadruple distance model Shielded




Triple distance model


Shielded



Unshielded




Unshielded




BASIC Model

Double distance model Shielded




Single distance model


Shielded



Unshielded



Unshielded




Influence of Sensing Object Size and Material


PREMIUM Model

Shielded

Quadruple distance model Size: M8 E2E-X4□8




Triple distance model Size: M8 E2E-X3□8




Unshielded


Quadruple distance model Size: M8 E2E-X8M□8




Triple distance model Size: M8 E2E-X6M□8




Size: M12 E2E-X9□12




Size: M12 E2E-X6□12




Size: M12 E2E-X16M□12




Size: M12 E2E-X10M□12




Size: M18 E2E-X14□18




Size: M18 E2E-X12□18




Size: M18 E2E-X30M□18




Size: M18 E2E-X20M□18




Size: M30 E2E-X23□30




Size: M30 E2E-X22□30



Size: M30 E2E-X50M□30




Size: M30 E2E-X40M□30




BASIC Model

Shielded

Double distance model Size: M8 E2E-X2□8




Single distance model Size: M8 E2E-X1R5□8




Unshielded


Double distance model Size: M8 E2E-X4M□8




Single distance model Size: M8 E2E-X2M□8




Size: M12 E2E-X4□12




Size: M12 E2E-X2□12




Size: M12 E2E-X8M□12




Size: M12 E2E-X5M□12




Size: M18 E2E-X8□18




Size: M18 E2E-X5□18




Size: M18 E2E-X16M□18




Size: M18 E2E-X10M□18




Size: M30 E2E-X15□30




Size: M30 E2E-X10□30



Size: M30 E2E-X30M□30



Size: M30 E2E-X18M□30




Monitor Output vs. Sensing Distance

PREMIUM Model

Shielded


Quadruple distance model

Size: M8 E2E-X4□8



Triple model


Size: M8 E2E-X3□8




Unshielded

Quadruple distance model


Size: M8 E2E-X8M□8




Triple distance model Size: M8 E2E-X6M□8




Size: M12 E2E-X9□12




Size: M12 E2E-X6□12




Size: M12 E2E-X16M□12




Size: M12 E2E-X10M□12




Size: M18 E2E-X14□18




Size: M18 E2E-X12□18




Size: M18 E2E-X30M□18




Size: M18 E2E-X20M□18




Size: M30 E2E-X23□30




Size: M30 E2E-X22□30



Size: M30 E2E-X50M□30




Size: M30 E2E-X40M□30




BASIC Model

Shielded

Double distance model Size: M8 E2E-X2□8




Single distance model Size: M8 E2E-X1R5□8




Unshielded


Double distance model Size: M8 E2E-X4M□8




Single distance model Size: M8 E2E-X2M□8




Size: M12 E2E-X4□12




Size: M12 E2E-X2□12




Size: M12 E2E-X8M□12




Size: M12 E2E-X5M□12




Size: M18 E2E-X8□18




Size: M18 E2E-X5□18




Size: M18 E2E-X16M□18




Size: M18 E2E-X10M□18




Size: M30 E2E-X15□30




Size: M30 E2E-X10□30



Size: M30 E2E-X30M□30



Size: M30 E2E-X18M□30



I/O Circuit Diagrams/Timing charts

DC 3-wire

PNP output


		Output	circuit
Operation mode	Model	Standard I/O mode (SIO mode) When using as a general	IO-Link Communication mode (COM mode) When using the Sensor connected to IO- Link Master Unit *1
NO	E2E-□B1	Proximity sensor main circuit Load Blue (3) 0V	Brown (1) L+ (1) Proximity sensor main circuit Blue (3) L- (3) IO-Link master
NC	E2E-□B2	DC10 to 30V Brown (1) Proximity sensor main circuit Black (2) OUT Circuit OV Note: M8 (3-pin) Connector: (1)(4)(3)	
NO+NC	E2E-□B3	Proximity Sensor Main circuit Black (4)(NO) *2 OUT1 White (2) Load (NC) *2 OUT2 Load Blue (3) OV	Brown (1) L+ (1) Black (4) C/Q (4) Sensor main circuit White (2) (NC) '2 DI (2) Blue (3) L- (3) IO-Link master

- *1. In the IO-Link mode, the cord between the IO-Link master and sensor must have a length of 20 m or less.
 *2. This is the factory setting. For models with IO-Link, the operation mode can be changed by the IO-Link communications.

Connector Pin Arrangement

M12 Connector M12 Smartclick Connector	M8 (4-pin) Connector	M8 (3-pin) Connector
② 4 3	(24 (1 3)	(1) ⁽⁴⁾ (3)

PNP output



Please contact your OMRON sales representative regarding assignment of data.


- *1. This is the factory setting. For models with IO-Link, the operation mode can be changed by the IO-Link communications.
- *2. If using a model with IO-Link as a general sensor or using a model without IO-Link, it operates in the standard I/O mode (SIO mode).

NPN output

Operation mode	Model	Output circuit
NO	E2E-□C1	DC10 to 30V Brown (1) Proximity sensor main circuit Black (4) Blue (3) 0V
NC	E2E-□C2	DC10 to 30V Brown (1) Proximity Sensor main circuit Black (2) Note: M8 (3-pin) Connector: (1)(4)(3)
NO+NC	E2E-□C3	Proximity sensor main circuit Black (4)(NO) White (2)(NC) Blue (3) OV

Connector Pin Arrangement

M12 Connector M12 Smartclick Connector	M8 (4-pin) Connector	M8 (3-pin) Connector
② (4) ② (3)		(1) (4) (3)




Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

∆WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols



↑ WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Otherwise, explosion may result.

Never use the product with an AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- Do not use the product in environments subject to flammable or explosive gases.
- 2. Do not attempt to disassemble, repair, or modify the product.
- Do not use a voltage that exceeds the rated operating voltage range.
 - Applying a voltage that is higher than the operating voltage range may result in explosion or fire.
- Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or fire.
- If the power supply is connected directly without a load, the internal elements may explode or burn.



Dispose of the product according to applicable regulations (laws).

Precautions for Correct Use

Do not use the product in any atmosphere or environment that exceeds the ratings.

Operating Environment


- 1. Do not install the Sensor in the following locations.
 - Outdoor locations directly subject to sunlight, rain, snow, waterdroplets, or oil.
 - (2) Locations subject to atmospheres with chemical vapors, inparticular solvents and acids.
 - (3) Locations subject to corrosive gases.
- 2. The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com) for typical measures.
- 3. Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- 5. The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ratio recommended by its manufacturer
 - Usage in oil or water is prohibited
 - Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.
- 6. When turning on the power by influence of temperature environment, an outputmis-pulse sometimes occurs. After the sensor has passed for 300 msec after turning on, please use in the stable state.
- 7. The sensor is adjusted with a high degree of accuracy, so do not use in the environment with sudden temperature change.
- Operation check is performed using an OMRON's IO-Link master. If using an IO-Link master from another company, perform the operation check in advance.

Design

Influence of Surrounding Metal

When mounting the Proximity Sensor using a nut, only use the provided nut. And ensure that the minimum distances given in the following table are maintained.

When mounting the Proximity Sensor using a nut, only use the provided nut. Nuts that are supplied along with each Sensor are different. Refer to Dimensions for details on shapes.



(Unit: mm)

Shielded


Туре	Model	L	d	D	m	n
	E2E-X4□8	3	30	3	12	20
Quadruple distance	E2E-X9□12	2	40	2	27	30
model	E2E-X14□18	2	60	2	42	70
	E2E-X23□30	2	100	2	69	100
	E2E-X3□8	0	20	0	9	18
Triple distance	E2E-X6□12	0	20	0	18	20
model	E2E-X12□18	0	50	0	36	54
	E2E-X22□30	0	70	0	66	90
	E2E-X2□8	0	8	0	4.5	12
Double distance	E2E-X4□12	0	18	0	12	18
model	E2E-X8□18	0	27	0	24	27
	E2E-X15□30	0	45	0	45	45
	E2E-X1R5□8	0	8	0	4.5	12
Single distance	E2E-X2□12	0	12	0	8	18
model	E2E-X5□18	0	18	0	20	27
	E2E-X10□30	0	30	0	40	45

Unshielded

Models	Model	L	d	D	m	n
	E2E-X8M□8	12	40	12	24	40
Quadruple distance	E2E-X16M□12	21	70	21	48	80
model	E2E-X30M□18	46	130	46	90	110
	E2E-X50M□30	60	200	60	150	180
	E2E-X6M□8	10	30	10	18	30
Triple distance model	E2E-X10M□12	16	50	16	30	50
	E2E-X20M□18	31	90	31	60	80
	E2E-X40M□30 *	50	170	50	120	140
	E2E-X4M□8	9	24	9	8	24
Double distance	E2E-X8M□12	11	40	11	20	40
model	E2E-X16M□18	21	70	21	48	70
	E2E-X30M□30	40	120	40	90	120
Single distance	E2E-X2M□8	6	24	6	8	24
	E2E-X5M□12	11	40	11	20	36
model	E2E-X10M□18	18	55	18	40	54
	E2E-X18M□30	25	90	25	70	90

^{*} If you use the model E2E-X40M□30, the panel thickness (t) is 4 mm or less.

When the Proximity Sensor is mounted in metal, ensure that the minimum distances given in the following table are maintained.



Shielded

(Unit: mm)

Models	Model	ı	d	D	m	n
	E2E-X4□8	4	30	4	12	20
Quadruple distance	E2E-X9□12	6	40	6	27	30
model	E2E-X14□18	7	60	7	42	70
	E2E-X23□30	9	100	9	69	100
	E2E-X3□8	2	20	2	9	18
Triple distance	E2E-X6□12	4	20	4	18	20
model	E2E-X12□18	4	50	4	36	54
	E2E-X22□30	8	70	8	66	90
	E2E-X2□8	0	8	0	4.5	12
Double distance	E2E-X4□12	2.4	18	2.4	12	18
model	E2E-X8□18	3.6	27	3.6	24	27
	E2E-X15□30	6	45	6	45	45
Single distance model	E2E-X1R5□8	0	8	0	4.5	12
	E2E-X2□12	0	12	0	8	18
	E2E-X5□18	0	18	0	20	27
	E2E-X10□30	0	30	0	40	45

Unshielded


Models	Model	ı	d	D	m	n
	E2E-X8M□8	15	40	15	24	40
Quadruple distance	E2E-X16M□12	25	70	25	48	80
model	E2E-X30M□18	50	130	50	90	110
	E2E-X50M□30	65	200	65	150	180
	E2E-X6M□8	13	30	13	18	30
Triple distance	E2E-X10M□12	20	50	20	30	50
model	E2E-X20M□18	35	90	35	60	80
	E2E-X40M□30 *	55	170	55	120	140
	E2E-X4M□8	12	24	12	8	24
Double distance	E2E-X8M□12	15	40	15	20	40
model	E2E-X16M□18	25	70	25	48	70
	E2E-X30M□30	45	120	45	90	120
Single distance	E2E-X2M□8	6	24	6	8	24
	E2E-X5M□12	15	40	15	20	36
model	E2E-X10M□18	22	55	22	40	54
	E2E-X18M□30	30	90	30	70	90

^{*} If you use the model E2E-X40M□30, the panel thickness (t) is 4 mm or less.

E2E NEXT Series

Mutual Interference

When installing two or more Proximity Sensors face-to-face or sideby-side, ensure that the minimum distances given in the following table are maintained.



Shielded

(Unit: mm)

		Item		
Models	Model	Α	В	
	E2E-X4□8	40	20	
Quadruple distance	E2E-X9□12	60	35	
model	E2E-X14□18	90	50	
	E2E-X23□30	150	90	
Triple distance model	E2E-X3□8	25	20	
	E2E-X6□12	40	30	
	E2E-X12□18	70	45	
	E2E-X22□30	150	90	
	E2E-X2□8	20	15	
Double distance model	E2E-X4□12	30	20	
Double distance model	E2E-X8□18	60	35	
	E2E-X15□30	110	90	
Single distance model	E2E-X1R5□8	20	15	
	E2E-X2□12	30	20	
	E2E-X5□18	50	35	
	E2E-X10□30	100	70	


Unshielded

Models	Model	Item		
Wodels	wodei	Α	В	
Quadruple distance	E2E-X8M□8	80	60	
	E2E-X16M□12	160	120	
model	E2E-X30M□18	360	300	
	E2E-X50M□30	700	480	
	E2E-X6M□8	80	60	
Triple distance model	E2E-X10M□12	120	100	
Triple distance model	E2E-X20M□18	200	120	
	E2E-X40M□30	380	300	
	E2E-X4M□8	80	60	
Double distance model	E2E-X8M□12	120	100	
Double distance model	E2E-X16M□18	200	120	
	E2E-X30M□30	350	300	
Single distance model	E2E-X2M□8	80	60	
	E2E-X5M□12	120	100	
	E2E-X10M□18	200	110	
	E2E-X18M□30	300	200	

Mounting

Tightening Force

Do not tighten the sensor mounting nuts with excessive force. Secure the mounting nuts to the corresponding torque values in the following table.



Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table.

(A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)

2. The following strengths assume washers are being used.

Quadruple distance model, Triple distance model, Spatter-resistant Triple distance model

		Part A		Part B
Size	Shielded	Dimension (mm)	Torque	Torque
M8	Shielded	9	4 N·m	10 N⋅m
IVIO	Unshielded	3	4 111111	IO IN-III
M12	Shielded	16	8 N⋅m	15 N⋅m
IVITZ	Unshielded	9	6 N⋅m	13 14-111
M18	Shielded	16	15 N⋅m	60 N⋅m
IVI I O	Unshielded	3	15 N·m	00 IN-III
M30	Shielded	23	40 N⋅m	80 N·m
10130	Unshielded	8	40 N·M	OU 14-111

Double distance model, Single distance model, Spatter-resistant Triple distance model, Spatter-resistant Single distance model

		Part A		Part B
Size	Shielded	Dimension (mm)	Torque	Torque
M8	Shielded	9	0.11	12 N⋅m
IVIO	Unshielded	3	9 N⋅m	12 N-111
M12			30 N·m	
M18			70 N⋅m	
M30			180	N⋅m

Dimensions


Sensor PREMIUM Model

DC 3-wire (Quadruple/Triple distance model)

Pre-wired Models Pre-wired Connector Models (Shielded)

Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.







DC 3-wire (Long-body Quadruple/Triple distance model)

Pre-wired Models Pre-wired Connector Models (Shielded)

Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.








Two clamping nuts


Two toothed washe


Operation mode: NO, NC Type 4-dia. vinyl-insulated round cable with 3 conductors (Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.05 mm), Standard length: 2 m Note: Operation mode: NO+NC Type 4.3-dia. vinylinsulated round cable with 4 conductors.












*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF) IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))

Pre-wired Connector Models (-M1TJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

\Box	Dimensions	F (mm)
$\downarrow \downarrow$	M8	8.5 dia. +0.5
- F →:	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire

10 mm	Dimensions	R (mm)
R	M8	12
Ш	M12	12
	M18	18
	M30	10

Wire pullo	out positio	n
	Dimensions	

Sc	•	
	Dimensions	Sc (mm)
	M8	- (0)
	M12	- (0)
	M18	2.5
	M30	2.5


Sensors PREMIUM Model


DC 3-wire (Quadruple/Triple distance model)

Pre-wired Models Pre-wired Connector Models (Unshielded)



Refer to the figure below the table for the connections of the Pre-wired Connector Model.






DC 3-wire (Long-body Quadruple/Triple distance model)


Pre-wired Models Pre-wired Connector Models (Unshielded)




Refer to the figure below the table for the connections of the Pre-wired


Connector Model.















*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF) IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))

Pre-wired Connector Models (-M1TJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions


_		
(1)	Dimensions	F (mm)
$\downarrow \downarrow$	M8	8.5 dia. +0.5
-F→;	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



Dimensions	R (mm)	
M8	12	
M12	12	
M18	18	
M30	10	



Dime	ensions	Sc (mm)
	M8	(0)
ı	VI12	- (0)
ı	M18	2.5
	08N	2.5

Sensors PREMIUM Model

DC 3-wire (Quadruple/Triple distance model)

Connector Models (Shielded)





DC 3-wire (Long-body Quadruple/Triple distance model)


Connector Models (Shielded)













E2E-X□8-M1







E2E-X L8-M1






E2E-X□12-M1






E2E-X L12-M1







E2E-X□18-M1






E2E-X L18-M1






E2E-X□30-M1



E2E-X□L30-M1



*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF) IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))

Mounting Hole Dimensions



Dimensions	F (mm)
M8 8.5 dia. +0.5	
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

E2E NEXT Series

Sensors PREMIUM Model

DC 3-wire (Quadruple/Triple distance model)

Connector Models (Unshielded)




DC 3-wire (Long-body Quadruple/Triple distance model)


Connector Models (Unshielded)




E2E-X M 8-M3/M5




E2E-X M L8-M3/M5




E2E-X□M□8-M1




E2E-X M L8-M1



E2E-X M 12-M1



E2E-X M L12-M1



*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF) IO-Link Communication mode (COM mode): Operation indicator

(orange/ON), communication indicator (green/Flashing (1sec cycle))

Mounting Hole Dimensions




Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5


Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

E2E-X M L18-M1 75 29 dia.-Indicators *1 _12

M18 x P1



M12 x P1



mode

Sensors BASIC Model

DC 3-wire (Double/Single distance model)

Pre-wired Models Pre-wired Connector Models (Shielded)




Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.


DC 3-wire (Long-body Double/Single distance model)


Pre-wired Models Pre-wired Connector Models (Shielded)


Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model

























*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF) IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))

Pre-wired Connector Models (-M1TJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions



Note: When installed with a long hole there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



Dimensions R (mm		
M8	12	
M12	12	
M18	18	
M30		

Wire pullout position

Sc	
	Dim

١	Dimensions	Sc (mm)	
<i>†</i>	M8	(0)	
M12	- (0)		
	M18	2.5	
	M30	2.5	

Sensors BASIC Model

DC 3-wire (Double/Single distance model)

Pre-wired Models Pre-wired Connector Models (Unshielded)


Refer to the figure below the table for the connections of the Pre-wired

Connector Model


DC 3-wire (Long-body Double/Single distance model)


Pre-wired Models Pre-wired Connector Models (Unshielded)


Refer to the figure below the table for the connections of the Pre-wired Connector Model




Operation mode: NO, NC Type 4-dia. vinyl-insulated round cable with 3 conductors (Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.05 mm), Standard length: 2 m











Operation mode: NO, NC Type -dia. vinyl-insulated round cable with 3 conductors (Conductor cross section: 0.2 mm2 (AWG24), Insulator diameter: 1.05 mm), Standard length: 2 m Note: Operation mode: NO+NC Type 4.3-dia. vinylinsulated round cable with 4 conductors













*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF) IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))



(n

Pre-wired Connector Models (-M1TJ)




Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

	_	
\triangle	Dimensions	F (mm)
W	M8	8.5 dia. +0.5
 F-	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



R (mm)	
12	1
18	

Wire pullout position		
Sc	Dimensions	Sc (mm)
	M8	- (0)
	M12	- (0)
	M18	2.5
	M30	2.5

Sensors BASIC Model DC 3-wire (Double/Single distance model) Connector Models



DC 3-wire (Long-body Double/Single distance model)


Connector Models (Shielded)




E2E-X□8-M3/M5

(Shielded)






E2E-X□L8-M3/M5




E2E-X□8-M1






E2E-X□L8-M1






E2E-X□12-M1







E2E-X L12-M1







E2E-X□18-M1






E2E-X□L18-M1






E2E-X□30-M1





E2E-X L30-M1



*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF)
IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))

Mounting Hole Dimensions



Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Sensors BASIC Model

DC 3-wire (Double/Single distance model)

Connector Models (Unshielded)



Note: The sensing surface of size M30 is light gray.

DC 3-wire (Long-body Double/Single distance model)


Connector Models (Unshielded)



Note: The sensing surface of size M30 is light gray.


E2E-X M 8-M3/M5






E2E-X M L8-M3/M5






E2E-X M 8-M1






E2E-X□M□L8-M1






E2E-X□M□12-M1






E2E-X M L12-M1







E2E-X□M□18-M1






E2E-X M L18-M1







E2E-X18M□30-M1





E2E-X18M□L30-M1





*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF)

IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))


Mounting Hole Dimensions




Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

E2E-X30M L30-M1







Accessories (Sold Separately)

e-jig (Mounting Sleeves)


Y92E-J8S12



Y92E-J12S18



Y92E-J18S30



Material

Mounting Sleeve	Polyetheretherketone (PEEK) / Polybutylene terephthalate (PBT)		
Mounting Sleeve clamping nut	Polybutylene terephthalate (PBT)		
Sensor lock nut	Polybutylene terephthalate (PBT)		
Sensor lock O-ring	Material combining HNBR and fluororubber		

Tightening Force

	Torque			
Model	Mounting Sleeve clamping nut	Sensor lock nut		
Y92E-J8S12	0.6 N°m	0.6 N°m		
Y92E-J12S18	1.2 N°m	1.2 N°m		
Y92E-J18S30	5 N°m	3.5 N°m		

Note:The dimensional control of the threaded part is based on the fit with the accompanying nut.

Round Oil-resistant Connectors (M12 Smartclick)

XS5 NEXT Series

Round Oil-resistive Smartclick Connectors for E2E NEXT Series proximity sensors, that are Resistant to Oil, and that Reduce Installation Work

- Uses unique OMRON technology*1 and the same PVC cable with increased oil resistance as the E2E NEXT Series proximity sensors.
 Oil-resistance performance values of 2 years*2 when used in combination with E2E NEXT Series proximity sensors.
- Oil-resistant robot cables for use with moving parts such as loaders and cableveyors
- OMRON's unique lock mechanism (Smartclick) that is compatible with round M12 connectors.
- Simply insert the Connectors, then turn them approximately 1/8 of a turn to lock.
- A positive click indicates locking.
- IP67, IP69K degree of protection.
- UL approved products.
- *1. Patented (as of March, 2022)
- ***2.** Covered types of oil: Cutting oil specified in JIS K 2241:2000

The oil-resistance performance value (2 years) indicates the median value (=Typ) at product design, and in evaluation testing results of oil-resistance performance. Shipped products will show some variance around this 2 year value in actual usage.

Note: For details, refer to XS5 NEXT Series on your OMRON website.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensor I/O Connectors

A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Appearance	Cable Specification	Туре	Cable diameter (mm)	Cable Connection Direction	Cable length (m)	Sensor I/O Connector model number	Applicable Proximity Sensor model number
					1	XS5F-D421-C80-X	
	0.1				2	XS5F-D421-D80-X	
	Oil-resistant PVC cable	Sockets on One Cable End	6 dia.	Straight	3	XS5F-D421-E80-X	
		000.0 2.10			5	XS5F-D421-G80-X	
					10	XS5F-D421-J80-X	
					1	XS5F-D421-C80-XR	
M12 Smartclick	0.1	0 1 1 0			2	XS5F-D421-D80-XR	
Connector Straight type	Oil-resistant PVC robot cable	Sockets on One Cable End	6 dia.	Straight	3	XS5F-D421-E80-XR	- E2E-X□D□-M1(T)(G)J(R)(-T) E2E-X□D□-M1(G)(-T)
					5	XS5F-D421-G80-XR	
					10	XS5F-D421-J80-XR	
				Straight (Socket)/ Straight (Plug)	1	XS5W-D421-C81-X	E2E-X□□□-M1TJ(R) - E2E-X□□□-M1
	0.1	Socket and Plug on Cable Ends	6 dia.		2	XS5W-D421-D81-X	EZE-XUUU-IVI I
	Oil-resistant PVC cable				3	XS5W-D421-E81-X	
0					5	XS5W-D421-G81-X	
					10	XS5W-D421-J81-X	
					1	XS5W-D421-C81-XR	
		0 1 1 151		0	2	XS5W-D421-D81-XR	
	Oil-resistant PVC robot cable	Socket and Plug on Cable Ends	6 dia.	Straight (Socket)/ Straight (Plug)	3	XS5W-D421-E81-XR	
		S. Cas.o Endo		5a.g (. 14g)	5	XS5W-D421-G81-XR	
					10	XS5W-D421-J81-XR	

Connections for Sensor I/O Connectors

DC 2-wire

	Proximity Sensor					
Туре	Polarity	Operation mode	Model	Sensor I/O Connector Model	Connections	
M12 Connector/ M12 Smartclick Connector		NO	E2E-X□D1□-M1(T)G(J)		E2E NEXT Series XS5 NEXT Brown (+) White (not connected) Blue (not connected) Black (-)	
	Voc	INO	E2E-X□D1□-M1(T)(J)		E2E NEXT Series XS5 NEXT O Blue (+) O Black (-)	
	Yes	NC	E2E-X□D2□-M1(T)G(J)		E2E NEXT Series XS5 NEXT Brown (+) White (-) Blue (not connected) Black (not connected)	
			E2E-X□D2□-M1(T)(J)	XS5F-D421-□80-X□	E2E NEXT Series XS5 NEXT Brown (not connected) White (+) Blue (-) Black (not connected)	
		NO	E2E-X□D1-M1(T)G(J)-T (Standard/Double distance model)	XS5W-D421-□81-X□	EZE NEXT Series XS5 NEXT O Brown (+) (-) O White (not connected) O Blue (not connected) O Black (-) (+)	
	No		E2E-X□D1-M1(T)(J)-T E2E-X□D1-M1TGJ-T (Triple distance/Single distance model)		E2E NEXT Series XS5 NEXT Brown (not connected) O White (not connected) O Blue (+) (-) Black (-) (+)	
		NC		E2E-X□D2-M1(T)G(J)-T (Standard/Double distance model)		EZE NEXT Series XS5 NEXT Srown (+)(-) White (-)(+) Blue (not connected) Black (not connected)
			E2E-X□D2-M1(T)(J)-T E2E-X□D2-M1TGJ-T (Triple distance/Single distance model)		E2E NEXT Series XS5 NEXT Brown (+)(-) White (-)(+) Blue (not connected) Black (not connected)	

Note: Different from Proximity Sensor wire colors.

^{*} If the XS5W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.

XS5 NEXT Series

DC 3-wire

	Pr	oximity Sens	sor	Sensor I/O Connectors			
Types	Output	Operation mode	Model	Model	Connections *		
		NO	E2E-X□B1□-M1TJ/ M1		EZE NEXT Series XSS NEXT Brown (+) White (not connected) Black (Output)		
M12 Connector/ M12 Smartclick Connector	PNP	NC	E2E-X□B2□-M1TJ/M1		E2E NEXT Series XS5 NEXT Brown (+) O White (Output) O Blue (-) O Black (not connected)		
		NO+NC	E2E-X□B3□-M1TJ/M1	XS5F-D421-□80-X□	EZE NEXT Series XS5 NEXT Brown (+) White (Output 2) Black (Output 1)		
		NO	E2E-X□C1□-M1TJ/M1	XS5W-D421-□81-X□	E2E NEXT Series XS5 NEXT OBrown (+) OBlue (-) OBlue (-) OBlack (Output)		
	NPN	NC	E2E-X□C2□-M1TJ/M1		EZE NEXT Series XSS NEXT Brown (+) O White (Output) O Blue (-) O Black (not connected)		
		NO+NC	E2E-X\(\text{C3}\(\text{-M1TJ/M1}\)		E2E NEXT Series XS5 NEXT O Brown (+) O White (Output 2) O Blue (-) O Black (Output 1)		

Note: Different from Proximity Sensor wire colors.


Sensor I/O Connectors Oil resistance performance of mating combination

E2E NEX	Applicable connector Model		
Connecting method	XS5 NEXT Series		
Pre-wired Connector Models	E2E-X□D□-M1T(G)J(R)	Oil resistant (2 years)*	
Fre-wired Confrector Models	E2E-X - M1TJ(R)	Oli resistant (2 years)	
M12 Connector Models	E2E-X□D□-M1(G)	Water-resistant (IP67)	
W12 Connector Wodels	E2E-X□□-M1	Water-resistant (IPO7)	


^{*} Applicable cutting oil type: specified in JIS K 2241:2000

Dimensions (Unit: mm)


Both end connector type XS5W Wiring Diagram for 4 Cores




Straight (Socket)/Straight (Plug) XS5W-D421-□81-X/XS5W-D421-□81-XR



One end connector type XS5F Wiring Diagram for 4 Cores



Straight XS5F-D421-□80-X/XS5F-D421-□80-XR



^{*} If the XS5W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.

² years of oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value). Products to be shipped will have around 2 years of oil resistance, but will very depending on the product.

XS5

Round Water-resistive Smartclick Connectors for E2E NEXT Series proximity sensors that Reduce Installation Work

- A newly developed lock mechanism that is compatible with round M12 connectors.
- Simply insert the Connectors, then turn them approximately 1/8 of a turn to lock.
- · A positive click indicates locking.
- IP67 degree of protection.
- UL approved products.

Note: For details, refer to XS5 on your OMRON website.



Smartclick

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensor I/O Connectors

A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Appearance	Cable Specification	Туре	Cable diameter (mm)	Cable Connection Direction	Cable length (m)	Sensor I/O Connector model number	Applicable Proximity Sensor model number
					1	XS5F-D421-C80-F	
					2	XS5F-D421-D80-F	
				Straight	3	XS5F-D421-E80-F	
					5	XS5F-D421-G80-F	
112		Sockets on One	6 dia.		10	XS5F-D421-J80-F	
martclick		Cable End	o ula.		1	XS5F-D422-C80-F	
Connector					2	XS5F-D422-D80-F	
Straight type				Right-angle	3	XS5F-D422-E80-F	
					5	XS5F-D422-G80-F	
					10	XS5F-D422-J80-F	
OF I	PVC robot cable			Straight (Socket)/ Straight (Plug)	1	XS5W-D421-C81-F	E2E-X□D□-M1(G)(-T)
	1 VO TODOL CADIE				2	XS5W-D421-D81-F	E2E-X□□□-M1TJ(R) - E2E-X□□□-M1
					3	XS5W-D421-E81-F	
ight-angle type					5	XS5W-D421-G81-F	
0 0 11					10	XS5W-D421-J81-F	
T		Socket and Plug	6 dia.	Right-angle (Socket)/	2	XS5W-D422-D81-F	
6		on Cable Ends	o uia.	Right-angle (Plug)	5	XS5W-D422-G81-F	
				Straight (Socket)/	2	XS5W-D423-D81-F	
				Right-angle (Plug)	5	XS5W-D423-G81-F	
				Right-angle (Socket)/	2	XS5W-D424-D81-F	
				Straight (Plug)	5	XS5W-D424-G81-F	

Connections for Sensor I/O Connectors

DC 2-wire

Proximity Sensor				Sensor I/O Connector	
Туре	Polarity	Operation mode	Model	model number	Connections
		NO	E2E-X□D1□-M1(T)G(J)		E2E NEXT Series XS5 Brown (+) White (not connected) Bluc (not connected) Black (-)
	Yes		E2E-X□D1□-M1(T)(J)		E2E NEXT Series XS5 Brown (not connected) White (not connected) Black (-)
	res	NC	E2E-X□D2□-M1(T)G(J)		E2E NEXT Series XS5 O White (-) O Blue (not connected) O Black (not connected)
M12 Connector/ M12 Smartclick			E2E-X□D2□-M1(T)(J)	XS5F-D42□-□80-F XS5W-D42□-□81-F	E2E NEXT Series XS5 Brown (not connected) White (+) Blue (-) Black (not connected)
Connector		NO	E2E-X□D1-M1(T)G(J)-T (Standard/Double distance model)		E2E NEXT Series XS5 Brown (+) (-) White (not connected) Blue (not connected) Black (-) (+)
	No		E2E-X□D1-M1(T)(J)-T E2E-X□D1-M1TGJ-T (Triple distance/Single distance model)		E2E NEXT Series XS5 Brown (not connected) O White (not connected) O Blue (+) (-) O Black (-) (+)
		NC	E2E-X□D2-M1(T)G(J)-T (Standard/Double distance model)		E2E NEXT Series XS5 Brown (+)(-) O White (-)(+) O Blue (not connected) O Black (not connected)
			NC	E2E-X□D2-M1(T)(J)-T E2E-X□D2-M1TGJ-T (Triple distance/Single distance model)	

Note: Different from Proximity Sensor wire colors.

* If the XS5W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.

DC 3-wire

	Proximity Sensor				Sensor I/O Connectors			
Types	Output	Operation mode	Model	Model	Connections			
	PNP	NO	E2E-X□B1□- M1TJ/ M1		EZE NEXT Series XS5 Brown (+) White (not connected) Blue (-) Black (Output)			
		NC	E2E-X□B2□-M1TJ/M1		EZE NEXT Series XS5 O Brown (+) O White (Output) O Blue (-) O Black (not connected)			
M12 Connector/ M12 Smartclick		NO+NC	E2E-X□B3□-M1TJ/M1	XS5F-D421-□80-X□	EZE NEXT Series XS5 Brown (+) White (Output 2) Bluc (-) Black (Output 1)			
Connector		NO	E2E-X□C1□-M1TJ/M1	XS5W-D421-□81-X□	E2E NEXT Series XS5 O Brown (+) O Blue (-) O Black (Output)			
	NPN	NC	E2E-X□C2□-M1TJ/M1		EZE NEXT Series XS5 Brown (+) White (Output) Blue (-) Black (not connected)			
		NO+NC	E2E-X□C3□-M1TJ/M1		E2E NEXT Series XS5 Brown (+) O White (Output 2) O Blue (-) O Black (Output 1)			

Sensor I/O Connectors Oil resistance performance of mating combination

E2E NE	Applicable connector Model		
Connecting method	XS5 Series		
Pre-wired Connector Models	E2E-X□D□-M1T(G)J(R)		
	E2E-X□□-M1TJ(R)	Water-resistant (IP67)	
M12 Connector Modele	E2E-X□D□-M1(G)		
M12 Connector Models	E2E-X□□-M1		


Note: Different from Proximity Sensor wire colors.

* If the XS5W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.


Dimensions (Unit: mm)

Socket and Plug on Cable Ends XS5W


Wiring Diagram for 4 Cores




Straight (Socket)/Straight (Plug) XS5W-D421-□81-F




Right-angle (Socket)/right-angle (Plug) XS5W-D422-□81-F




Straight (Socket)/right-angle (Plug) XS5W-D423-□81-F




Right-angle (Socket)/Straight (Plug) XS5W-D424-□81-F




Sockets on One Cable End XS5F Wiring Diagram for 4 Cores



Straight XS5F-D421-□80-F



Right-angle XS5F-D422-□80-F



Small Round Water-resistive Connectors

- Water-resistive, compact connector meets IP67 requirements.
- XS3-R Series; connectors with cables are available.
 M8 models are UL certified.
- Oil-resistant Polyurethane Robot Cables added.

Note: For details, refer to XS3 on your OMRON website.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensor I/O Connectors

A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Appearance	Cable specification	Туре	Cable diameter (mm)	No. of cable cores (Poles)	Cable connection direction	Cable length (m)	Sensor I/O Connector model number	Applicable Proximity Sensor model number
						2	XS3F-M321-302-R	
					Straight	5	XS3F-M321-305-R	
						10	XS3F-M321-310-R	FOE VOOD ME
M8 Connector				3		2	XS3F-M322-302-R	E2E-X□□□-M5
Straight type					Right-angle	5	XS3F-M322-305-R	
		Sockets on One				10	XS3F-M322-310-R	1
		Cable End			Straight	2	XS3F-M421-402-R	E2E-X\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\
						5	XS3F-M421-405-R	
	PVC robot					10	XS3F-M421-410-R	
	cable		4 dia.	4	Right-angle	2	XS3F-M422-402-R	
Right-angle type						5	XS3F-M422-405-R	
						10	XS3F-M422-410-R	
						2	XS3W-M321-302-R	
				3	Straight (Plug)/ Straight (Socket)	5	XS3W-M321-305-R	
		Socket and Plug			Straight (Socket)	10	XS3W-M321-310-R	
		on Cable Ends				2	XS3W-M421-402-R	
				4	Straight (Plug)/ Straight (Socket)	5	XS3W-M421-405-R	
					Giraigin (Gocket)	10	XS3W-M421-410-R	

Connections for Sensor I/O Connectors

DC 2-wire

Proximity Sensor				Sensor I/O Connector	
Туре	Polarity	Operation mode	Model	model number	Connections
M8 (4-pin) Connector	Yes	NO	E2E-X□D1-M3G	XS3W-M42□-4□-R XS3F-M42□-4□-R	E2E NEXT Series XS3 O Brown (+) O White (not connected) O Blue (not connected) O Black (-)
Models		NC	E2E-X□D2-M3G		E2E NEXT Series XS3 OBrown (+) OBrown (+) OBlue (not connected) OBlack (not connected)

DC 3-wire

	Proximity Sensor			Sensor I/O Connectors	
Types	Output	Operation mode	Model	Model	Connections
M8 (4-pin) Connector Models	PNP	NO	E2E-X□B1□-M3	XS3W-M42□-4□-R XS3F-M42□-4□-R	E2E/E2EQ NEXT Series XS3 Brown (+) White (not connected) Blue (-) Black (Output)
		NC	E2E-X□B2□-M3		E2E/E2EQ NEXT Series XS3 Brown (+) O Brown (+) O Blue (-) O Black (not connected)
	NPN	NO	E2E-X□C1□-M3		E2E/E2EQ NEXT Series XS3 Brown (+) White (not connected) Blue (-) Black (Output)
		NC	E2E-X□C2□-M3		E2E/E2EQ NEXT Series XS3 Brown (+) White (Output) Blue (-) Black (not connected)
	PNP	NO	E2E-X□B1□-M5	XS3W-M32□-3□-R XS3F-M32□-3□-R	E2E/E2EQ NEXT Series XS3
M8 (3-pin) Connector Models		NC	E2E-X□B2□-M5		Black (Output)
	NPN	NO	E2E-X□C1□-M5		E2E/E2EQ NEXT Series XS3
		NC	E2E-X□C2□-M5		O Black (Output)

Sensor I/O Connectors Oil resistance performance of mating combination

E2E NEX	Applicable connector Model	
Connecting method	Model	XS3 Series
M9 (4 pip) Connector Modela	E2E-X□D□-M3G	
M8 (4-pin) Connector Models	E2E-X□□-M3	Water-resistant (IP67)
M8 (3-pin) Connector Models	E2E-X□□-M5	


Note: Different from Proximity Sensor wire colors.

* If the XS3W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.


Dimensions (Unit: mm)

Socket and Plug on Cable Ends XS3W

Wiring Diagram for 3 Cores




Straight (Socket)/Straight (Plug) XS3W-M321-3□□-R




Sockets on One Cable End XS3F


Wiring Diagram for 3 Cores



Straight XS3F-M321-3□□-R




Right-angle XS3F-M322-3□□-R




Socket and Plug on Cable Ends XS3W

Wiring Diagram for 4 Cores




Straight (Socket)/Straight (Plug) XS3W-M421-4□□-R




Sockets on One Cable End XS3F


Wiring Diagram for 4 Cores



Straight XS3F-M421-4□□-R



Right-angle XS3F-M422-4□□-R



MEMO

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.


Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Related Products



Welding Proximity Sensors E2EW Series/E2EQ NEXT Series

Cat. No. D125



Environment-resistant Series Oil-resistant Components

Cat. No. Y215



IO-Link Series

Cat. No. Y229

Smartclick is a registered trademark of OMRON Corporation.

Company names and product names in this document are the trademarks or registered trademarks of their respective companies. The product photographs and figures that are used in this catalog may vary somewhat from the actual products.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact: www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

Authorized Distributor:

©OMRON Corporation 2022-2025 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM_6_6

Cat. No. D120-E1-15 1025 (0922)