

Improve productivity and cost reduction in harsh welding environments





E2EW Series boosts productivity while cutting equipment costs in welding processes

Sophisticated and complex production equipment and a severe shortage of skilled workers increase the need to easily design equipment and maintain and improve equipment uptime without relying on experience and skills. Omron's E2EW Series offers stable detection and excellent environmental resistance. This improves the efficiency of design, commissioning, operation, and maintenance of welding lines, contributing to increasing productivity and reducing equipment costs.



Issue of productivity

Improve productivity by evolving equipment to respond to changes in manufacturing



For full metal body proximity sensor users
Further increase design efficiency and
equipment uptime

> Page 4

Issue of equipment costs

Further reduce equipment costs other than by reducing parts procurement costs



For resin head proximity sensor users Reduce total equipment costs

> Page 6

Address the issue of productivity

For full metal body proximity sensor users

Further increase design efficiency and equipment uptime

	DC 2-wire	DC 3-wire
PREMIUM Model	_	•
BASIC Model	•	•

Reduce maintenance and replacement frequency even in harsh environments

E2EW spatter-resistant models are coated with fluororesin to prevent spatter from sticking, reducing maintenance frequency. Another technology to prevent coating abrasion reduces sensor replacement frequency.



Technologies > Page 8


^{* 1.} This value assumes that the sensor operates 10 hours a day in an arc welding environment and is cleaned once a month (12 times a year).

If our previous model (E2EF-Q) needs to be replaced once every 3 times it is cleaned, the E2EW-Q Proximity Sensor needs to be replaced once every 180 times it is cleaned. This means that there is no need to replace the E2EW-Q Proximity Sensor for 10 or more years.

	DC 2-wire	DC 3-wire
PREMIUM Model	_	•
BASIC Model	_	_

Less unexpected downtime due to false detections

Stable long distance detection reduces unexpected line stoppages previously caused by false detections due to vibrating workpieces.



Technologies > Page 9

Stable detection and common design for both iron and aluminum

The E2EW Proximity Sensor offers the same sensing distance for both iron and aluminum, enabling common design. Its exceptional sensing range mitigates false detections, thereby minimizing unexpected downtime.



Technologies > Page 10

Stable operation by identifying changes in equipment condition

In addition to presence detection, invisible temperature changes of equipment can be identified, which helps detect equipment abnormalities.



Technologies > Page 11

* 2. M12 quadruple distance models.


Address the issue of equipment costs

For resin head proximity sensor users

Reduce total equipment costs

The E2EW DC 2-wire BASIC Model can significantly reduce total costs because its robust and environmental resistant design eliminates hardware and labor costs associated with replacing sensors and opportunity loss caused by line stoppages due to sensor failures *7.

Reduction in total costs *7 for 10 years *1



Note: The graphs are for illustration purposes only.

^{*1.} It is defined that an automotive manufacturer makes a model changeover every 10 years. *2. The time required for replacement due to unexpected stoppages is estimated to be 1 hour per month, and opportunity loss per minute is estimated to be ¥10,000. *3. Hourly labor cost for replacement ¥2,000 x 1,000 sensors x replacement 4 times (for 10 years). *4. List price of E2E NEXT (DC 2-wire Standard Model, M12) ¥7,500 x 1,000 sensors x replacement 4 times (for 10 years). *5. List price of E2E NEXT (DC 2-wire Standard Model, M12) ¥7,500 x 1,000 sensors. *6. List price of E2EW (DC 2-wire Spatter-resistant Single distance Model, M12) ¥15,000 x 1,000 sensors. *7. Estimated from 1,000 sensors (20 sensors on a jig x 50 jigs) in a welding line for 250,000 cars. There is no need to replace the E2EW Series for 10 years from the viewpoints of shock resistance (*Y) and spatter resistance (*Z). (*Y) This value assumes that the equipment operates 10 hours a day and workpieces mounted to welding jigs hit a proximity sensor 100 times a day with the force equivalent to the force used in our continuous impact tests. Omron's sensor was not penetrated even after our continuous impact test consisting of 200,000 repetitions, which means that there is no need to replace it for 10 or more years. (*Z) This value assumes that the sensor operates 10 hours a day in an arc welding environment and is cleaned once a month (12 times a year). If our previous model (E2EF-Q) needs to be replaced once every 3 times it is cleaned, the E2EW-Q Proximity Sensor needs to be replaced once every 180 times it is cleaned. This means that there is no need to replace the E2EW-Q Proximity Sensor for 10 or more years.

	DC 2-wire	DC 3-wire
PREMIUM Model	_	•
BASIC Model	•	•

Reduce unexpected downtime and replacement frequency

The metal head resists friction and collision with workpieces and metal cleaning brushes, reducing unexpected downtime and replacement frequency due to failure caused by wear and collision compared to previous resin heads.



Technologies > Page 12

Reduce maintenance and replacement frequency even in harsh environments

The spatter and abrasion resistant fluororesin coating technology enables long-lasting spatter resistance. The maintenance and replacement frequency is much less than that of resin head proximity sensors without fluororesin coating.



Technologies > Page 8

*8. This value assumes that the sensor operates 10 hours a day in an arc welding environment and is cleaned once a month (12 times a year). If our previous model (E2EF-Q) needs to be replaced once every 3 times it is cleaned, the E2EW-Q Proximity Sensor needs to be replaced once every 180 times it is cleaned. This means that there is no need to replace the E2EW-Q Proximity Sensor for 10 or more years.

Fluororesin coated resin head models are also available.





	DC 2-wire	DC 3-wire
PREMIUM Model	_	•
BASIC Model		•

Long-lasting spatter resistance without need for replacement for 10 years*1

The spatter and abrasion resistant coating ensures long-lasting resistance.

Spatter resistance reduces maintenance frequency

The spatter resistant fluororesin coating reduces maintenance frequency even in environments with welding spatter.

Previous model *2

Spatter covering a wide area causes

malfunction in about

one month.



E2EW-Q

Fluororesin coating prevents spatter from sticking.



Cleaning frequency reduced to half*3

Abrasion

resistant

coating

Abrasion resistance reduces sensor replacement frequency


The abrasion resistant fluororesin coating provides long-lasting spatter resistance against cleaning, allowing for less frequent sensor replacement.





Technology to prevent spatter from sticking

The coating film formation technology to apply a highly hydrophobic coating reduces the amount of spatter sticking to the surface to approximately half of previous models.




Technology to prevent coating from wearing off

The unique coating film formation technology coupled with a specially treated base surface greatly reduces abrasion, to approximately 1/60 of previous models.

Coating

SUS



*1.This value assumes that the sensor operates 10 hours a day in an arc welding environment and is cleaned once a month (12 times a year). If our previous model (E2EF-Q) needs to be replaced once every 3 times it is cleaned, the E2EW-Q Proximity Sensor needs to be replaced once every 180 times it is cleaned. This means that there is no need to replace the E2EW-Q Proximity Sensor for 10 or more years. *2.0ur previous model E2EF-Q. *3.Comparison with our previous model E2EF-Q. Based on Omron investigation in September 2021. *4.The surface is brushed 10 times vertically and horizontally with a metal brush for each cleaning. Cleaning is repeated 6 times. *5.Comparison with our previous model E2EF-Q. Based on Omron investigation in September 2021. *6."Patent Pending" means that we applied for a patent in Japan, and "Patented" means that we obtained a patent in Japan. (As of October 2025)


	DC 2-wire	DC 3-wire
PREMIUM Model	_	•
BASIC Model	_	_

Exceptional sensing range

Previous full metal body proximity sensors with a shorter sensing distance than resin head proximity sensors cannot detect stably if workpieces are moved from their intended positions. E2EW PREMIUM Models with a longer sensing distance reduce false detections, minimizing unexpected downtime. Furthermore, when equipment is set up or a sensor is replaced, the sensor can be quickly and easily installed without strict adjustment of its installation distance. This maintains and further improves equipment uptime.

Approximately double the sensing distance of previous model*1 (quadruple distance model)

Sensing distance comparison



*1. Comparison with our previous model E2EF.

More efficient sensor installation design

E2EW Proximity Sensors with the exceptional sensing range provide accurate detection from a certain distance, which is impossible with previous models. They can be installed with sufficient space to reduce sensor damage.



Design example

(Size: M12)

When prioritizing sensing distance Use a quadruple distance model with an exceptional sensing range (sensing distance: 7 mm). The sensing surface of the proximity sensor must stick out from the plate. When installing flush with the surface Use a triple distance model (sensing distance: 6 mm). When the proximity sensor is embedded in iron metal, its sensing surface does not need to protrude from the surface.

Note: Refer to page 35 for detail.

	DC 2-wire	DC 3-wire
PREMIUM Model	_	•
BASIC Model	_	_

Equal sensing distances for iron and aluminum

A unique Omron technology provides equal sensing distances for both iron and aluminum. Mixed-metal production lines with less unexpected downtime can be designed.

Minimizing unexpected downtime maximizes uptime

E2EW Proximity Sensors provide equally long distance detection for iron and aluminum, reducing false detections even if workpieces are moved from their intended positions. Furthermore, when equipment is set up or a sensor is replaced, the sensor can be quickly and easily installed without strict adjustment of its installation distance.




Previous model

A workpiece that is out of position would cause false detections, leading to equipment stoppages.



Long-distance detection means improved detection margins, enabling stable detection even when a workpiece is out of position.



Checking correct positions of doors

False detection


Stable detection

*1.Triple distance models that can be installed flush with the surface are also available.Refer to page 9 for details.

Unified design reduces design work

Unlike previous sensors which need to be changed for different sensing distances, E2EW Proximity Sensors with the same sensing distance for both iron and aluminum eliminate the need to change sensors in order to detect positions in mixed production lines containing both metal components. This enables standardization of production equipment and mechanical drawings.

Technology for suppressing noise




Different designs are required for different size sensors.

Design can be standardized on a single sensor.


st2. Quadruple distance models.

A unique Omron technology provides equally long sensing distances for both iron and aluminum

The problem of previous full metal body proximity sensors was the short sensing distance. E2EW Proximity Sensors are equipped with a unique technology for suppressing noise influence as well as the PRD*3 technology. Together they reduce the influence of noise, extending the sensing distance. Furthermore, equally long distance detection for iron and aluminum is possible by adjusting the timing and time to detect current changes of sensing objects.



Long sensing distances for both iron and aluminum



	DC 2-wire	DC 3-wire
PREMIUM Model	_	•
BASIC Model	_	_

Detection level and temperature visualization with IO-Link

Daily changes in equipment conditions can be monitored via IO-Link, which helps you reduce tuning time during the commissioning phase and stabilize equipment operation during the mass production phase.


Identify changes in equipment by visualizing detection level

A real-time view of how the proximity sensors are detecting objects provides understanding of everyday changes in equipment conditions that may not be visible to the naked eye.

Application example

Maintenance management based on spatter accumulation

Weld spatter can cause proximity sensors to malfunction. Monitoring detection level changes can allow for timely maintenance.



Spatter accumulation

Detect equipment abnormalities by visualizing temperature


Temperature changes in tough environments are visualized in real time, helping detection of equipment abnormalities.


Application example

Identification of temperature changes during welding

Temperature changes can be monitored via the proximity sensors installed in multiple positions to locate abnormal locations.

Proximity sensor temperature changes during welding cycles






Time

	DC 2-wire	DC 3-wire
PREMIUM Model	_	•
BASIC Model	•	•

Durable full metal body

The full metal housing is robust enough to use in production sites where the sensor often collides with workpieces, reducing replacement frequency.

Reduce replacement of proximity sensor due to sensing surface damage



E2E (resin head)

Friction and collision with workpieces cause the sensing surface (head) to wear out, eventually leading to insulation breakdown.

E2EW (metal head)

The thick metal head structure eliminates abrasion factors to deliver insulation breakdown resistance.



Position detection of iron plates

Broken by collision

Resistant to collision

Thick metal head structure

Resistant to friction with workpieces and metal cleaning brushes

In wear resistance tests using stainless-steel brushes rotating at 130 rpm, insulation breakdown occurred in 50 minutes for resin heads, while no insulation breakdown occurred even after 400 minutes for metal heads.

Note: The tests were performed on E2EW M18 quadruple distance models with $0.4\,\mathrm{mm}$ sensing surface thickness.



Brush test

Resin head









Full metal body

E2EW-X12□18



Initial state



After 50 minutes



After 400

No insulation breakdown after 400 minutes

Resistant to collision with workpieces







Continuous impact test results showed that the sensing surface was not penetrated even after impact was repeated 200,000 times. No insulation breakdown occurred.

Continuous impact test

Note: Sensing surface thickness varies for different models. Refer to the datasheet for details.

	DC 2-wire	DC 3-wire
PREMIUM Model	_	•
BASIC Model	•	•

Excellent usability

360° visible indicator for easy identification of detection status

The high-brightness LED indicator provides 360° visibility no matter where the sensor is fixed, allowing for speedy installation regardless of sensor orientation and easy check of detection status during operation.



Note: The visibility of the indicator light differs for M8 size sensors. For details, refer to the dimensions in the datasheet.

Short body to fit in narrow spaces

The body that is up to 35% shorter than the previous models facilitates installation during commissioning and maintenance.



*1. E2EF. *2. M30.

Laser printed information to prevent replacement errors

Laser printed information (sensing distance on the sensor head*3 and model number on the cable) can withstand long-term use and be seen clearly, reducing errors during sensor replacement.


*3. Models without spatter-resistant coating only.



Simple inventory by standardizing on a single sensor

Inventory management can be streamlined by standardizing on a single sensor for iron and aluminum detection that previously required four sensors (e.g., E2EW Proximity Sensor 2-output (NO+NC) model instead of M12 NO and NC models and M18 NO and NC models). This also saves a great deal of storage space.

Note: DC 3-wire PREMIUM Models only.



Functions and Specifications

			DC 2-wire					
						Fluororesin head	1	
			Wietai	nedu	'	idororesiii nede	-	
		Series	E2	EW	E2EQ	NEXT	E2EQ	
			BASIC	Model	PREMIUM Model	BASIC Model		
Main functi	ons and spec	ifications	Double distance model	Single distance model	Triple distance model	Double distance model		
		M8	2 mm	1.5 mm	3 mm	_	_	
	Sensing	M12	3 mm	2 mm	7 mm	4 mm	3 mm	
	distance	M18	7 mm	5 mm	11 mm	8 mm	7 mm	
		M30	12 mm	10 mm	20 mm	15 mm	10 mm	
Detection performance	Detection of mixed materials	Equal sensing for iron and aluminum	_	_	_	-	_	
	Installation	Flush with surface	•	•	_	-	•	
	Installation Flush with surface using nut		•	•	•	•	•	
Environmental resistance	Spatter resistance	Long-lasting special fluororesin coating	• *1	●*1	_	_	_	
resistance	resistance	Standard fluororesin coating	_	_	•	•	•	
Industrial IoT enabled		vel and temp. n with IO-Link	_	_	_	_	_	
	360° visible	360° visible indicator *3		● (Green)	● (Green)	● (Green)	_	
Usability		nted model nber	•	•	•	•	_	
		O+NC) model	_	_	_	_	_	
	Datasheet		P11	7 ~	P4 ²	1~	P60 ~	

-	DC 3-wire							
		Metal	head	Fluororesin head				
		E2	EW			E2EQ NEXT		
	PREMIU	M Model	BASIC	Model	PREMIUM Model	BASIC	Model	
	Quadruple distance model	Triple distance model	Double distance model	Single distance model	Triple distance model	Double distance model	Single distance mode	
	_	_	_	1.5 mm	3 mm	2 mm	1.5 mm	
	7 mm	6 mm	3 mm	2 mm	6 mm	4 mm	2 mm	
	12 mm	10 mm	7 mm	5 mm	12 mm	8 mm	5 mm	
	22 mm	20 mm	12 mm	10 mm	22 mm	15 mm	10 mm	
	•	•	_	_	_	-	_	
	-	•	•	•	-	-	•	
	-	(M30 only)	•	•	•	•	•	
	•*1	● *1	•*1	•*1	_	-	_	
	_	_	_	_	•	•	•	
ľ	•	•	_	_	•	•	•	
	• (Orange)	• (Orange)	• (Orange)	• (Orange)	• (Orange)	• (Orange)	• (Orange)	
	•	•	•	•	•	•	•	
	• *2	• *2	● *2	• *2	• *2	• *2	• *2	
†		P17	7 ~			P41 ∼		

^{*1.} Spatter-resistant models only. *2. 2-output (NO+NC) models only.

^{*3.} The visibility of the indicator light differs for M8 size sensors. For details, refer to the dimensions in the datasheet.

MEMO

Welding Proximity Sensor

E2EW Series

DC 2-wire/DC 3-wire

Stable detection in lines containing both aluminum and iron

- Equivalent sensing distances for both iron and aluminum *1
- Enables common design for lines with both iron and aluminum *1
- Approximately double the sensing distance of previous model *2, which means fewer false detections and thereby fewer unexpected stoppages.
- OMRON's unique fluororesin coating technologies enable longlasting spatter resistance *4, eliminates the need to replace for 10 years *3.
- Durable full metal body to reduce unexpected stoppages
- 2-output (NO+NC) models and models with IO-Link *1 are also available
- Laser printed information (sensing distance on the sensor head, model on the cable, and model on the metal part of the connector model) can be reducing errors during sensor replacement. *5
- Equipped with a function, which effectively cancels pulse noise of current magnetic field. *1
- UL certification (UL60947-5-2) and CSA certification (CSA C22.2 UL60947-5-2-14)
- *1. PREMIUM Models only.
- *2. Comparison with our previous model E2EF.
- *3. This value assumes that the sensor operates 10 hours a day in an arc welding environment and is cleaned once a month (12 times a year). If our previous model (E2EF-Q) needs to be replaced once every 3 times it is cleaned, the E2EW-Q Proximity Sensor needs to be replaced once every 180 times it is cleaned. This means that there is no need to replace the E2EW-Q Proximity Sensor for 10 or more years.
- *4. Models with spatter-resistant coating only.
- *5. Models without spatter-resistant coating only.

E2EW Series Model Number Legend

No.	Туре	Code	Meaning	Remarks
(1)	Case	Blank	Without spatter-resistant coating	
(1)	Case	Q	With spatter-resistant coating	
(2)	Sensing distance	Number	Sensing distance (Unit: mm) (R: Indication of decimal point)	
		В	DC 3-wire PNP open collector	Whether the D model
(3)	Output configuration	С	DC 3-wire NPN open collector	has polarity is defined
		D	DC 2-wire polarity/no polarity	by number (8).
		1	Normally open (NO)	
(4)	Operation mode	2	Normally closed (NC)	
		3	Normally open, Normally closed (NO+NC)	
		Blank	Non IO-Link compliant	
(5)	IO-Link baud rate	D	COM2 (38.4kbps)	
	T		COM3 (230.4kbps)	
		8	M8	
(0)	0:	12	M12	
(6)	Size 18		M18	
		30	M30	
		Blank	Pre-wired Models	
(7)	O	M1	M12 Connector Models	
(7)	Connection method M1TGJ		M12 Pre-wired Smartclick Connector Models DC 2-wire	
		M1TJ	M12 Pre-wired Smartclick Connector Models DC 3-wire	
(0)	DC 2 wire polarity:	Blank	Polarity	
(8)	DC 2-wire polarity	Т	No polarity	
(9)	Cable length	Number M	Cable length	
		1	The state of the s	1

Note: The purpose of this model number legend is to provide understanding of the meaning of specifications from the model number.







For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



Be sure to read Safety Precautions on page 35.

E2EW Series

Ordering Information

BASIC Model

E2EW Series (Double distance model)

DC 2-wire [Refer to Ratings and Specifications on page 24, Dimensions on page 38.]

Size	Connection method	Polarity	Model	
(Sensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: NC
	Pre-wired (2 m)	Yes	E2EW-X2D18 2M *1	
M8	Fie-wiled (2 iii)	No	E2EW-X2D18-T 2M	
(2 mm)	M12 Pre-wired	Yes	E2EW-X2D18-M1TGJ 0.3M	
	Smartclick Connector (0.3 m)	No	E2EW-X2D18-M1TGJ-T 0.3M	
1440	Pre-wired (2 m) *1	Yes	E2EW-X3D112 2M	E2EW-X3D212 2M
M12 (3 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	Yes	E2EW-X3D112-M1TGJ 0.3M	
(0 11111)		No	E2EW-X3D112-M1TGJ-T 0.3M	
1440	Pre-wired (2 m) *1	Yes	E2EW-X7D118 2M	E2EW-X7D218 2M
M18 (7 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	Yes	E2EW-X7D118-M1TGJ 0.3M	
(, ,,,,,,		No	E2EW-X7D118-M1TGJ-T 0.3M	
	Pre-wired (2 m) *1	Yes	E2EW-X12D130 2M	E2EW-X12D230 2M
M30 (12 mm)	M12 Pre-wired	Yes	E2EW-X12D130-M1TGJ 0.3M	
(12 11111)	Smartclick Connector (0.3 m)	No	E2EW-X12D130-M1TGJ-T 0.3M	

BASIC Model

E2EW Series (Single distance model)

DC 2-wire [Refer to Ratings and Specifications on page 24, Dimensions on page 38.]

Size	Connection method	Dolority	M	odel
Sensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: NC
	Pre-wired (2 m)	Yes	E2EW-X1R5D18 2M *1	E2EW-X1R5D28 2M
M8	Pie-wiled (2 III)	No	E2EW-X1R5D18-T 2M	
(1.5 mm)	M12 Pre-wired	Yes	E2EW-X1R5D18-M1TGJ 0.3M	
	Smartclick Connector (0.3 m)	No	E2EW-X1R5D18-M1TGJ-T 0.3M	
	Pre-wired (2 m) *1	Yes	E2EW-X2D112 2M	E2EW-X2D212 2M
M12 (2 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	Yes	E2EW-X2D112-M1TGJ 0.3M	
(2 11111)		No	E2EW-X2D112-M1TGJ-T 0.3M	
	Pre-wired (2 m) *1	Yes	E2EW-X5D118 2M	E2EW-X5D218 2M
M18 (5 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	Yes	E2EW-X5D118-M1TGJ 0.3M	
(0 11111)		No	E2EW-X5D118-M1TGJ-T 0.3M	
	Pre-wired (2 m) *1	Yes	E2EW-X10D130 2M	E2EW-X10D230 2M
M30 (10 mm)	M12 Pre-wired	Yes	E2EW-X10D130-M1TGJ 0.3M	
(10 11111)	Smartclick Connector (0.3 m)	No	E2EW-X10D130-M1TGJ-T 0.3M	

^{*1.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-X3D112 5M)

Note: 1. When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 36.

2. IO-Link is not supported for BASIC Model.

E2EW-Q Series (Spatter-resistant Double distance model)

DC 2-wire [Refer to Ratings and Specifications on page 24, Dimensions on page 38.]

Size	Connection method	Polarity	Model	
Sensing distance)		Folanty	Operation mode: NO	Operation mode: NC
M8	Pre-wired (2 m)	Yes	E2EW-QX2D18 2M *1	
(2 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	Yes	E2EW-QX2D18-M1TGJ 0.3M	
	Pre-wired (2 m)	Yes	E2EW-QX3D112 2M *1	E2EW-QX3D212 2M
M12 (3 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	Yes	E2EW-QX3D112-M1TGJ 0.3M	
(0 11111)		No	E2EW-QX3D112-M1TGJ-T 0.3M	
1440	Pre-wired (2 m)	Yes	E2EW-QX7D118 2M *1	E2EW-QX7D218 2M
M18 (7 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	Yes	E2EW-QX7D118-M1TGJ 0.3M	
()		No	E2EW-QX7D118-M1TGJ-T 0.3M	
1400	Pre-wired (2 m)	Yes	E2EW-QX12D130 2M *1	E2EW-QX12D230 2M
M30 (12 mm)	M12 Pre-wired	Yes	E2EW-QX12D130-M1TGJ 0.3M	
()	Smartclick Connector (0.3 m)	No	E2EW-QX12D130-M1TGJ-T 0.3M	

BASIC Model

E2EW-Q Series (Spatter-resistant Single distance model)

DC 2-wire [Refer to Ratings and Specifications on page 24, Dimensions on page 38.]

Size	Commention mathed	Delevity	Model	
ensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: NC
	Pre-wired (2 m)	Yes	E2EW-QX1R5D18 2M *1	
M8 (1.5 mm)	M12 Pre-wired	Yes	E2EW-QX1R5D18-M1TGJ 0.3M	
(1.0 11111)	Smartclick Connector (0.3 m)	No	E2EW-QX1R5D18-M1TGJ-T 0.3M	
	Pre-wired (2 m)	Yes	E2EW-QX2D112 2M *1	E2EW-QX2D212 2M
M12 (2 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	Yes	E2EW-QX2D112-M1TGJ 0.3M	
(2)		No	E2EW-QX2D112-M1TGJ-T 0.3M	
	Pre-wired (2 m)	Yes	E2EW-QX5D118 2M *1	E2EW-QX5D218 2M
M18 (5 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	Yes	E2EW-QX5D118-M1TGJ 0.3M	
(6)		No	E2EW-QX5D118-M1TGJ-T 0.3M	
	Pre-wired (2 m)	Yes	E2EW-QX10D130 2M *1	E2EW-QX10D230 2M
M30 (10 mm)	M12 Pre-wired	Yes	E2EW-QX10D130-M1TGJ 0.3M	
	Smartclick Connector (0.3 m)	No	E2EW-QX10D130-M1TGJ-T 0.3M	

^{*1.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-QX3D112 5M)

Note: 1. When embedding the Proximity Sensor in metal, refer to *Influence of Surrounding Metal* on page 36.2. IO-Link is not supported for BASIC Model.

E2EW Series (Double distance model)

DC 3-wire [Refer to Ratings and Specifications on page 25, Dimensions on page 38.]

Size	Connection method	Operation mode	Model	
(Sensing distance)	Connection method	*3	PNP	NPN
	Decinc. d (0) *4	NO	E2EW-X3B112 2M	E2EW-X3C112 2M
M12	Pre-wired (2 m) *1	NO+NC	E2EW-X3B312 2M	NPN
(3 mm)	M12 Pre-wired	NO	E2EW-X3B112-M1TJ 0.3M	E2EW-X3C112-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-X3B312-M1TJ 0.3M	E2EW-X3C312-M1TJ 0.3M
	Pre-wired (2 m) *1	NO	E2EW-X7B118 2M	E2EW-X7C118 2M
M18		NO+NC	E2EW-X7B318 2M	E2EW-X7C318 2M
(7 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-X7B118-M1TJ 0.3M	E2EW-X7C118-M1TJ 0.3M
		NO+NC	E2EW-X7B318-M1TJ 0.3M	E2EW-X7C318-M1TJ 0.3M
	Dro wired (2 m) *4	NO	E2EW-X12B130 2M	E2EW-X12C130 2M
M30	Pre-wired (2 m) *1	NO+NC	E2EW-X12B330 2M	E2EW-X12C330 2M
(12 mm)	M12 Pre-wired	NO	E2EW-X12B130-M1TJ 0.3M	E2EW-X12C130-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-X12B330-M1TJ 0.3M	E2EW-X12C330-M1TJ 0.3M

BASIC Model

E2EW Series (Single distance model)

DC 3-wire [Refer to Ratings and Specifications on page 25, Dimensions on page 38, 39.]

Size	Connection method *2	oction method *2		del
Sensing distance)	Connection method 2	*3	PNP	NPN
M8 (1.5 mm)	Pre-wired (2 m)	NO	E2EW-X1R5B18 2M	E2EW-X1R5C18 2M
	Dro wired (2 m) *1	NO	E2EW-X2B112 2M	E2EW-X2C112 2M
M12	Pre-wired (2 m) *1	NO+NC	E2EW-X2B312 2M	E2EW-X2C312 2M
(2 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-X2B112-M1TJ 0.3M	E2EW-X2C112-M1TJ 0.3M
		NO+NC	E2EW-X2B312-M1TJ 0.3M	E2EW-X2C312-M1TJ 0.3M
	Pre-wired (2 m) *1	NO	E2EW-X5B118 2M	E2EW-X5C118 2M
M18		NO+NC	E2EW-X5B318 2M	E2EW-X5C318 2M
(5 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-X5B118-M1TJ 0.3M	E2EW-X5C118-M1TJ 0.3M
		NO+NC	E2EW-X5B318-M1TJ 0.3M	E2EW-X5C318-M1TJ 0.3M
	Dro wined (2 m) *4	NO	E2EW-X10B130 2M	E2EW-X10C130 2M
M30	Pre-wired (2 m) *1	NO+NC	E2EW-X10B330 2M	E2EW-X10C330 2M
(10 mm)	M12 Pre-wired	NO	E2EW-X10B130-M1TJ 0.3M	E2EW-X10C130-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-X10B330-M1TJ 0.3M	E2EW-X10C330-M1TJ 0.3M

^{*1.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-X3B112 5M)
*2. Model with M12 Connector are also available with "-M1" suffix. (Example: E2EW-X2B112 -M1)

Note: 1. When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 36.

2. IO-Link is not supported for all types of BASIC Model.

^{*3.} Operation model NC are also available with "E2EW-X□□2□□". (Example: E2EW-X3B212 2M)

E2EW-Q Series (Spatter-resistant Double distance model)

DC 3-wire [Refer to Ratings and Specifications on page 25, Dimensions on page 38.]

Size	Connection method	Operation mode	Model	
(Sensing distance)	Connection method	*2	PNP	NPN
	Dro wired (2 m) *4	NO	E2EW-QX3B112 2M	E2EW-QX3C112 2M
M12	Pre-wired (2 m) *1	NO+NC	E2EW-QX3B312 2M	NPN
(3 mm)	M12 Pre-wired	NO	E2EW-QX3B112-M1TJ 0.3M	E2EW-QX3C112-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-QX3B312-M1TJ 0.3M	E2EW-QX3C312-M1TJ 0.3M
	Pre-wired (2 m) *1	NO	E2EW-QX7B118 2M	E2EW-QX7C118 2M
M18		NO+NC	E2EW-QX7B318 2M	E2EW-QX7C318 2M
(7 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-QX7B118-M1TJ 0.3M	E2EW-QX7C118-M1TJ 0.3M
		NO+NC	E2EW-QX7B318-M1TJ 0.3M	E2EW-QX7C318-M1TJ 0.3M
	Dro wired (2 m) *4	NO	E2EW-QX12B130 2M	E2EW-QX12C130 2M
M30	Pre-wired (2 m) *1	NO+NC	E2EW-QX12B330 2M	E2EW-QX12C330 2M
(12 mm)	M12 Pre-wired	NO	E2EW-QX12B130-M1TJ 0.3M	E2EW-QX12C130-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-QX12B330-M1TJ 0.3M	E2EW-QX12C330-M1TJ 0.3M

BASIC Model

E2EW-Q Series (Spatter-resistant Single distance model)

DC 3-wire [Refer to Ratings and Specifications on page 25, Dimensions on page 38, 39.]

Size	Connection method	Operation mode	Model	
Sensing distance)	Connection method	*2	PNP NPN E2EW-QX1R5B18-M1 E2EW-QX2B112 2M E2EW-QX2C112 2M E2EW-QX2B312 2M E2EW-QX2C312 2M E2EW-QX2B112-M1TJ 0.3M E2EW-QX2C112-M1TJ E2EW-QX2B312-M1TJ 0.3M E2EW-QX2C312-M1TJ E2EW-QX5B118 2M E2EW-QX5C118 2M	NPN
M8 (1.5 mm)	M12 Connector	NO	E2EW-QX1R5B18-M1	
	Dro wired (2 m) *1	NO	E2EW-QX2B112 2M	E2EW-QX2C112 2M
M12	Pre-wired (2 m) *1	NO+NC	E2EW-QX2B312 2M	NPN E2EW-QX2C112 2M E2EW-QX2C312 2M E2EW-QX2C112-M1TJ 0.3M E2EW-QX2C312-M1TJ 0.3M
(2 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-QX2B112-M1TJ 0.3M	E2EW-QX2C112-M1TJ 0.3M
		NO+NC	E2EW-QX2B312-M1TJ 0.3M	E2EW-QX2C312-M1TJ 0.3M
	Pre-wired (2 m) *1	NO	E2EW-QX5B118 2M	E2EW-QX5C118 2M
M18		NO+NC	E2EW-QX5B318 2M	E2EW-QX5C318 2M
(5 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-QX5B118-M1TJ 0.3M	E2EW-QX5C118-M1TJ 0.3M
		NO+NC	E2EW-QX5B318-M1TJ 0.3M	E2EW-QX5C318-M1TJ 0.3M
	Decinc. d (0 ms) *4	NO	E2EW-QX10B130 2M	E2EW-QX10C130 2M
M30	Pre-wired (2 m) *1	NO+NC	E2EW-QX10B330 2M	E2EW-QX10C330 2M
(10 mm)	M12 Pre-wired	NO	E2EW-QX10B130-M1TJ 0.3M	E2EW-QX10C130-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-QX10B330-M1TJ 0.3M	E2EW-QX10C330-M1TJ 0.3M

Note: 1. When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 36.

2. IO-Link is not supported for all types of BASIC Model.

The NC type are not available for M8 size sensors.

PREMIUM Model

E2EW Series (Quadruple distance model)

DC 3-wire [Refer to Ratings and Specifications on page 26, Dimensions on page 40.]

Size	Connection method *2	Operation mode	Model	
(Sensing distance)	Connection method 2	*3	PNP	NPN
	Dro wined (2 m) *4	NO	E2EW-X7B1T12 2M	E2EW-X7C112 2M
M12	Pre-wired (2 m) *1	NO+NC	E2EW-X7B3T12 2M	E2EW-X7C312 2M
(7 mm)	M12 Pre-wired	NO	E2EW-X7B1T12-M1TJ 0.3M	E2EW-X7C112-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-X7B3T12-M1TJ 0.3M	E2EW-X7C312-M1TJ 0.3M
	Pre-wired (2 m) *1	NO	E2EW-X12B1T18 2M	E2EW-X12C118 2M
M18		NO+NC	E2EW-X12B3T18 2M	E2EW-X12C318 2M
(12 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-X12B1T18-M1TJ 0.3M	E2EW-X12C118-M1TJ 0.3M
		NO+NC	E2EW-X12B3T18-M1TJ 0.3M	E2EW-X12C318-M1TJ 0.3M
	Dro wined (2 m) *4	NO	E2EW-X22B1T30 2M	E2EW-X22C130 2M
M30	Pre-wired (2 m) *1	NO+NC	E2EW-X22B3T30 2M	E2EW-X22C330 2M
(22 mm)	M12 Pre-wired	NO	E2EW-X22B1T30-M1TJ 0.3M	E2EW-X22C130-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-X22B3T30-M1TJ 0.3M	E2EW-X22C330-M1TJ 0.3M

PREMIUM Model

E2EW Series (Triple distance model)

DC 3-wire [Refer to Ratings and Specifications on page 26, Dimensions on page 40.]

Size	Connection method *2	Operation mode	Model	
Sensing distance)	Connection method 2	*3	PNP	NPN
	Pre-wired (2 m) *1	NO	E2EW-X6B1T12 2M	E2EW-X6C112 2M
M12	Fie-wiled (2 iii)	NO+NC	E2EW-X6B3T12 2M	E2EW-X6C312 2M
(6 mm)	M12 Pre-wired	NO	E2EW-X6B1T12-M1TJ 0.3M	E2EW-X6C112-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-X6B3T12-M1TJ 0.3M	E2EW-X6C312-M1TJ 0.3M
	Pre-wired (2 m) *1	NO	E2EW-X10B1T18 2M	E2EW-X10C118 2M
M18		NO+NC	E2EW-X10B3T18 2M	E2EW-X10C318 2M
(10 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-X10B1T18-M1TJ 0.3M	E2EW-X10C118-M1TJ 0.3M
		NO+NC	E2EW-X10B3T18-M1TJ 0.3M	E2EW-X10C318-M1TJ 0.3M
	Dro wired (2 m) *1	NO	E2EW-X20B1T30 2M	E2EW-X20C130 2M
M30	Pre-wired (2 m) *1	NO+NC	E2EW-X20B3T30 2M	E2EW-X20C330 2M
(20 mm)	M12 Pre-wired	NO	E2EW-X20B1T30-M1TJ 0.3M	E2EW-X20C130-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-X20B3T30-M1TJ 0.3M	E2EW-X20C330-M1TJ 0.3M

- *1. Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-X7B1T12 5M) *2. Model with M12 Connector are also available with "-M1" suffix. (Example: E2EW-X7B1T12 -M1)
- *3. Operation model NC are also available with "E2EW-X = 2 = 1. (Example: E2EW-X7B212 2M)

Note: 1. When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 36.

- 2. Models in] are equipped with IO-Link (COM3). For IO-Link (COM2), select a model number with the format of "E2EW-X $\Box\Box\Box\Box\Box$ " (Example: E2EW-X7B1D12 2M). Operation mode NO can be changed to NC via IO-Link communications.
- 3. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

PREMIUM Model

E2EW-Q Series (Spatter-resistant Quadruple distance model)

DC 3-wire [Refer to Ratings and Specifications on page 26, Dimensions on page 40.]

Size	Connection method *2	Operation mode	Мо	del
(Sensing distance)	Connection method 2	*3	PNP	NPN
	Dro wired (2 m) *4	NO	E2EW-QX7B1T12 2M	E2EW-QX7C112 2M
M12	Pre-wired (2 m) *1	NO+NC	E2EW-QX7B3T12 2M	E2EW-QX7C312 2M
(7 mm)	M12 Pre-wired	NO	E2EW-QX7B1T12-M1TJ 0.3M	E2EW-QX7C112-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-QX7B3T12-M1TJ 0.3M	E2EW-QX7C312-M1TJ 0.3M
	Pre-wired (2 m) *1	NO	E2EW-QX12B1T18 2M	E2EW-QX12C118 2M
M18		NO+NC	E2EW-QX12B3T18 2M	E2EW-QX12C318 2M
(12 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-QX12B1T18-M1TJ 0.3M	E2EW-QX12C118-M1TJ 0.3M
		NO+NC	E2EW-QX12B3T18-M1TJ 0.3M	E2EW-QX12C318-M1TJ 0.3M
	B : 1/0 \ \	NO	E2EW-QX22B1T30 2M	E2EW-QX22C130 2M
M30	Pre-wired (2 m) *1	NO+NC	E2EW-QX22B3T30 2M	E2EW-QX22C330 2M
(22 mm)	M12 Pre-wired	NO	E2EW-QX22B1T30-M1TJ 0.3M	E2EW-QX22C130-M1TJ 0.3M
	Smartclick Connector (0.3 m)	NO+NC	E2EW-QX22B3T30-M1TJ 0.3M	E2EW-QX22C330-M1TJ 0.3M

PREMIUM Model

E2EW-Q Series (Spatter-resistant Triple distance model)

DC 3-wire [Refer to Ratings and Specifications on page 26, Dimensions on page 40.]

Size	Connection method *2	Operation mode	Model		
Sensing distance)	Connection method 2	*3	PNP	NPN	
	Dra wired (2 m) *1	NO	E2EW-QX6B1T12 2M	E2EW-QX6C112 2M	
M12	Pre-wired (2 m) *1	NO+NC	E2EW-QX6B3T12 2M	E2EW-QX6C312 2M	
(6 mm)	M12 Pre-wired	NO	E2EW-QX6B1T12-M1TJ 0.3M	E2EW-QX6C112-M1TJ 0.3M	
	Smartclick Connector (0.3 m)	NO+NC	E2EW-QX6B3T12-M1TJ 0.3M	E2EW-QX6C312-M1TJ 0.3M	
	Dra wired (2 m) *1	NO	E2EW-QX10B1T18 2M	E2EW-QX10C118 2M	
M18	Pre-wired (2 m) *1	NO+NC	E2EW-QX10B3T18 2M	E2EW-QX10C318 2M	
(10 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EW-QX10B1T18-M1TJ 0.3M	E2EW-QX10C118-M1TJ 0.3M	
		NO+NC	E2EW-QX10B3T18-M1TJ 0.3M	E2EW-QX10C318-M1TJ 0.3M	
	Dra wired (2 m) *1	NO	E2EW-QX20B1T30 2M	E2EW-QX20C130 2M	
M30 (20 mm)	Pre-wired (2 m) *1	NO+NC	E2EW-QX20B3T30 2M	E2EW-QX20C330 2M	
	M12 Pre-wired	NO	E2EW-QX20B1T30-M1TJ 0.3M	E2EW-QX20C130-M1TJ 0.3M	
	Smartclick Connector (0.3 m)	NO+NC	E2EW-QX20B3T30-M1TJ 0.3M	E2EW-QX20C330-M1TJ 0.3M	

^{*1.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2EW-QX7B1T12 5M)

Note: 1. When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 36.

- Models in _____ are equipped with IO-Link (COM3). For IO-Link (COM2), select a model number with the format of "E2EW-QXDDD" (Example: E2EW-QX7B1D12 2M).
 Operation mode NO can be changed to NC via IO-Link communications.
- 3. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

Sensor I/O Connectors (Sold Separately)

For details of the connector, refer to XS5 Series on page 66.

^{*2.} Model with M12 Connector are also available with "-M1" suffix. (Example: E2EW-QX7B1T12 -M1)

^{*3.} Operation model NC are also available with "E2EW-X□□2□□". (Example: E2EW-QX7B212 2M)

E2EW Series

Ratings and Specifications

BASIC Model

E2EW Series (Double distance model/Single distance model) E2EW-Q Series (Spatter-resistant Double distance model/Spatter-resistant Single distance model)

	Туре	Spatt	Double dist ter-resistant Do	ance model/ ouble distance	model	Spat	Single dista ter-resistant Si	ance model/ ngle distance r	nodel
	Size	M8	M12	M18	M30	M8	M12	M18	M30
Item	Model	E2EW- (Q)X2D□8	E2EW- (Q)X3D□12	E2EW- (Q)X7D□18	E2EW- (Q)X12D□30	E2EW- (Q)X1R5D□8	E2EW- (Q)X2D□12	E2EW- (Q)X5D□18	E2EW- (Q)X10D□30
Sensing dista	nce	2 mm ±10%	3 mm ±10%	7 mm ±10%	12 mm ±10%	1.5 mm ±10%	2 mm ±10%	5 mm ±10%	10 mm ±10%
Setting distan	ice	0 to 1.4 mm	0 to 2.1 mm	0 to 4.9 mm	0 to 8.4 mm	0 to 1.05 mm	0 to 1.4 mm	0 to 3.5 mm	0 to 7 mm
Differential tra	avel	15% max. of s	ensing distance			15% max. of sensing distance	10% max. of s	ensing distance	
Detectable ob	ject		s and non-ferrou ata on page 27.		ensing distance	depends on the	material of the	sensing object.	Refer to
Standard sens	sing object (Iron)	12 × 12 × 1 mm	21 × 21 × 1 mm	30 × 30 × 1 mm	54 × 54 × 1 mm	8 × 8 × 1 mm	12 × 12 × 1 mm	18 × 18 × 1 mm	30 × 30 × 1 mm
Response free	quency *1	100 Hz	80 Hz	90 Hz	50 Hz	100 Hz	100 Hz	80 Hz	40 Hz
Power supply	voltage	10 to 30 VDC	(including 10% r	ipple (p-p)), Cla	ss 2	1	1	1	
Leakage curre	ent	0.8 mA max.							
Output config	uration	D□ models: D1-T models:	Polarity No polarity						
Operation mo	de		O (Normally ope C (Normally clos						
Control	Load current	3 to 100 mA							
output	Residual voltage		V max. (Load cเ V max. (Load cเ						
Indicator			peration indicato peration indicato			ication indicator	green LED, no	t lit)	
Protection cir	cuits	Surge suppres	sor, Output sho	rt-circuit protect	on				
Ambient temperature range		M8 Size Operating: -10 to 70°C, Storage: -25 to 70°C (with no icing or condensation) *2 Operating: -25 to 70°C, Storage: -25 to 70°C (with no icing or condensation) *2 M8 Size Operating: -25 to 70°C, Storage: -25 to 70°C (with no icing or condensation) *2 M12/M18/M30 Size Operating: 0 to 85°C, Storage: -15 to 85°C (with no icing or condensation) *2 M8 Size Operating: -25 to 70°C, Storage: -25 to 70°C (with no icing or condensation) *2 M8 Size Operating: -25 to 70°C, Storage: -25 to 70°C (with no icing or condensation) *2							
Ambient hum	idity range	Operating/Storage: 35% to 95% (with no condensation)							
Temperature influence		M8 Size ±20% max. of sensing distance at 23°C in the temperature range of -10 to 70°C M12/M18/M30 Size ±20% max. of sensing distance at 23°C in the temperature range of 0 to 85°C M8 Size ±20% max. of sensing distance at 23°C in the temperature range of 0 to 85°C				·			
Voltage influe	ence	±1.5% max. of sensing distance at rated voltage in the rated voltage ±15% range							
Insulation res	istance	$50 \text{ M}\Omega$ min. (at 500 VDC) between current-carrying parts and case							
Dielectric stre	ength	1,000 VAC, 50)/60 Hz for 1 min	ute between cu	rrent-carrying pa	arts and case			
Vibration resis	stance (destruction)	10 to 55 Hz, 1.	.5-mm double ar	mplitude for 2 ho	ours each in X, Y	/, and Z directio	ns		
Shock resistance (destruction)		M8 Size 500 m/s² 10 times each in X, Y, and Z directions M12/M18/M30 Size 1,000 m/s² 10 times each in X, Y, and Z directions M12/M18/M30 Size 1,000 m/s² 10 times each in X, Y, and Z directions M8 Size 500 m/s² 10 times each in X, Y, and Z directions M12/M18/M30 Size 1,000 m/s² 10 times each in X, Y, and Z directions							
Degree of pro		IEC 60529: IP6	67						
Connection m	ethod	Pre-wired Mod	lels (Standard ca	able length: 2 m), Pre-wired Cor	nnector Models	(Standard cable	length: 0.3 m)	
Weight	Pre-wired	Approx. 105 g	Approx. 140 g	Approx. 165 g	Approx. 225 g	Approx. 105 g	Approx. 140 g	Approx. 160 g	Approx. 225 g
(packed state)	M12 Pre-wired Smartclick Connector	Approx. 65 g	Approx. 70 g	Approx. 100 g	Approx. 160 g	Approx. 65 g	Approx. 70 g	Approx. 95 g	Approx. 160 g
	Case	E2EW-X□: Sta	ainless steel (SL	JS303), E2EW-0	QX⊡: Fluororesi	n coating (Base	material: (SUS3	803))	
	Sensing surface	E2EW-X□: Sta	ainless steel (SU	JS303), E2EW-0	QX⊡: Fluororesi	n coating (Base	material: (SUS3	303))	
Materials	Sensing surface (Thickness)	0.2 mm	0.4 mm	0.4 mm	0.5 mm	0.4 mm	0.8 mm	0.8 mm	0.8 mm
	Clamping nuts	E2EW-X□: Sta	ainless steel (SL	JS303), E2EW-0	QX⊡: Fluororesi	n coating (Base	material: (SUS3	303))	
	Toothed washers	Zinc-plated iro	n						
	Cable	Vinyl chloride	(PVC)						
MTTFd (Year)		2,041	2,015	1,979	1,979	2,041	2,015	1,979	1,979
Accessories		Instruction ma	nual, Clamping ı	nuts, Toothed w	asher				

^{*1.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.
*2. UL temperature rating is between 0 °C to 60 °C.

E2EW Series (Double distance mode/Single distance model) E2EW-Q Series (Spatter-resistant Double distance model/Spatter-resistant Single distance model)

DC 3-wire

Туре			ble distance me stant Double dis		Single distance model/ Spatter-resistant Single distance model			
	Size	M12	M18	M30	M8	M12	M18	M30
Item	Model	E2EW- (Q)X3□12	E2EW- (Q)X7□18	E2EW- (Q)X12□30	E2EW- (Q)X1R5□8	E2EW- (Q)X2□12	E2EW- (Q)X5□18	E2EW- (Q)X10□30
Sensing distance	9	3 mm ±10%	7 mm ±10%	12 mm ±10%	1.5 mm ±10%	2 mm ±10%	5 mm ±10%	10 mm ±10%
Setting distance		0 to 2.1 mm	0 to 4.9 mm	0 to 8.4 mm	0 to 1.05 mm	0 to 1.4 mm	0 to 3.5 mm	0 to 7 mm
Differential trave	I	15% max. of se	ensing distance		15% max. of sensing distance	10% max. of se	ensing distance	
Detectable objec	t		and non-ferrous <i>Data</i> on page 27		sing distance dep	ends on the mat	erial of the sensi	ng object. Refer
Standard sensing	g object (Iron)	21 × 21 × 1 mm	30 × 30 × 1 mm	54 × 54 × 1 mm	8 × 8 × 1 mm	12 × 12 × 1 mm	18 × 18 × 1 mm	30 × 30 × 1 mm
Response freque	ency *1	80 Hz	90 Hz	50 Hz	100 Hz	100 Hz	80 Hz	40 Hz
Power supply vo	Itage	10 to 30 VDC (ncluding 10% rip	pple (p-p)), Class	2			
Current consum	ption							
Output configura	ition		P open collector					
Operation mode		1-output model		Normally open), Normally closed) NC (Normally ope		sed)		
Control output	Load current			2): 10 to 30 VDC 30 VDC, Class 2		A max.		
Control output	Residual voltage			2): 2 V max. (Loa nax. (Load currer			2 m)	
Indicator		Operation indic	ator (orange LEI	O, lit)				
Protection circui	ts	Power supply reverse polarity protection, Surge suppressor, Output short-circuit protection, Output reverse polarity protection						
Ambient tempera	ature range	M8 Size Operating: -25 to 70°C, Storage: -25 to 70°C (with no icing or condensation) *2 M12/M18/M30 Size Operating: 0 to 85°C, Storage: -15 to 85°C (with no icing or condensation) *2						
Ambient humidit	y range	Operating/Storage: 35% to 95% (with no condensation)						
Temperature infl	uence	M8 Size ±20% max. of sensing distance at 23°C in the temperature range of -25 to 70°C M12/M18/M30 Size ±20% max. of sensing distance at 23°C in the temperature range of 0 to 85°C						
Voltage influence	9	±1.5% max. of sensing distance at rated voltage in the rated voltage ±15% range						
Insulation resista	ance	50 MΩ min. (at 500 VDC) between current-carrying parts and case						
Dielectric streng	th	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case						
Vibration resista	nce (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions						
Shock resistance	e (destruction)	M8 Size 500 m/s² 10 times each in X, Y, and Z directions M12/M18/M30 Size 1,000 m/s² 10 times each in X, Y, and Z directions						
Degree of protec	tion	IEC 60529: IP6	7					
Connection meth	nod	Pre-wired Mode Connector Mod		ole length: 2 m), I	Pre-wired Conne	ctor Models (Sta	ndard cable leng	th: 0.3 m), M12
	Pre-wired	Approx. 140 g	Approx. 165 g	Approx. 225 g	Approx. 105 g	Approx. 140 g	Approx. 160 g	Approx. 225 g
Weight (packed state)	M12 Pre-wired Smartclick Connector	Approx. 70 g	Approx. 100 g	Approx. 160 g		Approx. 70 g	Approx. 95 g	Approx. 160 g
	M12 Connector				Approx. 43 g	Approx. 60 g	Approx. 75 g	Approx. 135 g
	Case	E2EW-X□: Sta	inless steel (SUS	303), E2EW-QX	∷ Fluororesin c	oating (Base ma	terial: (SUS303))	
	Sensing surface	E2EW-X□: Sta	inless steel (SUS	6303), E2EW-QX	∷ Fluororesin c	oating (Base ma	terial: (SUS303))	
Materials	Sensing surface (Thickness)	0.4 mm	0.4 mm	0.5 mm	0.4 mm	0.8 mm	0.8 mm	0.8 mm
	Clamping nuts	E2EW-X□: Sta	inless steel (SUS	303), E2EW-QX	∷ Fluororesin c	oating (Base ma	terial: (SUS303))	
	Toothed washers	Zinc-plated iron	1					
	Cable	Vinyl chloride (PVC)					
MTTFd (Year)		2,013	1,199	1,013	3,427	2,013	1,199	1,013
Accessories		Instruction man	ual, Clamping n	uts. Toothed was	her	+		+

^{*1.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

^{*2.} UL temperature rating is between 0 °C to 60 °C.

^{*3.} Only the Single distance model and the Spatter-resistant Single distance model (M8 size) are available.

PREMIUM Model

E2EW Series (Quadruple/Triple distance model) E2EW-Q Series (Spatter-resistant Quadruple/Triple distance model)

DC 3-wire

	Туре		adruple distance mo sistant Double dista			riple distance mode esistant Triple dista		
	Size	M12	M18	M30	M12	M18	M30	
Item	Model	E2EW-(Q)X7□12	E2EW-(Q)X12□18	E2EW-(Q)X22 30	E2EW-(Q)X6□12	E2EW-(Q)X10□18	E2EW-(Q)X20□3	
Sensing distance	e	7 mm ±10%	12 mm ±10%	22 mm ±10%	6 mm ±10%	10 mm ±10%	20 mm ±10%	
Setting distance		0 to 4.9 mm	0 to 8.4 mm	0 to 15.4 mm	0 to 4.2 mm	0 to 7.0 mm	0 to 14 mm	
Differential trave	ıl	15% max. of sensir	ng distance	+	1	+		
Detectable object	et	Ferrous metals and Engineering Data o		(The sensing distanc	e depends on the ma	aterial of the sensing	object. Refer to	
Standard sensin	g object (Iron)	21 × 21 × 1 mm	36 × 36 × 1 mm	66 × 66 × 1 mm	18 × 18 × 1 mm	30 × 30 × 1 mm	60 × 60 × 1 mm	
Response freque	ency *1	2 Hz (Equipped with	h a function, which e	fectively cancels pul	se noise of current m	nagnetic field.)	1	
Power supply vo	ltage	10 to 30 VDC (inclu	iding 10% ripple (p-p)), Class 2				
Current consum	ption	720 mW max. (Cur	rent consumption: 30	mA max. at power s	supply voltage of 24	V)		
Output configura	ation	B□ Models: PNP o	pen collector, C□ Mo	dels: NPN open colle	ector			
Operation mode		1-output models (B	1, C1): NO (Normally 2, C2): NC (Normally 3, C3): NO+NC (Norn	closed),	closed)			
Control output	Load current		1,B2,C1,C2): 10 to 3 3, C3): 10 to 30 VDC					
- Januar output	Residual voltage	2-output models (B	1,B2,C1,C2): 2 V ma 3, C3): 2 V max. (Loa	ad current: 100 mA, (Cable length: 2 m)	, 		
Indicator			nunication mode (CC			nunication indicator (g		
Protection circui	its	Power supply revers	se polarity protection,	Surge suppressor, C	output short-circuit pro	otection, Output rever	se polarity protection	
Ambient tempera	ature range	Operating: 0 to 85 °	°C, Storage: -15 to 8	5 °C (with no icing or	condensation) *3			
Ambient humidit	y range	Operating/Storage: 35% to 95% (with no condensation)						
Temperature infl	uence	±20% max. of sensing distance at 23 °C in the temperature range of 0 to 85 °C						
Voltage influence	е	±1.5% max. of sensing distance at rated voltage in the rated voltage ±15% range						
Insulation resista	ance	50 MΩ min. (at 500 VDC) between current-carrying parts and case						
Dielectric streng	th	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case						
Vibration resista	nce (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions						
Shock resistance	e (destruction)	1,000 m/s ² 10 times each in X, Y, and Z directions						
Degree of protec	tion	IEC 60529: IP67						
Connection meth	nod	Pre-wired Models (M12 Connector Mo		h: 2 m), Pre-wired Co	onnector Models (Sta	andard cable length:	0.3 m),	
	Pre-wired	Approx. 140 g	Approx. 165 g	Approx. 225 g	Approx. 140 g	Approx. 165 g	Approx. 225 g	
Weight (packed state)	M12 Pre-wired Smartclick Connector	Approx. 70 g	Approx. 100 g	Approx. 160 g	Approx. 70 g	Approx. 100 g	Approx. 160 g	
	M12 Connector	Approx. 60 g	Approx. 75 g	Approx. 135 g	Approx. 60 g	Approx. 75 g	Approx. 135 g	
	Case	E2EW-X□: Stainles	ss steel (SUS303), E	2EW-QX□: Fluorore	sin coating (Base ma	aterial: (SUS303))	·	
	Sensing surface	E2EW-X□: Stainles	ss steel (SUS303), E	2EW-QX□: Fluorore	sin coating (Base ma	aterial: (SUS303))		
Materials	Sensing surface (Thickness)	0.4 mm	0.4 mm	0.5 mm	0.4 mm	0.4 mm	0.5 mm	
	Clamping nuts	E2EW-X□: Stainles	ss steel (SUS303), E	2EW-QX□: Fluorore	sin coating (Base ma	aterial: (SUS303))		
	Toothed washers	Zinc-plated iron						
	Cable	Vinyl chloride (PVC)						
Main IO-Link fun	ctions *2	timer function of the	control output and ti	mer time selecting, in	nstability output (IO-L	ve proximity judgmen Link mode) ON delay temperature, and init	timer time selectin	
IO-Link	IO-Link specification	Ver.1.1						
Communication	Baud rate	E2EW(-Q) X□B□T	□: COM3 (230.4 kbp	s), E2EW(-Q) X□B□	D□: COM2 (38.4 kb	ps)		
specifications *2	Data length Minimum cycle		D size: 1 byte (M-sec	quence type: TYPE_	2_2)			
	time	COM2: 2.3 ms, CO	เงเฮ: 1.0 ms					
MTTFd (Year)		679	681	681	679	681	681	
Accessories		Instruction manual,	Clamping nuts, Toot	hed washer		·	·	

^{*1.} The response frequency is an average value. Factory setting: (timer function: ONOFF delay)
*2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.
*3. UL temperature rating is between 0 °C to 60 °C.


Engineering Data (Reference Value)

Sensing Area

BASIC Model


DC 2-wire/DC 3-wire Double distance model/ Spatter-resistant Double distance model

Sensing object: iron



DC 2-wire/DC 3-wire Single distance model/ Spatter-resistant Single distance model

Sensing object: iron




PREMIUM Model


DC 3-wire Quadruple distance model/ Spatter-resistant Quadruple distance model

Sensing object: iron


Sensing object: iron




DC 3-wire Triple distance model/ Spatter-resistant Triple distance model



Sensing object: Aluminum



Sensing object: Aluminum




Influence of Sensing Object Size and Material


BASIC Model

DC 2-wire/DC 3-wire Double distance model/ Spatter-resistant Double distance model


Size: M8 E2EW-(Q)X2□8




Size: M12 E2EW-(Q)X3□12



Size: M18 E2EW-(Q)X7□18




Size: M30 E2EW-(Q)X12□30




DC 2-wire/DC 3-wire Single distance model/ Spatter-resistant Single distance model


Size: M8 E2EW-(Q)X1R5□8




Size: M12 E2EW-(Q)X2□12



Size: M18 E2EW-(Q)X5□18




Size: M30 E2EW-(Q)X10□30




PREMIUM Model

DC 3-wire Quadruple distance model/ Spatter-resistant Quadruple distance model


Size: M12 E2EW-(Q)X7□12



Size: M18 E2EW-(Q)X12□18




Size: M30 E2EW-(Q)X22□30




DC 3-wire Triple distance model/ Spatter-resistant Triple distance model


Size: M12 E2EW-(Q)X6□12



Size: M18 E2EW-(Q)X10□18



Size: M30 E2EW-(Q)X20□30




Influence of Sensing Object Thickness and Material


BASIC Model

DC 2-wire/DC 3-wire Double distance model/ Spatter-resistant Double distance model


Size: M8 E2EW-(Q)X2□8




Size: M12 E2EW-(Q)X3□12



Size: M18 E2EW-(Q)X7□18




Size: M30 E2EW-(Q)X12□30




DC 2-wire/DC 3-wire Single distance model/ Spatter-resistant Single distance model


Size: M8 E2EW-(Q)X1R5□8




Size: M12 E2EW-(Q)X2□12



Size: M18 E2EW-(Q)X5□18




Size: M30 E2EW-(Q)X10□30




PREMIUM Model

DC 3-wire Quadruple distance model/ Spatter-resistant Quadruple distance model


Size: M12 E2EW-(Q)X7□12



Size: M18 E2EW-(Q)X12□18




Size: M30 E2EW-(Q)X22□30




DC 3-wire Triple distance model/ Spatter-resistant Triple distance model


Size: M12 E2EW-(Q)X6□12



Size: M18 E2EW-(Q)X10□18



Size: M30 E2EW-(Q)X20□30




E2EW Series

Monitor Output vs. Sensing Distance

PREMIUM Model


DC 3-wire

Quadruple distance model/Spatter-resistant Quadruple distance model



DC 3-wire


Triple distance model/Spatter-resistant Triple distance model



I/O Circuit Diagrams/Timing charts

DC 2-wire

BASIC Models



E2EW Series

DC 3-wire

PNP output (BASIC Model)

Operation mode	Model	Timing chart	Output circuit
NO	E2EW-(Q)X□B1	Nonsensing area Sensing area Sensing object Proximity Sensor Rated Sensing distance (%) 100 0 ON Operation indicator OFF (orange) ON OFF Control output	Black (4) Blue (3) O V
NC	E2EW-(Q)X□B2	Nonsensing area Sensing area Sensing object Proximity Sensor Rated Sensing distance (%) 100 ON Operation indicator OFF (orange) ON OFF Control output	Black (2) main circuit Blue (3) Blue (3)
NO+NC	E2EW-(Q)X□B3	Nonsensing area Sensing object Rated Sensing distance (%) 100 0 ON Operation indicator OFF (orange) ON Control output 1 ON Control output 2 OFF Control output 2	Black (4) OUT1 Proximity sensor main oricuit White (2) OUT2 Load Load Load O V

NPN output (BASIC Model)

Operation mode	Model	Timing chart	Output circuit
NO	E2EW-(Q)X□C1	Nonsensing area Sensing Sensing area Sensing Sensing Sensing area Proximity Sensor Proximity Sensor ON Operation indicator OFF (orange) ON OFF Control output	10 to 30 VDC Brown (1) +V Load Proxinity sensor main circuit Black (4) Blue (3) 0 V
NC	E2EW-(Q)X□C2	Nonsensing area Sensing object Rated Sensing distance (%) 100 ON Operation indicator OFF (orange) ON OFF Control output	Proximity sensor main circuit Black (2) Blue (3) 0 V
NO+NC	E2EW-(Q)X□C3	Nonsensing area Sensing object Rated Sensing distance (%) 100 ON Operation indicator OFF (orange) ON Control output 1 ON OFF Control output 2	Brown (1) 10 to 30 VDC Load Load Load Proximity OUT1 Sensor White (2) OUT2 Blue (3) O V

Connector Pin Arrangement

DC 3-wire

PNP output (PREMIUM Model) [Refer to Timing Chart on page 34]

Output circuit			circuit
Operation mode	Model	Standard I/O mode (SIO mode) When using as a general	IO-Link Communication mode (COM mode) When using the Sensor connected to IO-Link Master Unit
NO	E2EW-(Q)X□B1	Black (4) Black (4) Black (3) O V Blue (3)	Proximity Sensor main circuit Black (4) Blue (3) O V (3)
NC	E2EW-(Q)X□B2	Black (2) Black (2) Black (2) Black (2) Black (3) Black (3) Black (3) Black (3)	
NO+NC	E2EW-(Q)X□B3	Brown (1) +V Black (4) OUT1 white (2) OUT2 Load Load O V Blue (3)	Proximity HV (1) +V (1) +V (1) C/Q (4) Black (4) DO DI (2) White (2) 0 V (3)

In the IO-Link mode, the cord between the IO-Link master and sensor must have a length of 20 m or less.

NPN output (PREMIUM Model)

Operation mode	Model	Timing chart	Output circuit
NO	E2EW-(Q)X□C1	Nonsensing area Sensing object Rated Sensing distance (%) 100 ON Operation indicator OFF (orange) ON OFF Control output	Proximity Sensor Gircuit Black (4)
NC	E2EW-(Q)X□C2	Nonsensing area Sensing object Rated Sensing distance (%) 100 0 ON Operation indicator OFF (orange) ON OFF Control output	Proximity sensor main circuit Blue (3) 0 V
NO+NC	E2EW-(Q)X□C3	Nonsensing area Sensing object Rated Sensing distance (%) 100 ON Operation indicator OFF (orange) ON Control output 1 ON Control output 2	Brown (1) V Load Load Load Proximity Sensor White (2) OUT2 Blue (3) OUT2


Connector Pin Arrangement

M12 Connector M12 Smartclick Connector	(2) (4)
---	---------

E2EW Series

DC 3-wire

PNP output (PREMIUM Model)



Please contact your OMRON sales representative regarding assignment of data.

- *1. For models with IO-Link, the operation mode can be changed by the IO-Link communications.
- *2. If using a model with IO-Link as a general sensor or using a model without IO-Link, it operates in the standard I/O mode (SIO mode).

Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

	Warning level
∆WARNING	Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

General prohibition Indicates the instructions of unspecified prohibited action.
Caution, explosion Indicates the possibility of explosion under specific conditions.

⚠ WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.




Otherwise, explosion may result. Never use the product with an AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- Do not use the product in environments subject to flammable or explosive gases.
- 2. Do not attempt to disassemble, repair, or modify the product.
- Do not use a voltage that exceeds the rated operating voltage range.
 - Applying a voltage that is higher than the operating voltage range may result in explosion or fire.
- Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or fire.
- If the power supply is connected directly without a load, the internal elements may explode or burn.



Precautions for Correct Use


Do not use the product in any atmosphere or environment that exceeds the ratings.

Operating Environment

- 1. Do not install the Sensor in the following locations.
 - Outdoor locations directly subject to sunlight, rain, snow, waterdroplets, or oil.
 - (2) Locations subject to atmospheres with chemical vapors, inparticular solvents and acids.
 - (3) Locations subject to corrosive gases.
- 2. The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com/product/cautions/) for typical measures.
- 3. Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- 5. When turning on the power by influence of temperature environment, an outputmis-pulse sometimes occurs. After the sensor has passed for 300 msec after turning on, please use in the stable state.
- **6.** The sensor is adjusted with a high degree of accuracy, so do not use in the environment with sudden temperature change.
- Operation check is performed using an OMRON's IO-Link master.
 If using an IO-Link master from another company, perform the operation check in advance. (Models with IO-Link only.)
- 8. When connecting non IO-Link compliant models to the IO-Link master, use the SIO mode.
- In the IO-Link mode, the cord between the IO-Link master and sensor must have a length of 20 m or less. (Models with IO-Link only.)
- 10. The Sensor cannot be used embedded in where pressure is constantly applied to the sensing surface, such as hydraulic cylinders and hydraulic valves.


AND Connection of Proximity Sensors (DC 2-wire)

Two or more sensors cannot be connected in series on the AND circuit. Use them via a relay as shown on the figure.



OR Wiring of Proximity Sensors (DC 2-wire)

As a general principle, two or more sensors cannot be used in parallel on the OR circuit. It is possible only when sensors do not operate simultaneously and loads do not need to be maintained. When loads need to be maintained, use the sensors via a relay as shown on the figure.



E2EW Series


Design

Influence of Surrounding Metal

When mounting the Proximity Sensor, ensure that the minimum distances given in the following table are maintained.

If you use a nut, only use the provided nut. And ensure that the minimum distances between the sensing surface and nut is bigger than the "L" given in the following table.

Other non-ferrous metals affect sensor's performance in the same way as aluminum. Perform the operation check in advance.



(Unit: mm)

Mounting panel material: Iron


Models	Model	L	d	D	m	n
Quadruple distance model	E2EW-(Q)X7□12	4	30	4	28	36
	E2EW-(Q)X12□18	6	54	6	36	54
	E2EW-(Q)X22□30	8	90	8	66	90
Triple distance model	E2EW-(Q)X6□12	4	30	4	24	36
	E2EW-(Q)X10□18	2	54	2	30	54
	E2EW-(Q)X20□30	0	30	0	60	90
Double distance model	E2EW-(Q)X2□8	0	8	0	8	30
	E2EW-(Q)X3□12	0	12	0	12	40
	E2EW-(Q)X7□18	0	18	0	28	60
	E2EW-(Q)X12□30	0	30	0	48	100
Single distance model	E2EW-(Q)X1R5□8	0	8	0	4.5	30
	E2EW-(Q)X2□12	0	12	0	8	40
	E2EW-(Q)X5□18	0	18	0	20	60
	E2EW-(Q)X10□30	0	30	0	40	100

Mounting panel material: Aluminum

_						
Models	Model	L	d	D	m	n
Quadruple distance model	E2EW-(Q)X7□12	12	70	12	28	70
	E2EW-(Q)X12□18	12	80	12	36	80
	E2EW-(Q)X22□30 *1	16	120	16	66	120
Triple distance model	E2EW-(Q)X6□12	12	70	12	24	70
	E2EW-(Q)X10□18	12	80	12	30	80
	E2EW-(Q)X20□30 *1	16	120	16	60	120
Double distance model	E2EW-(Q)X2□8	10	50	10	8	50
	E2EW-(Q)X3□12	12	70	12	12	70
	E2EW-(Q)X7□18	12	80	12	28	80
	E2EW-(Q)X12□30	16	120	16	48	120
Single distance model	E2EW-(Q)X1R5□8	10	50	10	4.5	50
	E2EW-(Q)X2□12	12	70	12	8	70
	E2EW-(Q)X5□18	12	80	12	20	80
	E2EW-(Q)X10□30	16	120	16	40	120

^{*1.} If you use the model E2EW-(Q)X22□30, or E2EW-(Q)X20□30, the panel thickness (t) is 3 mm or less.

When the Proximity Sensor is mounted in metal, ensure that the minimum distances given in the following table are maintained.



(Unit: mm)

Embedded material: Iron

Models	Model	ı	d	D	m	n
Quadruple distance model	E2EW-(Q)X7□12	4	30	4	28	36
	E2EW-(Q)X12□18	6	54	6	36	54
	E2EW-(Q)X22□30	8	90	8	66	90
Triple distance model	E2EW-(Q)X6□12	0 *2	12 *2	0 *2	24	36
	E2EW-(Q)X10□18	0	18	0	30	54
mouoi	E2EW-(Q)X20□30	0	30	0	60	90
Double distance model	E2EW-(Q)X2□8	0	8	0	8	30
	E2EW-(Q)X3□12	0	12	0	12	40
	E2EW-(Q)X7□18	0	18	0	28	60
	E2EW-(Q)X12□30	0	30	0	48	100
Single distance model	E2EW-(Q)X1R5□8	0	8	0	4.5	30
	E2EW-(Q)X2□12	0	12	0	8	40
	E2EW-(Q)X5□18	0	18	0	20	60
	E2EW-(Q)X10□30	0	30	0	40	100


^{*2.} If the thickness of the mounting bracket (t) is less than 10 mm, be sure to install the Sensor so that $l \ge 2$, d (dia.) ≥ 30 , and D ≥ 2 .

Embedded material: Aluminum

Models	Model	I	d	D	m	n
Quadruple distance model	E2EW-(Q)X7□12	12	70	12	28	70
	E2EW-(Q)X12□18	12	80	12	36	80
	E2EW-(Q)X22□30	16	120	16	66	120
Triple distance model	E2EW-(Q)X6□12	12	70	12	24	70
	E2EW-(Q)X10□18	12	80	12	30	80
	E2EW-(Q)X20□30	16	120	16	60	120
Double distance model	E2EW-(Q)X2□8	10	50	10	8	50
	E2EW-(Q)X3□12	12	70	12	12	70
	E2EW-(Q)X7□18	12	80	12	28	80
	E2EW-(Q)X12□30	16	120	16	48	120
Single distance model	E2EW-(Q)X1R5□8	10	50	10	4.5	50
	E2EW-(Q)X2□12	12	70	12	8	70
	E2EW-(Q)X5□18	12	80	12	20	80
	E2EW-(Q)X10□30	16	120	16	40	120

Mutual Interference

When installing two or more Proximity Sensors face-to-face or sidebyside, ensure that the minimum distances given in the following table are maintained.



(Unit: mm)

			(,
Models	Model	Ite	em
Wodels	Wodel	Α	В
	E2EW-(Q)X7□12	45	40
Quadruple distance model	E2EW-(Q)X12□18	80	60
	E2EW-(Q)X22□30	135	110
Triple distance model	E2EW-(Q)X6□12	45	40
	E2EW-(Q)X10□18	80	60
	E2EW-(Q)X20□30	135	110
	E2EW-(Q)X2□8	35	35
Double distance	E2EW-(Q)X3□12	40	35
model	E2EW-(Q)X7□18	65	60
	E2EW-(Q)X12□30	110	100
	E2EW-(Q)X1R5□8	35	30
Single distance	E2EW-(Q)X2□12	40	35
model	E2EW-(Q)X5□18	65	60
	E2EW-(Q)X10□30	110	100

Chips from Cutting Aluminum

Normally, chips from cutting aluminum will not cause a detection signal to be output even if it adheres to or accumulates on the detection surface. In the following cases, however, a detection signal may be output.


Remove the cutting chips in these cases.


1. If $d \ge 2/3D$ at the center of the detection surface where d is the cutting chip size and D is the detection surface size

(Unit: mm)

Model	Dimension	D
E2EW-(Q)X□8		6
E2EW-(Q)X□12		10
E2EW-(Q)X□18		16
E2EW-(Q)X□30		28

2.If the cutting chips are pressed down





Mounting

Tightening Force

Do not tighten the nut with excessive force.

A washer must be used with the nut.

The tightening force must be the same or less than the figures in the following table.



Quadruple distance model, Triple distance model (Unit: N·m)

Size	Torque
M12	20 (15)
M18	70 (35)
M30	180 (60)

^{*} Tighten the nut of the E2EW-Q to a torque in parentheses.

Double distance model, Single distance model (Unit: N·m)

Size	Torque
M8	9 (6.2)
M12	30 (15)
M18	70 (35)
M30	180 (60)

^{*} Tighten the nut of the E2EW-Q to a torque in parentheses.

Note: When mounting the Proximity Sensor, only use the provided nut. Do not use set screws. The Sensor may malfunction.


BASIC Model DC 2-wire/DC 3-wire

E2EW/E2EW-Q Series (Double distance model/Spatter-resistant Double distance model/ Single distance model/Spatter-resistant Single distance model)

Pre-wired Model/Pre-wired Connector Model M12/M18/M30 Size







Pre-wired Model





Pre-wired Connector Model

(Operation mode): Output configuration (D1): NO (D2): NC (D2): NC Vinyl-insulated round cable with 2 conductors size: 6-dia. (Conductor cross section: 0.5 mm² (AWG20), Insulator diameter: 1.5 mm), Standard length: 2 m (Pre-wired Model), 0.3 m (Pre-wired Connector Model)


(Operation mode): Output configuration (B1/C1): NO (B2/C2): NC
Vinyl-insulated round cable with 3 conductors size: 6-dia.
(Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.05 mm), Standard length: 2 m (Pre-wired Model), 0.3 m (Pre-wired Connector Model)

(Operation mode): Output configuration (B3/C3): NO+NC Vinyl-insulated round cable with 4 conductors size: 6-dia. (Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.05 mm), Standard length: 2 m (Pre-wired Model), 0.3 m (Pre-wired Connector Model)

Models	Model	Α	В	C	D	Е	F	G
Double distance model	E2EW-(Q)X3 □12(-M1TJ) E2EW-(Q)X3D □12(-M1TGJ)	M12×P1	41.5	30	4	10	21 dia.	17
	E2EW-(Q)X7 □18(-M1TJ) E2EW-(Q)X7D □18(-M1TGJ)	M18×P1	41.5	30	4	13	29 dia.	24
	E2EW-(Q)X12 □30(-M1TJ) E2EW-(Q)X12D □30(-M1TGJ)	M30× P1.5	41.5	30	5	13	42 dia.	36
Single distance model	E2EW-(Q)X2 □12(-M1TJ) E2EW-(Q)X2D □12(-M1TGJ)	M12×P1	41.9	30.4	4	7	21 dia.	17
	E2EW-(Q)X5 □18(-M1TJ) E2EW-(Q)X5D □18(-M1TGJ)	M18×P1	41.9	30.4	4	10	29 dia.	24
	E2EW-(Q)X10 □30(-M1TJ) E2EW-(Q)X10D □30(-M1TGJ)	M30× P1.5	41.8	30.3	5	10	42 dia.	36

Pre-wired Model/Pre-wired Connector Model M8 Size





(M1TGJ) M12×P1

(Operation mode): Output configuration (D1): NO (D2): NC

Vinyl-insulated round cable with 2 conductors size: 4-dia.

(Conductor cross section: 0.26 mm² (AWG23), Insulator diameter: 1.15 mm), Standard length: 2 m (Pre-wired Model), 0.3 m (Pre-wired Connector Model)

(Operation mode): Output configuration (B1/C1): NO

Vinyl-insulated round cable with 3 conductors size: 4-dia.

(Conductor cross section: 0.26 mm² (AWG23), Insulator diameter: 1.15 mm), Standard length: 2 m (Pre-wired Model), 0.3 m (Pre-wired Connector Model)

Models	Model	Α	В	С	D	Е	F	G	Н
Double distance model	E2EW- (Q)X2□8 (-M1TGJ)	M8×P1	48.8	36.2	4	34.2	8	15 dia.	13
Single distance model	E2EW- (Q)X1R5□8 (-M1TGJ)	M8×P1	49	36.4	4	34.4	5	15 dia.	13

Mounting Hole Dimensions



Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5






Dimensions	R (mm)
M8	12
M12	
M18	18
M30	

BASIC Model DC 3-wire

E2EW/E2EW-Q Series (Single distance model/Spatter-resistant Single distance model)

M12 Connector Model







M12 Connector Model

M8 Size





Models	Model	Α	В	С	D	Е	F	G	Н
Single distance model	E2EW- X2□12-M1	M12×P1	54.8		4	28	6	21 dia.	17
	E2EW- X5□18-M1	M18×P1	54.8	32.4	4	28	9	29 dia.	24
	E2EW- X10□30-M1	M30× P1.5	54.7	32.3	5	28	9	42 dia.	36



Models	Model	Α	В	С	D	E	F	G	Н	I
Single distance model	E2EW- (Q)X1R5□8- M1	M8× P1	53.5	34.4	4	29.8	26.8	7	15 dia.	13

Mounting Hole Dimensions




F (mm)
8.5 dia. +0.5
12.5 dia. +0.5
18.5 dia. +0.5
30.5 dia. +0.5


PREMIUM Model DC 3-wire

E2EW/E2EW-Q Series (Quadruple distance/Triple distance/ Spatter-resistant Quadruple distance, Spatter-resistant Triple distance model)

Pre-wired Model/ Pre-wired Connector Model







(Operation mode): Output configuration (B1, C1): NO, (B2, C2); NC


Vinyl-insulated round cable with 3 conductors size: 6-dia. (Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.05 mm), Standard length: 2 m (Pre-wired Model), 0.3 m (Pre-wired Connector Model)

(Operation mode): Output configuration (B3, C3): NO+NC Vinyl-insulated round cable with 4 conductors size: 6-dia. (Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.05 mm), Standard length: 2 m (Pre-wired Model), 0.3 m (Pre-wired Connector Model)

Models	Model	Α	В	С	D	Е	F	G
Quadruple distance model	E2EW-(Q)X7 □12(-M1TJ)	M12×P1	41.5	30	4	10	21 dia.	17
	E2EW-(Q)X12 □18(-M1TJ)	M18×P1	41.5	30	4	13	29 dia.	24
	E2EW-(Q)X22 □30(-M1TJ)	M30×P1.5	41.5	30	5	13	42 dia.	36
Triple distance model	E2EW-(Q)X6 □12(-M1TJ)	M12×P1	41.5	30	4	10	21 dia.	17
	E2EW-(Q)X10 □18(-M1TJ)	M18×P1	41.5	30	4	13	29 dia.	24
	E2EW-(Q)X20 □30(-M1TJ)	M30×P1.5	41.5	30	5	13	42 dia.	36

M12 Connector Model






Models	Model	Α	В	С	D	Е	F	G	Н
	E2EW-(Q) X7□12-M1	M12×P1	54.4		4	28	8	21 dia.	17
Quadruple distance model	E2EW-(Q) X12□18-M1	M18×P1	54.4	32	4	28	11	29 dia.	24
model	E2EW-(Q) X22□30-M1	M30×P1.5	54.4	32	5	28	11	42 dia.	36
	E2EW-(Q) X6□12-M1	M12×P1	54.4		4	28	8	21 dia.	17
Triple distance model	E2EW-(Q) X10□18-M1	M18×P1	54.4	32	4	28	11	29 dia.	24
model	E2EW-(Q) X20□30-M1	M30×P1.5	54.4	32	5	28	11	42 dia.	36

Mounting Hole Dimensions



Dimensions	F (mm)
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Angle R of the Bending Wire



Dimensions	R (mm)
M12	
M18	18
M30	

Proximity Sensor

E2EQ NEXT Series

DC 2-wire/DC 3-wire

Enables easier and standardized designs previously not possible with fluororesin coating models

- Nearly double*1 the sensing distance of previous
- \bullet With high-brightness LED, the indicator is visible anywhere from 360°
- Comes in a wide variation to make sensor selection easy
- UL certification (UL60947-5-2)*2 and CSA certification (CSA C22.2 UL60947-5-2-14)
- Comparison with E2EQ products. Based on September 2021 OMRON investigation.
- *2. M8 (4-pin) Connector Models are not UL certified.



Be sure to read Safety Precautions on page 56.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

E2EQ NEXT Series Model Number Legend

E2EQ - X (1) (2) (3) (4) (5) (6) - (7) - (8) (9)

No.	Туре	Code	Meaning	Remarks
(1)	Sensing distance	Number	Sensing distance (Unit: mm) (R: Indication of decimal point)	
		B PNP open collector		Whether the D mode
(2)	Output configuration	С	NPN open collector	has polarity is define
		D	DC 2-wire polarity/no polarity	by number (7).
		1	Normally open (NO)	
(3)	Operation mode	2	Normally closed (NC)	
		3	Normally open, Normally closed (NO+NC)	
		Blank	Non IO-Link compliant	
(4)	IO-Link baud rate	D	COM2 (38.4 kbps)	
		Т	COM3 (230.4 kbps)	
		8	M8	
(E)	Size	12	M12	
(5)	GIZC	18	M18	
		30	M30	
		Blank	Pre-wired Models	
		M1	M12 Connector Models	
		M3	M8 (4-pin) Connector Models	
		M5	M8 (3-pin) Connector Models	
		M1GJ	M12 Pre-wired Standard Connector Models DC 2-wire	
(6)	Connection method	M1TGJ	M12 Pre-wired Smartclick Connector Models DC 2-wire	
		M1TGJR	M12 Pre-wired Smartclick Connector Models Robot (bending-resistant) cable DC 2-wire	
		M1TJ	M12 Pre-wired Smartclick Connector Models DC 3-wire	
		M1TJR	M12 Pre-wired Smartclick Connector Models Robot (bending-resistant) cable DC 3-wire	
(7)	DC 2 wire polarity	Blank	Polarity	
(7)	DC 2-wire polarity	Т	No polarity	
(0)	Coble apositionations *1	Blank	Standard PVC cable	
(8) Cable specifications *1		R	Robot (bending-resistant) cable	
(9)	Cable length	Number M	Cable length	

^{*1. (8)} is only shown in the model number of Pre-wired Models.

Note: The purpose of this model number legend is to provide understanding of the meaning of specifications from the model number.

Ordering Information

Sensors

BASIC Model

E2EQ NEXT Series (Spatter-resistant Double distance model)

DC 2-wire Shielded [Refer to Ratings and Specification on page 45, Dimension on page 58.]

Size	Connection method	Dolovity	Model
(Sensing distance)	Connection method	Polarity	Operation mode: NO
M12	Pre-wired (2 m) *1		E2EQ-X4D112-T 2M
(4 mm)	M12 Pre-wired Smartclick Connector (0.3 m)		E2EQ-X4D112-M1TGJ-T 0.3M
M18	Pre-wired (2 m) *1		E2EQ-X8D118-T 2M
(8 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EQ-X8D118-M1TGJ-T 0.3M
M30	Pre-wired (2 m) *1		E2EQ-X15D130-T 2M
(15 mm)	M12 Pre-wired Smartclick Connector (0.3 m)		E2EQ-X15D130-M1TGJ-T 0.3M

^{*1.} Models with 5-m cable length are also available (Example: E2EQ-X4D112-T 5M).

BASIC Model

E2EQ NEXT Series (Spatter-resistant Double distance model)

DC 3-wire Shielded [Refer to Ratings and Specification on page 46, Dimension on page 58.]

Size (Sensing	Connection method *2	Dade de	Operation	Мо	del
distance)	Connection method "2	Body size	mode *3	PNP	NPN
M8	Pre-wired (2 m) *1	38 mm	NO	E2EQ-X2B1D8 2M	E2EQ-X2C18 2M
(2 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	38 mm	NO	E2EQ-X2B1D8-M1TJ 0.3M	E2EQ-X2C18-M1TJ 0.3M
	Dro wired (2 m) *4	47 mm	NO	E2EQ-X4B1D12 2M	E2EQ-X4C112 2M
M12	Pre-wired (2 m) *1	47 111111	NO+NC	E2EQ-X4B3D12 2M	E2EQ-X4C312 2M
(4 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	47 mm	NO	E2EQ-X4B1D12-M1TJ 0.3M	E2EQ-X4C112-M1TJ 0.3M
			NO+NC	E2EQ-X4B3D12-M1TJ 0.3M	E2EQ-X4C312-M1TJ 0.3M
	D : 1/0) *4	55 mm	NO	E2EQ-X8B1D18 2M	E2EQ-X8C118 2M
M18	Pre-wired (2 m) *1	111111 66	NO+NC	E2EQ-X8B3D18 2M	E2EQ-X8C318 2M
(8 mm)	M12 Pre-wired		NO	E2EQ-X8B1D18-M1TJ 0.3M	E2EQ-X8C118-M1TJ 0.3M
	Smartclick Connector (0.3 m)	55 mm	NO+NC	E2EQ-X8B3D18-M1TJ 0.3M	E2EQ-X8C318-M1TJ 0.3M
	Dro wired (2 m) *4	60 mm	NO	E2EQ-X15B1D30 2M	E2EQ-X15C130 2M
M30	Pre-wired (2 m) *1	ou mm	NO+NC	E2EQ-X15B3D30 2M	E2EQ-X15C330 2M
(15 mm)	M12 Pre-wired	60 mm	NO	E2EQ-X15B1D30-M1TJ 0.3M	E2EQ-X15C130-M1TJ 0.3M
	Smartclick Connector (0.3 m)	ווווו טט	NO+NC	E2EQ-X15B3D30-M1TJ 0.3M	E2EQ-X15C330-M1TJ 0.3M

BASIC Model

E2EQ NEXT Series (Spatter-resistant Single distance model)

DC 3-wire Shielded [Refer to Ratings and Specification on page 46, Dimension on page 58.]

Size (Sensing	Connection method *2	Dada sia	Operation	Mo	del
distance)	Connection method 2	Body size	mode *3	PNP	NPN
M8	Pre-wired (2 m) *1	38 mm	NO	E2EQ-X1R5B1D8 2M	E2EQ-X1R5C18 2M
(1.5 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	38 mm	NO	E2EQ-X1R5B1D8-M1TJ 0.3M	E2EQ-X1R5C18-M1TJ 0.3M
	Drawinad (2 m) *1	47 mm	NO	E2EQ-X2B1D12 2M	E2EQ-X2C112 2M
M12	Pre-wired (2 m) *1	47 111111	NO+NC	E2EQ-X2B3D12 2M	E2EQ-X2C312 2M
(2 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	47 mm	NO	E2EQ-X2B1D12-M1TJ 0.3M	E2EQ-X2C112-M1TJ 0.3M
			NO+NC	E2EQ-X2B3D12-M1TJ 0.3M	E2EQ-X2C312-M1TJ 0.3M
	Pre-wired (2 m) *1	55 mm	NO	E2EQ-X5B1D18 2M	E2EQ-X5C118 2M
M18		22 11111	NO+NC	E2EQ-X5B3D18 2M	E2EQ-X5C318 2M
(5 mm)	M12 Pre-wired	EE mana	NO	E2EQ-X5B1D18-M1TJ 0.3M	E2EQ-X5C118-M1TJ 0.3M
	Smartclick Connector (0.3 m)	55 mm	NO+NC	E2EQ-X5B3D18-M1TJ 0.3M	E2EQ-X5C318-M1TJ 0.3M
	Pre-wired (2 m) *1	60 mm	NO	E2EQ-X10B1D30 2M	E2EQ-X10C130 2M
M30	rie-wiieu (Z III) T	60 mm	NO+NC	E2EQ-X10B3D30 2M	E2EQ-X10C330 2M
(10 mm)	M12 Pre-wired	60 mm	NO	E2EQ-X10B1D30-M1TJ 0.3M	E2EQ-X10C130-M1TJ 0.3M
	Smartclick Connector (0.3 m)	00 111111	NO+NC	E2EQ-X10B3D30-M1TJ 0.3M	E2EQ-X10C330-M1TJ 0.3M

^{*1.} Models with 5-m cable length are also available (Example: E2EQ-X6B1D12 5M)

Note: 1. Models in _____ are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X□□□T□" (Example: E2EQ-X6B1T12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

^{*2.} M12 Connector Models are also available with "M1" suffix. (Example: E2EQ-X2B1D8-M1)

^{*3.} NC models are also available. The model number is E2EQ-X\(\sum \)2\(\sum \) (Example: E2EQ-X3\(\beta \)2 2M).

^{2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

PREMIUM Model

E2EQ NEXT Series (Spatter-resistant Triple distance model)

DC 2-wire Shielded *1 [Refer to Ratings and Specification on page 47, Dimension on page 59.]

Size	Connection method	Polarity	Model			
(Sensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: NC		
	Dro wined (2 m) *2	Yes	E2EQ-X3D18 2M	E2EQ-X3D28 2M		
M8	Pre-wired (2 m) *2	No	E2EQ-X3D18-T 2M	E2EQ-X3D28-T 2M		
(3 mm)	M12 Pre-wired	Yes	E2EQ-X3D18-M1TGJ 0.3M	E2EQ-X3D28-M1TGJ 0.3M		
	Smartclick Connector (0.3 m)	No	E2EQ-X3D18-M1TGJ-T 0.3M	E2EQ-X3D28-M1TGJ-T 0.3M		
	Pre-wired (2 m) *2	Yes	E2EQ-X7D112 2M	E2EQ-X7D212 2M		
M12	rie-wiieu (2 iii) 2	No	E2EQ-X7D112-T 2M	E2EQ-X7D212-T 2M		
(7 mm)	M12 Pre-wired	Yes	E2EQ-X7D112-M1TGJ 0.3M	E2EQ-X7D212-M1TGJ 0.3M		
	Smartclick Connector (0.3 m)	No	E2EQ-X7D112-M1TGJ-T 0.3M	E2EQ-X7D212-M1TGJ-T 0.3M		
	Pre-wired (2 m) *2	Yes	E2EQ-X11D118 2M	E2EQ-X11D218 2M		
M18	Pre-wired (2 m) 2	No	E2EQ-X11D118-T 2M	E2EQ-X11D218-T 2M		
(11 mm)	M12 Pre-wired	Yes	E2EQ-X11D118-M1TGJ 0.3M	E2EQ-X11D218-M1TGJ 0.3M		
	Smartclick Connector (0.3 m)	No	E2EQ-X11D118-M1TGJ-T 0.3M	E2EQ-X11D218-M1TGJ-T 0.3M		
	Pre-wired (2 m) *2	Yes	E2EQ-X20D130 2M	E2EQ-X20D230 2M		
M30	rie-wiieu (2 iii) 2	No	E2EQ-X20D130-T 2M	E2EQ-X20D230-T 2M		
(20 mm)	M12 Pre-wired	Yes	E2EQ-X20D130-M1TGJ 0.3M	E2EQ-X20D230-M1TGJ 0.3M		
	Smartclick Connector (0.3 m)	No	E2EQ-X20D130-M1TGJ-T 0.3M	E2EQ-X20D230-M1TGJ-T 0.3M		

^{*1.} When embedding the Proximity Sensor in metal, refer to *Influence of Surrounding Metal* on page 57.

PREMIUM Model

E2EQ NEXT Series (Spatter-resistant Triple distance model)

DC 3-wire Shielded *1 [Refer to Ratings and Specification on page 48, Dimension on page 59.]

Size (Sensing	Connection method *3	Dody size	Operation	Mo	del
distance)	Connection method 3	Body size	mode *4	PNP	NPN
M8	Pre-wired (2 m) *2	38 mm	NO	E2EQ-X3B1D8 2M	E2EQ-X3C18 2M
(3 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	38 mm	NO	E2EQ-X3B1D8-M1TJ 0.3M	E2EQ-X3C18-M1TJ 0.3M
	Pre-wired (2 m) *2	47 mm	NO	E2EQ-X6B1D12 2M	E2EQ-X6C112 2M
M12	Pre-wired (2 m) 2	47 111111	NO+NC	E2EQ-X6B3D12 2M	E2EQ-X6C312 2M
(6 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	47 mm	NO	E2EQ-X6B1D12-M1TJ 0.3M	E2EQ-X6C112-M1TJ 0.3M
			NO+NC	E2EQ-X6B3D12-M1TJ 0.3M	E2EQ-X6C312-M1TJ 0.3M
	Pre-wired (2 m) *2	F.F	NO	E2EQ-X12B1D18 2M	E2EQ-X12C118 2M
M18		55 mm	NO+NC	E2EQ-X12B3D18 2M	E2EQ-X12C318 2M
(12 mm)	M12 Pre-wired	EE mama	NO	E2EQ-X12B1D18-M1TJ 0.3M	E2EQ-X12C118-M1TJ 0.3M
	Smartclick Connector (0.3 m)	55 mm	NO+NC	E2EQ-X12B3D18-M1TJ 0.3M	E2EQ-X12C318-M1TJ 0.3M
	D==i== d (0 ==) *0	CO	NO	E2EQ-X22B1D30 2M	E2EQ-X22C130 2M
M30	Pre-wired (2 m) *2	60 mm	NO+NC	E2EQ-X22B3D30 2M	E2EQ-X22C330 2M
(22 mm)	M12 Pre-wired	CO	NO	E2EQ-X22B1D30-M1TJ 0.3M	E2EQ-X22C130-M1TJ 0.3M
	Smartclick Connector (0.3 m)	60 mm	NO+NC	E2EQ-X22B3D30-M1TJ 0.3M	E2EQ-X22C330-M1TJ 0.3M

^{*1.} When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 57.

Sensor I/O Connectors (Sold Separately)

For details of the connector, refer to XS5 Series on page 66.

^{*2.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2EQ-X3D18 5M)

^{*2.} Models with 5-m cable length are also available (Example: E2EQ-X6B1D12 5M)

^{*3.} M12 Connector Models are also available with "M1" suffix. (Example: E2EQ-X3B1D8-M1).

^{*4.} NC models are also available. The model number is E2EQ- \square 2 \square 2 (Example: E2EQ-X3B28 2M).

Note: 1. Models in _____ are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X□□□T□" (Example: E2EQ-X6B1T12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

^{2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

Ratings and Specifications

BASIC Model

E2EQ NEXT Series (Spatter-resistant Double distance model)

DC 2-wire Shielded

	Size	M12	M18	M30						
Item	Model	E2EQ-X4D□12	E2EQ-X8D□18	E2EQ-X15D□30						
Sensing distan	се	4 mm ±10% 8 mm ±10%		15 mm ±10%						
Setting distanc	e *1	0 to 3.2 mm	0 to 6.4 mm	0 to 12 mm						
Differential trav	el	15% max. of sensing distance								
Detectable obje	ect	Ferrous metals (For non-ferrous meta	ls, refer to <i>Engineering Data</i> on page 4	9.)						
Standard sensi	ng object (Iron)	12 × 12 × 1 mm	18 × 18 × 1 mm	30 × 30 × 1 mm						
Response frequ	iency *2	1,000 Hz	500 Hz	250 Hz						
Power supply v	oltage	10 to 30 VDC (including 10% ripple (p	-p)), Class 2							
Current consun	nption	0.8 mA max.								
Control output	Load current	3 to 100 mA								
Control output	Residual voltage	5 V max. (Load current: 100 mA, Cab	5 V max. (Load current: 100 mA, Cable length: 2 m)							
Indicator		Operation indicator (orange), Setting i	ndicator (green)							
Operation mode	e	NO Refer to the timing charts under I/O C	ircuit Diagrams/Timing charts on page	52 for details.						
Protection circu	uits	Surge suppressor, Load short-circuit p	protection							
Ambient tempe	rature range	Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)								
Ambient humid	ity range	Operating and Storage: 35% to 95% (with no condensation)								
Temperature in	fluence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C								
Voltage influen	ce	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range								
Insulation resis	tance	50 M $Ω$ min. (at 500 VDC) between current-carrying parts and case								
Dielectric stren	gth	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case								
Vibration resist	ance (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions								
Shock resistan	ce (destruction)	1,000 m/s² 10 times each in X, Y, and Z directions								
Degree of prote	ection	Pre-wired Models, Pre-wired Connect	or Models: IEC 60529:IP67, JIS C 0920	Annex 1: IP67G						
Connection me	thod	Pre-wired Models (Standard cable len M12 Pre-wired Smartclick Connector	gth: 2 m) and Models (Standard cable length: 0.3 m)							
Weight	Pre-wired	Approx. 100 g	Approx. 180 g	Approx. 250 g						
(packed state)	M12 Pre-wired Smartclick Connector	Approx. 75 g	Approx. 110 g	Approx. 180 g						
	Materials	Fluororesin coating (Base material: br	ass)							
	Sensing surface	Fluororesin								
Materials	Clamping nuts	Fluororesin coating (Base material: brass)								
	Toothed washer	Zinc-plated iron								
	Cable	Vinyl chloride (PVC)								
MTTFd (Year)		2,846	2,786	2,782						
Accessories		Instruction manual, Clamping nuts, To	oothed washer							
4 11 4 0			D) O)							

^{*1.} Use the Sensor within the range in which the setting indicator (green LED) is ON.

^{*2.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

BASIC Model

E2EQ NEXT Series (Spatter-resistant Double distance/Single distance model)

DC 3-wire Shielded

	Types		Double dista	ance Models			Single dista	ance Models	
	Size	M8	M12	M18	M30	M8	M12	M18	M30
Item	Model	E2EQ-X2□8	E2EQ-X4□12	E2EQ-X8□18	E2EQ-X15□30	E2EQ-X1R5□8	E2EQ-X2□12	E2EQ-X5□18	E2EQ-X10□30
Sensing di	stance	2 mm±10%	4 mm±10%	8 mm±10%	15 mm±10%	1.5 mm±10%	2 mm±10%	5 mm±10%	10 mm±10%
Setting dis		0 to 1.6 mm	0 to 3.2 mm	0 to 6.4 mm	0 to 12 mm	0 to 1.2 mm	0 to 1.6 mm	0 to 4 mm	0 to 8 mm
Differential	l travel	15% max. of se	15% max. of sensing distance 10% max. of sensing distance						
Detectable	object	Ferrous metals	(For non-ferrous	metals, refer to	the Engineering	Data on page 49	1.)		
Standard se	ensing object (Iron)	8 × 8 × 1 mm	12 × 12 × 1 mm	24 × 24 × 1 mm	45 × 45 × 1 mm	8 × 8 × 1 mm	12 × 12 × 1 mm	18 × 18 × 1 mm	30 × 30 × 1 mm
Response	frequency *1	1,500 Hz	1,000 Hz	500 Hz	250 Hz	2,000 Hz	1,500 Hz	600 Hz	400 Hz
Power sup	ply voltage	10 to 30 VDC (i	ncluding 10% rip	ple (p-p)), Class	2				
Current co	nsumption	1-output models	s: 16 mA max., 2	-output models:	20 mA max.				
Output con	nfiguration	B□ Models: PN	P open collector	, C□ Models: NF	PN open collector	r			
	mode (with oject approaching)				1-output models en, Normally clos		ormally closed)		
Control	Load current	2-output models M12, M18, M30	s: 10 to 30 VDC, size	Class 2, 50 mA	A max., (-40 to 70 max. A max., 2-output	,	,	00 mA max.	
output	Residual voltage	M12, M18, M30	size `	•	Cable length: 2 m)	, ,	,	,	,
Indicator *2	2				n indicator (orange): Operation indi				
Protection	circuits	Power supply re	everse polarity p	rotection, Surge	suppressor, Outp	out short-circuit p	rotection, Outpu	t reverse polarity	protection
Ambient te	mperature range	Operating/Storage: -40 to 85°C (with no icing or condensation) Note: The UL temperature rating for M12 Pre-wired Connector Models is -25 to 70°C.							
Ambient hu	umidity range	Operating/Storage: 35% to 95% (with no condensation)							
Temperatu	re influence				mperature range mperature range				
Voltage inf	luence	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range							
Insulation	resistance	$50~\text{M}\Omega$ min. (at $500~\text{VDC}$) between current-carrying parts and case							
Dielectric s	strength	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case							
Vibration re (destructio		10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions							
Shock resistance (destruction		M8 size: 500 m/s² 10 times each in X, Y, and Z directions/M12, M18, M30 size: 1,000 m/s² 10 times each in X, Y, and Z directions							
Degree of p	protection	Pre-wired Models, Pre-wired Connector Models: IEC 60529:IP67, JIS C 0920 Annex 1: IP67G *4/Connector Models: IEC 60529 IP67							
Connection	n method	Pre-wired Mode	ls (Standard cabl	e length: 2 m) and	d Pre-wired Conn	ector Models (Sta	ndard cable leng	th: 0.3 m), M12 C	onnector Models
	Pre-wired	Approx. 85 g	Approx. 95 g	Approx. 170 g	Approx. 240 g	Approx. 85 g	Approx. 95 g	Approx. 170 g	Approx. 240 g
Weight *3 (packed state)	M12 Pre-wired Smartclick Connector	Approx. 55 g	Approx. 70 g	Approx. 105 g	Approx. 170 g	Approx. 55 g	Approx. 70 g	Approx. 105 g	Approx. 170 g
	Connector	Approx. 40 g	Approx. 55 g	Approx. 85 g	Approx. 160 g	Approx. 40 g	Approx. 55 g	Approx. 85 g	Approx. 160 g
	Case	M8 size: Fluororesin coating (Base material: SUS303)/M12, M18, M30 size: Fluororesin coating (Base material: brass)							
	Sensing surface	Fluorine resin							
Materials	Clamping nuts	Fluororesin coating (Base material: brass)							
	Toothed washers	Zinc-plated iron							
	Cable	Vinyl chloride (PVC)							
Main IO-Lir	nk functions *2	Operation mode switching between NO and NC, self diagnosis enabling, excessive proximity judgment distance selecting, timer function of the control output and timer time selecting, instability output (IO-Link mode) ON delay timer time selecting function, monitor output, operating hours read-out, readout of the sensor internal temperature, and initial reset							
IO-Link	IO-Link specification	Ver1.1							
Commun ication	Baud rate	COM2 (38.4 kb	ps), COM3 (230.	4 kbps)					
specifica	Data length	PD size: 2 byte:	s, OD size: 1 byt	e (M-sequence t	ype: TYPE_2_2)				
tions *2	Minimum cycle time	COM2: 2.3 ms,	COM3: 0.4 ms						
MTTFd (Ye	ar)	2,446	2,444			2,446	2,444		
Accessorie	es	Instruction man	ual, Clamping กเ	ıts, Toothed was	her				

^{*1.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

^{*2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*3.} Weight of the standard body-sized model.
*4. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

PREMIUM Model

E2EQ NEXT Series (Spatter-resistant Triple distance model)

DC 2-wire Shielded

	Size	M8	M12	M18	M30				
Item	Model	E2EQ-X3D□8	E2EQ-X7D□12	E2EQ-X11D□18	E2EQ-X20D□30				
Sensing distance	9	3 mm ±10%	7 mm ±10%	11 mm ±10%	20 mm ±10%				
Setting distance	*1	0 to 2.4 mm	0 to 4.9 mm	0 to 8.8 mm	0 to 16 mm				
Differential trave	I	15% max. of sensing distan	ce		1				
Detectable objec	t	Ferrous metal (The sensing	distance decreases with nor	-ferrous metal. Refer to Engi	ineering Data on page 49.				
Standard sensing	g object (Iron)	9 × 9 × 1 mm	21 × 21 × 1 mm	33 × 33 × 1 mm	60 × 60 × 1 mm				
Response freque	ency *2	250 Hz	250 Hz	250 Hz	200 Hz				
Power supply vo	Itage	10 to 30 VDC, (including 10	% ripple (p-p))		1				
Leakage current		0.8 mA max.							
	Load current	3 to 100 mA							
Control output	Residual voltage		rrent: 100 mA, Cable length: : current: 100 mA, Cable leng						
Indicator		D1 Models: Operation indicate D2 Mod	ator (orange), Setting indicato ator (orange)	or (green)					
Operation mode		D1 Models: NO D2 Models: NC	the timing charts under I/O (Circuit Diagrams/Timing chart	s on page 52 for details.				
Protection circui	ts	Surge suppressor, Load short-circuit protection							
Ambient tempera	ature range	Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)							
Ambient humidit	y range	Operating and Storage: 35% to 95% (with no condensation)							
Temperature infl	uence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C ±20% max. of sensing distance at 23°C in the temperature range of -25 to 70°C							
Voltage influence	е	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range							
Insulation resista	ance	50 M Ω min. (at 500 VDC) between current-carrying parts and case							
Dielectric streng	th	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case							
Vibration resista	nce (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions							
Shock resistance	e (destruction)	500 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions							
Degree of protec	tion	Pre-wired/Pre-wired M12 C	onnector: IP67 (IEC 60529) a	ind IP67G *3 (JIS C 0920 Ani	nex 1)				
Connecting meth	nod	Pre-wired (Standard cable I	ength: 2 m) and Pre-wired M	12 Connector (Standard cable	e length: 0.3 m)				
Weight	Pre-wired	Approx. 60 g	Approx. 70 g	Approx. 150 g	Approx. 210 g				
(packed state)	Pre-wired M12 Connector	Approx. 30 g	Approx. 40 g	Approx. 90 g	Approx. 140 g				
	Case	Fluororesin coating (Base n	naterial: brass)						
	Sensing surface	Fluororesin							
Materials	Clamping nuts	Fluororesin coating (Base n	naterial: brass)						
	Toothed washer	Zinc-plated iron							
	Cable	Vinyl chloride (PVC)							
MTTFd (Year)		2,852	4,390	4,236	5,464				
Accessories		Instruction manual, Clamping nuts, Toothed washer							
1. Use the Sen	sor within the range in whic	ch the setting indicator (gr	reen LED) is ON (except l	D2 Models).					

^{*1.} Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).
*2. The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

^{*3.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards). The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

PREMIUM Model

E2EQ NEXT Series (Spatter-resistant Triple distance model)

DC 3-wire Shielded

		Size	M8	M12	M18	M30			
Item	ı	Model	E2EQ-X3□8	E2EQ-X6□12	E2EQ-X12□18	E2EQ-X22□30			
Sensing dis	tance		3 mm±10%	6 mm±10%	12 mm±10%	22 mm±10%			
Setting dista	ance		to 2.4 mm 0 to 4.8 mm 0 to 9.6 mm 0 to 16.8 mm						
Differential 1			15% max. of sensing distance						
Detectable of	object		Ferrous metals (For non-ferrous metals, refer to the <i>Engineering Data</i> on page 49.)						
	nsing object (li	ron)	9 × 9 × 1 mm						
	requency *1		1,000 Hz	800 Hz	500 Hz	200 Hz			
Power supply voltage			10 to 30 VDC (including 10% r	ipple (p-p)). Class 2					
Current con			1-output models: 16 mA max.	1-output models: 16 mA max.,	2-output models: 20 mA max.				
Output conf	· ·		•	or, C□ Models: NPN open collec	· · · · · · · · · · · · · · · · · · ·				
Operation m with sensinapproaching	node ig object		1-output models (B1, C1): NO (Normally open), 1-output models (B2, C2): NC (Normally closed)	1-output models (B1, C1): NO 1-output models (B2, C2): NC 2-output models (B3, C3): NO-	(Normally open), (Normally closed),	closed)			
Control	Load current		1-output models: 10 to 30 VDC, Class 2, 100 mA max.	1-output models: 10 to 30 VDC 2-output models: 10 to 30 VDC					
output Residual voltage			1-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m)	1-output models: 2 V max. (Lo. 2-output models: 2 V max. (Lo.					
Indicator *2				mode): Operation indicator (ora node (COM mode): Operation ind					
Protection circuits			Power supply reverse polarity	protection, Surge suppressor, O	utput short-circuit protection, O	utput reverse polarity protection			
Ambient ten	nperature range	е	Operating/Storage: -25 to 70°C (with no icing or condensation)						
Ambient hu	midity range		Operating/Storage: 35% to 95% (with no condensation)						
Temperature influence			±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C						
Voltage influence			±1% max. of sensing distance at rated voltage in the rated voltage ±15% range						
Insulation resistance			50 MΩ min. (at 500 VDC) between current-carrying parts and case						
Dielectric st	rength		1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case						
/ibration res	sistance (destru	ction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions						
Shock resis	tance (destruct	tion)	500 m/s ² 10 times each in X, Y, and Z directions	1,000 m/s² 10 times each in X, Y, and Z directions					
Degree of p	rotection		Pre-wired Models, Pre-wired Connector Models: IEC 60529: IP67, JIS C 0920 Annex 1: IP67G *4 Connector Models: IEC 60529: IP67						
Connection	method		Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 0.3 m), W12 Connector Models						
	Pre-wired Mod	dels	Approx. 85 g	Approx. 95 g	Approx. 180 g	Approx. 260 g			
Weight *3 packed state)	M12 Pre-wired Smartclick Connector	I	Approx. 55 g	Approx. 70 g	Approx. 115 g	Approx. 200 g			
	Connector		Approx. 40 g	Approx. 55 g	Approx. 95 g	Approx. 180 g			
	Case		Fluororesin coating (Base mate	erial: brass)					
	Sensing surfa	се	Fluorine resin						
/laterials	Clamping nuts	S	Fluororesin coating (Base mate	erial: brass)					
	Toothed wash	ers	Zinc-plated iron						
	Cable		Vinyl chloride (PVC)						
Main IO-Link functions *2			Operation mode switching between NO and NC, self diagnosis enabling, excessive proximity judgment distance selecting, time function of the control output and timer time selecting, instability output (IO-Link mode) ON delay timer time selecting function monitor output, operating hours read-out, readout of the sensor internal temperature, and initial reset						
O-Link	IO-Link specification		Ver 1.1						
Communic ation	Baud rate		COM2 (38.4 kbps), COM3 (230	0.4 kbps)					
specificati	Data length		PD size: 2 bytes, OD size: 1 by	yte (M-sequence type: TYPE_2_	2)				
ons *2	Minimum cycl time	е	COM2: 2.3 ms, COM3: 0.4 ms						
MTTFd (Yea	r)		2,446	2,444	2,444	2,416			
Accessories	3		Instruction manual, Clamping r	nuts, Toothed washer	•				

^{*1.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

^{*2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*3.} Weight of the standard body-sized model.

^{*4.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).


The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

Engineering Data (Reference Value)


Sensing Area

BASIC Model


DC 2-wire Spatter-resistant Double distance model



DC 3-wire Spatter-resistant Double distance model




DC 3-wire Spatter-resistant Single distance model




PREMIUM Model

DC 2-wire Spatter-resistant Triple distance model





DC 3-wire Spatter-resistant Triple distance model



Leakage Current


DC 2-wire Spatter-resistant Triple distance/ Double distance model





Residual Output Voltage

DC 2-wire Spatter-resistant Triple distance/ Double distance model E2EQ-X□D□(-T)




Influence of Sensing Object Size and Material


BASIC Model

DC 2-wire/3-wire Spatter-resistant Double distance model


Size: M8 E2EQ-X2□8




Size: M12 E2EQ-X4□12



Size: M18 E2EQ-X8□18




Size: M30 E2EQ-X15□30




BASIC Model

DC 3-wire Spatter-resistant Single distance model


Size: M8 E2EQ-X1R5□8




Size: M12 E2EQ-X2□12



Size: M18 E2EQ-X5□18




Size: M30 E2EQ-X10□30




PREMIUM Model

DC 2-wire Spatter-resistant Triple distance model


Size: M8 E2EQ-X3D□8




Size: M12 E2EQ-X7D□12



Size: M18 E2EQ-X11D□18




Size: M30 E2EQ-X20D□30




PREMIUM Model

DC 3-wire Spatter-resistant Triple distance model


Size: M8 E2EQ-X3□8




Size: M12 E2EQ-X6□12



Size: M18 E2EQ-X12□18



Size: M30 E2EQ-X22□30




Monitor Output vs. Sensing Distance


BASIC Model

DC 3-wire Spatter-resistant Double distance model


Size: M8 E2EQ-X2□8




Size: M12 E2EQ-X4□12



Size: M18 E2EQ-X8□18




Size: M30 E2EQ-X15□30




BASIC Model

DC 3-wire Spatter-resistant Single distance model


Size: M8 E2EQ-X1R5□8




Size: M12 E2EQ-X2□12



Size: M18 E2EQ-X5□18




Size: M30 E2EQ-X10□30




PREMIUM Model

DC 3-wire Spatter-resistant Triple distance model


Size: M8 E2EQ-X3□8




Size: M12 E2EQ-X6□12



Size: M18 E2EQ-X12□18




Size: M30 E2EQ-X22□30



I/O Circuit Diagrams/Timing charts

DC 2-wire Models



DC 3-wire

PNP output

		Output circuit				
Operation mode	Model	Standard I/O mode (SIO mode) When using as a general	IO-Link Communication mode (COM mode) When using the Sensor connected to IO-Link Master Unit *			
NO	E2EQ-□B1	DC10 to 30V Brown (1) +V Proximity sensor main circuit Load Blue (3) 0V	Brown (1) L+ (1) Proximity sensor main circuit Black (4) C/Q (4) IO-Link master			
NC	E2EQ-□B2	Proximity Sensor (1) Black (2) OUT Condition (2) Note: M8 (3-pin) Connector: (1)(4)(3)				
NO+NC	E2EQ-□B3	Proximity Sensor Circuit White (3) OUT2 Load Blue (3) OV	DC10 to 30V Brown (1) L+ (1) Black (4) C/Q (4) White (3) OUT2 DI (2) Blue (3) L- (3)			


^{*} In the IO-Link mode, the cord between the IO-Link master and sensor must have a length of 20 m or less.

Connector Pin Arrangement

M12 Connector M12 Smartclick Connector	M8 (4-pin) Connector	M8 (3-pin) Connector
(2) (4) (2) (3)	(2)(4) (1) (3)	(1 ⁴ 3)

DC 3-wire

PNP output



Please contact your OMRON sales representative regarding assignment of data.

*1. For models with IO-Link, the operation mode can be changed by the IO-Link communications.

*2. If using a model with IO-Link as a general sensor or using a model without IO-Link, it operates in the standard I/O mode (SIO mode).


DC 3-wire

NPN output

Operation mode	Model	Output circuit
NO	E2E(Q)-□C1	DC10 to 30V Brown (1) +V Load Proximity sensor main circuit Black (4) OUT Black (3) OV
NC	E2E(Q)-□C2	DC10 to 30V Brown (1) +V Load Proximity sensor main circuit Black (2) Note: M8 (3-pin) Connector: (1)(4)(3)
NO+NC	E2E(Q)-□C3	Brown (1) DC10 to 30V +V Load Load ULoad U

Connector Pin Arrangement

M12 Connector M12 Smartclick Connector	M8 (4-pin) Connector	M8 (3-pin) Connector
(2) (4) (3)		(1 ⁽⁴⁾ (3)




Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

∆WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols



⚠ WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Otherwise, explosion may result. Never use the product with an AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- Do not use the product in environments subject to flammable or explosive gases.
- 2. Do not attempt to disassemble, repair, or modify the product.
- 3. Do not use a voltage that exceeds the rated operating voltage range
 - Applying a voltage that is higher than the operating voltage range may result in explosion or fire.
- Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or fire.
- If the power supply is connected directly without a load, the internal elements may explode or burn.
- 6. Be sure to insert a load when connecting the power supply.

Precautions for Correct Use


Do not use the product in any atmosphere or environment that exceeds the ratings.

Operating Environment

- 1. Do not install the Sensor in the following locations.
 - (1) Outdoor locations directly subject to sunlight, rain, snow, waterdroplets, or oil.
 - (2) Locations subject to atmospheres with chemical vapors, inparticular solvents and acids.
 - (3) Locations subject to corrosive gases.
- 2. The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com) for typical measures.
- Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- 5. The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ratio recommended by its manufacturer
 - · Usage in oil or water is prohibited
 - Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.
- **6.** When turning on the power by influence of temperature environment, an outputmis-pulse sometimes occurs. After the sensor has passed for 300 msec after turning on, please use in the stable state. (DC 3-wire only.)
- The sensor is adjusted with a high degree of accuracy, so do not use in the environment with sudden temperature change. (DC 3wire only.)
- Operation check is performed using an OMRON's IO-Link master. If using an IO-Link master from another company, perform the operation check in advance. (Models with IO-Link only.)
- In the IO-Link mode, the cord between the IO-Link master and sensor must have a length of 20 m or less. (Models with IO-Link only.)


AND Connection of Proximity Sensors (DC 2-wire)

Two or more sensors cannot be connected in series on the AND circuit. Use them via a relay as shown on the figure.



OR Wiring of Proximity Sensors (DC 2-wire)

As a general principle, two or more sensors cannot be used in parallel on the OR circuit. It is possible only when sensors do not operate simultaneously and loads do not need to be maintained. When loads need to be maintained, use the sensors via a relay as shown on the figure.




Design

Influence of Surrounding Metal

When mounting the Proximity Sensor using a nut, only use the provided nut. And ensure that the minimum distances given in the following table are maintained.


When mounting the Proximity Sensor using a nut, only use the provided nut. Nuts that are supplied along with each Sensor are different. Refer to Dimensions for details on shapes.



(Unit: mm)

Туре	Model	L	d	D	m	n
DC 2-wire	E2EQ-X3D□8	0	20	2	9	18
Spatter-resistant	E2EQ-X7D□12	0	20	4	18	20
Triple distance	E2EQ-X11D□18	0	50	4	33	54
model	E2EQ-X20D□30	0	70	8	60	90
DC 3-wire	E2EQ-X3□8	0	20	0	9	18
Spatter-resistant	E2EQ-X6□12	0	20	0	18	20
Triple distance	E2EQ-X12□18	0	50	0	36	54
model	E2EQ-X22□30	0	70	0	66	90
DC 2-wire/DC 3-wire	E2EQ-X2□8	0	8	0	4.5	12
Spatter-resistant	E2EQ-X4□12	0	18	0	12	18
Double distance	E2EQ-X8□18	0	27	0	24	27
model	E2EQ-X15□30	0	45	0	45	45
DC 3-wire	E2EQ-X1R5□8	0	8	0	4.5	12
Spatter-resistant	E2EQ-X2□12	0	12	0	8	18
Single distance	E2EQ-X5□18	0	18	0	20	27
model	E2EQ-X10□30	0	30	0	40	45

When the Proximity Sensor is mounted in metal, ensure that the minimum distances given in the following table are maintained.




(Unit: mm)

					`	,
Models	Model	ı	d	D	m	n
DC 2-wire	E2EQ-X3D□8	2	20	2	9	18
Spatter-resistant	E2EQ-X7D□12	4	20	4	18	20
Triple distance	E2EQ-X11D□18	4	50	4	33	54
model	E2EQ-X20D□30	8	70	8	60	90
DC 3-wire	E2EQ-X3□8	2	20	2	9	18
Spatter-resistant	E2EQ-X6□12	4	20	4	18	20
Triple distance model	E2EQ-X12□18	4	50	4	36	54
model	E2EQ-X22□30	8	70	8	66	90
DC 2-wire/DC 3-wire	E2EQ-X2□8	0	8	0	4.5	12
Spatter-resistant	E2EQ-X4□12	2.4	18	2.4	12	18
Double distance	E2EQ-X8□18	3.6	27	3.6	24	27
model	E2EQ-X15□30	6	45	6	45	45
DC 3-wire	E2EQ-X1R5□8	0	8	0	4.5	12
Spatter-resistant	E2EQ-X2□12	0	12	0	8	18
Single distance model	E2EQ-X5□18	0	18	0	20	27
model	E2EQ-X10□30	0	30	0	40	45

Mutual Interference

When installing two or more Proximity Sensors face-to-face or sideby-side, ensure that the minimum distances given in the following table are maintained.




(Unit: mm)

Models	Model	Ite	em
Widueis	Wiodei	Α	В
	E2EQ-X3D□8	25	20
DC 2-wire	E2EQ-X7D□12	40	30
Spatter-resistant Triple distance model	E2EQ-X11D□18	70	45
	E2EQ-X20D□30	140	70
	E2EQ-X3□8	25	20
DC 3-wire	E2EQ-X6□12	40	30
Spatter-resistant Triple distance model	E2EQ-X12□18	70	45
·	E2EQ-X22□30	150	90
	E2EQ-X2□8	20	15
DC 2-wire/DC 3-wire	E2EQ-X4□12	30	20
Spatter-resistant Double distance model	E2EQ-X8□18	60	35
	E2EQ-X15□30	110	90
	E2EQ-X1R5□8	20	15
DC 3-wire	E2EQ-X2□12	30	20
Spatter-resistant Single distance model	E2EQ-X5□18	50	35
5	E2EQ-X10□30	100	70

Mounting

Tightening Force

Do not tighten the nut with excessive force. A washer must be used with the nut.



Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table. (A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)

2. The following strengths assume washers are being used.

DC 2-wire/DC 3-wire Spatter-resistant Triple distance model

•	•		
Size	Pai	Part B	
Size	Dimension (mm)	Torque	Torque
M8	9	4 N·m	10 N·m
M12	16	8 N·m	15 N·m
M18	16	15 N·m	30 N·m
M30	23	40 N·m	80 N·m

DC 2-wire/DC 3-wire Spatter-resistant Double distance model, Spatter-resistant Single distance model

Size	Par	Part B			
Size	Dimension (mm)	Torque	Torque		
M8	9	9 N·m	12 N·m		
M12		30 N·m			
M18		70 N·m			
M30		100 N·m			

Tolerance class IT16 applies to dimensions in this data sheet unless otherwise specified

Sensors

BASIC Model

E2EQ NEXT Series (Spatter-resistant, Double distance/Single distance model) DC 2-wire/DC 3-wire


Pre-wired Model/Pre-wired Connector Model





Connector Models (M12 Connector, M8 (4-pin) Connector and M8 (3-pin) Connector)





Indicators

DC 2-wire D1 Models:

Operation indicator (orange), Setting indicator (green)

D2 Models:

Operation indicator (orange) DC 3-wire

Standard I/O mode (SIO mode): Operation indicator (orange/ON),

Comunication indicator (green/OFF) IO-Link Communication mode

(COM mode): Operation indicator (orange/ON), Comunication indicator (green/Flashing (1sec cycle))

Pre-wired Models







Operation mode, Output configuration (D1: NO, D2: NC)

Vinyl-insulated round cable with 2 conductors

M8. M12 size: 4-dia.

(Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm),

M18, M30 size: 6-dia.

(Conductor cross section: 0.5 mm² (AWG20), Insulator diameter: 1.5 mm), Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Operation mode, Output configuration (B1/C1: NO, B2/C2: NC)

Vinyl-insulated round cable with 3 conductors M8, M12 size: 4-dia.

M18, M30 size: 6-dia

(Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.5 mm), Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Operation mode, Output configuration (B3/C3: NO+NC Type)


Vinvl-insulated round cable with 4 conductors

M8, M12 size: 4.3-dia

M18. M30 size: 6-dia.

(Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.5 mm) Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Model	Α	В	С	D	F	Н	I	J
E2EQ-X□8	M8XP1	37.8	4.4	26	8	3	15	13
E2EQ-X□12	M12XP1	47.1	3.7	33	10	4	21	17
E2EQ-X□18	M18XP1	55.3	8.5	38	10	4	29	24
E2EQ-X□30	M30XP1.5	60.3	8.3	43	10	5	42	36



Model	Α	В	С	D	F	Н	ı	J
E2EQ-X□8-M3/M5	M8XP1	39	M8XP1	26	8	3	15	13
E2EQ-X□8-M1	M8XP1	43	M12XP1	26	8	3	15	13
E2EQ-X□12-M1	M12XP1	48	M12XP1	33	10	4	21	17
E2EQ-X□18-M1	M18XP1	53	M12XP1	38	10	4	29	24
E2EQ-X□30-M1	M30XP1.5	58	M12XP1	43	10	5	42	36

Mounting Hole Dimensions



Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Angle R of the **Bending Wire**



Dimensions	R (mm)	
M8	12	
M12	12	
M18	18	
M30	10	

Wire pullout position



Dimensions	Sc (mm)
M8	(0)
M12	- (0)
M18	2.5
M30	2.5

PREMIUM Model

E2EQ NEXT Series (Spatter-resistant, Triple distance model)

DC 2-wire/DC 3-wire

Pre-wired Model/Pre-wired Connector Model






Connector Models (M12 Connector, M8 (4-pin) Connector and M8 (3-pin) Connector)



Note: DC 3-wire only



Indicators DC 2-wire D1 Models:

Operation indicator (orange), Setting indicator (green) D2 Models:

Operation indicator (orange)

DC 3-wire Standard I/O mode (SIO mode): Operation indicator (orange/ON), Comunication indicator (green/OFF)

(GOM mode):
Operation indicator (orange/ON),
Comunication indicator (green/Flashing (1sec cycle))

Two clamping nuts

Indicators

Standard I/O mode (SIO mode): Operation indicator (orange/ON), Comunication indicator (green/OFF)

IO-Link Communication mode (COM mode):

Operation indicator (orange/ON), Comunication indicator (green/Flashing (1sec cycle))

Model E2EQ-X□8-M1; Shape of connection.

Model	Α	В	С	D	Е	F	Н	ı	J
E2EQ-X□8-M3/M5	M8XP1	39	M8XP1	26	1	10	4	15	13
E2EQ-X□8-M1	M8XP1	43	M12XP1	26	1	10	4	15	13
E2EQ-X□12-M1	M12XP1	48	M12XP1	33	1	12	5.5	21	17
E2EQ-X□18-M1	M18XP1	53	M12XP1	38	1	12	6	29	24
E2EQ-X□30-M1	M30XP1.5	58	M12XP1	43	1	12	7	42	36

Pre-wired Models

Pre-wired Connector Models (M1TJ/M1TGJ) M12×P1



Operation mode,Output configuration (D1: NO, D2: NC)

Vinyl-insulated round cable with 2 conductors

(Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm), M18, M30 size: 6-dia.

(Conductor cross section: 0.5 mm² (AWG20), Insulator diameter: 1.5 mm), Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Operation mode, Output configuration (B1/C1: NO, B2/C2: NC)

Vinyl-insulated round cable with 3 conductors M8, M12 size: 4-dia.

M18, M30 size: 6-dia.

(Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.5 mm), Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Operation mode, Output configuration (B3/C3: NO+NC Type)

Vinyl-insulated round cable with 4 conductors

M8, M12 size: 4.3-dia. M18. M30 size: 6-dia.

(Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.5 mm), Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Model	Α	В	С	D	Е	F	Н	-	J
E2EQ-X□□8	M8XP1	37.8	4.4	26	1	10 (8 *)	4	15	13
E2EQ-X□□12	M12XP1	47.1	3.7	33	1	12 (10*)	5.5	21	17
E2EQ-X□□18	M18XP1	55.3	8.5	38	1	12	6	29	24
E2EQ-X□□30	M30XP1.5	60.3	8.3	43	1	12	7	42	36

^{*} If using the E2EQ-X\(\subseteq\text{D}\subseteq\text{8, E2EQ-X\(\subseteq\text{D}\subseteq\text{12, refer to () dimensions.}}

Mounting Hole Dimensions



Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Angle R of the **Bending Wire**



Dimensions	R (mm)	
M8	12	
M12	12	
M18	18	
M30	10	

Wire pullout position



Dimensions	Sc (mm)	
M8	(0)	
M12	- (0)	
M18	2.5	
M30	2.5	

Spatter-resistant Proximity Sensor

E2EQ

Spatter-resistant Fluororesin-coated Proximity Sensor

- Superior spatter resistance.
- Pre-wired Smartclick Connector Models are also available.



Be sure to read *Safety Precautions* on page 63.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensors [Refer to Dimensions on page 64.]

Pre-wired Models

Appeara	nce	Sensing distance	Output configuration	Operation mode	Model
	M12	3 mm			E2EQ-X3D1 2M
Shielded	M18	7 mm	DC 2-wire	NO	E2EQ-X7D1 2M
	M30	10 mm			E2EQ-X10D1 2M

Pre-wired Smartclick Connector Models (M12)

Appeara	ınce	Sensing dist	ance	Output configuration	Operation mode	Model
Shielded	M12	3 mm		DC 2-wire		E2EQ-X3D1-M1TGJ 0.3M
	M18	7 mm		(1)-(4) pin arrangement	NO	E2EQ-X7D1-M1TGJ 0.3M
	M30	10 mm				E2EQ-X10D1-M1TGJ 0.3M

Pre-wired Connector Models (M12)

Appeara	nce	Sensing distance	Output configuration	Operation mode	Model
	M12	3 mm	DC 2-wire		E2EQ-X3D1-M1GJ 0.3M
Shielded	M18	7 mm	(1)-(4)	NO	E2EQ-X7D1-M1GJ 0.3M
	M30	10 mm	pin arrangement		E2EQ-X10D1-M1GJ 0.3M

Sensor I/O Connectors (Sold Separately)

For details of the connector, refer to XS5 Series on page 66.

Ratings and Specifications

Item	Model	E2EQ-X3D1 E2EQ-X3D1-M1(T)GJ	E2EQ-X7D1 E2EQ-X7D1-M1(T)GJ	E2EQ-X10D1 E2EQ-X10D1-M1(T)GJ		
Sensing distance		3 mm ±10%	7 mm ±10%	10 mm ±10%		
Set distance		0 to 2.4 mm	0 to 5.6 mm	0 to 8 mm		
Differential trav	/el	10% max. of sensing distance				
Standard sensi		Iron, 12 × 12 × 1 mm				
Response frequency *1		1 kHz	500 Hz	400 Hz		
Control	Load current	3 to 100 mA				
output	Residual voltage	3 V max. (Load current: 100 mA, Cable	lenath: 2 m)			
Operation mod	e (with sensing object	Load ON: NO; For details, refer to the ti	<u> </u>			
Protection circ	uits	Load short-circuit protection, Surge sup	pressor			
Ambient tempe	erature range	Operating/Storage: -25 to 70°C (with no	cicing or condensation)			
Temperature in	fluence	±10% max. of sensing distance at 23°C	in the temperature range of -25 to 70°C			
Voltage influen	ice	±2.5% max. of sensing distance at rated voltage in the rated voltage ±15% range				
Shock resistan	се	Destruction: 1,000 m/s² 10 times each in X, Y, and Z directions				
Connection method		E2EQ-X□D1: Pre-wired Models (Standard cable length: 2 m) E2EQ-X□D1-M1GJ: Pre-wired Connector Models (Standard cable length: 300mm)				
NA/-:	Pre-wired Models	Approx. 120 g	Approx. 160 g	Approx. 220 g		
Weight (packed state)	Pre-wired Connector Models	Approx. 80 g	Approx. 110 g	Approx. 190 g		
Detectable object		Ferrous metal (The sensing distance decreases with non-ferrous metal. Refer to Engineering Data on page 62.)				
Power supply voltage	•	12 to 24 VDC (10 to 30 VDC), ripple (p-p): 10% max.				
Leakage currer	nt	0.8 mA max.				
Indicators		Operation indicator (red), Setting indicator (green)				
Ambient humic	lity range	Operating/Storage: 35% to 95% (with no condensation)				
Insulation resis	stance	50 MΩ min. (at 500 VDC) between current-carrying parts and case				
Dielectric stren	igth	1,000 VAC for 1 min between current-carrying parts and case				
Vibration resis	tance	Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions				
Degree of protection		IEC 60529 IP67, in-house standards: oil-resistant				
	Case	Fluororesin coating (Base material: brass)				
Matariala	Sensing surface	Fluororesin				
Materials	Clamping nuts	Fluororesin coating (Base material: brass)				
	Toothed washer	Zinc-plated iron				
Accessories		Instruction manual				


^{*1.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

E2EQ

Engineering Data (Reference Value)


Sensing Area

$E2EQ-X\Box D\Box (-M1(T)GJ)$




Influence of Sensing Object Size and Material


E2EQ-X3D1(-M1(T)GJ)



E2EQ-X7D1(-M1(T)GJ)




E2EQ-X10D1(-M1(T)GJ)




Residual Output Voltage

E2EQ-X \square D \square (-M1(T)GJ)




Leakage Current

E2EQ-X□D



I/O Circuit Diagrams



Safety Precautions

Refer to Warranty and Limitations of Liability.

MARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.




Precautions for Correct Use

Do not use this product under ambient conditions that exceed the ratings.

Design

Influence of Surrounding Metal

When mounting the Sensor within a metal panel, ensure that the clearances given in the following table are maintained. Failure to maintain these distances may cause deterioration in the performance of the Sensor.



Influence of Surrounding Metal (Unit: mm)


	•		`	,		
Model	Item	1	d	D	m	n
E2EQ-X3D1(-M1(T)GJ)			12		8	18
E2EQ-X7D1(-M1(T)GJ)		0	18	0	20	27
E2EQ-X10D1(-M1(T)GJ)		ř	30		40	45

Mutual Interference

When installing two or more Sensors face-to-face or side-by-side, ensure that the minimum distances given in the following table are maintained.

Mutual Interference (Unit: mm)

Model Item	Α	В
E2EQ-X3D1(-M1(T)GJ)	30	20
E2EQ-X7D1(-M1(T)GJ)	50	35
E2EQ-X10D1(-M1(T)GJ)	100	70



Mounting

Do not tighten the nut with excessive force. A washer must be used with the nut.





- Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table. (A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)
 - The following torque assume washers are being used.


Torque	Part A	1	Part B
Model	Dimension (mm)	Torque	Torque
E2EQ-X3D1(-M1(T)GJ)	24	15 N·m	
E2EQ-X7D1(-M1(T)GJ)	29	19 19 111	
E2EQ-X10D1(-M1(T)GJ)	26	39 N·m	78 N·m

Pre-wired Models



E2EQ-X3D1






- *1. 6-dia. vinyl-insulated round cable with 2 conductors (Flame-resistant, Conductor cross section: 0.5 mm², Insulator diameter: 1.9 mm), Standard length: 2 m

 The cable can be extended up to 200 m (separate metal conduit).
 *2. Operation indicator (red), Setting indicator (green)


E2EQ-X7D1





- *1. 6-dia. vinyl-insulated round cable with 2 conductors (Flame-resistant, Conductor cross section: 0.5 mm², Insulator diameter: 1.9 mm), Standard length: 2 m The cable can be extended up to 200 m (separate metal conduit).
 *2. Operation indicator (red), Setting indicator (green)

E2EQ-X10D1




- *1. 6-dia. vinyl-insulated round cable with 2 conductors (Flame-resistant, Conductor cross section: 0.5 mm², Insulator diameter: 1.9 mm), Standard length: 2 m
 The cable can be extended up to 200 m (separate metal conduit).
 *2. Operation indicator (red), Setting indicator (green)

Pre-wired Connector Models




E2EQ-X3D1-M1(T)GJ




*1. 6-dia. vinyl-insulated round cable (flame-resistant), Standard length: 300 mm *2. Operation indicator (red), Setting indicator (green)

E2EQ-X7D1-M1(T)GJ



- *1. 6-dia. vinyl-insulated round cable (flame-resistant), Standard length: 300 mm *2. Operation indicator (red), Setting indicator (green)

E2EQ-X10D1-M1(T)GJ



- *1. 6-dia. vinyl-insulated round cable (flame-resistant), Standard length: 300 mm *2. Operation indicator (red), Setting indicator (green)

Mounting Hole Dimensions



Model E2EQ-X4X□ E2EQ-X3□		E2EQ-X8X E2EQ-X7	E2EQ-X15X E2EQ-X10
F (mm)	12.5 ₀ ^{+0.5} dia.	18.5 ₀ ^{+0.5} dia.	30.5 ₀ ^{+0.5} dia.

Round Water-resistant Connectors (M12 Smartclick)

XS5

Round Water-resistive Smartclick Connectors that Reduce Installation Work

- A newly developed lock mechanism that is compatible with round M12 connectors.
- Simply insert the Connectors, then turn them approximately 1/8 of a turn to lock.
- · A positive click indicates locking.
- Spatter-resistant Cables are also available.
- IP67 degree of protection.
- · UL approved products.

Note: For details, refer to XS5 on your OMRON website.





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensor I/O Connectors

A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Appearance	Cable Specification	Туре	Cable diameter (mm)	Cable Connection Direction	Cable length (m)	Sensor I/O Connector model number	Applicable Proximity Sensor model number
				Straight	1	XS5F-D421-C80-F	
					2	XS5F-D421-D80-F	
					3	XS5F-D421-E80-F	
					5	XS5F-D421-G80-F	
		Sockets on	6 dia.		10	XS5F-D421-J80-F	7
		One Cable End	o dia.		1	XS5F-D422-C80-F	7
M12 Smartclick Connector					2	XS5F-D422-D80-F	
Smartclick Connector				Right-angle	3	XS5F-D422-E80-F	
Straight type					5	XS5F-D422-G80-F	
	PVC robot cable				10	XS5F-D422-J80-F	
		Socket and Plug on Cable Ends	6 dia.	Straight (Socket)/ Straight (Plug)	1	XS5W-D421-C81-F	1
A F II					2	XS5W-D421-D81-F	E2EW, E2EQ NEXT,
					3	XS5W-D421-E81-F	E2EQ (M12 Pre-wired Smartclick Connector, M12 Connector)
					5	XS5W-D421-G81-F	
Right-angle type					10	XS5W-D421-J81-F	
ragin-angle type				Right-angle (Socket)/ Right-angle (Plug)	2	XS5W-D422-D81-F	
107					5	XS5W-D422-G81-F	
Mile II				Straight (Socket)/ Right-angle (Plug)	2	XS5W-D423-D81-F	
0					5	XS5W-D423-G81-F	
				Right-angle (Socket)/ Straight (Plug)	2	XS5W-D424-D81-F	
					5	XS5W-D424-G81-F	
	Spatter-resistant	Sockets on One Cable End	6.6 dia.	Straight	2	XS5F-D421-D80-SA	
					5	XS5F-D421-G80-SA	
	Cable	Socket and Plug		Straight (Socket)/ Straight (Plug)	2	XS5W-D421-D81-SA	
		on Cable Ends			5	XS5W-D421-G81-SA	

Connections for Sensor I/O Connectors

DC 2-Wire


Proximity Sensor			nsor	Sensor I/O Connectors		
Туре	Polarity Operation mode		Model	Model	Connections *1	
	Yes	NO	E2EW-(Q)X□D1□-M1TGJ E2EQ-X□D1□-M1TGJ	XS5F-D42□-□80-F XS5F-D421-□80-SA	Proximity Sensor State of the sensor of the	
DC 2-Wire (Smartclick		NC	E2EQ-X□D2□-M1TGJ		Proximity Sensor Sens	
Connector)	No	NO	E2EW-(Q)X□D1□-M1TGJ-T E2EQ-X□D1□-M1TGJ-T	XS5W-D42□-□81-F XS5W-D421-□81-SA	Proximity Sensor State of the sensor of the	
		NC	E2EQ-X□D2□-M1TGJ-T			Proximity Sensor XS5 Brown (+) (-) White (-) (+) Blue (not connected) Black (not connected)

	F	roximity Se	nsor	Sensor I/O Connectors			
Types	Output	Operation mode	Model	Model	Connections *1		
	PNP	NO	E2EW-(Q)X□B1□-M1TJ/M1 E2EQ-X□B1□-M1TJ/M1	XS5F-D42□-□80-F XS5F-D421-□80-SA XS5W-D42□-□81-F XS5W-D421-□81-SA	Proximity Sensor XS5 O Brown (+) O White (not connected) O Blue (-) O Black (Output)		
		NC	E2EW-(Q)X□B2□-M1TJ/M1 E2EQ-X□B2□-M1TJ/M1		Proximity Sensor XS5 Brown (+) O White (Output) Blue (-) Black (not connected)		
DC 3-Wire (M12 Connector /		NO+NC	E2EW-(Q)X□B3□-M1TJ/M1 E2EQ-X□B3□-M1TJ/M1		Proximity Sensor XS5 The sensor Sens		
M12 Smartclick Connector)		NO	E2EW-(Q)X□C1□-M1TJ/M1 E2EQ-X□C1□-M1TJ/M1		Proximity Sensor XS5 O Brown (+) O White (not connected) O Blue (-) O Black (Output)		
		NC	E2EW-(Q)X□C2□-M1TJ/M1 E2EQ-X□C2□-M1TJ/M1		Proximity Sensor XS5 Brown (+) O White (Output) Blue (-) Black (not connected)		
		NO+NC	E2EW-(Q)X□C3□-M1TJ/M1 E2EQ-X□C3□-M1TJ/M1		Proximity Sensor XS5 O Brown (+) O White (Output 2) O Blue (-) O Black (Output 1)		


^{*1.} If the XS5W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug. **Note:** Different from Proximity Sensor wire colors.

Dimensions (Unit: mm)


Socket and Plug on Cable Ends XS5W Wiring Diagram for 4 Cores




Straight (Socket)/straight (Plug) XS5W-D421-□81-F/XS5W-D421-□81-SA




Right-angle (Socket)/right-angle (Plug) XS5W-D422-□81-F




Straight (Socket)/right-angle (Plug) XS5W-D423-□81-F




Right-angle (Socket)/straight (Plug) XS5W-D424-□81-F




Sockets on One Cable End XS5F Wiring Diagram for 4 Cores



Straight type XS5F-D421-□80-F/XS5F-D421-□80-SA



Right-angle type XS5F-D422-□80-F



Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Related Products

Proximity Sensors E2E NEXT Series

- Exceptional sensing range*1. Approximately double the sensing distance of previous models
- High-brightness LED indicator visible from 360°
- Only 10 seconds*2 to replace a proximity sensor with the e-jig (mounting sleeve)
- Sensor cable with enhanced oil resistance to withstand oil for 2 years*3
- *1. DC 2-wire, Triple distance models. Based on Omron investigation in October 2025.
- *2. Time required to adjust the distance when a sensor is installed. Based on Omron investigation.
- *3. Refer to Ratings and Specifications in the catalog for details.




Refer to the catalog for details.

Cat. No. D120

Oil-resistant Proximity Sensors E2ER/E2ERZ

- Reduces failures caused by ingress of cutting oil and resists oil for 4 years *1
- Four years*1 of stable operation verified in oil resistance testing with representative cutting oils
- Fluororesin blocks ingress from cables
- State-of-the-art sealing methods block ingress through cable joints
- *1. Years in actual usage environment in Omron's unique accelerated evaluation tests. Applicable oil type: specified in JIS K 2241:2000



Refer to the catalog for details.

Cat. No. Y215

Smartclick is a trademark or registered trademark of OMRON Corporation in Japan and other countries. Company names and product names in this document are the trademarks or registered trademarks of their respective companies. The product photographs and figures that are used in this catalog may vary somewhat from the actual products.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact: www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

Authorized Distributor:

©OMRON Corporation 2021-2025 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM 6 2

Cat. No. D125-E1-12 1025 (0921)