

Photomicrosensor Selection Guide

Select the best suited sensor from our extensive line up



Find your desired sensor


Omron's Photomicrosensor Line up


Compact, simple photoelectric sensors with built-in amplifier for Positioning and workpiece detection.

Our broad product portfolio includes sensors for special applications as well as through-beam
(slot-type) and reflective sensors.

We offer connector and pre-wired models, supporting manufacturing.

Positioning Detection





Workpiece Detection

Special Application

Broad Slot-type Ambient Light-resistant Models

Reflective Models

Diffuse-reflective Models



Light Convergent







Pipe-mounting liquid level photomicrosensor.



Accurately detecting without being affected

Light modulation to reduce ambient light interference. 13 mm slot width and high noise immunity.

> Sensing distance 2 to 5 mm

Less affected by

background.

Sensing distance 5 mm


EE-SPY30/40


P.22

Light modulation to

reduce ambient light

interference.









Pre-wired Models

EE-SPX613

EE-SPX303N/EE-SPX403N

P.18



EE-SPY31/41

P.20



Pipe diameter 6 dim. to 13 mm



P.24



Pushbutton type

EE-SA701/801

P.26

EE-SX47/67

Global Standard Slot-type photomicrosensors with 50- to 100-mA direct switching capacity.

- Series includes models that enable switching between dark-ON and light-ON operation.
- Response frequency as high as 1 kHz.
- Easy operation monitoring with bright light indicator.
- Wide operating voltage range: 5 to 24 VDC
- Models in which the light indicator turns ON for dark-ON operation are also available.
- A wide range of variations in eight different shapes.
- Flexible robot cable is provided as a standard feature. *2
- *1. Pre-wired Models are available only in the EE-SX67 Series.
- *2. Only for Pre-wired Models.



Be sure to read Safety Precautions for All Photomicrosensors on page 30.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Connector Infrared light

Appearance	Sensing	Connect-	Sensing	distance	Output	Indicator mode	Mo	
Appearance	method	ing method	Sensing	uistance	configuration	maicator mode	NPN output	PNP output
Standard					Dark-ON/Light-ON	Incident light	EE-SX670	EE-SX670P
22.2					(selectable) *3 *4	No incident light	EE-SX670A	EE-SX670R
25.4					Light-ON	Incident light	EE-SX470	
L-shaped					Dark-ON/Light-ON	Incident light	EE-SX671	EE-SX671P
15.5					(selectable) *3 *4	No incident light	EE-SX671A	EE-SX671R
26.2					Light-ON	Incident light	EE-SX471	
T-shaped, slot center 7 mm					Dark-ON/Light-ON	Incident light	EE-SX672	EE-SX672P
22.2					(selectable) *3 *4	No incident light	EE-SX672A	EE-SX672R
13.4 010 26					Light-ON	Incident light	EE-SX472	
Close-mounting					Dark-ON/Light-ON	Incident light	EE-SX673	EE-SX673P
22.2			5 mm (slot width	(selectable) *3 *4	No incident light	EE-SX673A	EE-SX673R	
13.4	Through- beam	Connector (4 poles)		5 mm (slot width)	Light-ON	Incident light	EE-SX473	
Close-mounting	(slot-type)				Dark-ON/Light-ON (selectable) *3 *4	Incident light	EE-SX674	EE-SX674P
15.5						No incident light	EE-SX674A	EE-SX674R
13.6					Light-ON	Incident light	EE-SX474	
T-shaped, slot center 10 mm					Dark-ON/Light-ON (selectable) *3 *4	Incident light	EE-SX675	EE-SX675P
F-shaped 13.4 1222 13.2					Dark-ON/Light-ON (selectable) *3 *4	Incident light	EE-SX676	EE-SX676P
R-shaped 13.4					Dark-ON/Light-ON (selectable) *3 *4	Incident light	EE-SX677	EE-SX677P

 ^{*3.} Dark-ON when the L terminal of the connector is opened, and light-ON when the L terminal and positive (+) terminal are connected. Do not connect the L terminal to 0 V when using dark-ON operation. When using light-ON, it is useful to select the connector EE-1001-1. The L terminal and positive (+) terminal of this connector are connected in advance.
 *4. If you do not use the L terminal wire ((2) pink) when you use a Connector with Cable for an EE-1006 or EE-1010-series Photomicrosensor, noise may affect the Photomicrosensor. To prevent the effects of noise, cut the unused L terminal wire at the base of the connector and wrap it with insulating tape to prevent it from coming in contact with other terminals.

Pre-wired Models Infrared light

	Sensing			Output	Indicator	Connecting	Мо	del
Appearance	method	Sensing	distance	configura- tion	mode	method	NPN output	PNP output
Standard 6.35							EE-SX670-WR 1M	EE-SX670P-WR 1M
L-shaped 26.2							EE-GY671-WD 1M	EE-SX671P-WR 1M
T-shaped, slot center 7 mm							EE-SX672-WR 1M	EE-SX672P-WR 1M
Close-mounting	Through- beam	beam (slot-type) 5 mm Li (slot-type) (slot-type) 5 mm	5 mm		Incident	Pre-wired	EE-SX673-WR 1M	EE-SX673P-WR 1M
Close-mounting			(selectable) I *1	light	Models (1m)	EE-SX674-WR 1M	EE-SX674P-WR 1M	
T-shaped, slot center 10 mm							EE-SX675-WR 1M	EE-SX675P-WR 1M
F-shaped 13.2 26.2						EE-SX676-WR 1M	EE-SX676P-WR 1M	
R-shaped							EE-SX677-WR 1M	EE-SX677P-WR 1M

^{*1.} Dark-ON operation can be used when the L terminal is left unconnected or Light-ON operation can be used when the L terminal and positive (+) terminal are connected to each other. Do not connect the L terminal to 0 V when using dark-ON operation.

Accessories (Order Separately) Connector Models

	Туре	Cable length	Model				
Connector			EE-1001				
			EE-1001-1				
		EE-1009					
		1 m	EE-1006 1M				
	Connector with Cable	' ' '	EE-1010 1M				
	Connector with Cable	2 m	EE-1006 2M				
		2111	EE-1010 2M				
	Connector with Robot	1 m	EE-1010-R 1M				
	Cable	2 m	EE-1010-R 2M				
Connector I	Hold-down Clip		EE-1006A				

Note: 1. If you do not use the L terminal wire ((2) pink) when you use a Connector with Cable for an EE-1006 or EE-1010-series Photomicrosensor, noise may affect the Photomicrosensor. To prevent the effects of noise, cut the unused L terminal wire at the base of the connector and wrap it with insulating tape to prevent it from coming in contact with other terminals.


2. For details, refer to the *Accessories (Order Separately)* on page 28.

EE-SX47/67

Ratings and Specifications

		Туре	Standard	L-shaped	T-shaped, slot center 7 mm	Close-m	nounting	T-shaped, slot center 10 mm	F-shaped	R-shaped
ì	NPN models	Connector models	EE-SX670 EE-SX670A EE-SX470	EE-SX671 EE-SX671A EE-SX471	EE-SX672 EE-SX672A EE-SX472	EE-SX673 EE-SX673A EE-SX473	EE-SX674 EE-SX674A EE-SX474	EE-SX675	EE-SX676	EE-SX677
	illodeis	Pre-wired models	EE-SX670- WR	EE-SX671- WR	EE-SX672- WR	EE-SX673- WR	EE-SX674- WR	EE-SX675- WR	EE-SX676- WR	EE-SX677- WR
	PNP	Connector models	EE-SX670P EE-SX670R	EE-SX671P EE-SX671R	EE-SX672P EE-SX672R	EE-SX673P EE-SX673R	EE-SX674P EE-SX674R	EE-SX675P	EE-SX676P	EE-SX677P
Item	models	Pre-wired models	EE-SX670P- WR	EE-SX671P- WR	EE-SX672P- WR	EE-SX673P- WR	EE-SX674P- WR	EE-SX675P- WR	EE-SX676P- WR	EE-SX677P- WR
Sensi	ng distan	ce	5 mm (slot widtl	h)						
Sensi	ng object		Opaque: 2 × 0.8	3 mm min.						
Differe	ential dist	ance	0.025 mm							
	source			th a peak wavele	0					
Indica	tor *1		Light indicator (red) (turns ON w	hen light is interr	upted for models	with A or R suffi	x)		
Supply voltage 5 to 24 VDC ±10%, ripple (p-p): 10% max.										
Curre	nt consun	nption	12 mA max.	ector: 5 to 24 VD0						
Contro	ol output		100 mA load current with a residual voltage of 0.8 V max. 40 mA load current with a residual voltage of 0.4 V max. OFF current (leakage current): 0.5 mA max. PNP open collector: 5 to 24 VDC, 50 mA max. 50 mA load current with a residual voltage of 1.3 V max. OFF current (leakage current): 0.5 mA max.							
Protec	ction circu	uits	Load short circuit protection							
Respo	nse frequ	iency *2	1 kHz min. (3 kHz average)							
Ambie	ent illumin	ation	,		ght on the surface					
		rature range			je: -30 to +80°C	, ,				
Ambie	ent humid	ity range			5% to 95% (with		ensation)			
Vibrat	ion resist	ance	1.5-mm double	amplitude for 2 h	ak acceleration: 1 n (4-min periods)	each in X, Y, and	d Z directions			
	resistan				s each in X, Y, ar	nd Z directions				
Degre	e of prote	ction	IEC60529 IP50							
Connecting method Connector Models (direct soldering possible) Models with Connectors (Standard cable length							Standard cable le	ength: 1 m),		
Wei-		or models	Approx. 3.1 g	Approx. 3 g	Approx. 2.4 g	Approx. 2.3 g	Approx. 3 g	Approx. 2.7 g	Approx. 2.2 g	Approx. 2.2 g
ght	Pre-wire	d models	1	- 11	Approx. 17.8 g	Approx. 16.8 g	Approx. 17.1 g	Approx. 18.3 g	Approx. 16.9 g	Approx. 16.9 g
Ма-	Case		Polybutylene ph	nthalate (PBT)						
teri- al	Cover Fmitter/r	eceiver	Polycarbonate							

Note: For details, refer to *EE-SX47/SX67 Data sheet.**1. The indicator is a GaP red LED (peak wavelength: 690 nm).
*2. The response frequency was measured by detecting the rotating disk shown at the right.



MEMO

EE-SX97

Built-in connector enables downsizing and easier connection. Protective circuit for safe operation.

- A built-in connector minimizes the shape and dimensional requirements.
- Two outputs: light-ON and dark-ON.
- Complete lineup including seven different shapes.
- Safer operation with built-in power supply reverse polarity protection.
- Output overcurrent protection with a thermal shutdown circuit (patent pending). *1
- The indicator can be seen from many directions to enable installation in more locations.
- Connector with lock that mates with commercially available connectors. *2
- *1. Output overcurrent protection is provided only on output 2 (OUT2) on NPN models.
- *2. Recommended connector:
 - J.S.T. Mfg. Co., Ltd. Contacts: SPHD-001T-P0.5, Housing: PAP-04V-S Ask the manufacturer of the connector for details.



Be sure to read Safety Precautions for All Photomicrosensors on page 30.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensors Infrared light

Annogrange	Sensing	Connecting	Canaina diatana	Operating	Indicator	Model		
Appearance	method	method	Sensing distance	mode	mode	NPN output	PNP output	
Standard 22.0 26.0 7.0						EE-SX970-C1	EE-SX970P-C1	
L-shaped 26.2						EE-SX971-C1	EE-SX971P-C1	
T-shaped, slot center 7 mm	Through-	Connector	5 mm	Dark-ON/	Incident light	EE-SX972-C1	EE-SX972P-C1	
Close-mounting	- beam (slot-type)	model (4 poles)	(slot width)	Light-ON (2 outputs)		EE-SX974-C1	EE-SX974P-C1	
T-shaped, slot center 10 mm						EE-SX975-C1	EE-SX975P-C1	
F-shaped 13.4 22.0						EE-SX976-C1	EE-SX976P-C1	

Appearance	Sensing	Connecting	Sensing distance		Operating	Indicator	Model	
Арреагапсе	method	method	Sensing	uistarice	mode	mode	NPN output	PNP output
R-shaped 13.4 22.0	Through- beam (slot-type)	Connector model (4 poles)		5 mm (slot width)	Dark-ON/ Light-ON (2 outputs)	Incident light	EE-SX977-C1	EE-SX977P-C1

Accessories (Order Separately)


Туре	Cable length	Model
Connector with Cable	1 m	EE-1017 1M
Connector with Cable	3 m	EE-1017 3M
Connector with Robot Cable	1 m	EE-1017-R 1M
Connector with Robot Cable	3 m	EE-1017-R 3M

Note: For details, refer to the Accessories (Order Separately) on page 28.

Ratings and Specifications

	Туре	Standard	L-shaped	T-shaped, slot center 7 mm	Close-mount- ing	T-shaped, slot center 10 mm	F-shaped	R-shaped
	NPN	EE-SX970-C1	EE-SX971-C1	EE-SX972-C1	EE-SX974-C1	EE-SX975-C1	EE-SX976-C1	EE-SX977-C1
Item	PNP	EE-SX970P-C1	EE-SX971P-C1	EE-SX972P-C1	EE-SX974P-C1	EE-SX975P-C1	EE-SX976P-C1	EE-SX977P-C1
Sensing distance 5 mm (slot width)								
Sensing object		Opaque: 2 × 0.	8 mm min.					
Differential dista	ance	0.025 mm max	. *1					
Light source (Pellength)	eak wave-	Infrared LED w	rith a peak wave	elength of 940 n	m			
Indicator		Light indicator	(orange LED)					
Supply voltage		5 to 24 VDC ±	10%, ripple (p-p): 10% max.				
Current consum	nption	21 mA max.						
Control output Load power supply voltage: 5 to 24 VDC, Load current: 50 mA max., Off-state current: 0.5mA max 50 mA load current with a residual voltage of 1.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max., 5 mA load current with a residual voltage of 0.0 V max.						•		
Protection circu	iit			protection; outp UT2 on models				
Response frequ	iency	1 kHz min. (3 k	Hz average) *2	2				
Ambient illumin	ation	1,000 lx max. v	vith fluorescent	light on the surf	ace of the recei	ver		
Ambient temper range	rature	Operating: -25	to 55°C Storag	je: -30 to 80°C	(with no icing or	condensation)		
Ambient humidi	ity range	Operating: 5%	to 85% Storage	e: 5% to 95% (w	rith no icing or c	ondensation)		
Vibration resista struction)	ance (De-	10 to 2,000 Hz	0.75-mm single	e amplitude (15-	min periods, 10	cycles) each in	X, Y, and Z dire	ections
Shock resistand struction)	ce (De-	Destruction: 50	00 m/s ² for 3 tim	es each in X, Y	, and Z directior	ns		
Degree of protection IEC 60529 IP50								
Connecting method Connector								
Weight (Packed state) Approx. 3 g								
Mate- Case/Co	over	Polybutylene te	erephthalate (Pl	3T)				
rial Emitter/	receiver/	Polycarbonate	(PC)					

Note: For details, refer to *EE-SX97 Data sheet.**1. The differential distance is the value when a sensing object is moved in a lateral direction to the slot.
*2. The response frequency was measured by detecting the following rotating disk.





Ultra-compact Pre-wired Photomicrosensor (Non-modulated)

EE-SX95

Meeting Customer Needs with Ultra-compact Sensors that Mount with M3 Screws

- Mount using M3 or M2 screws.
- Reliable sensing slot depth of 6.5 mm.
- Indication of sensing window for easy confirmation of insertion depth.
- Bright indicator for confirmation from many directions.
- Both light-ON and dark-ON outputs provided.
- All models available with either standard cable or flexible robot cable.
- Load short-circuit protection circuit provided.



Be sure to read Safety Precautions for All Photomicrosensors on page page 30.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensors Infrared light

Appearance	Sensing method	Sensing distance	Output configuration	Connection method (Cable length)	Output type	Model	
Standard				Pre-wired model with	NPN	EE-SX950-W 1M	*1
				standard cable (1 m)	PNP	EE-SX950P-W 1M	*2
12 6				Pre-wired model with robot cable (1 m)	NPN	EE-SX950-R 1M	*1
23.9				Pre-wired connector model with robot cable (0.3 m)	NPN	EE-SX950-C1J-R 0.3	И
L-shaped				Pre-wired model with	NPN	EE-SX951-W 1M	*1
13.4				standard cable (1 m)	PNP	EE-SX951P-W 1M	*2
12 12				Pre-wired model with robot cable (1 m)	NPN	EE-SX951-R 1M	*1
				Pre-wired connector model with robot cable (0.3 m)	NPN	EE-SX951-C1J-R 0.3M	
F-shaped			Light-ON Dark-ON (2 outputs)	Pre-wired model with	NPN	EE-SX952-W 1M	*1
. 13.4	Through- beam (slot-type)			standard cable (1 m)	PNP	EE-SX952P-W 1M	*2
11.7		5 mm (slot width)		Pre-wired model with robot cable (1 m)	NPN	EE-SX952-R 1M	*1
	(3.3.3)[37			Pre-wired connector model with robot cable (0.3 m)	NPN	EE-SX952-C1J-R 0.3M	
R-shaped				Pre-wired model with	NPN	EE-SX953-W 1M	*1
13.4				standard cable (1 m)	PNP	EE-SX953P-W 1M	*2
12				Pre-wired model with robot cable (1 m)	NPN	EE-SX953-R 1M	*1
11.7				Pre-wired connector model with robot cable (0.3 m)	NPN	EE-SX953-C1J-R 0.3	И
U-shaped				Pre-wired model with	NPN	EE-SX954-W 1M	*1
0-snapeu				standard cable (1 m)	PNP	EE-SX954P-W 1M	*2
16				Pre-wired model with robot cable (1 m)	NPN	EE-SX954-R 1M	*1
13.4				Pre-wired connector model with robot cable (0.3 m)	NPN	EE-SX954-C1J-R 0.3	И

^{*1.} A model is available with a 3-m cable. The model number is EE-SX95□-□ 3M.(Example: EE-SX950-W 3M)

Accessories (Order Separately)


Connector with Robot Cable


Туре	Cable length	Model
Connector with Cable	2 m	EE-1016-R 2M

Note: For details, refer to the Accessories (Order Separately) on page page 28.

^{*2.} A pre-wired model with a PNP output and 1-m robot cable is available. The model number is EE-SX95□P-R 1M.(Example: EE-SX950P-R 1M)

		Туре	Standard	L-shaped	F-shaped	R-shaped	U-shaped			
		Pre-wired models	EE-SX950-□	EE-SX951-□	EE-SX952-□	EE-SX953-□	EE-SX954-□			
	NPN output	Pre-wired connector models	EE-SX950-C1J-R	EE-SX951-C1J-R	EE-SX952-C1J-R	EE-SX953-C1J-R	EE-SX954-C1J-R			
Item	PNP output	Pre-wired models	EE-SX950P-□	EE-SX951P-□	EE-SX952P-□	EE-SX953P-□	EE-SX954P-□			
Sensing	g distance		5 mm (slot width)							
Standa	rd sensing obj	ect	Opaque: 1.8 × 0.8 mm min.							
Differer	ntial travel		0.025 mm max. *1							
Light so	ource (wave le	ngth)	Infrared LED (940	nm)						
Indicate	or		Light indicator (red	LED)						
Power s	supply voltage		5 to 24 VDC ±10%	s, ripple (p-p): 10% n	nax.					
Current	t consumption		15 mA max.							
Control	l output		Load power supply voltage: 5 to 24 VDC Load current: 50 mA max. OFF current: 0.5 mA max. 50 mA load current with a residual voltage of 0.7 V max. 5 mA load current with a residual voltage of 0.4 V max.							
Protect	ion circuit		Load short-circuit protection							
Respon	nse frequency		1 kHz min. (3 kHz average) *2							
Ambien	nt illumination		1,000 lx max. with fluorescent light on the surface of the receiver							
Ambien	nt temperature	range	Operating: -25 to 55°C Storage: -30 to 80°C (with no icing or condensation)							
Ambien	nt humidity ran	ge	Operating: 5% to 85% Storage: 5% to 95% (with no icing or condensation)							
Vibratio	on resistance (destruction)	10 to 2,000 Hz (peak acceleration: 150m/s²) with a 0.75-mm single amplitude for 2.5 h (15-min periods, 10 cycles) each in X, Y, and Z directions							
Shock r	resistance (des	struction)	500 m/s ² for 3 times each in X, Y, and Z directions							
Degree	of protection		IEC60529 IP50							
Connec	ction method		Pre-wired models (standard length: 1 m), Pre-wired connector models (standard length: 0.3 m)							
Weight		Pre-wired models	Approx. 15 g							
(packed		Pre-wired connector models	Approx. 7 g							
Materia	ıle	Case/cover	Polybutylene terephthalate (PBT)							
wateria	ii S	Emitter/receiver	Polycarbonate (PC	C)						





Note: For details, refer to *EE-SX95 Data sheet*.

*1. The differential travel is the value when a sensing object is moved in a lateral direction to the slot.

*2. The response frequency was measured by detecting the following rotating disk.

Photomicrosensor with Slim Cable (Non-modulated) EE-SX77/87

Slim, Compact Photomicrosensor that is still easy to use.

- · Compact, thin profile enables dense mounting.
- Indicator is visible from both sides.
- Wide operating voltage range: 5 to 24 VDC



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



Be sure to read Safety Precautions for All Photomicrosensors on page 30.


Ordering Information

Pre-wired Models Infrared light

	Sensing	Cable		Output		Mo	odel	
Appearance	method	length	Sensing distance	configura- tion	Indicator mode	NPN output	PNP output	
Standard				Dark-ON	Incident light	EE-SX770 2M	EE-SX770P 2M	
18				Daik-ON	No incident light	EE-SX770A 2M	EE-SX770R 2M	
31.1				Light ON	Incident light	EE-SX870 2M	EE-SX870P 2M	
4.6		Dark-ON No incident light	No incident light	EE-SX870A 2M	EE-SX870R 2M			
L-shaped					Dorle ON	Incident light	EE-SX771 2M	EE-SX771P 2M
18	Through- beam			2 m	2	5 mm	Daik-ON	No incident light
21	(slot-type)	2 111	(slot width)	Light-ON	Incident light	EE-SX871 2M	EE-SX871P 2M	
					Light-ON	No incident light	EE-SX871A 2M	EE-SX871R 2M
T-shaped				Dark-ON	Incident light	EE-SX772 2M	EE-SX772P 2M	
-12				Dark-ON	No incident light	EE-SX772A 2M	EE-SX772R 2M	
31.1					Incident light	EE-SX872 2M	EE-SX872P 2M	
T				Light-ON	No incident light	EE-SX872A 2M	EE-SX872R 2M	

	Туре	Standard	L-shaped	T-shaped					
	NPN models	EE-SX770/EE-SX870 EE-SX770A/EE-SX870A	EE-SX771/EE-SX871 EE-SX771A/EE-SX871A	EE-SX772/EE-SX872 EE-SX772A/EE-SX872A					
Item	PNP models	EE-SX770P/EE-SX870P EE-SX770R/EE-SX870R	EE-SX771P/EE-SX871P EE-SX771R/EE-SX871R	EE-SX772P/EE-SX872P EE-SX772R/EE-SX872R					
Sensing distance	;	5 mm (slot width)							
Sensing object		Opaque: 2×0.8 mm min.							
Differential distar	nce	0.025 mm							
Light source		GaAs infrared LED with a peak wavelength of 940 nm							
Indicator		Light indicator (red) (turns ON when I	Light indicator (red) (turns ON when light is interrupted for models with A or R suffix)						
Supply voltage		5 to 24 VDC ±10%, ripple (p-p): 10%	max.						
Current consump	otion	12 mA max.							
Control output		40 mA load curry OFF current (lea PNP open collector: 5 to 24 VDC, 50 50 mA load curry	rent with a residual voltage of 0.8 V ment with a residual voltage of 0.4 V markage current): 0.5 mA max.	ıx.					
Protection circuit	ts	Load short-circuit protection							
Response time		Light-ON: 20 μs max, Dark-ON: 100 μ	us max.						
Maximum respon frequency *1	ise	3 kHz max.							
Ambient illumina	tion	1,000 lx max. with fluorescent light or	the surface of the receiver						
Ambient tempera	ture range	Operating: -25 to $+55$ °C Storage: -30 to $+80$ °C (with no icin	g)						
Ambient humidity	y range	Operating: 5% to 85% Storage: 5% to 95% (with no conde	ensation)						
Vibration resistar	Destruction: 10 to 2,000 Hz (peak acceleration: 100 m/s²) 1.5-mm double amplitude for 2 h (4-min periods) each in X, Y, and Z directions								
Shock resistance	Destruction: 500 m/s² for 3 times each in X, Y, and Z directions								
Degree of protect	tion *2	IEC60529 IP64							
Connecting meth	od	Pre-wired (standard cable length: 2 m	n)						
Weight (package		Approx. 20 g							
Weight (package	d)	· · · · ·							
Material	d)	Approx. 20 g Case: Polybutylene phthalate (PBT)							

Note: For details, refer to *EE-SX77/SX87 Data sheet.**1. The response frequency was measured by detecting the following rotating disk.



^{*2.} Degree of protection IP64 when conforming to ISO13849-1 (PLc, cat1). Conforms to September 2023.

Refer to the Instruction Sheet and Information for ISO13849-1 Compliance on our website (www.fa.omron.co.jp/products/family/435/download/manual.html) for conformance to ISO 13849-1.

EE-SPX-W

Photomicrosensor with built-in amplifier and attached cable reduces external light interference.

- Light modulation effectively reduces external light interference.
- Wide operation voltage range: 5 to 24 VDC
- Easy operation monitoring with bright light indicator.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



Be sure to read Safety Precautions for All Photomicrosensors on page 30.

Ordering Information


Infrared light

Appearance	Sensing method	Sensing dis		Output type	Output configuration	Cable length	Model				
21.2					Dark-ON		EE-SPX302-W2A 1M				
13		3.6	6 mm		Light-ON		EE-SPX402-W2A 1M				
21.2	7				Dark-ON		EE-SPX304-W2A 1M				
13	∠13 Through-beam	3.6	3.6 mm	NPN	Light-ON	1 m	EE-SPX404-W2A 1M				
21.2	(slot-type)	(slot-type)	(slot-type)	(slot-type)	(slot-type)			output	Dark-ON	1111	EE-SPX306-W2A 1M
7.4		3.6 mm] 3.6	3.6	6 mm		Light-ON		EE-SPX406-W2A 1M		
27.2					Dark-ON		EE-SPX305-W2A 1M*				
14.5			(4)	100	5	5 mm		Light-ON		EE-SPX405-W2A 1M*	

^{*} These models (EE-SPX305/405-W2A only) are not conformed to CE standards.


Item	Models	EE-SPX302-W2A, EE-SPX402-W2A EE-SPX304-W2A, EE-SPX404-W2A EE-SPX306-W2A, EE-SPX406-W2A	EE-SPX305-W2A EE-SPX405-W2A			
Sensing distance		3.6 mm (slot width)	5 mm (slot width)			
Sensing obj	ect	Opaque: 1 × 0.5 mm min.	Opaque: 2 × 0.8 mm min.			
Differential	distance	0.05 mm max.				
Light source)	GaAs infrared LED (pulse lighting) with a	peak wavelength of 940 nm			
Indicator *1		Light indicator (red)				
Supply volta	age	5 to 24 VDC ±10%, ripple (p-p): 5% max				
Current con	sumption	Average: 15 mA max.; Peak: 50 mA max				
Control outp	out	NPN voltage output: Load power supply voltage: 5 to 24 VDC Load current: 80 mA max. OFF current: 0.5 mA max. 80 mA load current with a residual voltage of 1.0 V max. 10 mA load current with a residual voltage of 0.4 V max.				
Response fr	equency *2	00 Hz min.				
Ambient illu	mination	3,000 lx max. with incandescent light or sunlight on the surface of the receiver				
Ambient ten	nperature	Operating: -10 to +55°C Storage: -25 to +65°C				
Ambient hu	midity range	Operating: 5% to 85% Storage: 5% to 95%				
Vibration re	sistance	Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 h each in X, Y, and Z directions				
Shock resis	tance	Destruction: 500 m/s² for 3 times each in X, Y, and Z directions				
Degree of p	rotection	IEC IP50				
Connecting	method	Pre-wired (standard cable length: 1 m)				
Weight		18.5 g				
Material	Case	Religenthemate				
waterial	Holder	Polycarbonate				


*1. The indicator is a GaP red LED (peak wavelength: 700 nm).*2. The response frequency was measured by detecting the following rotating disk.





EE-SPX305-W2A





Note: For details, refer to EE-SPX-W Data sheet.

EE-SPX74/84

Photomicrosensor with light modulation for reduced external light interference and a connector for easy maintenance.

- Built-in connectors
- Select from four easy-to-use shapes for efficient space utilization.
- Connectors with locks for safety against vibration.
- Convenient mounting method using M3 screws.
- Wide operating voltage range: 5 to 24 VDC



Be sure to read Safety Precautions for All Photomicrosensors on page 30.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensors Infrared light

Appearance	Sensing method	Sensing distance	Output type	Output configuration	Model
21.2				Dark-ON	EE-SPX740
7.4	Through-beam (slot-type)			Light-ON	EE-SPX840
21.2		3.6 mm		Dark-ON	EE-SPX742
7		(slot width)	NPN output	Light-ON	EE-SPX842
21,2				Dark-ON	EE-SPX743
13 7				Light-ON	EE-SPX843
15.5		E mm		Dark-ON	EE-SPX741
15.4		5 mm (slot width)		Light-ON	EE-SPX841

Accessories (Order Separately)

Connector with Cable


Туре	Cable length	Model
Connector	1 m	EE-1013 1M

Note: For details, refer to the Accessories (Order Separately) on page 28.

Item	Models	EE-SPX740, EE-SPX840 EE-SPX742, EE-SPX842 EE-SPX743, EE-SPX843	EE-SPX741 EE-SPX841			
Sensing distance		3.6 mm (slot width)	5 mm (slot width)			
Sensing obj	ect	Opaque: 1 × 0.5mm min.	Opaque: 2 × 0.8 mm min.			
Differential of	distance	0.05 mm max.				
Light source)	GaAs infrared LED (pulse lighting) with a	peak wavelength of 940 nm			
Indicator *1		Light indicator (red)				
Supply volta	ige	5 to 24 VDC ±10%, ripple (p-p): 5% max.				
Current consumption Average: 15 mA max.; Peak: 50 mA max.						
Control outp	out		power supply voltage: 5 to 24 VDC current: 50 mA max.			
Response fr	equency *2	500 Hz min.				
Ambient illu	mination	3,000 lx max. with incandescent light or s receiver	unlight on the surface of the			
Ambient ten	nperature	Operating: -10 to +55°C Storage: -25 to +65°C				
Ambient hui	midity range	Operating: 5% to 85% Storage: 5% to 95%				
Vibration res	sistance	Destruction: 10 to 55 Hz, 1.5-mm double Y, and Z directions	amplitude for 2 h each in X,			
Shock resis	tance	Destruction: 500 m/s ² for 3 times each in	uction: 500 m/s² for 3 times each in X, Y, and Z directions			
Degree of protection IEC IP50						
Connecting	method	Special connector				
Weight		Approx. 2.4 g				
Material	Case	Polycarhonate				
waterial	Holder	Polycarbonate				


Note: For details, refer to EE-SPX74/SPX84 Data sheet.

- *1. The indicator is a GaAlAs red LED (peak wavelength: 660 nm).*2. The response frequency was measured by detecting the following rotating disk.





EE-SPX741/841







EE-SPX740/840

EE-SPX303N/403N

A Wide Slot Width of 13 mm and Superior Resistance to Light Interference and Noise.



(€ 91°

- Noise resistance equivalent to photomicrosensors with built-in amplifiers.
- Resistance to common noise at least 30 times that of previous models.
- Resistance to inverter noise at least 10 times that of previous models.
- Reverse polarity protection built in.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensors Infrared light

Appearance	Sensing method	Sensing distance (slot width)	Output type	Output configuration	Model
26	Through-beam	13 mm	NPN output	Dark-ON	EE-SPX303N
26	(slot-type)	(slot width)	141 14 Output	Light-ON	EE-SPX403N

Accessories (Order Separately)


	Туре	Cable length	Model
Connector			EE-1001
			EE-1009
		1 m	EE-1006 1M
	Connector with	1 m	EE-1010 1M
	Cable	2 m	EE-1006 2M
		2 111	EE-1010 2M
	Connector with	1 m	EE-1010-R 1M
	Robot Cable	2 m	EE-1010-R 2M
NPN/PNP C	onversion Connector	0.46 m (total length)	EE-2002


Note: For details, refer to the Accessories (Order Separately) on page 28.

Note: For details, refer to EE-SPX303N/SPX403N Data sheet.

Manager Manager	EE ORYGONI EE ORYGONI			
Item Models	EE-SPX303N, EE-SPX403N			
Sensing distance	13 mm (slot width)			
Sensing object	Opaque: 2.2×0.5 mm min.			
Differential distance	0.05 mm max.			
Light source	Infrared LED (pulse lighting) with a peak wavelength of 940 nm			
Indicator	Light indicator (red)			
Supply voltage	12 to 24 VDC ±10%, ripple (p-p): 5% max.			
Current consumption	15 mA max.			
Control output	NPN voltage output: Load power supply voltage: 12 to 24 VDC Load current: 80 mA max. OFF current: 0.5 mA max. 80 mA load current with a residual voltage of 2.0 V max. 10 mA load current with a residual voltage of 1.0 V max.			
Protection circuits	Power supply reverse polarity protection, Output reverse polarity protection			
Response frequency *	100 Hz min.			
Ambient illumination	3,000 lx max. with incandescent light or sunlight on the surface of the receiver.			
Ambient temperature range	Operating: -10 to +55°C Storage: -25 to +65°C			
Ambient humidity range	Operating: 5% to 85% Storage: 5% to 95%			
Vibration resistance	Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 h each in X, Y, and Z directions			
Shock resistance	Destruction: 500 m/s² for 3 times each in X, Y, and Z directions			
Degree of protection	IEC IP50			
Connecting method	Special connector (soldering not possible)			
Weight	Approx. 4 g			
Material	Polycarbonate			

* The response frequency was measured by detecting the following rotating disk.





EE-SPY31/41

Accurately detects objects placed in front of shiny Background.

- A shiny background can be used as long as the distance between the sensor and the background is 20 mm or more.
- Detects minute objects such as a 0.05-mm-dia. pure copper wire.
- Small dispersion in sensing distance.
- Light modulation effectively reduces external light interference.
- Wide operating voltage range: 5 to 24 VDC



CE SU



Be sure to read Safety Precautions for All Photomicrosensors on page 30.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensors Infrared light

Appearance	Sensing method	Sensi	ng distance	Output type	Output configuration	Model		
Horizontal type					Dark-ON	EE-SPY311		
26 8	Convergent	2 to 5	2425	NPN output	Light-ON	EE-SPY411		
Vertical type	reflective type		2 10 5 111111	2 10 5 11111	2 10 5 111111	Ni N output	Dark-ON	EE-SPY312
22.8	22.8				Light-ON	EE-SPY412		


Accessories (Order Separately)

	Туре	Cable length	Model
Connector			EE-1001
			EE-1009
		1 m	EE-1006 1M
Connector with Cable	1 111	EE-1010 1M	
	Connector with Cable	2 m	EE-1006 2M
		2111	EE-1010 2M
Connector with Robot Cable		1 m	EE-1010-R 1M
		2 m	EE-1010-R 2M
NPN/PNP Conversion Connector		0.46 m (total length)	EE-2002

Note: For details, refer to the Accessories (Order Separately) on page 28.


Item	Models	EE-SPY311, EE-SPY411, EE-SPY312, EE-SPY412	
Sensing dista	ınce	2 to 5 mm (Reflection factor: 90%; white paper 15 × 15 mm)	
Minimum sensing object		Pure copper wire (0.05 mm dia.)	
Distance to background *1		20 mm max. (glass with aluminum deposition)	
Differential di	stance	0.2 mm (with a sensing distance of 3 mm, horizontally)	
Light source		GaAs infrared LED with a peak wavelength of 940 nm	
Indicator *2		Light indicator (red)	
Supply voltage	је	5 to 24 VDC ±10%, ripple (p-p): 5% max.	*1.
Current cons	umption	Average: 15 mA max., Peak: 50 mA max.	Sensing object
Control output		NPN voltage output: Load power supply voltage: 5 to 24 VDC Load current: 80 mA max. OFF current: 0.5 mA max. 80 mA load current with a residual voltage of 1.0 V max. 10 mA load current with a residual voltage of 0.4 V max.	20 mm Distance to backgre
Response frequency *3		100 Hz min.	*2. The indicator is a GaP red
Ambient illum	nination	3,000 lx max. with incandescent light or sunlight on the surface of the receiver	(peak wavelength: 700 nm *3. The response frequency w detecting the following rota
Ambient temp	perature range	Operating: -10 to +55°C Storage: -25 to +65°C	2000 mm dia.
Ambient hum	idity range	Operating: 5% to 85% Storage: 5% to 95%	15 mm / 15 mm
Vibration resistance		Destruction: 10 to 50 Hz, 1.5-mm double amplitude for 2 h each in X, Y, and Z directions	15 mm 15 mm
Shock resistance		Destruction: 500m/s ² for 3 times each in X, Y, and Z directions	Disk
Degree of protection		IEC IP50	
Connecting method		Special connector (soldering not possible)	EE CDVOAA/AAA
Weight		Approx. 2.6 g	EE-SPY311/411
Material	Case	Polycarbonate	
waterial	Holder	Polybutylene phthalate (PBT)	

Note: For details, refer to EE-SPY31/SPY41 Data sheet.



- ed LED
- nm).

 v was measured by otating disk.



EE-SPY30/40

Photomicrosensor with light modulation is not influenced by external light.

- Voltage-output models with wide operating voltage range (5 to 24 VDC).
- Fitted with an easy-to-adjust optical axis mark.
- Easy adjustment and optical axis monitoring with a light indicator.



(E 91)

Be s

Be sure to read Safety Precautions for All Photomicrosensors on page 30.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensors Infrared light

Appearance	Sensing method	Sensing distance	Output type	Output configuration	Model
Horizontal type	Reflective type	5 mm	NPN	Dark-ON	EE-SPY301
7——————————————————————————————————————	Reflective type	5 mm		Light-ON	EE-SPY401
Vertical type	Deflective type	D 5	output	Dark-ON	EE-SPY302
	Reflective type	5 mm		Light-ON	EE-SPY402

Accessories (Order Separately)

	Туре	Cable length	Model
Connector			EE-1002
Connector	Connector with Cable	1 m	EE-1003
NPN/PNP Co	onversion Connector	0.46 m (total length)	EE-2001
Connector H	old-down Clip		EE-1003A


Note: For details, refer to the Accessories (Order Separately) on page 28.


Sensing metho	Reflective type					
Item Model	EE-SPY301, EE-SPY401 EE-SPY302, EE-SPY402					
	·					
Sensing distance	5 mm (Reflection factor: 90%; white paper 15 × 15 mm) *1					
Sensing object						
Differential distance	0.2 mm max. (with a sensing distance of 3 mm, horizontally)					
Light source	GaAs infrared LED with a peak wavelength of 940 nm					
Indicator *2	Light indicator (red)					
Supply voltage	5 to 24 VDC ±10%, ripple (p-p): 5% max.					
Current consumption	Average: 15 mA max., Peak: 50 mA max.					
Control output	NPN voltage output: Load power supply voltage: 5 to 24 VDC Load current: 80 mA max. OFF current: 0.5 mA max. 80 mA load current with a residual voltage of 1.0 V max. 10 mA load current with a residual voltage of 0.4 V max.					
Response frequency *3	100 Hz min.					
Ambient illumination	3,000 lx max. with incandescent light or sunlight on the surface of the receiver					
Ambient temperature range	Operating: -10 to +55°C Storage: -25 to +65°C (with no icing)					
Ambient humidity range	Operating: 5% to 85% Storage: 5% to 95% (with no condensation)					
Vibration resistance	Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 h each in X, Y, and Z directions					
Shock resistance	Destruction: 500 m/s² for 3 times each in X, Y, and Z directions					
Degree of protection	IEC IP50					
Connecting method	Special connector (soldering not possible)					
Weight	Approx. 2.6 g					
Material Case	Polycarbonate					

Note: For details, refer to EE-SPX301/SPX401/SPY30/SPY40 Data sheet.

- *1. Operation may not be possible near the Sensor.
 *2. The indicator is a GaP red LED (peak wavelength: 700 nm).
 *3. The response frequency was measured by detecting the following rotating disk.

EE-SPY30□ EE-SPY40□





EE-SPX613

Liquid Level Photomicrosensor with operation mode and sensitivity selectors for easy application.

- Operation mode selector allows modes to be switched easily.
- Sensitivity selector is suitable for any 6- to 13-mm-diameter transparent or semi-transparent pipe with a wall thickness of 1 mm.
- Uses a clean (with no powder parting agent) cable.
- Operating voltage range: 12 to 24 VDC







Be sure to read Safety Precautions for All Photomicrosensors on page 30.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Appearance	Sensing method	Output type	Output configuration	Cable length	Model
17.2	Through-beam type	NPN output	Dark-ON or Light-ON (selectable)	1 m	EE-SPX613 1M

Item	Models	EE-SPX613					
Applicable pi	pe	Any 6- to 13-mm-diameter pipe with a wall thickness of 1 mm that is made of FEP or any other material as transparent as FEP.					
Sensing obje	ct	Liquids in pipes (High-viscosity liquids or liquids with floating materials may not be detected.)					
Light source		GaAs infrared LED with a peak wavelength of 940 nm					
Indicator		Light indicator GaP (Red LED: Peak wavelength of 700 nm)					
Supply voltage	ge	12 to 24 VDC ±10%, ripple (p-p): 5% max.					
Current cons	umption	Average: 30 mA max., Peak: 80 mA max.					
Control output		NPN open collector: Load power supply voltage: 5 to 24 VDC Load current: 100 mA max. OFF current: 0.5 mA max. 100 mA load current with a residual voltage of 0.8 V max. 40 mA load current with a residual voltage of 0.4 V max.					
Ambient illun	nination	3,000 lx max. with incandescent light or sunlight on the surface of the receiver					
Ambient temp	perature	Operating: -10 to +55°C Storage: -25 to +65°C (with no icing or condensation)					
Ambient hum range	idity	Operating: 5% to 85% Storage: 5% to 95% (with no condensation)					
Vibration resi	istance	Destruction: 10 to 500 Hz, 1.0-mm single amplitude or 150 m/s ² in X, Y, and Z directions 3 times and for 11 min each					
Shock resista	ance	Destruction: 500 m/s² for 3 times each in X, Y, and Z directions					
Degree of pro	otection	IEC 60529 IP50					
Connecting n	nethod	Pre-wired (Standard length: 1 m)					
Weight (pack	ed state)	Approx. 55 g					
Material Case Cover		Polycarbonate					
Accessories		Support belt (2), slip protection tube (2), Instruction Manual					

Note: For details, refer to EE-SPX613 Data sheet.

EE-SA701/801

Using a pushbutton enables accurately detecting difficult-to-detect objects.

- Conforms to standards for semiconductor FOUP cassettes to enable accurately detecting FOUP cassettes without being affected by the material, color, or reflectance of the bottoms of the cassettes.
- Thin design enables mounting in a wider range of applications, e.g., on transfer arms.
- Increased visibility with 4-direction indicator.
- Optical detection of actuator operation provides a long life (mechanical life: 5 million operations min.).
- Models available with PNP or NPN output.
- Models are available with very flexible robot cable.



Be sure to read Safety Precautions for All Photomicrosensors on page 30.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

List of Models

Appearance	Sensing distance		Sensing method	Operation mode	Cable length	Model	
Appearance						NPN output	PNP output
				ON with no load	1 m	EE-SA801A 1M	EE-SA801R 1M
25 9	*2 0 to 3.5 mm (pressed position *1		Pushbutton	ON WITH HO TOAC	1 m (robot cable)	EE-SA801A-R 1M	EE-SA801R-R 1M
				OFF with no load		EE-SA701-R 1M	EE-SA701P-R 1M

^{*1.} Distance from the top surface of the housing to the top of the actuator.

^{*2.} Output reverses between 3.5 and 4.5 mm.

	Maria	NPN output	EE-SA801A	EE-SA801A-R	EE-SA701-R		
Item	Model	PNP output	EE-SA801R	EE-SA801R-R	EE-SA701P-R		
Indicator			Light red when actuator is pre	Lit red while there is no load on actuator			
Operation	Free position	ı (FP)	5.0±0.4 mm				
Specifica-	Operating po		3.5 to 4.5 mm *2				
tions *1	Total travel p	osition (TTP)	0 mm max.				
Operating loa	ad *3		3 N max. (typical: 0.5 N)				
Supply voltage	ge		12 to 24 VDC±10%, ripple (p-	p): 10% max.			
Current cons	umption		35 mA max.				
Control output			NPN Models: NPN open collector, 5 to 24 VDC, 50 mA max.; residual voltage of 0.4 V max. at 50-mA load current OFF current: 0.5 mA max. PNP Models: PNP open collector, 5 to 24 VDC, 50 mA max.; residual voltage of 0.4 V max. at 50-mA load current OFF current: 0.5 mA max.				
External diagnosis input		NPN Models Emission OFF: Shorted to 0 V or 0.5 V max. (source current: 30 mA max.) Emission ON: Open (leakage current: 0.4 mA max.) PNP Models Emission OFF: Shorted to +DC or +DC-0.5 V max. (sink current: 30 mA max.) Emission ON: Open (leakage current: 0.4 mA max.)					
		Response time	1 ms max.				
Protection ci	rcuits		Reversed power supply polarity protection				
Ambient tem	perature range	•	Operating: -25 to +55°C Storage: -30 to +60°C (with no icing or condensation)				
Ambient hum	nidity range		Operating: 5% to 85% Storage: 5% to 95% (with no condensation)				
Mechanical d	lurability		5,000,000 operations min. (One operation is from the free position to operating position and back to the free position.)				
Vibration res	istance		Destruction: 10 to 500 Hz, 1.0-mm single amplitude or 150 m/s ² 3 times each in X, Y, and Z directions for 11 min. each				
Shock resista	ance		Destruction: 500 m/s ² for 3 tin	nes each in X, Y, and Z direction	ons		
Degree of pro	otection		IEC IP40				
Connecting r	nethod		Pre-wired (standard cable length: 1 m)				
Weight			Approx. 16.1 g				
Material	Case		Polycarbonate				
Material	Actuator		Polyacetal				
			Instruction Manual				

Note: For details, refer to EE-SA701/SA801 Data sheet.


*1. Free position (FP):

Operating position (OP):

The position of the top of the actuator when no force is being applied to the actuator.

The position of the top of the actuator when the actuator is pressed and the output transistor changes from OFF to ON for the EE-SA701-R/-SA701P-R and from ON to OFF for all other models.

Total travel position (TTP): The position of the top of the actuator when the actuator is pressed as far as it can be pressed.



*2. This does not indicate that the output will be ON from 3.5 to 4.5 mm, but rather that the output will change from ON to OFF at some point between 3.5 and 4.5 mm. *3. The force required to press the actuator from the FP to the OP.

Accessories (Order Separately)

Ordering Information Connectors and Connector Hold-down Clips

	Туре		Cable length	Model	Remarks
				EE-1001	
Conne	ctor			EE-1001-1	L terminal and positive (+) terminal are already short-circuited.
				EE-1009 *1	
			4	EE-1006 1M	
			1 m	EE-1010 1M *1	
	Connecto	r with	with 2 m	EE-1006 2M	4 conductors
	Cable			EE-1006D	3 conductors
				EE-1006L	2 conductors
				EE-1010 2M *1	
	Connecto	r with	1 m	EE-1010-R 1M *1	
	Robot Cal	ole	2 m	EE-1010-R 2M*1	
NPN/PI Conne	NP Convers	sion	0.46 m (total length)	EE-2002	
Conne	ctor Hold-d	own Clip	<u> </u>	EE-1006A	For EE-1006, EE-SX670□, 470, EE-SY671, and 672 only.
		Case (hou	using)	EE-1006H	100 per carton
		Dispersio	n Pins	EE-1006C	500 per carton
Connector Parts *2	Special Crimping Tool		EE-1006T	Appearance Switching knob Crimping section Ratchet Handle	

^{*1.} EE-1009- or EE-1010-series Connectors have a builtin locking mechanism to prevent cable disconnection when only the cable is pulled. To remove the Connector from the Sensor, grip the top and bottom of the Connector firmly and push into the Sensor once before pulling out. The locking mechanism



prevents the Connector from being removed by pulling on the cable only and enables removal only when the Connector flowing) is pulled.

*2. The case (housing) and dispersion pins (for hand-crimping) for EE-1006 Connectors can be ordered separately. Use the EE-1006T Special Crimping Tool to prepare the Connector.

Applicable Sensor models EE-SX95□-C1J-R								
Item	Cable length	Model	Remarks					
Connector with Robot Cable	2 m	EE-1016-R 2M						
Applicable Sensor models EE-SX97□-C1, EE-SX97□P-C	Applicable Sensor models EE-SX97□-C1, EE-SX97□P-C1							
Item	Cable length	Model	Remarks					
Connector with Cable	1 m	EE-1017 1M						
Connector with Cable	3 m	EE-1017 3M						
Connector with Robot Cable	1 m	EE-1017-R 1M						
Connector with Robot Cable	3 m	EE-1017-R 3M						
	L							
Applicable Sensor models EE-SPX74□/84□								
ltem	Cable length	Model	Remarks					
Connector with Cable	1 m	EE-1013 1M						
Applicable Sensor models EE-SPY30□/40□, EE-SPZ30°	1-A/401-A							
Item	Cable length	Model	Remarks					
Connector		EE-1002						
Connector with Cable	1 m	EE-1003						
NPN/PNP Conversion Connector	0.46 m (total length)	EE-2001						
Connector Hold-down Clip		EE-1003A	For EE-1003 only.					

	Product	Connector *1 *4	Connector with Cable *1	Connector with Robot Cable *1	Connector *4	Connector (short-circuited between posi- tive (+) and L terminals) *2 *4	Connector with Cable	
	Model	EE-1009	EE-1010	EE-1010-R	EE-1001	EE-1001-1	EE-1006	
ltem	Appearance	200 Apr 10 Apr 1			one of	\$55.101-1 44.1	0 s = 0	
Contact res	sistance	20 mΩ max. (at 2	0 mV max., 100 m	A max.)	15 mΩ max. (at 1	10 mΩ max. (100 VDC max.)		
Insertion/redurability *		50 times min.						
Insertion s	trength	No. of poles × 6 N	l max.		68.6 N max.	50 N max.		
Surplus street (housing hole	ngth ding strength)	No. of poles \times 0.4	N max.				20 N max.	
Standard c	able length		1 m, 2 m		-		1 m, 2 m	
Lock stren	gth *3	No. of poles × 29	N min.					
Ambient hu	umidity	−10 to +60°C			−10 to +75°C		−10 to 60°C	
Material	Housing	Polybutylene phth	nalate (PBT)					
waterial	Contact	Phosphor bronze						
Applicable Photomicrosensors		EE-SX67□ (A,P,F EE-SPW311/411	EE-SX67□ (A,P,R) (Connector Models only), EE-SX47□, EE-SY67□, EE-SPY31□/41□, EE-SPX303N/403N					

	Product	Connector *4	Connector with Cable	Connector with Cable	Connector with Robot Cable	Connector with Cable	Connector with Robot Cable
Model		EE-1002	EE-1003	EE-1013	EE-1016-R	EE-1017	EE-1017-R
Item	Appearance		O'ROON E: '003		Y		
Contact resistance		10 mΩ max. (at 10 mADC and 1 ADC)	20 mΩ max. (at minute current of 1 kHz and 500 VDC)		25 mΩ max. (at 10 mA DC and 20 mV max.)		
Insertion s	trength	20 N max.	23.5 N max.	40 N max.	20 N max.		
Surplus stre (housing hol	ngth ding strength)	15 N min. (initial) 10 N min. (ten times)	3.5 N min.	10 N min.	15 N min. 1.5 N min.		
Cable leng	th		1 m		2 m	1 m, 3 m	
Ambient h	umidity	−10 to +75°C	−10 to +60°C	−10 to +55°C	−25 to +85°C	-10 to +60°C	
Material	Housing	Nylon					
Material	Contact	Phosphor bronze					
Applicable Photomicrosensors		EE-SPY30 /40 EE-SPZ301-A/40		EE- SPX74□/84□	EE- SX95□-C1J-R	EE-SX97□C1, EE-SX97□P-C1	

^{*1.} The Connector has a built-in locking mechanism. To remove the Connector from the Sensor, grip the top and bottom of the Connector housing, as shown in the following diagram, and then pull out the Connector.

*2. EE-SX67□ and EE-SY67□ are the best used in the light-ON state.

*3. The insertion/removal durability and lock strength apply only to the lock mechanism.

They do not apply to the EE-1001, EE-1001-1, and EE-1006, which do not have lock mechanisms.

*4. Do not store the type EE-1009, EE-1001, EE-1001-1 and EE-1002 under the following conditions since their terminals may discolor.

⁽¹⁾In the place exposed to the direct sunlight, the high temperature or high humidity.



Refer to Safety Precautions for individual models for specific precautions for each model.



These products cannot be used in safety devices for presses or other safety devices used to protect human life.



This product is designed for use in applications for sensing workpieces and workers that will not affect levels of safety.

Precautions for Safe Use

To ensure safety, observe the following precautions.

Wiring

Item	Examples
Power Supply Do not apply any voltage exceeding the operating voltage range. Applying any excessive voltage or supplying AC power (100 VAC or higher) to a DC-type sensor may cause the Sensor to explode or burn.	DC 3-Wire NPN Output Sensors Brown Sensor Blue Blue
Load Short-circuit Do not short-circuit the load. Doing so may cause the Sensor to explode or burn.	DC 3-Wire NPN Output Sensors (Load short-circuit) Sensor Blue Blue
Wiring Be sure to wire the Sensor correctly and be careful not to connect the polarities incorrectly, otherwise the Sensor may explode or burn.	DC 3-Wire NPN Output Sensors (Example) Wrong polarity DC 3-Wire NPN Output Sensors (Example) Wrong polarity or wrong wiring Brown Sensor Blue Black Blue Black Blue Black Blue
Connection with No Load If connected to the power supply without any load, internal elements may explode or burn. Make sure that a proper load is connected to the Sensor.	DC 3-Wire NPN Output Sensor Brown 12 to 24 VDC
AND Connections Do not use AND connections such as in the example shown in the diagram here. Voltage will be applied to the Vcc terminal without the GND terminal of Sensor 2 being securely grounded, and may cause the Sensor to fail. Depending on the model used, inrush current to Sensor 2 when Sensor 1 is turned ON may cause product failure.	Sensor 1 Sensor 2 Brown (Vcc) Sensor Black (OUT) Blue (GND) Blue (GND) Blue (GND) Blue (GND)

Precautions for Correct Use

Installation

- The Photomicrosensors with Non-modulated Light (models that begin with EE-SX or EE-SY) are built into the device being used and are, therefore, not equipped to deal with interference from an external light source. When using a Photomicrosensor with Nonmodulated Light in an area exposed to an incandescent light or other external light interference, install so as to minimize the effects of external light sources.
- Mount the Photomicrosensors securely on a flat surface
- Mount the Photomicrosensors with M3 screws, using a spring washer to ensure the screws will not become loose. Use a tightening force of 0.59 N·m max.


Note: Be sure to read the precautions for the model being used before tightening the screws.

- Install so that nothing can collide with the sensing section of the Photomicrosensor. Damage to the sensing surface will cause inferior performance.
- Before using the Photomicrosensor, check to be sure that it has not become loose due to vibration or shock.


Wiring

Surge

 If there is surge in the power supply line, try connecting a capacitor (with a capacitance of 0.1 to 1 μF) or a Zener diode (ZD in the diagram below, with a rated voltage of 30 to 35 V). Use the Sensor only after confirming that the surge has been removed.



 When driving a small inductive load, such as a relay, wire as shown below. (Be sure to connect a diode to absorb the reverse voltage.)




- Separate the wiring for the Photomicrosensor from high-voltage lines or power lines. If the wiring is routed in the same conduit or duct as such lines, the Photomicrosensor may malfunction or may be damaged by inductive interference.
- Make sure that the connectors (either dedicated or commercially available) are securely locked.

Voltage Output

 A Sensor with an open-collector output can be connected to a counter with a voltage input by connecting a resistor between the power source and output. Select a resistor with reference to the following example. The resistance of the resistor is generally 4.7 kΩ and its wattage is 1/2 W for a supply voltage of 24 V and 1/4 W for 12 V.

Example



If resistance R = 4.7 $k\Omega$ for the EE-SX670, the input voltage at the high level is as follows:

Input voltage V_H =
$$\frac{Z}{R+Z}$$
 Vcc = $\frac{4.7k}{4.7k + 4.7k} \times 24V$
=12V

And the input voltage and load current at the low level are as follows:

Input voltage V_L ≤ 0.4 V (Residual voltage for 40-mA load current)

Load current IC =
$$\frac{Vcc}{R}$$
 = $\frac{Vcc}{R}$ = 5.1mA ≤ 40mA

Note: Refer to the ratings of the Sensor for the residual voltage of the load current.

Handling Methods when Wiring

 Do not apply stress (external force) to the terminals as shown in the figure below. Stress may damage the terminals.



Design

Design the application so that light will be completely interrupted. We recommend that you use a metal object as the sensing object. (The light beam from an Infrared Sensor may pass through plastic sensing objects, which may make detection unstable.)

Terminate the terminals that you do not use (e.g., the L terminal or output line) and do not connect them to anything.

Precautions for Photomicrosensors with Modulated Light

When using Photomicrosensors with Modulated Light (models that begin with EE-SP), the design must take into account the effects of power source and cable length. Photomicrosensors with Modulated Light are more easily affected than Photomicrosensors with Nonmodulated Light (models that begin with EE-SX or EE-SY).

• Photomicrosensors with Modulated Light that are easily affected: EE-SPY30□/40□, E-SPZ301□/401□, EE-SPX31□/41□, EE-SPX303N/403N,

EE-SPW311/411, EE-SPX74 /84,

 Photomicrosensors with Modulated Light that are not easily affected:

EE-SPX613, EE-SPY801/802

Reasons for Interference from Power and Cable Length on Photomicrosensors with Modulated Light


As explained in the *Operating Principles* in the *Technical Explanation* for *Photomicrosensors*, an LED emitter is pulse-lighted to produce modulated light. A large current momentarily flows to the Photomicrosensor in sync with this pulse timing. This causes a pulsating consumption current.

A photoelectric sensor incorporates a capacitor with sufficient capacity, and is virtually unaffected by the pulse of the consumption current. With a small Photomicrosensor, however, it is difficult to have a capacitor with a sufficient capacity. Accordingly, when the cable length is long or depending on the type of power source, it may become impossible to keep up with the pulse of the consumption current and operation may become unstable.

Countermeasures


Adding a Capacitor

• Attach a capacitor of 10 μ F min. (e.g., a film capacitor) to the wires as close as possible to the Sensor. (Use a capacitor with a dielectric strength that is at least twice the Sensor's power supply voltage. Do not use tantalum capacitors. A short-circuit may cause the capacitor to ignite due to the large current flow.)




Cable Length

- Design the configuration so that the maximum total cable length for the Photomicrosensor with Modulated Light is 2 m.
- When using a cable longer than 2 m, attach a capacitor (e.g., an aluminum electrolytic capacitor) with a capacity of approximately 10 μF to the wires as shown below. The distance between the terminal and the capacitor must be within 2 m. Make sure that the total cable length is no longer than 5 m. To use a cable length longer than 5 m, use a PLC or other means to read the sensor output and then transmit the signals using a PLC's communications.
- Regardless of whether a Photomicrosensor with Modulated Light or a Photomicrosensor with Non-modulated Light is used, make sure that the total combined length of the Photomicrosensor cable and the connecting cable is less than 10 m.
- Although cables are capable of being extended longer than 5 m, performance is likely to be affected by noise interference from adjacent cables and other devices. Voltage drops due to the resistance of the cable material itself will also influence performance. Therefore, factors, such as the difference in voltage between the end of the cable and the sensor and noise levels, must be given full consideration.




Countermeasures for Switching Power Supplies

- Take either of the following countermeasures as required if connecting a Photomicrosensor with Modulated Light to a switching power supply.
- Attach a capacitor of 10 μF min. to the wires as close as possible to the Photomicrosensor. (Use a capacitor with a dielectric strength that is at least twice the Photomicrosensor's power supply voltage. Do not use tantalum capacitors. A short-circuit may cause the capacitor to ignite due to the large current flow.)




 Connect to the 0-V line of the power source or connect to the power source via a capacitor of approximately 0.47 μF to reduce the impedance of the mounting base to prevent inductive noise from entering the mounting base.



Connect the noise filter terminal (neutral terminal to ACG) of the switching power supply to the case (FG) and 0-V terminal of the power supply.

The line connected as mentioned above should be grounded or connected to the mounting base to ensure stable operation. (Recommended by power supply manufacturers.)


Countermeasures to Handle Inductive Noise



Insert a plastic insulator of approximately 10 mm between the Sensor and the mounting base.

Effects of Inductive Noise


 When there is inductive noise in the Sensor mounting frame (metal), the output of the Sensor may be affected. In this case, ensure that there is no electrical potential difference between the Sensor 0-V terminal and the Sensor mounting frame, or put a 0.47-μF capacitor between the 0-V terminal and the frame.



Precautions for Reflective Photomicrosensors Sensing Distance


 The Reflective Photomicrosensor model is based on sensing a sheet of white paper with a reflection factor of 90%. The sensing distance varies with the other conditions of the objects being detected.

Typical Example EE-SPY30/40 Series




Background Objects

 Use the Sensor only after carefully studying the possibility of light entering the Sensor due to light being reflected off background objects.




Decrease reflection from the background object, e.g., by providing a sufficient distance to the background or by using a black sponge as the background.


PLC Connections



Relay Connections



Counter Connections



Other Precautions

- Do not disconnect the Connector from the Sensor when power is supplied to the Sensor. Doing so may damage the Sensor.
- Avoid installing the Sensor in the following locations to prevent malfunction or product failure:
 - 1. Location exposed to high concentrations of dust, oil mist, etc.
 - 2. Locations exposed to corrosive gases
 - 3. Locations exposed directly or indirectly to water, oil, or chemical spray
 - 4. Outdoors or locations exposed to intensive light, such as direct sunlight
- Be sure to use the Sensor under the rated ambient temperature.
- The Sensor may be dissolved by exposure to organic solvents, acids, alkali, aromatic hydrocarbons or chloride resin hydrocarbons, causing
 deterioration in characteristics. Do not expose the Sensor to such chemicals.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011 OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.Room 2211, Bank of China Tower,

200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388 Authorized Distributor:

©OMRON Corporation 2023-2024 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM_2_2

Cat. No. E617-E1-04 0224 (0323)