

プロダクト・ニュース

この商品は
生産終了しました

OMRON

1993年7月1日


No.1649

フォト・マイクロセンサ形EE-SX450-P1生産中止のお知らせ

フォト・マイクロセンサ

フォト・マイクロセンサ形EE-SX450-P1の生産を中止します。

生産中止機種と代替推奨機種

生産中止機種	代替推奨機種
	形EE-SX450-P1
	形EE-SX4009-P1

注1. 外形図および内部回路は裏面を参照ください。

2. 電気的特性および性能については変わりません。

旧製品の製造可否

不可能です。

生産中止時期

*1994年3月末日をもって生産を中止します。

オムロン株式会社 営業統轄事業部

限定配布
特約店・特約販売店・特販店様用

形EE-SX450-P1/形EE-SX4009-P1比較

生産中止機種	代替推奨機種
形EE-SX450-P1 Top view dimensions: 36, (7.5), 23±0.2, (2), 3.5, 11, 13, 3-□0.64, φ4.2±0.2穴, φ3 深さ2. Side view dimensions: 14.6, 5, 2-R1, 10.5, 7.5, 3, φ4 C0.5, 5.6±1. Cross-section dimensions: 7, 3.5, 0.5(スリット幅), 15, 光軸. Circuit diagram showing an op-amp with a photodiode input, connected to Vcc, OUTPUT, and GND. The output is labeled 出力トランジスタ.	形EE-SX4009-P1 Top view dimensions: 34, (10.5), 23±0.2, (2), 3.5, 11, 13, φ4.2±0.2穴, φ3 深さ2. Side view dimensions: 14.6, 5, 2-R1, 10.5, 7.5, 3, φ4 C0.5, 5.6±1. Cross-section dimensions: 7, 3.5, 0.5(スリット幅), 15, 光軸. Circuit diagram showing an op-amp with a photodiode input, connected to Vcc, OUTPUT, and GND. The output is labeled 出力トランジスタ.