

Catalog Correction Notice

Catalog / Manual

Issue Date
March 2, 2020

No. 202003DE

The mistake of the print and the description is found in the catalog / manual that our company issued. We apologize.

[Name of catalog / manual]

- “ MicroHAWK V430-F Autofocus Multi Code Reader DATASHEET ” < Publication in December, 2019 >
< Catalog number Q274-E-01 >
- “ MicroHAWK V420-F Autofocus Multi Code Reader DATASHEET ” < Publication in December, 2019 >
< Catalog number Q275-E-01 >
- “ MicroHAWK F430-F Smart Camera DATASHEET ” < Publication in December, 2019 >
< Catalog number Q278-E-01 >
- “ MicroHAWK F420-F Smart Camera DATASHEET ” < Publication in December, 2019 >
< Catalog number Q279-E-01 >
- “ Code Reader GROUP CATALOG ” < Publication in December, 2019 > < Catalog number Q263-E1-03 >
- “ MicroHAWK V320-F / V330-F / V420-F / V430-F Barcode Reader USER'S MANUAL ”
< Publication in December, 2019 > < Manual number Z432-E-01 >
- “ MicroHAWK F320-F / F330-F / F420-F / F430-F Smart Camera USER'S MANUAL ”
< Publication in December, 2019 > < Manual number Z433-E-03 >

[Correction method]

We revise it at the time of a Catalog reprint on the next time.







[Content of correction]

“ MicroHAWK V430-F Autofocus Multi Code Reader DATASHEET ” < Catalog number Q274-E-01 > page 2

“ MicroHAWK V420-F Autofocus Multi Code Reader DATASHEET ” < Catalog number Q275-E-01 > page 2

“ MicroHAWK F430-F Smart Camera DATASHEET ” < Catalog number Q278-E-01 > page 2

“ MicroHAWK F420-F Smart Camera DATASHEET ” < Catalog number Q279-E-01 > page 2





	Appearance	Type	Part Number												
Before		Front Window Installation Kit	V430-AF0												
		Diffuser Installation Kit	V430-AF1												
		Polarizer Installation Kit	V430-AF2												
	Appearance	Type	Part Number												
After		Front Window Installation Kit	V430-AF10 *												
		Diffuser Installation Kit	V430-AF11 *												
		Polarizer Installation Kit	V430-AF12 *												
<p>* Note: V430-AF10, AF11, and AF12 are used for MicroHAWK V/F4X0-FXXXXXXX-XXX readers in this datasheet. The prior generation MicroHAWK V430-FXXXXXXX code reader uses part numbers V430-AF0, AF1, and AF2. Please select the correct accessory from the table based on your camera part number format.</p> <table border="1"> <thead> <tr> <th>Accessory</th> <th>Prior V430-FXXXXXXX Code Reader</th> <th>New V/F4X0-FXXXXXXX-XXX Code Reader and Smart Camera</th> </tr> </thead> <tbody> <tr> <td>Front Window Installation Kit</td> <td>V430-AF0</td> <td>V430-AF10</td> </tr> <tr> <td>Diffuser Installation Kit</td> <td>V430-AF1</td> <td>V430-AF11</td> </tr> <tr> <td>Polarizer Installation Kit</td> <td>V430-AF2</td> <td>V430-AF12</td> </tr> </tbody> </table>				Accessory	Prior V430-FXXXXXXX Code Reader	New V/F4X0-FXXXXXXX-XXX Code Reader and Smart Camera	Front Window Installation Kit	V430-AF0	V430-AF10	Diffuser Installation Kit	V430-AF1	V430-AF11	Polarizer Installation Kit	V430-AF2	V430-AF12
Accessory	Prior V430-FXXXXXXX Code Reader	New V/F4X0-FXXXXXXX-XXX Code Reader and Smart Camera													
Front Window Installation Kit	V430-AF0	V430-AF10													
Diffuser Installation Kit	V430-AF1	V430-AF11													
Polarizer Installation Kit	V430-AF2	V430-AF12													

“ MicroHAWK V430-F Autofocus Multi Code Reader DATASHEET ” < Catalog number Q274-E-01 > page 17

“ MicroHAWK V420-F Autofocus Multi Code Reader DATASHEET ” < Catalog number Q275-E-01 > page 14

“ MicroHAWK F430-F Smart Camera DATASHEET ” < Catalog number Q278-E-01 > page 17

“ MicroHAWK F420-F Smart Camera DATASHEET ” < Catalog number Q279-E-01 > page 14

<p>Before</p>	<p>Front Window Installation Kit V430-AF0 Diffuser Installation Kit V430-AF1 Polarizer Installation Kit V430-AF2 YAG Filter Installation Kit V430-AF4 ESD-Safe Window Installation Kit V430-AF5</p> 	
<p>After</p>	<p>Front Window Installation Kit V430-AF10 Diffuser Installation Kit V430-AF11 Polarizer Installation Kit V430-AF12 YAG Filter Installation Kit V430-AF4 ESD-Safe Window Installation Kit V430-AF5</p> 	

“ Code Reader GROUP CATALOG ” < Catalog number Q263-E1-03 > page 7

<p>Before</p>	<p>Code Reader</p>	<table border="1"> <thead> <tr> <th>Old model</th> <th>New model</th> </tr> </thead> <tbody> <tr> <td>V430-F000W50C</td> <td>V430-F000W50C-SRX</td> </tr> <tr> <td>V430-F000M50C</td> <td>V430-F000M50C-SRX</td> </tr> <tr> <td>V430-F000W12M</td> <td>V430-F000W12M-SRX</td> </tr> <tr> <td>V430-F000M12M</td> <td>V430-F000M12M-SRX</td> </tr> <tr> <td>V430-F000N12M</td> <td>V430-F000N12M-SRX</td> </tr> <tr> <td>V430-F050M03M</td> <td>V430-F050M03M-SRX</td> </tr> <tr> <td>V430-F081M03M</td> <td>V430-F081M03M-SRX</td> </tr> <tr> <td>V430-F102M03M</td> <td>V430-F102M03M-SRX</td> </tr> </tbody> </table>	Old model	New model	V430-F000W50C	V430-F000W50C-SRX	V430-F000M50C	V430-F000M50C-SRX	V430-F000W12M	V430-F000W12M-SRX	V430-F000M12M	V430-F000M12M-SRX	V430-F000N12M	V430-F000N12M-SRX	V430-F050M03M	V430-F050M03M-SRX	V430-F081M03M	V430-F081M03M-SRX	V430-F102M03M	V430-F102M03M-SRX	
Old model	New model																				
V430-F000W50C	V430-F000W50C-SRX																				
V430-F000M50C	V430-F000M50C-SRX																				
V430-F000W12M	V430-F000W12M-SRX																				
V430-F000M12M	V430-F000M12M-SRX																				
V430-F000N12M	V430-F000N12M-SRX																				
V430-F050M03M	V430-F050M03M-SRX																				
V430-F081M03M	V430-F081M03M-SRX																				
V430-F102M03M	V430-F102M03M-SRX																				
<p>After</p>	<p>Code Reader</p>	<table border="1"> <thead> <tr> <th>Old model</th> <th>New model</th> </tr> </thead> <tbody> <tr> <td>V430-F000W50C</td> <td>V430-F000W50C-SWX</td> </tr> <tr> <td>V430-F000M50C</td> <td>V430-F000M50C-SWX</td> </tr> <tr> <td>V430-F000W12M</td> <td>V430-F000W12M-SRX</td> </tr> <tr> <td>V430-F000M12M</td> <td>V430-F000M12M-SRX</td> </tr> <tr> <td>V430-F000N12M</td> <td>V430-F000N12M-SRX</td> </tr> <tr> <td>V430-F050M03M</td> <td>V430-F050M03M-SRX</td> </tr> <tr> <td>V430-F081M03M</td> <td>V430-F081M03M-SRX</td> </tr> <tr> <td>V430-F102M03M</td> <td>V430-F102M03M-SRX</td> </tr> </tbody> </table>	Old model	New model	V430-F000W50C	V430-F000W50C-SWX	V430-F000M50C	V430-F000M50C-SWX	V430-F000W12M	V430-F000W12M-SRX	V430-F000M12M	V430-F000M12M-SRX	V430-F000N12M	V430-F000N12M-SRX	V430-F050M03M	V430-F050M03M-SRX	V430-F081M03M	V430-F081M03M-SRX	V430-F102M03M	V430-F102M03M-SRX	
Old model	New model																				
V430-F000W50C	V430-F000W50C-SWX																				
V430-F000M50C	V430-F000M50C-SWX																				
V430-F000W12M	V430-F000W12M-SRX																				
V430-F000M12M	V430-F000M12M-SRX																				
V430-F000N12M	V430-F000N12M-SRX																				
V430-F050M03M	V430-F050M03M-SRX																				
V430-F081M03M	V430-F081M03M-SRX																				
V430-F102M03M	V430-F102M03M-SRX																				

“ Code Reader GROUP CATALOG ” < Catalog number Q263-E1-03 > page 11

Before	Type	Model
	Front Window Installation Kit	V430-AF0
	Diffuser Installation Kit	V430-AF1
	Polarizer Installation Kit	V430-AF2

After	Type	Model
	Front Window Installation Kit	V430-AF10*1
	Diffuser Installation Kit	V430-AF11*1
	Polarizer Installation Kit	V430-AF12*1

*1. The accessories V430-AF10, V430-AF11, and V430-AF12 are shown in relation to MicroHAWK V4□□-F□□□□□□□□-□□□ code readers in this datasheet. Previous-generation MicroHAWK V4X0-F□□□□□□□□ code readers are compatible with accessory part numbers V430-AF0, V430-AF1, and V430-AF2. Please select the correct accessory from the table based on your code reader part number format.

Accessory	Prior Code Reader V430-F□□□□□□□□-□□□	New Code Reader V430-F□□□□□□□□
Front Window Installation Kit	V430-AF10	V430-AF0
Diffuser Installation Kit	V430-AF11	V430-AF1
Polarizer Installation Kit	V430-AF12	V430-AF2

“ MicroHAWK V320-F/V330-F/V420-F/V430-F Barcode Reader USER'S MANUAL ”

< Manual number Z432-E-01 > page A-24, A-33, R-7

“ MicroHAWK F320-F/F330-F/F420-F/F430-F Smart Camera USER'S MANUAL ”

< Manual number Z433-E-03 > page 2-14

Updated accessory part numbers.

Before	Front Window - Installation Kit	V430-AF0
	Diffuser – Installation Kit	V430-AF1
	Polarizer – Installation Kit	V430-AF2
After	Front Window - Installation Kit	V430-AF10
	Diffuser – Installation Kit	V430-AF11
	Polarizer – Installation Kit	V430-AF12

Specifications in this product news are as of the issue date and are subject to change without notice. Only main changes in specifications are described in this document. Please be sure to read the relevant catalogs, datasheets, product specifications, instructions, and manuals for precautions and necessary information when using products.