

当社発行のカタログにおいて下記のとおり印刷・記載の誤りがありました。  
お詫び申し上げます。

カタログ名

「押ボタンスイッチ/サムロータリスイッチ 総合カタログ '99」( '98年10月発行) カタログ番号 : SGFS-305

掲載場所/正誤内容 40ページ

誤					➔	正											
使用電圧	形式	標準価格( ¥ )	口操作部の色記号( 色 )		使用電圧	形式											
DC6V	形A22W-2M -6D-10	1,800			DC6V	形A22W-2M -6D-10	A22W-2M										
AC6V	形A22W-2M -6A-10				AC6V	形A22W-2M -6A-10											
AC/DC12V	形A22W-2M -12A-10				AC/DC12V	形A22W-2M -12A-10											
AC/DC24V	形A22W-2M -24A-10				AC/DC24V	形A22W-2M -24A-10											
DC6V	形A22W-2M -6D-01				DC6V	形A22W-2M -6D-01											
AC6V	形A22W-2M -6A-01				AC6V	形A22W-2M -6A-01											
AC/DC12V	形A22W-2M -12A-01				AC/DC12V	形A22W-2M -12A-01											
AC/DC24V	形A22W-2M -24A-01				AC/DC24V	形A22W-2M -24A-01											
DC6V	形A22W-2M -6D-11				DC6V	形A22W-2M -6D-11											
AC6V	形A22W-2M -6A-11				AC6V	形A22W-2M -6A-11											
AC/DC12V	形A22W-2M -12A-11				AC/DC12V	形A22W-2M -12A-11											
AC/DC24V	形A22W-2M -24A-11				AC/DC24V	形A22W-2M -24A-11											
DC6V	形A22W-2M -6D-20	2,030			DC6V	形A22W-2M -6D-20	A22W-2M										
AC6V	形A22W-2M -6A-20				AC6V	形A22W-2M -6A-20											
AC/DC12V	形A22W-2M -12A-20				AC/DC12V	形A22W-2M -12A-20											
AC/DC24V	形A22W-2M -24A-20				AC/DC24V	形A22W-2M -24A-20											
DC6V	形A22W-2M -6D-02				DC6V	形A22W-2M -6D-02											
AC6V	形A22W-2M -6A-02				AC6V	形A22W-2M -6A-02											
AC/DC12V	形A22W-2M -12A-02				AC/DC12V	形A22W-2M -12A-02											
AC/DC24V	形A22W-2M -24A-02				AC/DC24V	形A22W-2M -24A-02											
DC6V	形A22W-2M -6D-10				1,800							DC6V	形A22W-2A -6D-10	A22W-2A			
AC6V	形A22W-2M -6A-10											AC6V	形A22W-2A -6A-10				
AC/DC12V	形A22W-2M -12A-10											AC/DC12V	形A22W-2A -12A-10				
AC/DC24V	形A22W-2M -24A-10											AC/DC24V	形A22W-2A -24A-10				
DC6V	形A22W-2M -6D-01	DC6V	形A22W-2A -6D-01														
AC6V	形A22W-2M -6A-01	AC6V	形A22W-2A -6A-01														
AC/DC12V	形A22W-2M -12A-01	AC/DC12V	形A22W-2A -12A-01														
AC/DC24V	形A22W-2M -24A-01	AC/DC24V	形A22W-2A -24A-01														
DC6V	形A22W-2M -6D-11	DC6V	形A22W-2A -6D-11														
AC6V	形A22W-2M -6A-11	AC6V	形A22W-2A -6A-11														
AC/DC12V	形A22W-2M -12A-11	AC/DC12V	形A22W-2A -12A-11														
AC/DC24V	形A22W-2M -24A-11	AC/DC24V	形A22W-2A -24A-11														
DC6V	形A22W-2M -6D-20	2,030	R( 赤 ) Y( 黄 ) G( 緑 ) A( 青 )*		DC6V	形A22W-2A -6D-20	A22W-2A										
AC6V	形A22W-2M -6A-20				AC6V	形A22W-2A -6A-20											
AC/DC12V	形A22W-2M -12A-20				AC/DC12V	形A22W-2A -12A-20											
AC/DC24V	形A22W-2M -24A-20				AC/DC24V	形A22W-2A -24A-20											
DC6V	形A22W-2M -6D-02				DC6V	形A22W-2A -6D-02											
AC6V	形A22W-2M -6A-02				AC6V	形A22W-2A -6A-02											
AC/DC12V	形A22W-2M -12A-02				AC/DC12V	形A22W-2A -12A-02											
AC/DC24V	形A22W-2M -24A-02				AC/DC24V	形A22W-2A -24A-02											
DC6V	形A22W-2M -6D-11				2,030							DC6V	形A22W-3M -6D-11	A22W-3M			
AC6V	形A22W-2M -6A-11											AC6V	形A22W-3M -6A-11				
AC/DC12V	形A22W-2M -12A-11											AC/DC12V	形A22W-3M -12A-11				
AC/DC24V	形A22W-2M -24A-11											AC/DC24V	形A22W-3M -24A-11				
DC6V	形A22W-2M -6D-20	DC6V	形A22W-3M -6D-20														
AC6V	形A22W-2M -6A-20	AC6V	形A22W-3M -6A-20														
AC/DC12V	形A22W-2M -12A-20	AC/DC12V	形A22W-3M -12A-20														
AC/DC24V	形A22W-2M -24A-20	AC/DC24V	形A22W-3M -24A-20														
DC6V	形A22W-2M -6D-02	DC6V	形A22W-3M -6D-02														
AC6V	形A22W-2M -6A-02	AC6V	形A22W-3M -6A-02														
AC/DC12V	形A22W-2M -12A-02	AC/DC12V	形A22W-3M -12A-02														
AC/DC24V	形A22W-2M -24A-02	AC/DC24V	形A22W-3M -24A-02														
DC6V	形A22W-2A -6D-11	2,030			DC6V	形A22W-3A -6D-11	A22W-3A										
AC6V	形A22W-2A -6A-11				AC6V	形A22W-3A -6A-11											
AC/DC12V	形A22W-2A -12A-11				AC/DC12V	形A22W-3A -12A-11											
AC/DC24V	形A22W-2A -24A-11				AC/DC24V	形A22W-3A -24A-11											
DC6V	形A22W-2A -6D-20				DC6V	形A22W-3A -6D-20											
AC6V	形A22W-2A -6A-20				AC6V	形A22W-3A -6A-20											
AC/DC12V	形A22W-2A -12A-20				AC/DC12V	形A22W-3A -12A-20											
AC/DC24V	形A22W-2A -24A-20				AC/DC24V	形A22W-3A -24A-20											
DC6V	形A22W-2A -6D-02				DC6V	形A22W-3A -6D-02											
AC6V	形A22W-2A -6A-02				AC6V	形A22W-3A -6A-02											
AC/DC12V	形A22W-2A -12A-02				AC/DC12V	形A22W-3A -12A-02											
AC/DC24V	形A22W-2A -24A-02				AC/DC24V	形A22W-3A -24A-02											

対応方法

・12月7日以降オムロンのカタログセンターより出荷されたものについては、訂正済みです。