

モータ・リレー

K2CM-Q1L

No Image Available

商品概要

Motor Relay, Instantaneous type, Current range: 8 to 26 A, Manual reset, Current reverse-phase detection, Control power supply voltage: $100/110/120 \, \text{V}$

販売状況 2025/12/05 00:00 情報更新

| 販売状況 | 販売中 |
|----------|----------|
| 機種区分 | 標準在庫機種 |
| 標準価格(税別) | ¥ 18,700 |

推奨代替品の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「生産終了品/推奨代替品」をご覧ください。 在庫状況/標準価格の最新情報につきましては、当社Webサイト(www.fa.omron.co.jp)の「在庫状況/標準価格 照会」をご覧ください。

情報更新: 2025/09/25

詳細情報

Specifications

Ratings

| Contact form | SPST-NO SPST-NC | | |
|------------------------------------|--|---|--|
| Rated load | NO contact: 2 A at 120 VAC, 1 A at 240 VAC, 0.5 A at 440 VAC, 0.2 A at 110 VDC, 0.1 A at 220 VDC NC contact: 5 A at 120 VAC, 2 A at 240 VAC, 1 A at 440 VAC, 0.2 A at 110 VDC, 0.1 A at 220 VDC | | |
| Contact capacity class | Contact capacity class | | |
| Mortor circuit | Rated voltage | 500 VAC max. Three-phase | |
| | Rated current | 8 to 26 A Three-phase | |
| Control power supply circuit | Rated voltage | 100/110/120 VAC | |
| | Allowable voltage variable range | 85% to 110% of rated voltage (Phase-loss element: Operate normally at 50% of rated operating voltage) | |
| Frequency | | 50/60 Hz | |
| Allowable-frequency variable range | ±5% of rated frequency | | |
| Power consumption | at operating state (50 Hz): 5 VA at standby state (50 Hz): 3 VA | | |
| Current set range | | 8 to 26 A AC | |

Performance

| Overcurrent function | Operating value | 115% of current setting value | |
|----------------------|---|---|--|
| | Operating value (Start-up lock) | 30% max. of the current setting value. | |
| | Operating time characteristic | Start-up lock, Momentary operating | |
| | Operating time | when current is increased from 100 to 140% of the set current value: 0.5 s max. | |
| | Setting accuracy of operating value | $\pm 10\%$ of current setting value | |
| | Overcurrent SV accuracy (Start-up lock) | ±20% of maximum setting value (at 140% overload) | |
| Open-phase | Operating value | 85% max. of the current setting value. (at open- phase) | |
| | Operating time | 2 s max. Note: at open-phase | |
| | Operating asymmetry rate | High sensitivity (H): 35±10% Low sensitivity (L): 65±10% | |

| Reverse-phase | Operating value | 50% max. of the current setting value. | |
|--|---|--|--|
| | Operating time | 1 s max. | |
| Overload capacity | Mortor circuit | 20 times the current SV for 2 s, applied twice with a 1 min interval. | |
| | Control power supply circuit | 1.15 times the rated control voltage for 3 h. | |
| Influence of temperature | | 0 to 20 to 40 °C: Operating value: ±5%, Operating time: ±10% (overload) 0 to 20 to 40 °C: Operating value: ±10%, Operating time: ±10% (phase-loss/reverse-phase) -10 to 0 °C, 40 to 50 °C: Operating value: ±10%, Operating time: ±20% (overload) -10 to 0 °C, 40 to 50 °C: Operating value: ±20%, Operating time: ±20% (phase-loss/reverse-phase) | |
| Influence of voltage | | 85 to 100 to 110%: Operating value: \pm 5%, Operating time: \pm 10% | |
| Influence of frequency | | Operating value: ±5%, Operating time: ±10% (overload/phase-loss/reverse-phase) 95 to 100 to 105% | |
| Infection of current waveform distortion | | No malfunction occurs when pulse containing 100% of the 2nd to 9th harmonics is applied (openphase switch set to Low). | |
| Endurance | | 10,000 operations min. | |
| Tese botton operation | Tese botton operation | | |
| Insulation resistance | | Between current-carrying terminal and mounting panel: $10~\text{M}\Omega$ min. Between current-carrying terminals: $5~\text{M}\Omega$ min. Between contact of same pole: $5~\text{M}\Omega$ min. | |
| Dielectric strength | | Between current-carrying terminal and mounting panel: 2,500 VAC for 1 min Between current-carrying terminals: 2,500 VAC for 1 min Between contact of same pole: 1,000 VAC for 1 min | |
| Impulse withstand voltage | | 1.2/50 µs wave form (JEC 212) Between current-carrying terminal and mounting panel: 6,000 V Between current-carrying terminals: 4,500 V Between control power supply terminals: 4,500 V | |
| Ambient temperature (Operating) | | -10 to 60 °C | |
| Ambient temperature (Storage) | -25 to 65 °C | | |
| Ambient humidity (Operating) | 35 to 85 % | | |
| Vibration resistance | Destruction: 10 to 25 Hz, 2 mm double amplitude, 2 h each in X, Y and Z directions. Malfunction: 10 to 55 Hz, 0.3 mm double amplitude, 10 min each in X, Y and Z directions. | | |
| Shock resistance | | Destruction: 294 m/s ² , 3 times each in X, Y and Z directions Malfunction: 98 m/s ² , 3 times each in X, Y and Z directions | |

| Dimensions | Width | 126 mm | |
|-----------------|--|--------|--|
| | Height | 60 mm | |
| | Depth | 120 mm | |
| | Primary side electric(al) wire through hole diameter | 20 mm | |
| Weight | Арргох. 800 g | | |
| Mounting method | Screw mounting | | |
| Case color | Munsell 5Y7/1 | | |

RoHS/REACH対応状況

情報更新: 2025/12/03

EU RoHS

| 対応状況 ※1 | 対応予定月 ※2 | 非含有証明書 ※3 |
|---------------|----------|------------|
| ® 対応済み | | ダウンロードはこちら |

中国 RoHS

| 中国 RoHS表 ※ 1 ※ 2 | | | | | | | | | | |
|--------------------------------|----|----|--------|------|-----------|-----|------|-----|----------|----------------------|
| Pb | Hg | Cd | Cr(VI) | PBBs | PBDE s | DBP | DIBP | BBP | DEH P | 環境 保護 使用 期限 |
| Х | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 10 |

- ・"対応済み"や非含有の記載がされた商品であっても、流通在庫等で未対応品が混在する可能性があります。
- ・非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

この製品のRoHS/REACH対応状況ページへ >

注意事項 • 凡例

"対応済み"で記載される商品であっても、流通在庫等で未対応品が混在する可能性があります。 非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

※1 対応状況

・ 📵 対応済み :EU RoHS指令(10物質)の非含有に対応した製品が提供可能な商品です。

対応予定 : EU RoHS指令 (10物質) の非含有に対応した製品に切り替える予定のある商品です。
 対応予定なし : EU RoHS指令 (10物質) の非含有に非対応の商品で、対応品を出す予定はありません。
 調査・確認中 : EU RoHS指令 (10物質) の非含有の対応状況を調査中または確認中の商品です。

・非該当品:ライセンス料など無形物で、有害物質有無と関係のない商品です。

仕入先様の事情により、非含有部品としていたものが、含有品と判明した場合などやむを得ず変更することがあります。

* EU RoHS指令(10物質):

鉛(Pb) 1000ppm以下、水銀(Hg) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、ポリ臭化ビフェニル類(PBB) 1000ppm以下、ポリ臭化ジフェニルエーテル類(PBDE) 1000ppm以下、フタル酸ビス(2-エチルヘキシル) (DEHP)(別名:DOP) 1000ppm以下、フタル酸ブチルベンジル (BBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ンプチル (DBP) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、プタル酸ブチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、カルマンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチルベンジル (BBP) 1000ppm以下、フタル酸ンプチル (DBP) 1000ppm以下、フタル酸シスタル酸シスタル酸シスタル酸シスタル酸シスタル (DBP) 1000ppm以下、フタル酸シスタル (DBP) 1000ppm以下、DBP (DBP) 1000ppm以下、D

※2 対応予定月

部品在庫の切り替え状況などにより、予定月が前後することがあります。

※3 非含有証明書ダウンロード

下記の非含有証明書をダウンロードすることができます。

- ・EU RoHS指令(10物質)の非含有証明書
- ・49物質の非含有証明書(当社基準)
- ※本証明書は発行日時点で非含有を証明するもので、過去に遡って非含有を証明するものではありません。

また、RoHS指令のフタル酸エステル類 4 物質の対応では、対応完了までの期間は出荷製品に未対応品が混在することから備考欄に対応日を記載しておりました。

既に当社にて対応品への在庫切替を完了していることから、特段のことがない限り、2022年1月12日より割愛しております。

規格認証/適合状況

| UL認証 | CSA認証 | CEマーキング適合 | CCC認証 |
|------|-------|-----------|-------|
| No | No | No | No |

| LR型式承認 | DNV型式承認 | BV型式承認 | KR型式承認 | NK型式承認 | ABS型式承認 |
|--------|---------|--------|--------|--------|---------|
| (イギリス | (ノルウェー | (フランス | (韓国 | (日本 | (アメリカ |
| 船舶規格) | 船舶規格) | 船舶規格) | 船舶規格) | 船舶規格) | 船舶規格) |
| No | No | No | No | No | No |

この製品の規格認証/適合状況ページへ > その他の認証はこちらのページからご検索ください >