

スイッチング・パワーサプライ(15/30/60/90/120/180/240/480Wタイプ)

# S8VS-12024BP-F



## 商品概要

Switch Mode Power Supply, Capacity 120 W, Output voltage 24 V, with Indication Monitor, Total Run Time Monitor, Sourcing, Screwless terminal block

## 販売状況

2026/03/04 00:00 情報更新

|          |          |
|----------|----------|
| 販売状況     | 販売中      |
| 機種区分     | 受注生産機種   |
| 標準価格(税別) | ¥ 21,000 |

推奨代替品の最新情報につきましては、当社Webサイト([www.fa.omron.co.jp](http://www.fa.omron.co.jp))の「生産終了品/推奨代替品」をご覧ください。  
在庫状況/標準価格の最新情報につきましては、当社Webサイト([www.fa.omron.co.jp](http://www.fa.omron.co.jp))の「在庫状況/標準価格照会」をご覧ください。

# 詳細情報

## Specifications

情報更新：2025/11/04

|                      |   |   |
|----------------------|---|---|
| Power rating         |   | 120 W   |
| Output voltage       |   | 24 VDC  |
| Efficiency           |   | 83 % typ. (at 100 VAC input)<br>85 % typ. (at 200 VAC input)                            |
| Input                | Rated input voltage                     | 100 to 240 VAC  |
|                      | Allowable input voltage variable range  | 85 to 264 VAC<br>80 to 370 VDC  |
|                      | Frequency                               | 50/60Hz (47 to 63 Hz)   |
|                      | Rated input current                     | 1.9 A max., 1.5 A typ. (at 100 VAC input)<br>1.1 A max., 0.72 A typ. (at 200 VAC input) |
|                      | Power factor                            | 0.9 min.  |
|                      | Leakage current                         | 0.5 mA max. (at 100 VAC input)<br>1.0 mA max. (at 200 VAC input)                        |
|                      | Inrush current (cold start at 25 °C)    | 17.5 A max., 14 A typ. (at 100 VAC input)<br>35 A max., 28 A typ. (at 200 VAC input)    |
| Output               | Rated output current                    | 5 A   |
|                      | Output voltage variable range           | -10 to +15 % With V.ADJ   |
|                      | Ripple                                  | 130 mV max. (at rated input and output)   |
|                      | Static input variation influence        | 0.5 % max. (at 100% load)   |
|                      | Static load variation influence         | 1.5 % max. (at rated input, 0 to 100% load)   |
|                      | Ambient temperature variation influence | 0.05 %/°C max.  |
|                      | Start up time                           | 650 ms typ. (at 100 VAC input)<br>520 ms typ. (at 200 VAC input)                        |
|                      | Hold time                               | 56 ms typ. (at 100 VAC input)<br>56 ms typ. (at 200 VAC input)                          |
| Additional functions | Overload protection                     | Yes, automatic reset  |
|                      | Overvoltage protection                  | Yes, Shut off the input voltage and turn on the input again                             |
|                      | Series operation                        | Yes (Up to 2 Power Supplies with external diode)  |
|                      | Parallel operation                      | No (However, backup operation is possible, external diodes required.)                   |
|                      | Output indicator                        | Yes (color: green)  |



|              |                                 |  |
|--------------|---------------------------------|--|
|              | Output voltage indication       | Yes (switching)  |
|              | Output current indication       | Yes (switching)  |
|              | Peak-hold current indication    | Yes (switching)  |
|              | Total run time monitor          | Output: Yes (Transistor output, 30 VDC max., 50 mA max)<br>Indication: Yes (switching)   |
|              | Undervoltage alarm              | Output: Yes (Transistor output, 30 VDC max., 50 mA max)<br>Indication: Yes (switching)   |
| Insulation   | Dielectric strength             | Between all input terminals and PE terminals: 2 kVAC for 1 min, Detection current: 20 mA<br>Between all input terminals and all output terminals/alarm outputs: 3 kVAC for 1 min, Detection current: 20 mA<br>Between all output terminals/alarm outputs and all PE terminals: 1 kVAC for 1 min, Detection current: 20 mA<br>Between all output terminals and all alarm outputs: 500 VAC for 1 min, Detection current: 20 mA |
|              | Insulation resistance           | Between all output terminals/alarm outputs and all input terminals/PE terminals: 100 MΩ min., at 500 VDC   |
| Environment  | Vibration resistance            | 10 to 55 Hz, 0.375 mm single amplitude in each 3 directions for 2 hours  |
|              | Shock resistance                | 150 m/s <sup>2</sup> , in each 6 directions 3 times  |
|              | Ambient temperature (Operating) | -10 to 60 °C   |
|              | Ambient temperature (Storage)   | -25 to 65 °C   |
|              | Ambient humidity (Operating)    | 25 to 85 %   |
|              | Ambient humidity (Storage)      | 25 to 90 %   |
| Reliability  | Life expectancy                 | 10 years (at rated input, a load rate of 50% load, under the temperature of 40 °C, standard mounting)  |
| Construction | Construction                    | Covered type   |
|              | Connection                      | Terminal blocks  |
|              | Terminal type                   | Screwless terminal   |
|              | Mounting                        | DIN track mounting   |
|              | Attachment                      | Terminal block cover   |
|              | Weight (Main)                   | 550 g max.   |

## Note

Do not use the Inverter output for the Power Supply. Inverters with an output frequency of 50/60 Hz are available, but the rise in the internal temperature of the Power Supply may result in ignition or burning.

# Dimension

情報更新：2025/11/04




# Connection diagram

情報更新：2025/11/04

## Block diagram

- S8VS-12024A**□-□ (120 W)
- S8VS-12024B**□-□ (120 W)
- S8VS-12024BE**□-□ (120 W)

- Sinking type  
(S8VS-12024A-□, S8VS-12024B-□)
- Sourcing type  
(S8VS-12024AP-□ S8VS-12024BP-□)




## Derating curve

情報更新：2025/11/04

# (60-W, 90-W, 120-W, 180-W, 240-W, and 480-W Models)

## Derating Curve



- Note: 1.** Using side mounting bracket for right-side mounting (excluding 240-W models).
- 2.** Internal parts may occasionally deteriorate or be damaged. Do not use the Power Supply in areas outside the derating curve (i.e., the area shown by shading ① in the above graph).
- 3.** If there is a derating problem, use forced air-cooling.
- 4.** When using a 480-W model at an input voltage of 95 VAC or less, derate the load by at least 80%.

## RoHS/REACH対応状況

情報更新：2026/3/04

### EU RoHS

| 対応状況 ※1  | 対応予定月 ※2 | 非含有証明書 ※3                  |
|--|----------|----------------------------|
|  対応済み |          | <a href="#">ダウンロードはこちら</a> |

### 中国 RoHS

| 中国 RoHS表 ※1※2 |    |    |        |      |       |     |      |     |      |              |
|---------------|----|----|--------|------|-------|-----|------|-----|------|--------------|
| Pb            | Hg | Cd | Cr(VI) | PBBs | PBDEs | DBP | DIBP | BBP | DEHP | 環境保護<br>使用期限 |
| X             | 0  | 0  | 0      | 0    | 0     | 0   | 0    | 0   | 0    | 10           |

- ・“対応済み”や非含有の記載がされた商品であっても、流通在庫等で未対応品が混在する可能性があります。
- ・非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

[この製品のRoHS/REACH対応状況ページへ>](#)

## 注意事項・凡例

”対応済み”で記載される商品であっても、流通在庫等で未対応品が混在する可能性があります。  
非含有品が必要な際は、弊社営業部門もしくは販売店へお問い合わせください。

### ※1 対応状況

- ・  対応済み : EU RoHS指令（10物質）の非含有に対応した製品が提供可能な商品です。
- ・ 対応予定 : EU RoHS指令（10物質）の非含有に対応した製品に切り替える予定のある商品です。
- ・ 対応予定なし : EU RoHS指令（10物質）の非含有に非対応の商品で、対応品を出す予定はありません。
- ・ 調査・確認中 : EU RoHS指令（10物質）の非含有の対応状況を調査中または確認中の商品です。
- ・ 非該当品 : ライセンス料など無形物で、有害物質有無と関係のない商品です。

仕入先様の事情により、非含有部品としていたものが、含有品と判明した場合などやむを得ず変更することがあります。

\* EU RoHS指令（10物質）：

鉛(Pb) 1000ppm以下、水銀(Hg) 1000ppm以下、カドミウム(Cd) 100ppm以下、六価クロム(Cr(VI)) 1000ppm以下、  
ポリ臭化ビフェニル類(PBB) 1000ppm以下、ポリ臭化ジフェニルエーテル類(PBDE) 1000ppm以下、  
フタル酸ビス(2-エチルヘキシル) (DEHP)(別名：DOP) 1000ppm以下、フタル酸ブチルベンジル (BBP) 1000ppm以下、  
フタル酸ジブチル (DBP) 1000ppm以下、フタル酸ジイソブチル (DIBP) 1000ppm以下  
但し、RoHS指令で産業用監視および制御機器に対する適用除外項目は除く。  
フタル酸エステル類の4物質については閾値を超える意図的な使用がないことを確認しています。

### ※2 対応予定月

部品在庫の切り替え状況などにより、予定月が前後することがあります。

### ※3 非含有証明書ダウンロード

下記の非含有証明書をダウンロードすることができます。

- ・ EU RoHS指令（10物質）の非含有証明書
- ・ 49物質の非含有証明書（当社基準）

※ 本証明書は発行日時時点で非含有を証明するもので、過去に遡って非含有を証明するものではありません。

また、RoHS指令のフタル酸エステル類4物質の対応では、対応完了までの期間は出荷製品に未対応品が混在することから備考欄に  
対応日を記載しておりました。

既に当社にて対応品への在庫切替を完了していることから、特段のことがない限り、2022年1月12日より割愛しております。

## 規格認証/適合状況

| UL認証 | CSA認証 | CEマーキング適合 | CCC認証 |
|------|-------|-----------|-------|
| Yes  | Yes   | Yes       | N/A   |

| LR型式承認<br>(イギリス<br>船舶規格) | DNV型式承認<br>(ノルウェー<br>船舶規格) | BV型式承認<br>(フランス<br>船舶規格) | KR型式承認<br>(韓国<br>船舶規格) | NK型式承認<br>(日本<br>船舶規格) | ABS型式承認<br>(アメリカ<br>船舶規格) |
|--------------------------|----------------------------|--------------------------|------------------------|------------------------|---------------------------|
| No                       | No                         | No                       | No                     | No                     | No                        |

[この製品の規格認証/適合状況ページへ>](#)  
[その他の認証はこちらのページからご検索ください>](#)